

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333022-840

Luminaire Tested: **S124RDIW-S350D770U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333022-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4133.9 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75		58	58	58		42	42	42	35
1	95	90	87	83	85	82	79	76	66	64	62		51	50	49		38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51		45	43	41		33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43		40	37	35		30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37		36	32	30		27	24	23	19
5	66	55	47	41	60	50	43	38	41	36	32		32	29	26		24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28		29	25	23		22	19	18	14
7	56	44	37	31	51	41	34	29	33	28	24		26	23	20		20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22		24	20	18		18	16	14	12
9	48	37	29	25	44	34	27	23	28	23	19		22	19	16		17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17		20	17	14		16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	1.4
10°-20°	163.5	4.0
20°-30°	236.1	5.7
30°-40°	267.7	6.5
40°-50°	258.5	6.3
50°-60°	214.9	5.2
60°-70°	148.4	3.6
70°-80°	75.2	1.8
80°-90°	22.2	0.5
90°-100°	63.9	1.5
100°-110°	189.3	4.6
110°-120°	321.4	7.8
120°-130°	423.8	10.3
130°-140°	475.9	11.5
140°-150°	467.7	11.3
150°-160°	393.4	9.5
160°-170°	261.7	6.3
170°-180°	91.6	2.2
0°-30°	458.3	11.1
0°-40°	726.0	17.6
0°-60°	1199.4	29.0
0°-90°	1445.2	35.0
90°-120°	574.6	13.9
90°-150°	1942.0	47.0
90°-180°	2689.0	65.0
0°-180°	4133.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	2	10	16	21	22	4
95°	45	52	57	59	59	50
105°	175	176	178	181	183	185
115°	327	327	325	325	324	322
125°	476	476	475	474	472	424
135°	614	618	618	617	615	475
145°	746	749	750	749	746	467
155°	854	854	854	856	854	393
165°	930	928	926	930	928	262
175°	968	964	963	968	963	92
180°	969	969	969	969	969	



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.3	8.9	8.6	8.3	8.0	7.9	8.1	8.3	8.5	8.7	8.8
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	16.1	18.2	20.2	22.3	24.4	26.0	26.9	27.8	28.8	29.7	30.3
95°	44.9	46.5	48.0	49.5	51.0	52.3	53.4	54.6	55.8	57.0	57.5
97.5°	78.6	79.8	81.0	82.1	83.3	84.6	86.0	87.4	88.8	90.1	90.7
100°	104.9	105.6	106.2	106.9	107.6	108.7	110.2	111.7	113.2	114.7	115.0
102.5°	132.5	132.8	133.0	133.3	133.6	134.4	135.7	137.1	138.5	139.9	140.4
105°	174.6	174.8	175.0	175.1	175.3	175.7	176.4	177.0	177.7	178.3	178.8
107.5°	218.8	219.0	219.2	219.4	219.6	219.8	219.9	220.0	220.2	220.3	220.7
110°	248.8	249.1	249.5	249.8	250.1	250.2	250.0	249.9	249.7	249.5	249.2



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.0	280.0	280.1	280.2	280.2	280.1	279.8	279.5	279.2	278.9	278.9
115°	326.8	326.8	326.8	326.8	326.8	326.6	326.3	326.0	325.6	325.3	325.1
117.5°	370.8	371.0	371.1	371.2	371.4	371.3	371.1	370.9	370.6	370.4	369.8
120°	400.2	400.9	401.5	402.2	402.9	402.9	402.5	402.0	401.5	401.0	400.1
122.5°	430.8	431.1	431.3	431.6	431.9	431.9	431.7	431.4	431.2	431.0	430.4
125°	475.9	475.9	475.9	475.9	475.9	475.8	475.6	475.5	475.3	475.1	474.8
127.5°	516.8	517.4	517.9	518.4	518.9	519.0	518.7	518.5	518.2	518.0	517.6
130°	545.6	546.1	546.6	547.1	547.6	547.9	547.9	547.9	547.9	547.9	547.5
132.5°	575.0	575.4	575.7	576.1	576.5	576.6	576.4	576.3	576.2	576.0	575.7
135°	613.9	614.8	615.8	616.8	617.8	618.3	618.3	618.3	618.3	618.3	618.0
137.5°	656.1	656.6	657.0	657.5	658.0	658.3	658.6	658.8	659.1	659.4	658.9
140°	684.3	684.6	685.0	685.3	685.6	685.8	685.8	685.8	685.8	685.8	685.6
142.5°	710.0	710.4	710.7	711.0	711.4	711.6	711.3	711.2	711.1	710.9	710.9
145°	745.8	746.4	747.1	747.8	748.4	748.8	749.0	749.2	749.3	749.5	749.3
147.5°	781.1	781.9	782.7	783.6	784.4	784.7	784.6	784.4	784.3	784.2	784.0
150°	802.7	803.3	804.1	804.8	805.4	805.8	805.8	805.8	805.8	805.8	805.8
152.5°	823.1	823.5	823.9	824.4	824.8	825.0	825.1	825.3	825.4	825.5	825.9
155°	854.4	854.4	854.4	854.4	854.4	854.3	854.1	854.0	853.8	853.7	854.3
157.5°	880.8	880.5	880.2	879.9	879.6	879.5	879.4	879.4	879.4	879.3	879.8
160°	896.5	896.3	896.1	896.0	895.8	895.5	895.4	895.2	895.0	894.9	895.4
162.5°	910.8	910.4	909.9	909.5	909.1	908.8	908.6	908.5	908.3	908.1	909.0
165°	930.2	929.7	929.2	928.7	928.2	927.8	927.4	927.1	926.8	926.3	927.4
167.5°	944.9	944.3	943.6	942.9	942.2	941.8	941.9	941.9	941.9	942.0	943.0
170°	953.4	952.5	951.7	950.9	950.1	949.7	949.9	950.1	950.2	950.4	951.4
172.5°	959.4	958.7	958.0	957.3	956.5	956.2	956.2	956.3	956.3	956.3	957.6
175°	967.7	966.7	965.9	965.1	964.3	963.8	963.6	963.4	963.3	963.1	964.3
177.5°	970.3	969.7	969.0	968.4	967.7	967.3	967.3	967.3	967.3	967.3	968.3
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	8.9	9.0	9.1	9.3	9.4	9.6	9.7	9.9
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	30.9	31.5	32.1	32.5	32.7	32.9	33.1	33.3
95°	58.0	58.5	59.0	59.2	59.2	59.2	59.2	59.2
97.5°	91.3	91.9	92.5	92.8	92.8	92.8	92.8	92.8
100°	115.3	115.6	116.0	116.1	116.1	116.1	116.1	116.1
102.5°	140.8	141.3	141.7	142.0	142.2	142.3	142.4	142.6
105°	179.4	179.9	180.4	180.9	181.4	181.9	182.4	182.9
107.5°	221.2	221.6	222.1	222.3	222.3	222.3	222.2	222.2
110°	248.9	248.6	248.2	248.3	248.8	249.3	249.8	250.3



TEST NUMBER: P333022-840

CATALOG NUMBER: S124RDIW-S350D770U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.8	278.7	278.7	278.7	278.8	278.9	279.0	279.1
115°	325.0	324.8	324.6	324.5	324.3	324.2	324.0	323.8
117.5°	369.3	368.7	368.1	367.7	367.4	367.0	366.7	366.4
120°	399.3	398.5	397.7	397.4	397.8	398.1	398.4	398.7
122.5°	429.8	429.3	428.7	428.1	427.5	426.9	426.4	425.8
125°	474.5	474.2	473.8	473.5	473.2	472.8	472.5	472.2
127.5°	517.3	516.9	516.5	516.2	516.0	515.7	515.4	515.2
130°	547.2	546.8	546.5	546.0	545.4	544.7	544.0	543.4
132.5°	575.4	575.1	574.7	574.4	574.2	573.9	573.6	573.4
135°	617.6	617.3	617.0	616.6	616.1	615.6	615.1	614.6
137.5°	658.5	658.1	657.7	657.5	657.6	657.7	657.8	657.9
140°	685.5	685.3	685.1	685.0	684.8	684.6	684.5	684.3
142.5°	710.9	710.8	710.8	710.8	710.7	710.7	710.7	710.6
145°	749.2	749.0	748.8	748.5	748.0	747.5	747.0	746.5
147.5°	783.9	783.8	783.6	783.5	783.3	783.2	782.9	782.7
150°	805.8	805.8	805.8	805.7	805.5	805.3	805.2	805.0
152.5°	826.3	826.7	827.1	827.1	826.7	826.3	825.8	825.4
155°	855.1	855.7	856.4	856.4	855.7	855.1	854.3	853.7
157.5°	880.3	880.8	881.3	881.3	880.7	880.2	879.6	879.0
160°	896.0	896.5	897.0	896.8	896.0	895.0	894.2	893.4
162.5°	909.9	910.8	911.7	911.7	910.9	910.1	909.3	908.4
165°	928.4	929.4	930.4	930.6	929.9	929.2	928.6	927.9
167.5°	944.0	944.9	945.9	945.9	944.9	943.9	942.9	941.8
170°	952.4	953.4	954.4	954.3	953.1	952.0	950.8	949.7
172.5°	958.7	959.8	960.9	960.9	959.7	958.6	957.4	956.2
175°	965.4	966.6	967.8	967.8	966.6	965.4	964.3	963.1
177.5°	969.2	970.1	971.1	971.0	969.9	968.9	967.8	966.7
180°	969.1	969.1	969.1	969.1	969.1	969.1	969.1	969.1

(END OF REPORT)