

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332750

Luminaire Tested: **S124DIW-S575D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332750
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D470U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4119.4 lumens
Efficiency: N/A
Efficacy: 136.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	84	77	72	85	78	73	68	69	64	61	59	56	54	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.2
10°-20°	257.7	6.3
20°-30°	379.3	9.2
30°-40°	440.9	10.7
40°-50°	440.9	10.7
50°-60°	385.7	9.4
60°-70°	286.4	7.0
70°-80°	162.7	4.0
80°-90°	48.7	1.2
90°-100°	38.6	0.9
100°-110°	114.5	2.8
110°-120°	194.3	4.7
120°-130°	256.2	6.2
130°-140°	287.7	7.0
140°-150°	282.7	6.9
150°-160°	237.8	5.8
160°-170°	158.2	3.8
170°-180°	55.4	1.3
0°-30°	728.4	17.7
0°-40°	1169.3	28.4
0°-60°	1996.0	48.5
0°-90°	2493.8	60.5
90°-120°	347.4	8.4
90°-150°	1174.1	28.5
90°-180°	1626.0	39.5
0°-180°	4119.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	1	6	10	13	14	4
95°	27	31	34	36	36	30
105°	106	106	108	109	111	112
115°	198	198	197	196	196	195
125°	288	288	287	286	286	256
135°	371	374	374	373	372	287
145°	451	453	453	453	451	282
155°	517	517	516	518	516	238
165°	562	561	560	563	561	158
175°	585	583	582	585	582	56
180°	586	586	586	586	586	



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.5	16.5	16.6	16.7	16.8	16.8	16.9	16.9	16.9	16.9	17.1
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	9.7	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3
95°	27.2	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7
97.5°	47.5	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8
100°	63.4	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5
102.5°	80.1	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8
105°	105.6	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1
107.5°	132.3	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4
110°	150.4	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.3	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6
115°	197.6	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6
117.5°	224.2	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6
120°	242.0	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9
122.5°	260.5	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2
125°	287.7	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1
127.5°	312.5	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9
130°	329.9	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0
132.5°	347.6	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1
135°	371.1	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6
137.5°	396.7	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4
140°	413.7	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5
142.5°	429.3	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8
145°	450.9	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	472.3	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0
150°	485.3	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.6	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3
155°	516.6	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5
157.5°	532.5	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9
160°	542.0	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4
162.5°	550.7	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6
165°	562.3	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7
167.5°	571.3	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1
170°	576.4	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2
172.5°	580.0	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9
175°	585.0	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0
177.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	17.2	17.3	17.4	17.5	17.5	17.6	17.6	17.7
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	18.7	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.0	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.2	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.7	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.1	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.5	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	133.7	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.5	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P332750

CATALOG NUMBER: S124DIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.5	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	223.3	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	241.4	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.9	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.9	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.7	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.8	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.9	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.4	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	398.1	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.4	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.9	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.9	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.6	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.2	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	541.7	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.1	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.3	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	570.7	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	575.8	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	579.6	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.0	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)