

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333051-840

Luminaire Tested: **S124RDIW-S575D1560U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333051-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D1560U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8769.4 lumens  
Efficiency: N/A  
Efficacy: 144.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	14	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.5	1.1
10°-20°	285.0	3.3
20°-30°	445.8	5.1
30°-40°	495.6	5.7
40°-50°	439.7	5.0
50°-60°	342.6	3.9
60°-70°	224.3	2.6
70°-80°	110.3	1.3
80°-90°	33.1	0.4
90°-100°	69.6	0.8
100°-110°	444.0	5.1
110°-120°	849.4	9.7
120°-130°	1078.3	12.3
130°-140°	1153.7	13.2
140°-150°	1078.8	12.3
150°-160°	870.0	9.9
160°-170°	561.1	6.4
170°-180°	193.4	2.2
0°-30°	825.3	9.4
0°-40°	1320.9	15.1
0°-60°	2103.3	24.0
0°-90°	2471.0	28.2
90°-120°	1363.1	15.5
90°-150°	4673.9	53.3
90°-180°	6298.0	71.8
0°-180°	8769.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	23
90°	46	4	46	4	46	20
95°	44	84	44	84	44	35
105°	434	458	434	458	434	379
115°	862	856	862	856	862	853
125°	1212	1203	1212	1203	1212	1080
135°	1503	1492	1503	1492	1503	1157
145°	1730	1721	1730	1721	1730	1081
155°	1885	1887	1885	1887	1885	869
165°	1981	1990	1981	1990	1981	560
175°	2024	2036	2024	2036	2024	193
180°	2036	2036	2036	2036	2036	



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	16.1	15.7	15.8	15.7	15.9	15.2	15.1	15.3	14.3	14.2	13.7
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4	34.3	32.3	29.6
95°	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6	35.5	33.5	33.1
97.5°	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6	40.4	40.2	78.0
100°	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5	61.3	67.1	113.7
102.5°	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7	260.7	322.9	328.9
105°	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2	478.2	475.1	473.4
107.5°	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4	593.9	592.4	590.1
110°	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0	672.3	671.6	669.5



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1	748.2	748.4	747.4
115°	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3	859.6	858.9	859.3
117.5°	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2	973.3	973.4	972.7
120°	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7	1042.0
122.5°	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0	1111.6	1111.2	1110.6
125°	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2	1207.2	1206.2	1206.8
127.5°	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8	1304.0	1304.2	1302.6
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2	1361.8	1361.5	1360.5
132.5°	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5	1419.1	1418.8	1417.4
135°	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3	1497.7	1497.0	1495.7
137.5°	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1	1573.3	1572.6	1571.0
140°	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9	1619.9	1618.8	1618.2
142.5°	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3	1663.4	1662.7	1662.3
145°	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2	1725.8	1725.5	1725.5
147.5°	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5	1780.3	1780.0	1780.3
150°	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3	1815.3	1815.3	1815.6
152.5°	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6	1845.1	1844.5	1845.1
155°	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5	1885.2	1883.8	1884.9
157.5°	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2	1919.5
160°	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2	1940.6
162.5°	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6	1960.5	1958.4	1958.8
165°	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2	1985.5	1982.9	1982.9
167.5°	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1	2004.1	2001.1	2001.4
170°	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7	2016.0	2013.3	2013.0
172.5°	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0	2023.3	2020.6	2020.2
175°	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6	2031.5	2028.5	2028.2
177.5°	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0	2035.9	2033.7	2033.2
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	13.1	12.3	12.4	11.7	11.3	11.8	12.0	11.6	11.4	11.2	11.0
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2	19.4	19.6	19.8
95°	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7	72.2	60.8	49.3
97.5°	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8	185.0	192.2	199.4
100°	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7	255.9	262.0	268.0
102.5°	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1	334.7	339.1	343.6
105°	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4	460.4	462.4	464.5
107.5°	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4	578.6	579.6	580.6
110°	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9	658.9	659.9	661.0





TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9	737.7	739.5	741.3
115°	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9	856.9	857.9	858.9
117.5°	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0	965.3	966.7	968.1
120°	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1	1038.4	1039.9	1041.2
122.5°	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3	1106.1	1106.9	1107.7
125°	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2	1204.5	1205.8	1207.2
127.5°	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7	1296.1	1296.4	1296.7
130°	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4	1355.7	1356.0	1356.5
132.5°	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2	1410.8	1411.5	1412.1
135°	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5	1492.1	1491.8	1491.5
137.5°	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3	1565.4	1565.5	1565.7
140°	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8	1613.5	1614.2	1614.8
142.5°	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4	1656.6	1657.9	1659.1
145°	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9	1721.9	1722.9	1723.9
147.5°	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0	1774.8	1776.8	1778.7
150°	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8	1812.1	1813.4	1814.8
152.5°	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4	1843.5	1844.6	1845.6
155°	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9	1887.2	1887.5	1887.9
157.5°	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4	1924.2	1924.0	1923.8
160°	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3	1945.3	1944.3	1943.3
162.5°	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8	1964.5	1963.2	1962.0
165°	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4	1988.7	1987.1	1985.4
167.5°	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9	2008.2	2006.4	2004.7
170°	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9	2018.9	2016.8	2014.8
172.5°	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2	2026.2	2024.2	2022.2
175°	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1	2034.1	2032.1	2030.0
177.5°	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8	2037.9	2036.0	2034.1
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	11.7	12.1	12.6	12.5	13.4	13.9	14.0	14.4	15.1	14.9	15.1
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4	38.4	40.4	41.5
95°	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6	39.6	41.6	42.8
97.5°	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6	40.8	41.0	41.3
100°	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5	49.8	44.0	41.3
102.5°	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7	136.6	74.6	43.6
105°	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2	484.3	487.4	482.7
107.5°	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4	596.9	598.3	599.8
110°	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0	673.7	674.3	675.2



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1	747.9	747.8	748.4
115°	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3	860.9	861.6	862.0
117.5°	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2	973.0	972.9	972.8
120°	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4
122.5°	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0	1112.4	1112.8	1112.6
125°	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2	1209.2	1210.2	1210.9
127.5°	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8	1303.6	1303.4	1303.1
130°	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2	1362.5	1362.8	1363.0
132.5°	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5	1419.8	1420.1	1420.2
135°	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3	1499.0	1499.8	1500.5
137.5°	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1	1574.8	1575.6	1575.8
140°	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9	1621.9	1623.0	1623.6
142.5°	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3	1665.0	1665.7	1666.1
145°	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2	1726.5	1726.8	1727.4
147.5°	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5	1780.8	1781.1	1781.4
150°	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3	1815.3	1815.3	1815.5
152.5°	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6	1846.1	1846.7	1846.8
155°	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5	1887.9	1889.3	1889.5
157.5°	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3
160°	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3
162.5°	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6	1964.6	1966.6	1966.4
165°	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2	1990.9	1993.7	1993.5
167.5°	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1	2010.0	2013.1	2012.9
170°	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7	2021.4	2024.2	2023.8
172.5°	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0	2028.7	2031.4	2030.9
175°	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6	2037.7	2040.7	2040.2
177.5°	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0	2040.2	2042.4	2041.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	16.0	15.8	15.7	16.1	15.7	15.8	16.0	15.1	14.9	15.1	14.4
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	41.6	41.8	41.9	42.0	41.9	41.8	41.6	41.5	40.4	38.4	36.4
95°	43.1	43.5	43.8	44.1	43.8	43.5	43.1	42.8	41.6	39.6	37.6
97.5°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	41.0	40.8	40.6
100°	41.6	42.0	42.3	42.6	42.3	42.0	41.6	41.3	44.0	49.8	55.5
102.5°	43.6	43.7	43.8	43.8	43.8	43.7	43.6	43.6	74.6	136.6	198.7
105°	470.6	458.4	446.3	434.0	446.3	458.4	470.6	482.7	487.4	484.3	481.2
107.5°	601.1	602.3	603.6	604.9	603.6	602.3	601.1	599.8	598.3	596.9	595.4
110°	676.2	677.2	678.2	679.2	678.2	677.2	676.2	675.2	674.3	673.7	673.0



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	749.7	750.9	752.2	753.6	752.2	750.9	749.7	748.4	747.8	747.9	748.1
115°	862.0	862.0	862.0	862.0	862.0	862.0	862.0	862.0	861.6	860.9	860.3
117.5°	972.6	972.5	972.4	972.2	972.4	972.5	972.6	972.8	972.9	973.0	973.2
120°	1043.7	1043.0	1042.4	1041.7	1042.4	1043.0	1043.7	1044.4	1044.4	1043.7	1043.0
122.5°	1112.0	1111.3	1110.5	1109.9	1110.5	1111.3	1112.0	1112.6	1112.8	1112.4	1112.0
125°	1211.2	1211.5	1211.9	1212.2	1211.9	1211.5	1211.2	1210.9	1210.2	1209.2	1208.2
127.5°	1302.9	1302.6	1302.3	1302.1	1302.3	1302.6	1302.9	1303.1	1303.4	1303.6	1303.8
130°	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1363.0	1362.8	1362.5	1362.2
132.5°	1419.9	1419.6	1419.4	1419.1	1419.4	1419.6	1419.9	1420.2	1420.1	1419.8	1419.5
135°	1501.1	1501.8	1502.5	1503.1	1502.5	1501.8	1501.1	1500.5	1499.8	1499.0	1498.3
137.5°	1575.6	1575.4	1575.2	1575.0	1575.2	1575.4	1575.6	1575.8	1575.6	1574.8	1574.1
140°	1624.0	1624.3	1624.6	1625.0	1624.6	1624.3	1624.0	1623.6	1623.0	1621.9	1620.9
142.5°	1666.2	1666.3	1666.3	1666.4	1666.3	1666.3	1666.2	1666.1	1665.7	1665.0	1664.3
145°	1728.0	1728.7	1729.4	1730.0	1729.4	1728.7	1728.0	1727.4	1726.8	1726.5	1726.2
147.5°	1781.7	1782.0	1782.4	1782.7	1782.4	1782.0	1781.7	1781.4	1781.1	1780.8	1780.5
150°	1815.8	1816.1	1816.5	1816.8	1816.5	1816.1	1815.8	1815.5	1815.3	1815.3	1815.3
152.5°	1846.6	1846.4	1846.2	1846.0	1846.2	1846.4	1846.6	1846.8	1846.7	1846.1	1845.6
155°	1888.4	1887.4	1886.4	1885.4	1886.4	1887.4	1888.4	1889.5	1889.3	1887.9	1886.5
157.5°	1923.6	1921.8	1920.1	1918.2	1920.1	1921.8	1923.6	1925.3	1925.3	1923.6	1921.8
160°	1946.3	1944.3	1942.3	1940.2	1942.3	1944.3	1946.3	1948.3	1948.3	1946.3	1944.3
162.5°	1964.2	1961.9	1959.5	1957.2	1959.5	1961.9	1964.2	1966.4	1966.6	1964.6	1962.6
165°	1990.4	1987.4	1984.4	1981.4	1984.4	1987.4	1990.4	1993.5	1993.7	1990.9	1988.2
167.5°	2009.4	2006.1	2002.7	1999.3	2002.7	2006.1	2009.4	2012.9	2013.1	2010.0	2007.1
170°	2020.4	2017.0	2013.7	2010.2	2013.7	2017.0	2020.4	2023.8	2024.2	2021.4	2018.7
172.5°	2027.3	2023.7	2020.0	2016.3	2020.0	2023.7	2027.3	2030.9	2031.4	2028.7	2026.0
175°	2036.1	2032.1	2028.0	2024.0	2028.0	2032.1	2036.1	2040.2	2040.7	2037.7	2034.6
177.5°	2038.6	2035.3	2032.1	2028.8	2032.1	2035.3	2038.6	2041.8	2042.4	2040.2	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	14.0	13.9	13.4	12.5	12.6	12.1	11.7	11.0	11.2	11.4	11.6
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	34.3	32.3	29.6	26.9	24.1	21.4	20.0	19.8	19.6	19.4	19.2
95°	35.5	33.5	33.1	32.8	32.5	32.1	37.8	49.3	60.8	72.2	83.7
97.5°	40.4	40.2	78.0	115.7	153.5	191.3	206.6	199.4	192.2	185.0	177.8
100°	61.3	67.1	113.7	160.4	207.1	253.8	274.1	268.0	262.0	255.9	249.7
102.5°	260.7	322.9	328.9	335.1	341.1	347.2	348.0	343.6	339.1	334.7	330.1
105°	478.2	475.1	473.4	471.8	470.1	468.4	466.6	464.5	462.4	460.4	458.4
107.5°	593.9	592.4	590.1	587.8	585.5	583.2	581.6	580.6	579.6	578.6	577.4
110°	672.3	671.6	669.5	667.5	665.5	663.5	662.0	661.0	659.9	658.9	657.9



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	748.2	748.4	747.4	746.5	745.5	744.6	743.2	741.3	739.5	737.7	735.9
115°	859.6	858.9	859.3	859.6	859.9	860.3	859.9	858.9	857.9	856.9	855.9
117.5°	973.3	973.4	972.7	972.0	971.2	970.5	969.5	968.1	966.7	965.3	964.0
120°	1042.4	1041.7	1042.0	1042.4	1042.7	1043.0	1042.5	1041.2	1039.9	1038.4	1037.1
122.5°	1111.6	1111.2	1110.6	1110.1	1109.7	1109.2	1108.6	1107.7	1106.9	1106.1	1105.3
125°	1207.2	1206.2	1206.8	1207.5	1208.2	1208.8	1208.5	1207.2	1205.8	1204.5	1203.2
127.5°	1304.0	1304.2	1302.6	1301.1	1299.6	1298.0	1297.1	1296.7	1296.4	1296.1	1295.7
130°	1361.8	1361.5	1360.5	1359.5	1358.5	1357.5	1356.8	1356.5	1356.0	1355.7	1355.4
132.5°	1419.1	1418.8	1417.4	1416.1	1414.9	1413.6	1412.7	1412.1	1411.5	1410.8	1410.2
135°	1497.7	1497.0	1495.7	1494.3	1493.0	1491.6	1491.1	1491.5	1491.8	1492.1	1492.5
137.5°	1573.3	1572.6	1571.0	1569.6	1568.1	1566.6	1565.8	1565.7	1565.5	1565.4	1565.3
140°	1619.9	1618.8	1618.2	1617.5	1616.8	1616.2	1615.5	1614.8	1614.2	1613.5	1612.8
142.5°	1663.4	1662.7	1662.3	1661.9	1661.5	1661.1	1660.3	1659.1	1657.9	1656.6	1655.4
145°	1725.8	1725.5	1725.5	1725.5	1725.5	1725.5	1725.0	1723.9	1722.9	1721.9	1720.9
147.5°	1780.3	1780.0	1780.3	1780.7	1781.0	1781.3	1780.6	1778.7	1776.8	1774.8	1773.0
150°	1815.3	1815.3	1815.6	1816.0	1816.3	1816.6	1816.1	1814.8	1813.4	1812.1	1810.8
152.5°	1845.1	1844.5	1845.1	1845.7	1846.3	1847.0	1846.7	1845.6	1844.6	1843.5	1842.4
155°	1885.2	1883.8	1884.9	1885.9	1886.9	1887.9	1888.2	1887.9	1887.5	1887.2	1886.9
157.5°	1920.1	1918.2	1919.5	1920.6	1921.7	1922.9	1923.6	1923.8	1924.0	1924.2	1924.4
160°	1942.3	1940.2	1940.6	1940.9	1941.2	1941.6	1942.3	1943.3	1944.3	1945.3	1946.3
162.5°	1960.5	1958.4	1958.8	1959.1	1959.4	1959.8	1960.7	1962.0	1963.2	1964.5	1965.8
165°	1985.5	1982.9	1982.9	1982.9	1982.9	1982.9	1983.7	1985.4	1987.1	1988.7	1990.4
167.5°	2004.1	2001.1	2001.4	2001.6	2001.8	2002.0	2002.9	2004.7	2006.4	2008.2	2009.9
170°	2016.0	2013.3	2013.0	2012.7	2012.3	2012.0	2012.8	2014.8	2016.8	2018.9	2020.9
172.5°	2023.3	2020.6	2020.2	2019.9	2019.6	2019.2	2020.1	2022.2	2024.2	2026.2	2028.2
175°	2031.5	2028.5	2028.2	2027.8	2027.5	2027.2	2028.0	2030.0	2032.1	2034.1	2036.1
177.5°	2035.9	2033.7	2033.2	2032.7	2032.1	2031.5	2032.3	2034.1	2036.0	2037.9	2039.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	12.0	11.8	11.3	11.7	12.4	12.3	13.1	13.7	14.2	14.3	15.3
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	19.4	19.6	19.8	20.0	21.4	24.1	26.9	29.6	32.3	34.3	36.4
95°	72.2	60.8	49.3	37.8	32.1	32.5	32.8	33.1	33.5	35.5	37.6
97.5°	185.0	192.2	199.4	206.6	191.3	153.5	115.7	78.0	40.2	40.4	40.6
100°	255.9	262.0	268.0	274.1	253.8	207.1	160.4	113.7	67.1	61.3	55.5
102.5°	334.7	339.1	343.6	348.0	347.2	341.1	335.1	328.9	322.9	260.7	198.7
105°	460.4	462.4	464.5	466.6	468.4	470.1	471.8	473.4	475.1	478.2	481.2
107.5°	578.6	579.6	580.6	581.6	583.2	585.5	587.8	590.1	592.4	593.9	595.4
110°	658.9	659.9	661.0	662.0	663.5	665.5	667.5	669.5	671.6	672.3	673.0





TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	737.7	739.5	741.3	743.2	744.6	745.5	746.5	747.4	748.4	748.2	748.1
115°	856.9	857.9	858.9	859.9	860.3	859.9	859.6	859.3	858.9	859.6	860.3
117.5°	965.3	966.7	968.1	969.5	970.5	971.2	972.0	972.7	973.4	973.3	973.2
120°	1038.4	1039.9	1041.2	1042.5	1043.0	1042.7	1042.4	1042.0	1041.7	1042.4	1043.0
122.5°	1106.1	1106.9	1107.7	1108.6	1109.2	1109.7	1110.1	1110.6	1111.2	1111.6	1112.0
125°	1204.5	1205.8	1207.2	1208.5	1208.8	1208.2	1207.5	1206.8	1206.2	1207.2	1208.2
127.5°	1296.1	1296.4	1296.7	1297.1	1298.0	1299.6	1301.1	1302.6	1304.2	1304.0	1303.8
130°	1355.7	1356.0	1356.5	1356.8	1357.5	1358.5	1359.5	1360.5	1361.5	1361.8	1362.2
132.5°	1410.8	1411.5	1412.1	1412.7	1413.6	1414.9	1416.1	1417.4	1418.8	1419.1	1419.5
135°	1492.1	1491.8	1491.5	1491.1	1491.6	1493.0	1494.3	1495.7	1497.0	1497.7	1498.3
137.5°	1565.4	1565.5	1565.7	1565.8	1566.6	1568.1	1569.6	1571.0	1572.6	1573.3	1574.1
140°	1613.5	1614.2	1614.8	1615.5	1616.2	1616.8	1617.5	1618.2	1618.8	1619.9	1620.9
142.5°	1656.6	1657.9	1659.1	1660.3	1661.1	1661.5	1661.9	1662.3	1662.7	1663.4	1664.3
145°	1721.9	1722.9	1723.9	1725.0	1725.5	1725.5	1725.5	1725.5	1725.5	1725.8	1726.2
147.5°	1774.8	1776.8	1778.7	1780.6	1781.3	1781.0	1780.7	1780.3	1780.0	1780.3	1780.5
150°	1812.1	1813.4	1814.8	1816.1	1816.6	1816.3	1816.0	1815.6	1815.3	1815.3	1815.3
152.5°	1843.5	1844.6	1845.6	1846.7	1847.0	1846.3	1845.7	1845.1	1844.5	1845.1	1845.6
155°	1887.2	1887.5	1887.9	1888.2	1887.9	1886.9	1885.9	1884.9	1883.8	1885.2	1886.5
157.5°	1924.2	1924.0	1923.8	1923.6	1922.9	1921.7	1920.6	1919.5	1918.2	1920.1	1921.8
160°	1945.3	1944.3	1943.3	1942.3	1941.6	1941.2	1940.9	1940.6	1940.2	1942.3	1944.3
162.5°	1964.5	1963.2	1962.0	1960.7	1959.8	1959.4	1959.1	1958.8	1958.4	1960.5	1962.6
165°	1988.7	1987.1	1985.4	1983.7	1982.9	1982.9	1982.9	1982.9	1982.9	1985.5	1988.2
167.5°	2008.2	2006.4	2004.7	2002.9	2002.0	2001.8	2001.6	2001.4	2001.1	2004.1	2007.1
170°	2018.9	2016.8	2014.8	2012.8	2012.0	2012.3	2012.7	2013.0	2013.3	2016.0	2018.7
172.5°	2026.2	2024.2	2022.2	2020.1	2019.2	2019.6	2019.9	2020.2	2020.6	2023.3	2026.0
175°	2034.1	2032.1	2030.0	2028.0	2027.2	2027.5	2027.8	2028.2	2028.5	2031.5	2034.6
177.5°	2037.9	2036.0	2034.1	2032.3	2031.5	2032.1	2032.7	2033.2	2033.7	2035.9	2038.0
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	15.1	15.2	15.9	15.7	15.8	15.7	16.1
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	38.4	40.4	41.5	41.6	41.8	41.9	42.0
95°	39.6	41.6	42.8	43.1	43.5	43.8	44.1
97.5°	40.8	41.0	41.3	41.6	42.0	42.3	42.6
100°	49.8	44.0	41.3	41.6	42.0	42.3	42.6
102.5°	136.6	74.6	43.6	43.6	43.7	43.8	43.8
105°	484.3	487.4	482.7	470.6	458.4	446.3	434.0
107.5°	596.9	598.3	599.8	601.1	602.3	603.6	604.9
110°	673.7	674.3	675.2	676.2	677.2	678.2	679.2



TEST NUMBER: P333051-840

CATALOG NUMBER: S124RDIW-S575D1560U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	747.9	747.8	748.4	749.7	750.9	752.2	753.6
115°	860.9	861.6	862.0	862.0	862.0	862.0	862.0
117.5°	973.0	972.9	972.8	972.6	972.5	972.4	972.2
120°	1043.7	1044.4	1044.4	1043.7	1043.0	1042.4	1041.7
122.5°	1112.4	1112.8	1112.6	1112.0	1111.3	1110.5	1109.9
125°	1209.2	1210.2	1210.9	1211.2	1211.5	1211.9	1212.2
127.5°	1303.6	1303.4	1303.1	1302.9	1302.6	1302.3	1302.1
130°	1362.5	1362.8	1363.0	1363.0	1363.0	1363.0	1363.0
132.5°	1419.8	1420.1	1420.2	1419.9	1419.6	1419.4	1419.1
135°	1499.0	1499.8	1500.5	1501.1	1501.8	1502.5	1503.1
137.5°	1574.8	1575.6	1575.8	1575.6	1575.4	1575.2	1575.0
140°	1621.9	1623.0	1623.6	1624.0	1624.3	1624.6	1625.0
142.5°	1665.0	1665.7	1666.1	1666.2	1666.3	1666.3	1666.4
145°	1726.5	1726.8	1727.4	1728.0	1728.7	1729.4	1730.0
147.5°	1780.8	1781.1	1781.4	1781.7	1782.0	1782.4	1782.7
150°	1815.3	1815.3	1815.5	1815.8	1816.1	1816.5	1816.8
152.5°	1846.1	1846.7	1846.8	1846.6	1846.4	1846.2	1846.0
155°	1887.9	1889.3	1889.5	1888.4	1887.4	1886.4	1885.4
157.5°	1923.6	1925.3	1925.3	1923.6	1921.8	1920.1	1918.2
160°	1946.3	1948.3	1948.3	1946.3	1944.3	1942.3	1940.2
162.5°	1964.6	1966.6	1966.4	1964.2	1961.9	1959.5	1957.2
165°	1990.9	1993.7	1993.5	1990.4	1987.4	1984.4	1981.4
167.5°	2010.0	2013.1	2012.9	2009.4	2006.1	2002.7	1999.3
170°	2021.4	2024.2	2023.8	2020.4	2017.0	2013.7	2010.2
172.5°	2028.7	2031.4	2030.9	2027.3	2023.7	2020.0	2016.3
175°	2037.7	2040.7	2040.2	2036.1	2032.1	2028.0	2024.0
177.5°	2040.2	2042.4	2041.8	2038.6	2035.3	2032.1	2028.8
180°	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1	2036.1

(END OF REPORT)