

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332756

Luminaire Tested: **S124DIW-S575D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332756  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D770U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5157.4 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48						48														
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41						41														
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34						34														
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29						29														
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25						25														
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21						21														
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19						19														
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17						17														
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15						15														
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14						14														
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12						12														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.5	1.8
10°-20°	257.7	5.0
20°-30°	379.3	7.4
30°-40°	440.9	8.5
40°-50°	440.9	8.5
50°-60°	385.7	7.5
60°-70°	286.4	5.6
70°-80°	162.7	3.2
80°-90°	49.8	1.0
90°-100°	63.3	1.2
100°-110°	187.5	3.6
110°-120°	318.2	6.2
120°-130°	419.6	8.1
130°-140°	471.3	9.1
140°-150°	463.1	9.0
150°-160°	389.5	7.6
160°-170°	259.1	5.0
170°-180°	90.7	1.8
0°-30°	728.4	14.1
0°-40°	1169.3	22.7
0°-60°	1996.0	38.7
0°-90°	2495.0	48.4
90°-120°	569.0	11.0
90°-150°	1923.1	37.3
90°-180°	2662.0	51.6
0°-180°	5157.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	2	10	16	21	22	5
95°	44	51	56	58	59	50
105°	173	174	177	179	181	183
115°	324	324	322	321	321	319
125°	471	471	470	469	468	420
135°	608	612	612	611	609	470
145°	738	741	742	741	739	462
155°	846	846	845	848	845	389
165°	921	919	917	921	919	260
175°	958	955	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.6	16.9	17.1	17.3	17.5	17.7	17.8	18.0	18.1	18.2	18.4
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	15.9	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0
95°	44.5	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9
97.5°	77.8	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8
100°	103.9	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9
102.5°	131.2	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0
105°	172.9	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1
107.5°	216.7	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5
110°	246.4	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8



TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.3	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2
115°	323.6	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9
117.5°	367.2	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2
120°	396.3	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2
122.5°	426.6	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2
125°	471.3	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2
127.5°	511.8	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5
130°	540.3	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2
132.5°	569.4	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1
135°	607.9	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0
137.5°	649.7	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5
140°	677.6	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9
142.5°	703.1	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0
145°	738.5	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	773.5	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3
150°	794.9	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.1	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8
155°	846.1	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0
157.5°	872.2	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2
160°	887.7	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7
162.5°	901.9	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1
165°	921.1	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3
167.5°	935.7	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8
170°	944.1	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1
172.5°	950.0	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2
175°	958.2	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9
177.5°	960.8	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	18.6	18.8	19.0	19.1	19.2	19.3	19.3	19.4
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	30.6	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.4	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	90.4	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.2	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.4	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	177.6	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.0	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.5	246.2	245.8	245.9	246.4	246.9	247.4	247.9





TEST NUMBER: P332756

CATALOG NUMBER: S124DIW-S575D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.1	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.8	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.7	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	395.4	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.6	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.9	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	512.2	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.9	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.8	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.6	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	652.1	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.8	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	704.0	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.9	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.2	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.2	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	871.7	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.2	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.0	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	919.3	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	934.8	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	943.1	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	949.3	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	959.7	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)