

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332792

Luminaire Tested: **S124DIW-S795D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332792  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1050U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7044.5 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48					48			
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46					41				
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39					34				
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33					29				
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28					25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25					21				
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22					19				
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19					17				
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17					15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16					14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14					12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	1.8
10°-20°	352.2	5.0
20°-30°	518.4	7.4
30°-40°	602.7	8.6
40°-50°	602.7	8.6
50°-60°	527.2	7.5
60°-70°	391.5	5.6
70°-80°	222.4	3.2
80°-90°	68.1	1.0
90°-100°	86.4	1.2
100°-110°	255.9	3.6
110°-120°	434.4	6.2
120°-130°	572.8	8.1
130°-140°	643.3	9.1
140°-150°	632.1	9.0
150°-160°	531.7	7.5
160°-170°	353.7	5.0
170°-180°	123.9	1.8
0°-30°	995.7	14.1
0°-40°	1598.4	22.7
0°-60°	2728.3	38.7
0°-90°	3410.4	48.4
90°-120°	776.7	11.0
90°-150°	2624.9	37.3
90°-180°	3634.0	51.6
0°-180°	7044.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	3	14	22	28	30	7
95°	61	70	77	80	80	68
105°	236	237	241	244	247	250
115°	442	442	440	439	438	435
125°	643	643	642	640	638	573
135°	830	835	836	834	831	642
145°	1008	1012	1013	1012	1009	631
155°	1155	1155	1154	1158	1154	531
165°	1257	1254	1252	1258	1254	354
175°	1308	1303	1302	1308	1302	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	22.7	23.0	23.3	23.7	24.0	24.2	24.4	24.5	24.7	24.9	25.2
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	21.7	24.5	27.4	30.2	33.0	35.1	36.3	37.6	38.9	40.1	40.9
95°	60.8	62.8	64.8	66.9	68.9	70.7	72.3	73.8	75.4	77.0	77.7
97.5°	106.2	107.8	109.4	111.0	112.7	114.4	116.2	118.1	119.9	121.8	122.6
100°	141.8	142.7	143.6	144.5	145.4	146.9	148.9	150.9	153.0	155.0	155.4
102.5°	179.1	179.5	179.8	180.2	180.5	181.6	183.5	185.3	187.2	189.0	189.7
105°	236.0	236.3	236.5	236.7	236.9	237.5	238.4	239.3	240.2	241.1	241.8
107.5°	295.8	296.1	296.3	296.6	296.9	297.1	297.2	297.4	297.5	297.6	298.3
110°	336.3	336.8	337.2	337.7	338.1	338.2	338.0	337.8	337.6	337.3	336.9



TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.5	378.6	378.7	378.7	378.8	378.7	378.3	377.9	377.5	377.1	377.0
115°	441.7	441.7	441.7	441.7	441.7	441.5	441.0	440.6	440.1	439.7	439.4
117.5°	501.3	501.4	501.6	501.8	502.0	501.9	501.6	501.3	501.0	500.6	499.9
120°	541.0	541.9	542.8	543.7	544.6	544.7	544.0	543.3	542.7	542.0	540.9
122.5°	582.3	582.7	583.0	583.4	583.7	583.8	583.4	583.1	582.8	582.5	581.7
125°	643.3	643.3	643.3	643.3	643.3	643.2	642.9	642.7	642.5	642.3	641.8
127.5°	698.6	699.3	699.9	700.6	701.3	701.5	701.1	700.7	700.4	700.0	699.6
130°	737.5	738.2	738.8	739.5	740.2	740.5	740.5	740.5	740.5	740.5	740.1
132.5°	777.2	777.7	778.2	778.7	779.2	779.3	779.2	779.0	778.8	778.6	778.2
135°	829.7	831.0	832.4	833.7	835.1	835.8	835.8	835.8	835.8	835.8	835.3
137.5°	886.8	887.4	888.1	888.7	889.3	889.8	890.2	890.6	890.9	891.3	890.7
140°	924.9	925.4	925.8	926.3	926.7	926.9	926.9	926.9	926.9	926.9	926.7
142.5°	959.8	960.2	960.7	961.1	961.6	961.7	961.5	961.3	961.2	961.0	960.9
145°	1008.0	1008.9	1009.8	1010.7	1011.6	1012.1	1012.4	1012.6	1012.8	1013.0	1012.8
147.5°	1055.8	1056.9	1058.0	1059.0	1060.1	1060.6	1060.4	1060.2	1060.0	1059.8	1059.7
150°	1085.0	1085.9	1086.8	1087.7	1088.6	1089.0	1089.0	1089.0	1089.0	1089.0	1089.0
152.5°	1112.5	1113.1	1113.6	1114.1	1114.7	1115.0	1115.2	1115.4	1115.6	1115.8	1116.3
155°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.3	1154.1	1153.9	1154.8
157.5°	1190.5	1190.1	1189.7	1189.3	1188.9	1188.7	1188.6	1188.6	1188.5	1188.5	1189.2
160°	1211.6	1211.4	1211.1	1210.9	1210.7	1210.5	1210.2	1210.0	1209.8	1209.6	1210.2
162.5°	1231.0	1230.5	1229.9	1229.3	1228.7	1228.3	1228.1	1227.9	1227.6	1227.4	1228.6
165°	1257.2	1256.5	1255.8	1255.2	1254.5	1253.9	1253.5	1253.0	1252.6	1252.1	1253.5
167.5°	1277.2	1276.3	1275.4	1274.4	1273.5	1273.0	1273.1	1273.1	1273.1	1273.2	1274.5
170°	1288.6	1287.5	1286.3	1285.2	1284.1	1283.6	1283.9	1284.1	1284.3	1284.5	1285.9
172.5°	1296.7	1295.7	1294.8	1293.9	1292.9	1292.5	1292.5	1292.6	1292.6	1292.6	1294.2
175°	1307.8	1306.7	1305.6	1304.5	1303.3	1302.7	1302.4	1302.2	1302.0	1301.8	1303.3
177.5°	1311.5	1310.6	1309.7	1308.8	1307.9	1307.4	1307.4	1307.4	1307.4	1307.4	1308.7
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9



TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	25.4	25.7	26.0	26.1	26.2	26.3	26.4	26.5
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	41.7	42.5	43.4	43.9	44.2	44.4	44.7	45.0
95°	78.3	79.0	79.7	80.0	80.0	80.0	80.0	80.0
97.5°	123.4	124.2	125.0	125.4	125.4	125.4	125.4	125.4
100°	155.9	156.3	156.8	157.0	157.0	157.0	157.0	157.0
102.5°	190.3	190.9	191.6	192.0	192.1	192.3	192.5	192.7
105°	242.5	243.1	243.8	244.5	245.2	245.8	246.5	247.2
107.5°	298.9	299.5	300.2	300.4	300.4	300.4	300.3	300.3
110°	336.4	336.0	335.5	335.7	336.3	337.0	337.7	338.4





TEST NUMBER: P332792

CATALOG NUMBER: S124DIW-S795D1050U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	376.9	376.8	376.7	376.7	376.9	377.0	377.1	377.3
115°	439.2	439.0	438.8	438.5	438.3	438.1	437.9	437.6
117.5°	499.1	498.3	497.6	497.0	496.5	496.1	495.6	495.2
120°	539.7	538.6	537.5	537.1	537.6	538.0	538.5	538.9
122.5°	581.0	580.2	579.4	578.6	577.8	577.0	576.2	575.4
125°	641.4	640.9	640.5	640.0	639.6	639.1	638.7	638.2
127.5°	699.1	698.7	698.2	697.8	697.4	697.1	696.7	696.4
130°	739.6	739.2	738.7	738.1	737.2	736.3	735.4	734.5
132.5°	777.7	777.3	776.8	776.4	776.1	775.7	775.3	775.0
135°	834.9	834.4	834.0	833.4	832.7	832.0	831.4	830.7
137.5°	890.1	889.5	888.9	888.7	888.8	889.0	889.1	889.2
140°	926.5	926.3	926.0	925.8	925.6	925.4	925.1	924.9
142.5°	960.9	960.8	960.8	960.7	960.7	960.7	960.6	960.6
145°	1012.6	1012.4	1012.1	1011.7	1011.0	1010.3	1009.7	1009.0
147.5°	1059.5	1059.3	1059.1	1058.9	1058.7	1058.5	1058.2	1058.0
150°	1089.0	1089.0	1089.0	1088.9	1088.7	1088.5	1088.2	1088.0
152.5°	1116.8	1117.4	1117.9	1117.9	1117.3	1116.7	1116.1	1115.6
155°	1155.7	1156.6	1157.5	1157.5	1156.6	1155.7	1154.8	1153.9
157.5°	1189.9	1190.5	1191.2	1191.2	1190.4	1189.6	1188.9	1188.1
160°	1210.9	1211.6	1212.3	1212.0	1210.9	1209.8	1208.7	1207.5
162.5°	1229.8	1231.0	1232.3	1232.3	1231.2	1230.1	1228.9	1227.8
165°	1254.8	1256.2	1257.5	1257.7	1256.8	1255.9	1255.0	1254.1
167.5°	1275.9	1277.2	1278.6	1278.6	1277.2	1275.8	1274.4	1273.0
170°	1287.2	1288.6	1289.9	1289.8	1288.3	1286.7	1285.1	1283.5
172.5°	1295.7	1297.2	1298.8	1298.7	1297.2	1295.6	1294.0	1292.4
175°	1304.9	1306.5	1308.1	1308.1	1306.5	1304.9	1303.3	1301.8
177.5°	1310.0	1311.2	1312.5	1312.4	1310.9	1309.5	1308.1	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)