

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332793

Luminaire Tested: **S124DIW-S795D1340U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332793  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1340U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8911.5 lumens  
Efficiency: N/A  
Efficacy: 145.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																												
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	42	41	40	34																												
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29																												
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24																												
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21																												
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	18																												
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																												
7	57	45	37	32	52	41	35	30	35	29	25	28	24	21	22	19	17	14																												
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	1.4
10°-20°	385.5	4.3
20°-30°	611.3	6.9
30°-40°	680.3	7.6
40°-50°	619.3	6.9
50°-60°	506.1	5.7
60°-70°	361.3	4.1
70°-80°	198.9	2.2
80°-90°	59.3	0.7
90°-100°	59.3	0.7
100°-110°	378.2	4.2
110°-120°	723.4	8.1
120°-130°	918.4	10.3
130°-140°	982.6	11.0
140°-150°	918.8	10.3
150°-160°	741.0	8.3
160°-170°	477.9	5.4
170°-180°	164.7	1.8
0°-30°	1121.9	12.6
0°-40°	1802.3	20.2
0°-60°	2927.7	32.9
0°-90°	3547.2	39.8
90°-120°	1160.9	13.0
90°-150°	3980.7	44.7
90°-180°	5364.0	60.2
0°-180°	8911.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	40
90°	39	4	39	4	39	18
95°	38	71	38	71	38	30
105°	370	390	370	390	370	323
115°	734	729	734	729	734	727
125°	1032	1025	1032	1025	1032	919
135°	1280	1271	1280	1271	1280	985
145°	1474	1466	1474	1466	1474	921
155°	1606	1607	1606	1607	1606	740
165°	1688	1695	1688	1695	1688	477
175°	1724	1734	1724	1734	1724	164
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	17.1	18.3	18.2	18.5	19.2	19.4	19.5	18.7	20.1	20.2	21.4
90°	38.9	38.3	37.8	37.2	36.6	35.5	33.7	32.0	30.3	28.5	26.2
92.5°	35.8	35.7	35.6	35.5	35.3	34.4	32.7	31.0	29.2	27.5	25.2
95°	37.6	37.3	37.0	36.7	36.5	35.5	33.7	32.0	30.3	28.5	28.2
97.5°	36.3	36.0	35.7	35.5	35.2	34.9	34.8	34.6	34.4	34.2	66.4
100°	36.3	36.0	35.7	35.5	35.2	37.5	42.4	47.3	52.2	57.1	96.8
102.5°	37.4	37.3	37.2	37.2	37.1	63.5	116.4	169.3	222.1	275.0	280.2
105°	369.7	380.0	390.4	400.8	411.2	415.1	412.5	409.9	407.3	404.7	403.2
107.5°	515.2	514.1	513.0	511.9	510.8	509.6	508.4	507.1	505.8	504.6	502.6
110°	578.5	577.6	576.8	575.9	575.0	574.3	573.7	573.2	572.6	572.0	570.3



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	641.8	640.7	639.6	638.5	637.4	636.9	637.0	637.1	637.3	637.4	636.6
115°	734.1	734.1	734.1	734.1	734.1	733.8	733.3	732.7	732.1	731.5	731.8
117.5°	828.0	828.2	828.3	828.4	828.5	828.6	828.7	828.8	829.0	829.1	828.4
120°	887.2	887.8	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2	887.5
122.5°	945.3	945.9	946.4	947.0	947.6	947.7	947.4	947.0	946.7	946.3	945.9
125°	1032.5	1032.2	1031.9	1031.6	1031.3	1030.7	1029.9	1029.0	1028.1	1027.3	1027.8
127.5°	1109.0	1109.2	1109.4	1109.7	1109.9	1110.1	1110.3	1110.5	1110.6	1110.8	1109.5
130°	1160.9	1160.9	1160.9	1160.9	1160.9	1160.7	1160.4	1160.1	1159.9	1159.6	1158.7
132.5°	1208.6	1208.8	1209.1	1209.3	1209.5	1209.5	1209.2	1208.9	1208.6	1208.3	1207.2
135°	1280.2	1279.6	1279.0	1278.5	1277.9	1277.3	1276.7	1276.2	1275.6	1275.0	1273.9
137.5°	1341.4	1341.6	1341.8	1341.9	1342.1	1341.9	1341.2	1340.6	1340.0	1339.3	1338.1
140°	1384.0	1383.7	1383.4	1383.1	1382.8	1382.2	1381.4	1380.5	1379.6	1378.8	1378.2
142.5°	1419.2	1419.2	1419.1	1419.1	1419.0	1418.7	1418.0	1417.4	1416.8	1416.1	1415.8
145°	1473.5	1472.9	1472.3	1471.7	1471.2	1470.7	1470.4	1470.1	1469.9	1469.6	1469.6
147.5°	1518.3	1518.0	1517.8	1517.5	1517.2	1516.9	1516.7	1516.5	1516.2	1516.0	1516.3
150°	1547.4	1547.1	1546.8	1546.5	1546.2	1546.1	1546.1	1546.1	1546.1	1546.1	1546.4
152.5°	1572.3	1572.5	1572.6	1572.8	1573.0	1572.8	1572.4	1571.9	1571.5	1571.0	1571.5
155°	1605.8	1606.6	1607.5	1608.4	1609.2	1609.1	1607.9	1606.8	1605.6	1604.5	1605.3
157.5°	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8	1634.8
160°	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5	1652.7
162.5°	1667.0	1668.9	1670.9	1672.9	1674.8	1674.9	1673.2	1671.5	1669.7	1668.0	1668.3
165°	1687.5	1690.1	1692.7	1695.3	1697.8	1698.0	1695.7	1693.4	1691.1	1688.8	1688.8
167.5°	1702.8	1705.7	1708.5	1711.4	1714.3	1714.5	1711.9	1709.4	1706.9	1704.3	1704.5
170°	1712.1	1715.0	1717.9	1720.8	1723.6	1723.9	1721.6	1719.3	1717.0	1714.7	1714.4
172.5°	1717.3	1720.4	1723.5	1726.6	1729.8	1730.2	1727.9	1725.5	1723.2	1720.9	1720.6
175°	1723.8	1727.2	1730.7	1734.2	1737.6	1738.1	1735.5	1732.9	1730.3	1727.7	1727.4
177.5°	1727.9	1730.7	1733.5	1736.2	1739.0	1739.5	1737.6	1735.8	1733.9	1732.1	1731.6
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	21.0	20.9	20.0	17.8	15.9	14.0	12.9	11.8	12.9	14.0	15.0
90°	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.3	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.1	41.9	51.7	61.5	71.3	61.5	51.7	41.9
97.5°	98.6	130.7	162.9	175.9	169.8	163.7	157.6	151.5	157.6	163.7	169.8
100°	136.6	176.4	216.2	233.5	228.3	223.1	217.9	212.7	217.9	223.1	228.3
102.5°	285.4	290.5	295.7	296.4	292.6	288.8	285.0	281.2	285.0	288.8	292.6
105°	401.8	400.4	398.9	397.3	395.6	393.9	392.1	390.4	392.1	393.9	395.6
107.5°	500.6	498.7	496.7	495.3	494.4	493.6	492.7	491.8	492.7	493.6	494.4
110°	568.5	566.8	565.1	563.8	562.9	562.1	561.2	560.3	561.2	562.1	562.9





TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	635.8	635.0	634.1	633.0	631.4	629.9	628.3	626.7	628.3	629.9	631.4
115°	732.1	732.4	732.7	732.4	731.5	730.7	729.8	728.9	729.8	730.7	731.5
117.5°	827.8	827.2	826.5	825.6	824.5	823.3	822.2	821.0	822.2	823.3	824.5
120°	887.8	888.1	888.3	887.9	886.8	885.6	884.4	883.3	884.4	885.6	886.8
122.5°	945.5	945.1	944.7	944.2	943.5	942.8	942.1	941.4	942.1	942.8	943.5
125°	1028.4	1029.0	1029.6	1029.3	1028.1	1027.0	1025.8	1024.7	1025.8	1027.0	1028.1
127.5°	1108.1	1106.8	1105.5	1104.7	1104.4	1104.1	1103.8	1103.5	1103.8	1104.1	1104.4
130°	1157.8	1157.0	1156.1	1155.5	1155.2	1155.0	1154.7	1154.4	1154.7	1155.0	1155.2
132.5°	1206.1	1205.1	1204.0	1203.1	1202.6	1202.1	1201.6	1201.1	1201.6	1202.1	1202.6
135°	1272.7	1271.5	1270.4	1270.0	1270.3	1270.5	1270.8	1271.1	1270.8	1270.5	1270.3
137.5°	1336.8	1335.5	1334.3	1333.6	1333.5	1333.3	1333.2	1333.1	1333.2	1333.3	1333.5
140°	1377.6	1377.0	1376.5	1375.9	1375.3	1374.7	1374.2	1373.6	1374.2	1374.7	1375.3
142.5°	1415.4	1415.1	1414.7	1414.1	1413.0	1412.0	1410.9	1409.9	1410.9	1412.0	1413.0
145°	1469.6	1469.6	1469.6	1469.1	1468.3	1467.4	1466.5	1465.7	1466.5	1467.4	1468.3
147.5°	1516.6	1516.9	1517.2	1516.5	1514.9	1513.3	1511.6	1510.0	1511.6	1513.3	1514.9
150°	1546.7	1547.0	1547.2	1546.8	1545.7	1544.5	1543.4	1542.2	1543.4	1544.5	1545.7
152.5°	1572.0	1572.6	1573.1	1572.9	1571.9	1571.0	1570.1	1569.2	1570.1	1571.0	1571.9
155°	1606.2	1607.1	1607.9	1608.2	1607.9	1607.6	1607.3	1607.1	1607.3	1607.6	1607.9
157.5°	1635.7	1636.7	1637.7	1638.3	1638.4	1638.6	1638.8	1639.0	1638.8	1638.6	1638.4
160°	1653.0	1653.3	1653.6	1654.2	1655.0	1655.9	1656.8	1657.6	1656.8	1655.9	1655.0
162.5°	1668.6	1668.9	1669.2	1669.9	1671.0	1672.1	1673.1	1674.2	1673.1	1672.1	1671.0
165°	1688.8	1688.8	1688.8	1689.5	1690.9	1692.4	1693.8	1695.3	1693.8	1692.4	1690.9
167.5°	1704.7	1704.9	1705.0	1705.9	1707.4	1708.9	1710.4	1711.9	1710.4	1708.9	1707.4
170°	1714.1	1713.8	1713.6	1714.3	1716.0	1717.7	1719.5	1721.2	1719.5	1717.7	1716.0
172.5°	1720.4	1720.1	1719.8	1720.5	1722.2	1724.0	1725.7	1727.4	1725.7	1724.0	1722.2
175°	1727.1	1726.8	1726.5	1727.2	1729.0	1730.7	1732.4	1734.2	1732.4	1730.7	1729.0
177.5°	1731.2	1730.7	1730.2	1730.8	1732.4	1734.0	1735.7	1737.3	1735.7	1734.0	1732.4
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	16.9	17.5	19.6	21.0	22.7	25.3	26.5	31.5	33.5	36.0	40.1
90°	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0	33.7	35.5	36.6
92.5°	17.0	18.3	20.6	22.9	25.2	27.5	29.2	31.0	32.7	34.4	35.3
95°	32.1	27.4	27.7	28.0	28.2	28.5	30.3	32.0	33.7	35.5	36.5
97.5°	175.9	162.9	130.7	98.6	66.4	34.2	34.4	34.6	34.8	34.9	35.2
100°	233.5	216.2	176.4	136.6	96.8	57.1	52.2	47.3	42.4	37.5	35.2
102.5°	296.4	295.7	290.5	285.4	280.2	275.0	222.1	169.3	116.4	63.5	37.1
105°	397.3	398.9	400.4	401.8	403.2	404.7	407.3	409.9	412.5	415.1	411.2
107.5°	495.3	496.7	498.7	500.6	502.6	504.6	505.8	507.1	508.4	509.6	510.8
110°	563.8	565.1	566.8	568.5	570.3	572.0	572.6	573.2	573.7	574.3	575.0



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.0	634.1	635.0	635.8	636.6	637.4	637.3	637.1	637.0	636.9	637.4
115°	732.4	732.7	732.4	732.1	731.8	731.5	732.1	732.7	733.3	733.8	734.1
117.5°	825.6	826.5	827.2	827.8	828.4	829.1	829.0	828.8	828.7	828.6	828.5
120°	887.9	888.3	888.1	887.8	887.5	887.2	887.8	888.3	888.9	889.5	889.5
122.5°	944.2	944.7	945.1	945.5	945.9	946.3	946.7	947.0	947.4	947.7	947.6
125°	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1	1029.0	1029.9	1030.7	1031.3
127.5°	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6	1110.5	1110.3	1110.1	1109.9
130°	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9	1160.1	1160.4	1160.7	1160.9
132.5°	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6	1208.9	1209.2	1209.5	1209.5
135°	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6	1276.2	1276.7	1277.3	1277.9
137.5°	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0	1340.6	1341.2	1341.9	1342.1
140°	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6	1380.5	1381.4	1382.2	1382.8
142.5°	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8	1417.4	1418.0	1418.7	1419.0
145°	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9	1470.1	1470.4	1470.7	1471.2
147.5°	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2	1516.5	1516.7	1516.9	1517.2
150°	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1	1546.1	1546.1	1546.1	1546.2
152.5°	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5	1571.9	1572.4	1572.8	1573.0
155°	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6	1606.8	1607.9	1609.1	1609.2
157.5°	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8
160°	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4
162.5°	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7	1671.5	1673.2	1674.9	1674.8
165°	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1	1693.4	1695.7	1698.0	1697.8
167.5°	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9	1709.4	1711.9	1714.5	1714.3
170°	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0	1719.3	1721.6	1723.9	1723.6
172.5°	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2	1725.5	1727.9	1730.2	1729.8
175°	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3	1732.9	1735.5	1738.1	1737.6
177.5°	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9	1735.8	1737.6	1739.5	1739.0
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	41.5	42.0	43.4	44.4	43.4	42.0	41.5	40.1	36.0	33.5	31.5
90°	37.2	37.8	38.3	38.9	38.3	37.8	37.2	36.6	35.5	33.7	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.3	34.4	32.7	31.0
95°	36.7	37.0	37.3	37.6	37.3	37.0	36.7	36.5	35.5	33.7	32.0
97.5°	35.5	35.7	36.0	36.3	36.0	35.7	35.5	35.2	34.9	34.8	34.6
100°	35.5	35.7	36.0	36.3	36.0	35.7	35.5	35.2	37.5	42.4	47.3
102.5°	37.2	37.2	37.3	37.4	37.3	37.2	37.2	37.1	63.5	116.4	169.3
105°	400.8	390.4	380.0	369.7	380.0	390.4	400.8	411.2	415.1	412.5	409.9
107.5°	511.9	513.0	514.1	515.2	514.1	513.0	511.9	510.8	509.6	508.4	507.1
110°	575.9	576.8	577.6	578.5	577.6	576.8	575.9	575.0	574.3	573.7	573.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	638.5	639.6	640.7	641.8	640.7	639.6	638.5	637.4	636.9	637.0	637.1
115°	734.1	734.1	734.1	734.1	734.1	734.1	734.1	734.1	733.8	733.3	732.7
117.5°	828.4	828.3	828.2	828.0	828.2	828.3	828.4	828.5	828.6	828.7	828.8
120°	888.9	888.3	887.8	887.2	887.8	888.3	888.9	889.5	889.5	888.9	888.3
122.5°	947.0	946.4	945.9	945.3	945.9	946.4	947.0	947.6	947.7	947.4	947.0
125°	1031.6	1031.9	1032.2	1032.5	1032.2	1031.9	1031.6	1031.3	1030.7	1029.9	1029.0
127.5°	1109.7	1109.4	1109.2	1109.0	1109.2	1109.4	1109.7	1109.9	1110.1	1110.3	1110.5
130°	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.7	1160.4	1160.1
132.5°	1209.3	1209.1	1208.8	1208.6	1208.8	1209.1	1209.3	1209.5	1209.5	1209.2	1208.9
135°	1278.5	1279.0	1279.6	1280.2	1279.6	1279.0	1278.5	1277.9	1277.3	1276.7	1276.2
137.5°	1341.9	1341.8	1341.6	1341.4	1341.6	1341.8	1341.9	1342.1	1341.9	1341.2	1340.6
140°	1383.1	1383.4	1383.7	1384.0	1383.7	1383.4	1383.1	1382.8	1382.2	1381.4	1380.5
142.5°	1419.1	1419.1	1419.2	1419.2	1419.2	1419.1	1419.1	1419.0	1418.7	1418.0	1417.4
145°	1471.7	1472.3	1472.9	1473.5	1472.9	1472.3	1471.7	1471.2	1470.7	1470.4	1470.1
147.5°	1517.5	1517.8	1518.0	1518.3	1518.0	1517.8	1517.5	1517.2	1516.9	1516.7	1516.5
150°	1546.5	1546.8	1547.1	1547.4	1547.1	1546.8	1546.5	1546.2	1546.1	1546.1	1546.1
152.5°	1572.8	1572.6	1572.5	1572.3	1572.5	1572.6	1572.8	1573.0	1572.8	1572.4	1571.9
155°	1608.4	1607.5	1606.6	1605.8	1606.6	1607.5	1608.4	1609.2	1609.1	1607.9	1606.8
157.5°	1638.3	1636.8	1635.3	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8
160°	1657.6	1655.9	1654.2	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9
162.5°	1672.9	1670.9	1668.9	1667.0	1668.9	1670.9	1672.9	1674.8	1674.9	1673.2	1671.5
165°	1695.3	1692.7	1690.1	1687.5	1690.1	1692.7	1695.3	1697.8	1698.0	1695.7	1693.4
167.5°	1711.4	1708.5	1705.7	1702.8	1705.7	1708.5	1711.4	1714.3	1714.5	1711.9	1709.4
170°	1720.8	1717.9	1715.0	1712.1	1715.0	1717.9	1720.8	1723.6	1723.9	1721.6	1719.3
172.5°	1726.6	1723.5	1720.4	1717.3	1720.4	1723.5	1726.6	1729.8	1730.2	1727.9	1725.5
175°	1734.2	1730.7	1727.2	1723.8	1727.2	1730.7	1734.2	1737.6	1738.1	1735.5	1732.9
177.5°	1736.2	1733.5	1730.7	1727.9	1730.7	1733.5	1736.2	1739.0	1739.5	1737.6	1735.8
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	26.5	25.3	22.7	21.0	19.6	17.5	16.9	15.0	14.0	12.9	11.8
90°	30.3	28.5	26.2	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9
92.5°	29.2	27.5	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.3
95°	30.3	28.5	28.2	28.0	27.7	27.4	32.1	41.9	51.7	61.5	71.3
97.5°	34.4	34.2	66.4	98.6	130.7	162.9	175.9	169.8	163.7	157.6	151.5
100°	52.2	57.1	96.8	136.6	176.4	216.2	233.5	228.3	223.1	217.9	212.7
102.5°	222.1	275.0	280.2	285.4	290.5	295.7	296.4	292.6	288.8	285.0	281.2
105°	407.3	404.7	403.2	401.8	400.4	398.9	397.3	395.6	393.9	392.1	390.4
107.5°	505.8	504.6	502.6	500.6	498.7	496.7	495.3	494.4	493.6	492.7	491.8
110°	572.6	572.0	570.3	568.5	566.8	565.1	563.8	562.9	562.1	561.2	560.3



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.3	637.4	636.6	635.8	635.0	634.1	633.0	631.4	629.9	628.3	626.7
115°	732.1	731.5	731.8	732.1	732.4	732.7	732.4	731.5	730.7	729.8	728.9
117.5°	829.0	829.1	828.4	827.8	827.2	826.5	825.6	824.5	823.3	822.2	821.0
120°	887.8	887.2	887.5	887.8	888.1	888.3	887.9	886.8	885.6	884.4	883.3
122.5°	946.7	946.3	945.9	945.5	945.1	944.7	944.2	943.5	942.8	942.1	941.4
125°	1028.1	1027.3	1027.8	1028.4	1029.0	1029.6	1029.3	1028.1	1027.0	1025.8	1024.7
127.5°	1110.6	1110.8	1109.5	1108.1	1106.8	1105.5	1104.7	1104.4	1104.1	1103.8	1103.5
130°	1159.9	1159.6	1158.7	1157.8	1157.0	1156.1	1155.5	1155.2	1155.0	1154.7	1154.4
132.5°	1208.6	1208.3	1207.2	1206.1	1205.1	1204.0	1203.1	1202.6	1202.1	1201.6	1201.1
135°	1275.6	1275.0	1273.9	1272.7	1271.5	1270.4	1270.0	1270.3	1270.5	1270.8	1271.1
137.5°	1340.0	1339.3	1338.1	1336.8	1335.5	1334.3	1333.6	1333.5	1333.3	1333.2	1333.1
140°	1379.6	1378.8	1378.2	1377.6	1377.0	1376.5	1375.9	1375.3	1374.7	1374.2	1373.6
142.5°	1416.8	1416.1	1415.8	1415.4	1415.1	1414.7	1414.1	1413.0	1412.0	1410.9	1409.9
145°	1469.9	1469.6	1469.6	1469.6	1469.6	1469.6	1469.1	1468.3	1467.4	1466.5	1465.7
147.5°	1516.2	1516.0	1516.3	1516.6	1516.9	1517.2	1516.5	1514.9	1513.3	1511.6	1510.0
150°	1546.1	1546.1	1546.4	1546.7	1547.0	1547.2	1546.8	1545.7	1544.5	1543.4	1542.2
152.5°	1571.5	1571.0	1571.5	1572.0	1572.6	1573.1	1572.9	1571.9	1571.0	1570.1	1569.2
155°	1605.6	1604.5	1605.3	1606.2	1607.1	1607.9	1608.2	1607.9	1607.6	1607.3	1607.1
157.5°	1635.3	1633.8	1634.8	1635.7	1636.7	1637.7	1638.3	1638.4	1638.6	1638.8	1639.0
160°	1654.2	1652.5	1652.7	1653.0	1653.3	1653.6	1654.2	1655.0	1655.9	1656.8	1657.6
162.5°	1669.7	1668.0	1668.3	1668.6	1668.9	1669.2	1669.9	1671.0	1672.1	1673.1	1674.2
165°	1691.1	1688.8	1688.8	1688.8	1688.8	1688.8	1689.5	1690.9	1692.4	1693.8	1695.3
167.5°	1706.9	1704.3	1704.5	1704.7	1704.9	1705.0	1705.9	1707.4	1708.9	1710.4	1711.9
170°	1717.0	1714.7	1714.4	1714.1	1713.8	1713.6	1714.3	1716.0	1717.7	1719.5	1721.2
172.5°	1723.2	1720.9	1720.6	1720.4	1720.1	1719.8	1720.5	1722.2	1724.0	1725.7	1727.4
175°	1730.3	1727.7	1727.4	1727.1	1726.8	1726.5	1727.2	1729.0	1730.7	1732.4	1734.2
177.5°	1733.9	1732.1	1731.6	1731.2	1730.7	1730.2	1730.8	1732.4	1734.0	1735.7	1737.3
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	12.9	14.0	15.9	17.8	20.0	20.9	21.0	21.4	20.2	20.1	18.7
90°	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2	31.0
95°	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3	32.0
97.5°	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4	34.6
100°	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2	47.3
102.5°	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1	169.3
105°	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3	409.9
107.5°	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8	507.1
110°	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6	573.2





TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3	637.1
115°	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1	732.7
117.5°	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0	828.8
120°	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8	888.3
122.5°	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7	947.0
125°	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1	1029.0
127.5°	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6	1110.5
130°	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9	1160.1
132.5°	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6	1208.9
135°	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6	1276.2
137.5°	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0	1340.6
140°	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6	1380.5
142.5°	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8	1417.4
145°	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9	1470.1
147.5°	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2	1516.5
150°	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1	1546.1
152.5°	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5	1571.9
155°	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6	1606.8
157.5°	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3	1636.8
160°	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2	1655.9
162.5°	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7	1671.5
165°	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1	1693.4
167.5°	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9	1709.4
170°	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0	1719.3
172.5°	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2	1725.5
175°	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3	1732.9
177.5°	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9	1735.8
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	19.5	19.4	19.2	18.5	18.2	18.3	17.1
90°	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.7	574.3	575.0	575.9	576.8	577.6	578.5



TEST NUMBER: P332793

CATALOG NUMBER: S124DIW-S795D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)