

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333041-840

Luminaire Tested: **S124RDIW-S575D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333041-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D770U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5474.3 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43			43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37			37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31			31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27			27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23			23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20			20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18			18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16			16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14			14
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13			13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	1.8
10°-20°	268.8	4.9
20°-30°	388.2	7.1
30°-40°	440.0	8.0
40°-50°	424.9	7.8
50°-60°	353.4	6.5
60°-70°	244.0	4.5
70°-80°	123.7	2.3
80°-90°	34.6	0.6
90°-100°	34.3	0.6
100°-110°	218.6	4.0
110°-120°	418.1	7.6
120°-130°	530.7	9.7
130°-140°	567.9	10.4
140°-150°	531.0	9.7
150°-160°	428.2	7.8
160°-170°	276.2	5.0
170°-180°	95.2	1.7
0°-30°	753.5	13.8
0°-40°	1193.5	21.8
0°-60°	1971.8	36.0
0°-90°	2374.1	43.4
90°-120°	670.9	12.3
90°-150°	2300.6	42.0
90°-180°	3100.0	56.6
0°-180°	5474.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	2	10	16	21	22	4
95°	41	17	16	21	22	53
105°	226	230	234	239	214	236
115°	421	423	423	424	424	414
125°	592	595	594	596	597	529
135°	735	734	737	738	740	566
145°	847	849	849	850	852	529
155°	929	929	927	930	928	428
165°	980	976	976	981	975	277
175°	1002	998	998	1004	996	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	14.9	14.1	13.4	12.6	11.9	11.6	11.7	11.8	12.0	12.1	12.1
90°	2.2	4.0	6.0	7.8	9.6	11.2	12.5	13.8	15.1	16.5	17.5
92.5°	9.5	9.6	9.7	9.7	9.8	10.6	11.9	13.2	14.5	15.9	16.9
95°	41.2	35.5	29.9	24.2	18.6	15.9	16.0	16.2	16.4	16.5	17.5
97.5°	87.6	91.1	94.6	98.2	101.7	94.1	75.5	57.0	38.4	19.8	19.9
100°	122.9	125.9	129.0	131.9	134.9	124.9	102.0	79.0	55.9	33.0	30.2
102.5°	162.5	164.7	166.9	169.2	171.3	170.9	167.9	164.9	161.9	159.0	128.4
105°	225.6	226.6	227.6	228.6	229.6	230.6	231.4	232.2	233.1	233.9	235.4
107.5°	284.3	284.8	285.3	285.8	286.3	287.1	288.2	289.3	290.4	291.5	292.4
110°	323.9	324.4	324.9	325.4	325.8	326.6	327.6	328.6	329.6	330.5	330.9



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	362.2	363.1	364.1	364.9	365.8	366.5	367.0	367.4	367.9	368.4	368.3
115°	421.3	421.8	422.3	422.7	423.2	423.4	423.2	423.1	422.9	422.7	423.1
117.5°	474.5	475.1	475.8	476.5	477.2	477.7	478.1	478.4	478.8	479.2	479.1
120°	510.5	511.2	511.8	512.5	513.1	513.4	513.2	513.1	512.9	512.7	513.1
122.5°	544.1	544.4	544.8	545.2	545.6	545.9	546.2	546.4	546.6	546.9	547.1
125°	592.2	592.9	593.5	594.2	594.8	595.0	594.7	594.4	594.0	593.7	594.2
127.5°	637.7	637.9	638.1	638.2	638.4	638.9	639.6	640.5	641.2	642.0	641.9
130°	667.1	667.3	667.5	667.6	667.8	668.1	668.6	669.1	669.6	670.1	670.3
132.5°	694.2	694.5	694.8	695.0	695.3	695.8	696.4	697.1	697.7	698.3	698.5
135°	734.6	734.5	734.3	734.1	734.0	734.2	734.9	735.5	736.2	736.9	737.2
137.5°	770.4	770.5	770.6	770.6	770.7	771.1	771.8	772.5	773.4	774.1	774.4
140°	793.9	794.2	794.5	794.9	795.2	795.5	795.9	796.2	796.5	796.9	797.3
142.5°	814.9	815.5	816.1	816.6	817.2	817.6	817.8	818.0	818.2	818.4	818.8
145°	847.1	847.6	848.1	848.6	849.1	849.3	849.3	849.3	849.3	849.3	849.5
147.5°	872.7	873.6	874.5	875.5	876.5	876.8	876.7	876.5	876.3	876.2	876.3
150°	891.3	891.9	892.6	893.3	893.9	894.2	894.0	893.8	893.7	893.5	893.5
152.5°	906.9	907.4	908.0	908.5	909.0	909.1	908.8	908.6	908.3	908.0	908.2
155°	928.8	929.0	929.1	929.3	929.5	929.3	928.8	928.3	927.8	927.3	928.0
157.5°	947.3	947.2	947.1	947.0	946.8	946.4	945.9	945.3	944.7	944.2	945.0
160°	958.0	957.5	957.0	956.5	956.0	955.6	955.5	955.3	955.1	955.0	956.0
162.5°	967.6	966.9	966.3	965.7	965.0	964.6	964.5	964.3	964.1	964.0	965.0
165°	979.8	978.9	978.1	977.2	976.4	976.0	976.0	976.0	976.0	976.0	977.3
167.5°	989.4	988.5	987.6	986.7	985.8	985.4	985.3	985.2	985.1	985.0	986.4
170°	994.7	993.7	992.7	991.7	990.8	990.3	990.5	990.7	990.8	991.0	992.3
172.5°	998.4	997.3	996.3	995.3	994.3	993.9	994.1	994.2	994.4	994.6	995.9
175°	1002.2	1001.2	1000.3	999.3	998.3	997.8	997.9	998.2	998.4	998.5	1000.0
177.5°	1004.0	1003.1	1002.2	1001.2	1000.3	1000.0	1000.3	1000.5	1000.8	1001.0	1002.1
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	12.2	12.3	12.3	12.5	12.7	12.9	13.1	13.3
90°	18.5	19.5	20.5	21.1	21.5	21.8	22.1	22.5
92.5°	17.9	18.9	19.9	20.4	20.5	20.6	20.6	20.7
95°	18.5	19.5	20.5	21.1	21.2	21.4	21.6	21.7
97.5°	20.0	20.1	20.2	20.3	20.5	20.7	20.8	21.0
100°	27.4	24.4	21.6	20.3	20.5	20.7	20.8	21.0
102.5°	97.9	67.3	36.8	21.4	21.5	21.5	21.5	21.6
105°	236.9	238.3	239.8	237.6	231.7	225.6	219.6	213.7
107.5°	293.1	293.8	294.6	295.2	295.9	296.5	297.1	297.7
110°	331.2	331.5	331.9	332.3	332.9	333.4	333.9	334.4



TEST NUMBER: P333041-840

CATALOG NUMBER: S124RDIW-S575D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.2	368.2	368.1	368.4	369.0	369.6	370.3	370.9
115°	423.4	423.7	424.1	424.2	424.2	424.2	424.2	424.2
117.5°	479.0	479.0	478.9	478.8	478.8	478.7	478.6	478.6
120°	513.4	513.7	514.0	514.0	513.7	513.4	513.1	512.7
122.5°	547.3	547.5	547.8	547.6	547.3	546.9	546.6	546.3
125°	594.7	595.2	595.7	596.0	596.2	596.3	596.5	596.7
127.5°	641.8	641.7	641.6	641.5	641.4	641.2	641.1	641.0
130°	670.4	670.7	670.9	670.9	670.9	670.9	670.9	670.9
132.5°	698.6	698.8	699.0	699.0	698.9	698.7	698.6	698.5
135°	737.5	737.9	738.2	738.5	738.8	739.2	739.5	739.8
137.5°	774.8	775.2	775.5	775.7	775.6	775.5	775.4	775.3
140°	797.8	798.3	798.8	799.2	799.3	799.5	799.7	799.8
142.5°	819.2	819.5	819.9	820.1	820.1	820.1	820.2	820.2
145°	849.6	849.8	850.0	850.2	850.5	850.9	851.2	851.5
147.5°	876.4	876.6	876.7	876.9	877.0	877.2	877.4	877.5
150°	893.5	893.5	893.5	893.6	893.8	893.9	894.1	894.2
152.5°	908.5	908.7	909.0	909.1	909.0	908.9	908.8	908.7
155°	928.6	929.3	929.9	930.0	929.5	929.0	928.5	928.1
157.5°	945.9	946.8	947.7	947.7	946.8	945.9	945.0	944.2
160°	957.0	958.0	959.0	959.0	958.0	957.0	956.0	955.0
162.5°	966.0	966.9	968.0	968.0	966.8	965.6	964.5	963.4
165°	978.7	980.0	981.3	981.3	979.8	978.3	976.7	975.2
167.5°	988.0	989.4	990.9	990.8	989.1	987.4	985.7	984.1
170°	993.6	995.0	996.3	996.1	994.5	992.8	991.2	989.5
172.5°	997.2	998.6	999.9	999.7	997.8	996.1	994.3	992.5
175°	1001.5	1003.0	1004.5	1004.2	1002.2	1000.3	998.3	996.2
177.5°	1003.2	1004.2	1005.3	1005.0	1003.4	1001.8	1000.3	998.7
180°	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2

(END OF REPORT)