

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333066-840

Luminaire Tested: **S124RDIW-S795D1050U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333066-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1050U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6915.1 lumens  
Efficiency: N/A  
Efficacy: 131.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	47	46	45				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11326	11326	11326
5°	11351	11212	11281
10°	11280	11077	11077
15°	11150	10845	10764
20°	10972	10539	10345
25°	10745	10180	9922
30°	10523	9803	9392
35°	10279	9411	8861
40°	9985	8965	8286
45°	9712	8524	7702
50°	9403	8013	7082
55°	9071	7484	6410
60°	8707	6902	5724
65°	8373	6178	5049
70°	7886	5375	4286
75°	7271	4457	3484
80°	6341	3394	3199
85°	5372	3084	2881



TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	1.9
10°-20°	367.5	5.3
20°-30°	530.6	7.7
30°-40°	601.5	8.7
40°-50°	580.8	8.4
50°-60°	483.0	7.0
60°-70°	333.5	4.8
70°-80°	169.1	2.4
80°-90°	47.3	0.7
90°-100°	87.2	1.3
100°-110°	258.4	3.7
110°-120°	438.7	6.3
120°-130°	578.4	8.4
130°-140°	649.6	9.4
140°-150°	638.4	9.2
150°-160°	536.9	7.8
160°-170°	357.2	5.2
170°-180°	125.1	1.8
0°-30°	1029.9	14.9
0°-40°	1631.4	23.6
0°-60°	2695.2	39.0
0°-90°	3245.1	46.9
90°-120°	784.3	11.3
90°-150°	2650.7	38.3
90°-180°	3670.0	53.1
0°-180°	6915.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1401	1396	1384	1394	1392	133
15°	1334	1324	1298	1295	1288	376
25°	1206	1186	1143	1125	1114	556
35°	1043	1008	955	919	899	651
45°	851	810	747	696	675	656
55°	644	600	532	478	455	576
65°	438	391	323	279	264	433
75°	233	193	143	119	112	246
85°	58	38	33	31	31	65
90°	3	14	22	28	31	7
95°	61	70	78	81	81	68
105°	238	240	244	247	250	253
115°	446	446	444	443	442	440
125°	650	650	649	647	644	579
135°	838	844	844	842	839	648
145°	1018	1022	1023	1022	1019	637
155°	1166	1166	1165	1169	1165	536
165°	1270	1267	1264	1270	1266	358
175°	1321	1316	1315	1321	1315	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1406.3	1405.5	1404.7	1404.0	1403.2	1401.8	1399.7	1397.7	1395.5	1393.4	1395.5
5°	1400.7	1399.8	1398.8	1397.9	1396.8	1395.0	1392.1	1389.3	1386.3	1383.5	1385.9
7.5°	1388.1	1387.0	1386.0	1385.0	1384.0	1381.7	1378.0	1374.2	1370.5	1366.8	1368.3
10°	1376.0	1374.8	1373.6	1372.4	1371.2	1368.5	1364.2	1359.9	1355.6	1351.3	1352.2
12.5°	1360.5	1359.2	1357.8	1356.3	1355.0	1351.8	1346.8	1341.6	1336.6	1331.5	1332.1
15°	1334.1	1332.0	1329.8	1327.7	1325.5	1321.5	1315.5	1309.5	1303.5	1297.6	1297.1
17.5°	1302.1	1299.0	1295.9	1292.8	1289.7	1284.5	1277.4	1270.2	1263.0	1255.9	1254.6
20°	1277.2	1274.0	1271.0	1267.9	1264.8	1259.2	1251.0	1242.9	1234.8	1226.7	1224.8
22.5°	1249.7	1246.2	1242.7	1239.2	1235.8	1229.6	1220.9	1212.2	1203.6	1194.9	1192.0
25°	1206.3	1201.9	1197.7	1193.4	1189.1	1182.0	1172.3	1162.5	1152.7	1142.9	1138.8
27.5°	1160.7	1155.4	1149.9	1144.6	1139.1	1131.3	1120.7	1110.3	1099.8	1089.4	1084.4
30°	1128.9	1123.0	1117.0	1111.1	1105.1	1096.5	1085.3	1074.1	1062.8	1051.6	1045.6
32.5°	1095.4	1088.7	1082.0	1075.2	1068.5	1059.3	1047.7	1036.1	1024.5	1012.9	1006.0
35°	1043.0	1035.4	1027.7	1020.1	1012.5	1002.7	990.8	978.8	966.8	954.9	946.8
37.5°	986.9	979.1	971.2	963.3	955.4	944.9	931.7	918.5	905.2	892.0	882.9
40°	947.5	939.6	931.7	923.8	915.9	905.1	891.5	878.0	864.3	850.7	840.7
42.5°	909.6	901.3	893.1	884.8	876.6	865.4	851.2	837.0	822.8	808.6	798.4
45°	850.7	841.9	833.0	824.3	815.4	803.9	789.5	775.2	760.8	746.6	734.9
47.5°	789.9	780.8	771.7	762.5	753.5	741.4	726.6	711.7	696.8	681.9	669.7
50°	748.7	739.4	730.0	720.7	711.4	699.1	683.9	668.6	653.3	638.0	626.1
52.5°	706.6	697.5	688.3	679.2	670.1	657.7	642.1	626.4	610.8	595.1	583.0
55°	644.5	634.9	625.4	615.8	606.3	593.8	578.2	562.7	547.2	531.7	519.3
57.5°	583.1	573.1	563.2	553.3	543.3	530.7	515.4	500.2	484.9	469.6	457.1
60°	539.3	529.7	520.2	510.6	501.0	488.7	473.3	458.1	442.8	427.5	415.1
62.5°	499.7	489.8	479.9	469.9	460.0	447.2	431.5	415.9	400.2	384.6	373.0
65°	438.3	428.0	417.7	407.5	397.2	384.5	369.1	353.9	338.6	323.4	313.1
67.5°	374.5	364.7	354.8	345.0	335.1	323.2	308.9	294.8	280.5	266.4	257.5
70°	334.1	324.1	314.0	304.0	294.0	282.2	268.5	254.9	241.4	227.7	219.8
72.5°	291.1	282.1	273.0	263.9	254.8	243.9	231.1	218.1	205.3	192.5	185.7
75°	233.1	224.3	215.4	206.6	197.7	187.7	176.5	165.3	154.1	142.9	137.3
77.5°	174.2	166.7	159.3	151.8	144.2	135.9	126.9	117.9	108.8	99.7	96.4
80°	136.4	129.5	122.6	115.6	108.8	101.7	94.5	87.4	80.2	73.0	72.3
82.5°	103.8	97.5	91.1	84.7	78.4	73.1	69.1	64.9	60.8	56.8	56.1
85°	58.0	53.2	48.5	43.7	38.9	36.2	35.4	34.7	34.0	33.3	32.8
87.5°	20.4	19.4	18.3	17.3	16.3	15.9	16.1	16.2	16.4	16.6	16.7
90°	3.0	5.6	8.1	10.6	13.0	15.2	17.1	18.9	20.7	22.5	23.8
92.5°	21.9	24.7	27.7	30.5	33.3	35.4	36.7	38.0	39.3	40.5	41.3
95°	61.4	63.4	65.4	67.6	69.6	71.4	73.0	74.5	76.1	77.8	78.5
97.5°	107.2	108.9	110.5	112.1	113.8	115.5	117.3	119.3	121.1	123.0	123.8
100°	143.2	144.1	145.0	145.9	146.8	148.3	150.4	152.4	154.5	156.5	156.9
102.5°	180.9	181.3	181.6	182.0	182.3	183.4	185.3	187.1	189.0	190.9	191.6
105°	238.3	238.6	238.8	239.0	239.2	239.8	240.8	241.7	242.6	243.5	244.2
107.5°	298.7	299.0	299.2	299.5	299.8	300.0	300.1	300.3	300.4	300.5	301.2
110°	339.6	340.1	340.5	341.0	341.4	341.5	341.3	341.1	340.9	340.6	340.2



TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.2	382.3	382.4	382.4	382.5	382.4	382.0	381.6	381.2	380.8	380.7
115°	446.1	446.1	446.1	446.1	446.1	445.9	445.4	444.9	444.4	444.0	443.7
117.5°	506.2	506.3	506.5	506.8	507.0	506.9	506.5	506.2	505.9	505.5	504.8
120°	546.3	547.2	548.2	549.1	550.0	550.1	549.4	548.7	548.1	547.3	546.2
122.5°	588.0	588.4	588.8	589.2	589.5	589.6	589.2	588.9	588.5	588.2	587.4
125°	649.6	649.6	649.6	649.6	649.6	649.5	649.2	649.0	648.8	648.6	648.1
127.5°	705.5	706.2	706.8	707.5	708.2	708.4	708.0	707.6	707.3	706.9	706.5
130°	744.8	745.5	746.1	746.8	747.5	747.8	747.8	747.8	747.8	747.8	747.4
132.5°	784.9	785.4	785.9	786.4	786.9	787.0	786.9	786.7	786.5	786.3	785.9
135°	837.9	839.2	840.6	841.9	843.3	844.0	844.0	844.0	844.0	844.0	843.5
137.5°	895.5	896.2	896.9	897.5	898.1	898.6	899.0	899.4	899.7	900.1	899.5
140°	934.0	934.5	934.9	935.4	935.8	936.0	936.0	936.0	936.0	936.0	935.8
142.5°	969.3	969.7	970.2	970.6	971.1	971.2	971.0	970.8	970.7	970.5	970.4
145°	1017.9	1018.9	1019.8	1020.7	1021.6	1022.1	1022.4	1022.6	1022.8	1023.0	1022.8
147.5°	1066.2	1067.3	1068.4	1069.4	1070.6	1071.1	1070.9	1070.7	1070.5	1070.3	1070.2
150°	1095.7	1096.6	1097.5	1098.4	1099.3	1099.7	1099.7	1099.7	1099.7	1099.7	1099.7
152.5°	1123.5	1124.1	1124.6	1125.1	1125.7	1126.0	1126.2	1126.4	1126.6	1126.8	1127.3
155°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.7	1165.5	1165.3	1166.2
157.5°	1202.2	1201.8	1201.4	1201.0	1200.6	1200.4	1200.3	1200.3	1200.2	1200.2	1200.9
160°	1223.6	1223.4	1223.0	1222.8	1222.6	1222.4	1222.1	1221.9	1221.7	1221.5	1222.1
162.5°	1243.1	1242.6	1242.0	1241.4	1240.8	1240.4	1240.2	1240.0	1239.7	1239.5	1240.7
165°	1269.6	1268.9	1268.2	1267.6	1266.9	1266.3	1265.9	1265.4	1265.0	1264.5	1265.9
167.5°	1289.8	1288.9	1288.0	1287.0	1286.1	1285.6	1285.7	1285.7	1285.7	1285.8	1287.1
170°	1301.3	1300.2	1299.0	1297.9	1296.8	1296.3	1296.6	1296.8	1297.0	1297.2	1298.6
172.5°	1309.5	1308.5	1307.6	1306.7	1305.7	1305.3	1305.3	1305.4	1305.4	1305.4	1307.0
175°	1320.7	1319.6	1318.5	1317.4	1316.2	1315.6	1315.2	1315.0	1314.8	1314.6	1316.2
177.5°	1324.4	1323.5	1322.6	1321.7	1320.8	1320.3	1320.3	1320.3	1320.3	1320.3	1321.6
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8



TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1397.7	1399.7	1401.8	1402.8	1402.6	1402.4	1402.2	1402.0
5°	1388.3	1390.7	1393.1	1394.0	1393.5	1393.1	1392.6	1392.1
7.5°	1369.8	1371.4	1372.9	1373.2	1372.5	1371.7	1371.0	1370.2
10°	1353.2	1354.1	1355.1	1355.1	1354.1	1353.2	1352.2	1351.3
12.5°	1332.7	1333.2	1333.8	1333.4	1332.1	1330.8	1329.4	1328.1
15°	1296.7	1296.2	1295.7	1294.6	1292.9	1291.2	1289.6	1287.9
17.5°	1253.2	1251.9	1250.5	1248.6	1246.1	1243.5	1241.0	1238.5
20°	1222.8	1220.9	1219.0	1216.6	1213.5	1210.3	1207.2	1204.2
22.5°	1189.2	1186.3	1183.5	1180.7	1178.2	1175.7	1173.2	1170.6
25°	1134.8	1130.7	1126.7	1123.5	1121.1	1118.7	1116.3	1113.9
27.5°	1079.3	1074.4	1069.3	1065.1	1061.7	1058.2	1054.8	1051.4
30°	1039.7	1033.7	1027.7	1022.8	1019.1	1015.2	1011.4	1007.5
32.5°	999.1	992.2	985.2	980.0	976.3	972.7	969.1	965.4
35°	938.7	930.6	922.5	916.3	912.0	907.7	903.3	899.1
37.5°	873.8	864.7	855.7	849.0	844.8	840.4	836.2	831.8
40°	830.7	820.6	810.6	803.4	799.2	794.9	790.6	786.3
42.5°	788.2	778.0	767.8	760.4	755.9	751.4	747.0	742.5
45°	723.2	711.4	699.7	691.8	687.4	683.2	678.8	674.6
47.5°	657.6	645.5	633.4	624.9	620.3	615.5	610.8	606.0
50°	614.2	602.3	590.3	582.1	577.5	573.0	568.5	563.9
52.5°	570.9	558.8	546.5	538.2	533.4	528.7	524.0	519.3
55°	506.9	494.4	482.1	473.6	469.1	464.5	460.0	455.4
57.5°	444.4	431.8	419.2	411.2	407.8	404.3	400.9	397.5
60°	402.7	390.3	377.9	369.7	366.0	362.1	358.3	354.5
62.5°	361.6	350.2	338.7	331.4	328.4	325.4	322.2	319.2
65°	302.8	292.6	282.3	275.7	272.9	269.9	267.1	264.3
67.5°	248.7	239.9	231.1	225.1	222.0	218.7	215.6	212.5
70°	212.0	204.1	196.2	191.1	188.7	186.3	183.9	181.6
72.5°	179.0	172.3	165.5	161.1	159.0	156.7	154.5	152.3
75°	131.9	126.4	120.9	117.4	116.0	114.6	113.1	111.7
77.5°	93.3	90.1	86.8	85.0	84.6	84.2	83.8	83.3
80°	71.6	70.9	70.2	69.7	69.5	69.2	69.0	68.8
82.5°	55.6	55.1	54.6	54.2	54.0	53.7	53.5	53.3
85°	32.3	31.9	31.4	31.1	31.1	31.1	31.1	31.1
87.5°	16.7	16.8	16.9	17.1	17.4	17.6	17.9	18.2
90°	25.2	26.6	28.0	28.9	29.3	29.8	30.2	30.7
92.5°	42.1	42.9	43.8	44.3	44.6	44.8	45.1	45.4
95°	79.1	79.8	80.5	80.8	80.8	80.8	80.8	80.8
97.5°	124.6	125.4	126.2	126.6	126.6	126.6	126.6	126.6
100°	157.4	157.8	158.3	158.5	158.5	158.5	158.5	158.5
102.5°	192.2	192.8	193.5	193.9	194.0	194.2	194.4	194.6
105°	244.9	245.5	246.2	246.9	247.6	248.2	248.9	249.6
107.5°	301.8	302.5	303.2	303.4	303.4	303.4	303.3	303.3
110°	339.7	339.3	338.8	339.0	339.6	340.3	341.0	341.7





TEST NUMBER: P333066-840

CATALOG NUMBER: S124RDIW-S795D1050U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.6	380.5	380.4	380.4	380.6	380.7	380.8	381.0
115°	443.5	443.3	443.1	442.8	442.6	442.4	442.2	441.9
117.5°	504.0	503.2	502.5	501.9	501.4	501.0	500.5	500.1
120°	545.0	543.9	542.8	542.4	542.9	543.3	543.8	544.2
122.5°	586.7	585.9	585.1	584.3	583.5	582.7	581.9	581.1
125°	647.7	647.2	646.8	646.3	645.9	645.4	645.0	644.5
127.5°	706.0	705.6	705.1	704.7	704.3	704.0	703.6	703.3
130°	746.9	746.5	746.0	745.4	744.5	743.6	742.7	741.7
132.5°	785.4	785.0	784.5	784.1	783.8	783.4	782.9	782.6
135°	843.1	842.6	842.2	841.6	840.9	840.2	839.6	838.9
137.5°	898.9	898.3	897.7	897.5	897.6	897.8	897.9	898.0
140°	935.6	935.4	935.1	934.9	934.7	934.5	934.2	934.0
142.5°	970.4	970.3	970.3	970.2	970.2	970.2	970.1	970.1
145°	1022.6	1022.4	1022.1	1021.7	1021.0	1020.3	1019.7	1019.0
147.5°	1070.0	1069.8	1069.5	1069.3	1069.1	1068.9	1068.6	1068.4
150°	1099.7	1099.7	1099.7	1099.6	1099.4	1099.2	1098.9	1098.7
152.5°	1127.8	1128.4	1128.9	1128.9	1128.3	1127.7	1127.1	1126.6
155°	1167.1	1168.0	1168.9	1168.9	1168.0	1167.1	1166.2	1165.3
157.5°	1201.6	1202.2	1203.0	1203.0	1202.1	1201.3	1200.6	1199.8
160°	1222.8	1223.6	1224.3	1224.0	1222.8	1221.7	1220.6	1219.4
162.5°	1241.9	1243.1	1244.5	1244.5	1243.3	1242.2	1241.0	1239.9
165°	1267.2	1268.6	1269.9	1270.1	1269.2	1268.3	1267.4	1266.5
167.5°	1288.5	1289.8	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
170°	1299.9	1301.3	1302.6	1302.5	1301.0	1299.4	1297.8	1296.2
172.5°	1308.5	1310.0	1311.6	1311.5	1310.0	1308.4	1306.8	1305.1
175°	1317.8	1319.4	1321.0	1321.0	1319.4	1317.8	1316.2	1314.6
177.5°	1322.9	1324.1	1325.4	1325.3	1323.8	1322.4	1321.0	1319.5
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)