

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333072-840

Luminaire Tested: **S124RDIW-S795D1560U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333072-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1560U840-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8838.0 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38								
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33								
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28								
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24								
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18								
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16								
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15								
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	17	16	13								
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12								
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.5
10°-20°	389.6	4.4
20°-30°	609.4	6.9
30°-40°	677.4	7.7
40°-50°	601.0	6.8
50°-60°	468.4	5.3
60°-70°	306.6	3.5
70°-80°	150.8	1.7
80°-90°	43.1	0.5
90°-100°	129.9	1.5
100°-110°	384.7	4.4
110°-120°	652.9	7.4
120°-130°	861.0	9.7
130°-140°	966.9	10.9
140°-150°	950.1	10.8
150°-160°	799.1	9.0
160°-170°	531.7	6.0
170°-180°	186.2	2.1
0°-30°	1128.1	12.8
0°-40°	1805.6	20.4
0°-60°	2875.0	32.5
0°-90°	3375.5	38.2
90°-120°	1167.5	13.2
90°-150°	3945.5	44.6
90°-180°	5463.0	61.8
0°-180°	8838.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	46	4	46	4	46	24
95°	120	91	120	91	120	125
105°	372	355	372	355	372	392
115°	658	664	658	664	658	650
125°	959	967	959	967	959	856
135°	1249	1247	1249	1247	1249	964
145°	1517	1515	1517	1515	1517	949
155°	1734	1736	1734	1736	1734	798
165°	1885	1890	1885	1890	1885	531
175°	1957	1966	1957	1966	1957	186
180°	1969	1969	1969	1969	1969	



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	18.6	18.0	18.3	18.2	18.5	17.8	17.8	18.3	17.0	17.0	16.5
90°	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6	35.5	33.5	30.8
92.5°	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7	61.5	60.3	58.4
95°	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8	116.7	115.7	113.4
97.5°	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5	184.2	183.0	180.3
100°	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3	233.7	233.0	229.9
102.5°	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0	285.1	284.2	281.3
105°	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5	363.5	362.4	361.0
107.5°	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3	448.3	447.4	447.2
110°	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7	506.3	507.1	507.4



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4	566.6	566.7	567.3
115°	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1	660.6	660.9	661.6
117.5°	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2	751.3	752.6	753.0
120°	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2	812.9	814.7	815.7
122.5°	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2	874.4	875.6	876.1
125°	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0	964.7	965.4	965.7
127.5°	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9	1051.5	1052.2	1052.8
130°	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8	1112.5	1113.1	1113.1
132.5°	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0	1169.7	1170.3	1170.6
135°	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9	1255.6	1256.3	1256.3
137.5°	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0	1338.8	1339.7	1339.2
140°	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6	1392.9	1393.3	1393.3
142.5°	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3	1444.4	1444.4	1444.7
145°	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4
147.5°	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6	1592.8	1593.1	1593.4
150°	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7	1677.9	1677.1	1676.9
155°	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3	1734.7
157.5°	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5	1787.5	1786.5	1786.6
160°	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2	1819.2	1818.2	1818.5
162.5°	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6	1846.7	1844.9	1845.2
165°	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1	1884.1	1882.1	1882.8
167.5°	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8	1915.8	1913.8	1913.7
170°	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9	1932.8	1930.8	1930.5
172.5°	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6	1945.3	1943.0	1942.9
175°	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7	1957.0
177.5°	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0	1967.1	1965.2	1965.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	16.0	14.9	15.2	14.6	14.3	15.2	15.9	15.6	14.9	14.4	13.9
90°	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5	8.3	12.0	15.8
92.5°	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6	36.9	41.1	45.3
95°	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4	94.4	97.5	100.5
97.5°	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6	162.0	164.4	166.9
100°	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2	214.5	215.9	217.2
102.5°	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2	269.7	270.3	270.8
105°	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8	355.2	355.5	355.8
107.5°	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6	445.0	445.5	445.9
110°	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5	506.2	506.9	507.6



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9	569.1	569.2	569.3
115°	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9
117.5°	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5	753.7	754.0	754.3
120°	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1	814.5	815.9	817.2
122.5°	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3	875.8	876.4	876.9
125°	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9	966.9	966.9	966.9
127.5°	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1	1051.1	1052.1	1053.1
130°	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5	1109.5	1110.5	1111.6
132.5°	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2	1169.0	1169.7	1170.4
135°	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1	1249.1	1251.1	1253.2
137.5°	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0	1333.9	1334.8	1335.8
140°	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3	1390.9	1391.6	1392.3
142.5°	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6	1443.3	1444.0	1444.6
145°	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1	1516.4	1517.8	1519.1
147.5°	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0	1588.6	1590.2	1591.9
150°	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8	1632.1	1633.6	1634.9
152.5°	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2	1673.0	1673.9	1674.7
155°	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5	1788.9	1788.3	1787.7
160°	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2	1820.8	1820.5	1820.2
162.5°	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4	1849.6	1848.7	1847.8
165°	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7	1888.6	1887.6	1886.6
167.5°	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9	1918.4	1917.0	1915.6
170°	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9	1935.2	1933.5	1931.8
172.5°	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0	1947.6	1946.2	1944.8
175°	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8	1964.1	1962.5	1960.8
177.5°	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3	1969.9	1968.6	1967.2
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	14.6	14.8	15.3	15.0	16.1	16.6	16.6	17.0	17.8	17.4	17.6
90°	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6	39.6	41.6	43.0
92.5°	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7	63.9	65.1	65.9
95°	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8	118.8	119.8	120.3
97.5°	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5	186.7	187.9	188.5
100°	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3	235.0	235.7	236.0
102.5°	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0	287.0	287.9	288.5
105°	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5	365.5	366.5	367.5
107.5°	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3	450.2	451.2	451.6
110°	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7	505.0	504.3	504.5



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4	566.3	566.2	566.2
115°	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1	659.8	659.5	659.1
117.5°	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2	749.1	747.9	747.0
120°	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2	809.6	807.9	807.4
122.5°	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2	872.1	871.0	869.8
125°	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0	963.4	962.7	962.0
127.5°	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9	1050.2	1049.5	1048.8
130°	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8	1111.1	1110.3	1109.3
132.5°	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0	1168.3	1167.6	1167.0
135°	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9	1254.3	1253.5	1252.6
137.5°	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0	1337.1	1336.2	1335.8
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6	1392.3	1391.9	1391.6
142.5°	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3	1444.2	1444.2	1444.1
145°	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.7
147.5°	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6	1592.3	1592.0	1591.6
150°	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8
152.5°	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7	1679.5	1680.3	1680.3
155°	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8
157.5°	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5	1789.5	1790.5	1790.4
160°	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2	1821.2	1822.2	1821.8
162.5°	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6	1850.4	1852.2	1852.3
165°	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1	1888.1	1890.2	1890.6
167.5°	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8	1919.9	1921.9	1921.9
170°	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9	1936.9	1938.9	1938.7
172.5°	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6	1949.8	1952.2	1952.2
175°	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2
177.5°	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0	1970.9	1972.8	1972.7
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	18.6	18.3	18.0	18.6	18.0	18.3	18.6	17.6	17.4	17.8	17.0
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	41.6	39.6	37.6
92.5°	66.3	66.8	67.2	67.6	67.2	66.8	66.3	65.9	65.1	63.9	62.7
95°	120.3	120.3	120.3	120.3	120.3	120.3	120.3	120.3	119.8	118.8	117.8
97.5°	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.5	187.9	186.7	185.5
100°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	235.7	235.0	234.3
102.5°	288.8	289.1	289.3	289.6	289.3	289.1	288.8	288.5	287.9	287.0	286.0
105°	368.5	369.5	370.5	371.5	370.5	369.5	368.5	367.5	366.5	365.5	364.5
107.5°	451.5	451.5	451.4	451.3	451.4	451.5	451.5	451.6	451.2	450.2	449.3
110°	505.5	506.5	507.6	508.6	507.6	506.5	505.5	504.5	504.3	505.0	505.7



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	566.4	566.6	566.8	567.0	566.8	566.6	566.4	566.2	566.2	566.3	566.4
115°	658.8	658.5	658.1	657.8	658.1	658.5	658.8	659.1	659.5	659.8	660.1
117.5°	746.3	745.7	745.0	744.3	745.0	745.7	746.3	747.0	747.9	749.1	750.2
120°	808.1	808.7	809.4	810.1	809.4	808.7	808.1	807.4	807.9	809.6	811.2
122.5°	868.6	867.4	866.2	864.9	866.2	867.4	868.6	869.8	871.0	872.1	873.2
125°	961.3	960.7	960.0	959.3	960.0	960.7	961.3	962.0	962.7	963.4	964.0
127.5°	1048.3	1047.8	1047.2	1046.7	1047.2	1047.8	1048.3	1048.8	1049.5	1050.2	1050.9
130°	1108.0	1106.7	1105.3	1104.0	1105.3	1106.7	1108.0	1109.3	1110.3	1111.1	1111.8
132.5°	1166.5	1166.0	1165.4	1164.9	1165.4	1166.0	1166.5	1167.0	1167.6	1168.3	1169.0
135°	1251.6	1250.6	1249.6	1248.6	1249.6	1250.6	1251.6	1252.6	1253.5	1254.3	1254.9
137.5°	1336.1	1336.3	1336.5	1336.7	1336.5	1336.3	1336.1	1335.8	1336.2	1337.1	1338.0
140°	1391.3	1390.9	1390.6	1390.3	1390.6	1390.9	1391.3	1391.6	1391.9	1392.3	1392.6
142.5°	1444.0	1444.0	1443.9	1443.8	1443.9	1444.0	1444.0	1444.1	1444.2	1444.2	1444.3
145°	1519.6	1518.6	1517.6	1516.6	1517.6	1518.6	1519.6	1520.7	1521.4	1521.7	1522.1
147.5°	1591.3	1591.0	1590.6	1590.3	1590.6	1591.0	1591.3	1591.6	1592.0	1592.3	1592.6
150°	1636.4	1636.1	1635.8	1635.4	1635.8	1636.1	1636.4	1636.8	1636.9	1636.9	1636.9
152.5°	1679.4	1678.6	1677.7	1676.8	1677.7	1678.6	1679.4	1680.3	1680.3	1679.5	1678.7
155°	1738.4	1737.1	1735.8	1734.3	1735.8	1737.1	1738.4	1739.8	1739.8	1738.4	1737.1
157.5°	1789.3	1788.2	1787.0	1785.8	1787.0	1788.2	1789.3	1790.4	1790.5	1789.5	1788.5
160°	1820.2	1818.5	1816.7	1815.0	1816.7	1818.5	1820.2	1821.8	1822.2	1821.2	1820.2
162.5°	1850.6	1849.0	1847.2	1845.5	1847.2	1849.0	1850.6	1852.3	1852.2	1850.4	1848.6
165°	1889.2	1887.8	1886.4	1885.1	1886.4	1887.8	1889.2	1890.6	1890.2	1888.1	1886.1
167.5°	1919.8	1917.6	1915.5	1913.4	1915.5	1917.6	1919.8	1921.9	1921.9	1919.9	1917.8
170°	1936.4	1934.0	1931.7	1929.2	1931.7	1934.0	1936.4	1938.7	1938.9	1936.9	1934.9
172.5°	1949.7	1947.4	1945.0	1942.7	1945.0	1947.4	1949.7	1952.2	1952.2	1949.8	1947.6
175°	1963.8	1961.5	1959.0	1956.7	1959.0	1961.5	1963.8	1966.2	1966.2	1963.8	1961.5
177.5°	1970.4	1968.3	1966.2	1964.0	1966.2	1968.3	1970.4	1972.7	1972.8	1970.9	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	16.6	16.6	16.1	15.0	15.3	14.8	14.6	13.9	14.4	14.9	15.6
90°	35.5	33.5	30.8	28.1	25.3	22.7	19.5	15.8	12.0	8.3	4.5
92.5°	61.5	60.3	58.4	56.6	54.6	52.7	49.7	45.3	41.1	36.9	32.6
95°	116.7	115.7	113.4	111.0	108.7	106.2	103.5	100.5	97.5	94.4	91.4
97.5°	184.2	183.0	180.3	177.4	174.7	172.0	169.4	166.9	164.4	162.0	159.6
100°	233.7	233.0	229.9	226.9	223.9	220.8	218.6	217.2	215.9	214.5	213.2
102.5°	285.1	284.2	281.3	278.6	275.8	273.1	271.4	270.8	270.3	269.7	269.2
105°	363.5	362.4	361.0	359.7	358.3	357.0	356.2	355.8	355.5	355.2	354.8
107.5°	448.3	447.4	447.2	447.0	446.8	446.6	446.3	445.9	445.5	445.0	444.6
110°	506.3	507.1	507.4	507.8	508.1	508.5	508.3	507.6	506.9	506.2	505.5



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	566.6	566.7	567.3	567.9	568.6	569.2	569.5	569.3	569.2	569.1	568.9
115°	660.6	660.9	661.6	662.2	662.9	663.6	663.9	663.9	663.9	663.9	663.9
117.5°	751.3	752.6	753.0	753.5	754.0	754.5	754.6	754.3	754.0	753.7	753.5
120°	812.9	814.7	815.7	816.7	817.7	818.7	818.5	817.2	815.9	814.5	813.1
122.5°	874.4	875.6	876.1	876.5	877.0	877.5	877.4	876.9	876.4	875.8	875.3
125°	964.7	965.4	965.7	966.0	966.4	966.7	966.9	966.9	966.9	966.9	966.9
127.5°	1051.5	1052.2	1052.8	1053.3	1053.8	1054.4	1054.1	1053.1	1052.1	1051.1	1050.1
130°	1112.5	1113.1	1113.1	1113.1	1113.1	1113.1	1112.6	1111.6	1110.5	1109.5	1108.5
132.5°	1169.7	1170.3	1170.6	1170.9	1171.1	1171.4	1171.2	1170.4	1169.7	1169.0	1168.2
135°	1255.6	1256.3	1256.3	1256.3	1256.3	1256.3	1255.3	1253.2	1251.1	1249.1	1247.1
137.5°	1338.8	1339.7	1339.2	1338.6	1338.1	1337.6	1336.8	1335.8	1334.8	1333.9	1333.0
140°	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.3	1391.6	1390.9	1390.3
142.5°	1444.4	1444.4	1444.7	1445.0	1445.2	1445.5	1445.3	1444.6	1444.0	1443.3	1442.6
145°	1522.4	1522.7	1522.4	1522.1	1521.7	1521.4	1520.6	1519.1	1517.8	1516.4	1515.1
147.5°	1592.8	1593.1	1593.4	1593.6	1593.9	1594.2	1593.5	1591.9	1590.2	1588.6	1587.0
150°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.3	1634.9	1633.6	1632.1	1630.8
152.5°	1677.9	1677.1	1676.9	1676.6	1676.3	1676.1	1675.5	1674.7	1673.9	1673.0	1672.2
155°	1735.8	1734.3	1734.7	1735.0	1735.4	1735.8	1735.9	1735.9	1735.9	1735.9	1735.9
157.5°	1787.5	1786.5	1786.6	1786.6	1786.7	1786.8	1787.1	1787.7	1788.3	1788.9	1789.5
160°	1819.2	1818.2	1818.5	1818.8	1819.2	1819.5	1819.8	1820.2	1820.5	1820.8	1821.2
162.5°	1846.7	1844.9	1845.2	1845.6	1845.9	1846.2	1846.8	1847.8	1848.7	1849.6	1850.4
165°	1884.1	1882.1	1882.8	1883.4	1884.1	1884.8	1885.6	1886.6	1887.6	1888.6	1889.7
167.5°	1915.8	1913.8	1913.7	1913.6	1913.6	1913.5	1914.2	1915.6	1917.0	1918.4	1919.9
170°	1932.8	1930.8	1930.5	1930.2	1929.8	1929.4	1930.2	1931.8	1933.5	1935.2	1936.9
172.5°	1945.3	1943.0	1942.9	1942.9	1942.8	1942.7	1943.4	1944.8	1946.2	1947.6	1949.0
175°	1959.0	1956.7	1957.0	1957.3	1957.7	1958.0	1959.0	1960.8	1962.5	1964.1	1965.8
177.5°	1967.1	1965.2	1965.2	1965.2	1965.2	1965.2	1965.9	1967.2	1968.6	1969.9	1971.3
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	15.9	15.2	14.3	14.6	15.2	14.9	16.0	16.5	17.0	17.0	18.3
90°	8.3	12.0	15.8	19.5	22.7	25.3	28.1	30.8	33.5	35.5	37.6
92.5°	36.9	41.1	45.3	49.7	52.7	54.6	56.6	58.4	60.3	61.5	62.7
95°	94.4	97.5	100.5	103.5	106.2	108.7	111.0	113.4	115.7	116.7	117.8
97.5°	162.0	164.4	166.9	169.4	172.0	174.7	177.4	180.3	183.0	184.2	185.5
100°	214.5	215.9	217.2	218.6	220.8	223.9	226.9	229.9	233.0	233.7	234.3
102.5°	269.7	270.3	270.8	271.4	273.1	275.8	278.6	281.3	284.2	285.1	286.0
105°	355.2	355.5	355.8	356.2	357.0	358.3	359.7	361.0	362.4	363.5	364.5
107.5°	445.0	445.5	445.9	446.3	446.6	446.8	447.0	447.2	447.4	448.3	449.3
110°	506.2	506.9	507.6	508.3	508.5	508.1	507.8	507.4	507.1	506.3	505.7



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	569.1	569.2	569.3	569.5	569.2	568.6	567.9	567.3	566.7	566.6	566.4
115°	663.9	663.9	663.9	663.9	663.6	662.9	662.2	661.6	660.9	660.6	660.1
117.5°	753.7	754.0	754.3	754.6	754.5	754.0	753.5	753.0	752.6	751.3	750.2
120°	814.5	815.9	817.2	818.5	818.7	817.7	816.7	815.7	814.7	812.9	811.2
122.5°	875.8	876.4	876.9	877.4	877.5	877.0	876.5	876.1	875.6	874.4	873.2
125°	966.9	966.9	966.9	966.9	966.7	966.4	966.0	965.7	965.4	964.7	964.0
127.5°	1051.1	1052.1	1053.1	1054.1	1054.4	1053.8	1053.3	1052.8	1052.2	1051.5	1050.9
130°	1109.5	1110.5	1111.6	1112.6	1113.1	1113.1	1113.1	1113.1	1113.1	1112.5	1111.8
132.5°	1169.0	1169.7	1170.4	1171.2	1171.4	1171.1	1170.9	1170.6	1170.3	1169.7	1169.0
135°	1249.1	1251.1	1253.2	1255.3	1256.3	1256.3	1256.3	1256.3	1256.3	1255.6	1254.9
137.5°	1333.9	1334.8	1335.8	1336.8	1337.6	1338.1	1338.6	1339.2	1339.7	1338.8	1338.0
140°	1390.9	1391.6	1392.3	1392.9	1393.3	1393.3	1393.3	1393.3	1393.3	1392.9	1392.6
142.5°	1443.3	1444.0	1444.6	1445.3	1445.5	1445.2	1445.0	1444.7	1444.4	1444.4	1444.3
145°	1516.4	1517.8	1519.1	1520.6	1521.4	1521.7	1522.1	1522.4	1522.7	1522.4	1522.1
147.5°	1588.6	1590.2	1591.9	1593.5	1594.2	1593.9	1593.6	1593.4	1593.1	1592.8	1592.6
150°	1632.1	1633.6	1634.9	1636.3	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
152.5°	1673.0	1673.9	1674.7	1675.5	1676.1	1676.3	1676.6	1676.9	1677.1	1677.9	1678.7
155°	1735.9	1735.9	1735.9	1735.9	1735.8	1735.4	1735.0	1734.7	1734.3	1735.8	1737.1
157.5°	1788.9	1788.3	1787.7	1787.1	1786.8	1786.7	1786.6	1786.6	1786.5	1787.5	1788.5
160°	1820.8	1820.5	1820.2	1819.8	1819.5	1819.2	1818.8	1818.5	1818.2	1819.2	1820.2
162.5°	1849.6	1848.7	1847.8	1846.8	1846.2	1845.9	1845.6	1845.2	1844.9	1846.7	1848.6
165°	1888.6	1887.6	1886.6	1885.6	1884.8	1884.1	1883.4	1882.8	1882.1	1884.1	1886.1
167.5°	1918.4	1917.0	1915.6	1914.2	1913.5	1913.6	1913.6	1913.7	1913.8	1915.8	1917.8
170°	1935.2	1933.5	1931.8	1930.2	1929.4	1929.8	1930.2	1930.5	1930.8	1932.8	1934.9
172.5°	1947.6	1946.2	1944.8	1943.4	1942.7	1942.8	1942.9	1942.9	1943.0	1945.3	1947.6
175°	1964.1	1962.5	1960.8	1959.0	1958.0	1957.7	1957.3	1957.0	1956.7	1959.0	1961.5
177.5°	1969.9	1968.6	1967.2	1965.9	1965.2	1965.2	1965.2	1965.2	1965.2	1967.1	1969.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	17.8	17.8	18.5	18.2	18.3	18.0	18.6
90°	39.6	41.6	43.0	43.6	44.3	45.0	45.6
92.5°	63.9	65.1	65.9	66.3	66.8	67.2	67.6
95°	118.8	119.8	120.3	120.3	120.3	120.3	120.3
97.5°	186.7	187.9	188.5	188.5	188.5	188.5	188.5
100°	235.0	235.7	236.0	236.0	236.0	236.0	236.0
102.5°	287.0	287.9	288.5	288.8	289.1	289.3	289.6
105°	365.5	366.5	367.5	368.5	369.5	370.5	371.5
107.5°	450.2	451.2	451.6	451.5	451.5	451.4	451.3
110°	505.0	504.3	504.5	505.5	506.5	507.6	508.6



TEST NUMBER: P333072-840

CATALOG NUMBER: S124RDIW-S795D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	566.3	566.2	566.2	566.4	566.6	566.8	567.0
115°	659.8	659.5	659.1	658.8	658.5	658.1	657.8
117.5°	749.1	747.9	747.0	746.3	745.7	745.0	744.3
120°	809.6	807.9	807.4	808.1	808.7	809.4	810.1
122.5°	872.1	871.0	869.8	868.6	867.4	866.2	864.9
125°	963.4	962.7	962.0	961.3	960.7	960.0	959.3
127.5°	1050.2	1049.5	1048.8	1048.3	1047.8	1047.2	1046.7
130°	1111.1	1110.3	1109.3	1108.0	1106.7	1105.3	1104.0
132.5°	1168.3	1167.6	1167.0	1166.5	1166.0	1165.4	1164.9
135°	1254.3	1253.5	1252.6	1251.6	1250.6	1249.6	1248.6
137.5°	1337.1	1336.2	1335.8	1336.1	1336.3	1336.5	1336.7
140°	1392.3	1391.9	1391.6	1391.3	1390.9	1390.6	1390.3
142.5°	1444.2	1444.2	1444.1	1444.0	1444.0	1443.9	1443.8
145°	1521.7	1521.4	1520.7	1519.6	1518.6	1517.6	1516.6
147.5°	1592.3	1592.0	1591.6	1591.3	1591.0	1590.6	1590.3
150°	1636.9	1636.9	1636.8	1636.4	1636.1	1635.8	1635.4
152.5°	1679.5	1680.3	1680.3	1679.4	1678.6	1677.7	1676.8
155°	1738.4	1739.8	1739.8	1738.4	1737.1	1735.8	1734.3
157.5°	1789.5	1790.5	1790.4	1789.3	1788.2	1787.0	1785.8
160°	1821.2	1822.2	1821.8	1820.2	1818.5	1816.7	1815.0
162.5°	1850.4	1852.2	1852.3	1850.6	1849.0	1847.2	1845.5
165°	1888.1	1890.2	1890.6	1889.2	1887.8	1886.4	1885.1
167.5°	1919.9	1921.9	1921.9	1919.8	1917.6	1915.5	1913.4
170°	1936.9	1938.9	1938.7	1936.4	1934.0	1931.7	1929.2
172.5°	1949.8	1952.2	1952.2	1949.7	1947.4	1945.0	1942.7
175°	1963.8	1966.2	1966.2	1963.8	1961.5	1959.0	1956.7
177.5°	1970.9	1972.8	1972.7	1970.4	1968.3	1966.2	1964.0
180°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8

(END OF REPORT)