

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333094

Luminaire Tested: **S124RDIW-S1020D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333094
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9586.8 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	1.8
10°-20°	473.0	4.9
20°-30°	683.0	7.1
30°-40°	774.2	8.1
40°-50°	747.6	7.8
50°-60°	621.7	6.5
60°-70°	429.3	4.5
70°-80°	217.6	2.3
80°-90°	61.6	0.6
90°-100°	128.6	1.3
100°-110°	380.9	4.0
110°-120°	646.6	6.7
120°-130°	852.5	8.9
130°-140°	957.5	10.0
140°-150°	940.9	9.8
150°-160°	791.3	8.3
160°-170°	526.5	5.5
170°-180°	184.4	1.9
0°-30°	1325.6	13.8
0°-40°	2099.9	21.9
0°-60°	3469.2	36.2
0°-90°	4177.7	43.6
90°-120°	1156.1	12.1
90°-150°	3906.9	40.8
90°-180°	5409.0	56.4
0°-180°	9586.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	4	21	33	42	45	9
95°	90	104	115	119	119	101
105°	351	353	359	363	368	373
115°	657	657	654	653	651	648
125°	958	957	956	953	950	853
135°	1235	1244	1244	1241	1236	955
145°	1500	1506	1508	1506	1502	939
155°	1719	1719	1717	1723	1717	791
165°	1871	1867	1864	1872	1867	527
175°	1947	1939	1938	1947	1938	185
180°	1950	1950	1950	1950	1950	



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	26.3	25.1	23.9	22.7	21.4	21.0	21.2	21.5	21.8	22.1	22.3
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	32.3	36.5	40.7	44.9	49.2	52.2	54.1	56.0	57.8	59.7	60.9
95°	90.5	93.5	96.5	99.5	102.5	105.2	107.6	109.9	112.3	114.6	115.6
97.5°	158.0	160.4	162.8	165.3	167.7	170.3	173.0	175.7	178.5	181.2	182.4
100°	211.1	212.4	213.8	215.1	216.5	218.6	221.7	224.7	227.7	230.7	231.4
102.5°	266.6	267.1	267.7	268.2	268.7	270.4	273.1	275.9	278.6	281.4	282.3
105°	351.3	351.7	352.0	352.3	352.7	353.5	354.8	356.2	357.5	358.9	359.9
107.5°	440.3	440.7	441.1	441.5	441.9	442.2	442.4	442.6	442.8	443.0	443.9
110°	500.6	501.3	501.9	502.6	503.3	503.5	503.1	502.8	502.4	502.1	501.4



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	563.3	563.5	563.6	563.7	563.9	563.6	563.0	562.4	561.8	561.2	561.1
115°	657.4	657.4	657.4	657.4	657.4	657.1	656.4	655.7	655.1	654.4	654.1
117.5°	746.1	746.3	746.6	746.9	747.2	747.1	746.6	746.1	745.6	745.2	744.0
120°	805.2	806.5	807.9	809.2	810.5	810.7	809.7	808.7	807.7	806.7	805.0
122.5°	866.7	867.2	867.8	868.3	868.8	868.9	868.4	867.9	867.5	867.0	865.9
125°	957.5	957.5	957.5	957.5	957.5	957.3	957.0	956.6	956.3	956.0	955.3
127.5°	1039.8	1040.8	1041.8	1042.8	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2
130°	1097.7	1098.7	1099.7	1100.7	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6
132.5°	1156.8	1157.6	1158.3	1159.0	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3
135°	1234.9	1236.9	1238.9	1241.0	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3
137.5°	1320.0	1320.9	1321.8	1322.8	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7
140°	1376.7	1377.3	1378.0	1378.7	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3
142.5°	1428.5	1429.2	1429.9	1430.5	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3
145°	1500.3	1501.6	1503.0	1504.3	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5
147.5°	1571.5	1573.1	1574.7	1576.3	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2
150°	1614.9	1616.2	1617.6	1618.9	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1655.9	1656.7	1657.5	1658.3	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5
155°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8
157.5°	1772.0	1771.4	1770.8	1770.2	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0
160°	1803.4	1803.0	1802.7	1802.4	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4
162.5°	1832.3	1831.5	1830.6	1829.7	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7
165°	1871.2	1870.2	1869.2	1868.2	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7
167.5°	1901.1	1899.7	1898.3	1896.9	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1
170°	1918.0	1916.3	1914.6	1912.9	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9
172.5°	1930.0	1928.6	1927.2	1925.8	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3
175°	1946.6	1944.9	1943.3	1941.6	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9
177.5°	1952.0	1950.7	1949.4	1948.0	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	22.4	22.6	22.7	23.0	23.4	23.8	24.2	24.5
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	62.1	63.3	64.5	65.3	65.7	66.1	66.5	66.9
95°	116.6	117.6	118.6	119.1	119.1	119.1	119.1	119.1
97.5°	183.7	184.9	186.1	186.7	186.7	186.7	186.7	186.7
100°	232.0	232.7	233.4	233.7	233.7	233.7	233.7	233.7
102.5°	283.2	284.2	285.1	285.7	286.0	286.3	286.5	286.8
105°	360.9	361.9	362.9	363.9	364.9	365.9	366.9	367.9
107.5°	444.9	445.8	446.8	447.2	447.1	447.1	447.0	446.9
110°	500.8	500.1	499.4	499.6	500.6	501.6	502.6	503.6



TEST NUMBER: P333094

CATALOG NUMBER: S124RDIW-S1020D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	560.9	560.8	560.7	560.7	560.9	561.1	561.3	561.5
115°	653.7	653.4	653.1	652.7	652.4	652.1	651.7	651.4
117.5°	742.9	741.8	740.6	739.7	739.0	738.4	737.7	737.0
120°	803.3	801.7	800.0	799.5	800.2	800.8	801.5	802.2
122.5°	864.7	863.6	862.5	861.3	860.1	858.9	857.7	856.5
125°	954.6	954.0	953.3	952.6	951.9	951.3	950.6	949.9
127.5°	1040.6	1039.9	1039.2	1038.6	1038.1	1037.6	1037.0	1036.5
130°	1100.9	1100.2	1099.5	1098.5	1097.2	1095.9	1094.5	1093.2
132.5°	1157.6	1156.9	1156.2	1155.6	1155.1	1154.6	1154.0	1153.5
135°	1242.6	1242.0	1241.3	1240.4	1239.4	1238.4	1237.4	1236.4
137.5°	1324.9	1324.0	1323.1	1322.8	1323.0	1323.2	1323.4	1323.6
140°	1379.0	1378.7	1378.3	1378.0	1377.7	1377.3	1377.0	1376.7
142.5°	1430.2	1430.1	1430.1	1430.0	1429.9	1429.9	1429.8	1429.7
145°	1507.2	1506.8	1506.5	1505.8	1504.8	1503.8	1502.8	1501.8
147.5°	1577.0	1576.7	1576.4	1576.1	1575.8	1575.5	1575.1	1574.8
150°	1620.9	1620.9	1620.9	1620.8	1620.4	1620.1	1619.8	1619.4
152.5°	1662.3	1663.1	1663.9	1663.9	1663.0	1662.2	1661.3	1660.4
155°	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4
157.5°	1771.0	1772.0	1773.0	1772.9	1771.8	1770.7	1769.5	1768.4
160°	1802.4	1803.4	1804.4	1804.0	1802.4	1800.7	1799.0	1797.3
162.5°	1830.5	1832.3	1834.1	1834.2	1832.5	1830.9	1829.2	1827.5
165°	1867.7	1869.7	1871.7	1872.1	1870.7	1869.4	1868.0	1866.7
167.5°	1899.1	1901.1	1903.1	1903.1	1901.0	1898.9	1896.8	1894.7
170°	1916.0	1918.0	1920.0	1919.8	1917.5	1915.1	1912.8	1910.4
172.5°	1928.6	1930.8	1933.1	1933.1	1930.7	1928.4	1926.0	1923.7
175°	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6
177.5°	1949.8	1951.6	1953.5	1953.4	1951.2	1949.1	1947.0	1944.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6

(END OF REPORT)