

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332822-940

Luminaire Tested: **S124DIW-S1020D1050U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332822-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7192.5 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	2.0
10°-20°	408.3	5.7
20°-30°	600.9	8.4
30°-40°	698.6	9.7
40°-50°	698.6	9.7
50°-60°	611.1	8.5
60°-70°	453.8	6.3
70°-80°	257.8	3.6
80°-90°	77.9	1.1
90°-100°	77.0	1.1
100°-110°	228.2	3.2
110°-120°	387.4	5.4
120°-130°	510.8	7.1
130°-140°	573.6	8.0
140°-150°	563.7	7.8
150°-160°	474.1	6.6
160°-170°	315.4	4.4
170°-180°	110.5	1.5
0°-30°	1154.1	16.0
0°-40°	1852.6	25.8
0°-60°	3162.3	44.0
0°-90°	3951.9	54.9
90°-120°	692.6	9.6
90°-150°	2340.6	32.5
90°-180°	3241.0	45.1
0°-180°	7192.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	3	12	20	25	27	7
95°	54	62	69	71	71	60
105°	210	212	215	218	220	223
115°	394	394	392	391	390	388
125°	574	574	573	571	569	511
135°	740	745	745	743	741	572
145°	899	902	903	902	900	562
155°	1030	1030	1029	1032	1029	474
165°	1121	1118	1116	1121	1118	316
175°	1166	1162	1161	1166	1161	111
180°	1168	1168	1168	1168	1168	



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	26.2	26.4	26.7	26.8	27.1	27.2	27.4	27.5	27.6	27.6	27.9
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	19.4	21.8	24.4	26.9	29.4	31.3	32.4	33.5	34.7	35.8	36.5
95°	54.2	56.0	57.8	59.7	61.4	63.0	64.5	65.8	67.2	68.7	69.3
97.5°	94.7	96.1	97.6	99.0	100.5	102.0	103.6	105.3	106.9	108.6	109.3
100°	126.4	127.2	128.0	128.9	129.7	131.0	132.8	134.6	136.4	138.2	138.6
102.5°	159.7	160.1	160.3	160.7	161.0	161.9	163.6	165.2	166.9	168.5	169.2
105°	210.4	210.7	210.9	211.1	211.2	211.8	212.6	213.4	214.2	215.0	215.6
107.5°	263.8	264.0	264.2	264.5	264.7	264.9	265.0	265.2	265.3	265.4	266.0
110°	299.9	300.3	300.7	301.1	301.5	301.6	301.4	301.2	301.0	300.8	300.4



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	337.5	337.6	337.7	337.7	337.8	337.7	337.3	337.0	336.6	336.3	336.2
115°	393.9	393.9	393.9	393.9	393.9	393.7	393.2	392.9	392.4	392.1	391.8
117.5°	447.0	447.1	447.3	447.5	447.6	447.5	447.3	447.0	446.7	446.4	445.8
120°	482.4	483.2	484.0	484.8	485.6	485.7	485.1	484.5	483.9	483.3	482.3
122.5°	519.2	519.6	519.9	520.2	520.5	520.6	520.2	520.0	519.7	519.4	518.7
125°	573.6	573.6	573.6	573.6	573.6	573.5	573.3	573.1	572.9	572.7	572.3
127.5°	622.9	623.6	624.1	624.7	625.4	625.5	625.2	624.8	624.6	624.2	623.8
130°	657.6	658.3	658.8	659.4	660.0	660.3	660.3	660.3	660.3	660.3	660.0
132.5°	693.0	693.5	693.9	694.4	694.8	694.9	694.8	694.6	694.5	694.3	693.9
135°	739.9	741.0	742.3	743.4	744.7	745.3	745.3	745.3	745.3	745.3	744.8
137.5°	790.8	791.3	791.9	792.5	793.0	793.4	793.8	794.2	794.4	794.8	794.2
140°	824.7	825.2	825.5	826.0	826.3	826.5	826.5	826.5	826.5	826.5	826.3
142.5°	855.9	856.2	856.7	857.0	857.5	857.6	857.4	857.2	857.1	856.9	856.8
145°	898.8	899.6	900.4	901.3	902.1	902.5	902.8	902.9	903.1	903.3	903.1
147.5°	941.5	942.4	943.4	944.3	945.3	945.7	945.6	945.4	945.2	945.0	944.9
150°	967.5	968.3	969.1	969.9	970.7	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	992.0	992.6	993.0	993.5	994.0	994.3	994.4	994.6	994.8	995.0	995.4
155°	1029.8	1029.8	1029.8	1029.8	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7
157.5°	1061.6	1061.2	1060.9	1060.5	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4
160°	1080.4	1080.2	1080.0	1079.8	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1
162.5°	1097.7	1097.3	1096.7	1096.2	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6
165°	1121.1	1120.4	1119.8	1119.3	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8
167.5°	1138.9	1138.1	1137.3	1136.4	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5
170°	1149.1	1148.1	1147.0	1146.0	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7
172.5°	1156.3	1155.4	1154.6	1153.8	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1
175°	1166.2	1165.2	1164.2	1163.2	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2
177.5°	1169.5	1168.7	1167.9	1167.1	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	28.1	28.4	28.6	28.8	28.9	28.9	29.0	29.1
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	37.2	37.9	38.7	39.1	39.4	39.6	39.9	40.1
95°	69.8	70.4	71.1	71.3	71.3	71.3	71.3	71.3
97.5°	110.0	110.8	111.5	111.8	111.8	111.8	111.8	111.8
100°	139.0	139.4	139.8	140.0	140.0	140.0	140.0	140.0
102.5°	169.7	170.2	170.9	171.2	171.3	171.5	171.7	171.8
105°	216.2	216.8	217.4	218.0	218.6	219.2	219.8	220.4
107.5°	266.5	267.1	267.7	267.9	267.9	267.9	267.8	267.8
110°	300.0	299.6	299.2	299.3	299.9	300.5	301.1	301.8



TEST NUMBER: P332822-940

CATALOG NUMBER: S124DIW-S1020D1050U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	336.1	336.0	335.9	335.9	336.1	336.2	336.3	336.4
115°	391.6	391.5	391.3	391.0	390.8	390.7	390.5	390.2
117.5°	445.1	444.3	443.7	443.2	442.7	442.4	441.9	441.6
120°	481.3	480.3	479.3	478.9	479.4	479.7	480.2	480.5
122.5°	518.1	517.4	516.7	515.9	515.2	514.5	513.8	513.1
125°	571.9	571.5	571.1	570.7	570.3	569.9	569.5	569.1
127.5°	623.4	623.0	622.6	622.2	621.9	621.6	621.3	621.0
130°	659.5	659.2	658.7	658.2	657.4	656.6	655.8	655.0
132.5°	693.5	693.1	692.7	692.3	692.1	691.7	691.3	691.1
135°	744.5	744.0	743.7	743.2	742.5	741.9	741.4	740.7
137.5°	793.7	793.2	792.6	792.5	792.6	792.7	792.8	792.9
140°	826.2	826.0	825.7	825.5	825.4	825.2	824.9	824.7
142.5°	856.8	856.8	856.8	856.7	856.7	856.7	856.6	856.6
145°	902.9	902.8	902.5	902.1	901.5	900.9	900.4	899.7
147.5°	944.8	944.6	944.4	944.2	944.1	943.9	943.6	943.4
150°	971.1	971.1	971.1	971.0	970.8	970.6	970.4	970.2
152.5°	995.9	996.4	996.8	996.8	996.3	995.8	995.2	994.8
155°	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9
157.5°	1061.0	1061.6	1062.2	1062.2	1061.5	1060.8	1060.2	1059.4
160°	1079.8	1080.4	1081.0	1080.8	1079.8	1078.8	1077.8	1076.7
162.5°	1096.6	1097.7	1098.9	1098.9	1097.9	1096.9	1095.8	1094.8
165°	1118.9	1120.2	1121.3	1121.5	1120.7	1119.9	1119.1	1118.3
167.5°	1137.7	1138.9	1140.1	1140.1	1138.9	1137.6	1136.4	1135.1
170°	1147.8	1149.1	1150.2	1150.1	1148.8	1147.4	1145.9	1144.5
172.5°	1155.4	1156.7	1158.2	1158.1	1156.7	1155.3	1153.9	1152.4
175°	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8
177.5°	1168.1	1169.2	1170.4	1170.3	1168.9	1167.7	1166.4	1165.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1

(END OF REPORT)