

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333105

Luminaire Tested: **S124RDIW-S1195D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333105
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9012.4 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54					54			
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46					46			
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39					39			
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33					33			
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29					29			
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25					25			
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22					22			
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22	20					20			
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	23	20	18					18			
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16					16			
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15					15			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	2.2
10°-20°	546.3	6.1
20°-30°	788.8	8.8
30°-40°	894.2	9.9
40°-50°	863.5	9.6
50°-60°	718.0	8.0
60°-70°	495.8	5.5
70°-80°	251.3	2.8
80°-90°	68.4	0.8
90°-100°	46.3	0.5
100°-110°	295.4	3.3
110°-120°	565.1	6.3
120°-130°	717.4	8.0
130°-140°	767.5	8.5
140°-150°	717.7	8.0
150°-160°	578.8	6.4
160°-170°	373.3	4.1
170°-180°	128.7	1.4
0°-30°	1531.0	17.0
0°-40°	2425.2	26.9
0°-60°	4006.7	44.5
0°-90°	4822.1	53.5
90°-120°	906.8	10.1
90°-150°	3109.5	34.5
90°-180°	4190.0	46.5
0°-180°	9012.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	3	14	22	28	30	7
95°	56	23	22	28	29	72
105°	305	311	316	323	289	319
115°	569	572	571	573	574	560
125°	800	804	802	805	806	714
135°	993	992	996	998	1000	765
145°	1145	1148	1148	1149	1151	715
155°	1255	1256	1253	1257	1254	579
165°	1324	1319	1319	1326	1318	374
175°	1355	1349	1350	1358	1346	129
180°	1355	1355	1355	1355	1355	



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	30.0	28.2	26.4	24.7	22.9	22.0	22.1	22.2	22.3	22.3	22.3
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	12.8	12.9	13.0	13.2	13.3	14.3	16.1	17.9	19.7	21.5	22.8
95°	55.7	48.1	40.4	32.8	25.1	21.4	21.6	21.8	22.1	22.3	23.6
97.5°	118.3	123.1	127.9	132.7	137.4	127.3	102.1	77.0	51.9	26.7	26.9
100°	166.2	170.2	174.3	178.3	182.4	168.9	137.8	106.7	75.7	44.6	40.8
102.5°	219.7	222.6	225.6	228.6	231.5	231.0	227.0	222.9	218.8	214.8	173.5
105°	305.0	306.3	307.7	309.0	310.4	311.6	312.7	313.9	315.0	316.1	318.1
107.5°	384.2	384.9	385.5	386.2	386.9	388.0	389.5	391.1	392.6	394.1	395.1
110°	437.7	438.4	439.0	439.7	440.4	441.4	442.8	444.1	445.5	446.8	447.3



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	489.6	490.8	492.0	493.2	494.4	495.4	496.0	496.6	497.2	497.9	497.8
115°	569.4	570.1	570.8	571.4	572.1	572.3	572.1	571.9	571.7	571.4	571.9
117.5°	641.3	642.2	643.1	644.0	644.9	645.6	646.1	646.6	647.1	647.6	647.5
120°	690.0	690.9	691.8	692.7	693.6	693.9	693.7	693.5	693.2	693.0	693.5
122.5°	735.4	735.9	736.4	737.0	737.5	738.0	738.3	738.6	738.9	739.2	739.5
125°	800.4	801.3	802.2	803.1	804.0	804.2	803.8	803.3	802.9	802.4	803.1
127.5°	862.0	862.2	862.5	862.7	862.9	863.5	864.6	865.6	866.6	867.7	867.6
130°	901.7	902.0	902.2	902.4	902.6	903.1	903.8	904.4	905.1	905.8	906.0
132.5°	938.2	938.6	939.0	939.4	939.8	940.5	941.3	942.2	943.0	943.9	944.1
135°	992.9	992.7	992.5	992.2	992.0	992.4	993.3	994.2	995.1	996.0	996.4
137.5°	1041.3	1041.4	1041.5	1041.6	1041.7	1042.2	1043.2	1044.2	1045.2	1046.2	1046.7
140°	1073.0	1073.4	1073.9	1074.3	1074.8	1075.2	1075.7	1076.1	1076.6	1077.0	1077.7
142.5°	1101.3	1102.1	1102.9	1103.8	1104.6	1105.1	1105.4	1105.6	1105.9	1106.2	1106.7
145°	1144.9	1145.6	1146.2	1146.9	1147.6	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2
147.5°	1179.5	1180.8	1182.1	1183.3	1184.6	1185.1	1184.9	1184.7	1184.4	1184.2	1184.4
150°	1204.7	1205.6	1206.5	1207.4	1208.3	1208.6	1208.4	1208.2	1207.9	1207.7	1207.7
152.5°	1225.7	1226.5	1227.2	1227.9	1228.6	1228.8	1228.4	1228.0	1227.6	1227.2	1227.5
155°	1255.3	1255.6	1255.8	1256.0	1256.2	1256.0	1255.3	1254.7	1254.0	1253.3	1254.2
157.5°	1280.3	1280.1	1280.0	1279.8	1279.7	1279.3	1278.5	1277.7	1277.0	1276.2	1277.4
160°	1294.8	1294.2	1293.5	1292.8	1292.1	1291.7	1291.5	1291.2	1291.0	1290.8	1292.1
162.5°	1307.8	1307.0	1306.1	1305.2	1304.4	1303.8	1303.6	1303.4	1303.2	1302.9	1304.3
165°	1324.2	1323.1	1322.0	1320.8	1319.7	1319.2	1319.2	1319.2	1319.2	1319.2	1321.0
167.5°	1337.2	1336.0	1334.9	1333.7	1332.5	1331.9	1331.7	1331.6	1331.5	1331.3	1333.3
170°	1344.5	1343.1	1341.8	1340.4	1339.1	1338.5	1338.7	1339.0	1339.2	1339.4	1341.2
172.5°	1349.3	1348.0	1346.6	1345.3	1343.9	1343.4	1343.6	1343.8	1344.1	1344.3	1346.1
175°	1354.6	1353.3	1351.9	1350.6	1349.2	1348.7	1348.9	1349.1	1349.3	1349.6	1351.6
177.5°	1357.0	1355.8	1354.5	1353.3	1352.0	1351.6	1351.9	1352.3	1352.6	1353.0	1354.4
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	22.3	22.3	22.3	22.5	22.8	23.2	23.6	24.0
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	24.2	25.5	26.9	27.6	27.7	27.8	27.9	28.0
95°	25.0	26.3	27.7	28.5	28.7	28.9	29.2	29.4
97.5°	27.0	27.2	27.3	27.5	27.7	27.9	28.1	28.4
100°	36.9	33.1	29.3	27.5	27.7	27.9	28.1	28.4
102.5°	132.2	90.9	49.6	29.0	29.0	29.1	29.1	29.2
105°	320.2	322.2	324.2	321.2	313.1	305.0	296.9	288.8
107.5°	396.1	397.1	398.1	399.0	399.9	400.7	401.6	402.4
110°	447.7	448.2	448.6	449.2	449.9	450.5	451.2	451.9



TEST NUMBER: P333105

CATALOG NUMBER: S124RDIW-S1195D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.7	497.6	497.5	497.9	498.8	499.6	500.5	501.3
115°	572.3	572.8	573.2	573.5	573.5	573.5	573.5	573.5
117.5°	647.4	647.4	647.3	647.2	647.1	647.0	646.9	646.8
120°	693.9	694.4	694.8	694.8	694.4	693.9	693.5	693.0
122.5°	739.8	740.0	740.3	740.2	739.8	739.3	738.9	738.4
125°	803.8	804.5	805.1	805.6	805.8	806.0	806.3	806.5
127.5°	867.4	867.3	867.1	867.0	866.8	866.6	866.4	866.3
130°	906.2	906.5	906.7	906.8	906.8	906.8	906.8	906.8
132.5°	944.3	944.6	944.8	944.8	944.6	944.4	944.3	944.1
135°	996.9	997.3	997.8	998.2	998.7	999.1	999.6	1000.0
137.5°	1047.2	1047.7	1048.2	1048.4	1048.2	1048.1	1048.0	1047.8
140°	1078.4	1079.0	1079.7	1080.2	1080.4	1080.6	1080.8	1081.1
142.5°	1107.2	1107.7	1108.2	1108.4	1108.5	1108.5	1108.6	1108.6
145°	1148.4	1148.6	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1184.6	1184.7	1184.9	1185.1	1185.4	1185.6	1185.8	1186.0
150°	1207.7	1207.7	1207.7	1207.8	1208.0	1208.3	1208.5	1208.7
152.5°	1227.9	1228.2	1228.6	1228.7	1228.6	1228.4	1228.3	1228.2
155°	1255.1	1256.0	1256.9	1257.0	1256.3	1255.7	1255.0	1254.3
157.5°	1278.5	1279.7	1280.9	1280.9	1279.7	1278.5	1277.4	1276.2
160°	1293.5	1294.8	1296.2	1296.2	1294.8	1293.5	1292.1	1290.8
162.5°	1305.6	1307.0	1308.3	1308.3	1306.7	1305.2	1303.7	1302.1
165°	1322.8	1324.6	1326.4	1326.2	1324.2	1322.2	1320.2	1318.1
167.5°	1335.3	1337.3	1339.2	1339.1	1336.9	1334.6	1332.4	1330.1
170°	1343.0	1344.8	1346.6	1346.4	1344.1	1341.9	1339.6	1337.4
172.5°	1347.9	1349.7	1351.5	1351.2	1348.7	1346.3	1343.9	1341.4
175°	1353.6	1355.6	1357.7	1357.3	1354.6	1351.9	1349.2	1346.5
177.5°	1355.9	1357.3	1358.8	1358.4	1356.2	1354.1	1351.9	1349.8
180°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6

(END OF REPORT)