

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333107

Luminaire Tested: **S124RDIW-S1195D1340U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333107  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1340U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10378.5 lumens  
Efficiency: N/A  
Efficacy: 136.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15998	15998	15998	15998
5°	18556	16046	14182	16046
10°	21952	15976	12658	15976
15°	25357	15828	10877	15828
20°	28233	15625	9836	15625
25°	29144	15425	9132	15425
30°	25513	15183	8708	15183
35°	19860	14824	8451	14824
40°	14893	14413	8313	14413
45°	11758	13755	8241	13755
50°	9927	12995	8002	12995
55°	8653	12159	7574	12159
60°	7786	11292	6704	11292
65°	6863	10355	5765	10355
70°	6182	9385	5202	9385
75°	5181	8319	4432	8319
80°	4379	7090	4156	7090
85°	3696	5548	3696	5548



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	192.0	1.9
10°-20°	579.2	5.6
20°-30°	905.9	8.7
30°-40°	1007.1	9.7
40°-50°	893.5	8.6
50°-60°	696.2	6.7
60°-70°	455.8	4.4
70°-80°	224.2	2.2
80°-90°	60.3	0.6
90°-100°	59.3	0.6
100°-110°	378.2	3.6
110°-120°	723.4	7.0
120°-130°	918.4	8.8
130°-140°	982.6	9.5
140°-150°	918.8	8.9
150°-160°	741.0	7.1
160°-170°	477.9	4.6
170°-180°	164.7	1.6
0°-30°	1677.1	16.2
0°-40°	2684.1	25.9
0°-60°	4273.8	41.2
0°-90°	5014.2	48.3
90°-120°	1160.9	11.2
90°-150°	3980.7	38.4
90°-180°	5364.0	51.7
0°-180°	10378.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1982	1982	1982	1982	1982	
5°	2290	1980	1750	1980	2290	232
15°	3034	1894	1301	1894	3034	863
25°	3272	1732	1025	1732	3272	1452
35°	2015	1504	858	1504	2015	1263
45°	1030	1205	722	1205	1030	816
55°	615	864	538	864	615	559
65°	359	542	302	542	359	361
75°	166	267	142	267	166	183
85°	40	60	40	60	40	46
90°	39	4	39	4	39	19
95°	38	71	38	71	38	30
105°	370	390	370	390	370	323
115°	734	729	734	729	734	727
125°	1032	1025	1032	1025	1032	919
135°	1280	1271	1280	1271	1280	985
145°	1474	1466	1474	1466	1474	921
155°	1606	1607	1606	1607	1606	740
165°	1688	1695	1688	1695	1688	477
175°	1724	1734	1724	1734	1724	164
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2090.2	2096.0	2090.2	2089.6	2083.2	2081.3	2078.7	2070.4	2055.1	2046.2	2048.1
5°	2289.8	2309.8	2298.6	2297.0	2279.5	2261.9	2250.7	2225.2	2198.0	2179.7	2164.5
7.5°	2520.7	2532.2	2525.2	2514.0	2485.6	2469.5	2443.6	2409.9	2361.2	2324.0	2290.0
10°	2677.9	2687.4	2684.3	2663.5	2642.7	2600.4	2576.5	2529.4	2467.9	2419.2	2373.7
12.5°	2832.4	2842.7	2814.6	2815.5	2776.2	2742.9	2704.9	2645.6	2574.6	2511.8	2454.8
15°	3034.0	3021.2	3021.2	3005.2	2961.3	2915.0	2875.9	2813.6	2724.2	2649.1	2570.1
17.5°	3191.7	3196.2	3189.6	3152.0	3117.5	3069.6	2997.9	2925.2	2842.2	2741.4	2660.6
20°	3286.3	3286.3	3279.1	3253.5	3208.8	3157.7	3080.3	3001.2	2895.8	2794.4	2703.4
22.5°	3324.6	3327.1	3318.7	3297.6	3257.4	3207.5	3141.6	3061.3	2952.7	2838.5	2725.8
25°	3271.9	3287.1	3288.6	3283.1	3271.1	3240.7	3184.1	3101.8	3004.4	2880.7	2759.3
27.5°	3003.9	3023.1	3039.9	3067.5	3104.2	3123.4	3125.9	3084.1	2999.1	2880.0	2757.9
30°	2736.9	2752.9	2804.8	2872.7	2925.4	2973.3	3014.8	3026.0	2978.1	2871.1	2742.5
32.5°	2440.6	2462.3	2514.2	2587.2	2675.0	2756.1	2849.4	2896.9	2895.7	2831.5	2712.5
35°	2015.2	2031.2	2079.1	2155.7	2261.1	2381.7	2529.4	2644.3	2722.6	2717.0	2644.3
37.5°	1625.2	1643.3	1691.7	1755.2	1857.4	2006.7	2149.6	2308.0	2452.7	2534.0	2509.7
40°	1413.2	1414.0	1461.1	1526.6	1622.4	1752.5	1908.2	2083.8	2245.1	2376.9	2402.4
42.5°	1245.8	1246.0	1277.1	1347.7	1416.7	1539.2	1687.8	1862.2	2051.0	2203.1	2270.8
45°	1029.9	1037.1	1062.7	1105.0	1159.3	1263.1	1382.0	1544.1	1755.7	1936.1	2048.7
47.5°	872.2	882.7	899.0	933.5	976.8	1045.9	1144.3	1289.9	1462.0	1660.5	1820.7
50°	790.4	792.0	812.8	831.9	869.5	924.6	1010.8	1132.1	1290.2	1481.0	1659.1
52.5°	720.2	719.8	732.3	756.6	787.1	830.0	899.6	1010.1	1150.3	1321.4	1505.2
55°	614.8	618.8	628.3	647.5	670.7	701.0	756.1	839.1	949.3	1095.4	1262.3
57.5°	534.6	536.7	544.2	552.3	573.6	595.6	637.0	694.6	787.6	907.2	1062.7
60°	482.2	483.0	485.4	497.4	514.2	534.9	562.9	611.6	689.8	799.2	922.2
62.5°	431.1	432.6	436.3	445.0	458.0	472.3	501.6	540.7	605.5	698.9	809.7
65°	359.3	360.1	365.7	368.9	379.2	392.0	413.6	439.9	484.6	562.9	646.7
67.5°	300.2	300.2	300.5	304.8	312.0	320.5	333.4	354.5	388.2	436.3	510.2
70°	261.9	261.9	263.5	265.9	269.9	277.0	284.2	300.2	325.0	364.1	420.8
72.5°	226.1	226.7	228.3	228.8	230.9	236.8	242.1	252.3	270.7	300.2	346.0
75°	166.1	168.5	172.5	175.7	179.6	178.8	184.4	190.8	196.4	214.0	240.3
77.5°	123.6	122.3	122.8	125.5	126.0	126.8	130.8	135.7	139.9	148.2	157.6
80°	94.2	94.2	96.6	97.4	96.6	97.4	101.4	103.8	105.4	108.6	117.4
82.5°	71.2	72.5	71.7	72.5	73.0	73.8	77.1	77.6	79.2	80.5	84.2
85°	39.9	40.7	41.5	39.9	39.9	39.9	41.5	42.3	43.9	43.1	44.7
87.5°	21.8	21.1	21.6	21.5	22.0	21.1	21.4	22.4	20.7	21.0	20.6
90°	38.9	38.3	37.8	37.2	36.6	35.5	33.7	32.0	30.3	28.5	26.2
92.5°	35.8	35.7	35.6	35.5	35.3	34.4	32.7	31.0	29.2	27.5	25.2
95°	37.6	37.3	37.0	36.7	36.5	35.5	33.7	32.0	30.3	28.5	28.2
97.5°	36.3	36.0	35.7	35.5	35.2	34.9	34.8	34.6	34.4	34.2	66.4
100°	36.3	36.0	35.7	35.5	35.2	37.5	42.4	47.3	52.2	57.1	96.8
102.5°	37.4	37.3	37.2	37.2	37.1	63.5	116.4	169.3	222.1	275.0	280.2
105°	369.7	380.0	390.4	400.8	411.2	415.1	412.5	409.9	407.3	404.7	403.2
107.5°	515.2	514.1	513.0	511.9	510.8	509.6	508.4	507.1	505.8	504.6	502.6
110°	578.5	577.6	576.8	575.9	575.0	574.3	573.7	573.2	572.6	572.0	570.3



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	641.8	640.7	639.6	638.5	637.4	636.9	637.0	637.1	637.3	637.4	636.6
115°	734.1	734.1	734.1	734.1	734.1	733.8	733.3	732.7	732.1	731.5	731.8
117.5°	828.0	828.2	828.3	828.4	828.5	828.6	828.7	828.8	829.0	829.1	828.4
120°	887.2	887.8	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2	887.5
122.5°	945.3	945.9	946.4	947.0	947.6	947.7	947.4	947.0	946.7	946.3	945.9
125°	1032.5	1032.2	1031.9	1031.6	1031.3	1030.7	1029.9	1029.0	1028.1	1027.3	1027.8
127.5°	1109.0	1109.2	1109.4	1109.7	1109.9	1110.1	1110.3	1110.5	1110.6	1110.8	1109.5
130°	1160.9	1160.9	1160.9	1160.9	1160.9	1160.7	1160.4	1160.1	1159.9	1159.6	1158.7
132.5°	1208.6	1208.8	1209.1	1209.3	1209.5	1209.5	1209.2	1208.9	1208.6	1208.3	1207.2
135°	1280.2	1279.6	1279.0	1278.5	1277.9	1277.3	1276.7	1276.2	1275.6	1275.0	1273.9
137.5°	1341.4	1341.6	1341.8	1341.9	1342.1	1341.9	1341.2	1340.6	1340.0	1339.3	1338.1
140°	1384.0	1383.7	1383.4	1383.1	1382.8	1382.2	1381.4	1380.5	1379.6	1378.8	1378.2
142.5°	1419.2	1419.2	1419.1	1419.1	1419.0	1418.7	1418.0	1417.4	1416.8	1416.1	1415.8
145°	1473.5	1472.9	1472.3	1471.7	1471.2	1470.7	1470.4	1470.1	1469.9	1469.6	1469.6
147.5°	1518.3	1518.0	1517.8	1517.5	1517.2	1516.9	1516.7	1516.5	1516.2	1516.0	1516.3
150°	1547.4	1547.1	1546.8	1546.5	1546.2	1546.1	1546.1	1546.1	1546.1	1546.1	1546.4
152.5°	1572.3	1572.5	1572.6	1572.8	1573.0	1572.8	1572.4	1571.9	1571.5	1571.0	1571.5
155°	1605.8	1606.6	1607.5	1608.4	1609.2	1609.1	1607.9	1606.8	1605.6	1604.5	1605.3
157.5°	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8	1634.8
160°	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5	1652.7
162.5°	1667.0	1668.9	1670.9	1672.9	1674.8	1674.9	1673.2	1671.5	1669.7	1668.0	1668.3
165°	1687.5	1690.1	1692.7	1695.3	1697.8	1698.0	1695.7	1693.4	1691.1	1688.8	1688.8
167.5°	1702.8	1705.7	1708.5	1711.4	1714.3	1714.5	1711.9	1709.4	1706.9	1704.3	1704.5
170°	1712.1	1715.0	1717.9	1720.8	1723.6	1723.9	1721.6	1719.3	1717.0	1714.7	1714.4
172.5°	1717.3	1720.4	1723.5	1726.6	1729.8	1730.2	1727.9	1725.5	1723.2	1720.9	1720.6
175°	1723.8	1727.2	1730.7	1734.2	1737.6	1738.1	1735.5	1732.9	1730.3	1727.7	1727.4
177.5°	1727.9	1730.7	1733.5	1736.2	1739.0	1739.5	1737.6	1735.8	1733.9	1732.1	1731.6
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2041.7	2032.8	2028.3	2018.1	2005.9	1999.5	1993.8	1985.5	1974.6	1963.1	1954.8
5°	2145.3	2126.2	2102.2	2073.5	2047.9	2023.2	2001.6	1980.1	1955.3	1929.8	1904.2
7.5°	2251.7	2214.0	2173.3	2126.2	2080.3	2038.7	2000.3	1963.6	1922.1	1884.9	1851.0
10°	2325.8	2274.7	2218.0	2158.1	2098.2	2046.3	1995.2	1948.9	1897.8	1852.3	1814.0
12.5°	2385.8	2325.8	2257.6	2183.0	2111.0	2048.2	1989.5	1929.1	1871.0	1821.7	1770.6
15°	2485.4	2403.2	2311.4	2222.0	2128.6	2043.1	1964.1	1893.8	1827.6	1758.1	1709.4
17.5°	2554.0	2456.4	2344.8	2237.3	2127.0	2026.2	1935.0	1851.4	1774.9	1704.0	1646.0
20°	2594.8	2487.0	2363.3	2241.1	2117.4	2009.6	1911.4	1818.8	1739.7	1663.1	1603.2
22.5°	2617.8	2498.5	2363.3	2235.4	2107.2	1990.4	1882.6	1786.2	1700.1	1623.5	1557.2
25°	2625.2	2497.4	2359.3	2212.4	2071.9	1948.1	1836.3	1731.7	1635.9	1559.3	1489.0
27.5°	2615.0	2464.5	2323.1	2172.3	2027.3	1896.9	1779.5	1669.6	1573.7	1491.4	1419.4
30°	2599.6	2438.3	2286.6	2130.2	1983.2	1857.9	1734.1	1628.8	1529.0	1443.5	1370.9
32.5°	2566.4	2406.4	2243.2	2082.9	1934.1	1804.9	1687.5	1581.5	1483.6	1396.3	1319.1
35°	2500.6	2338.5	2161.3	1996.8	1850.7	1716.6	1606.4	1504.2	1410.8	1317.4	1235.9
37.5°	2413.9	2248.3	2072.0	1891.9	1745.6	1619.0	1517.9	1422.0	1330.8	1245.5	1155.3
40°	2332.2	2181.3	1999.2	1820.4	1670.3	1548.1	1454.7	1367.7	1275.9	1191.2	1101.0
42.5°	2233.2	2104.6	1920.7	1741.2	1593.0	1475.3	1388.3	1303.2	1219.7	1137.6	1043.5
45°	2067.9	1970.5	1798.0	1625.6	1476.3	1359.7	1279.9	1204.8	1131.3	1053.1	964.5
47.5°	1878.5	1812.5	1663.7	1487.1	1349.0	1244.1	1167.0	1105.6	1043.5	965.3	887.5
50°	1746.9	1704.6	1560.9	1399.6	1267.9	1171.3	1092.2	1034.7	982.8	907.8	838.3
52.5°	1606.4	1583.9	1462.5	1308.3	1181.0	1086.3	1018.8	967.0	914.5	852.2	787.2
55°	1392.4	1404.4	1301.4	1168.1	1048.3	968.5	907.0	863.9	819.2	766.5	716.2
57.5°	1173.7	1217.4	1148.3	1031.2	919.0	845.2	798.9	762.6	725.1	681.4	638.4
60°	1042.7	1079.4	1040.3	937.3	839.1	770.5	727.4	699.4	661.9	622.0	589.2
62.5°	915.0	954.3	931.1	847.9	756.7	697.7	659.6	633.6	605.7	570.9	536.9
65°	754.5	780.0	768.9	711.4	646.7	596.4	561.3	542.1	516.6	491.0	460.7
67.5°	577.9	627.2	620.7	590.2	534.3	495.0	472.0	455.1	431.8	412.8	392.2
70°	475.1	520.6	519.8	495.0	464.7	427.9	412.0	397.6	376.8	358.5	341.7
72.5°	388.8	430.5	436.7	417.7	397.0	369.2	353.9	344.0	323.8	311.2	297.6
75°	272.3	302.6	310.6	310.6	301.0	286.6	273.1	266.7	252.3	241.1	233.1
77.5°	178.5	197.7	210.1	213.0	214.5	209.7	198.5	194.0	183.0	179.0	171.3
80°	126.1	138.9	153.3	158.1	162.1	160.5	155.7	152.5	142.1	138.1	134.9
82.5°	87.2	94.2	106.0	116.6	115.4	119.6	115.4	112.9	105.1	103.6	100.4
85°	45.5	46.3	47.9	55.1	59.1	60.7	61.5	59.9	57.5	57.5	51.9
87.5°	20.1	19.0	19.8	19.3	19.3	21.2	22.5	22.5	21.2	19.9	18.6
90°	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.3	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.1	41.9	51.7	61.5	71.3	61.5	51.7	41.9
97.5°	98.6	130.7	162.9	175.9	169.8	163.7	157.6	151.5	157.6	163.7	169.8
100°	136.6	176.4	216.2	233.5	228.3	223.1	217.9	212.7	217.9	223.1	228.3
102.5°	285.4	290.5	295.7	296.4	292.6	288.8	285.0	281.2	285.0	288.8	292.6
105°	401.8	400.4	398.9	397.3	395.6	393.9	392.1	390.4	392.1	393.9	395.6
107.5°	500.6	498.7	496.7	495.3	494.4	493.6	492.7	491.8	492.7	493.6	494.4
110°	568.5	566.8	565.1	563.8	562.9	562.1	561.2	560.3	561.2	562.1	562.9





TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	635.8	635.0	634.1	633.0	631.4	629.9	628.3	626.7	628.3	629.9	631.4
115°	732.1	732.4	732.7	732.4	731.5	730.7	729.8	728.9	729.8	730.7	731.5
117.5°	827.8	827.2	826.5	825.6	824.5	823.3	822.2	821.0	822.2	823.3	824.5
120°	887.8	888.1	888.3	887.9	886.8	885.6	884.4	883.3	884.4	885.6	886.8
122.5°	945.5	945.1	944.7	944.2	943.5	942.8	942.1	941.4	942.1	942.8	943.5
125°	1028.4	1029.0	1029.6	1029.3	1028.1	1027.0	1025.8	1024.7	1025.8	1027.0	1028.1
127.5°	1108.1	1106.8	1105.5	1104.7	1104.4	1104.1	1103.8	1103.5	1103.8	1104.1	1104.4
130°	1157.8	1157.0	1156.1	1155.5	1155.2	1155.0	1154.7	1154.4	1154.7	1155.0	1155.2
132.5°	1206.1	1205.1	1204.0	1203.1	1202.6	1202.1	1201.6	1201.1	1201.6	1202.1	1202.6
135°	1272.7	1271.5	1270.4	1270.0	1270.3	1270.5	1270.8	1271.1	1270.8	1270.5	1270.3
137.5°	1336.8	1335.5	1334.3	1333.6	1333.5	1333.3	1333.2	1333.1	1333.2	1333.3	1333.5
140°	1377.6	1377.0	1376.5	1375.9	1375.3	1374.7	1374.2	1373.6	1374.2	1374.7	1375.3
142.5°	1415.4	1415.1	1414.7	1414.1	1413.0	1412.0	1410.9	1409.9	1410.9	1412.0	1413.0
145°	1469.6	1469.6	1469.6	1469.1	1468.3	1467.4	1466.5	1465.7	1466.5	1467.4	1468.3
147.5°	1516.6	1516.9	1517.2	1516.5	1514.9	1513.3	1511.6	1510.0	1511.6	1513.3	1514.9
150°	1546.7	1547.0	1547.2	1546.8	1545.7	1544.5	1543.4	1542.2	1543.4	1544.5	1545.7
152.5°	1572.0	1572.6	1573.1	1572.9	1571.9	1571.0	1570.1	1569.2	1570.1	1571.0	1571.9
155°	1606.2	1607.1	1607.9	1608.2	1607.9	1607.6	1607.3	1607.1	1607.3	1607.6	1607.9
157.5°	1635.7	1636.7	1637.7	1638.3	1638.4	1638.6	1638.8	1639.0	1638.8	1638.6	1638.4
160°	1653.0	1653.3	1653.6	1654.2	1655.0	1655.9	1656.8	1657.6	1656.8	1655.9	1655.0
162.5°	1668.6	1668.9	1669.2	1669.9	1671.0	1672.1	1673.1	1674.2	1673.1	1672.1	1671.0
165°	1688.8	1688.8	1688.8	1689.5	1690.9	1692.4	1693.8	1695.3	1693.8	1692.4	1690.9
167.5°	1704.7	1704.9	1705.0	1705.9	1707.4	1708.9	1710.4	1711.9	1710.4	1708.9	1707.4
170°	1714.1	1713.8	1713.6	1714.3	1716.0	1717.7	1719.5	1721.2	1719.5	1717.7	1716.0
172.5°	1720.4	1720.1	1719.8	1720.5	1722.2	1724.0	1725.7	1727.4	1725.7	1724.0	1722.2
175°	1727.1	1726.8	1726.5	1727.2	1729.0	1730.7	1732.4	1734.2	1732.4	1730.7	1729.0
177.5°	1731.2	1730.7	1730.2	1730.8	1732.4	1734.0	1735.7	1737.3	1735.7	1734.0	1732.4
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1945.9	1939.5	1931.2	1921.6	1910.1	1899.9	1895.4	1899.3	1901.2	1896.1	1895.4
5°	1886.6	1866.7	1850.7	1826.8	1807.6	1791.6	1780.5	1775.7	1777.3	1764.5	1761.3
7.5°	1820.1	1796.4	1770.2	1741.8	1715.3	1691.8	1679.5	1672.8	1659.3	1653.5	1643.8
10°	1777.3	1745.3	1719.8	1686.2	1655.9	1628.0	1614.4	1603.2	1589.6	1583.2	1569.7
12.5°	1733.2	1696.1	1668.0	1633.2	1602.2	1568.6	1555.6	1534.9	1513.6	1500.2	1482.8
15°	1671.1	1626.4	1592.0	1550.5	1513.8	1475.5	1441.1	1402.8	1388.4	1358.1	1340.5
17.5°	1598.4	1553.1	1510.6	1454.9	1398.2	1350.6	1314.0	1277.3	1255.3	1235.9	1227.0
20°	1550.5	1509.0	1449.9	1385.2	1322.2	1269.5	1239.9	1216.0	1192.0	1178.5	1168.9
22.5°	1505.2	1452.1	1383.5	1313.7	1250.6	1209.4	1184.4	1159.8	1140.3	1127.4	1114.6
25°	1429.2	1359.7	1287.0	1207.2	1164.1	1128.2	1101.0	1081.0	1069.1	1052.3	1045.9
27.5°	1351.1	1266.9	1186.8	1133.1	1088.2	1055.3	1031.7	1016.7	1001.5	990.8	982.5
30°	1291.0	1205.6	1133.7	1082.6	1037.1	1010.0	990.8	973.3	961.3	952.5	946.1
32.5°	1231.6	1146.2	1085.8	1030.9	995.0	968.5	948.0	934.9	925.5	914.2	910.3
35°	1145.7	1069.9	1017.2	967.7	930.9	907.0	891.0	877.5	869.5	866.3	863.9
37.5°	1063.2	1001.0	944.4	903.8	871.1	852.2	833.4	826.7	821.2	815.5	818.1
40°	1010.8	952.5	902.2	859.1	832.7	812.0	800.8	792.8	788.0	788.0	788.0
42.5°	965.4	908.4	859.4	820.8	794.4	776.9	764.4	757.7	756.1	755.5	759.3
45°	895.0	842.3	792.8	760.9	738.5	721.0	713.8	708.2	708.2	711.4	712.2
47.5°	825.2	775.9	736.1	700.4	679.9	668.9	662.7	659.8	660.1	663.3	667.0
50°	782.4	733.7	694.6	662.7	643.5	633.1	627.5	626.0	627.5	627.5	633.1
52.5°	735.8	692.2	653.7	626.9	605.2	595.5	592.4	590.2	591.1	593.7	596.1
55°	667.5	628.3	591.6	566.1	550.1	543.7	536.5	537.3	535.7	537.3	537.3
57.5°	599.0	563.8	529.7	509.4	495.3	486.1	478.2	480.5	478.1	477.8	476.5
60°	554.9	516.6	489.4	471.1	455.1	447.1	439.9	441.5	439.1	437.5	434.3
62.5°	507.0	475.1	449.2	431.5	418.7	409.4	402.2	400.6	395.1	389.6	382.6
65°	437.5	411.2	388.0	371.3	359.3	352.1	346.5	341.7	329.7	317.0	310.6
67.5°	370.0	351.0	329.4	315.2	305.5	296.1	285.4	277.2	266.0	259.0	255.0
70°	326.5	308.2	289.8	276.2	265.9	257.1	245.1	239.5	231.5	228.3	224.4
72.5°	285.0	267.9	250.9	238.6	227.5	220.7	211.3	205.7	202.2	200.9	196.9
75°	222.0	208.4	195.6	184.4	175.7	170.9	166.9	162.9	161.3	154.1	150.1
77.5°	161.9	153.0	145.0	137.0	130.8	127.6	119.9	115.3	112.6	109.2	108.4
80°	126.1	119.8	111.8	107.0	98.2	95.0	91.8	91.0	90.2	89.4	88.6
82.5°	94.9	88.5	80.5	77.6	75.2	73.3	71.4	70.6	69.8	70.3	70.1
85°	47.9	44.7	44.7	43.9	43.1	42.3	41.5	41.5	40.7	41.5	40.7
87.5°	19.3	19.2	19.7	18.8	19.9	20.4	20.1	20.5	21.4	20.5	20.7
90°	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0	33.7	35.5	36.6
92.5°	17.0	18.3	20.6	22.9	25.2	27.5	29.2	31.0	32.7	34.4	35.3
95°	32.1	27.4	27.7	28.0	28.2	28.5	30.3	32.0	33.7	35.5	36.5
97.5°	175.9	162.9	130.7	98.6	66.4	34.2	34.4	34.6	34.8	34.9	35.2
100°	233.5	216.2	176.4	136.6	96.8	57.1	52.2	47.3	42.4	37.5	35.2
102.5°	296.4	295.7	290.5	285.4	280.2	275.0	222.1	169.3	116.4	63.5	37.1
105°	397.3	398.9	400.4	401.8	403.2	404.7	407.3	409.9	412.5	415.1	411.2
107.5°	495.3	496.7	498.7	500.6	502.6	504.6	505.8	507.1	508.4	509.6	510.8
110°	563.8	565.1	566.8	568.5	570.3	572.0	572.6	573.2	573.7	574.3	575.0



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.0	634.1	635.0	635.8	636.6	637.4	637.3	637.1	637.0	636.9	637.4
115°	732.4	732.7	732.4	732.1	731.8	731.5	732.1	732.7	733.3	733.8	734.1
117.5°	825.6	826.5	827.2	827.8	828.4	829.1	829.0	828.8	828.7	828.6	828.5
120°	887.9	888.3	888.1	887.8	887.5	887.2	887.8	888.3	888.9	889.5	889.5
122.5°	944.2	944.7	945.1	945.5	945.9	946.3	946.7	947.0	947.4	947.7	947.6
125°	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1	1029.0	1029.9	1030.7	1031.3
127.5°	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6	1110.5	1110.3	1110.1	1109.9
130°	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9	1160.1	1160.4	1160.7	1160.9
132.5°	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6	1208.9	1209.2	1209.5	1209.5
135°	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6	1276.2	1276.7	1277.3	1277.9
137.5°	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0	1340.6	1341.2	1341.9	1342.1
140°	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6	1380.5	1381.4	1382.2	1382.8
142.5°	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8	1417.4	1418.0	1418.7	1419.0
145°	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9	1470.1	1470.4	1470.7	1471.2
147.5°	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2	1516.5	1516.7	1516.9	1517.2
150°	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1	1546.1	1546.1	1546.1	1546.2
152.5°	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5	1571.9	1572.4	1572.8	1573.0
155°	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6	1606.8	1607.9	1609.1	1609.2
157.5°	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8
160°	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4
162.5°	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7	1671.5	1673.2	1674.9	1674.8
165°	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1	1693.4	1695.7	1698.0	1697.8
167.5°	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9	1709.4	1711.9	1714.5	1714.3
170°	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0	1719.3	1721.6	1723.9	1723.6
172.5°	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2	1725.5	1727.9	1730.2	1729.8
175°	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3	1732.9	1735.5	1738.1	1737.6
177.5°	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9	1735.8	1737.6	1739.5	1739.0
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1891.6	1892.9	1888.4	1887.1	1888.4	1892.9	1891.6	1895.4	1896.1	1901.2	1899.3
5°	1754.9	1753.3	1749.3	1750.1	1749.3	1753.3	1754.9	1761.3	1764.5	1777.3	1775.7
7.5°	1638.0	1631.8	1633.5	1627.2	1633.5	1631.8	1638.0	1643.8	1653.5	1659.3	1672.8
10°	1566.5	1557.7	1550.5	1544.1	1550.5	1557.7	1566.5	1569.7	1583.2	1589.6	1603.2
12.5°	1468.8	1461.2	1451.5	1453.4	1451.5	1461.2	1468.8	1482.8	1500.2	1513.6	1534.9
15°	1330.1	1318.2	1299.0	1301.4	1299.0	1318.2	1330.1	1340.5	1358.1	1388.4	1402.8
17.5°	1212.8	1212.9	1204.2	1206.2	1204.2	1212.9	1212.8	1227.0	1235.9	1255.3	1277.3
20°	1152.1	1146.5	1147.3	1144.9	1147.3	1146.5	1152.1	1168.9	1178.5	1192.0	1216.0
22.5°	1109.9	1103.1	1097.5	1092.5	1097.5	1103.1	1109.9	1114.6	1127.4	1140.3	1159.8
25°	1038.7	1033.9	1026.8	1025.2	1026.8	1033.9	1038.7	1045.9	1052.3	1069.1	1081.0
27.5°	976.1	975.2	972.3	968.6	972.3	975.2	976.1	982.5	990.8	1001.5	1016.7
30°	939.7	938.1	936.5	934.1	936.5	938.1	939.7	946.1	952.5	961.3	973.3
32.5°	907.2	906.2	904.6	904.8	904.6	906.2	907.2	910.3	914.2	925.5	934.9
35°	860.7	859.9	858.3	857.5	858.3	859.9	860.7	863.9	866.3	869.5	877.5
37.5°	817.3	819.3	818.4	818.2	818.4	819.3	817.3	818.1	815.5	821.2	826.7
40°	787.2	788.0	789.6	788.8	789.6	788.0	787.2	788.0	788.0	788.0	792.8
42.5°	762.3	762.5	764.7	762.0	764.7	762.5	762.3	759.3	755.5	756.1	757.7
45°	717.8	722.6	721.8	721.8	721.8	722.6	717.8	712.2	711.4	708.2	708.2
47.5°	669.1	673.2	674.3	674.2	674.3	673.2	669.1	667.0	663.3	660.1	659.8
50°	637.1	635.5	637.9	637.1	637.9	635.5	637.1	633.1	627.5	627.5	626.0
52.5°	598.2	598.5	598.3	597.5	598.3	598.5	598.2	596.1	593.7	591.1	590.2
55°	538.1	538.9	537.3	538.1	537.3	538.9	538.1	537.3	537.3	535.7	537.3
57.5°	473.0	469.1	470.7	468.8	470.7	469.1	473.0	476.5	477.8	478.1	480.5
60°	426.4	420.0	418.4	415.2	418.4	420.0	426.4	434.3	437.5	439.1	441.5
62.5°	374.0	369.5	364.1	366.6	364.1	369.5	374.0	382.6	389.6	395.1	400.6
65°	304.2	301.0	298.6	301.8	298.6	301.0	304.2	310.6	317.0	329.7	341.7
67.5°	251.8	250.1	250.1	248.5	250.1	250.1	251.8	255.0	259.0	266.0	277.2
70°	224.4	222.0	222.0	220.4	222.0	222.0	224.4	224.4	228.3	231.5	239.5
72.5°	196.2	193.9	194.5	193.5	194.5	193.9	196.2	196.9	200.9	202.2	205.7
75°	145.3	141.3	141.3	142.1	141.3	141.3	145.3	150.1	154.1	161.3	162.9
77.5°	108.4	107.6	108.7	107.3	108.7	107.6	108.4	108.4	109.2	112.6	115.3
80°	88.6	87.8	87.0	89.4	87.0	87.8	88.6	88.6	89.4	90.2	91.0
82.5°	68.8	68.7	68.5	71.5	68.5	68.7	68.8	70.1	70.3	69.8	70.6
85°	41.5	39.9	41.5	39.9	41.5	39.9	41.5	40.7	41.5	40.7	41.5
87.5°	22.1	21.6	21.1	21.8	21.1	21.6	22.1	20.7	20.5	21.4	20.5
90°	37.2	37.8	38.3	38.9	38.3	37.8	37.2	36.6	35.5	33.7	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.3	34.4	32.7	31.0
95°	36.7	37.0	37.3	37.6	37.3	37.0	36.7	36.5	35.5	33.7	32.0
97.5°	35.5	35.7	36.0	36.3	36.0	35.7	35.5	35.2	34.9	34.8	34.6
100°	35.5	35.7	36.0	36.3	36.0	35.7	35.5	35.2	37.5	42.4	47.3
102.5°	37.2	37.2	37.3	37.4	37.3	37.2	37.2	37.1	63.5	116.4	169.3
105°	400.8	390.4	380.0	369.7	380.0	390.4	400.8	411.2	415.1	412.5	409.9
107.5°	511.9	513.0	514.1	515.2	514.1	513.0	511.9	510.8	509.6	508.4	507.1
110°	575.9	576.8	577.6	578.5	577.6	576.8	575.9	575.0	574.3	573.7	573.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	638.5	639.6	640.7	641.8	640.7	639.6	638.5	637.4	636.9	637.0	637.1
115°	734.1	734.1	734.1	734.1	734.1	734.1	734.1	734.1	733.8	733.3	732.7
117.5°	828.4	828.3	828.2	828.0	828.2	828.3	828.4	828.5	828.6	828.7	828.8
120°	888.9	888.3	887.8	887.2	887.8	888.3	888.9	889.5	889.5	888.9	888.3
122.5°	947.0	946.4	945.9	945.3	945.9	946.4	947.0	947.6	947.7	947.4	947.0
125°	1031.6	1031.9	1032.2	1032.5	1032.2	1031.9	1031.6	1031.3	1030.7	1029.9	1029.0
127.5°	1109.7	1109.4	1109.2	1109.0	1109.2	1109.4	1109.7	1109.9	1110.1	1110.3	1110.5
130°	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.9	1160.7	1160.4	1160.1
132.5°	1209.3	1209.1	1208.8	1208.6	1208.8	1209.1	1209.3	1209.5	1209.5	1209.2	1208.9
135°	1278.5	1279.0	1279.6	1280.2	1279.6	1279.0	1278.5	1277.9	1277.3	1276.7	1276.2
137.5°	1341.9	1341.8	1341.6	1341.4	1341.6	1341.8	1341.9	1342.1	1341.9	1341.2	1340.6
140°	1383.1	1383.4	1383.7	1384.0	1383.7	1383.4	1383.1	1382.8	1382.2	1381.4	1380.5
142.5°	1419.1	1419.1	1419.2	1419.2	1419.2	1419.1	1419.1	1419.0	1418.7	1418.0	1417.4
145°	1471.7	1472.3	1472.9	1473.5	1472.9	1472.3	1471.7	1471.2	1470.7	1470.4	1470.1
147.5°	1517.5	1517.8	1518.0	1518.3	1518.0	1517.8	1517.5	1517.2	1516.9	1516.7	1516.5
150°	1546.5	1546.8	1547.1	1547.4	1547.1	1546.8	1546.5	1546.2	1546.1	1546.1	1546.1
152.5°	1572.8	1572.6	1572.5	1572.3	1572.5	1572.6	1572.8	1573.0	1572.8	1572.4	1571.9
155°	1608.4	1607.5	1606.6	1605.8	1606.6	1607.5	1608.4	1609.2	1609.1	1607.9	1606.8
157.5°	1638.3	1636.8	1635.3	1633.8	1635.3	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8
160°	1657.6	1655.9	1654.2	1652.5	1654.2	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9
162.5°	1672.9	1670.9	1668.9	1667.0	1668.9	1670.9	1672.9	1674.8	1674.9	1673.2	1671.5
165°	1695.3	1692.7	1690.1	1687.5	1690.1	1692.7	1695.3	1697.8	1698.0	1695.7	1693.4
167.5°	1711.4	1708.5	1705.7	1702.8	1705.7	1708.5	1711.4	1714.3	1714.5	1711.9	1709.4
170°	1720.8	1717.9	1715.0	1712.1	1715.0	1717.9	1720.8	1723.6	1723.9	1721.6	1719.3
172.5°	1726.6	1723.5	1720.4	1717.3	1720.4	1723.5	1726.6	1729.8	1730.2	1727.9	1725.5
175°	1734.2	1730.7	1727.2	1723.8	1727.2	1730.7	1734.2	1737.6	1738.1	1735.5	1732.9
177.5°	1736.2	1733.5	1730.7	1727.9	1730.7	1733.5	1736.2	1739.0	1739.5	1737.6	1735.8
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1895.4	1899.9	1910.1	1921.6	1931.2	1939.5	1945.9	1954.8	1963.1	1974.6	1985.5
5°	1780.5	1791.6	1807.6	1826.8	1850.7	1866.7	1886.6	1904.2	1929.8	1955.3	1980.1
7.5°	1679.5	1691.8	1715.3	1741.8	1770.2	1796.4	1820.1	1851.0	1884.9	1922.1	1963.6
10°	1614.4	1628.0	1655.9	1686.2	1719.8	1745.3	1777.3	1814.0	1852.3	1897.8	1948.9
12.5°	1555.6	1568.6	1602.2	1633.2	1668.0	1696.1	1733.2	1770.6	1821.7	1871.0	1929.1
15°	1441.1	1475.5	1513.8	1550.5	1592.0	1626.4	1671.1	1709.4	1758.1	1827.6	1893.8
17.5°	1314.0	1350.6	1398.2	1454.9	1510.6	1553.1	1598.4	1646.0	1704.0	1774.9	1851.4
20°	1239.9	1269.5	1322.2	1385.2	1449.9	1509.0	1550.5	1603.2	1663.1	1739.7	1818.8
22.5°	1184.4	1209.4	1250.6	1313.7	1383.5	1452.1	1505.2	1557.2	1623.5	1700.1	1786.2
25°	1101.0	1128.2	1164.1	1207.2	1287.0	1359.7	1429.2	1489.0	1559.3	1635.9	1731.7
27.5°	1031.7	1055.3	1088.2	1133.1	1186.8	1266.9	1351.1	1419.4	1491.4	1573.7	1669.6
30°	990.8	1010.0	1037.1	1082.6	1133.7	1205.6	1291.0	1370.9	1443.5	1529.0	1628.8
32.5°	948.0	968.5	995.0	1030.9	1085.8	1146.2	1231.6	1319.1	1396.3	1483.6	1581.5
35°	891.0	907.0	930.9	967.7	1017.2	1069.9	1145.7	1235.9	1317.4	1410.8	1504.2
37.5°	833.4	852.2	871.1	903.8	944.4	1001.0	1063.2	1155.3	1245.5	1330.8	1422.0
40°	800.8	812.0	832.7	859.1	902.2	952.5	1010.8	1101.0	1191.2	1275.9	1367.7
42.5°	764.4	776.9	794.4	820.8	859.4	908.4	965.4	1043.5	1137.6	1219.7	1303.2
45°	713.8	721.0	738.5	760.9	792.8	842.3	895.0	964.5	1053.1	1131.3	1204.8
47.5°	662.7	668.9	679.9	700.4	736.1	775.9	825.2	887.5	965.3	1043.5	1105.6
50°	627.5	633.1	643.5	662.7	694.6	733.7	782.4	838.3	907.8	982.8	1034.7
52.5°	592.4	595.5	605.2	626.9	653.7	692.2	735.8	787.2	852.2	914.5	967.0
55°	536.5	543.7	550.1	566.1	591.6	628.3	667.5	716.2	766.5	819.2	863.9
57.5°	478.2	486.1	495.3	509.4	529.7	563.8	599.0	638.4	681.4	725.1	762.6
60°	439.9	447.1	455.1	471.1	489.4	516.6	554.9	589.2	622.0	661.9	699.4
62.5°	402.2	409.4	418.7	431.5	449.2	475.1	507.0	536.9	570.9	605.7	633.6
65°	346.5	352.1	359.3	371.3	388.0	411.2	437.5	460.7	491.0	516.6	542.1
67.5°	285.4	296.1	305.5	315.2	329.4	351.0	370.0	392.2	412.8	431.8	455.1
70°	245.1	257.1	265.9	276.2	289.8	308.2	326.5	341.7	358.5	376.8	397.6
72.5°	211.3	220.7	227.5	238.6	250.9	267.9	285.0	297.6	311.2	323.8	344.0
75°	166.9	170.9	175.7	184.4	195.6	208.4	222.0	233.1	241.1	252.3	266.7
77.5°	119.9	127.6	130.8	137.0	145.0	153.0	161.9	171.3	179.0	183.0	194.0
80°	91.8	95.0	98.2	107.0	111.8	119.8	126.1	134.9	138.1	142.1	152.5
82.5°	71.4	73.3	75.2	77.6	80.5	88.5	94.9	100.4	103.6	105.1	112.9
85°	41.5	42.3	43.1	43.9	44.7	44.7	47.9	51.9	57.5	57.5	59.9
87.5°	20.1	20.4	19.9	18.8	19.7	19.2	19.3	18.6	19.9	21.2	22.5
90°	30.3	28.5	26.2	23.9	21.6	19.3	16.6	13.4	10.2	7.1	3.9
92.5°	29.2	27.5	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.3
95°	30.3	28.5	28.2	28.0	27.7	27.4	32.1	41.9	51.7	61.5	71.3
97.5°	34.4	34.2	66.4	98.6	130.7	162.9	175.9	169.8	163.7	157.6	151.5
100°	52.2	57.1	96.8	136.6	176.4	216.2	233.5	228.3	223.1	217.9	212.7
102.5°	222.1	275.0	280.2	285.4	290.5	295.7	296.4	292.6	288.8	285.0	281.2
105°	407.3	404.7	403.2	401.8	400.4	398.9	397.3	395.6	393.9	392.1	390.4
107.5°	505.8	504.6	502.6	500.6	498.7	496.7	495.3	494.4	493.6	492.7	491.8
110°	572.6	572.0	570.3	568.5	566.8	565.1	563.8	562.9	562.1	561.2	560.3



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.3	637.4	636.6	635.8	635.0	634.1	633.0	631.4	629.9	628.3	626.7
115°	732.1	731.5	731.8	732.1	732.4	732.7	732.4	731.5	730.7	729.8	728.9
117.5°	829.0	829.1	828.4	827.8	827.2	826.5	825.6	824.5	823.3	822.2	821.0
120°	887.8	887.2	887.5	887.8	888.1	888.3	887.9	886.8	885.6	884.4	883.3
122.5°	946.7	946.3	945.9	945.5	945.1	944.7	944.2	943.5	942.8	942.1	941.4
125°	1028.1	1027.3	1027.8	1028.4	1029.0	1029.6	1029.3	1028.1	1027.0	1025.8	1024.7
127.5°	1110.6	1110.8	1109.5	1108.1	1106.8	1105.5	1104.7	1104.4	1104.1	1103.8	1103.5
130°	1159.9	1159.6	1158.7	1157.8	1157.0	1156.1	1155.5	1155.2	1155.0	1154.7	1154.4
132.5°	1208.6	1208.3	1207.2	1206.1	1205.1	1204.0	1203.1	1202.6	1202.1	1201.6	1201.1
135°	1275.6	1275.0	1273.9	1272.7	1271.5	1270.4	1270.0	1270.3	1270.5	1270.8	1271.1
137.5°	1340.0	1339.3	1338.1	1336.8	1335.5	1334.3	1333.6	1333.5	1333.3	1333.2	1333.1
140°	1379.6	1378.8	1378.2	1377.6	1377.0	1376.5	1375.9	1375.3	1374.7	1374.2	1373.6
142.5°	1416.8	1416.1	1415.8	1415.4	1415.1	1414.7	1414.1	1413.0	1412.0	1410.9	1409.9
145°	1469.9	1469.6	1469.6	1469.6	1469.6	1469.6	1469.1	1468.3	1467.4	1466.5	1465.7
147.5°	1516.2	1516.0	1516.3	1516.6	1516.9	1517.2	1516.5	1514.9	1513.3	1511.6	1510.0
150°	1546.1	1546.1	1546.4	1546.7	1547.0	1547.2	1546.8	1545.7	1544.5	1543.4	1542.2
152.5°	1571.5	1571.0	1571.5	1572.0	1572.6	1573.1	1572.9	1571.9	1571.0	1570.1	1569.2
155°	1605.6	1604.5	1605.3	1606.2	1607.1	1607.9	1608.2	1607.9	1607.6	1607.3	1607.1
157.5°	1635.3	1633.8	1634.8	1635.7	1636.7	1637.7	1638.3	1638.4	1638.6	1638.8	1639.0
160°	1654.2	1652.5	1652.7	1653.0	1653.3	1653.6	1654.2	1655.0	1655.9	1656.8	1657.6
162.5°	1669.7	1668.0	1668.3	1668.6	1668.9	1669.2	1669.9	1671.0	1672.1	1673.1	1674.2
165°	1691.1	1688.8	1688.8	1688.8	1688.8	1688.8	1689.5	1690.9	1692.4	1693.8	1695.3
167.5°	1706.9	1704.3	1704.5	1704.7	1704.9	1705.0	1705.9	1707.4	1708.9	1710.4	1711.9
170°	1717.0	1714.7	1714.4	1714.1	1713.8	1713.6	1714.3	1716.0	1717.7	1719.5	1721.2
172.5°	1723.2	1720.9	1720.6	1720.4	1720.1	1719.8	1720.5	1722.2	1724.0	1725.7	1727.4
175°	1730.3	1727.7	1727.4	1727.1	1726.8	1726.5	1727.2	1729.0	1730.7	1732.4	1734.2
177.5°	1733.9	1732.1	1731.6	1731.2	1730.7	1730.2	1730.8	1732.4	1734.0	1735.7	1737.3
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1993.8	1999.5	2005.9	2018.1	2028.3	2032.8	2041.7	2048.1	2046.2	2055.1	2070.4
5°	2001.6	2023.2	2047.9	2073.5	2102.2	2126.2	2145.3	2164.5	2179.7	2198.0	2225.2
7.5°	2000.3	2038.7	2080.3	2126.2	2173.3	2214.0	2251.7	2290.0	2324.0	2361.2	2409.9
10°	1995.2	2046.3	2098.2	2158.1	2218.0	2274.7	2325.8	2373.7	2419.2	2467.9	2529.4
12.5°	1989.5	2048.2	2111.0	2183.0	2257.6	2325.8	2385.8	2454.8	2511.8	2574.6	2645.6
15°	1964.1	2043.1	2128.6	2222.0	2311.4	2403.2	2485.4	2570.1	2649.1	2724.2	2813.6
17.5°	1935.0	2026.2	2127.0	2237.3	2344.8	2456.4	2554.0	2660.6	2741.4	2842.2	2925.2
20°	1911.4	2009.6	2117.4	2241.1	2363.3	2487.0	2594.8	2703.4	2794.4	2895.8	3001.2
22.5°	1882.6	1990.4	2107.2	2235.4	2363.3	2498.5	2617.8	2725.8	2838.5	2952.7	3061.3
25°	1836.3	1948.1	2071.9	2212.4	2359.3	2497.4	2625.2	2759.3	2880.7	3004.4	3101.8
27.5°	1779.5	1896.9	2027.3	2172.3	2323.1	2464.5	2615.0	2757.9	2880.0	2999.1	3084.1
30°	1734.1	1857.9	1983.2	2130.2	2286.6	2438.3	2599.6	2742.5	2871.1	2978.1	3026.0
32.5°	1687.5	1804.9	1934.1	2082.9	2243.2	2406.4	2566.4	2712.5	2831.5	2895.7	2896.9
35°	1606.4	1716.6	1850.7	1996.8	2161.3	2338.5	2500.6	2644.3	2717.0	2722.6	2644.3
37.5°	1517.9	1619.0	1745.6	1891.9	2072.0	2248.3	2413.9	2509.7	2534.0	2452.7	2308.0
40°	1454.7	1548.1	1670.3	1820.4	1999.2	2181.3	2332.2	2402.4	2376.9	2245.1	2083.8
42.5°	1388.3	1475.3	1593.0	1741.2	1920.7	2104.6	2233.2	2270.8	2203.1	2051.0	1862.2
45°	1279.9	1359.7	1476.3	1625.6	1798.0	1970.5	2067.9	2048.7	1936.1	1755.7	1544.1
47.5°	1167.0	1244.1	1349.0	1487.1	1663.7	1812.5	1878.5	1820.7	1660.5	1462.0	1289.9
50°	1092.2	1171.3	1267.9	1399.6	1560.9	1704.6	1746.9	1659.1	1481.0	1290.2	1132.1
52.5°	1018.8	1086.3	1181.0	1308.3	1462.5	1583.9	1606.4	1505.2	1321.4	1150.3	1010.1
55°	907.0	968.5	1048.3	1168.1	1301.4	1404.4	1392.4	1262.3	1095.4	949.3	839.1
57.5°	798.9	845.2	919.0	1031.2	1148.3	1217.4	1173.7	1062.7	907.2	787.6	694.6
60°	727.4	770.5	839.1	937.3	1040.3	1079.4	1042.7	922.2	799.2	689.8	611.6
62.5°	659.6	697.7	756.7	847.9	931.1	954.3	915.0	809.7	698.9	605.5	540.7
65°	561.3	596.4	646.7	711.4	768.9	780.0	754.5	646.7	562.9	484.6	439.9
67.5°	472.0	495.0	534.3	590.2	620.7	627.2	577.9	510.2	436.3	388.2	354.5
70°	412.0	427.9	464.7	495.0	519.8	520.6	475.1	420.8	364.1	325.0	300.2
72.5°	353.9	369.2	397.0	417.7	436.7	430.5	388.8	346.0	300.2	270.7	252.3
75°	273.1	286.6	301.0	310.6	310.6	302.6	272.3	240.3	214.0	196.4	190.8
77.5°	198.5	209.7	214.5	213.0	210.1	197.7	178.5	157.6	148.2	139.9	135.7
80°	155.7	160.5	162.1	158.1	153.3	138.9	126.1	117.4	108.6	105.4	103.8
82.5°	115.4	119.6	115.4	116.6	106.0	94.2	87.2	84.2	80.5	79.2	77.6
85°	61.5	60.7	59.1	55.1	47.9	46.3	45.5	44.7	43.1	43.9	42.3
87.5°	22.5	21.2	19.3	19.3	19.8	19.0	20.1	20.6	21.0	20.7	22.4
90°	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2	31.0
95°	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3	32.0
97.5°	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4	34.6
100°	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2	47.3
102.5°	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1	169.3
105°	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3	409.9
107.5°	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8	507.1
110°	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6	573.2





TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3	637.1
115°	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1	732.7
117.5°	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0	828.8
120°	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8	888.3
122.5°	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7	947.0
125°	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1	1029.0
127.5°	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6	1110.5
130°	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9	1160.1
132.5°	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6	1208.9
135°	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6	1276.2
137.5°	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0	1340.6
140°	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6	1380.5
142.5°	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8	1417.4
145°	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9	1470.1
147.5°	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2	1516.5
150°	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1	1546.1
152.5°	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5	1571.9
155°	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6	1606.8
157.5°	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3	1636.8
160°	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2	1655.9
162.5°	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7	1671.5
165°	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1	1693.4
167.5°	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9	1709.4
170°	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0	1719.3
172.5°	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2	1725.5
175°	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3	1732.9
177.5°	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9	1735.8
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2078.7	2081.3	2083.2	2089.6	2090.2	2096.0	2090.2
5°	2250.7	2261.9	2279.5	2297.0	2298.6	2309.8	2289.8
7.5°	2443.6	2469.5	2485.6	2514.0	2525.2	2532.2	2520.7
10°	2576.5	2600.4	2642.7	2663.5	2684.3	2687.4	2677.9
12.5°	2704.9	2742.9	2776.2	2815.5	2814.6	2842.7	2832.4
15°	2875.9	2915.0	2961.3	3005.2	3021.2	3021.2	3034.0
17.5°	2997.9	3069.6	3117.5	3152.0	3189.6	3196.2	3191.7
20°	3080.3	3157.7	3208.8	3253.5	3279.1	3286.3	3286.3
22.5°	3141.6	3207.5	3257.4	3297.6	3318.7	3327.1	3324.6
25°	3184.1	3240.7	3271.1	3283.1	3288.6	3287.1	3271.9
27.5°	3125.9	3123.4	3104.2	3067.5	3039.9	3023.1	3003.9
30°	3014.8	2973.3	2925.4	2872.7	2804.8	2752.9	2736.9
32.5°	2849.4	2756.1	2675.0	2587.2	2514.2	2462.3	2440.6
35°	2529.4	2381.7	2261.1	2155.7	2079.1	2031.2	2015.2
37.5°	2149.6	2006.7	1857.4	1755.2	1691.7	1643.3	1625.2
40°	1908.2	1752.5	1622.4	1526.6	1461.1	1414.0	1413.2
42.5°	1687.8	1539.2	1416.7	1347.7	1277.1	1246.0	1245.8
45°	1382.0	1263.1	1159.3	1105.0	1062.7	1037.1	1029.9
47.5°	1144.3	1045.9	976.8	933.5	899.0	882.7	872.2
50°	1010.8	924.6	869.5	831.9	812.8	792.0	790.4
52.5°	899.6	830.0	787.1	756.6	732.3	719.8	720.2
55°	756.1	701.0	670.7	647.5	628.3	618.8	614.8
57.5°	637.0	595.6	573.6	552.3	544.2	536.7	534.6
60°	562.9	534.9	514.2	497.4	485.4	483.0	482.2
62.5°	501.6	472.3	458.0	445.0	436.3	432.6	431.1
65°	413.6	392.0	379.2	368.9	365.7	360.1	359.3
67.5°	333.4	320.5	312.0	304.8	300.5	300.2	300.2
70°	284.2	277.0	269.9	265.9	263.5	261.9	261.9
72.5°	242.1	236.8	230.9	228.8	228.3	226.7	226.1
75°	184.4	178.8	179.6	175.7	172.5	168.5	166.1
77.5°	130.8	126.8	126.0	125.5	122.8	122.3	123.6
80°	101.4	97.4	96.6	97.4	96.6	94.2	94.2
82.5°	77.1	73.8	73.0	72.5	71.7	72.5	71.2
85°	41.5	39.9	39.9	39.9	41.5	40.7	39.9
87.5°	21.4	21.1	22.0	21.5	21.6	21.1	21.8
90°	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.7	574.3	575.0	575.9	576.8	577.6	578.5



TEST NUMBER: P333107

CATALOG NUMBER: S124RDIW-S1195D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)