

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333100

Luminaire Tested: **S124RDIW-S1195D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333100
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D770U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7674.5 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	102	98	94	91	96	92	89	86	82	79	77	72	70	68	63	62	61	56
2	93	86	80	75	87	81	76	71	72	68	65	64	61	58	56	54	52	48
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	32
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	34	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	28	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15998	15998	15998	15998
5°	18556	16046	14182	16046
10°	21952	15976	12658	15976
15°	25357	15828	10877	15828
20°	28233	15625	9836	15625
25°	29144	15425	9132	15425
30°	25513	15183	8708	15183
35°	19860	14824	8451	14824
40°	14893	14413	8313	14413
45°	11758	13755	8241	13755
50°	9927	12995	8002	12995
55°	8653	12159	7574	12159
60°	7786	11292	6704	11292
65°	6863	10355	5765	10355
70°	6182	9385	5202	9385
75°	5181	8319	4432	8319
80°	4379	7090	4156	7090
85°	3696	5548	3696	5548



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.0	2.5
10°-20°	579.2	7.5
20°-30°	905.9	11.8
30°-40°	1007.1	13.1
40°-50°	893.5	11.6
50°-60°	696.2	9.1
60°-70°	455.8	5.9
70°-80°	224.2	2.9
80°-90°	58.2	0.8
90°-100°	63.3	0.8
100°-110°	187.5	2.4
110°-120°	318.2	4.1
120°-130°	419.6	5.5
130°-140°	471.3	6.1
140°-150°	463.1	6.0
150°-160°	389.5	5.1
160°-170°	259.1	3.4
170°-180°	90.7	1.2
0°-30°	1677.1	21.9
0°-40°	2684.1	35.0
0°-60°	4273.8	55.7
0°-90°	5012.0	65.3
90°-120°	569.0	7.4
90°-150°	1923.1	25.1
90°-180°	2662.0	34.7
0°-180°	7674.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1982	1982	1982	1982	1982	
5°	2290	1980	1750	1980	2290	232
15°	3034	1894	1301	1894	3034	863
25°	3272	1732	1025	1732	3272	1452
35°	2015	1504	858	1504	2015	1263
45°	1030	1205	722	1205	1030	816
55°	615	864	538	864	615	559
65°	359	542	302	542	359	361
75°	166	267	142	267	166	183
85°	40	60	40	60	40	46
90°	22	2	22	2	22	13
95°	59	44	59	44	59	61
105°	181	173	181	173	181	191
115°	321	324	321	324	321	317
125°	468	471	468	471	468	417
135°	609	608	609	608	609	470
145°	739	738	739	738	739	463
155°	845	846	845	846	845	389
165°	919	921	919	921	919	259
175°	954	958	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2090.2	2096.0	2090.2	2089.6	2083.2	2081.3	2078.7	2070.4	2055.1	2046.2	2048.1
5°	2289.8	2309.8	2298.6	2297.0	2279.5	2261.9	2250.7	2225.2	2198.0	2179.7	2164.5
7.5°	2520.7	2532.2	2525.2	2514.0	2485.6	2469.5	2443.6	2409.9	2361.2	2324.0	2290.0
10°	2677.9	2687.4	2684.3	2663.5	2642.7	2600.4	2576.5	2529.4	2467.9	2419.2	2373.7
12.5°	2832.4	2842.7	2814.6	2815.5	2776.2	2742.9	2704.9	2645.6	2574.6	2511.8	2454.8
15°	3034.0	3021.2	3021.2	3005.2	2961.3	2915.0	2875.9	2813.6	2724.2	2649.1	2570.1
17.5°	3191.7	3196.2	3189.6	3152.0	3117.5	3069.6	2997.9	2925.2	2842.2	2741.4	2660.6
20°	3286.3	3286.3	3279.1	3253.5	3208.8	3157.7	3080.3	3001.2	2895.8	2794.4	2703.4
22.5°	3324.6	3327.1	3318.7	3297.6	3257.4	3207.5	3141.6	3061.3	2952.7	2838.5	2725.8
25°	3271.9	3287.1	3288.6	3283.1	3271.1	3240.7	3184.1	3101.8	3004.4	2880.7	2759.3
27.5°	3003.9	3023.1	3039.9	3067.5	3104.2	3123.4	3125.9	3084.1	2999.1	2880.0	2757.9
30°	2736.9	2752.9	2804.8	2872.7	2925.4	2973.3	3014.8	3026.0	2978.1	2871.1	2742.5
32.5°	2440.6	2462.3	2514.2	2587.2	2675.0	2756.1	2849.4	2896.9	2895.7	2831.5	2712.5
35°	2015.2	2031.2	2079.1	2155.7	2261.1	2381.7	2529.4	2644.3	2722.6	2717.0	2644.3
37.5°	1625.2	1643.3	1691.7	1755.2	1857.4	2006.7	2149.6	2308.0	2452.7	2534.0	2509.7
40°	1413.2	1414.0	1461.1	1526.6	1622.4	1752.5	1908.2	2083.8	2245.1	2376.9	2402.4
42.5°	1245.8	1246.0	1277.1	1347.7	1416.7	1539.2	1687.8	1862.2	2051.0	2203.1	2270.8
45°	1029.9	1037.1	1062.7	1105.0	1159.3	1263.1	1382.0	1544.1	1755.7	1936.1	2048.7
47.5°	872.2	882.7	899.0	933.5	976.8	1045.9	1144.3	1289.9	1462.0	1660.5	1820.7
50°	790.4	792.0	812.8	831.9	869.5	924.6	1010.8	1132.1	1290.2	1481.0	1659.1
52.5°	720.2	719.8	732.3	756.6	787.1	830.0	899.6	1010.1	1150.3	1321.4	1505.2
55°	614.8	618.8	628.3	647.5	670.7	701.0	756.1	839.1	949.3	1095.4	1262.3
57.5°	534.6	536.7	544.2	552.3	573.6	595.6	637.0	694.6	787.6	907.2	1062.7
60°	482.2	483.0	485.4	497.4	514.2	534.9	562.9	611.6	689.8	799.2	922.2
62.5°	431.1	432.6	436.3	445.0	458.0	472.3	501.6	540.7	605.5	698.9	809.7
65°	359.3	360.1	365.7	368.9	379.2	392.0	413.6	439.9	484.6	562.9	646.7
67.5°	300.2	300.2	300.5	304.8	312.0	320.5	333.4	354.5	388.2	436.3	510.2
70°	261.9	261.9	263.5	265.9	269.9	277.0	284.2	300.2	325.0	364.1	420.8
72.5°	226.1	226.7	228.3	228.8	230.9	236.8	242.1	252.3	270.7	300.2	346.0
75°	166.1	168.5	172.5	175.7	179.6	178.8	184.4	190.8	196.4	214.0	240.3
77.5°	123.6	122.3	122.8	125.5	126.0	126.8	130.8	135.7	139.9	148.2	157.6
80°	94.2	94.2	96.6	97.4	96.6	97.4	101.4	103.8	105.4	108.6	117.4
82.5°	71.2	72.5	71.7	72.5	73.0	73.8	77.1	77.6	79.2	80.5	84.2
85°	39.9	40.7	41.5	39.9	39.9	39.9	41.5	42.3	43.9	43.1	44.7
87.5°	18.5	17.8	18.4	18.3	18.9	18.1	18.6	19.6	18.2	18.6	18.3
90°	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3	17.3	16.3	15.0
92.5°	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6	30.0	29.4	28.5
95°	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4	56.9	56.4	55.3
97.5°	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4	89.8	89.2	87.9
100°	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2	113.9	113.6	112.1
102.5°	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4	139.0	138.5	137.1
105°	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6	177.1	176.6	176.0
107.5°	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0	218.5	218.1	218.0
110°	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5	246.8	247.1	247.3



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1	276.2	276.2	276.5
115°	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8	321.9	322.1	322.4
117.5°	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7	366.2	366.8	367.0
120°	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4	396.2	397.1	397.6
122.5°	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6	426.2	426.8	427.0
125°	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9	470.2	470.5	470.7
127.5°	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2	512.5	512.9	513.1
130°	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9	542.2	542.5	542.5
132.5°	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8	570.1	570.4	570.6
135°	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6	612.0	612.3	612.3
137.5°	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1	652.5	653.0	652.7
140°	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8	678.9	679.1	679.1
142.5°	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0	704.0	704.0	704.2
145°	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2	776.3	776.5	776.6
150°	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2	817.8	817.4	817.3
155°	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4	845.5
157.5°	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7	871.2	870.7	870.8
160°	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2	886.7	886.2	886.3
162.5°	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0	900.1	899.2	899.4
165°	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3	918.3	917.3	917.7
167.5°	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8	933.8	932.8	932.7
170°	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1	942.1	941.1	940.9
172.5°	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3	948.2	947.0	947.0
175°	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7	953.9
177.5°	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7	958.8	957.9	957.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2041.7	2032.8	2028.3	2018.1	2005.9	1999.5	1993.8	1985.5	1974.6	1963.1	1954.8
5°	2145.3	2126.2	2102.2	2073.5	2047.9	2023.2	2001.6	1980.1	1955.3	1929.8	1904.2
7.5°	2251.7	2214.0	2173.3	2126.2	2080.3	2038.7	2000.3	1963.6	1922.1	1884.9	1851.0
10°	2325.8	2274.7	2218.0	2158.1	2098.2	2046.3	1995.2	1948.9	1897.8	1852.3	1814.0
12.5°	2385.8	2325.8	2257.6	2183.0	2111.0	2048.2	1989.5	1929.1	1871.0	1821.7	1770.6
15°	2485.4	2403.2	2311.4	2222.0	2128.6	2043.1	1964.1	1893.8	1827.6	1758.1	1709.4
17.5°	2554.0	2456.4	2344.8	2237.3	2127.0	2026.2	1935.0	1851.4	1774.9	1704.0	1646.0
20°	2594.8	2487.0	2363.3	2241.1	2117.4	2009.6	1911.4	1818.8	1739.7	1663.1	1603.2
22.5°	2617.8	2498.5	2363.3	2235.4	2107.2	1990.4	1882.6	1786.2	1700.1	1623.5	1557.2
25°	2625.2	2497.4	2359.3	2212.4	2071.9	1948.1	1836.3	1731.7	1635.9	1559.3	1489.0
27.5°	2615.0	2464.5	2323.1	2172.3	2027.3	1896.9	1779.5	1669.6	1573.7	1491.4	1419.4
30°	2599.6	2438.3	2286.6	2130.2	1983.2	1857.9	1734.1	1628.8	1529.0	1443.5	1370.9
32.5°	2566.4	2406.4	2243.2	2082.9	1934.1	1804.9	1687.5	1581.5	1483.6	1396.3	1319.1
35°	2500.6	2338.5	2161.3	1996.8	1850.7	1716.6	1606.4	1504.2	1410.8	1317.4	1235.9
37.5°	2413.9	2248.3	2072.0	1891.9	1745.6	1619.0	1517.9	1422.0	1330.8	1245.5	1155.3
40°	2332.2	2181.3	1999.2	1820.4	1670.3	1548.1	1454.7	1367.7	1275.9	1191.2	1101.0
42.5°	2233.2	2104.6	1920.7	1741.2	1593.0	1475.3	1388.3	1303.2	1219.7	1137.6	1043.5
45°	2067.9	1970.5	1798.0	1625.6	1476.3	1359.7	1279.9	1204.8	1131.3	1053.1	964.5
47.5°	1878.5	1812.5	1663.7	1487.1	1349.0	1244.1	1167.0	1105.6	1043.5	965.3	887.5
50°	1746.9	1704.6	1560.9	1399.6	1267.9	1171.3	1092.2	1034.7	982.8	907.8	838.3
52.5°	1606.4	1583.9	1462.5	1308.3	1181.0	1086.3	1018.8	967.0	914.5	852.2	787.2
55°	1392.4	1404.4	1301.4	1168.1	1048.3	968.5	907.0	863.9	819.2	766.5	716.2
57.5°	1173.7	1217.4	1148.3	1031.2	919.0	845.2	798.9	762.6	725.1	681.4	638.4
60°	1042.7	1079.4	1040.3	937.3	839.1	770.5	727.4	699.4	661.9	622.0	589.2
62.5°	915.0	954.3	931.1	847.9	756.7	697.7	659.6	633.6	605.7	570.9	536.9
65°	754.5	780.0	768.9	711.4	646.7	596.4	561.3	542.1	516.6	491.0	460.7
67.5°	577.9	627.2	620.7	590.2	534.3	495.0	472.0	455.1	431.8	412.8	392.2
70°	475.1	520.6	519.8	495.0	464.7	427.9	412.0	397.6	376.8	358.5	341.7
72.5°	388.8	430.5	436.7	417.7	397.0	369.2	353.9	344.0	323.8	311.2	297.6
75°	272.3	302.6	310.6	310.6	301.0	286.6	273.1	266.7	252.3	241.1	233.1
77.5°	178.5	197.7	210.1	213.0	214.5	209.7	198.5	194.0	183.0	179.0	171.3
80°	126.1	138.9	153.3	158.1	162.1	160.5	155.7	152.5	142.1	138.1	134.9
82.5°	87.2	94.2	106.0	116.6	115.4	119.6	115.4	112.9	105.1	103.6	100.4
85°	45.5	46.3	47.9	55.1	59.1	60.7	61.5	59.9	57.5	57.5	51.9
87.5°	18.1	17.2	18.2	17.9	18.1	20.3	21.9	22.2	20.6	19.1	17.5
90°	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2	4.0	5.9	7.7
92.5°	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9	18.0	20.0	22.1
95°	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5	46.0	47.5	49.0
97.5°	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8	79.0	80.2	81.3
100°	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9	104.6	105.2	105.9
102.5°	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2	131.5	131.7	132.0
105°	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9	173.1	173.3	173.4
107.5°	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7	216.9	217.1	217.3
110°	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4	246.7	247.1	247.4



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3	277.3	277.4	277.5
115°	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6	323.6	323.6	323.6
117.5°	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2	367.4	367.5	367.6
120°	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3	397.0	397.6	398.3
122.5°	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6	426.9	427.1	427.4
125°	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3
127.5°	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8	512.3	512.8	513.3
130°	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3	540.8	541.3	541.8
132.5°	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4	569.8	570.1	570.5
135°	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9	608.8	609.8	610.8
137.5°	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7	650.2	650.6	651.1
140°	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6	677.9	678.3	678.6
142.5°	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1	703.5	703.8	704.1
145°	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5	739.1	739.8	740.5
147.5°	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5	774.3	775.1	775.9
150°	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9	795.5	796.2	796.9
152.5°	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1	815.5	815.9	816.3
155°	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1	846.1	846.1	846.1
157.5°	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2	871.9	871.6	871.3
160°	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7	887.5	887.3	887.2
162.5°	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9	901.5	901.0	900.6
165°	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1	920.6	920.1	919.6
167.5°	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7	935.1	934.4	933.7
170°	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1	943.2	942.4	941.6
172.5°	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0	949.3	948.6	947.9
175°	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2	957.3	956.5	955.7
177.5°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1945.9	1939.5	1931.2	1921.6	1910.1	1899.9	1895.4	1899.3	1901.2	1896.1	1895.4
5°	1886.6	1866.7	1850.7	1826.8	1807.6	1791.6	1780.5	1775.7	1777.3	1764.5	1761.3
7.5°	1820.1	1796.4	1770.2	1741.8	1715.3	1691.8	1679.5	1672.8	1659.3	1653.5	1643.8
10°	1777.3	1745.3	1719.8	1686.2	1655.9	1628.0	1614.4	1603.2	1589.6	1583.2	1569.7
12.5°	1733.2	1696.1	1668.0	1633.2	1602.2	1568.6	1555.6	1534.9	1513.6	1500.2	1482.8
15°	1671.1	1626.4	1592.0	1550.5	1513.8	1475.5	1441.1	1402.8	1388.4	1358.1	1340.5
17.5°	1598.4	1553.1	1510.6	1454.9	1398.2	1350.6	1314.0	1277.3	1255.3	1235.9	1227.0
20°	1550.5	1509.0	1449.9	1385.2	1322.2	1269.5	1239.9	1216.0	1192.0	1178.5	1168.9
22.5°	1505.2	1452.1	1383.5	1313.7	1250.6	1209.4	1184.4	1159.8	1140.3	1127.4	1114.6
25°	1429.2	1359.7	1287.0	1207.2	1164.1	1128.2	1101.0	1081.0	1069.1	1052.3	1045.9
27.5°	1351.1	1266.9	1186.8	1133.1	1088.2	1055.3	1031.7	1016.7	1001.5	990.8	982.5
30°	1291.0	1205.6	1133.7	1082.6	1037.1	1010.0	990.8	973.3	961.3	952.5	946.1
32.5°	1231.6	1146.2	1085.8	1030.9	995.0	968.5	948.0	934.9	925.5	914.2	910.3
35°	1145.7	1069.9	1017.2	967.7	930.9	907.0	891.0	877.5	869.5	866.3	863.9
37.5°	1063.2	1001.0	944.4	903.8	871.1	852.2	833.4	826.7	821.2	815.5	818.1
40°	1010.8	952.5	902.2	859.1	832.7	812.0	800.8	792.8	788.0	788.0	788.0
42.5°	965.4	908.4	859.4	820.8	794.4	776.9	764.4	757.7	756.1	755.5	759.3
45°	895.0	842.3	792.8	760.9	738.5	721.0	713.8	708.2	708.2	711.4	712.2
47.5°	825.2	775.9	736.1	700.4	679.9	668.9	662.7	659.8	660.1	663.3	667.0
50°	782.4	733.7	694.6	662.7	643.5	633.1	627.5	626.0	627.5	627.5	633.1
52.5°	735.8	692.2	653.7	626.9	605.2	595.5	592.4	590.2	591.1	593.7	596.1
55°	667.5	628.3	591.6	566.1	550.1	543.7	536.5	537.3	535.7	537.3	537.3
57.5°	599.0	563.8	529.7	509.4	495.3	486.1	478.2	480.5	478.1	477.8	476.5
60°	554.9	516.6	489.4	471.1	455.1	447.1	439.9	441.5	439.1	437.5	434.3
62.5°	507.0	475.1	449.2	431.5	418.7	409.4	402.2	400.6	395.1	389.6	382.6
65°	437.5	411.2	388.0	371.3	359.3	352.1	346.5	341.7	329.7	317.0	310.6
67.5°	370.0	351.0	329.4	315.2	305.5	296.1	285.4	277.2	266.0	259.0	255.0
70°	326.5	308.2	289.8	276.2	265.9	257.1	245.1	239.5	231.5	228.3	224.4
72.5°	285.0	267.9	250.9	238.6	227.5	220.7	211.3	205.7	202.2	200.9	196.9
75°	222.0	208.4	195.6	184.4	175.7	170.9	166.9	162.9	161.3	154.1	150.1
77.5°	161.9	153.0	145.0	137.0	130.8	127.6	119.9	115.3	112.6	109.2	108.4
80°	126.1	119.8	111.8	107.0	98.2	95.0	91.8	91.0	90.2	89.4	88.6
82.5°	94.9	88.5	80.5	77.6	75.2	73.3	71.4	70.6	69.8	70.3	70.1
85°	47.9	44.7	44.7	43.9	43.1	42.3	41.5	41.5	40.7	41.5	40.7
87.5°	17.9	17.5	17.8	16.8	17.7	18.0	17.5	17.7	18.6	17.5	17.6
90°	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3	19.3	20.3	20.9
92.5°	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6	31.2	31.8	32.2
95°	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4	57.9	58.4	58.6
97.5°	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4	91.0	91.6	91.9
100°	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2	114.5	114.9	115.0
102.5°	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4	139.9	140.3	140.6
105°	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6	178.1	178.6	179.1
107.5°	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0	219.4	219.9	220.1
110°	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5	246.2	245.8	245.9



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1	276.0	276.0	276.0
115°	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8	321.6	321.4	321.3
117.5°	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7	365.1	364.5	364.1
120°	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4	394.6	393.8	393.5
122.5°	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6	425.1	424.5	423.9
125°	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9	469.6	469.2	468.9
127.5°	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2	511.9	511.5	511.2
130°	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9	541.5	541.2	540.7
132.5°	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8	569.5	569.1	568.8
135°	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6	611.3	611.0	610.6
137.5°	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1	651.7	651.3	651.1
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8	678.6	678.4	678.3
142.5°	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0	703.9	703.9	703.9
145°	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9	741.7	741.5	741.2
147.5°	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2	776.1	775.9	775.8
150°	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.8
152.5°	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2	818.6	819.0	819.0
155°	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7	847.3	848.0	848.0
157.5°	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7	872.2	872.7	872.7
160°	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2	887.7	888.2	888.0
162.5°	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0	901.9	902.8	902.8
165°	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3	920.3	921.3	921.5
167.5°	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8	935.7	936.7	936.7
170°	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1	944.1	945.1	945.0
172.5°	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3	950.4	951.5	951.5
175°	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0	957.2	958.3	958.3
177.5°	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7	960.6	961.6	961.5
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1891.6	1892.9	1888.4	1887.1	1888.4	1892.9	1891.6	1895.4	1896.1	1901.2	1899.3
5°	1754.9	1753.3	1749.3	1750.1	1749.3	1753.3	1754.9	1761.3	1764.5	1777.3	1775.7
7.5°	1638.0	1631.8	1633.5	1627.2	1633.5	1631.8	1638.0	1643.8	1653.5	1659.3	1672.8
10°	1566.5	1557.7	1550.5	1544.1	1550.5	1557.7	1566.5	1569.7	1583.2	1589.6	1603.2
12.5°	1468.8	1461.2	1451.5	1453.4	1451.5	1461.2	1468.8	1482.8	1500.2	1513.6	1534.9
15°	1330.1	1318.2	1299.0	1301.4	1299.0	1318.2	1330.1	1340.5	1358.1	1388.4	1402.8
17.5°	1212.8	1212.9	1204.2	1206.2	1204.2	1212.9	1212.8	1227.0	1235.9	1255.3	1277.3
20°	1152.1	1146.5	1147.3	1144.9	1147.3	1146.5	1152.1	1168.9	1178.5	1192.0	1216.0
22.5°	1109.9	1103.1	1097.5	1092.5	1097.5	1103.1	1109.9	1114.6	1127.4	1140.3	1159.8
25°	1038.7	1033.9	1026.8	1025.2	1026.8	1033.9	1038.7	1045.9	1052.3	1069.1	1081.0
27.5°	976.1	975.2	972.3	968.6	972.3	975.2	976.1	982.5	990.8	1001.5	1016.7
30°	939.7	938.1	936.5	934.1	936.5	938.1	939.7	946.1	952.5	961.3	973.3
32.5°	907.2	906.2	904.6	904.8	904.6	906.2	907.2	910.3	914.2	925.5	934.9
35°	860.7	859.9	858.3	857.5	858.3	859.9	860.7	863.9	866.3	869.5	877.5
37.5°	817.3	819.3	818.4	818.2	818.4	819.3	817.3	818.1	815.5	821.2	826.7
40°	787.2	788.0	789.6	788.8	789.6	788.0	787.2	788.0	788.0	788.0	792.8
42.5°	762.3	762.5	764.7	762.0	764.7	762.5	762.3	759.3	755.5	756.1	757.7
45°	717.8	722.6	721.8	721.8	721.8	722.6	717.8	712.2	711.4	708.2	708.2
47.5°	669.1	673.2	674.3	674.2	674.3	673.2	669.1	667.0	663.3	660.1	659.8
50°	637.1	635.5	637.9	637.1	637.9	635.5	637.1	633.1	627.5	627.5	626.0
52.5°	598.2	598.5	598.3	597.5	598.3	598.5	598.2	596.1	593.7	591.1	590.2
55°	538.1	538.9	537.3	538.1	537.3	538.9	538.1	537.3	537.3	535.7	537.3
57.5°	473.0	469.1	470.7	468.8	470.7	469.1	473.0	476.5	477.8	478.1	480.5
60°	426.4	420.0	418.4	415.2	418.4	420.0	426.4	434.3	437.5	439.1	441.5
62.5°	374.0	369.5	364.1	366.6	364.1	369.5	374.0	382.6	389.6	395.1	400.6
65°	304.2	301.0	298.6	301.8	298.6	301.0	304.2	310.6	317.0	329.7	341.7
67.5°	251.8	250.1	250.1	248.5	250.1	250.1	251.8	255.0	259.0	266.0	277.2
70°	224.4	222.0	222.0	220.4	222.0	222.0	224.4	224.4	228.3	231.5	239.5
72.5°	196.2	193.9	194.5	193.5	194.5	193.9	196.2	196.9	200.9	202.2	205.7
75°	145.3	141.3	141.3	142.1	141.3	141.3	145.3	150.1	154.1	161.3	162.9
77.5°	108.4	107.6	108.7	107.3	108.7	107.6	108.4	108.4	109.2	112.6	115.3
80°	88.6	87.8	87.0	89.4	87.0	87.8	88.6	88.6	89.4	90.2	91.0
82.5°	68.8	68.7	68.5	71.5	68.5	68.7	68.8	70.1	70.3	69.8	70.6
85°	41.5	39.9	41.5	39.9	41.5	39.9	41.5	40.7	41.5	40.7	41.5
87.5°	18.9	18.4	17.8	18.5	17.8	18.4	18.9	17.6	17.5	18.6	17.7
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3
92.5°	32.4	32.6	32.8	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6
95°	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4
97.5°	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4
100°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2
102.5°	140.8	140.9	141.0	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4
105°	179.6	180.1	180.6	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6
107.5°	220.1	220.1	220.0	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0
110°	246.4	246.9	247.4	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	276.1	276.2	276.3	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1
115°	321.1	321.0	320.8	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8
117.5°	363.8	363.4	363.1	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7
120°	393.9	394.2	394.5	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4
122.5°	423.3	422.7	422.2	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6
125°	468.6	468.2	467.9	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9
127.5°	511.0	510.7	510.4	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2
130°	540.1	539.4	538.7	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9
132.5°	568.6	568.3	568.0	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8
135°	610.1	609.6	609.1	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6
137.5°	651.2	651.3	651.4	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1
140°	678.1	677.9	677.8	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8
142.5°	703.8	703.8	703.8	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0
145°	740.7	740.2	739.7	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9
147.5°	775.6	775.5	775.3	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2
150°	797.6	797.4	797.3	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9
152.5°	818.6	818.2	817.7	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2
155°	847.3	846.7	846.0	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7
157.5°	872.1	871.6	871.0	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7
160°	887.2	886.3	885.5	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2
162.5°	902.0	901.2	900.4	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0
165°	920.8	920.1	919.5	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3
167.5°	935.7	934.7	933.7	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8
170°	943.8	942.7	941.5	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1
172.5°	950.3	949.2	948.0	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3
175°	957.2	956.0	954.9	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0
177.5°	960.4	959.4	958.3	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1895.4	1899.9	1910.1	1921.6	1931.2	1939.5	1945.9	1954.8	1963.1	1974.6	1985.5
5°	1780.5	1791.6	1807.6	1826.8	1850.7	1866.7	1886.6	1904.2	1929.8	1955.3	1980.1
7.5°	1679.5	1691.8	1715.3	1741.8	1770.2	1796.4	1820.1	1851.0	1884.9	1922.1	1963.6
10°	1614.4	1628.0	1655.9	1686.2	1719.8	1745.3	1777.3	1814.0	1852.3	1897.8	1948.9
12.5°	1555.6	1568.6	1602.2	1633.2	1668.0	1696.1	1733.2	1770.6	1821.7	1871.0	1929.1
15°	1441.1	1475.5	1513.8	1550.5	1592.0	1626.4	1671.1	1709.4	1758.1	1827.6	1893.8
17.5°	1314.0	1350.6	1398.2	1454.9	1510.6	1553.1	1598.4	1646.0	1704.0	1774.9	1851.4
20°	1239.9	1269.5	1322.2	1385.2	1449.9	1509.0	1550.5	1603.2	1663.1	1739.7	1818.8
22.5°	1184.4	1209.4	1250.6	1313.7	1383.5	1452.1	1505.2	1557.2	1623.5	1700.1	1786.2
25°	1101.0	1128.2	1164.1	1207.2	1287.0	1359.7	1429.2	1489.0	1559.3	1635.9	1731.7
27.5°	1031.7	1055.3	1088.2	1133.1	1186.8	1266.9	1351.1	1419.4	1491.4	1573.7	1669.6
30°	990.8	1010.0	1037.1	1082.6	1133.7	1205.6	1291.0	1370.9	1443.5	1529.0	1628.8
32.5°	948.0	968.5	995.0	1030.9	1085.8	1146.2	1231.6	1319.1	1396.3	1483.6	1581.5
35°	891.0	907.0	930.9	967.7	1017.2	1069.9	1145.7	1235.9	1317.4	1410.8	1504.2
37.5°	833.4	852.2	871.1	903.8	944.4	1001.0	1063.2	1155.3	1245.5	1330.8	1422.0
40°	800.8	812.0	832.7	859.1	902.2	952.5	1010.8	1101.0	1191.2	1275.9	1367.7
42.5°	764.4	776.9	794.4	820.8	859.4	908.4	965.4	1043.5	1137.6	1219.7	1303.2
45°	713.8	721.0	738.5	760.9	792.8	842.3	895.0	964.5	1053.1	1131.3	1204.8
47.5°	662.7	668.9	679.9	700.4	736.1	775.9	825.2	887.5	965.3	1043.5	1105.6
50°	627.5	633.1	643.5	662.7	694.6	733.7	782.4	838.3	907.8	982.8	1034.7
52.5°	592.4	595.5	605.2	626.9	653.7	692.2	735.8	787.2	852.2	914.5	967.0
55°	536.5	543.7	550.1	566.1	591.6	628.3	667.5	716.2	766.5	819.2	863.9
57.5°	478.2	486.1	495.3	509.4	529.7	563.8	599.0	638.4	681.4	725.1	762.6
60°	439.9	447.1	455.1	471.1	489.4	516.6	554.9	589.2	622.0	661.9	699.4
62.5°	402.2	409.4	418.7	431.5	449.2	475.1	507.0	536.9	570.9	605.7	633.6
65°	346.5	352.1	359.3	371.3	388.0	411.2	437.5	460.7	491.0	516.6	542.1
67.5°	285.4	296.1	305.5	315.2	329.4	351.0	370.0	392.2	412.8	431.8	455.1
70°	245.1	257.1	265.9	276.2	289.8	308.2	326.5	341.7	358.5	376.8	397.6
72.5°	211.3	220.7	227.5	238.6	250.9	267.9	285.0	297.6	311.2	323.8	344.0
75°	166.9	170.9	175.7	184.4	195.6	208.4	222.0	233.1	241.1	252.3	266.7
77.5°	119.9	127.6	130.8	137.0	145.0	153.0	161.9	171.3	179.0	183.0	194.0
80°	91.8	95.0	98.2	107.0	111.8	119.8	126.1	134.9	138.1	142.1	152.5
82.5°	71.4	73.3	75.2	77.6	80.5	88.5	94.9	100.4	103.6	105.1	112.9
85°	41.5	42.3	43.1	43.9	44.7	44.7	47.9	51.9	57.5	57.5	59.9
87.5°	17.5	18.0	17.7	16.8	17.8	17.5	17.9	17.5	19.1	20.6	22.2
90°	17.3	16.3	15.0	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2
92.5°	30.0	29.4	28.5	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9
95°	56.9	56.4	55.3	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5
97.5°	89.8	89.2	87.9	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8
100°	113.9	113.6	112.1	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9
102.5°	139.0	138.5	137.1	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2
105°	177.1	176.6	176.0	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9
107.5°	218.5	218.1	218.0	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7
110°	246.8	247.1	247.3	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	276.2	276.2	276.5	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3
115°	321.9	322.1	322.4	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6
117.5°	366.2	366.8	367.0	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2
120°	396.2	397.1	397.6	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3
122.5°	426.2	426.8	427.0	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6
125°	470.2	470.5	470.7	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3
127.5°	512.5	512.9	513.1	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8
130°	542.2	542.5	542.5	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3
132.5°	570.1	570.4	570.6	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4
135°	612.0	612.3	612.3	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9
137.5°	652.5	653.0	652.7	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6
142.5°	704.0	704.0	704.2	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1
145°	742.0	742.2	742.0	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5
147.5°	776.3	776.5	776.6	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5
150°	797.9	797.9	797.9	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9
152.5°	817.8	817.4	817.3	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1
155°	846.0	845.4	845.5	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1
157.5°	871.2	870.7	870.8	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2
160°	886.7	886.2	886.3	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7
162.5°	900.1	899.2	899.4	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9
165°	918.3	917.3	917.7	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1
167.5°	933.8	932.8	932.7	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7
170°	942.1	941.1	940.9	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1
172.5°	948.2	947.0	947.0	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0
175°	954.9	953.7	953.9	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2
177.5°	958.8	957.9	957.9	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	1993.8	1999.5	2005.9	2018.1	2028.3	2032.8	2041.7	2048.1	2046.2	2055.1	2070.4
5°	2001.6	2023.2	2047.9	2073.5	2102.2	2126.2	2145.3	2164.5	2179.7	2198.0	2225.2
7.5°	2000.3	2038.7	2080.3	2126.2	2173.3	2214.0	2251.7	2290.0	2324.0	2361.2	2409.9
10°	1995.2	2046.3	2098.2	2158.1	2218.0	2274.7	2325.8	2373.7	2419.2	2467.9	2529.4
12.5°	1989.5	2048.2	2111.0	2183.0	2257.6	2325.8	2385.8	2454.8	2511.8	2574.6	2645.6
15°	1964.1	2043.1	2128.6	2222.0	2311.4	2403.2	2485.4	2570.1	2649.1	2724.2	2813.6
17.5°	1935.0	2026.2	2127.0	2237.3	2344.8	2456.4	2554.0	2660.6	2741.4	2842.2	2925.2
20°	1911.4	2009.6	2117.4	2241.1	2363.3	2487.0	2594.8	2703.4	2794.4	2895.8	3001.2
22.5°	1882.6	1990.4	2107.2	2235.4	2363.3	2498.5	2617.8	2725.8	2838.5	2952.7	3061.3
25°	1836.3	1948.1	2071.9	2212.4	2359.3	2497.4	2625.2	2759.3	2880.7	3004.4	3101.8
27.5°	1779.5	1896.9	2027.3	2172.3	2323.1	2464.5	2615.0	2757.9	2880.0	2999.1	3084.1
30°	1734.1	1857.9	1983.2	2130.2	2286.6	2438.3	2599.6	2742.5	2871.1	2978.1	3026.0
32.5°	1687.5	1804.9	1934.1	2082.9	2243.2	2406.4	2566.4	2712.5	2831.5	2895.7	2896.9
35°	1606.4	1716.6	1850.7	1996.8	2161.3	2338.5	2500.6	2644.3	2717.0	2722.6	2644.3
37.5°	1517.9	1619.0	1745.6	1891.9	2072.0	2248.3	2413.9	2509.7	2534.0	2452.7	2308.0
40°	1454.7	1548.1	1670.3	1820.4	1999.2	2181.3	2332.2	2402.4	2376.9	2245.1	2083.8
42.5°	1388.3	1475.3	1593.0	1741.2	1920.7	2104.6	2233.2	2270.8	2203.1	2051.0	1862.2
45°	1279.9	1359.7	1476.3	1625.6	1798.0	1970.5	2067.9	2048.7	1936.1	1755.7	1544.1
47.5°	1167.0	1244.1	1349.0	1487.1	1663.7	1812.5	1878.5	1820.7	1660.5	1462.0	1289.9
50°	1092.2	1171.3	1267.9	1399.6	1560.9	1704.6	1746.9	1659.1	1481.0	1290.2	1132.1
52.5°	1018.8	1086.3	1181.0	1308.3	1462.5	1583.9	1606.4	1505.2	1321.4	1150.3	1010.1
55°	907.0	968.5	1048.3	1168.1	1301.4	1404.4	1392.4	1262.3	1095.4	949.3	839.1
57.5°	798.9	845.2	919.0	1031.2	1148.3	1217.4	1173.7	1062.7	907.2	787.6	694.6
60°	727.4	770.5	839.1	937.3	1040.3	1079.4	1042.7	922.2	799.2	689.8	611.6
62.5°	659.6	697.7	756.7	847.9	931.1	954.3	915.0	809.7	698.9	605.5	540.7
65°	561.3	596.4	646.7	711.4	768.9	780.0	754.5	646.7	562.9	484.6	439.9
67.5°	472.0	495.0	534.3	590.2	620.7	627.2	577.9	510.2	436.3	388.2	354.5
70°	412.0	427.9	464.7	495.0	519.8	520.6	475.1	420.8	364.1	325.0	300.2
72.5°	353.9	369.2	397.0	417.7	436.7	430.5	388.8	346.0	300.2	270.7	252.3
75°	273.1	286.6	301.0	310.6	310.6	302.6	272.3	240.3	214.0	196.4	190.8
77.5°	198.5	209.7	214.5	213.0	210.1	197.7	178.5	157.6	148.2	139.9	135.7
80°	155.7	160.5	162.1	158.1	153.3	138.9	126.1	117.4	108.6	105.4	103.8
82.5°	115.4	119.6	115.4	116.6	106.0	94.2	87.2	84.2	80.5	79.2	77.6
85°	61.5	60.7	59.1	55.1	47.9	46.3	45.5	44.7	43.1	43.9	42.3
87.5°	21.9	20.3	18.1	17.9	18.2	17.2	18.1	18.3	18.6	18.2	19.6
90°	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3
92.5°	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6
95°	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4
97.5°	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4
100°	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2
102.5°	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4
105°	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6
107.5°	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0
110°	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1
115°	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8
117.5°	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7
120°	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4
122.5°	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6
125°	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9
127.5°	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2
130°	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9
132.5°	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8
135°	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6
137.5°	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1
140°	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8
142.5°	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0
145°	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9
147.5°	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2
150°	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2
155°	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7
157.5°	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7
160°	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2
162.5°	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0
165°	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3
167.5°	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8
170°	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1
172.5°	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3
175°	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0
177.5°	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7	1981.7
2.5°	2078.7	2081.3	2083.2	2089.6	2090.2	2096.0	2090.2
5°	2250.7	2261.9	2279.5	2297.0	2298.6	2309.8	2289.8
7.5°	2443.6	2469.5	2485.6	2514.0	2525.2	2532.2	2520.7
10°	2576.5	2600.4	2642.7	2663.5	2684.3	2687.4	2677.9
12.5°	2704.9	2742.9	2776.2	2815.5	2814.6	2842.7	2832.4
15°	2875.9	2915.0	2961.3	3005.2	3021.2	3021.2	3034.0
17.5°	2997.9	3069.6	3117.5	3152.0	3189.6	3196.2	3191.7
20°	3080.3	3157.7	3208.8	3253.5	3279.1	3286.3	3286.3
22.5°	3141.6	3207.5	3257.4	3297.6	3318.7	3327.1	3324.6
25°	3184.1	3240.7	3271.1	3283.1	3288.6	3287.1	3271.9
27.5°	3125.9	3123.4	3104.2	3067.5	3039.9	3023.1	3003.9
30°	3014.8	2973.3	2925.4	2872.7	2804.8	2752.9	2736.9
32.5°	2849.4	2756.1	2675.0	2587.2	2514.2	2462.3	2440.6
35°	2529.4	2381.7	2261.1	2155.7	2079.1	2031.2	2015.2
37.5°	2149.6	2006.7	1857.4	1755.2	1691.7	1643.3	1625.2
40°	1908.2	1752.5	1622.4	1526.6	1461.1	1414.0	1413.2
42.5°	1687.8	1539.2	1416.7	1347.7	1277.1	1246.0	1245.8
45°	1382.0	1263.1	1159.3	1105.0	1062.7	1037.1	1029.9
47.5°	1144.3	1045.9	976.8	933.5	899.0	882.7	872.2
50°	1010.8	924.6	869.5	831.9	812.8	792.0	790.4
52.5°	899.6	830.0	787.1	756.6	732.3	719.8	720.2
55°	756.1	701.0	670.7	647.5	628.3	618.8	614.8
57.5°	637.0	595.6	573.6	552.3	544.2	536.7	534.6
60°	562.9	534.9	514.2	497.4	485.4	483.0	482.2
62.5°	501.6	472.3	458.0	445.0	436.3	432.6	431.1
65°	413.6	392.0	379.2	368.9	365.7	360.1	359.3
67.5°	333.4	320.5	312.0	304.8	300.5	300.2	300.2
70°	284.2	277.0	269.9	265.9	263.5	261.9	261.9
72.5°	242.1	236.8	230.9	228.8	228.3	226.7	226.1
75°	184.4	178.8	179.6	175.7	172.5	168.5	166.1
77.5°	130.8	126.8	126.0	125.5	122.8	122.3	123.6
80°	101.4	97.4	96.6	97.4	96.6	94.2	94.2
82.5°	77.1	73.8	73.0	72.5	71.7	72.5	71.2
85°	41.5	39.9	39.9	39.9	41.5	40.7	39.9
87.5°	18.6	18.1	18.9	18.3	18.4	17.8	18.5
90°	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.2	245.8	245.9	246.4	246.9	247.4	247.9



TEST NUMBER: P333100

CATALOG NUMBER: S124RDIW-S1195D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)