

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332739-940

Luminaire Tested: **S124DIW-S350D1560U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332739-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6972.3 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	65	73	67	63	59	51	48	45	36	34	33	23	22	21	15
3	76	67	60	54	67	59	54	49	45	41	38	32	30	28	20	19	18	12
4	69	59	52	46	61	53	46	41	40	36	32	29	26	24	18	16	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12	8
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9	7
9	46	35	28	23	41	31	25	21	24	20	16	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4112	4112	4112	4112
5°	4843	4123	3639	4123
10°	5799	4105	3277	4105
15°	6861	4064	3010	4064
20°	7640	4021	2770	4021
25°	7764	3958	2605	3958
30°	6605	3899	2553	3899
35°	5078	3802	2553	3802
40°	3959	3687	2602	3687
45°	3301	3515	2646	3515
50°	2905	3304	2735	3304
55°	2662	3054	2846	3054
60°	2493	2827	2977	2827
65°	2321	2575	3089	2575
70°	2122	2325	3158	2325
75°	1896	2046	3119	2046
80°	1590	1678	3022	1678
85°	1176	1213	2890	1213



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	0.7
10°-20°	153.0	2.2
20°-30°	242.6	3.5
30°-40°	270.0	3.9
40°-50°	245.7	3.5
50°-60°	200.8	2.9
60°-70°	143.4	2.1
70°-80°	78.9	1.1
80°-90°	26.7	0.4
90°-100°	61.5	0.9
100°-110°	392.1	5.6
110°-120°	750.0	10.8
120°-130°	952.1	13.7
130°-140°	1018.7	14.6
140°-150°	952.6	13.7
150°-160°	768.2	11.0
160°-170°	495.5	7.1
170°-180°	170.8	2.4
0°-30°	445.2	6.4
0°-40°	715.2	10.3
0°-60°	1161.7	16.7
0°-90°	1410.8	20.2
90°-120°	1203.6	17.3
90°-150°	4127.0	59.2
90°-180°	5561.0	79.8
0°-180°	6972.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	598	509	449	509	598	61
15°	821	486	360	486	821	232
25°	872	444	292	444	872	384
35°	515	386	259	386	515	327
45°	289	308	232	308	289	228
55°	189	217	202	217	189	171
65°	122	135	162	135	122	120
75°	61	66	100	66	61	65
85°	13	13	31	13	13	17
90°	40	4	40	4	40	18
95°	39	74	39	74	39	31
105°	383	405	383	405	383	334
115°	761	756	761	756	761	753
125°	1070	1062	1070	1062	1070	953
135°	1327	1318	1327	1318	1327	1022
145°	1528	1520	1528	1520	1528	955
155°	1665	1666	1665	1666	1665	768
165°	1750	1758	1750	1758	1750	494
175°	1787	1798	1787	1798	1787	170
180°	1798	1798	1798	1798	1798	



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	542.2	542.1	540.4	540.0	538.9	537.3	537.0	534.2	528.9	526.3	525.7
5°	597.6	601.9	596.4	595.3	594.7	587.7	584.2	580.0	570.2	564.5	560.1
7.5°	663.9	664.3	661.9	660.0	654.6	648.5	639.4	629.7	618.1	606.2	597.1
10°	707.4	709.1	706.3	706.0	695.2	688.4	674.9	663.5	650.4	635.9	622.6
12.5°	753.3	751.0	749.6	740.6	738.5	726.2	710.5	698.8	678.6	661.8	644.2
15°	820.9	816.3	813.3	800.9	794.8	777.7	761.0	748.1	721.8	696.6	677.6
17.5°	860.6	865.2	858.4	853.3	837.5	825.5	808.4	781.4	760.8	729.6	705.6
20°	889.3	889.7	885.9	880.7	868.3	853.0	834.5	804.9	780.2	749.2	716.2
22.5°	897.1	897.2	895.5	890.6	881.2	868.9	850.2	825.5	795.6	761.9	728.9
25°	871.6	870.8	872.6	878.2	874.6	870.8	860.0	841.6	813.8	778.1	742.6
27.5°	776.9	782.7	793.4	806.9	819.9	829.8	832.6	828.8	811.6	782.3	745.1
30°	708.6	715.9	723.9	737.4	763.6	778.6	795.0	807.4	800.5	777.0	742.4
32.5°	633.7	635.5	647.4	662.7	686.7	715.5	741.6	767.0	775.3	763.0	734.1
35°	515.3	518.4	531.2	546.4	575.7	611.0	650.2	685.3	714.2	725.8	711.0
37.5°	420.5	429.0	438.1	454.4	480.3	512.0	552.8	598.2	641.2	670.1	675.0
40°	375.7	380.9	387.4	399.9	421.9	453.1	488.1	540.0	585.9	627.2	640.7
42.5°	340.2	343.3	347.3	358.6	375.2	406.4	438.4	484.0	529.9	579.4	602.1
45°	289.1	292.3	299.1	305.6	318.3	339.7	369.5	407.1	453.3	501.0	542.8
47.5°	252.3	254.2	258.2	265.3	276.1	290.3	314.4	345.8	388.6	435.0	479.5
50°	231.3	233.0	236.1	242.5	250.7	263.4	283.2	312.5	346.1	392.7	436.4
52.5°	214.7	215.4	217.8	222.0	228.6	239.2	255.6	279.8	311.0	352.6	396.1
55°	189.1	189.9	192.1	195.2	200.9	207.7	220.1	238.3	265.5	301.6	339.4
57.5°	168.0	168.6	170.3	171.6	176.3	181.7	191.4	204.3	224.9	255.6	289.3
60°	154.4	154.1	156.1	157.2	160.4	165.1	172.5	184.9	202.8	227.5	258.5
62.5°	141.3	140.7	142.5	143.9	145.7	149.6	155.7	165.4	180.0	202.3	229.2
65°	121.5	120.7	121.8	123.5	125.1	127.2	131.7	140.4	151.9	168.0	188.4
67.5°	101.7	102.6	102.8	103.6	104.6	107.5	110.5	116.6	124.8	137.7	155.0
70°	89.9	90.2	91.0	91.0	91.6	94.2	96.7	100.2	108.3	120.1	134.2
72.5°	78.1	79.0	78.6	79.3	79.8	81.5	83.3	86.8	93.5	102.4	114.3
75°	60.8	61.4	61.4	61.6	62.2	62.9	64.4	66.9	71.8	78.3	86.5
77.5°	44.3	44.4	44.7	45.5	45.5	46.5	47.5	49.6	52.0	56.4	61.5
80°	34.2	34.6	34.4	34.9	34.9	35.7	36.1	38.6	39.7	42.6	46.6
82.5°	25.1	25.5	25.4	26.0	26.4	26.6	27.1	28.2	29.2	31.8	33.4
85°	12.7	13.1	12.7	13.1	13.7	13.9	14.5	14.8	15.6	16.2	17.7
87.5°	11.8	12.1	12.0	12.1	12.3	12.2	12.0	11.5	11.9	11.7	11.9
90°	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2	31.4	29.6	27.2
92.5°	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1	30.3	28.5	26.1
95°	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2	31.4	29.6	29.2
97.5°	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8	35.7	35.5	68.8
100°	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0	54.1	59.2	100.4
102.5°	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5	230.2	285.1	290.4
105°	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9	422.2	419.5	418.0
107.5°	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8	524.4	523.1	521.0
110°	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2	593.6	593.0	591.2



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6	660.7	660.8	660.0
115°	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6	759.0	758.4	758.8
117.5°	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3	859.4	859.5	858.9
120°	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0	920.4	919.8	920.1
122.5°	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9	981.5	981.1	980.7
125°	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8	1066.0	1065.1	1065.6
127.5°	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3	1151.5	1151.6	1150.2
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8	1202.5	1202.2	1201.3
132.5°	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4	1253.0	1252.8	1251.6
135°	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0	1322.5	1321.9	1320.7
137.5°	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9	1389.2	1388.6	1387.2
140°	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3	1430.4	1429.4	1428.9
142.5°	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5	1468.8	1468.2	1467.8
145°	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2	1523.8	1523.6	1523.6
147.5°	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2	1572.0	1571.7	1572.0
150°	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9	1602.9	1602.9	1603.2
152.5°	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7	1629.2	1628.7	1629.2
155°	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8	1664.6	1663.4	1664.4
157.5°	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8	1694.9
160°	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2	1713.5
162.5°	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0	1731.1	1729.3	1729.7
165°	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6	1753.2	1750.9	1750.9
167.5°	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3	1769.6	1767.0	1767.2
170°	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5	1780.1	1777.7	1777.4
172.5°	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0	1786.5	1784.2	1783.9
175°	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5	1793.9	1791.2	1790.9
177.5°	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6	1797.7	1795.7	1795.3
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	525.8	523.4	521.7	520.4	516.7	514.5	512.8	510.5	507.7	504.9	501.3
5°	555.6	548.5	543.2	535.2	527.6	521.3	514.7	508.8	501.7	493.8	488.1
7.5°	587.0	576.3	562.7	550.8	537.4	525.8	515.5	504.9	493.8	483.0	473.2
10°	607.0	593.3	578.0	560.1	543.2	528.2	514.3	500.8	487.7	474.7	463.4
12.5°	628.4	611.3	588.8	567.8	548.9	528.9	512.1	495.5	479.7	466.0	453.0
15°	657.2	632.5	606.5	578.5	553.6	530.1	507.1	486.2	468.5	450.3	437.7
17.5°	674.8	644.3	614.7	585.3	555.2	525.6	500.8	476.7	454.5	436.5	420.5
20°	686.5	656.1	619.2	589.9	554.0	523.6	494.9	468.1	444.9	425.7	409.2
22.5°	696.6	661.6	624.6	585.9	550.3	518.0	486.6	459.7	436.0	415.7	399.9
25°	702.1	661.8	621.7	583.3	542.8	504.6	476.1	444.4	419.1	397.8	380.9
27.5°	702.8	659.6	614.2	571.6	529.8	494.2	458.3	429.9	403.7	381.1	364.9
30°	700.9	655.9	607.2	561.0	519.0	480.4	449.1	418.3	391.5	369.1	352.2
32.5°	694.9	648.2	598.1	549.1	505.6	467.8	435.6	406.3	380.1	358.1	340.4
35°	677.9	631.6	578.3	527.4	482.9	444.7	415.5	385.8	359.6	338.8	321.6
37.5°	651.1	609.4	555.1	502.5	458.7	420.4	391.5	364.6	341.0	319.8	302.3
40°	627.9	591.1	536.6	485.4	438.1	401.6	374.6	349.9	326.5	306.4	289.7
42.5°	601.0	569.0	518.8	464.5	418.8	382.2	355.9	333.7	311.7	293.1	276.4
45°	553.1	532.0	484.7	434.5	387.0	352.4	327.3	307.9	289.4	271.2	257.3
47.5°	498.1	487.6	447.8	400.1	355.1	320.9	299.2	281.2	264.9	249.6	237.3
50°	461.1	456.0	421.7	375.7	332.6	300.5	278.6	263.1	249.2	235.8	224.1
52.5°	424.6	424.5	393.4	351.3	311.5	280.6	258.8	244.4	232.4	221.4	211.0
55°	368.9	374.8	350.5	313.0	277.3	249.4	229.8	217.0	208.5	199.5	191.6
57.5°	317.7	327.5	307.5	274.4	244.6	219.0	201.9	192.3	183.2	177.7	172.0
60°	284.3	293.6	277.9	250.1	222.0	200.1	183.8	175.1	167.4	163.5	159.5
62.5°	254.6	262.8	251.3	225.4	201.1	179.9	166.2	157.9	152.7	148.6	145.9
65°	212.1	219.1	209.1	190.4	169.4	152.6	141.4	134.8	129.8	128.1	125.1
67.5°	171.5	177.8	172.5	156.5	139.7	126.9	118.2	111.9	108.9	107.5	105.3
70°	147.3	153.6	147.9	134.0	121.1	110.4	102.1	98.5	95.4	94.8	91.8
72.5°	126.9	131.2	125.5	114.6	103.6	94.5	88.1	84.4	82.8	81.6	80.0
75°	95.1	99.0	95.1	86.8	78.9	72.6	67.1	65.6	63.8	63.1	62.1
77.5°	67.3	70.6	67.8	62.5	56.6	51.7	48.8	46.9	46.5	45.4	45.9
80°	51.5	53.6	50.8	47.3	42.6	39.2	37.2	36.1	34.9	34.4	35.2
82.5°	37.0	37.9	36.5	34.1	30.7	28.4	27.0	25.8	25.5	25.6	25.6
85°	19.2	19.0	18.8	16.7	15.6	14.2	13.3	13.1	12.8	13.3	13.7
87.5°	11.4	11.1	10.4	9.2	8.0	6.9	6.1	5.2	6.1	6.9	7.7
90°	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0	7.3	10.6	13.9
92.5°	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9	17.1	17.3	17.5
95°	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9	63.8	53.7	43.5
97.5°	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0	163.4	169.7	176.1
100°	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5	226.0	231.3	236.7
102.5°	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5	295.5	299.4	303.4
105°	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7	406.5	408.3	410.2
107.5°	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9	510.9	511.8	512.6
110°	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9	581.8	582.7	583.6



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8	651.4	653.0	654.6
115°	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7	756.6	757.5	758.4
117.5°	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2	852.4	853.6	854.8
120°	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8	916.9	918.2	919.4
122.5°	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0	976.7	977.4	978.1
125°	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4	1063.5	1064.7	1066.0
127.5°	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1	1144.4	1144.7	1145.0
130°	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9	1197.1	1197.4	1197.7
132.5°	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2	1245.7	1246.3	1246.9
135°	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9	1317.5	1317.2	1317.0
137.5°	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2	1382.2	1382.3	1382.5
140°	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1	1424.7	1425.3	1425.8
142.5°	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7	1462.8	1463.9	1465.0
145°	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6	1520.5	1521.3	1522.2
147.5°	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6	1567.2	1568.9	1570.6
150°	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9	1600.1	1601.2	1602.5
152.5°	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8	1627.8	1628.8	1629.7
155°	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2	1666.4	1666.7	1667.1
157.5°	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2	1699.1	1698.9	1698.7
160°	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6	1717.7	1716.8	1715.9
162.5°	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8	1734.6	1733.5	1732.4
165°	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6	1756.0	1754.6	1753.1
167.5°	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8	1773.3	1771.7	1770.1
170°	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5	1782.7	1780.8	1779.1
172.5°	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9	1789.1	1787.3	1785.6
175°	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9	1796.1	1794.3	1792.5
177.5°	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2	1799.5	1797.8	1796.1
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	499.6	498.1	496.0	492.9	490.4	487.7	487.0	486.0	488.0	486.3	485.8
5°	483.3	478.8	473.1	466.6	462.8	457.4	456.3	454.1	452.0	451.8	449.7
7.5°	465.9	459.4	451.9	445.3	439.2	433.1	429.2	428.4	425.3	423.4	421.3
10°	454.8	446.7	438.1	431.8	424.6	418.3	413.8	411.3	409.2	406.9	404.7
12.5°	441.7	433.1	426.0	419.1	410.6	405.8	398.5	394.1	393.7	393.7	388.3
15°	426.3	417.9	406.9	397.2	392.5	383.3	379.2	374.2	371.0	367.8	365.3
17.5°	408.8	398.2	389.7	378.5	369.7	362.3	357.0	354.0	349.2	344.7	341.5
20°	397.8	386.6	377.6	365.7	356.1	347.0	342.5	338.3	334.7	330.9	327.3
22.5°	386.6	375.0	363.9	352.4	343.4	333.8	329.5	323.8	320.4	318.3	314.7
25°	369.1	356.4	343.8	332.8	323.5	315.0	309.4	305.0	301.1	299.4	297.1
27.5°	350.0	337.4	325.2	312.7	302.2	296.0	291.5	288.2	286.0	283.7	282.7
30°	337.9	324.8	311.7	300.1	290.4	284.3	280.1	277.8	276.1	275.0	273.9
32.5°	325.6	312.6	298.9	288.3	279.6	274.1	270.9	268.6	267.8	267.4	267.0
35°	305.8	292.7	280.1	270.5	262.3	260.2	257.4	256.2	255.7	257.3	257.9
37.5°	286.7	274.6	262.9	253.7	248.3	245.2	244.2	244.3	245.8	247.1	248.6
40°	274.4	262.5	251.6	243.5	238.4	236.6	236.1	237.2	238.9	240.4	242.1
42.5°	262.3	250.7	240.8	233.3	229.7	227.9	228.2	229.3	231.7	233.4	235.9
45°	243.8	234.1	224.4	218.2	215.3	215.7	215.7	217.6	219.9	222.7	225.4
47.5°	226.2	216.4	208.5	203.3	201.8	201.4	202.6	205.1	208.4	211.8	215.6
50°	214.5	205.1	198.1	193.5	191.8	192.4	194.1	196.4	200.5	204.7	208.7
52.5°	202.4	193.9	187.5	183.2	182.0	183.2	184.9	188.5	192.1	196.6	201.4
55°	183.8	176.6	171.6	168.4	168.0	168.6	170.5	174.5	179.6	185.3	189.9
57.5°	165.3	159.3	154.6	152.5	152.7	153.3	156.4	161.1	166.6	172.6	178.6
60°	152.8	147.3	143.5	141.8	142.0	143.3	147.1	151.5	158.3	164.2	170.5
62.5°	141.0	136.2	132.5	131.0	130.7	133.5	137.1	141.7	148.5	155.1	161.9
65°	122.0	118.2	115.2	114.4	115.0	117.2	121.8	127.9	133.6	140.5	147.8
67.5°	103.4	100.3	98.3	98.6	99.4	102.5	106.4	111.6	118.2	125.4	132.4
70°	91.6	88.6	86.9	87.1	88.5	92.2	95.6	100.9	107.8	115.2	121.1
72.5°	79.5	77.5	76.0	76.9	78.1	80.7	85.0	90.2	96.4	103.3	109.5
75°	61.0	61.0	60.2	60.8	62.7	65.2	68.4	73.8	80.0	85.5	90.5
77.5°	45.2	44.8	45.3	46.1	47.2	50.2	53.9	57.8	62.3	67.9	72.1
80°	34.6	34.9	35.8	37.2	37.5	39.9	43.7	47.3	50.8	55.5	59.5
82.5°	26.0	26.2	26.8	28.4	28.8	31.3	33.7	37.3	40.6	43.7	47.0
85°	14.2	14.2	15.2	15.9	16.9	18.5	20.1	22.2	25.1	27.2	30.4
87.5°	8.8	9.4	10.5	11.4	12.4	13.6	14.4	16.6	17.7	18.8	20.6
90°	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2	35.0	36.7	38.0
92.5°	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1	33.9	35.7	36.6
95°	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2	35.0	36.7	37.8
97.5°	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8	36.0	36.2	36.5
100°	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0	44.0	38.9	36.5
102.5°	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5	120.6	65.9	38.5
105°	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9	427.7	430.3	426.2
107.5°	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8	527.1	528.3	529.6
110°	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2	594.9	595.4	596.2



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6	660.4	660.3	660.8
115°	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6	760.2	760.8	761.2
117.5°	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3	859.2	859.1	859.0
120°	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0	921.6	922.2	922.2
122.5°	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9	982.2	982.6	982.4
125°	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8	1067.7	1068.6	1069.3
127.5°	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3	1151.1	1150.9	1150.7
130°	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8	1203.1	1203.4	1203.5
132.5°	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4	1253.7	1253.9	1254.0
135°	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0	1323.7	1324.3	1324.9
137.5°	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9	1390.5	1391.2	1391.4
140°	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3	1432.2	1433.1	1433.6
142.5°	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5	1470.2	1470.8	1471.1
145°	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2	1524.5	1524.7	1525.3
147.5°	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2	1572.4	1572.7	1573.0
150°	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9	1602.9	1602.9	1603.1
152.5°	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7	1630.1	1630.7	1630.8
155°	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8	1667.1	1668.2	1668.4
157.5°	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0
160°	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4
162.5°	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0	1734.7	1736.5	1736.3
165°	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6	1758.0	1760.4	1760.2
167.5°	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3	1774.9	1777.5	1777.4
170°	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5	1784.9	1787.3	1787.0
172.5°	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0	1791.4	1793.8	1793.3
175°	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5	1799.3	1802.0	1801.5
177.5°	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6	1801.5	1803.4	1803.0
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	485.4	485.2	483.9	483.8	483.9	485.2	485.4	485.8	486.3	488.0	486.0
5°	448.4	447.4	446.7	449.1	446.7	447.4	448.4	449.7	451.8	452.0	454.1
7.5°	420.5	419.7	417.9	417.2	417.9	419.7	420.5	421.3	423.4	425.3	428.4
10°	402.7	401.8	400.1	399.7	400.1	401.8	402.7	404.7	406.9	409.2	411.3
12.5°	385.4	383.8	383.4	383.9	383.4	383.8	385.4	388.3	393.7	393.7	394.1
15°	362.6	361.7	359.4	360.1	359.4	361.7	362.6	365.3	367.8	371.0	374.2
17.5°	340.0	339.0	336.2	338.7	336.2	339.0	340.0	341.5	344.7	349.2	354.0
20°	325.8	324.1	322.7	322.4	322.7	324.1	325.8	327.3	330.9	334.7	338.3
22.5°	312.4	310.9	310.7	309.3	310.7	310.9	312.4	314.7	318.3	320.4	323.8
25°	295.4	294.0	293.6	292.5	293.6	294.0	295.4	297.1	299.4	301.1	305.0
27.5°	282.5	281.8	281.0	281.3	281.0	281.8	282.5	282.7	283.7	286.0	288.2
30°	274.6	274.4	273.9	273.9	273.9	274.4	274.6	273.9	275.0	276.1	277.8
32.5°	268.0	268.0	268.2	268.2	268.2	268.0	268.0	267.0	267.4	267.8	268.6
35°	258.8	259.4	259.8	259.1	259.8	259.4	258.8	257.9	257.3	255.7	256.2
37.5°	250.4	251.0	251.6	252.4	251.6	251.0	250.4	248.6	247.1	245.8	244.3
40°	244.0	245.4	245.8	246.9	245.8	245.4	244.0	242.1	240.4	238.9	237.2
42.5°	237.9	239.5	240.6	240.9	240.6	239.5	237.9	235.9	233.4	231.7	229.3
45°	228.5	230.2	231.8	231.8	231.8	230.2	228.5	225.4	222.7	219.9	217.6
47.5°	218.9	221.3	222.8	223.2	222.8	221.3	218.9	215.6	211.8	208.4	205.1
50°	212.3	215.3	216.8	217.8	216.8	215.3	212.3	208.7	204.7	200.5	196.4
52.5°	205.9	208.8	210.8	211.3	210.8	208.8	205.9	201.4	196.6	192.1	188.5
55°	194.7	199.0	201.3	202.2	201.3	199.0	194.7	189.9	185.3	179.6	174.5
57.5°	184.3	188.2	190.9	191.5	190.9	188.2	184.3	178.6	172.6	166.6	161.1
60°	176.2	180.5	183.8	184.4	183.8	180.5	176.2	170.5	164.2	158.3	151.5
62.5°	167.9	172.4	175.4	177.0	175.4	172.4	167.9	161.9	155.1	148.5	141.7
65°	153.6	158.1	161.0	161.7	161.0	158.1	153.6	147.8	140.5	133.6	127.9
67.5°	138.0	142.5	144.4	145.6	144.4	142.5	138.0	132.4	125.4	118.2	111.6
70°	127.1	130.6	132.8	133.8	132.8	130.6	127.1	121.1	115.2	107.8	100.9
72.5°	114.6	118.3	120.7	121.0	120.7	118.3	114.6	109.5	103.3	96.4	90.2
75°	95.4	98.8	100.0	100.0	100.0	98.8	95.4	90.5	85.5	80.0	73.8
77.5°	75.5	77.2	78.8	79.2	78.8	77.2	75.5	72.1	67.9	62.3	57.8
80°	62.7	63.8	65.0	65.0	65.0	63.8	62.7	59.5	55.5	50.8	47.3
82.5°	49.5	50.4	51.6	51.5	51.6	50.4	49.5	47.0	43.7	40.6	37.3
85°	30.0	31.8	31.7	31.2	31.7	31.8	30.0	30.4	27.2	25.1	22.2
87.5°	21.2	21.5	22.1	22.6	22.1	21.5	21.2	20.6	18.8	17.7	16.6
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2
92.5°	36.7	36.9	37.0	37.1	37.0	36.9	36.7	36.6	35.7	33.9	32.1
95°	38.1	38.4	38.7	39.0	38.7	38.4	38.1	37.8	36.7	35.0	33.2
97.5°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	36.2	36.0	35.8
100°	36.7	37.1	37.4	37.6	37.4	37.1	36.7	36.5	38.9	44.0	49.0
102.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	65.9	120.6	175.5
105°	415.5	404.7	394.0	383.3	394.0	404.7	415.5	426.2	430.3	427.7	424.9
107.5°	530.7	531.8	533.0	534.1	533.0	531.8	530.7	529.6	528.3	527.1	525.8
110°	597.1	598.0	598.9	599.8	598.9	598.0	597.1	596.2	595.4	594.9	594.2



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	662.0	663.1	664.2	665.4	664.2	663.1	662.0	660.8	660.3	660.4	660.6
115°	761.2	761.2	761.2	761.2	761.2	761.2	761.2	761.2	760.8	760.2	759.6
117.5°	858.8	858.7	858.6	858.4	858.6	858.7	858.8	859.0	859.1	859.2	859.3
120°	921.6	921.0	920.4	919.8	920.4	921.0	921.6	922.2	922.2	921.6	921.0
122.5°	981.9	981.2	980.6	980.1	980.6	981.2	981.9	982.4	982.6	982.2	981.9
125°	1069.5	1069.8	1070.1	1070.4	1070.1	1069.8	1069.5	1069.3	1068.6	1067.7	1066.8
127.5°	1150.5	1150.2	1150.0	1149.8	1150.0	1150.2	1150.5	1150.7	1150.9	1151.1	1151.3
130°	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4	1203.1	1202.8
132.5°	1253.7	1253.5	1253.3	1253.0	1253.3	1253.5	1253.7	1254.0	1253.9	1253.7	1253.4
135°	1325.4	1326.1	1326.7	1327.2	1326.7	1326.1	1325.4	1324.9	1324.3	1323.7	1323.0
137.5°	1391.2	1391.1	1390.9	1390.7	1390.9	1391.1	1391.2	1391.4	1391.2	1390.5	1389.9
140°	1434.0	1434.2	1434.5	1434.9	1434.5	1434.2	1434.0	1433.6	1433.1	1432.2	1431.3
142.5°	1471.2	1471.3	1471.3	1471.4	1471.3	1471.3	1471.2	1471.1	1470.8	1470.2	1469.5
145°	1525.8	1526.4	1527.1	1527.6	1527.1	1526.4	1525.8	1525.3	1524.7	1524.5	1524.2
147.5°	1573.2	1573.5	1573.9	1574.1	1573.9	1573.5	1573.2	1573.0	1572.7	1572.4	1572.2
150°	1603.4	1603.7	1604.0	1604.3	1604.0	1603.7	1603.4	1603.1	1602.9	1602.9	1602.9
152.5°	1630.6	1630.4	1630.2	1630.0	1630.2	1630.4	1630.6	1630.8	1630.7	1630.1	1629.7
155°	1667.5	1666.6	1665.7	1664.8	1665.7	1666.6	1667.5	1668.4	1668.2	1667.1	1665.8
157.5°	1698.5	1696.9	1695.4	1693.8	1695.4	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9
160°	1718.6	1716.8	1715.0	1713.2	1715.0	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8
162.5°	1734.4	1732.3	1730.3	1728.2	1730.3	1732.3	1734.4	1736.3	1736.5	1734.7	1733.0
165°	1757.6	1754.9	1752.2	1749.5	1752.2	1754.9	1757.6	1760.2	1760.4	1758.0	1755.6
167.5°	1774.3	1771.4	1768.4	1765.4	1768.4	1771.4	1774.3	1777.4	1777.5	1774.9	1772.3
170°	1784.0	1781.0	1778.1	1775.0	1778.1	1781.0	1784.0	1787.0	1787.3	1784.9	1782.5
172.5°	1790.1	1786.9	1783.7	1780.4	1783.7	1786.9	1790.1	1793.3	1793.8	1791.4	1789.0
175°	1797.9	1794.3	1790.7	1787.2	1790.7	1794.3	1797.9	1801.5	1802.0	1799.3	1796.5
177.5°	1800.1	1797.2	1794.3	1791.4	1794.3	1797.2	1800.1	1803.0	1803.4	1801.5	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	487.0	487.7	490.4	492.9	496.0	498.1	499.6	501.3	504.9	507.7	510.5
5°	456.3	457.4	462.8	466.6	473.1	478.8	483.3	488.1	493.8	501.7	508.8
7.5°	429.2	433.1	439.2	445.3	451.9	459.4	465.9	473.2	483.0	493.8	504.9
10°	413.8	418.3	424.6	431.8	438.1	446.7	454.8	463.4	474.7	487.7	500.8
12.5°	398.5	405.8	410.6	419.1	426.0	433.1	441.7	453.0	466.0	479.7	495.5
15°	379.2	383.3	392.5	397.2	406.9	417.9	426.3	437.7	450.3	468.5	486.2
17.5°	357.0	362.3	369.7	378.5	389.7	398.2	408.8	420.5	436.5	454.5	476.7
20°	342.5	347.0	356.1	365.7	377.6	386.6	397.8	409.2	425.7	444.9	468.1
22.5°	329.5	333.8	343.4	352.4	363.9	375.0	386.6	399.9	415.7	436.0	459.7
25°	309.4	315.0	323.5	332.8	343.8	356.4	369.1	380.9	397.8	419.1	444.4
27.5°	291.5	296.0	302.2	312.7	325.2	337.4	350.0	364.9	381.1	403.7	429.9
30°	280.1	284.3	290.4	300.1	311.7	324.8	337.9	352.2	369.1	391.5	418.3
32.5°	270.9	274.1	279.6	288.3	298.9	312.6	325.6	340.4	358.1	380.1	406.3
35°	257.4	260.2	262.3	270.5	280.1	292.7	305.8	321.6	338.8	359.6	385.8
37.5°	244.2	245.2	248.3	253.7	262.9	274.6	286.7	302.3	319.8	341.0	364.6
40°	236.1	236.6	238.4	243.5	251.6	262.5	274.4	289.7	306.4	326.5	349.9
42.5°	228.2	227.9	229.7	233.3	240.8	250.7	262.3	276.4	293.1	311.7	333.7
45°	215.7	215.7	215.3	218.2	224.4	234.1	243.8	257.3	271.2	289.4	307.9
47.5°	202.6	201.4	201.8	203.3	208.5	216.4	226.2	237.3	249.6	264.9	281.2
50°	194.1	192.4	191.8	193.5	198.1	205.1	214.5	224.1	235.8	249.2	263.1
52.5°	184.9	183.2	182.0	183.2	187.5	193.9	202.4	211.0	221.4	232.4	244.4
55°	170.5	168.6	168.0	168.4	171.6	176.6	183.8	191.6	199.5	208.5	217.0
57.5°	156.4	153.3	152.7	152.5	154.6	159.3	165.3	172.0	177.7	183.2	192.3
60°	147.1	143.3	142.0	141.8	143.5	147.3	152.8	159.5	163.5	167.4	175.1
62.5°	137.1	133.5	130.7	131.0	132.5	136.2	141.0	145.9	148.6	152.7	157.9
65°	121.8	117.2	115.0	114.4	115.2	118.2	122.0	125.1	128.1	129.8	134.8
67.5°	106.4	102.5	99.4	98.6	98.3	100.3	103.4	105.3	107.5	108.9	111.9
70°	95.6	92.2	88.5	87.1	86.9	88.6	91.6	91.8	94.8	95.4	98.5
72.5°	85.0	80.7	78.1	76.9	76.0	77.5	79.5	80.0	81.6	82.8	84.4
75°	68.4	65.2	62.7	60.8	60.2	61.0	61.0	62.1	63.1	63.8	65.6
77.5°	53.9	50.2	47.2	46.1	45.3	44.8	45.2	45.9	45.4	46.5	46.9
80°	43.7	39.9	37.5	37.2	35.8	34.9	34.6	35.2	34.4	34.9	36.1
82.5°	33.7	31.3	28.8	28.4	26.8	26.2	26.0	25.6	25.6	25.5	25.8
85°	20.1	18.5	16.9	15.9	15.2	14.2	14.2	13.7	13.3	12.8	13.1
87.5°	14.4	13.6	12.4	11.4	10.5	9.4	8.8	7.7	6.9	6.1	5.2
90°	31.4	29.6	27.2	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0
92.5°	30.3	28.5	26.1	23.7	21.3	18.9	17.7	17.5	17.3	17.1	16.9
95°	31.4	29.6	29.2	29.0	28.7	28.4	33.3	43.5	53.7	63.8	73.9
97.5°	35.7	35.5	68.8	102.2	135.5	168.9	182.4	176.1	169.7	163.4	157.0
100°	54.1	59.2	100.4	141.6	182.9	224.1	242.0	236.7	231.3	226.0	220.5
102.5°	230.2	285.1	290.4	295.9	301.2	306.6	307.3	303.4	299.4	295.5	291.5
105°	422.2	419.5	418.0	416.6	415.1	413.6	412.0	410.2	408.3	406.5	404.7
107.5°	524.4	523.1	521.0	519.1	517.0	515.0	513.5	512.6	511.8	510.9	509.9
110°	593.6	593.0	591.2	589.4	587.6	585.9	584.5	583.6	582.7	581.8	580.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	660.7	660.8	660.0	659.2	658.3	657.5	656.2	654.6	653.0	651.4	649.8
115°	759.0	758.4	758.8	759.0	759.3	759.6	759.3	758.4	757.5	756.6	755.7
117.5°	859.4	859.5	858.9	858.3	857.6	856.9	856.0	854.8	853.6	852.4	851.2
120°	920.4	919.8	920.1	920.4	920.7	921.0	920.5	919.4	918.2	916.9	915.8
122.5°	981.5	981.1	980.7	980.3	979.9	979.5	978.9	978.1	977.4	976.7	976.0
125°	1066.0	1065.1	1065.6	1066.2	1066.8	1067.4	1067.1	1066.0	1064.7	1063.5	1062.4
127.5°	1151.5	1151.6	1150.2	1148.9	1147.5	1146.1	1145.3	1145.0	1144.7	1144.4	1144.1
130°	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6	1198.0	1197.7	1197.4	1197.1	1196.9
132.5°	1253.0	1252.8	1251.6	1250.4	1249.4	1248.2	1247.4	1246.9	1246.3	1245.7	1245.2
135°	1322.5	1321.9	1320.7	1319.5	1318.3	1317.1	1316.6	1317.0	1317.2	1317.5	1317.9
137.5°	1389.2	1388.6	1387.2	1386.0	1384.6	1383.3	1382.6	1382.5	1382.3	1382.2	1382.2
140°	1430.4	1429.4	1428.9	1428.3	1427.6	1427.1	1426.5	1425.8	1425.3	1424.7	1424.1
142.5°	1468.8	1468.2	1467.8	1467.5	1467.1	1466.8	1466.1	1465.0	1463.9	1462.8	1461.7
145°	1523.8	1523.6	1523.6	1523.6	1523.6	1523.6	1523.1	1522.2	1521.3	1520.5	1519.6
147.5°	1572.0	1571.7	1572.0	1572.4	1572.6	1572.9	1572.3	1570.6	1568.9	1567.2	1565.6
150°	1602.9	1602.9	1603.2	1603.6	1603.8	1604.1	1603.7	1602.5	1601.2	1600.1	1598.9
152.5°	1629.2	1628.7	1629.2	1629.8	1630.3	1630.9	1630.7	1629.7	1628.8	1627.8	1626.8
155°	1664.6	1663.4	1664.4	1665.3	1666.2	1667.1	1667.3	1667.1	1666.7	1666.4	1666.2
157.5°	1695.4	1693.8	1694.9	1695.9	1696.8	1697.9	1698.5	1698.7	1698.9	1699.1	1699.2
160°	1715.0	1713.2	1713.5	1713.8	1714.0	1714.4	1715.0	1715.9	1716.8	1717.7	1718.6
162.5°	1731.1	1729.3	1729.7	1729.9	1730.2	1730.5	1731.3	1732.4	1733.5	1734.6	1735.8
165°	1753.2	1750.9	1750.9	1750.9	1750.9	1750.9	1751.6	1753.1	1754.6	1756.0	1757.6
167.5°	1769.6	1767.0	1767.2	1767.4	1767.5	1767.7	1768.5	1770.1	1771.7	1773.3	1774.8
170°	1780.1	1777.7	1777.4	1777.2	1776.8	1776.6	1777.3	1779.1	1780.8	1782.7	1784.5
172.5°	1786.5	1784.2	1783.9	1783.6	1783.3	1783.0	1783.8	1785.6	1787.3	1789.1	1790.9
175°	1793.9	1791.2	1790.9	1790.6	1790.3	1790.0	1790.7	1792.5	1794.3	1796.1	1797.9
177.5°	1797.7	1795.7	1795.3	1794.8	1794.3	1793.9	1794.5	1796.1	1797.8	1799.5	1801.2
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	512.8	514.5	516.7	520.4	521.7	523.4	525.8	525.7	526.3	528.9	534.2
5°	514.7	521.3	527.6	535.2	543.2	548.5	555.6	560.1	564.5	570.2	580.0
7.5°	515.5	525.8	537.4	550.8	562.7	576.3	587.0	597.1	606.2	618.1	629.7
10°	514.3	528.2	543.2	560.1	578.0	593.3	607.0	622.6	635.9	650.4	663.5
12.5°	512.1	528.9	548.9	567.8	588.8	611.3	628.4	644.2	661.8	678.6	698.8
15°	507.1	530.1	553.6	578.5	606.5	632.5	657.2	677.6	696.6	721.8	748.1
17.5°	500.8	525.6	555.2	585.3	614.7	644.3	674.8	705.6	729.6	760.8	781.4
20°	494.9	523.6	554.0	589.9	619.2	656.1	686.5	716.2	749.2	780.2	804.9
22.5°	486.6	518.0	550.3	585.9	624.6	661.6	696.6	728.9	761.9	795.6	825.5
25°	476.1	504.6	542.8	583.3	621.7	661.8	702.1	742.6	778.1	813.8	841.6
27.5°	458.3	494.2	529.8	571.6	614.2	659.6	702.8	745.1	782.3	811.6	828.8
30°	449.1	480.4	519.0	561.0	607.2	655.9	700.9	742.4	777.0	800.5	807.4
32.5°	435.6	467.8	505.6	549.1	598.1	648.2	694.9	734.1	763.0	775.3	767.0
35°	415.5	444.7	482.9	527.4	578.3	631.6	677.9	711.0	725.8	714.2	685.3
37.5°	391.5	420.4	458.7	502.5	555.1	609.4	651.1	675.0	670.1	641.2	598.2
40°	374.6	401.6	438.1	485.4	536.6	591.1	627.9	640.7	627.2	585.9	540.0
42.5°	355.9	382.2	418.8	464.5	518.8	569.0	601.0	602.1	579.4	529.9	484.0
45°	327.3	352.4	387.0	434.5	484.7	532.0	553.1	542.8	501.0	453.3	407.1
47.5°	299.2	320.9	355.1	400.1	447.8	487.6	498.1	479.5	435.0	388.6	345.8
50°	278.6	300.5	332.6	375.7	421.7	456.0	461.1	436.4	392.7	346.1	312.5
52.5°	258.8	280.6	311.5	351.3	393.4	424.5	424.6	396.1	352.6	311.0	279.8
55°	229.8	249.4	277.3	313.0	350.5	374.8	368.9	339.4	301.6	265.5	238.3
57.5°	201.9	219.0	244.6	274.4	307.5	327.5	317.7	289.3	255.6	224.9	204.3
60°	183.8	200.1	222.0	250.1	277.9	293.6	284.3	258.5	227.5	202.8	184.9
62.5°	166.2	179.9	201.1	225.4	251.3	262.8	254.6	229.2	202.3	180.0	165.4
65°	141.4	152.6	169.4	190.4	209.1	219.1	212.1	188.4	168.0	151.9	140.4
67.5°	118.2	126.9	139.7	156.5	172.5	177.8	171.5	155.0	137.7	124.8	116.6
70°	102.1	110.4	121.1	134.0	147.9	153.6	147.3	134.2	120.1	108.3	100.2
72.5°	88.1	94.5	103.6	114.6	125.5	131.2	126.9	114.3	102.4	93.5	86.8
75°	67.1	72.6	78.9	86.8	95.1	99.0	95.1	86.5	78.3	71.8	66.9
77.5°	48.8	51.7	56.6	62.5	67.8	70.6	67.3	61.5	56.4	52.0	49.6
80°	37.2	39.2	42.6	47.3	50.8	53.6	51.5	46.6	42.6	39.7	38.6
82.5°	27.0	28.4	30.7	34.1	36.5	37.9	37.0	33.4	31.8	29.2	28.2
85°	13.3	14.2	15.6	16.7	18.8	19.0	19.2	17.7	16.2	15.6	14.8
87.5°	6.1	6.9	8.0	9.2	10.4	11.1	11.4	11.9	11.7	11.9	11.5
90°	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2
92.5°	17.1	17.3	17.5	17.7	18.9	21.3	23.7	26.1	28.5	30.3	32.1
95°	63.8	53.7	43.5	33.3	28.4	28.7	29.0	29.2	29.6	31.4	33.2
97.5°	163.4	169.7	176.1	182.4	168.9	135.5	102.2	68.8	35.5	35.7	35.8
100°	226.0	231.3	236.7	242.0	224.1	182.9	141.6	100.4	59.2	54.1	49.0
102.5°	295.5	299.4	303.4	307.3	306.6	301.2	295.9	290.4	285.1	230.2	175.5
105°	406.5	408.3	410.2	412.0	413.6	415.1	416.6	418.0	419.5	422.2	424.9
107.5°	510.9	511.8	512.6	513.5	515.0	517.0	519.1	521.0	523.1	524.4	525.8
110°	581.8	582.7	583.6	584.5	585.9	587.6	589.4	591.2	593.0	593.6	594.2



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	651.4	653.0	654.6	656.2	657.5	658.3	659.2	660.0	660.8	660.7	660.6
115°	756.6	757.5	758.4	759.3	759.6	759.3	759.0	758.8	758.4	759.0	759.6
117.5°	852.4	853.6	854.8	856.0	856.9	857.6	858.3	858.9	859.5	859.4	859.3
120°	916.9	918.2	919.4	920.5	921.0	920.7	920.4	920.1	919.8	920.4	921.0
122.5°	976.7	977.4	978.1	978.9	979.5	979.9	980.3	980.7	981.1	981.5	981.9
125°	1063.5	1064.7	1066.0	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0	1066.8
127.5°	1144.4	1144.7	1145.0	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5	1151.3
130°	1197.1	1197.4	1197.7	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.8
132.5°	1245.7	1246.3	1246.9	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0	1253.4
135°	1317.5	1317.2	1317.0	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5	1323.0
137.5°	1382.2	1382.3	1382.5	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2	1389.9
140°	1424.7	1425.3	1425.8	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4	1431.3
142.5°	1462.8	1463.9	1465.0	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8	1469.5
145°	1520.5	1521.3	1522.2	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8	1524.2
147.5°	1567.2	1568.9	1570.6	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0	1572.2
150°	1600.1	1601.2	1602.5	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9	1602.9
152.5°	1627.8	1628.8	1629.7	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2	1629.7
155°	1666.4	1666.7	1667.1	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6	1665.8
157.5°	1699.1	1698.9	1698.7	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4	1696.9
160°	1717.7	1716.8	1715.9	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0	1716.8
162.5°	1734.6	1733.5	1732.4	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1	1733.0
165°	1756.0	1754.6	1753.1	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2	1755.6
167.5°	1773.3	1771.7	1770.1	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6	1772.3
170°	1782.7	1780.8	1779.1	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1	1782.5
172.5°	1789.1	1787.3	1785.6	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5	1789.0
175°	1796.1	1794.3	1792.5	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9	1796.5
177.5°	1799.5	1797.8	1796.1	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7	1799.6
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	537.0	537.3	538.9	540.0	540.4	542.1	542.2
5°	584.2	587.7	594.7	595.3	596.4	601.9	597.6
7.5°	639.4	648.5	654.6	660.0	661.9	664.3	663.9
10°	674.9	688.4	695.2	706.0	706.3	709.1	707.4
12.5°	710.5	726.2	738.5	740.6	749.6	751.0	753.3
15°	761.0	777.7	794.8	800.9	813.3	816.3	820.9
17.5°	808.4	825.5	837.5	853.3	858.4	865.2	860.6
20°	834.5	853.0	868.3	880.7	885.9	889.7	889.3
22.5°	850.2	868.9	881.2	890.6	895.5	897.2	897.1
25°	860.0	870.8	874.6	878.2	872.6	870.8	871.6
27.5°	832.6	829.8	819.9	806.9	793.4	782.7	776.9
30°	795.0	778.6	763.6	737.4	723.9	715.9	708.6
32.5°	741.6	715.5	686.7	662.7	647.4	635.5	633.7
35°	650.2	611.0	575.7	546.4	531.2	518.4	515.3
37.5°	552.8	512.0	480.3	454.4	438.1	429.0	420.5
40°	488.1	453.1	421.9	399.9	387.4	380.9	375.7
42.5°	438.4	406.4	375.2	358.6	347.3	343.3	340.2
45°	369.5	339.7	318.3	305.6	299.1	292.3	289.1
47.5°	314.4	290.3	276.1	265.3	258.2	254.2	252.3
50°	283.2	263.4	250.7	242.5	236.1	233.0	231.3
52.5°	255.6	239.2	228.6	222.0	217.8	215.4	214.7
55°	220.1	207.7	200.9	195.2	192.1	189.9	189.1
57.5°	191.4	181.7	176.3	171.6	170.3	168.6	168.0
60°	172.5	165.1	160.4	157.2	156.1	154.1	154.4
62.5°	155.7	149.6	145.7	143.9	142.5	140.7	141.3
65°	131.7	127.2	125.1	123.5	121.8	120.7	121.5
67.5°	110.5	107.5	104.6	103.6	102.8	102.6	101.7
70°	96.7	94.2	91.6	91.0	91.0	90.2	89.9
72.5°	83.3	81.5	79.8	79.3	78.6	79.0	78.1
75°	64.4	62.9	62.2	61.6	61.4	61.4	60.8
77.5°	47.5	46.5	45.5	45.5	44.7	44.4	44.3
80°	36.1	35.7	34.9	34.9	34.4	34.6	34.2
82.5°	27.1	26.6	26.4	26.0	25.4	25.5	25.1
85°	14.5	13.9	13.7	13.1	12.7	13.1	12.7
87.5°	12.0	12.2	12.3	12.1	12.0	12.1	11.8
90°	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	33.9	35.7	36.6	36.7	36.9	37.0	37.1
95°	35.0	36.7	37.8	38.1	38.4	38.7	39.0
97.5°	36.0	36.2	36.5	36.7	37.1	37.4	37.6
100°	44.0	38.9	36.5	36.7	37.1	37.4	37.6
102.5°	120.6	65.9	38.5	38.5	38.6	38.7	38.7
105°	427.7	430.3	426.2	415.5	404.7	394.0	383.3
107.5°	527.1	528.3	529.6	530.7	531.8	533.0	534.1
110°	594.9	595.4	596.2	597.1	598.0	598.9	599.8



TEST NUMBER: P332739-940

CATALOG NUMBER: S124DIW-S350D1560U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	660.4	660.3	660.8	662.0	663.1	664.2	665.4
115°	760.2	760.8	761.2	761.2	761.2	761.2	761.2
117.5°	859.2	859.1	859.0	858.8	858.7	858.6	858.4
120°	921.6	922.2	922.2	921.6	921.0	920.4	919.8
122.5°	982.2	982.6	982.4	981.9	981.2	980.6	980.1
125°	1067.7	1068.6	1069.3	1069.5	1069.8	1070.1	1070.4
127.5°	1151.1	1150.9	1150.7	1150.5	1150.2	1150.0	1149.8
130°	1203.1	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5
132.5°	1253.7	1253.9	1254.0	1253.7	1253.5	1253.3	1253.0
135°	1323.7	1324.3	1324.9	1325.4	1326.1	1326.7	1327.2
137.5°	1390.5	1391.2	1391.4	1391.2	1391.1	1390.9	1390.7
140°	1432.2	1433.1	1433.6	1434.0	1434.2	1434.5	1434.9
142.5°	1470.2	1470.8	1471.1	1471.2	1471.3	1471.3	1471.4
145°	1524.5	1524.7	1525.3	1525.8	1526.4	1527.1	1527.6
147.5°	1572.4	1572.7	1573.0	1573.2	1573.5	1573.9	1574.1
150°	1602.9	1602.9	1603.1	1603.4	1603.7	1604.0	1604.3
152.5°	1630.1	1630.7	1630.8	1630.6	1630.4	1630.2	1630.0
155°	1667.1	1668.2	1668.4	1667.5	1666.6	1665.7	1664.8
157.5°	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8
160°	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2
162.5°	1734.7	1736.5	1736.3	1734.4	1732.3	1730.3	1728.2
165°	1758.0	1760.4	1760.2	1757.6	1754.9	1752.2	1749.5
167.5°	1774.9	1777.5	1777.4	1774.3	1771.4	1768.4	1765.4
170°	1784.9	1787.3	1787.0	1784.0	1781.0	1778.1	1775.0
172.5°	1791.4	1793.8	1793.3	1790.1	1786.9	1783.7	1780.4
175°	1799.3	1802.0	1801.5	1797.9	1794.3	1790.7	1787.2
177.5°	1801.5	1803.4	1803.0	1800.1	1797.2	1794.3	1791.4
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9

(END OF REPORT)