

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333031

Luminaire Tested: **S124RDIW-S350D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333031
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7727.5 lumens
Efficiency: N/A
Efficacy: 144.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17				
2	83	76	70	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14				
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	18	17	12				
4	69	59	52	46	61	53	46	42	40	36	32	28	26	24	18	16	15	11				
5	63	53	45	39	56	47	40	36	36	31	28	25	23	20	16	14	13	9				
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8				
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	12	10	7				
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7				
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	0.7
10°-20°	171.7	2.2
20°-30°	268.5	3.5
30°-40°	298.5	3.9
40°-50°	264.9	3.4
50°-60°	206.4	2.7
60°-70°	135.1	1.7
70°-80°	66.4	0.9
80°-90°	22.2	0.3
90°-100°	69.0	0.9
100°-110°	439.7	5.7
110°-120°	841.1	10.9
120°-130°	1067.8	13.8
130°-140°	1142.4	14.8
140°-150°	1068.3	13.8
150°-160°	861.5	11.1
160°-170°	555.6	7.2
170°-180°	191.5	2.5
0°-30°	497.1	6.4
0°-40°	795.6	10.3
0°-60°	1266.9	16.4
0°-90°	1490.6	19.3
90°-120°	1349.8	17.5
90°-150°	4628.2	59.9
90°-180°	6237.0	80.7
0°-180°	7727.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	15
90°	45	4	45	4	45	20
95°	44	83	44	83	44	35
105°	430	454	430	454	430	375
115°	854	848	854	848	854	845
125°	1200	1191	1200	1191	1200	1069
135°	1488	1478	1488	1478	1488	1146
145°	1713	1704	1713	1704	1713	1071
155°	1867	1868	1867	1868	1867	861
165°	1962	1971	1962	1971	1962	554
175°	2004	2016	2004	2016	2004	191
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	13.2	12.9	12.9	12.8	12.9	12.4	12.2	12.2	11.4	11.2	10.6
90°	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2	35.2	33.2	30.5
92.5°	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0	34.0	32.0	29.3
95°	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2	35.2	33.2	32.8
97.5°	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2	40.0	39.8	77.2
100°	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0	60.7	66.4	112.6
102.5°	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8	258.2	319.7	325.7
105°	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5	473.5	470.5	468.8
107.5°	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6	588.1	586.6	584.3
110°	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4	665.7	665.0	663.0



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8	740.9	741.1	740.1
115°	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9	851.2	850.5	850.9
117.5°	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7	963.8	963.9	963.2
120°	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5	1031.8
122.5°	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1	1100.7	1100.3	1099.8
125°	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4	1195.4	1194.4	1195.0
127.5°	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1	1291.3	1291.5	1289.9
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9	1348.5	1348.2	1347.2
132.5°	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6	1405.2	1404.9	1403.6
135°	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7	1483.1	1482.4	1481.1
137.5°	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7	1557.9	1557.2	1555.7
140°	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1	1604.1	1603.0	1602.4
142.5°	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0	1647.2	1646.5	1646.1
145°	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3	1708.9	1708.6	1708.6
147.5°	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1	1762.9	1762.6	1762.9
150°	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6	1797.6	1797.6	1797.9
152.5°	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6	1827.1	1826.5	1827.1
155°	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1	1866.8	1865.4	1866.5
157.5°	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5	1900.7
160°	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2	1921.6
162.5°	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4	1941.3	1939.3	1939.7
165°	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8	1966.1	1963.5	1963.5
167.5°	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5	1984.5	1981.6	1981.8
170°	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0	1996.3	1993.6	1993.3
172.5°	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2	2003.5	2000.9	2000.5
175°	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7	2011.7	2008.7	2008.4
177.5°	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1	2016.0	2013.8	2013.3
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	10.1	9.4	9.2	8.6	8.0	8.1	7.9	7.3	7.5	7.7	7.8
90°	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5	8.2	11.9	15.6
92.5°	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0	19.2	19.4	19.6
95°	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9	71.5	60.2	48.8
97.5°	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1	183.2	190.3	197.5
100°	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3	253.4	259.4	265.4
102.5°	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9	331.4	335.8	340.2
105°	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9	455.9	457.9	460.0
107.5°	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8	572.9	573.9	574.9
110°	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5	652.5	653.5	654.5



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7	730.5	732.3	734.1
115°	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5	848.5	849.5	850.5
117.5°	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6	955.9	957.3	958.6
120°	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0	1028.3	1029.7	1031.0
122.5°	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5	1095.3	1096.1	1096.9
125°	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4	1192.7	1194.0	1195.4
127.5°	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0	1283.4	1283.7	1284.0
130°	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2	1342.5	1342.8	1343.2
132.5°	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4	1397.0	1397.7	1398.3
135°	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9	1477.5	1477.2	1476.9
137.5°	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0	1550.1	1550.2	1550.4
140°	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0	1597.7	1598.4	1599.0
142.5°	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2	1640.4	1641.7	1642.9
145°	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1	1705.1	1706.1	1707.1
147.5°	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7	1757.5	1759.4	1761.3
150°	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1	1794.4	1795.7	1797.1
152.5°	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4	1825.5	1826.6	1827.6
155°	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5	1868.8	1869.1	1869.5
157.5°	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6	1905.4	1905.2	1905.0
160°	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3	1926.3	1925.3	1924.3
162.5°	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6	1945.3	1944.0	1942.8
165°	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0	1969.3	1967.7	1966.0
167.5°	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3	1988.6	1986.8	1985.1
170°	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2	1999.2	1997.1	1995.1
172.5°	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4	2006.4	2004.4	2002.4
175°	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2	2014.2	2012.2	2010.2
177.5°	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9	2018.0	2016.1	2014.2
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	8.6	9.0	9.6	9.7	10.5	11.0	11.2	11.6	12.2	12.2	12.5
90°	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2	39.2	41.2	42.6
92.5°	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0	38.0	40.0	41.1
95°	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2	39.2	41.2	42.4
97.5°	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2	40.4	40.6	40.9
100°	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0	49.3	43.6	40.9
102.5°	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8	135.3	73.9	43.2
105°	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5	479.6	482.6	478.0
107.5°	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6	591.1	592.5	593.9
110°	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4	667.1	667.7	668.6



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8	740.6	740.5	741.1
115°	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9	852.5	853.2	853.6
117.5°	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7	963.5	963.4	963.3
120°	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2
122.5°	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1	1101.5	1101.9	1101.7
125°	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4	1197.4	1198.4	1199.1
127.5°	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1	1290.9	1290.7	1290.4
130°	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9	1349.2	1349.5	1349.7
132.5°	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6	1405.9	1406.2	1406.3
135°	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7	1484.4	1485.1	1485.8
137.5°	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7	1559.4	1560.2	1560.4
140°	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1	1606.1	1607.1	1607.7
142.5°	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0	1648.7	1649.4	1649.8
145°	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3	1709.6	1709.9	1710.5
147.5°	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1	1763.4	1763.7	1764.0
150°	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6	1797.6	1797.6	1797.8
152.5°	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6	1828.1	1828.7	1828.8
155°	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1	1869.5	1870.8	1871.0
157.5°	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5
160°	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3
162.5°	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4	1945.4	1947.4	1947.2
165°	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8	1971.5	1974.2	1974.0
167.5°	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5	1990.4	1993.4	1993.2
170°	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0	2001.7	2004.4	2004.0
172.5°	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2	2008.9	2011.6	2011.1
175°	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7	2017.8	2020.8	2020.3
177.5°	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1	2020.3	2022.4	2021.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	13.0	12.9	12.9	13.2	12.9	12.9	13.0	12.5	12.2	12.2	11.6
90°	43.2	43.9	44.6	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2
92.5°	41.2	41.4	41.5	41.6	41.5	41.4	41.2	41.1	40.0	38.0	36.0
95°	42.7	43.1	43.4	43.7	43.4	43.1	42.7	42.4	41.2	39.2	37.2
97.5°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	40.6	40.4	40.2
100°	41.2	41.6	41.9	42.2	41.9	41.6	41.2	40.9	43.6	49.3	55.0
102.5°	43.2	43.3	43.4	43.4	43.4	43.3	43.2	43.2	73.9	135.3	196.8
105°	466.0	453.9	441.9	429.8	441.9	453.9	466.0	478.0	482.6	479.6	476.5
107.5°	595.2	596.4	597.7	599.0	597.7	596.4	595.2	593.9	592.5	591.1	589.6
110°	669.6	670.6	671.6	672.6	671.6	670.6	669.6	668.6	667.7	667.1	666.4



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	742.4	743.6	744.9	746.2	744.9	743.6	742.4	741.1	740.5	740.6	740.8
115°	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.6	853.2	852.5	851.9
117.5°	963.1	963.0	962.9	962.7	962.9	963.0	963.1	963.3	963.4	963.5	963.7
120°	1033.5	1032.8	1032.2	1031.5	1032.2	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8
122.5°	1101.1	1100.4	1099.7	1099.1	1099.7	1100.4	1101.1	1101.7	1101.9	1101.5	1101.1
125°	1199.4	1199.7	1200.1	1200.4	1200.1	1199.7	1199.4	1199.1	1198.4	1197.4	1196.4
127.5°	1290.2	1289.9	1289.6	1289.4	1289.6	1289.9	1290.2	1290.4	1290.7	1290.9	1291.1
130°	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.7	1349.5	1349.2	1348.9
132.5°	1406.0	1405.7	1405.5	1405.2	1405.5	1405.7	1406.0	1406.3	1406.2	1405.9	1405.6
135°	1486.4	1487.1	1487.8	1488.4	1487.8	1487.1	1486.4	1485.8	1485.1	1484.4	1483.7
137.5°	1560.2	1560.0	1559.8	1559.6	1559.8	1560.0	1560.2	1560.4	1560.2	1559.4	1558.7
140°	1608.1	1608.4	1608.7	1609.1	1608.7	1608.4	1608.1	1607.7	1607.1	1606.1	1605.1
142.5°	1649.9	1650.0	1650.0	1650.1	1650.0	1650.0	1649.9	1649.8	1649.4	1648.7	1648.0
145°	1711.1	1711.8	1712.5	1713.1	1712.5	1711.8	1711.1	1710.5	1709.9	1709.6	1709.3
147.5°	1764.3	1764.6	1765.0	1765.3	1765.0	1764.6	1764.3	1764.0	1763.7	1763.4	1763.1
150°	1798.1	1798.4	1798.8	1799.1	1798.8	1798.4	1798.1	1797.8	1797.6	1797.6	1797.6
152.5°	1828.6	1828.4	1828.2	1828.0	1828.2	1828.4	1828.6	1828.8	1828.7	1828.1	1827.6
155°	1870.0	1869.0	1868.0	1867.0	1868.0	1869.0	1870.0	1871.0	1870.8	1869.5	1868.1
157.5°	1904.8	1903.0	1901.3	1899.5	1901.3	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0
160°	1927.3	1925.3	1923.3	1921.2	1923.3	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3
162.5°	1945.0	1942.7	1940.4	1938.1	1940.4	1942.7	1945.0	1947.2	1947.4	1945.4	1943.4
165°	1971.0	1968.0	1965.0	1962.0	1965.0	1968.0	1971.0	1974.0	1974.2	1971.5	1968.8
167.5°	1989.8	1986.5	1983.1	1979.8	1983.1	1986.5	1989.8	1993.2	1993.4	1990.4	1987.5
170°	2000.7	1997.3	1994.0	1990.6	1994.0	1997.3	2000.7	2004.0	2004.4	2001.7	1999.0
172.5°	2007.5	2003.9	2000.3	1996.6	2000.3	2003.9	2007.5	2011.1	2011.6	2008.9	2006.2
175°	2016.2	2012.2	2008.2	2004.2	2008.2	2012.2	2016.2	2020.3	2020.8	2017.8	2014.7
177.5°	2018.7	2015.4	2012.2	2009.0	2012.2	2015.4	2018.7	2021.9	2022.4	2020.3	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	11.2	11.0	10.5	9.7	9.6	9.0	8.6	7.8	7.7	7.5	7.3
90°	35.2	33.2	30.5	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5
92.5°	34.0	32.0	29.3	26.6	23.9	21.2	19.8	19.6	19.4	19.2	19.0
95°	35.2	33.2	32.8	32.5	32.2	31.8	37.4	48.8	60.2	71.5	82.9
97.5°	40.0	39.8	77.2	114.6	152.0	189.4	204.6	197.5	190.3	183.2	176.1
100°	60.7	66.4	112.6	158.8	205.1	251.3	271.4	265.4	259.4	253.4	247.3
102.5°	258.2	319.7	325.7	331.8	337.8	343.8	344.6	340.2	335.8	331.4	326.9
105°	473.5	470.5	468.8	467.2	465.5	463.8	462.0	460.0	457.9	455.9	453.9
107.5°	588.1	586.6	584.3	582.1	579.8	577.5	575.9	574.9	573.9	572.9	571.8
110°	665.7	665.0	663.0	661.0	659.0	657.0	655.5	654.5	653.5	652.5	651.5



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	740.9	741.1	740.1	739.2	738.2	737.3	735.9	734.1	732.3	730.5	728.7
115°	851.2	850.5	850.9	851.2	851.5	851.9	851.5	850.5	849.5	848.5	847.5
117.5°	963.8	963.9	963.2	962.5	961.7	961.0	960.0	958.6	957.3	955.9	954.6
120°	1032.2	1031.5	1031.8	1032.2	1032.5	1032.8	1032.3	1031.0	1029.7	1028.3	1027.0
122.5°	1100.7	1100.3	1099.8	1099.3	1098.9	1098.4	1097.8	1096.9	1096.1	1095.3	1094.5
125°	1195.4	1194.4	1195.0	1195.7	1196.4	1197.0	1196.7	1195.4	1194.0	1192.7	1191.4
127.5°	1291.3	1291.5	1289.9	1288.4	1286.9	1285.3	1284.4	1284.0	1283.7	1283.4	1283.0
130°	1348.5	1348.2	1347.2	1346.2	1345.2	1344.2	1343.5	1343.2	1342.8	1342.5	1342.2
132.5°	1405.2	1404.9	1403.6	1402.3	1401.1	1399.8	1398.9	1398.3	1397.7	1397.0	1396.4
135°	1483.1	1482.4	1481.1	1479.7	1478.4	1477.0	1476.5	1476.9	1477.2	1477.5	1477.9
137.5°	1557.9	1557.2	1555.7	1554.3	1552.8	1551.3	1550.5	1550.4	1550.2	1550.1	1550.0
140°	1604.1	1603.0	1602.4	1601.7	1601.0	1600.4	1599.7	1599.0	1598.4	1597.7	1597.0
142.5°	1647.2	1646.5	1646.1	1645.7	1645.3	1644.9	1644.1	1642.9	1641.7	1640.4	1639.2
145°	1708.9	1708.6	1708.6	1708.6	1708.6	1708.6	1708.1	1707.1	1706.1	1705.1	1704.1
147.5°	1762.9	1762.6	1762.9	1763.3	1763.6	1763.9	1763.2	1761.3	1759.4	1757.5	1755.7
150°	1797.6	1797.6	1797.9	1798.3	1798.6	1798.9	1798.4	1797.1	1795.7	1794.4	1793.1
152.5°	1827.1	1826.5	1827.1	1827.7	1828.3	1829.0	1828.7	1827.6	1826.6	1825.5	1824.4
155°	1866.8	1865.4	1866.5	1867.5	1868.5	1869.5	1869.8	1869.5	1869.1	1868.8	1868.5
157.5°	1901.3	1899.5	1900.7	1901.8	1902.9	1904.1	1904.8	1905.0	1905.2	1905.4	1905.6
160°	1923.3	1921.2	1921.6	1921.9	1922.2	1922.6	1923.3	1924.3	1925.3	1926.3	1927.3
162.5°	1941.3	1939.3	1939.7	1940.0	1940.3	1940.7	1941.5	1942.8	1944.0	1945.3	1946.6
165°	1966.1	1963.5	1963.5	1963.5	1963.5	1963.5	1964.3	1966.0	1967.7	1969.3	1971.0
167.5°	1984.5	1981.6	1981.8	1982.0	1982.2	1982.4	1983.3	1985.1	1986.8	1988.6	1990.3
170°	1996.3	1993.6	1993.3	1993.0	1992.6	1992.3	1993.1	1995.1	1997.1	1999.2	2001.2
172.5°	2003.5	2000.9	2000.5	2000.2	1999.9	1999.5	2000.4	2002.4	2004.4	2006.4	2008.4
175°	2011.7	2008.7	2008.4	2008.0	2007.7	2007.4	2008.2	2010.2	2012.2	2014.2	2016.2
177.5°	2016.0	2013.8	2013.3	2012.8	2012.2	2011.7	2012.4	2014.2	2016.1	2018.0	2019.9
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	7.9	8.1	8.0	8.6	9.2	9.4	10.1	10.6	11.2	11.4	12.2
90°	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2
92.5°	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0	36.0
95°	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2	37.2
97.5°	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0	40.2
100°	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7	55.0
102.5°	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2	196.8
105°	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5	476.5
107.5°	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1	589.6
110°	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7	666.4



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9	740.8
115°	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2	851.9
117.5°	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8	963.7
120°	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2	1032.8
122.5°	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7	1101.1
125°	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4	1196.4
127.5°	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3	1291.1
130°	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5	1348.9
132.5°	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2	1405.6
135°	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1	1483.7
137.5°	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9	1558.7
140°	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1	1605.1
142.5°	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2	1648.0
145°	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9	1709.3
147.5°	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.3	1762.9	1762.6	1762.9	1763.1
150°	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6	1797.6
152.5°	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1	1827.6
155°	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8	1868.1
157.5°	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3	1903.0
160°	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3	1925.3
162.5°	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3	1943.4
165°	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1	1968.8
167.5°	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5	1987.5
170°	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3	1999.0
172.5°	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5	2006.2
175°	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7	2014.7
177.5°	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0	2018.1
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	12.2	12.4	12.9	12.8	12.9	12.9	13.2
90°	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P333031

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)