

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332767-940

Luminaire Tested: **S124DIW-S575D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332767-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1340U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7010.1 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.2
10°-20°	229.8	3.3
20°-30°	338.2	4.8
30°-40°	393.2	5.6
40°-50°	393.2	5.6
50°-60°	343.9	4.9
60°-70°	255.4	3.6
70°-80°	145.1	2.1
80°-90°	46.3	0.7
90°-100°	52.9	0.8
100°-110°	337.2	4.8
110°-120°	645.1	9.2
120°-130°	818.9	11.7
130°-140°	876.2	12.5
140°-150°	819.3	11.7
150°-160°	660.7	9.4
160°-170°	426.2	6.1
170°-180°	146.9	2.1
0°-30°	649.5	9.3
0°-40°	1042.7	14.9
0°-60°	1779.8	25.4
0°-90°	2226.7	31.8
90°-120°	1035.2	14.8
90°-150°	3549.6	50.6
90°-180°	4783.0	68.2
0°-180°	7010.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	4	16	25	32	35	5
95°	64	26	25	32	34	82
105°	348	355	361	368	330	364
115°	650	653	652	654	655	639
125°	914	918	916	919	921	815
135°	1134	1133	1137	1139	1142	873
145°	1307	1310	1310	1312	1314	816
155°	1433	1434	1431	1435	1432	660
165°	1512	1506	1506	1514	1505	427
175°	1546	1540	1541	1550	1537	147
180°	1546	1546	1546	1546	1546	



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	15.2	15.6	16.1	16.5	16.9	17.3	17.6	17.8	18.1	18.4	18.7
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	14.5	14.7	14.9	15.1	15.2	16.3	18.4	20.4	22.5	24.5	26.0
95°	63.6	54.8	46.1	37.4	28.6	24.4	24.7	25.0	25.1	25.4	27.0
97.5°	135.1	140.5	146.0	151.4	156.9	145.3	116.5	87.9	59.2	30.5	30.7
100°	189.7	194.3	198.9	203.6	208.2	192.8	157.3	121.8	86.3	50.9	46.5
102.5°	250.7	254.1	257.5	260.9	264.3	263.7	259.0	254.5	249.9	245.2	198.0
105°	348.1	349.6	351.2	352.8	354.3	355.7	357.0	358.3	359.5	360.9	363.2
107.5°	438.5	439.3	440.1	440.9	441.7	442.9	444.7	446.4	448.2	450.0	451.0
110°	499.6	500.4	501.2	501.9	502.7	503.9	505.4	506.9	508.5	510.1	510.6



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.8	560.3	561.7	563.0	564.5	565.4	566.2	566.9	567.7	568.4	568.3
115°	650.0	650.8	651.6	652.3	653.1	653.4	653.1	652.8	652.6	652.3	652.8
117.5°	732.1	733.2	734.1	735.2	736.2	737.0	737.6	738.2	738.7	739.3	739.2
120°	787.6	788.6	789.7	790.8	791.8	792.1	791.9	791.7	791.4	791.1	791.7
122.5°	839.5	840.1	840.7	841.3	842.0	842.4	842.8	843.1	843.5	843.8	844.2
125°	913.7	914.7	915.8	916.8	917.8	918.1	917.6	917.0	916.5	916.1	916.8
127.5°	984.0	984.3	984.5	984.8	985.1	985.8	986.9	988.1	989.4	990.5	990.3
130°	1029.4	1029.7	1029.9	1030.1	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3
132.5°	1071.0	1071.5	1071.9	1072.4	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7
135°	1133.5	1133.2	1132.9	1132.7	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5
137.5°	1188.7	1188.8	1188.9	1189.1	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9
140°	1224.9	1225.4	1225.8	1226.4	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2
142.5°	1257.2	1258.1	1259.1	1260.0	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4
145°	1307.0	1307.7	1308.5	1309.3	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7
147.5°	1346.5	1347.9	1349.4	1350.9	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0
150°	1375.2	1376.3	1377.2	1378.3	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7
152.5°	1399.3	1400.1	1400.9	1401.7	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3
155°	1433.1	1433.2	1433.5	1433.8	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7
157.5°	1461.5	1461.3	1461.2	1461.0	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2
160°	1478.1	1477.4	1476.6	1475.8	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1
162.5°	1492.9	1491.9	1491.0	1490.0	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9
165°	1511.7	1510.4	1509.1	1507.8	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0
167.5°	1526.5	1525.2	1523.8	1522.5	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1
170°	1534.8	1533.3	1531.7	1530.2	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1
172.5°	1540.3	1538.8	1537.3	1535.7	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6
175°	1546.4	1544.8	1543.3	1541.8	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9
177.5°	1549.2	1547.7	1546.2	1544.8	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	19.0	19.4	19.6	19.9	20.0	20.1	20.2	20.2
90°	28.5	30.1	31.7	32.6	33.2	33.7	34.2	34.7
92.5°	27.6	29.2	30.7	31.5	31.7	31.7	31.8	31.9
95°	28.5	30.1	31.7	32.5	32.7	33.0	33.3	33.5
97.5°	30.9	31.0	31.1	31.4	31.7	31.8	32.1	32.4
100°	42.2	37.8	33.4	31.4	31.7	31.8	32.1	32.4
102.5°	151.0	103.8	56.6	33.1	33.2	33.2	33.3	33.3
105°	365.5	367.8	370.1	366.7	357.4	348.1	338.9	329.7
107.5°	452.2	453.3	454.4	455.5	456.5	457.4	458.4	459.4
110°	511.1	511.6	512.1	512.7	513.5	514.3	515.1	515.9



TEST NUMBER: P332767-940

CATALOG NUMBER: S124DIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.1	568.0	567.9	568.4	569.4	570.3	571.3	572.3
115°	653.4	653.9	654.3	654.6	654.6	654.6	654.6	654.6
117.5°	739.0	739.0	738.9	738.8	738.7	738.6	738.5	738.3
120°	792.1	792.6	793.2	793.2	792.6	792.1	791.7	791.1
122.5°	844.5	844.8	845.1	845.0	844.5	843.9	843.5	842.9
125°	917.6	918.4	919.1	919.6	919.9	920.2	920.4	920.7
127.5°	990.2	990.1	989.9	989.7	989.5	989.3	989.1	988.9
130°	1034.5	1034.7	1035.0	1035.2	1035.2	1035.2	1035.2	1035.2
132.5°	1078.0	1078.3	1078.5	1078.5	1078.3	1078.2	1077.9	1077.7
135°	1138.0	1138.4	1139.0	1139.5	1140.1	1140.5	1141.0	1141.6
137.5°	1195.4	1196.0	1196.6	1196.8	1196.6	1196.5	1196.3	1196.1
140°	1231.0	1231.8	1232.5	1233.1	1233.3	1233.6	1233.9	1234.1
142.5°	1263.9	1264.4	1265.1	1265.3	1265.4	1265.4	1265.5	1265.5
145°	1310.9	1311.2	1311.4	1311.9	1312.3	1312.9	1313.4	1313.9
147.5°	1352.3	1352.5	1352.6	1352.9	1353.2	1353.4	1353.6	1353.9
150°	1378.7	1378.7	1378.7	1378.8	1379.0	1379.3	1379.6	1379.8
152.5°	1401.7	1402.1	1402.5	1402.7	1402.5	1402.3	1402.2	1402.0
155°	1432.8	1433.8	1434.9	1434.9	1434.2	1433.4	1432.6	1431.9
157.5°	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9
160°	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6
162.5°	1490.5	1492.0	1493.5	1493.4	1491.7	1490.0	1488.2	1486.5
165°	1510.0	1512.1	1514.1	1513.9	1511.7	1509.4	1507.1	1504.8
167.5°	1524.3	1526.5	1528.8	1528.7	1526.1	1523.5	1521.0	1518.4
170°	1533.1	1535.2	1537.2	1537.0	1534.5	1531.9	1529.3	1526.7
172.5°	1538.6	1540.8	1542.8	1542.5	1539.6	1536.9	1534.1	1531.3
175°	1545.2	1547.6	1549.9	1549.4	1546.4	1543.3	1540.2	1537.1
177.5°	1547.8	1549.4	1551.1	1550.7	1548.2	1545.8	1543.3	1540.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4

(END OF REPORT)