

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333034

Luminaire Tested: **S124RDIW-S350D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333034
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6843.2 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	0.8
10°-20°	161.9	2.4
20°-30°	233.8	3.4
30°-40°	265.1	3.9
40°-50°	255.9	3.7
50°-60°	212.8	3.1
60°-70°	147.0	2.1
70°-80°	74.5	1.1
80°-90°	24.9	0.4
90°-100°	128.6	1.9
100°-110°	380.9	5.6
110°-120°	646.6	9.4
120°-130°	852.5	12.5
130°-140°	957.5	14.0
140°-150°	940.9	13.7
150°-160°	791.3	11.6
160°-170°	526.5	7.7
170°-180°	184.4	2.7
0°-30°	453.8	6.6
0°-40°	718.9	10.5
0°-60°	1187.7	17.4
0°-90°	1434.1	21.0
90°-120°	1156.1	16.9
90°-150°	3906.9	57.1
90°-180°	5409.0	79.0
0°-180°	6843.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	4	21	33	42	45	7
95°	90	104	115	119	119	101
105°	351	353	359	363	368	373
115°	657	657	654	653	651	648
125°	958	957	956	953	950	853
135°	1235	1244	1244	1241	1236	955
145°	1500	1506	1508	1506	1502	939
155°	1719	1719	1717	1723	1717	791
165°	1871	1867	1864	1872	1867	527
175°	1947	1939	1938	1947	1938	185
180°	1950	1950	1950	1950	1950	



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.6	9.7	9.7	9.8	9.9	10.1	10.6	11.0	11.5	11.9	12.3
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	32.3	36.5	40.7	44.9	49.2	52.2	54.1	56.0	57.8	59.7	60.9
95°	90.5	93.5	96.5	99.5	102.5	105.2	107.6	109.9	112.3	114.6	115.6
97.5°	158.0	160.4	162.8	165.3	167.7	170.3	173.0	175.7	178.5	181.2	182.4
100°	211.1	212.4	213.8	215.1	216.5	218.6	221.7	224.7	227.7	230.7	231.4
102.5°	266.6	267.1	267.7	268.2	268.7	270.4	273.1	275.9	278.6	281.4	282.3
105°	351.3	351.7	352.0	352.3	352.7	353.5	354.8	356.2	357.5	358.9	359.9
107.5°	440.3	440.7	441.1	441.5	441.9	442.2	442.4	442.6	442.8	443.0	443.9
110°	500.6	501.3	501.9	502.6	503.3	503.5	503.1	502.8	502.4	502.1	501.4



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	563.3	563.5	563.6	563.7	563.9	563.6	563.0	562.4	561.8	561.2	561.1
115°	657.4	657.4	657.4	657.4	657.4	657.1	656.4	655.7	655.1	654.4	654.1
117.5°	746.1	746.3	746.6	746.9	747.2	747.1	746.6	746.1	745.6	745.2	744.0
120°	805.2	806.5	807.9	809.2	810.5	810.7	809.7	808.7	807.7	806.7	805.0
122.5°	866.7	867.2	867.8	868.3	868.8	868.9	868.4	867.9	867.5	867.0	865.9
125°	957.5	957.5	957.5	957.5	957.5	957.3	957.0	956.6	956.3	956.0	955.3
127.5°	1039.8	1040.8	1041.8	1042.8	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2
130°	1097.7	1098.7	1099.7	1100.7	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6
132.5°	1156.8	1157.6	1158.3	1159.0	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3
135°	1234.9	1236.9	1238.9	1241.0	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3
137.5°	1320.0	1320.9	1321.8	1322.8	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7
140°	1376.7	1377.3	1378.0	1378.7	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3
142.5°	1428.5	1429.2	1429.9	1430.5	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3
145°	1500.3	1501.6	1503.0	1504.3	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5
147.5°	1571.5	1573.1	1574.7	1576.3	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2
150°	1614.9	1616.2	1617.6	1618.9	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1655.9	1656.7	1657.5	1658.3	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5
155°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8
157.5°	1772.0	1771.4	1770.8	1770.2	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0
160°	1803.4	1803.0	1802.7	1802.4	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4
162.5°	1832.3	1831.5	1830.6	1829.7	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7
165°	1871.2	1870.2	1869.2	1868.2	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7
167.5°	1901.1	1899.7	1898.3	1896.9	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1
170°	1918.0	1916.3	1914.6	1912.9	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9
172.5°	1930.0	1928.6	1927.2	1925.8	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3
175°	1946.6	1944.9	1943.3	1941.6	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9
177.5°	1952.0	1950.7	1949.4	1948.0	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	12.6	12.9	13.2	13.5	13.7	13.9	14.1	14.3
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	62.1	63.3	64.5	65.3	65.7	66.1	66.5	66.9
95°	116.6	117.6	118.6	119.1	119.1	119.1	119.1	119.1
97.5°	183.7	184.9	186.1	186.7	186.7	186.7	186.7	186.7
100°	232.0	232.7	233.4	233.7	233.7	233.7	233.7	233.7
102.5°	283.2	284.2	285.1	285.7	286.0	286.3	286.5	286.8
105°	360.9	361.9	362.9	363.9	364.9	365.9	366.9	367.9
107.5°	444.9	445.8	446.8	447.2	447.1	447.1	447.0	446.9
110°	500.8	500.1	499.4	499.6	500.6	501.6	502.6	503.6



TEST NUMBER: P333034

CATALOG NUMBER: S124RDIW-S350D1560U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	560.9	560.8	560.7	560.7	560.9	561.1	561.3	561.5
115°	653.7	653.4	653.1	652.7	652.4	652.1	651.7	651.4
117.5°	742.9	741.8	740.6	739.7	739.0	738.4	737.7	737.0
120°	803.3	801.7	800.0	799.5	800.2	800.8	801.5	802.2
122.5°	864.7	863.6	862.5	861.3	860.1	858.9	857.7	856.5
125°	954.6	954.0	953.3	952.6	951.9	951.3	950.6	949.9
127.5°	1040.6	1039.9	1039.2	1038.6	1038.1	1037.6	1037.0	1036.5
130°	1100.9	1100.2	1099.5	1098.5	1097.2	1095.9	1094.5	1093.2
132.5°	1157.6	1156.9	1156.2	1155.6	1155.1	1154.6	1154.0	1153.5
135°	1242.6	1242.0	1241.3	1240.4	1239.4	1238.4	1237.4	1236.4
137.5°	1324.9	1324.0	1323.1	1322.8	1323.0	1323.2	1323.4	1323.6
140°	1379.0	1378.7	1378.3	1378.0	1377.7	1377.3	1377.0	1376.7
142.5°	1430.2	1430.1	1430.1	1430.0	1429.9	1429.9	1429.8	1429.7
145°	1507.2	1506.8	1506.5	1505.8	1504.8	1503.8	1502.8	1501.8
147.5°	1577.0	1576.7	1576.4	1576.1	1575.8	1575.5	1575.1	1574.8
150°	1620.9	1620.9	1620.9	1620.8	1620.4	1620.1	1619.8	1619.4
152.5°	1662.3	1663.1	1663.9	1663.9	1663.0	1662.2	1661.3	1660.4
155°	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4
157.5°	1771.0	1772.0	1773.0	1772.9	1771.8	1770.7	1769.5	1768.4
160°	1802.4	1803.4	1804.4	1804.0	1802.4	1800.7	1799.0	1797.3
162.5°	1830.5	1832.3	1834.1	1834.2	1832.5	1830.9	1829.2	1827.5
165°	1867.7	1869.7	1871.7	1872.1	1870.7	1869.4	1868.0	1866.7
167.5°	1899.1	1901.1	1903.1	1903.1	1901.0	1898.9	1896.8	1894.7
170°	1916.0	1918.0	1920.0	1919.8	1917.5	1915.1	1912.8	1910.4
172.5°	1928.6	1930.8	1933.1	1933.1	1930.7	1928.4	1926.0	1923.7
175°	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6
177.5°	1949.8	1951.6	1953.5	1953.4	1951.2	1949.1	1947.0	1944.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6

(END OF REPORT)