

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333018

Luminaire Tested: **S124RDIW-S350D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333018  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D470U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3055.5 lumens  
Efficiency: N/A  
Efficacy: 132.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.1	1.9
10°-20°	161.9	5.3
20°-30°	233.8	7.7
30°-40°	265.1	8.7
40°-50°	255.9	8.4
50°-60°	212.8	7.0
60°-70°	147.0	4.8
70°-80°	74.5	2.4
80°-90°	20.9	0.7
90°-100°	38.6	1.3
100°-110°	114.5	3.7
110°-120°	194.3	6.4
120°-130°	256.2	8.4
130°-140°	287.7	9.4
140°-150°	282.7	9.3
150°-160°	237.8	7.8
160°-170°	158.2	5.2
170°-180°	55.4	1.8
0°-30°	453.8	14.9
0°-40°	718.9	23.5
0°-60°	1187.7	38.9
0°-90°	1430.0	46.8
90°-120°	347.4	11.4
90°-150°	1174.1	38.4
90°-180°	1626.0	53.2
0°-180°	3055.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	1	6	10	13	14	3
95°	27	31	34	36	36	30
105°	106	106	108	109	111	112
115°	198	198	197	196	196	195
125°	288	288	287	286	286	256
135°	371	374	374	373	372	287
145°	451	453	453	453	451	282
155°	517	517	516	518	516	238
165°	562	561	560	563	561	158
175°	585	583	582	585	582	56
180°	586	586	586	586	586	



TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.0	8.5	8.1	7.6	7.2	7.0	7.1	7.1	7.2	7.3	7.3
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	9.7	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3
95°	27.2	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7
97.5°	47.5	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8
100°	63.4	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5
102.5°	80.1	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8
105°	105.6	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1
107.5°	132.3	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4
110°	150.4	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7



TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.3	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6
115°	197.6	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6
117.5°	224.2	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6
120°	242.0	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9
122.5°	260.5	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2
125°	287.7	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1
127.5°	312.5	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9
130°	329.9	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0
132.5°	347.6	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1
135°	371.1	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6
137.5°	396.7	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4
140°	413.7	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5
142.5°	429.3	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8
145°	450.9	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	472.3	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0
150°	485.3	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.6	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3
155°	516.6	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5
157.5°	532.5	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9
160°	542.0	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4
162.5°	550.7	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6
165°	562.3	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7
167.5°	571.3	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1
170°	576.4	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2
172.5°	580.0	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9
175°	585.0	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0
177.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	7.4	7.4	7.4	7.5	7.6	7.8	7.9	8.0
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	18.7	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.0	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.2	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.7	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.1	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.5	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	133.7	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.5	150.3	150.1	150.1	150.4	150.7	151.0	151.3





TEST NUMBER: P333018

CATALOG NUMBER: S124RDIW-S350D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.5	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	223.3	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	241.4	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.9	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.9	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.7	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.8	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.9	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.4	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	398.1	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.4	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.9	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.9	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.6	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.2	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	541.7	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.1	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.3	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	570.7	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	575.8	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	579.6	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.0	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)