

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333020

Luminaire Tested: **S124RDIW-S350D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333020
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4150.2 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36																				
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31																				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26																				
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23																				
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	28	25	24	20																				
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21	17																				
6	61	50	42	36	55	46	39	34	37	32	29	30	26	23	23	20	18	15																				
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14																				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12																				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11																				
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	16	14	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	1.4
10°-20°	171.7	4.1
20°-30°	268.5	6.5
30°-40°	298.5	7.2
40°-50°	264.9	6.4
50°-60°	206.4	5.0
60°-70°	135.1	3.3
70°-80°	66.4	1.6
80°-90°	19.3	0.5
90°-100°	63.3	1.5
100°-110°	187.5	4.5
110°-120°	318.2	7.7
120°-130°	419.6	10.1
130°-140°	471.3	11.4
140°-150°	463.1	11.2
150°-160°	389.5	9.4
160°-170°	259.1	6.2
170°-180°	90.7	2.2
0°-30°	497.1	12.0
0°-40°	795.6	19.2
0°-60°	1266.9	30.5
0°-90°	1487.7	35.8
90°-120°	569.0	13.7
90°-150°	1923.1	46.3
90°-180°	2662.0	64.1
0°-180°	4150.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	22	2	22	2	22	12
95°	59	44	59	44	59	61
105°	181	173	181	173	181	191
115°	321	324	321	324	321	317
125°	468	471	468	471	468	417
135°	609	608	609	608	609	470
145°	739	738	739	738	739	463
155°	845	846	845	846	845	389
165°	919	921	919	921	919	259
175°	954	958	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	8.6	8.4	8.5	8.4	8.5	8.2	8.2	8.4	7.8	7.8	7.5
90°	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3	17.3	16.3	15.0
92.5°	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6	30.0	29.4	28.5
95°	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4	56.9	56.4	55.3
97.5°	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4	89.8	89.2	87.9
100°	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2	113.9	113.6	112.1
102.5°	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4	139.0	138.5	137.1
105°	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6	177.1	176.6	176.0
107.5°	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0	218.5	218.1	218.0
110°	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5	246.8	247.1	247.3



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1	276.2	276.2	276.5
115°	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8	321.9	322.1	322.4
117.5°	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7	366.2	366.8	367.0
120°	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4	396.2	397.1	397.6
122.5°	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6	426.2	426.8	427.0
125°	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9	470.2	470.5	470.7
127.5°	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2	512.5	512.9	513.1
130°	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9	542.2	542.5	542.5
132.5°	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8	570.1	570.4	570.6
135°	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6	612.0	612.3	612.3
137.5°	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1	652.5	653.0	652.7
140°	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8	678.9	679.1	679.1
142.5°	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0	704.0	704.0	704.2
145°	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2	776.3	776.5	776.6
150°	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2	817.8	817.4	817.3
155°	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4	845.5
157.5°	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7	871.2	870.7	870.8
160°	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2	886.7	886.2	886.3
162.5°	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0	900.1	899.2	899.4
165°	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3	918.3	917.3	917.7
167.5°	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8	933.8	932.8	932.7
170°	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1	942.1	941.1	940.9
172.5°	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3	948.2	947.0	947.0
175°	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7	953.9
177.5°	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7	958.8	957.9	957.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	7.3	6.8	6.9	6.6	6.5	6.9	7.1	6.9	6.7	6.5	6.3
90°	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2	4.0	5.9	7.7
92.5°	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9	18.0	20.0	22.1
95°	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5	46.0	47.5	49.0
97.5°	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8	79.0	80.2	81.3
100°	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9	104.6	105.2	105.9
102.5°	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2	131.5	131.7	132.0
105°	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9	173.1	173.3	173.4
107.5°	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7	216.9	217.1	217.3
110°	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4	246.7	247.1	247.4



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3	277.3	277.4	277.5
115°	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6	323.6	323.6	323.6
117.5°	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2	367.4	367.5	367.6
120°	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3	397.0	397.6	398.3
122.5°	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6	426.9	427.1	427.4
125°	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3
127.5°	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8	512.3	512.8	513.3
130°	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3	540.8	541.3	541.8
132.5°	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4	569.8	570.1	570.5
135°	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9	608.8	609.8	610.8
137.5°	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7	650.2	650.6	651.1
140°	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6	677.9	678.3	678.6
142.5°	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1	703.5	703.8	704.1
145°	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5	739.1	739.8	740.5
147.5°	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5	774.3	775.1	775.9
150°	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9	795.5	796.2	796.9
152.5°	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1	815.5	815.9	816.3
155°	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1	846.1	846.1	846.1
157.5°	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2	871.9	871.6	871.3
160°	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7	887.5	887.3	887.2
162.5°	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9	901.5	901.0	900.6
165°	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1	920.6	920.1	919.6
167.5°	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7	935.1	934.4	933.7
170°	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1	943.2	942.4	941.6
172.5°	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0	949.3	948.6	947.9
175°	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2	957.3	956.5	955.7
177.5°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	6.6	6.8	7.0	6.9	7.4	7.6	7.6	7.8	8.2	8.0	8.2
90°	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3	19.3	20.3	20.9
92.5°	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6	31.2	31.8	32.2
95°	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4	57.9	58.4	58.6
97.5°	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4	91.0	91.6	91.9
100°	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2	114.5	114.9	115.0
102.5°	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4	139.9	140.3	140.6
105°	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6	178.1	178.6	179.1
107.5°	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0	219.4	219.9	220.1
110°	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5	246.2	245.8	245.9



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1	276.0	276.0	276.0
115°	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8	321.6	321.4	321.3
117.5°	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7	365.1	364.5	364.1
120°	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4	394.6	393.8	393.5
122.5°	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6	425.1	424.5	423.9
125°	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9	469.6	469.2	468.9
127.5°	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2	511.9	511.5	511.2
130°	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9	541.5	541.2	540.7
132.5°	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8	569.5	569.1	568.8
135°	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6	611.3	611.0	610.6
137.5°	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1	651.7	651.3	651.1
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8	678.6	678.4	678.3
142.5°	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0	703.9	703.9	703.9
145°	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9	741.7	741.5	741.2
147.5°	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2	776.1	775.9	775.8
150°	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.9	797.8
152.5°	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2	818.6	819.0	819.0
155°	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7	847.3	848.0	848.0
157.5°	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7	872.2	872.7	872.7
160°	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2	887.7	888.2	888.0
162.5°	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0	901.9	902.8	902.8
165°	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3	920.3	921.3	921.5
167.5°	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8	935.7	936.7	936.7
170°	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1	944.1	945.1	945.0
172.5°	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3	950.4	951.5	951.5
175°	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0	957.2	958.3	958.3
177.5°	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7	960.6	961.6	961.5
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	8.6	8.5	8.4	8.6	8.4	8.5	8.6	8.2	8.0	8.2	7.8
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.3	19.3	18.3
92.5°	32.4	32.6	32.8	33.0	32.8	32.6	32.4	32.2	31.8	31.2	30.6
95°	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.4	57.9	57.4
97.5°	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.6	91.0	90.4
100°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0	114.9	114.5	114.2
102.5°	140.8	140.9	141.0	141.2	141.0	140.9	140.8	140.6	140.3	139.9	139.4
105°	179.6	180.1	180.6	181.1	180.6	180.1	179.6	179.1	178.6	178.1	177.6
107.5°	220.1	220.1	220.0	220.0	220.0	220.1	220.1	220.1	219.9	219.4	219.0
110°	246.4	246.9	247.4	247.9	247.4	246.9	246.4	245.9	245.8	246.2	246.5



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	276.1	276.2	276.3	276.4	276.3	276.2	276.1	276.0	276.0	276.0	276.1
115°	321.1	321.0	320.8	320.6	320.8	321.0	321.1	321.3	321.4	321.6	321.8
117.5°	363.8	363.4	363.1	362.8	363.1	363.4	363.8	364.1	364.5	365.1	365.7
120°	393.9	394.2	394.5	394.8	394.5	394.2	393.9	393.5	393.8	394.6	395.4
122.5°	423.3	422.7	422.2	421.6	422.2	422.7	423.3	423.9	424.5	425.1	425.6
125°	468.6	468.2	467.9	467.6	467.9	468.2	468.6	468.9	469.2	469.6	469.9
127.5°	511.0	510.7	510.4	510.2	510.4	510.7	511.0	511.2	511.5	511.9	512.2
130°	540.1	539.4	538.7	538.1	538.7	539.4	540.1	540.7	541.2	541.5	541.9
132.5°	568.6	568.3	568.0	567.8	568.0	568.3	568.6	568.8	569.1	569.5	569.8
135°	610.1	609.6	609.1	608.6	609.1	609.6	610.1	610.6	611.0	611.3	611.6
137.5°	651.2	651.3	651.4	651.5	651.4	651.3	651.2	651.1	651.3	651.7	652.1
140°	678.1	677.9	677.8	677.6	677.8	677.9	678.1	678.3	678.4	678.6	678.8
142.5°	703.8	703.8	703.8	703.7	703.8	703.8	703.8	703.9	703.9	703.9	704.0
145°	740.7	740.2	739.7	739.2	739.7	740.2	740.7	741.2	741.5	741.7	741.9
147.5°	775.6	775.5	775.3	775.1	775.3	775.5	775.6	775.8	775.9	776.1	776.2
150°	797.6	797.4	797.3	797.1	797.3	797.4	797.6	797.8	797.9	797.9	797.9
152.5°	818.6	818.2	817.7	817.3	817.7	818.2	818.6	819.0	819.0	818.6	818.2
155°	847.3	846.7	846.0	845.4	846.0	846.7	847.3	848.0	848.0	847.3	846.7
157.5°	872.1	871.6	871.0	870.4	871.0	871.6	872.1	872.7	872.7	872.2	871.7
160°	887.2	886.3	885.5	884.7	885.5	886.3	887.2	888.0	888.2	887.7	887.2
162.5°	902.0	901.2	900.4	899.5	900.4	901.2	902.0	902.8	902.8	901.9	901.0
165°	920.8	920.1	919.5	918.8	919.5	920.1	920.8	921.5	921.3	920.3	919.3
167.5°	935.7	934.7	933.7	932.6	933.7	934.7	935.7	936.7	936.7	935.7	934.8
170°	943.8	942.7	941.5	940.4	941.5	942.7	943.8	945.0	945.1	944.1	943.1
172.5°	950.3	949.2	948.0	946.9	948.0	949.2	950.3	951.5	951.5	950.4	949.3
175°	957.2	956.0	954.9	953.7	954.9	956.0	957.2	958.3	958.3	957.2	956.0
177.5°	960.4	959.4	958.3	957.3	958.3	959.4	960.4	961.5	961.6	960.6	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	7.6	7.6	7.4	6.9	7.0	6.8	6.6	6.3	6.5	6.7	6.9
90°	17.3	16.3	15.0	13.7	12.4	11.1	9.5	7.7	5.9	4.0	2.2
92.5°	30.0	29.4	28.5	27.5	26.6	25.7	24.2	22.1	20.0	18.0	15.9
95°	56.9	56.4	55.3	54.1	52.9	51.8	50.5	49.0	47.5	46.0	44.5
97.5°	89.8	89.2	87.9	86.5	85.2	83.8	82.5	81.3	80.2	79.0	77.8
100°	113.9	113.6	112.1	110.6	109.1	107.6	106.5	105.9	105.2	104.6	103.9
102.5°	139.0	138.5	137.1	135.8	134.4	133.1	132.3	132.0	131.7	131.5	131.2
105°	177.1	176.6	176.0	175.3	174.7	174.0	173.6	173.4	173.3	173.1	172.9
107.5°	218.5	218.1	218.0	217.9	217.8	217.7	217.5	217.3	217.1	216.9	216.7
110°	246.8	247.1	247.3	247.5	247.6	247.8	247.7	247.4	247.1	246.7	246.4



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	276.2	276.2	276.5	276.8	277.1	277.4	277.5	277.5	277.4	277.3	277.3
115°	321.9	322.1	322.4	322.8	323.1	323.4	323.6	323.6	323.6	323.6	323.6
117.5°	366.2	366.8	367.0	367.3	367.5	367.7	367.8	367.6	367.5	367.4	367.2
120°	396.2	397.1	397.6	398.1	398.6	399.0	399.0	398.3	397.6	397.0	396.3
122.5°	426.2	426.8	427.0	427.2	427.5	427.7	427.7	427.4	427.1	426.9	426.6
125°	470.2	470.5	470.7	470.9	471.0	471.2	471.3	471.3	471.3	471.3	471.3
127.5°	512.5	512.9	513.1	513.4	513.6	513.9	513.8	513.3	512.8	512.3	511.8
130°	542.2	542.5	542.5	542.5	542.5	542.5	542.3	541.8	541.3	540.8	540.3
132.5°	570.1	570.4	570.6	570.7	570.8	571.0	570.9	570.5	570.1	569.8	569.4
135°	612.0	612.3	612.3	612.3	612.3	612.3	611.8	610.8	609.8	608.8	607.9
137.5°	652.5	653.0	652.7	652.4	652.2	651.9	651.6	651.1	650.6	650.2	649.7
140°	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.6	678.3	677.9	677.6
142.5°	704.0	704.0	704.2	704.3	704.4	704.6	704.5	704.1	703.8	703.5	703.1
145°	742.0	742.2	742.0	741.9	741.7	741.5	741.1	740.5	739.8	739.1	738.5
147.5°	776.3	776.5	776.6	776.7	776.9	777.0	776.7	775.9	775.1	774.3	773.5
150°	797.9	797.9	797.9	797.9	797.9	797.9	797.5	796.9	796.2	795.5	794.9
152.5°	817.8	817.4	817.3	817.2	817.0	816.9	816.7	816.3	815.9	815.5	815.1
155°	846.0	845.4	845.5	845.7	845.8	846.0	846.1	846.1	846.1	846.1	846.1
157.5°	871.2	870.7	870.8	870.8	870.8	870.9	871.0	871.3	871.6	871.9	872.2
160°	886.7	886.2	886.3	886.5	886.7	886.8	887.0	887.2	887.3	887.5	887.7
162.5°	900.1	899.2	899.4	899.6	899.7	899.9	900.2	900.6	901.0	901.5	901.9
165°	918.3	917.3	917.7	918.0	918.3	918.7	919.1	919.6	920.1	920.6	921.1
167.5°	933.8	932.8	932.7	932.7	932.7	932.6	933.0	933.7	934.4	935.1	935.7
170°	942.1	941.1	940.9	940.8	940.6	940.4	940.8	941.6	942.4	943.2	944.1
172.5°	948.2	947.0	947.0	947.0	946.9	946.9	947.2	947.9	948.6	949.3	950.0
175°	954.9	953.7	953.9	954.0	954.2	954.4	954.9	955.7	956.5	957.3	958.2
177.5°	958.8	957.9	957.9	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	7.1	6.9	6.5	6.6	6.9	6.8	7.3	7.5	7.8	7.8	8.4
90°	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3	18.3
92.5°	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0	30.6
95°	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9	57.4
97.5°	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8	90.4
100°	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9	114.2
102.5°	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0	139.4
105°	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1	177.6
107.5°	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5	219.0
110°	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8	246.5



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2	276.1
115°	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9	321.8
117.5°	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2	365.7
120°	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2	395.4
122.5°	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2	425.6
125°	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2	469.9
127.5°	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5	512.2
130°	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2	541.9
132.5°	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1	569.8
135°	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0	611.6
137.5°	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5	652.1
140°	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9	678.8
142.5°	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0	704.0
145°	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0	741.9
147.5°	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3	776.2
150°	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8	818.2
155°	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0	846.7
157.5°	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2	871.7
160°	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7	887.2
162.5°	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1	901.0
165°	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3	919.3
167.5°	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8	934.8
170°	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1	943.1
172.5°	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2	949.3
175°	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9	956.0
177.5°	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8	959.7
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	8.2	8.2	8.5	8.4	8.5	8.4	8.6
90°	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.2	245.8	245.9	246.4	246.9	247.4	247.9



TEST NUMBER: P333020

CATALOG NUMBER: S124RDIW-S350D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)