

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332797-940

Luminaire Tested: **S124DIW-S795D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332797-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1340U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7825.5 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	40	39	33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	1.4
10°-20°	314.1	4.0
20°-30°	462.3	5.9
30°-40°	537.4	6.9
40°-50°	537.5	6.9
50°-60°	470.1	6.0
60°-70°	349.1	4.5
70°-80°	198.4	2.5
80°-90°	61.7	0.8
90°-100°	52.9	0.7
100°-110°	337.2	4.3
110°-120°	645.1	8.2
120°-130°	818.9	10.5
130°-140°	876.2	11.2
140°-150°	819.3	10.5
150°-160°	660.7	8.4
160°-170°	426.2	5.4
170°-180°	146.9	1.9
0°-30°	887.8	11.3
0°-40°	1425.3	18.2
0°-60°	2432.8	31.1
0°-90°	3042.0	38.9
90°-120°	1035.2	13.2
90°-150°	3549.6	45.4
90°-180°	4783.0	61.1
0°-180°	7825.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	4	16	25	32	35	6
95°	64	26	25	32	34	82
105°	348	355	361	368	330	364
115°	650	653	652	654	655	639
125°	914	918	916	919	921	815
135°	1134	1133	1137	1139	1142	873
145°	1307	1310	1310	1312	1314	816
155°	1433	1434	1431	1435	1432	660
165°	1512	1506	1506	1514	1505	427
175°	1546	1540	1541	1550	1537	147
180°	1546	1546	1546	1546	1546	



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.4	20.8	21.2	21.6	22.0	22.3	22.6	22.8	23.1	23.3	23.6
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	14.5	14.7	14.9	15.1	15.2	16.3	18.4	20.4	22.5	24.5	26.0
95°	63.6	54.8	46.1	37.4	28.6	24.4	24.7	25.0	25.1	25.4	27.0
97.5°	135.1	140.5	146.0	151.4	156.9	145.3	116.5	87.9	59.2	30.5	30.7
100°	189.7	194.3	198.9	203.6	208.2	192.8	157.3	121.8	86.3	50.9	46.5
102.5°	250.7	254.1	257.5	260.9	264.3	263.7	259.0	254.5	249.9	245.2	198.0
105°	348.1	349.6	351.2	352.8	354.3	355.7	357.0	358.3	359.5	360.9	363.2
107.5°	438.5	439.3	440.1	440.9	441.7	442.9	444.7	446.4	448.2	450.0	451.0
110°	499.6	500.4	501.2	501.9	502.7	503.9	505.4	506.9	508.5	510.1	510.6



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.8	560.3	561.7	563.0	564.5	565.4	566.2	566.9	567.7	568.4	568.3
115°	650.0	650.8	651.6	652.3	653.1	653.4	653.1	652.8	652.6	652.3	652.8
117.5°	732.1	733.2	734.1	735.2	736.2	737.0	737.6	738.2	738.7	739.3	739.2
120°	787.6	788.6	789.7	790.8	791.8	792.1	791.9	791.7	791.4	791.1	791.7
122.5°	839.5	840.1	840.7	841.3	842.0	842.4	842.8	843.1	843.5	843.8	844.2
125°	913.7	914.7	915.8	916.8	917.8	918.1	917.6	917.0	916.5	916.1	916.8
127.5°	984.0	984.3	984.5	984.8	985.1	985.8	986.9	988.1	989.4	990.5	990.3
130°	1029.4	1029.7	1029.9	1030.1	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3
132.5°	1071.0	1071.5	1071.9	1072.4	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7
135°	1133.5	1133.2	1132.9	1132.7	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5
137.5°	1188.7	1188.8	1188.9	1189.1	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9
140°	1224.9	1225.4	1225.8	1226.4	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2
142.5°	1257.2	1258.1	1259.1	1260.0	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4
145°	1307.0	1307.7	1308.5	1309.3	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7
147.5°	1346.5	1347.9	1349.4	1350.9	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0
150°	1375.2	1376.3	1377.2	1378.3	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7
152.5°	1399.3	1400.1	1400.9	1401.7	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3
155°	1433.1	1433.2	1433.5	1433.8	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7
157.5°	1461.5	1461.3	1461.2	1461.0	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2
160°	1478.1	1477.4	1476.6	1475.8	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1
162.5°	1492.9	1491.9	1491.0	1490.0	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9
165°	1511.7	1510.4	1509.1	1507.8	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0
167.5°	1526.5	1525.2	1523.8	1522.5	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1
170°	1534.8	1533.3	1531.7	1530.2	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1
172.5°	1540.3	1538.8	1537.3	1535.7	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6
175°	1546.4	1544.8	1543.3	1541.8	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9
177.5°	1549.2	1547.7	1546.2	1544.8	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	23.9	24.3	24.5	24.7	24.9	25.0	25.1	25.1
90°	28.5	30.1	31.7	32.6	33.2	33.7	34.2	34.7
92.5°	27.6	29.2	30.7	31.5	31.7	31.7	31.8	31.9
95°	28.5	30.1	31.7	32.5	32.7	33.0	33.3	33.5
97.5°	30.9	31.0	31.1	31.4	31.7	31.8	32.1	32.4
100°	42.2	37.8	33.4	31.4	31.7	31.8	32.1	32.4
102.5°	151.0	103.8	56.6	33.1	33.2	33.2	33.3	33.3
105°	365.5	367.8	370.1	366.7	357.4	348.1	338.9	329.7
107.5°	452.2	453.3	454.4	455.5	456.5	457.4	458.4	459.4
110°	511.1	511.6	512.1	512.7	513.5	514.3	515.1	515.9



TEST NUMBER: P332797-940

CATALOG NUMBER: S124DIW-S795D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.1	568.0	567.9	568.4	569.4	570.3	571.3	572.3
115°	653.4	653.9	654.3	654.6	654.6	654.6	654.6	654.6
117.5°	739.0	739.0	738.9	738.8	738.7	738.6	738.5	738.3
120°	792.1	792.6	793.2	793.2	792.6	792.1	791.7	791.1
122.5°	844.5	844.8	845.1	845.0	844.5	843.9	843.5	842.9
125°	917.6	918.4	919.1	919.6	919.9	920.2	920.4	920.7
127.5°	990.2	990.1	989.9	989.7	989.5	989.3	989.1	988.9
130°	1034.5	1034.7	1035.0	1035.2	1035.2	1035.2	1035.2	1035.2
132.5°	1078.0	1078.3	1078.5	1078.5	1078.3	1078.2	1077.9	1077.7
135°	1138.0	1138.4	1139.0	1139.5	1140.1	1140.5	1141.0	1141.6
137.5°	1195.4	1196.0	1196.6	1196.8	1196.6	1196.5	1196.3	1196.1
140°	1231.0	1231.8	1232.5	1233.1	1233.3	1233.6	1233.9	1234.1
142.5°	1263.9	1264.4	1265.1	1265.3	1265.4	1265.4	1265.5	1265.5
145°	1310.9	1311.2	1311.4	1311.9	1312.3	1312.9	1313.4	1313.9
147.5°	1352.3	1352.5	1352.6	1352.9	1353.2	1353.4	1353.6	1353.9
150°	1378.7	1378.7	1378.7	1378.8	1379.0	1379.3	1379.6	1379.8
152.5°	1401.7	1402.1	1402.5	1402.7	1402.5	1402.3	1402.2	1402.0
155°	1432.8	1433.8	1434.9	1434.9	1434.2	1433.4	1432.6	1431.9
157.5°	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9
160°	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6
162.5°	1490.5	1492.0	1493.5	1493.4	1491.7	1490.0	1488.2	1486.5
165°	1510.0	1512.1	1514.1	1513.9	1511.7	1509.4	1507.1	1504.8
167.5°	1524.3	1526.5	1528.8	1528.7	1526.1	1523.5	1521.0	1518.4
170°	1533.1	1535.2	1537.2	1537.0	1534.5	1531.9	1529.3	1526.7
172.5°	1538.6	1540.8	1542.8	1542.5	1539.6	1536.9	1534.1	1531.3
175°	1545.2	1547.6	1549.9	1549.4	1546.4	1543.3	1540.2	1537.1
177.5°	1547.8	1549.4	1551.1	1550.7	1548.2	1545.8	1543.3	1540.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4

(END OF REPORT)