

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333053

Luminaire Tested: **S124RDIW-S575D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333053
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1560U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8590.7 lumens
Efficiency: N/A
Efficacy: 141.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	75	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	45	35	29	24	28	24	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.1
10°-20°	266.2	3.1
20°-30°	384.4	4.5
30°-40°	435.7	5.1
40°-50°	420.8	4.9
50°-60°	349.9	4.1
60°-70°	241.6	2.8
70°-80°	122.5	1.4
80°-90°	37.2	0.4
90°-100°	69.0	0.8
100°-110°	439.7	5.1
110°-120°	841.1	9.8
120°-130°	1067.8	12.4
130°-140°	1142.4	13.3
140°-150°	1068.3	12.4
150°-160°	861.5	10.0
160°-170°	555.6	6.5
170°-180°	191.5	2.2
0°-30°	746.1	8.7
0°-40°	1181.8	13.8
0°-60°	1952.5	22.7
0°-90°	2353.8	27.4
90°-120°	1349.8	15.7
90°-150°	4628.2	53.9
90°-180°	6237.0	72.6
0°-180°	8590.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	4	21	33	42	45	6
95°	83	35	33	42	44	107
105°	454	463	470	480	430	475
115°	848	852	850	853	854	834
125°	1191	1197	1194	1199	1200	1063
135°	1478	1477	1482	1485	1488	1138
145°	1704	1708	1709	1710	1713	1064
155°	1868	1870	1865	1871	1867	861
165°	1971	1964	1964	1974	1962	557
175°	2016	2008	2009	2021	2004	192
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	15.2	14.9	14.5	14.1	13.7	13.8	14.2	14.6	15.0	15.4	15.6
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	19.0	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0
95°	82.9	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2
97.5°	176.1	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0
100°	247.3	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7
102.5°	326.9	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2
105°	453.9	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5
107.5°	571.8	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1
110°	651.5	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	728.7	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9
115°	847.5	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2
117.5°	954.6	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8
120°	1027.0	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2
122.5°	1094.5	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7
125°	1191.4	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4
127.5°	1283.0	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3
130°	1342.2	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5
132.5°	1396.4	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2
135°	1477.9	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1
137.5°	1550.0	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9
140°	1597.0	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1
142.5°	1639.2	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2
145°	1704.1	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9
147.5°	1755.7	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.6	1762.9	1762.6	1762.9
150°	1793.1	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6
152.5°	1824.4	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1
155°	1868.5	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8
157.5°	1905.6	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3
160°	1927.3	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3
162.5°	1946.6	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3
165°	1971.0	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1
167.5°	1990.3	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5
170°	2001.2	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3
172.5°	2008.4	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5
175°	2016.2	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7
177.5°	2019.9	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	15.9	16.1	16.4	16.7	16.9	17.2	17.5	17.8
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	36.0	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	37.2	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.2	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	55.0	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	196.8	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	476.5	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	589.6	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	666.4	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P333053

CATALOG NUMBER: S124RDIW-S575D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	740.8	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	851.9	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.7	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.1	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1196.4	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1291.1	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1348.9	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.6	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1483.7	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1558.7	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1605.1	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.0	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.3	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.1	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1827.6	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1868.1	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1943.4	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1968.8	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1987.5	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	1999.0	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2006.2	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2014.7	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2018.1	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)