

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333038

Luminaire Tested: **S124RDIW-S575D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333038
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3975.3 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	2.4
10°-20°	266.2	6.7
20°-30°	384.4	9.7
30°-40°	435.7	11.0
40°-50°	420.8	10.6
50°-60°	349.9	8.8
60°-70°	241.6	6.1
70°-80°	122.5	3.1
80°-90°	33.2	0.8
90°-100°	38.6	1.0
100°-110°	114.5	2.9
110°-120°	194.3	4.9
120°-130°	256.2	6.4
130°-140°	287.7	7.2
140°-150°	282.7	7.1
150°-160°	237.8	6.0
160°-170°	158.2	4.0
170°-180°	55.4	1.4
0°-30°	746.1	18.8
0°-40°	1181.8	29.7
0°-60°	1952.5	49.1
0°-90°	2349.8	59.1
90°-120°	347.4	8.7
90°-150°	1174.1	29.5
90°-180°	1626.0	40.9
0°-180°	3975.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	1	6	10	13	14	4
95°	27	31	34	36	36	30
105°	106	106	108	109	111	112
115°	198	198	197	196	196	195
125°	288	288	287	286	286	256
135°	371	374	374	373	372	287
145°	451	453	453	453	451	282
155°	517	517	516	518	516	238
165°	562	561	560	563	561	158
175°	585	583	582	585	582	56
180°	586	586	586	586	586	



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	14.6	13.7	12.8	11.9	11.0	10.6	10.6	10.7	10.7	10.7	10.7
90°	1.4	2.5	3.6	4.7	5.8	6.7	7.6	8.4	9.2	10.0	10.6
92.5°	9.7	11.0	12.2	13.5	14.8	15.7	16.3	16.8	17.4	17.9	18.3
95°	27.2	28.1	29.0	29.9	30.8	31.6	32.3	33.0	33.7	34.4	34.7
97.5°	47.5	48.2	48.9	49.7	50.4	51.2	52.0	52.8	53.6	54.5	54.8
100°	63.4	63.8	64.2	64.6	65.1	65.7	66.6	67.5	68.4	69.3	69.5
102.5°	80.1	80.3	80.4	80.6	80.8	81.3	82.1	82.9	83.7	84.6	84.8
105°	105.6	105.7	105.8	105.9	106.0	106.2	106.6	107.0	107.4	107.8	108.1
107.5°	132.3	132.4	132.6	132.7	132.8	132.9	133.0	133.0	133.1	133.1	133.4
110°	150.4	150.6	150.8	151.0	151.2	151.3	151.2	151.1	151.0	150.9	150.7



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.3	169.3	169.4	169.4	169.5	169.4	169.2	169.0	168.8	168.7	168.6
115°	197.6	197.6	197.6	197.6	197.6	197.5	197.3	197.1	196.9	196.7	196.6
117.5°	224.2	224.3	224.4	224.5	224.5	224.5	224.4	224.2	224.1	223.9	223.6
120°	242.0	242.4	242.8	243.2	243.6	243.6	243.3	243.0	242.7	242.4	241.9
122.5°	260.5	260.6	260.8	260.9	261.1	261.1	261.0	260.8	260.7	260.6	260.2
125°	287.7	287.7	287.7	287.7	287.7	287.7	287.6	287.5	287.4	287.3	287.1
127.5°	312.5	312.8	313.1	313.4	313.7	313.8	313.6	313.4	313.3	313.1	312.9
130°	329.9	330.2	330.5	330.8	331.1	331.2	331.2	331.2	331.2	331.2	331.0
132.5°	347.6	347.9	348.1	348.3	348.5	348.6	348.5	348.4	348.4	348.3	348.1
135°	371.1	371.7	372.3	372.9	373.5	373.8	373.8	373.8	373.8	373.8	373.6
137.5°	396.7	397.0	397.2	397.5	397.8	398.0	398.2	398.4	398.5	398.7	398.4
140°	413.7	413.9	414.1	414.3	414.5	414.6	414.6	414.6	414.6	414.6	414.5
142.5°	429.3	429.5	429.7	429.9	430.1	430.2	430.1	430.0	429.9	429.8	429.8
145°	450.9	451.3	451.7	452.1	452.5	452.7	452.8	452.9	453.0	453.1	453.0
147.5°	472.3	472.7	473.2	473.7	474.2	474.4	474.3	474.2	474.2	474.1	474.0
150°	485.3	485.7	486.1	486.5	486.9	487.1	487.1	487.1	487.1	487.1	487.1
152.5°	497.6	497.9	498.1	498.4	498.6	498.8	498.8	498.9	499.0	499.1	499.3
155°	516.6	516.6	516.6	516.6	516.6	516.5	516.4	516.3	516.2	516.1	516.5
157.5°	532.5	532.3	532.2	532.0	531.8	531.7	531.7	531.7	531.6	531.6	531.9
160°	542.0	541.9	541.8	541.7	541.6	541.5	541.4	541.3	541.2	541.1	541.4
162.5°	550.7	550.4	550.1	549.9	549.6	549.4	549.3	549.2	549.1	549.0	549.6
165°	562.3	562.0	561.7	561.4	561.1	560.9	560.7	560.5	560.3	560.1	560.7
167.5°	571.3	570.9	570.5	570.1	569.6	569.4	569.4	569.5	569.5	569.5	570.1
170°	576.4	575.9	575.4	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.2
172.5°	580.0	579.6	579.2	578.8	578.3	578.1	578.1	578.2	578.2	578.2	578.9
175°	585.0	584.5	584.0	583.5	583.0	582.7	582.6	582.5	582.4	582.3	583.0
177.5°	586.6	586.2	585.8	585.4	585.0	584.8	584.8	584.8	584.8	584.8	585.4
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	10.7	10.7	10.6	10.7	10.9	11.1	11.3	11.4
90°	11.2	11.8	12.4	12.8	13.0	13.2	13.4	13.6
92.5°	18.7	19.0	19.4	19.6	19.8	19.9	20.0	20.1
95°	35.0	35.3	35.6	35.8	35.8	35.8	35.8	35.8
97.5°	55.2	55.6	55.9	56.1	56.1	56.1	56.1	56.1
100°	69.7	69.9	70.1	70.2	70.2	70.2	70.2	70.2
102.5°	85.1	85.4	85.7	85.9	85.9	86.0	86.1	86.2
105°	108.5	108.8	109.1	109.4	109.7	110.0	110.3	110.6
107.5°	133.7	134.0	134.3	134.4	134.4	134.4	134.3	134.3
110°	150.5	150.3	150.1	150.1	150.4	150.7	151.0	151.3



TEST NUMBER: P333038

CATALOG NUMBER: S124RDIW-S575D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.6	168.5	168.5	168.5	168.6	168.6	168.7	168.7
115°	196.5	196.4	196.3	196.2	196.1	196.0	195.9	195.8
117.5°	223.3	222.9	222.6	222.3	222.1	221.9	221.7	221.5
120°	241.4	240.9	240.4	240.3	240.5	240.7	240.9	241.1
122.5°	259.9	259.5	259.2	258.8	258.5	258.1	257.7	257.4
125°	286.9	286.7	286.5	286.3	286.1	285.9	285.7	285.5
127.5°	312.7	312.5	312.3	312.1	312.0	311.8	311.7	311.5
130°	330.8	330.6	330.4	330.1	329.7	329.3	328.9	328.5
132.5°	347.9	347.7	347.5	347.3	347.1	347.0	346.8	346.7
135°	373.4	373.2	373.0	372.8	372.5	372.2	371.9	371.6
137.5°	398.1	397.9	397.6	397.5	397.6	397.6	397.7	397.8
140°	414.4	414.3	414.2	414.1	414.0	413.9	413.8	413.7
142.5°	429.8	429.8	429.8	429.7	429.7	429.7	429.7	429.7
145°	452.9	452.8	452.7	452.5	452.2	451.9	451.6	451.3
147.5°	473.9	473.8	473.8	473.7	473.6	473.5	473.4	473.3
150°	487.1	487.1	487.1	487.1	487.0	486.9	486.8	486.7
152.5°	499.6	499.8	500.1	500.0	499.8	499.5	499.3	499.0
155°	516.9	517.3	517.7	517.7	517.3	516.9	516.5	516.1
157.5°	532.2	532.5	532.8	532.8	532.5	532.1	531.8	531.4
160°	541.7	542.0	542.3	542.2	541.7	541.2	540.6	540.1
162.5°	550.1	550.7	551.2	551.2	550.7	550.2	549.7	549.2
165°	561.3	561.9	562.5	562.6	562.2	561.8	561.4	561.0
167.5°	570.7	571.3	571.9	571.9	571.3	570.7	570.0	569.4
170°	575.8	576.4	577.0	576.9	576.2	575.5	574.8	574.1
172.5°	579.6	580.3	580.9	580.9	580.2	579.5	578.8	578.1
175°	583.7	584.4	585.1	585.1	584.4	583.7	583.0	582.3
177.5°	586.0	586.5	587.1	587.0	586.4	585.8	585.1	584.5
180°	585.9	585.9	585.9	585.9	585.9	585.9	585.9	585.9

(END OF REPORT)