

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332804-940

Luminaire Tested: **S124DIW-S795D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332804-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1560U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7866.1 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	1.4
10°-20°	314.1	4.0
20°-30°	462.3	5.9
30°-40°	537.4	6.8
40°-50°	537.5	6.8
50°-60°	470.1	6.0
60°-70°	349.1	4.4
70°-80°	198.4	2.5
80°-90°	62.4	0.8
90°-100°	114.7	1.5
100°-110°	339.7	4.3
110°-120°	576.5	7.3
120°-130°	760.2	9.7
130°-140°	853.8	10.9
140°-150°	839.0	10.7
150°-160°	705.6	9.0
160°-170°	469.5	6.0
170°-180°	164.4	2.1
0°-30°	887.8	11.3
0°-40°	1425.3	18.1
0°-60°	2432.8	30.9
0°-90°	3042.8	38.7
90°-120°	1030.9	13.1
90°-150°	3483.9	44.3
90°-180°	4823.0	61.3
0°-180°	7866.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	4	19	30	37	40	8
95°	81	93	102	106	106	90
105°	313	315	320	324	328	332
115°	586	586	584	582	581	578
125°	854	854	852	850	847	761
135°	1101	1109	1109	1106	1102	852
145°	1338	1343	1344	1343	1339	837
155°	1533	1533	1531	1536	1531	705
165°	1669	1665	1662	1669	1665	470
175°	1736	1729	1728	1736	1728	165
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.5	21.0	21.5	22.0	22.5	22.9	23.2	23.5	23.8	24.2	24.5
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	28.8	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3
95°	80.7	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1
97.5°	140.9	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6
100°	188.2	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3
102.5°	237.7	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7
105°	313.3	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9
107.5°	392.6	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8
110°	446.4	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1



TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.3	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3
115°	586.2	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3
117.5°	665.3	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4
120°	718.0	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8
122.5°	772.8	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1
125°	853.8	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9
127.5°	927.2	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4
130°	978.8	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3
132.5°	1031.5	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9
135°	1101.2	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7
137.5°	1177.1	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1
140°	1227.6	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9
142.5°	1273.8	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4
145°	1337.8	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1401.3	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4
150°	1440.0	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1476.6	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6
155°	1532.8	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7
157.5°	1580.1	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3
160°	1608.1	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3
162.5°	1633.9	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7
165°	1668.6	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7
167.5°	1695.2	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7
170°	1710.3	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6
172.5°	1721.0	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7
175°	1735.8	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8
177.5°	1740.6	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	24.9	25.2	25.6	25.8	25.9	26.0	26.1	26.3
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	55.4	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.0	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	163.8	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	206.9	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	252.5	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	321.8	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	396.7	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	446.6	445.9	445.3	445.5	446.4	447.3	448.2	449.1





TEST NUMBER: P332804-940

CATALOG NUMBER: S124DIW-S795D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.2	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.9	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	662.5	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	716.3	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	771.1	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	851.2	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.9	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.7	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1032.2	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1108.0	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1181.4	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.7	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.3	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1344.0	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.2	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1482.3	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1579.2	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1607.2	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1632.3	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1665.4	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1693.4	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1708.5	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1719.8	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1738.7	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)