

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332780-940

Luminaire Tested: **S124DIW-S795D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332780-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D470U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4488.7 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	85	75	67	61	79	71	64	58	63	58	53	56	52	48	50	47	44	40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	45	41	38	35
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	46	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	2.5
10°-20°	314.1	7.0
20°-30°	462.3	10.3
30°-40°	537.4	12.0
40°-50°	537.5	12.0
50°-60°	470.1	10.5
60°-70°	349.1	7.8
70°-80°	198.4	4.4
80°-90°	58.8	1.3
90°-100°	34.5	0.8
100°-110°	102.1	2.3
110°-120°	173.3	3.9
120°-130°	228.5	5.1
130°-140°	256.6	5.7
140°-150°	252.1	5.6
150°-160°	212.1	4.7
160°-170°	141.1	3.1
170°-180°	49.4	1.1
0°-30°	887.8	19.8
0°-40°	1425.3	31.8
0°-60°	2432.8	54.2
0°-90°	3039.1	67.7
90°-120°	309.8	6.9
90°-150°	1047.0	23.3
90°-180°	1450.0	32.3
0°-180°	4488.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	1	6	9	11	12	4
95°	24	28	31	32	32	27
105°	94	95	96	97	99	100
115°	176	176	175	175	175	174
125°	256	256	256	255	255	229
135°	331	333	333	332	331	256
145°	402	404	404	404	402	252
155°	461	461	460	462	460	212
165°	501	500	499	502	500	141
175°	522	520	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.0	20.0	20.1	20.1	20.1	20.1	20.1	20.1	20.0	20.0	20.1
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	8.6	9.8	10.9	12.0	13.2	14.0	14.5	15.0	15.5	16.0	16.3
95°	24.3	25.1	25.9	26.7	27.5	28.2	28.8	29.4	30.1	30.7	30.9
97.5°	42.4	43.0	43.6	44.3	44.9	45.7	46.4	47.1	47.8	48.6	48.9
100°	56.5	56.9	57.2	57.6	58.1	58.6	59.4	60.2	61.0	61.8	62.0
102.5°	71.4	71.6	71.7	71.9	72.1	72.5	73.2	73.9	74.6	75.4	75.6
105°	94.2	94.3	94.3	94.4	94.5	94.7	95.1	95.4	95.8	96.1	96.4
107.5°	118.0	118.1	118.2	118.3	118.4	118.5	118.6	118.6	118.7	118.7	119.0
110°	134.1	134.3	134.5	134.6	134.8	134.9	134.8	134.7	134.6	134.6	134.4



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	151.0	151.0	151.1	151.1	151.1	151.1	150.9	150.7	150.5	150.4	150.3
115°	176.2	176.2	176.2	176.2	176.2	176.1	175.9	175.8	175.6	175.4	175.3
117.5°	199.9	200.0	200.1	200.2	200.2	200.2	200.1	199.9	199.8	199.7	199.4
120°	215.8	216.2	216.5	216.9	217.2	217.2	217.0	216.7	216.4	216.2	215.7
122.5°	232.3	232.4	232.6	232.6	232.8	232.8	232.7	232.6	232.5	232.4	232.0
125°	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.3	256.2	256.0
127.5°	278.7	278.9	279.2	279.5	279.7	279.8	279.6	279.5	279.4	279.2	279.0
130°	294.2	294.4	294.7	295.0	295.2	295.3	295.3	295.3	295.3	295.3	295.2
132.5°	310.0	310.2	310.4	310.6	310.8	310.9	310.8	310.7	310.7	310.6	310.4
135°	330.9	331.4	332.0	332.5	333.1	333.3	333.3	333.3	333.3	333.3	333.1
137.5°	353.7	354.0	354.2	354.5	354.7	354.9	355.1	355.3	355.3	355.5	355.3
140°	368.9	369.1	369.3	369.4	369.6	369.7	369.7	369.7	369.7	369.7	369.6
142.5°	382.8	383.0	383.2	383.3	383.5	383.6	383.5	383.4	383.3	383.3	383.3
145°	402.1	402.4	402.8	403.1	403.5	403.7	403.8	403.9	403.9	404.0	403.9
147.5°	421.2	421.5	422.0	422.4	422.8	423.0	422.9	422.8	422.8	422.8	422.7
150°	432.7	433.1	433.5	433.8	434.2	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	443.7	444.0	444.2	444.4	444.6	444.8	444.8	444.9	445.0	445.1	445.2
155°	460.7	460.7	460.7	460.7	460.7	460.6	460.5	460.4	460.3	460.2	460.6
157.5°	474.8	474.7	474.6	474.4	474.2	474.1	474.1	474.1	474.0	474.0	474.3
160°	483.3	483.2	483.1	483.0	483.0	482.9	482.8	482.7	482.6	482.5	482.8
162.5°	491.1	490.8	490.5	490.4	490.1	489.9	489.8	489.7	489.6	489.5	490.1
165°	501.4	501.1	500.9	500.6	500.3	500.2	500.0	499.8	499.6	499.4	500.0
167.5°	509.4	509.1	508.7	508.4	507.9	507.7	507.7	507.8	507.8	507.8	508.4
170°	514.0	513.5	513.1	512.6	512.2	512.0	512.1	512.2	512.3	512.4	512.9
172.5°	517.2	516.8	516.5	516.1	515.7	515.5	515.5	515.6	515.6	515.6	516.2
175°	521.7	521.2	520.8	520.3	519.9	519.6	519.5	519.4	519.3	519.2	519.9
177.5°	523.1	522.7	522.4	522.0	521.7	521.5	521.5	521.5	521.5	521.5	522.0
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	20.2	20.3	20.4	20.5	20.5	20.6	20.6	20.6
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.7	16.9	17.3	17.5	17.7	17.7	17.8	17.9
95°	31.2	31.5	31.7	31.9	31.9	31.9	31.9	31.9
97.5°	49.2	49.6	49.8	50.0	50.0	50.0	50.0	50.0
100°	62.2	62.3	62.5	62.6	62.6	62.6	62.6	62.6
102.5°	75.9	76.2	76.4	76.6	76.6	76.7	76.8	76.9
105°	96.8	97.0	97.3	97.6	97.8	98.1	98.4	98.6
107.5°	119.2	119.5	119.8	119.8	119.8	119.8	119.8	119.8
110°	134.2	134.0	133.8	133.8	134.1	134.4	134.6	134.9



TEST NUMBER: P332780-940

CATALOG NUMBER: S124DIW-S795D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	150.3	150.3	150.3	150.3	150.3	150.3	150.4	150.4
115°	175.2	175.1	175.0	175.0	174.9	174.8	174.7	174.6
117.5°	199.1	198.8	198.5	198.2	198.0	197.9	197.7	197.5
120°	215.3	214.8	214.4	214.3	214.5	214.6	214.8	215.0
122.5°	231.8	231.4	231.1	230.8	230.5	230.2	229.8	229.5
125°	255.8	255.7	255.5	255.3	255.1	254.9	254.8	254.6
127.5°	278.8	278.7	278.5	278.3	278.2	278.0	277.9	277.8
130°	295.0	294.8	294.6	294.4	294.0	293.6	293.3	292.9
132.5°	310.2	310.0	309.9	309.7	309.5	309.4	309.2	309.2
135°	333.0	332.8	332.6	332.4	332.2	331.9	331.6	331.4
137.5°	355.0	354.8	354.5	354.5	354.5	354.5	354.6	354.7
140°	369.5	369.4	369.3	369.3	369.2	369.1	369.0	368.9
142.5°	383.3	383.3	383.3	383.2	383.2	383.2	383.2	383.2
145°	403.9	403.8	403.7	403.5	403.2	403.0	402.7	402.4
147.5°	422.6	422.5	422.5	422.4	422.3	422.2	422.1	422.0
150°	434.4	434.4	434.4	434.4	434.3	434.2	434.1	434.0
152.5°	445.5	445.7	445.9	445.9	445.7	445.4	445.2	445.0
155°	460.9	461.3	461.6	461.6	461.3	460.9	460.6	460.2
157.5°	474.6	474.8	475.1	475.1	474.8	474.5	474.2	473.9
160°	483.0	483.3	483.6	483.5	483.0	482.6	482.1	481.6
162.5°	490.5	491.1	491.5	491.5	491.1	490.6	490.2	489.7
165°	500.5	501.1	501.6	501.7	501.3	501.0	500.6	500.2
167.5°	508.9	509.4	510.0	510.0	509.4	508.9	508.3	507.7
170°	513.4	514.0	514.5	514.4	513.8	513.2	512.6	511.9
172.5°	516.8	517.5	518.0	518.0	517.4	516.7	516.1	515.5
175°	520.5	521.1	521.7	521.7	521.1	520.5	519.9	519.2
177.5°	522.5	523.0	523.5	523.4	522.9	522.4	521.7	521.2
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5

(END OF REPORT)