

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333041

Luminaire Tested: **S124RDIW-S575D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333041  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5420.8 lumens  
Efficiency: N/A  
Efficacy: 144.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8205	8205	8205
5°	8223	8122	8173
10°	8171	8025	8025
15°	8078	7856	7798
20°	7948	7635	7494
25°	7784	7375	7187
30°	7623	7101	6804
35°	7447	6818	6419
40°	7233	6495	6003
45°	7036	6174	5579
50°	6812	5805	5130
55°	6572	5422	4643
60°	6307	5000	4146
65°	6065	4474	3656
70°	5712	3895	3104
75°	5268	3228	2523
80°	4593	2459	2315
85°	3890	2232	2093



TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	1.8
10°-20°	266.2	4.9
20°-30°	384.4	7.1
30°-40°	435.7	8.0
40°-50°	420.8	7.8
50°-60°	349.9	6.5
60°-70°	241.6	4.5
70°-80°	122.5	2.3
80°-90°	34.3	0.6
90°-100°	33.9	0.6
100°-110°	216.4	4.0
110°-120°	414.0	7.6
120°-130°	525.6	9.7
130°-140°	562.3	10.4
140°-150°	525.8	9.7
150°-160°	424.0	7.8
160°-170°	273.5	5.0
170°-180°	94.3	1.7
0°-30°	746.1	13.8
0°-40°	1181.8	21.8
0°-60°	1952.5	36.0
0°-90°	2350.9	43.4
90°-120°	664.4	12.3
90°-150°	2278.1	42.0
90°-180°	3070.0	56.6
0°-180°	5420.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1015	1011	1002	1010	1008	96
15°	966	959	940	938	933	272
25°	874	859	828	815	807	402
35°	756	730	692	666	651	472
45°	616	586	541	504	489	475
55°	467	435	385	346	330	418
65°	318	283	234	202	191	313
75°	169	140	104	86	81	178
85°	42	27	24	23	23	47
90°	2	10	16	21	22	4
95°	41	17	16	21	22	52
105°	223	228	232	236	212	234
115°	417	419	419	420	420	410
125°	586	589	588	590	591	523
135°	727	727	730	731	733	560
145°	839	841	841	842	843	524
155°	920	920	918	921	919	424
165°	970	967	966	972	966	274
175°	992	988	989	995	986	94
180°	992	992	992	992	992	



TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1018.8	1018.2	1017.7	1017.1	1016.6	1015.5	1014.0	1012.5	1010.9	1009.4	1010.9
5°	1014.7	1014.0	1013.3	1012.6	1012.0	1010.6	1008.5	1006.4	1004.3	1002.3	1004.0
7.5°	1005.5	1004.8	1004.1	1003.4	1002.6	1000.9	998.2	995.5	992.8	990.1	991.2
10°	996.8	996.0	995.1	994.2	993.4	991.4	988.3	985.1	982.0	978.9	979.6
12.5°	985.6	984.6	983.6	982.6	981.6	979.3	975.6	971.9	968.3	964.6	965.0
15°	966.5	964.9	963.4	961.8	960.2	957.3	953.0	948.7	944.3	940.0	939.7
17.5°	943.3	941.0	938.8	936.5	934.3	930.6	925.4	920.2	915.0	909.8	908.9
20°	925.2	923.0	920.7	918.5	916.2	912.2	906.3	900.4	894.5	888.7	887.3
22.5°	905.3	902.8	900.3	897.7	895.2	890.8	884.5	878.2	871.9	865.6	863.5
25°	873.9	870.8	867.6	864.5	861.4	856.3	849.2	842.1	835.0	828.0	825.0
27.5°	840.9	837.0	833.1	829.2	825.2	819.5	811.9	804.4	796.8	789.2	785.6
30°	817.8	813.5	809.2	804.9	800.6	794.3	786.2	778.1	769.9	761.8	757.5
32.5°	793.6	788.7	783.8	778.9	774.1	767.4	759.0	750.6	742.2	733.8	728.8
35°	755.6	750.1	744.5	739.0	733.5	726.4	717.7	709.1	700.4	691.8	685.9
37.5°	715.0	709.3	703.6	697.9	692.1	684.5	674.9	665.3	655.8	646.2	639.6
40°	686.3	680.6	674.9	669.2	663.5	655.7	645.9	636.0	626.2	616.3	609.0
42.5°	658.9	653.0	647.0	641.0	635.0	626.9	616.6	606.3	596.1	585.8	578.4
45°	616.3	609.9	603.5	597.1	590.7	582.3	571.9	561.6	551.2	540.8	532.3
47.5°	572.3	565.7	559.0	552.4	545.8	537.1	526.3	515.6	504.8	494.0	485.2
50°	542.4	535.6	528.9	522.1	515.4	506.5	495.4	484.4	473.3	462.2	453.6
52.5°	511.9	505.3	498.7	492.1	485.4	476.5	465.1	453.8	442.4	431.1	422.3
55°	466.9	460.0	453.1	446.1	439.2	430.1	418.9	407.7	396.4	385.2	376.2
57.5°	422.4	415.2	408.0	400.8	393.6	384.5	373.4	362.3	351.3	340.2	331.1
60°	390.6	383.7	376.8	369.9	363.0	354.0	342.9	331.8	320.8	309.7	300.7
62.5°	362.0	354.8	347.6	340.4	333.2	324.0	312.6	301.3	289.9	278.6	270.3
65°	317.5	310.1	302.6	295.2	287.7	278.5	267.4	256.4	245.3	234.2	226.8
67.5°	271.3	264.1	257.0	249.9	242.8	234.1	223.8	213.5	203.3	193.0	186.6
70°	242.0	234.7	227.5	220.2	213.0	204.4	194.5	184.7	174.8	165.0	159.3
72.5°	210.9	204.3	197.7	191.2	184.6	176.7	167.4	158.1	148.7	139.4	134.6
75°	168.9	162.5	156.1	149.7	143.3	136.0	127.9	119.7	111.6	103.5	99.5
77.5°	126.2	120.8	115.4	109.9	104.5	98.5	91.9	85.4	78.8	72.2	69.9
80°	98.8	93.8	88.8	83.8	78.8	73.7	68.5	63.3	58.1	52.9	52.4
82.5°	75.2	70.6	66.0	61.4	56.8	53.0	50.0	47.0	44.1	41.1	40.7
85°	42.0	38.6	35.1	31.6	28.2	26.2	25.7	25.2	24.6	24.1	23.8
87.5°	14.8	14.0	13.3	12.5	11.8	11.5	11.6	11.7	11.9	12.0	12.0
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	9.4	9.5	9.6	9.6	9.7	10.5	11.8	13.1	14.4	15.7	16.7
95°	40.8	35.2	29.6	24.0	18.4	15.7	15.8	16.0	16.2	16.3	17.3
97.5°	86.7	90.2	93.7	97.2	100.7	93.2	74.8	56.4	38.0	19.6	19.7
100°	121.7	124.7	127.7	130.6	133.6	123.7	101.0	78.2	55.4	32.7	29.9
102.5°	160.9	163.1	165.3	167.5	169.6	169.2	166.3	163.3	160.3	157.4	127.1
105°	223.4	224.4	225.4	226.4	227.4	228.3	229.1	229.9	230.8	231.6	233.1
107.5°	281.5	282.0	282.5	283.0	283.5	284.3	285.4	286.5	287.6	288.7	289.5
110°	320.7	321.2	321.7	322.2	322.6	323.4	324.4	325.4	326.4	327.3	327.7



TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.6	360.5	361.3	362.2	362.9	363.4	363.8	364.3	364.8	364.7
115°	417.2	417.7	418.2	418.6	419.1	419.3	419.1	419.0	418.8	418.6	419.0
117.5°	469.9	470.5	471.2	471.8	472.5	473.0	473.4	473.7	474.1	474.5	474.4
120°	505.5	506.2	506.8	507.5	508.1	508.4	508.2	508.1	507.9	507.7	508.1
122.5°	538.8	539.1	539.5	539.9	540.3	540.6	540.9	541.1	541.3	541.6	541.8
125°	586.4	587.1	587.7	588.4	589.0	589.2	588.9	588.6	588.2	587.9	588.4
127.5°	631.5	631.7	631.9	632.0	632.2	632.7	633.4	634.2	634.9	635.7	635.6
130°	660.6	660.8	661.0	661.1	661.3	661.6	662.1	662.6	663.1	663.6	663.8
132.5°	687.4	687.7	688.0	688.2	688.5	689.0	689.6	690.3	690.9	691.5	691.7
135°	727.4	727.3	727.1	726.9	726.8	727.0	727.7	728.3	729.0	729.7	730.0
137.5°	762.9	763.0	763.1	763.1	763.2	763.6	764.3	765.0	765.8	766.5	766.8
140°	786.1	786.4	786.7	787.1	787.4	787.7	788.1	788.4	788.7	789.1	789.5
142.5°	806.9	807.5	808.1	808.6	809.2	809.6	809.8	810.0	810.2	810.4	810.8
145°	838.8	839.3	839.8	840.3	840.8	841.0	841.0	841.0	841.0	841.0	841.2
147.5°	864.2	865.1	866.0	866.9	867.9	868.2	868.1	867.9	867.7	867.6	867.7
150°	882.6	883.2	883.9	884.6	885.2	885.5	885.3	885.1	885.0	884.8	884.8
152.5°	898.0	898.5	899.1	899.6	900.1	900.2	899.9	899.7	899.4	899.1	899.3
155°	919.7	919.9	920.0	920.2	920.4	920.2	919.7	919.2	918.7	918.2	918.9
157.5°	938.0	937.9	937.8	937.7	937.6	937.2	936.7	936.1	935.5	935.0	935.8
160°	948.6	948.1	947.7	947.2	946.7	946.3	946.2	946.0	945.8	945.7	946.7
162.5°	958.1	957.5	956.9	956.3	955.6	955.2	955.1	954.9	954.7	954.6	955.6
165°	970.2	969.3	968.5	967.7	966.9	966.5	966.5	966.5	966.5	966.5	967.8
167.5°	979.7	978.8	978.0	977.1	976.2	975.8	975.7	975.6	975.5	975.4	976.8
170°	985.0	984.0	983.0	982.0	981.1	980.6	980.8	981.0	981.1	981.3	982.6
172.5°	988.6	987.6	986.6	985.6	984.6	984.2	984.4	984.5	984.7	984.9	986.2
175°	992.4	991.4	990.5	989.5	988.5	988.1	988.2	988.4	988.6	988.7	990.2
177.5°	994.2	993.3	992.4	991.4	990.5	990.2	990.5	990.7	991.0	991.2	992.3
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4



TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3
2.5°	1012.5	1014.0	1015.5	1016.2	1016.1	1015.9	1015.8	1015.7
5°	1005.7	1007.5	1009.2	1009.9	1009.5	1009.2	1008.8	1008.5
7.5°	992.3	993.4	994.6	994.8	994.3	993.7	993.2	992.6
10°	980.3	981.0	981.7	981.7	981.0	980.3	979.6	978.9
12.5°	965.4	965.8	966.3	966.0	965.0	964.1	963.1	962.1
15°	939.3	939.0	938.6	937.9	936.6	935.4	934.2	933.0
17.5°	907.9	906.9	905.9	904.5	902.7	900.9	899.0	897.2
20°	885.9	884.5	883.1	881.3	879.1	876.8	874.6	872.3
22.5°	861.5	859.4	857.3	855.4	853.5	851.7	849.9	848.0
25°	822.1	819.1	816.2	813.9	812.1	810.4	808.7	806.9
27.5°	781.9	778.3	774.7	771.6	769.1	766.6	764.2	761.7
30°	753.2	748.8	744.5	741.0	738.2	735.4	732.7	729.9
32.5°	723.8	718.8	713.7	709.9	707.3	704.7	702.0	699.4
35°	680.0	674.1	668.3	663.8	660.7	657.5	654.4	651.3
37.5°	633.0	626.5	619.9	615.1	611.9	608.8	605.7	602.6
40°	601.8	594.5	587.2	582.1	578.9	575.8	572.7	569.6
42.5°	571.0	563.6	556.2	550.9	547.6	544.4	541.1	537.9
45°	523.9	515.4	506.9	501.1	498.0	494.9	491.8	488.7
47.5°	476.4	467.6	458.8	452.7	449.3	445.9	442.5	439.0
50°	444.9	436.3	427.6	421.7	418.4	415.1	411.8	408.5
52.5°	413.5	404.7	396.0	389.9	386.4	383.0	379.6	376.2
55°	367.2	358.2	349.2	343.1	339.8	336.5	333.2	329.9
57.5°	321.9	312.8	303.7	297.9	295.4	292.9	290.4	287.9
60°	291.7	282.7	273.7	267.9	265.1	262.3	259.6	256.8
62.5°	262.0	253.7	245.4	240.1	237.9	235.7	233.5	231.3
65°	219.4	211.9	204.5	199.7	197.7	195.6	193.5	191.4
67.5°	180.2	173.8	167.4	163.1	160.8	158.5	156.2	153.9
70°	153.6	147.9	142.1	138.4	136.7	135.0	133.2	131.5
72.5°	129.7	124.8	119.9	116.7	115.1	113.5	111.9	110.3
75°	95.5	91.6	87.6	85.1	84.0	83.0	82.0	80.9
77.5°	67.6	65.3	62.9	61.6	61.3	61.0	60.7	60.4
80°	51.9	51.4	50.8	50.5	50.3	50.1	50.0	49.8
82.5°	40.3	39.9	39.6	39.3	39.1	38.9	38.8	38.6
85°	23.4	23.1	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	12.1	12.2	12.2	12.4	12.6	12.8	13.0	13.2
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	17.7	18.7	19.7	20.2	20.3	20.4	20.4	20.5
95°	18.3	19.3	20.3	20.9	21.0	21.2	21.4	21.5
97.5°	19.8	19.9	20.0	20.1	20.3	20.5	20.6	20.8
100°	27.1	24.2	21.4	20.1	20.3	20.5	20.6	20.8
102.5°	96.9	66.6	36.4	21.2	21.3	21.3	21.3	21.4
105°	234.6	236.0	237.5	235.3	229.4	223.4	217.5	211.6
107.5°	290.2	290.9	291.7	292.3	293.0	293.6	294.2	294.8
110°	328.0	328.3	328.7	329.1	329.6	330.1	330.6	331.1





TEST NUMBER: P333041

CATALOG NUMBER: S124RDIW-S575D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	364.6	364.6	364.5	364.8	365.4	366.0	366.7	367.3
115°	419.3	419.6	420.0	420.1	420.1	420.1	420.1	420.1
117.5°	474.3	474.3	474.2	474.1	474.1	474.0	473.9	473.9
120°	508.4	508.7	509.0	509.0	508.7	508.4	508.1	507.7
122.5°	542.0	542.2	542.4	542.3	542.0	541.6	541.3	541.0
125°	588.9	589.4	589.9	590.2	590.4	590.5	590.7	590.9
127.5°	635.5	635.4	635.3	635.2	635.1	634.9	634.8	634.7
130°	663.9	664.1	664.3	664.3	664.3	664.3	664.3	664.3
132.5°	691.8	692.0	692.2	692.2	692.1	691.9	691.8	691.7
135°	730.3	730.7	731.0	731.3	731.6	732.0	732.3	732.6
137.5°	767.2	767.6	767.9	768.1	768.0	767.9	767.8	767.7
140°	790.0	790.5	791.0	791.4	791.5	791.7	791.9	792.0
142.5°	811.2	811.5	811.9	812.1	812.1	812.1	812.2	812.2
145°	841.3	841.5	841.7	841.9	842.2	842.6	842.9	843.2
147.5°	867.8	868.0	868.1	868.3	868.4	868.6	868.8	868.9
150°	884.8	884.8	884.8	884.9	885.1	885.2	885.4	885.5
152.5°	899.6	899.8	900.1	900.2	900.1	900.0	899.9	899.8
155°	919.5	920.2	920.8	920.9	920.4	919.9	919.4	919.0
157.5°	936.7	937.6	938.4	938.4	937.6	936.7	935.8	935.0
160°	947.7	948.6	949.6	949.6	948.6	947.7	946.7	945.7
162.5°	956.6	957.5	958.5	958.5	957.4	956.2	955.1	954.0
165°	969.1	970.4	971.7	971.7	970.2	968.7	967.2	965.7
167.5°	978.3	979.7	981.2	981.1	979.4	977.8	976.1	974.5
170°	983.9	985.3	986.6	986.4	984.8	983.1	981.5	979.8
172.5°	987.5	988.8	990.1	989.9	988.1	986.4	984.6	982.8
175°	991.7	993.2	994.7	994.4	992.4	990.5	988.5	986.5
177.5°	993.4	994.4	995.5	995.2	993.6	992.0	990.5	988.9
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4

(END OF REPORT)