

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333072

Luminaire Tested: **S124RDIW-S795D1560U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333072
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1560U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8751.6 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38																				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33																				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28																				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24																				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18																				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16																				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15																				
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	17	16	13																				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10656	10656	10656	10656
5°	12361	10689	9447	10689
10°	14623	10642	8432	10642
15°	16891	10543	7245	10543
20°	18806	10408	6552	10408
25°	19414	10276	6083	10276
30°	16995	10113	5800	10113
35°	13230	9875	5629	9875
40°	9921	9601	5538	9601
45°	7833	9162	5489	9162
50°	6612	8657	5330	8657
55°	5764	8099	5046	8099
60°	5186	7522	4466	7522
65°	4571	6898	3840	6898
70°	4116	6253	3465	6253
75°	3450	5540	2954	5540
80°	2920	4723	2771	4723
85°	2464	3696	2464	3696



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.9	1.5
10°-20°	385.8	4.4
20°-30°	603.4	6.9
30°-40°	670.8	7.7
40°-50°	595.2	6.8
50°-60°	463.8	5.3
60°-70°	303.6	3.5
70°-80°	149.3	1.7
80°-90°	42.7	0.5
90°-100°	128.6	1.5
100°-110°	380.9	4.4
110°-120°	646.6	7.4
120°-130°	852.5	9.7
130°-140°	957.5	10.9
140°-150°	940.9	10.8
150°-160°	791.3	9.0
160°-170°	526.5	6.0
170°-180°	184.4	2.1
0°-30°	1117.1	12.8
0°-40°	1787.9	20.4
0°-60°	2846.9	32.5
0°-90°	3342.5	38.2
90°-120°	1156.1	13.2
90°-150°	3906.9	44.6
90°-180°	5409.0	61.8
0°-180°	8751.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1320	1320	1320	1320	1320	
5°	1525	1319	1166	1319	1525	154
15°	2021	1262	867	1262	2021	575
25°	2180	1154	683	1154	2180	967
35°	1342	1002	571	1002	1342	841
45°	686	802	481	802	686	543
55°	410	575	358	575	410	372
65°	239	361	201	361	239	241
75°	111	178	95	178	111	122
85°	27	40	27	40	27	31
90°	45	4	45	4	45	24
95°	119	90	119	90	119	124
105°	368	351	368	351	368	388
115°	651	657	651	657	651	644
125°	950	958	950	958	950	847
135°	1236	1235	1236	1235	1236	955
145°	1502	1500	1502	1500	1502	940
155°	1717	1719	1717	1719	1717	791
165°	1867	1871	1867	1871	1867	526
175°	1938	1947	1938	1947	1938	184
180°	1950	1950	1950	1950	1950	



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1392.3	1396.2	1392.3	1391.9	1387.7	1386.4	1384.7	1379.2	1368.9	1363.0	1364.3
5°	1525.3	1538.6	1531.2	1530.1	1518.4	1506.7	1499.2	1482.2	1464.1	1451.9	1441.8
7.5°	1679.1	1686.8	1682.1	1674.6	1655.7	1645.0	1627.7	1605.3	1572.9	1548.1	1525.4
10°	1783.8	1790.2	1788.0	1774.2	1760.4	1732.2	1716.2	1684.9	1643.9	1611.5	1581.2
12.5°	1886.7	1893.6	1874.8	1875.5	1849.3	1827.1	1801.8	1762.3	1715.0	1673.2	1635.2
15°	2021.0	2012.5	2012.5	2001.8	1972.6	1941.7	1915.7	1874.2	1814.6	1764.6	1712.0
17.5°	2126.1	2129.0	2124.7	2099.6	2076.6	2044.7	1996.9	1948.5	1893.2	1826.1	1772.3
20°	2189.0	2189.0	2184.3	2167.2	2137.5	2103.4	2051.8	1999.2	1929.0	1861.4	1800.8
22.5°	2214.6	2216.3	2210.6	2196.6	2169.8	2136.6	2092.7	2039.2	1966.8	1890.8	1815.7
25°	2179.5	2189.6	2190.6	2186.9	2178.9	2158.7	2121.0	2066.2	2001.3	1918.9	1838.0
27.5°	2001.0	2013.7	2024.9	2043.3	2067.8	2080.5	2082.2	2054.4	1997.8	1918.4	1837.1
30°	1823.1	1833.8	1868.3	1913.5	1948.7	1980.6	2008.2	2015.7	1983.8	1912.5	1826.9
32.5°	1625.7	1640.2	1674.8	1723.4	1781.9	1835.9	1898.0	1929.7	1928.9	1886.1	1806.9
35°	1342.4	1353.0	1384.9	1436.0	1506.2	1586.5	1684.9	1761.4	1813.6	1809.8	1761.4
37.5°	1082.6	1094.6	1126.9	1169.2	1237.3	1336.7	1431.9	1537.4	1633.8	1687.9	1671.8
40°	941.4	941.9	973.3	1016.9	1080.7	1167.4	1271.1	1388.1	1495.5	1583.3	1600.3
42.5°	829.9	830.0	850.7	897.7	943.7	1025.3	1124.3	1240.5	1366.2	1467.6	1512.7
45°	686.1	690.9	707.9	736.1	772.2	841.4	920.6	1028.6	1169.5	1289.7	1364.7
47.5°	581.0	588.0	598.8	621.8	650.6	696.7	762.2	859.2	973.9	1106.1	1212.8
50°	526.5	527.6	541.4	554.2	579.2	615.9	673.3	754.1	859.4	986.6	1105.2
52.5°	479.7	479.5	487.8	504.0	524.3	552.9	599.3	672.9	766.3	880.2	1002.6
55°	409.5	412.2	418.6	431.3	446.7	467.0	503.6	559.0	632.4	729.7	840.8
57.5°	356.1	357.5	362.5	367.9	382.1	396.8	424.3	462.7	524.6	604.3	707.9
60°	321.2	321.8	323.4	331.3	342.5	356.3	374.9	407.4	459.5	532.4	614.3
62.5°	287.2	288.1	290.6	296.4	305.1	314.6	334.1	360.2	403.3	465.6	539.4
65°	239.3	239.9	243.6	245.7	252.6	261.1	275.5	293.0	322.8	374.9	430.8
67.5°	200.0	200.0	200.2	203.1	207.8	213.5	222.1	236.1	258.6	290.6	339.8
70°	174.4	174.4	175.5	177.1	179.8	184.5	189.3	200.0	216.5	242.5	280.3
72.5°	150.6	151.0	152.1	152.4	153.8	157.7	161.3	168.1	180.3	200.0	230.5
75°	110.6	112.2	114.9	117.0	119.7	119.1	122.9	127.1	130.8	142.5	160.1
77.5°	82.3	81.5	81.8	83.6	83.9	84.5	87.1	90.4	93.2	98.7	105.0
80°	62.8	62.8	64.4	64.9	64.4	64.9	67.5	69.1	70.2	72.3	78.2
82.5°	47.4	48.3	47.8	48.3	48.6	49.1	51.4	51.7	52.8	53.6	56.1
85°	26.6	27.1	27.7	26.6	26.6	26.6	27.7	28.2	29.3	28.7	29.8
87.5°	18.4	17.8	18.1	18.0	18.3	17.6	17.6	18.1	16.8	16.8	16.3
90°	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2	35.2	33.2	30.5
92.5°	66.9	66.5	66.1	65.7	65.3	64.5	63.3	62.1	60.9	59.7	57.8
95°	119.1	119.1	119.1	119.1	119.1	118.6	117.6	116.6	115.6	114.6	112.3
97.5°	186.7	186.7	186.7	186.7	186.7	186.1	184.9	183.7	182.4	181.2	178.5
100°	233.7	233.7	233.7	233.7	233.7	233.4	232.7	232.0	231.4	230.7	227.7
102.5°	286.8	286.5	286.3	286.0	285.7	285.1	284.2	283.2	282.3	281.4	278.6
105°	367.9	366.9	365.9	364.9	363.9	362.9	361.9	360.9	359.9	358.9	357.5
107.5°	446.9	447.0	447.1	447.1	447.2	446.8	445.8	444.9	443.9	443.0	442.8
110°	503.6	502.6	501.6	500.6	499.6	499.4	500.1	500.8	501.4	502.1	502.4



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.5	561.3	561.1	560.9	560.7	560.7	560.8	560.9	561.1	561.2	561.8
115°	651.4	651.7	652.1	652.4	652.7	653.1	653.4	653.7	654.1	654.4	655.1
117.5°	737.0	737.7	738.4	739.0	739.7	740.6	741.8	742.9	744.0	745.2	745.6
120°	802.2	801.5	800.8	800.2	799.5	800.0	801.7	803.3	805.0	806.7	807.7
122.5°	856.5	857.7	858.9	860.1	861.3	862.5	863.6	864.7	865.9	867.0	867.5
125°	949.9	950.6	951.3	951.9	952.6	953.3	954.0	954.6	955.3	956.0	956.3
127.5°	1036.5	1037.0	1037.6	1038.1	1038.6	1039.2	1039.9	1040.6	1041.2	1041.9	1042.5
130°	1093.2	1094.5	1095.9	1097.2	1098.5	1099.5	1100.2	1100.9	1101.6	1102.2	1102.2
132.5°	1153.5	1154.0	1154.6	1155.1	1155.6	1156.2	1156.9	1157.6	1158.3	1158.9	1159.2
135°	1236.4	1237.4	1238.4	1239.4	1240.4	1241.3	1242.0	1242.6	1243.3	1244.0	1244.0
137.5°	1323.6	1323.4	1323.2	1323.0	1322.8	1323.1	1324.0	1324.9	1325.7	1326.6	1326.1
140°	1376.7	1377.0	1377.3	1377.7	1378.0	1378.3	1378.7	1379.0	1379.3	1379.7	1379.7
142.5°	1429.7	1429.8	1429.9	1429.9	1430.0	1430.1	1430.1	1430.2	1430.3	1430.3	1430.6
145°	1501.8	1502.8	1503.8	1504.8	1505.8	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5
147.5°	1574.8	1575.1	1575.5	1575.8	1576.1	1576.4	1576.7	1577.0	1577.2	1577.5	1577.8
150°	1619.4	1619.8	1620.1	1620.4	1620.8	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1660.4	1661.3	1662.2	1663.0	1663.9	1663.9	1663.1	1662.3	1661.5	1660.7	1660.5
155°	1717.4	1718.8	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4	1717.8
157.5°	1768.4	1769.5	1770.7	1771.8	1772.9	1773.0	1772.0	1771.0	1770.0	1769.0	1769.1
160°	1797.3	1799.0	1800.7	1802.4	1804.0	1804.4	1803.4	1802.4	1801.4	1800.4	1800.7
162.5°	1827.5	1829.2	1830.9	1832.5	1834.2	1834.1	1832.3	1830.5	1828.7	1826.9	1827.2
165°	1866.7	1868.0	1869.4	1870.7	1872.1	1871.7	1869.7	1867.7	1865.7	1863.7	1864.4
167.5°	1894.7	1896.8	1898.9	1901.0	1903.1	1903.1	1901.1	1899.1	1897.1	1895.1	1895.0
170°	1910.4	1912.8	1915.1	1917.5	1919.8	1920.0	1918.0	1916.0	1913.9	1911.9	1911.6
172.5°	1923.7	1926.0	1928.4	1930.7	1933.1	1933.1	1930.8	1928.6	1926.3	1924.0	1923.9
175°	1937.6	1939.9	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6	1937.9
177.5°	1944.8	1947.0	1949.1	1951.2	1953.4	1953.5	1951.6	1949.8	1947.9	1946.0	1946.0
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1360.0	1354.1	1351.1	1344.3	1336.2	1331.9	1328.1	1322.6	1315.3	1307.7	1302.1
5°	1429.0	1416.3	1400.3	1381.2	1364.2	1347.7	1333.3	1319.0	1302.5	1285.4	1268.4
7.5°	1499.9	1474.8	1447.7	1416.3	1385.8	1358.0	1332.5	1308.0	1280.3	1255.6	1233.0
10°	1549.2	1515.2	1477.4	1437.6	1397.7	1363.1	1329.1	1298.2	1264.2	1233.9	1208.3
12.5°	1589.2	1549.2	1503.8	1454.1	1406.2	1364.4	1325.2	1285.0	1246.3	1213.4	1179.4
15°	1655.6	1600.8	1539.7	1480.1	1417.9	1361.0	1308.3	1261.5	1217.4	1171.1	1138.7
17.5°	1701.2	1636.2	1561.9	1490.3	1416.8	1349.7	1289.0	1233.2	1182.3	1135.0	1096.4
20°	1728.5	1656.7	1574.2	1492.9	1410.4	1338.6	1273.2	1211.5	1158.9	1107.8	1067.9
22.5°	1743.8	1664.3	1574.2	1489.0	1403.6	1325.9	1254.1	1189.8	1132.5	1081.4	1037.3
25°	1748.7	1663.6	1571.6	1473.7	1380.1	1297.7	1223.2	1153.6	1089.7	1038.7	991.9
27.5°	1741.9	1641.7	1547.4	1447.0	1350.4	1263.5	1185.4	1112.2	1048.3	993.5	945.5
30°	1731.7	1624.2	1523.2	1418.9	1321.1	1237.6	1155.1	1084.9	1018.5	961.6	913.2
32.5°	1709.5	1603.0	1494.2	1387.5	1288.3	1202.3	1124.1	1053.5	988.3	930.1	878.7
35°	1665.7	1557.8	1439.7	1330.1	1232.8	1143.4	1070.1	1002.0	939.8	877.5	823.3
37.5°	1608.0	1497.7	1380.2	1260.2	1162.8	1078.5	1011.1	947.2	886.5	829.7	769.6
40°	1553.5	1453.0	1331.7	1212.6	1112.6	1031.2	969.0	911.0	849.9	793.5	733.4
42.5°	1487.5	1401.9	1279.4	1159.8	1061.1	982.7	924.8	868.1	812.4	757.8	695.1
45°	1377.5	1312.6	1197.7	1082.8	983.4	905.7	852.5	802.5	753.6	701.5	642.5
47.5°	1251.3	1207.4	1108.2	990.6	898.6	828.7	777.3	736.5	695.1	643.0	591.2
50°	1163.7	1135.5	1039.7	932.3	844.6	780.2	727.6	689.3	654.7	604.7	558.4
52.5°	1070.1	1055.1	974.2	871.5	786.7	723.6	678.6	644.2	609.2	567.7	524.4
55°	927.5	935.5	866.9	778.1	698.3	645.1	604.2	575.4	545.7	510.6	477.1
57.5°	781.8	810.9	764.9	686.9	612.1	563.0	532.2	508.0	483.0	453.9	425.3
60°	694.6	719.0	693.0	624.4	559.0	513.2	484.5	465.9	440.9	414.3	392.5
62.5°	609.5	635.7	620.2	564.8	504.1	464.7	439.4	422.1	403.5	380.3	357.6
65°	502.6	519.6	512.2	473.9	430.8	397.3	373.9	361.1	344.1	327.1	306.9
67.5°	384.9	417.8	413.5	393.1	355.9	329.7	314.4	303.1	287.6	275.0	261.2
70°	316.4	346.8	346.2	329.7	309.5	285.1	274.4	264.9	251.0	238.8	227.6
72.5°	259.0	286.8	290.9	278.3	264.4	245.9	235.7	229.1	215.7	207.3	198.3
75°	181.4	201.6	206.9	206.9	200.5	190.9	181.9	177.6	168.1	160.6	155.3
77.5°	118.9	131.7	140.0	141.9	142.9	139.7	132.2	129.2	121.9	119.2	114.1
80°	84.0	92.5	102.1	105.3	108.0	106.9	103.7	101.6	94.7	92.0	89.9
82.5°	58.1	62.8	70.6	77.6	76.9	79.7	76.9	75.2	70.0	69.0	66.9
85°	30.3	30.8	31.9	36.7	39.4	40.4	41.0	39.9	38.3	38.3	34.6
87.5°	15.8	14.8	15.1	14.5	14.2	15.1	15.7	15.4	14.8	14.3	13.8
90°	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5	8.2	11.9	15.6
92.5°	56.0	54.1	52.2	49.2	44.9	40.7	36.5	32.3	36.5	40.7	44.9
95°	109.9	107.6	105.2	102.5	99.5	96.5	93.5	90.5	93.5	96.5	99.5
97.5°	175.7	173.0	170.3	167.7	165.3	162.8	160.4	158.0	160.4	162.8	165.3
100°	224.7	221.7	218.6	216.5	215.1	213.8	212.4	211.1	212.4	213.8	215.1
102.5°	275.9	273.1	270.4	268.7	268.2	267.7	267.1	266.6	267.1	267.7	268.2
105°	356.2	354.8	353.5	352.7	352.3	352.0	351.7	351.3	351.7	352.0	352.3
107.5°	442.6	442.4	442.2	441.9	441.5	441.1	440.7	440.3	440.7	441.1	441.5
110°	502.8	503.1	503.5	503.3	502.6	501.9	501.3	500.6	501.3	501.9	502.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	562.4	563.0	563.6	563.9	563.7	563.6	563.5	563.3	563.5	563.6	563.7
115°	655.7	656.4	657.1	657.4	657.4	657.4	657.4	657.4	657.4	657.4	657.4
117.5°	746.1	746.6	747.1	747.2	746.9	746.6	746.3	746.1	746.3	746.6	746.9
120°	808.7	809.7	810.7	810.5	809.2	807.9	806.5	805.2	806.5	807.9	809.2
122.5°	867.9	868.4	868.9	868.8	868.3	867.8	867.2	866.7	867.2	867.8	868.3
125°	956.6	957.0	957.3	957.5	957.5	957.5	957.5	957.5	957.5	957.5	957.5
127.5°	1043.0	1043.5	1044.1	1043.8	1042.8	1041.8	1040.8	1039.8	1040.8	1041.8	1042.8
130°	1102.2	1102.2	1102.2	1101.7	1100.7	1099.7	1098.7	1097.7	1098.7	1099.7	1100.7
132.5°	1159.5	1159.7	1160.0	1159.8	1159.0	1158.3	1157.6	1156.8	1157.6	1158.3	1159.0
135°	1244.0	1244.0	1244.0	1243.0	1241.0	1238.9	1236.9	1234.9	1236.9	1238.9	1241.0
137.5°	1325.5	1325.0	1324.5	1323.7	1322.8	1321.8	1320.9	1320.0	1320.9	1321.8	1322.8
140°	1379.7	1379.7	1379.7	1379.3	1378.7	1378.0	1377.3	1376.7	1377.3	1378.0	1378.7
142.5°	1430.9	1431.1	1431.4	1431.2	1430.5	1429.9	1429.2	1428.5	1429.2	1429.9	1430.5
145°	1507.2	1506.8	1506.5	1505.7	1504.3	1503.0	1501.6	1500.3	1501.6	1503.0	1504.3
147.5°	1578.0	1578.3	1578.6	1577.9	1576.3	1574.7	1573.1	1571.5	1573.1	1574.7	1576.3
150°	1620.9	1620.9	1620.9	1620.3	1618.9	1617.6	1616.2	1614.9	1616.2	1617.6	1618.9
152.5°	1660.2	1659.9	1659.7	1659.1	1658.3	1657.5	1656.7	1655.9	1656.7	1657.5	1658.3
155°	1718.1	1718.4	1718.8	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
157.5°	1769.1	1769.2	1769.3	1769.6	1770.2	1770.8	1771.4	1772.0	1771.4	1770.8	1770.2
160°	1801.0	1801.4	1801.7	1802.0	1802.4	1802.7	1803.0	1803.4	1803.0	1802.7	1802.4
162.5°	1827.6	1827.9	1828.2	1828.8	1829.7	1830.6	1831.5	1832.3	1831.5	1830.6	1829.7
165°	1865.0	1865.7	1866.4	1867.2	1868.2	1869.2	1870.2	1871.2	1870.2	1869.2	1868.2
167.5°	1894.9	1894.9	1894.8	1895.5	1896.9	1898.3	1899.7	1901.1	1899.7	1898.3	1896.9
170°	1911.3	1910.9	1910.6	1911.3	1912.9	1914.6	1916.3	1918.0	1916.3	1914.6	1912.9
172.5°	1923.9	1923.8	1923.7	1924.4	1925.8	1927.2	1928.6	1930.0	1928.6	1927.2	1925.8
175°	1938.2	1938.6	1938.9	1939.9	1941.6	1943.3	1944.9	1946.6	1944.9	1943.3	1941.6
177.5°	1946.0	1946.0	1946.0	1946.7	1948.0	1949.4	1950.7	1952.0	1950.7	1949.4	1948.0
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1296.2	1291.9	1286.4	1280.0	1272.4	1265.6	1262.6	1265.1	1266.4	1263.0	1262.6
5°	1256.7	1243.4	1232.8	1216.8	1204.1	1193.4	1186.0	1182.8	1183.9	1175.4	1173.2
7.5°	1212.4	1196.6	1179.2	1160.3	1142.6	1127.0	1118.8	1114.3	1105.3	1101.4	1094.9
10°	1183.9	1162.6	1145.6	1123.2	1103.0	1084.4	1075.4	1067.9	1058.9	1054.6	1045.6
12.5°	1154.5	1129.8	1111.1	1087.9	1067.3	1044.8	1036.2	1022.4	1008.3	999.3	987.7
15°	1113.1	1083.4	1060.5	1032.8	1008.4	982.8	960.0	934.4	924.9	904.7	893.0
17.5°	1064.7	1034.5	1006.2	969.1	931.4	899.7	875.3	850.8	836.2	823.3	817.3
20°	1032.8	1005.2	965.8	922.7	880.7	845.6	825.9	810.0	794.0	785.0	778.6
22.5°	1002.6	967.3	921.6	875.1	833.1	805.6	788.9	772.5	759.6	751.0	742.4
25°	952.0	905.7	857.3	804.1	775.4	751.5	733.4	720.1	712.1	701.0	696.7
27.5°	900.0	843.9	790.5	754.8	724.9	703.0	687.2	677.2	667.1	660.0	654.5
30°	860.0	803.1	755.2	721.2	690.9	672.8	660.0	648.3	640.3	634.5	630.2
32.5°	820.4	763.5	723.3	686.7	662.8	645.1	631.5	622.8	616.5	609.0	606.4
35°	763.2	712.7	677.6	644.6	620.1	604.2	593.5	584.5	579.2	577.0	575.4
37.5°	708.2	666.8	629.1	602.0	580.2	567.7	555.1	550.7	547.0	543.2	544.9
40°	673.3	634.5	601.0	572.3	554.7	540.9	533.4	528.1	524.9	524.9	524.9
42.5°	643.1	605.1	572.5	546.7	529.2	517.5	509.2	504.7	503.6	503.2	505.8
45°	596.2	561.1	528.1	506.8	491.9	480.2	475.5	471.7	471.7	473.9	474.4
47.5°	549.7	516.8	490.4	466.5	452.9	445.6	441.4	439.5	439.7	441.9	444.3
50°	521.2	488.8	462.7	441.4	428.7	421.7	418.0	417.0	418.0	418.0	421.7
52.5°	490.1	461.1	435.5	417.6	403.1	396.6	394.6	393.1	393.8	395.5	397.1
55°	444.6	418.6	394.1	377.1	366.4	362.2	357.4	357.9	356.9	357.9	357.9
57.5°	399.0	375.6	352.8	339.3	330.0	323.8	318.6	320.1	318.5	318.3	317.4
60°	369.6	344.1	326.0	313.8	303.1	297.8	293.0	294.1	292.5	291.4	289.3
62.5°	337.7	316.4	299.2	287.4	278.9	272.7	267.9	266.9	263.2	259.5	254.9
65°	291.4	273.9	258.5	247.3	239.3	234.5	230.8	227.6	219.6	211.1	206.9
67.5°	246.5	233.8	219.4	210.0	203.5	197.2	190.1	184.7	177.2	172.5	169.9
70°	217.5	205.3	193.1	184.0	177.1	171.3	163.3	159.6	154.2	152.1	149.4
72.5°	189.9	178.5	167.1	158.9	151.6	147.0	140.7	137.0	134.7	133.8	131.2
75°	147.9	138.8	130.3	122.9	117.0	113.8	111.2	108.5	107.4	102.6	100.0
77.5°	107.9	101.9	96.6	91.3	87.1	85.0	79.9	76.8	75.0	72.8	72.2
80°	84.0	79.8	74.5	71.3	65.4	63.3	61.2	60.6	60.1	59.6	59.0
82.5°	63.2	58.9	53.6	51.7	50.1	48.8	47.5	47.0	46.5	46.8	46.7
85°	31.9	29.8	29.8	29.3	28.7	28.2	27.7	27.7	27.1	27.7	27.1
87.5°	14.5	14.7	15.2	14.9	15.9	16.4	16.4	16.8	17.6	17.2	17.4
90°	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2	39.2	41.2	42.6
92.5°	49.2	52.2	54.1	56.0	57.8	59.7	60.9	62.1	63.3	64.5	65.3
95°	102.5	105.2	107.6	109.9	112.3	114.6	115.6	116.6	117.6	118.6	119.1
97.5°	167.7	170.3	173.0	175.7	178.5	181.2	182.4	183.7	184.9	186.1	186.7
100°	216.5	218.6	221.7	224.7	227.7	230.7	231.4	232.0	232.7	233.4	233.7
102.5°	268.7	270.4	273.1	275.9	278.6	281.4	282.3	283.2	284.2	285.1	285.7
105°	352.7	353.5	354.8	356.2	357.5	358.9	359.9	360.9	361.9	362.9	363.9
107.5°	441.9	442.2	442.4	442.6	442.8	443.0	443.9	444.9	445.8	446.8	447.2
110°	503.3	503.5	503.1	502.8	502.4	502.1	501.4	500.8	500.1	499.4	499.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	563.9	563.6	563.0	562.4	561.8	561.2	561.1	560.9	560.8	560.7	560.7
115°	657.4	657.1	656.4	655.7	655.1	654.4	654.1	653.7	653.4	653.1	652.7
117.5°	747.2	747.1	746.6	746.1	745.6	745.2	744.0	742.9	741.8	740.6	739.7
120°	810.5	810.7	809.7	808.7	807.7	806.7	805.0	803.3	801.7	800.0	799.5
122.5°	868.8	868.9	868.4	867.9	867.5	867.0	865.9	864.7	863.6	862.5	861.3
125°	957.5	957.3	957.0	956.6	956.3	956.0	955.3	954.6	954.0	953.3	952.6
127.5°	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2	1040.6	1039.9	1039.2	1038.6
130°	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6	1100.9	1100.2	1099.5	1098.5
132.5°	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3	1157.6	1156.9	1156.2	1155.6
135°	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3	1242.6	1242.0	1241.3	1240.4
137.5°	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7	1324.9	1324.0	1323.1	1322.8
140°	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3	1379.0	1378.7	1378.3	1378.0
142.5°	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3	1430.2	1430.1	1430.1	1430.0
145°	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5	1507.2	1506.8	1506.5	1505.8
147.5°	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2	1577.0	1576.7	1576.4	1576.1
150°	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.8
152.5°	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5	1662.3	1663.1	1663.9	1663.9
155°	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8	1720.1	1721.4	1722.8	1722.8
157.5°	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0	1771.0	1772.0	1773.0	1772.9
160°	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4	1802.4	1803.4	1804.4	1804.0
162.5°	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7	1830.5	1832.3	1834.1	1834.2
165°	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7	1867.7	1869.7	1871.7	1872.1
167.5°	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1	1899.1	1901.1	1903.1	1903.1
170°	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9	1916.0	1918.0	1920.0	1919.8
172.5°	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3	1928.6	1930.8	1933.1	1933.1
175°	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9	1942.3	1944.6	1947.0	1947.0
177.5°	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9	1949.8	1951.6	1953.5	1953.4
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1260.0	1260.9	1257.9	1257.0	1257.9	1260.9	1260.0	1262.6	1263.0	1266.4	1265.1
5°	1169.0	1167.9	1165.3	1165.8	1165.3	1167.9	1169.0	1173.2	1175.4	1183.9	1182.8
7.5°	1091.1	1087.0	1088.1	1083.9	1088.1	1087.0	1091.1	1094.9	1101.4	1105.3	1114.3
10°	1043.5	1037.6	1032.8	1028.6	1032.8	1037.6	1043.5	1045.6	1054.6	1058.9	1067.9
12.5°	978.4	973.4	966.9	968.2	966.9	973.4	978.4	987.7	999.3	1008.3	1022.4
15°	886.0	878.1	865.3	866.9	865.3	878.1	886.0	893.0	904.7	924.9	934.4
17.5°	807.9	808.0	802.1	803.5	802.1	808.0	807.9	817.3	823.3	836.2	850.8
20°	767.4	763.7	764.2	762.7	764.2	763.7	767.4	778.6	785.0	794.0	810.0
22.5°	739.4	734.8	731.1	727.8	731.1	734.8	739.4	742.4	751.0	759.6	772.5
25°	691.9	688.7	683.9	682.9	683.9	688.7	691.9	696.7	701.0	712.1	720.1
27.5°	650.2	649.6	647.7	645.2	647.7	649.6	650.2	654.5	660.0	667.1	677.2
30°	626.0	624.9	623.8	622.2	623.8	624.9	626.0	630.2	634.5	640.3	648.3
32.5°	604.3	603.6	602.6	602.7	602.6	603.6	604.3	606.4	609.0	616.5	622.8
35°	573.3	572.8	571.7	571.2	571.7	572.8	573.3	575.4	577.0	579.2	584.5
37.5°	544.4	545.8	545.1	545.0	545.1	545.8	544.4	544.9	543.2	547.0	550.7
40°	524.4	524.9	526.0	525.5	526.0	524.9	524.4	524.9	524.9	524.9	528.1
42.5°	507.8	507.9	509.4	507.6	509.4	507.9	507.8	505.8	503.2	503.6	504.7
45°	478.1	481.3	480.8	480.8	480.8	481.3	478.1	474.4	473.9	471.7	471.7
47.5°	445.7	448.4	449.2	449.1	449.2	448.4	445.7	444.3	441.9	439.7	439.5
50°	424.4	423.3	424.9	424.4	424.9	423.3	424.4	421.7	418.0	418.0	417.0
52.5°	398.5	398.7	398.6	398.0	398.6	398.7	398.5	397.1	395.5	393.8	393.1
55°	358.5	359.0	357.9	358.5	357.9	359.0	358.5	357.9	357.9	356.9	357.9
57.5°	315.1	312.5	313.6	312.3	313.6	312.5	315.1	317.4	318.3	318.5	320.1
60°	284.0	279.7	278.7	276.6	278.7	279.7	284.0	289.3	291.4	292.5	294.1
62.5°	249.1	246.1	242.5	244.2	242.5	246.1	249.1	254.9	259.5	263.2	266.9
65°	202.6	200.5	198.9	201.0	198.9	200.5	202.6	206.9	211.1	219.6	227.6
67.5°	167.7	166.6	166.6	165.5	166.6	166.6	167.7	169.9	172.5	177.2	184.7
70°	149.4	147.9	147.9	146.8	147.9	147.9	149.4	149.4	152.1	154.2	159.6
72.5°	130.7	129.1	129.6	128.9	129.6	129.1	130.7	131.2	133.8	134.7	137.0
75°	96.8	94.1	94.1	94.7	94.1	94.1	96.8	100.0	102.6	107.4	108.5
77.5°	72.2	71.7	72.4	71.5	72.4	71.7	72.2	72.2	72.8	75.0	76.8
80°	59.0	58.5	58.0	59.6	58.0	58.5	59.0	59.0	59.6	60.1	60.6
82.5°	45.8	45.7	45.6	47.7	45.6	45.7	45.8	46.7	46.8	46.5	47.0
85°	27.7	26.6	27.7	26.6	27.7	26.6	27.7	27.1	27.7	27.1	27.7
87.5°	18.4	18.1	17.8	18.4	17.8	18.1	18.4	17.4	17.2	17.6	16.8
90°	43.2	43.9	44.6	45.2	44.6	43.9	43.2	42.6	41.2	39.2	37.2
92.5°	65.7	66.1	66.5	66.9	66.5	66.1	65.7	65.3	64.5	63.3	62.1
95°	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	118.6	117.6	116.6
97.5°	186.7	186.7	186.7	186.7	186.7	186.7	186.7	186.7	186.1	184.9	183.7
100°	233.7	233.7	233.7	233.7	233.7	233.7	233.7	233.7	233.4	232.7	232.0
102.5°	286.0	286.3	286.5	286.8	286.5	286.3	286.0	285.7	285.1	284.2	283.2
105°	364.9	365.9	366.9	367.9	366.9	365.9	364.9	363.9	362.9	361.9	360.9
107.5°	447.1	447.1	447.0	446.9	447.0	447.1	447.1	447.2	446.8	445.8	444.9
110°	500.6	501.6	502.6	503.6	502.6	501.6	500.6	499.6	499.4	500.1	500.8



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	560.9	561.1	561.3	561.5	561.3	561.1	560.9	560.7	560.7	560.8	560.9
115°	652.4	652.1	651.7	651.4	651.7	652.1	652.4	652.7	653.1	653.4	653.7
117.5°	739.0	738.4	737.7	737.0	737.7	738.4	739.0	739.7	740.6	741.8	742.9
120°	800.2	800.8	801.5	802.2	801.5	800.8	800.2	799.5	800.0	801.7	803.3
122.5°	860.1	858.9	857.7	856.5	857.7	858.9	860.1	861.3	862.5	863.6	864.7
125°	951.9	951.3	950.6	949.9	950.6	951.3	951.9	952.6	953.3	954.0	954.6
127.5°	1038.1	1037.6	1037.0	1036.5	1037.0	1037.6	1038.1	1038.6	1039.2	1039.9	1040.6
130°	1097.2	1095.9	1094.5	1093.2	1094.5	1095.9	1097.2	1098.5	1099.5	1100.2	1100.9
132.5°	1155.1	1154.6	1154.0	1153.5	1154.0	1154.6	1155.1	1155.6	1156.2	1156.9	1157.6
135°	1239.4	1238.4	1237.4	1236.4	1237.4	1238.4	1239.4	1240.4	1241.3	1242.0	1242.6
137.5°	1323.0	1323.2	1323.4	1323.6	1323.4	1323.2	1323.0	1322.8	1323.1	1324.0	1324.9
140°	1377.7	1377.3	1377.0	1376.7	1377.0	1377.3	1377.7	1378.0	1378.3	1378.7	1379.0
142.5°	1429.9	1429.9	1429.8	1429.7	1429.8	1429.9	1429.9	1430.0	1430.1	1430.1	1430.2
145°	1504.8	1503.8	1502.8	1501.8	1502.8	1503.8	1504.8	1505.8	1506.5	1506.8	1507.2
147.5°	1575.8	1575.5	1575.1	1574.8	1575.1	1575.5	1575.8	1576.1	1576.4	1576.7	1577.0
150°	1620.4	1620.1	1619.8	1619.4	1619.8	1620.1	1620.4	1620.8	1620.9	1620.9	1620.9
152.5°	1663.0	1662.2	1661.3	1660.4	1661.3	1662.2	1663.0	1663.9	1663.9	1663.1	1662.3
155°	1721.4	1720.1	1718.8	1717.4	1718.8	1720.1	1721.4	1722.8	1722.8	1721.4	1720.1
157.5°	1771.8	1770.7	1769.5	1768.4	1769.5	1770.7	1771.8	1772.9	1773.0	1772.0	1771.0
160°	1802.4	1800.7	1799.0	1797.3	1799.0	1800.7	1802.4	1804.0	1804.4	1803.4	1802.4
162.5°	1832.5	1830.9	1829.2	1827.5	1829.2	1830.9	1832.5	1834.2	1834.1	1832.3	1830.5
165°	1870.7	1869.4	1868.0	1866.7	1868.0	1869.4	1870.7	1872.1	1871.7	1869.7	1867.7
167.5°	1901.0	1898.9	1896.8	1894.7	1896.8	1898.9	1901.0	1903.1	1903.1	1901.1	1899.1
170°	1917.5	1915.1	1912.8	1910.4	1912.8	1915.1	1917.5	1919.8	1920.0	1918.0	1916.0
172.5°	1930.7	1928.4	1926.0	1923.7	1926.0	1928.4	1930.7	1933.1	1933.1	1930.8	1928.6
175°	1944.6	1942.3	1939.9	1937.6	1939.9	1942.3	1944.6	1947.0	1947.0	1944.6	1942.3
177.5°	1951.2	1949.1	1947.0	1944.8	1947.0	1949.1	1951.2	1953.4	1953.5	1951.6	1949.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1262.6	1265.6	1272.4	1280.0	1286.4	1291.9	1296.2	1302.1	1307.7	1315.3	1322.6
5°	1186.0	1193.4	1204.1	1216.8	1232.8	1243.4	1256.7	1268.4	1285.4	1302.5	1319.0
7.5°	1118.8	1127.0	1142.6	1160.3	1179.2	1196.6	1212.4	1233.0	1255.6	1280.3	1308.0
10°	1075.4	1084.4	1103.0	1123.2	1145.6	1162.6	1183.9	1208.3	1233.9	1264.2	1298.2
12.5°	1036.2	1044.8	1067.3	1087.9	1111.1	1129.8	1154.5	1179.4	1213.4	1246.3	1285.0
15°	960.0	982.8	1008.4	1032.8	1060.5	1083.4	1113.1	1138.7	1171.1	1217.4	1261.5
17.5°	875.3	899.7	931.4	969.1	1006.2	1034.5	1064.7	1096.4	1135.0	1182.3	1233.2
20°	825.9	845.6	880.7	922.7	965.8	1005.2	1032.8	1067.9	1107.8	1158.9	1211.5
22.5°	788.9	805.6	833.1	875.1	921.6	967.3	1002.6	1037.3	1081.4	1132.5	1189.8
25°	733.4	751.5	775.4	804.1	857.3	905.7	952.0	991.9	1038.7	1089.7	1153.6
27.5°	687.2	703.0	724.9	754.8	790.5	843.9	900.0	945.5	993.5	1048.3	1112.2
30°	660.0	672.8	690.9	721.2	755.2	803.1	860.0	913.2	961.6	1018.5	1084.9
32.5°	631.5	645.1	662.8	686.7	723.3	763.5	820.4	878.7	930.1	988.3	1053.5
35°	593.5	604.2	620.1	644.6	677.6	712.7	763.2	823.3	877.5	939.8	1002.0
37.5°	555.1	567.7	580.2	602.0	629.1	666.8	708.2	769.6	829.7	886.5	947.2
40°	533.4	540.9	554.7	572.3	601.0	634.5	673.3	733.4	793.5	849.9	911.0
42.5°	509.2	517.5	529.2	546.7	572.5	605.1	643.1	695.1	757.8	812.4	868.1
45°	475.5	480.2	491.9	506.8	528.1	561.1	596.2	642.5	701.5	753.6	802.5
47.5°	441.4	445.6	452.9	466.5	490.4	516.8	549.7	591.2	643.0	695.1	736.5
50°	418.0	421.7	428.7	441.4	462.7	488.8	521.2	558.4	604.7	654.7	689.3
52.5°	394.6	396.6	403.1	417.6	435.5	461.1	490.1	524.4	567.7	609.2	644.2
55°	357.4	362.2	366.4	377.1	394.1	418.6	444.6	477.1	510.6	545.7	575.4
57.5°	318.6	323.8	330.0	339.3	352.8	375.6	399.0	425.3	453.9	483.0	508.0
60°	293.0	297.8	303.1	313.8	326.0	344.1	369.6	392.5	414.3	440.9	465.9
62.5°	267.9	272.7	278.9	287.4	299.2	316.4	337.7	357.6	380.3	403.5	422.1
65°	230.8	234.5	239.3	247.3	258.5	273.9	291.4	306.9	327.1	344.1	361.1
67.5°	190.1	197.2	203.5	210.0	219.4	233.8	246.5	261.2	275.0	287.6	303.1
70°	163.3	171.3	177.1	184.0	193.1	205.3	217.5	227.6	238.8	251.0	264.9
72.5°	140.7	147.0	151.6	158.9	167.1	178.5	189.9	198.3	207.3	215.7	229.1
75°	111.2	113.8	117.0	122.9	130.3	138.8	147.9	155.3	160.6	168.1	177.6
77.5°	79.9	85.0	87.1	91.3	96.6	101.9	107.9	114.1	119.2	121.9	129.2
80°	61.2	63.3	65.4	71.3	74.5	79.8	84.0	89.9	92.0	94.7	101.6
82.5°	47.5	48.8	50.1	51.7	53.6	58.9	63.2	66.9	69.0	70.0	75.2
85°	27.7	28.2	28.7	29.3	29.8	29.8	31.9	34.6	38.3	38.3	39.9
87.5°	16.4	16.4	15.9	14.9	15.2	14.7	14.5	13.8	14.3	14.8	15.4
90°	35.2	33.2	30.5	27.8	25.1	22.5	19.3	15.6	11.9	8.2	4.5
92.5°	60.9	59.7	57.8	56.0	54.1	52.2	49.2	44.9	40.7	36.5	32.3
95°	115.6	114.6	112.3	109.9	107.6	105.2	102.5	99.5	96.5	93.5	90.5
97.5°	182.4	181.2	178.5	175.7	173.0	170.3	167.7	165.3	162.8	160.4	158.0
100°	231.4	230.7	227.7	224.7	221.7	218.6	216.5	215.1	213.8	212.4	211.1
102.5°	282.3	281.4	278.6	275.9	273.1	270.4	268.7	268.2	267.7	267.1	266.6
105°	359.9	358.9	357.5	356.2	354.8	353.5	352.7	352.3	352.0	351.7	351.3
107.5°	443.9	443.0	442.8	442.6	442.4	442.2	441.9	441.5	441.1	440.7	440.3
110°	501.4	502.1	502.4	502.8	503.1	503.5	503.3	502.6	501.9	501.3	500.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	561.1	561.2	561.8	562.4	563.0	563.6	563.9	563.7	563.6	563.5	563.3
115°	654.1	654.4	655.1	655.7	656.4	657.1	657.4	657.4	657.4	657.4	657.4
117.5°	744.0	745.2	745.6	746.1	746.6	747.1	747.2	746.9	746.6	746.3	746.1
120°	805.0	806.7	807.7	808.7	809.7	810.7	810.5	809.2	807.9	806.5	805.2
122.5°	865.9	867.0	867.5	867.9	868.4	868.9	868.8	868.3	867.8	867.2	866.7
125°	955.3	956.0	956.3	956.6	957.0	957.3	957.5	957.5	957.5	957.5	957.5
127.5°	1041.2	1041.9	1042.5	1043.0	1043.5	1044.1	1043.8	1042.8	1041.8	1040.8	1039.8
130°	1101.6	1102.2	1102.2	1102.2	1102.2	1102.2	1101.7	1100.7	1099.7	1098.7	1097.7
132.5°	1158.3	1158.9	1159.2	1159.5	1159.7	1160.0	1159.8	1159.0	1158.3	1157.6	1156.8
135°	1243.3	1244.0	1244.0	1244.0	1244.0	1244.0	1243.0	1241.0	1238.9	1236.9	1234.9
137.5°	1325.7	1326.6	1326.1	1325.5	1325.0	1324.5	1323.7	1322.8	1321.8	1320.9	1320.0
140°	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3	1378.7	1378.0	1377.3	1376.7
142.5°	1430.3	1430.3	1430.6	1430.9	1431.1	1431.4	1431.2	1430.5	1429.9	1429.2	1428.5
145°	1507.5	1507.8	1507.5	1507.2	1506.8	1506.5	1505.7	1504.3	1503.0	1501.6	1500.3
147.5°	1577.2	1577.5	1577.8	1578.0	1578.3	1578.6	1577.9	1576.3	1574.7	1573.1	1571.5
150°	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.3	1618.9	1617.6	1616.2	1614.9
152.5°	1661.5	1660.7	1660.5	1660.2	1659.9	1659.7	1659.1	1658.3	1657.5	1656.7	1655.9
155°	1718.8	1717.4	1717.8	1718.1	1718.4	1718.8	1718.9	1718.9	1718.9	1718.9	1718.9
157.5°	1770.0	1769.0	1769.1	1769.1	1769.2	1769.3	1769.6	1770.2	1770.8	1771.4	1772.0
160°	1801.4	1800.4	1800.7	1801.0	1801.4	1801.7	1802.0	1802.4	1802.7	1803.0	1803.4
162.5°	1828.7	1826.9	1827.2	1827.6	1827.9	1828.2	1828.8	1829.7	1830.6	1831.5	1832.3
165°	1865.7	1863.7	1864.4	1865.0	1865.7	1866.4	1867.2	1868.2	1869.2	1870.2	1871.2
167.5°	1897.1	1895.1	1895.0	1894.9	1894.9	1894.8	1895.5	1896.9	1898.3	1899.7	1901.1
170°	1913.9	1911.9	1911.6	1911.3	1910.9	1910.6	1911.3	1912.9	1914.6	1916.3	1918.0
172.5°	1926.3	1924.0	1923.9	1923.9	1923.8	1923.7	1924.4	1925.8	1927.2	1928.6	1930.0
175°	1939.9	1937.6	1937.9	1938.2	1938.6	1938.9	1939.9	1941.6	1943.3	1944.9	1946.6
177.5°	1947.9	1946.0	1946.0	1946.0	1946.0	1946.0	1946.7	1948.0	1949.4	1950.7	1952.0
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1328.1	1331.9	1336.2	1344.3	1351.1	1354.1	1360.0	1364.3	1363.0	1368.9	1379.2
5°	1333.3	1347.7	1364.2	1381.2	1400.3	1416.3	1429.0	1441.8	1451.9	1464.1	1482.2
7.5°	1332.5	1358.0	1385.8	1416.3	1447.7	1474.8	1499.9	1525.4	1548.1	1572.9	1605.3
10°	1329.1	1363.1	1397.7	1437.6	1477.4	1515.2	1549.2	1581.2	1611.5	1643.9	1684.9
12.5°	1325.2	1364.4	1406.2	1454.1	1503.8	1549.2	1589.2	1635.2	1673.2	1715.0	1762.3
15°	1308.3	1361.0	1417.9	1480.1	1539.7	1600.8	1655.6	1712.0	1764.6	1814.6	1874.2
17.5°	1289.0	1349.7	1416.8	1490.3	1561.9	1636.2	1701.2	1772.3	1826.1	1893.2	1948.5
20°	1273.2	1338.6	1410.4	1492.9	1574.2	1656.7	1728.5	1800.8	1861.4	1929.0	1999.2
22.5°	1254.1	1325.9	1403.6	1489.0	1574.2	1664.3	1743.8	1815.7	1890.8	1966.8	2039.2
25°	1223.2	1297.7	1380.1	1473.7	1571.6	1663.6	1748.7	1838.0	1918.9	2001.3	2066.2
27.5°	1185.4	1263.5	1350.4	1447.0	1547.4	1641.7	1741.9	1837.1	1918.4	1997.8	2054.4
30°	1155.1	1237.6	1321.1	1418.9	1523.2	1624.2	1731.7	1826.9	1912.5	1983.8	2015.7
32.5°	1124.1	1202.3	1288.3	1387.5	1494.2	1603.0	1709.5	1806.9	1886.1	1928.9	1929.7
35°	1070.1	1143.4	1232.8	1330.1	1439.7	1557.8	1665.7	1761.4	1809.8	1813.6	1761.4
37.5°	1011.1	1078.5	1162.8	1260.2	1380.2	1497.7	1608.0	1671.8	1687.9	1633.8	1537.4
40°	969.0	1031.2	1112.6	1212.6	1331.7	1453.0	1553.5	1600.3	1583.3	1495.5	1388.1
42.5°	924.8	982.7	1061.1	1159.8	1279.4	1401.9	1487.5	1512.7	1467.6	1366.2	1240.5
45°	852.5	905.7	983.4	1082.8	1197.7	1312.6	1377.5	1364.7	1289.7	1169.5	1028.6
47.5°	777.3	828.7	898.6	990.6	1108.2	1207.4	1251.3	1212.8	1106.1	973.9	859.2
50°	727.6	780.2	844.6	932.3	1039.7	1135.5	1163.7	1105.2	986.6	859.4	754.1
52.5°	678.6	723.6	786.7	871.5	974.2	1055.1	1070.1	1002.6	880.2	766.3	672.9
55°	604.2	645.1	698.3	778.1	866.9	935.5	927.5	840.8	729.7	632.4	559.0
57.5°	532.2	563.0	612.1	686.9	764.9	810.9	781.8	707.9	604.3	524.6	462.7
60°	484.5	513.2	559.0	624.4	693.0	719.0	694.6	614.3	532.4	459.5	407.4
62.5°	439.4	464.7	504.1	564.8	620.2	635.7	609.5	539.4	465.6	403.3	360.2
65°	373.9	397.3	430.8	473.9	512.2	519.6	502.6	430.8	374.9	322.8	293.0
67.5°	314.4	329.7	355.9	393.1	413.5	417.8	384.9	339.8	290.6	258.6	236.1
70°	274.4	285.1	309.5	329.7	346.2	346.8	316.4	280.3	242.5	216.5	200.0
72.5°	235.7	245.9	264.4	278.3	290.9	286.8	259.0	230.5	200.0	180.3	168.1
75°	181.9	190.9	200.5	206.9	206.9	201.6	181.4	160.1	142.5	130.8	127.1
77.5°	132.2	139.7	142.9	141.9	140.0	131.7	118.9	105.0	98.7	93.2	90.4
80°	103.7	106.9	108.0	105.3	102.1	92.5	84.0	78.2	72.3	70.2	69.1
82.5°	76.9	79.7	76.9	77.6	70.6	62.8	58.1	56.1	53.6	52.8	51.7
85°	41.0	40.4	39.4	36.7	31.9	30.8	30.3	29.8	28.7	29.3	28.2
87.5°	15.7	15.1	14.2	14.5	15.1	14.8	15.8	16.3	16.8	16.8	18.1
90°	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2	37.2
92.5°	36.5	40.7	44.9	49.2	52.2	54.1	56.0	57.8	59.7	60.9	62.1
95°	93.5	96.5	99.5	102.5	105.2	107.6	109.9	112.3	114.6	115.6	116.6
97.5°	160.4	162.8	165.3	167.7	170.3	173.0	175.7	178.5	181.2	182.4	183.7
100°	212.4	213.8	215.1	216.5	218.6	221.7	224.7	227.7	230.7	231.4	232.0
102.5°	267.1	267.7	268.2	268.7	270.4	273.1	275.9	278.6	281.4	282.3	283.2
105°	351.7	352.0	352.3	352.7	353.5	354.8	356.2	357.5	358.9	359.9	360.9
107.5°	440.7	441.1	441.5	441.9	442.2	442.4	442.6	442.8	443.0	443.9	444.9
110°	501.3	501.9	502.6	503.3	503.5	503.1	502.8	502.4	502.1	501.4	500.8



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.5	563.6	563.7	563.9	563.6	563.0	562.4	561.8	561.2	561.1	560.9
115°	657.4	657.4	657.4	657.4	657.1	656.4	655.7	655.1	654.4	654.1	653.7
117.5°	746.3	746.6	746.9	747.2	747.1	746.6	746.1	745.6	745.2	744.0	742.9
120°	806.5	807.9	809.2	810.5	810.7	809.7	808.7	807.7	806.7	805.0	803.3
122.5°	867.2	867.8	868.3	868.8	868.9	868.4	867.9	867.5	867.0	865.9	864.7
125°	957.5	957.5	957.5	957.5	957.3	957.0	956.6	956.3	956.0	955.3	954.6
127.5°	1040.8	1041.8	1042.8	1043.8	1044.1	1043.5	1043.0	1042.5	1041.9	1041.2	1040.6
130°	1098.7	1099.7	1100.7	1101.7	1102.2	1102.2	1102.2	1102.2	1102.2	1101.6	1100.9
132.5°	1157.6	1158.3	1159.0	1159.8	1160.0	1159.7	1159.5	1159.2	1158.9	1158.3	1157.6
135°	1236.9	1238.9	1241.0	1243.0	1244.0	1244.0	1244.0	1244.0	1244.0	1243.3	1242.6
137.5°	1320.9	1321.8	1322.8	1323.7	1324.5	1325.0	1325.5	1326.1	1326.6	1325.7	1324.9
140°	1377.3	1378.0	1378.7	1379.3	1379.7	1379.7	1379.7	1379.7	1379.7	1379.3	1379.0
142.5°	1429.2	1429.9	1430.5	1431.2	1431.4	1431.1	1430.9	1430.6	1430.3	1430.3	1430.2
145°	1501.6	1503.0	1504.3	1505.7	1506.5	1506.8	1507.2	1507.5	1507.8	1507.5	1507.2
147.5°	1573.1	1574.7	1576.3	1577.9	1578.6	1578.3	1578.0	1577.8	1577.5	1577.2	1577.0
150°	1616.2	1617.6	1618.9	1620.3	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9	1620.9
152.5°	1656.7	1657.5	1658.3	1659.1	1659.7	1659.9	1660.2	1660.5	1660.7	1661.5	1662.3
155°	1718.9	1718.9	1718.9	1718.9	1718.8	1718.4	1718.1	1717.8	1717.4	1718.8	1720.1
157.5°	1771.4	1770.8	1770.2	1769.6	1769.3	1769.2	1769.1	1769.1	1769.0	1770.0	1771.0
160°	1803.0	1802.7	1802.4	1802.0	1801.7	1801.4	1801.0	1800.7	1800.4	1801.4	1802.4
162.5°	1831.5	1830.6	1829.7	1828.8	1828.2	1827.9	1827.6	1827.2	1826.9	1828.7	1830.5
165°	1870.2	1869.2	1868.2	1867.2	1866.4	1865.7	1865.0	1864.4	1863.7	1865.7	1867.7
167.5°	1899.7	1898.3	1896.9	1895.5	1894.8	1894.9	1894.9	1895.0	1895.1	1897.1	1899.1
170°	1916.3	1914.6	1912.9	1911.3	1910.6	1910.9	1911.3	1911.6	1911.9	1913.9	1916.0
172.5°	1928.6	1927.2	1925.8	1924.4	1923.7	1923.8	1923.9	1923.9	1924.0	1926.3	1928.6
175°	1944.9	1943.3	1941.6	1939.9	1938.9	1938.6	1938.2	1937.9	1937.6	1939.9	1942.3
177.5°	1950.7	1949.4	1948.0	1946.7	1946.0	1946.0	1946.0	1946.0	1946.0	1947.9	1949.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1384.7	1386.4	1387.7	1391.9	1392.3	1396.2	1392.3
5°	1499.2	1506.7	1518.4	1530.1	1531.2	1538.6	1525.3
7.5°	1627.7	1645.0	1655.7	1674.6	1682.1	1686.8	1679.1
10°	1716.2	1732.2	1760.4	1774.2	1788.0	1790.2	1783.8
12.5°	1801.8	1827.1	1849.3	1875.5	1874.8	1893.6	1886.7
15°	1915.7	1941.7	1972.6	2001.8	2012.5	2012.5	2021.0
17.5°	1996.9	2044.7	2076.6	2099.6	2124.7	2129.0	2126.1
20°	2051.8	2103.4	2137.5	2167.2	2184.3	2189.0	2189.0
22.5°	2092.7	2136.6	2169.8	2196.6	2210.6	2216.3	2214.6
25°	2121.0	2158.7	2178.9	2186.9	2190.6	2189.6	2179.5
27.5°	2082.2	2080.5	2067.8	2043.3	2024.9	2013.7	2001.0
30°	2008.2	1980.6	1948.7	1913.5	1868.3	1833.8	1823.1
32.5°	1898.0	1835.9	1781.9	1723.4	1674.8	1640.2	1625.7
35°	1684.9	1586.5	1506.2	1436.0	1384.9	1353.0	1342.4
37.5°	1431.9	1336.7	1237.3	1169.2	1126.9	1094.6	1082.6
40°	1271.1	1167.4	1080.7	1016.9	973.3	941.9	941.4
42.5°	1124.3	1025.3	943.7	897.7	850.7	830.0	829.9
45°	920.6	841.4	772.2	736.1	707.9	690.9	686.1
47.5°	762.2	696.7	650.6	621.8	598.8	588.0	581.0
50°	673.3	615.9	579.2	554.2	541.4	527.6	526.5
52.5°	599.3	552.9	524.3	504.0	487.8	479.5	479.7
55°	503.6	467.0	446.7	431.3	418.6	412.2	409.5
57.5°	424.3	396.8	382.1	367.9	362.5	357.5	356.1
60°	374.9	356.3	342.5	331.3	323.4	321.8	321.2
62.5°	334.1	314.6	305.1	296.4	290.6	288.1	287.2
65°	275.5	261.1	252.6	245.7	243.6	239.9	239.3
67.5°	222.1	213.5	207.8	203.1	200.2	200.0	200.0
70°	189.3	184.5	179.8	177.1	175.5	174.4	174.4
72.5°	161.3	157.7	153.8	152.4	152.1	151.0	150.6
75°	122.9	119.1	119.7	117.0	114.9	112.2	110.6
77.5°	87.1	84.5	83.9	83.6	81.8	81.5	82.3
80°	67.5	64.9	64.4	64.9	64.4	62.8	62.8
82.5°	51.4	49.1	48.6	48.3	47.8	48.3	47.4
85°	27.7	26.6	26.6	26.6	27.7	27.1	26.6
87.5°	17.6	17.6	18.3	18.0	18.1	17.8	18.4
90°	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	63.3	64.5	65.3	65.7	66.1	66.5	66.9
95°	117.6	118.6	119.1	119.1	119.1	119.1	119.1
97.5°	184.9	186.1	186.7	186.7	186.7	186.7	186.7
100°	232.7	233.4	233.7	233.7	233.7	233.7	233.7
102.5°	284.2	285.1	285.7	286.0	286.3	286.5	286.8
105°	361.9	362.9	363.9	364.9	365.9	366.9	367.9
107.5°	445.8	446.8	447.2	447.1	447.1	447.0	446.9
110°	500.1	499.4	499.6	500.6	501.6	502.6	503.6



TEST NUMBER: P333072

CATALOG NUMBER: S124RDIW-S795D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	560.8	560.7	560.7	560.9	561.1	561.3	561.5
115°	653.4	653.1	652.7	652.4	652.1	651.7	651.4
117.5°	741.8	740.6	739.7	739.0	738.4	737.7	737.0
120°	801.7	800.0	799.5	800.2	800.8	801.5	802.2
122.5°	863.6	862.5	861.3	860.1	858.9	857.7	856.5
125°	954.0	953.3	952.6	951.9	951.3	950.6	949.9
127.5°	1039.9	1039.2	1038.6	1038.1	1037.6	1037.0	1036.5
130°	1100.2	1099.5	1098.5	1097.2	1095.9	1094.5	1093.2
132.5°	1156.9	1156.2	1155.6	1155.1	1154.6	1154.0	1153.5
135°	1242.0	1241.3	1240.4	1239.4	1238.4	1237.4	1236.4
137.5°	1324.0	1323.1	1322.8	1323.0	1323.2	1323.4	1323.6
140°	1378.7	1378.3	1378.0	1377.7	1377.3	1377.0	1376.7
142.5°	1430.1	1430.1	1430.0	1429.9	1429.9	1429.8	1429.7
145°	1506.8	1506.5	1505.8	1504.8	1503.8	1502.8	1501.8
147.5°	1576.7	1576.4	1576.1	1575.8	1575.5	1575.1	1574.8
150°	1620.9	1620.9	1620.8	1620.4	1620.1	1619.8	1619.4
152.5°	1663.1	1663.9	1663.9	1663.0	1662.2	1661.3	1660.4
155°	1721.4	1722.8	1722.8	1721.4	1720.1	1718.8	1717.4
157.5°	1772.0	1773.0	1772.9	1771.8	1770.7	1769.5	1768.4
160°	1803.4	1804.4	1804.0	1802.4	1800.7	1799.0	1797.3
162.5°	1832.3	1834.1	1834.2	1832.5	1830.9	1829.2	1827.5
165°	1869.7	1871.7	1872.1	1870.7	1869.4	1868.0	1866.7
167.5°	1901.1	1903.1	1903.1	1901.0	1898.9	1896.8	1894.7
170°	1918.0	1920.0	1919.8	1917.5	1915.1	1912.8	1910.4
172.5°	1930.8	1933.1	1933.1	1930.7	1928.4	1926.0	1923.7
175°	1944.6	1947.0	1947.0	1944.6	1942.3	1939.9	1937.6
177.5°	1951.6	1953.5	1953.4	1951.2	1949.1	1947.0	1944.8
180°	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6	1949.6

(END OF REPORT)