

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332781-940

Luminaire Tested: **S124DIW-S795D770U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332781-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D770U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5898.7 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	45	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9243	9243	9243	9243
5°	10884	9266	8178	9266
10°	13032	9225	7363	9225
15°	15419	9132	6761	9132
20°	17169	9037	6225	9037
25°	17446	8897	5855	8897
30°	14845	8763	5738	8763
35°	11413	8544	5740	8544
40°	8897	8286	5848	8286
45°	7418	7900	5946	7900
50°	6528	7428	6148	7428
55°	5980	6861	6394	6861
60°	5604	6355	6692	6355
65°	5217	5788	6940	5788
70°	4770	5228	7098	5228
75°	4261	4601	7012	4601
80°	3575	3770	6792	3770
85°	2631	2723	6502	2723



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	1.9
10°-20°	343.8	5.8
20°-30°	545.1	9.2
30°-40°	606.7	10.3
40°-50°	552.2	9.4
50°-60°	451.3	7.7
60°-70°	322.2	5.5
70°-80°	177.4	3.0
80°-90°	51.0	0.9
90°-100°	30.3	0.5
100°-110°	193.0	3.3
110°-120°	369.2	6.3
120°-130°	468.7	7.9
130°-140°	501.4	8.5
140°-150°	468.9	7.9
150°-160°	378.1	6.4
160°-170°	243.9	4.1
170°-180°	84.1	1.4
0°-30°	1000.4	17.0
0°-40°	1607.1	27.2
0°-60°	2610.6	44.3
0°-90°	3161.2	53.6
90°-120°	592.4	10.0
90°-150°	2031.4	34.4
90°-180°	2737.0	46.4
0°-180°	5898.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1343	1143	1009	1143	1343	137
15°	1845	1093	809	1093	1845	521
25°	1959	999	657	999	1959	863
35°	1158	867	582	867	1158	735
45°	650	692	521	692	650	512
55°	425	488	454	488	425	384
65°	273	303	363	303	273	270
75°	137	148	225	148	137	145
85°	28	29	70	29	28	35
90°	20	2	20	2	20	10
95°	19	36	19	36	19	15
105°	189	199	189	199	189	165
115°	375	372	375	372	375	371
125°	527	523	527	523	527	469
135°	653	649	653	649	653	503
145°	752	748	752	748	752	470
155°	820	820	820	820	820	378
165°	861	865	861	865	861	243
175°	880	885	880	885	880	84
180°	885	885	885	885	885	



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1218.4	1218.1	1214.2	1213.5	1210.9	1207.5	1206.7	1200.6	1188.5	1182.8	1181.2
5°	1343.1	1352.5	1340.2	1337.8	1336.4	1320.8	1312.7	1303.2	1281.4	1268.6	1258.6
7.5°	1491.8	1492.9	1487.6	1483.2	1471.1	1457.4	1437.0	1415.1	1389.2	1362.1	1341.8
10°	1589.7	1593.5	1587.3	1586.4	1562.2	1547.0	1516.6	1491.0	1461.6	1428.9	1399.0
12.5°	1692.9	1687.6	1684.4	1664.1	1659.7	1632.0	1596.7	1570.3	1525.0	1487.4	1447.6
15°	1844.9	1834.4	1827.7	1799.7	1786.0	1747.6	1710.1	1681.2	1621.9	1565.5	1522.8
17.5°	1933.9	1944.4	1929.0	1917.5	1882.0	1855.0	1816.8	1756.0	1709.7	1639.6	1585.7
20°	1998.5	1999.4	1990.9	1979.1	1951.1	1916.9	1875.2	1808.7	1753.3	1683.6	1609.6
22.5°	2015.9	2016.2	2012.5	2001.4	1980.2	1952.6	1910.5	1855.0	1787.8	1712.0	1638.1
25°	1958.6	1956.8	1961.1	1973.4	1965.2	1956.8	1932.5	1891.3	1828.7	1748.6	1668.8
27.5°	1745.8	1758.9	1783.0	1813.3	1842.5	1864.8	1871.1	1862.6	1823.8	1757.9	1674.5
30°	1592.5	1608.6	1626.7	1657.0	1715.8	1749.5	1786.5	1814.5	1798.8	1746.1	1668.4
32.5°	1424.1	1428.1	1454.8	1489.3	1543.2	1608.0	1666.6	1723.4	1742.3	1714.7	1649.8
35°	1158.1	1164.8	1193.6	1227.8	1293.8	1373.0	1461.2	1539.9	1604.8	1630.9	1597.8
37.5°	945.0	964.1	984.5	1021.3	1079.3	1150.6	1242.2	1344.1	1440.9	1505.8	1516.8
40°	844.2	856.0	870.8	898.7	948.0	1018.2	1096.9	1213.6	1316.5	1409.4	1439.8
42.5°	764.5	771.4	780.4	805.7	843.3	913.1	985.0	1087.6	1191.0	1302.1	1352.9
45°	649.7	656.8	672.0	686.7	715.2	763.6	830.4	914.8	1018.7	1125.9	1219.8
47.5°	566.9	571.4	580.4	596.1	620.3	652.2	706.6	777.1	873.3	977.4	1077.5
50°	519.8	523.5	530.7	544.9	563.4	591.8	636.4	702.4	777.8	882.6	980.7
52.5°	482.6	484.1	489.4	499.0	513.7	537.6	574.2	628.7	698.8	792.3	890.1
55°	424.9	426.9	431.6	438.7	451.5	466.6	494.6	535.4	596.6	677.7	762.6
57.5°	377.5	378.8	382.8	385.6	396.1	408.4	430.0	459.1	505.4	574.2	650.0
60°	347.1	346.2	351.0	353.3	360.4	370.9	387.4	415.4	455.8	511.2	580.9
62.5°	317.5	316.2	320.2	323.3	327.4	336.4	349.9	371.8	404.6	454.7	515.0
65°	273.1	271.3	273.7	277.4	281.2	286.0	296.0	315.4	341.4	377.5	423.5
67.5°	228.5	230.6	231.0	232.8	235.1	241.5	248.3	262.1	280.4	309.3	348.3
70°	202.1	202.5	204.4	204.4	205.8	211.5	217.2	225.2	243.3	269.8	301.6
72.5°	175.5	177.5	176.7	178.3	179.2	183.1	187.3	194.9	210.3	230.0	256.8
75°	136.6	138.0	138.0	138.5	139.9	141.3	144.6	150.3	161.2	175.9	194.5
77.5°	99.6	99.8	100.4	102.2	102.2	104.4	106.9	111.5	116.8	126.9	138.2
80°	76.9	77.8	77.3	78.3	78.3	80.2	81.1	86.8	89.2	95.8	104.8
82.5°	56.4	57.2	57.2	58.5	59.3	59.7	61.0	63.2	65.6	71.5	75.2
85°	28.4	29.4	28.4	29.4	30.9	31.3	32.7	33.2	35.1	36.6	39.9
87.5°	12.3	13.4	13.4	13.6	14.4	14.6	14.8	14.3	15.6	15.8	17.1
90°	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3	15.4	14.5	13.4
92.5°	18.3	18.2	18.2	18.1	18.0	17.6	16.7	15.8	14.9	14.0	12.8
95°	19.2	19.1	18.9	18.7	18.6	18.1	17.2	16.3	15.4	14.5	14.4
97.5°	18.5	18.4	18.3	18.1	17.9	17.8	17.7	17.7	17.6	17.5	33.9
100°	18.5	18.4	18.3	18.1	17.9	19.1	21.6	24.2	26.7	29.2	49.4
102.5°	19.1	19.0	19.0	19.0	18.9	32.5	59.4	86.4	113.3	140.4	142.9
105°	188.7	193.9	199.2	204.6	209.8	211.8	210.4	209.2	207.9	206.5	205.8
107.5°	262.9	262.3	261.8	261.3	260.6	260.1	259.4	258.8	258.2	257.4	256.5
110°	295.2	294.8	294.4	293.9	293.5	293.1	292.7	292.5	292.2	291.9	291.1



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.5	327.0	326.4	325.8	325.3	325.0	325.1	325.1	325.2	325.3	324.9
115°	374.6	374.6	374.6	374.6	374.6	374.5	374.2	373.9	373.6	373.3	373.4
117.5°	422.6	422.6	422.7	422.8	422.8	422.8	422.9	422.9	423.0	423.1	422.8
120°	452.7	453.1	453.3	453.6	453.9	453.9	453.6	453.3	453.1	452.7	452.9
122.5°	482.4	482.7	483.0	483.3	483.6	483.7	483.5	483.3	483.1	483.0	482.7
125°	526.9	526.7	526.6	526.5	526.3	526.0	525.6	525.1	524.7	524.2	524.5
127.5°	566.0	566.1	566.1	566.3	566.4	566.5	566.6	566.7	566.8	566.9	566.1
130°	592.4	592.4	592.4	592.4	592.4	592.4	592.2	592.0	591.9	591.7	591.3
132.5°	616.8	616.9	617.0	617.2	617.2	617.2	617.1	616.9	616.8	616.6	616.1
135°	653.3	653.0	652.7	652.4	652.1	651.8	651.6	651.2	650.9	650.7	650.1
137.5°	684.6	684.7	684.7	684.8	684.9	684.7	684.5	684.1	683.8	683.5	682.9
140°	706.2	706.1	706.0	705.8	705.7	705.3	704.9	704.5	704.0	703.6	703.3
142.5°	724.2	724.2	724.2	724.2	724.2	724.0	723.6	723.4	723.0	722.6	722.5
145°	751.9	751.6	751.4	751.0	750.7	750.6	750.4	750.2	750.1	749.9	749.9
147.5°	774.8	774.7	774.5	774.4	774.3	774.1	774.0	773.8	773.7	773.6	773.7
150°	789.6	789.5	789.3	789.3	789.1	789.0	789.0	789.0	789.0	789.0	789.2
152.5°	802.4	802.5	802.5	802.6	802.7	802.6	802.4	802.2	801.9	801.7	802.0
155°	819.5	819.8	820.3	820.7	821.2	821.1	820.6	819.9	819.4	818.8	819.2
157.5°	833.7	834.5	835.3	836.1	836.8	836.8	836.1	835.3	834.5	833.7	834.2
160°	843.3	844.2	845.1	845.9	846.8	846.8	845.9	845.1	844.2	843.3	843.4
162.5°	850.7	851.7	852.7	853.7	854.7	854.7	853.8	853.0	852.1	851.2	851.3
165°	861.1	862.5	863.8	865.1	866.5	866.5	865.3	864.2	863.0	861.8	861.8
167.5°	869.0	870.4	871.9	873.3	874.9	874.9	873.6	872.4	871.0	869.8	869.9
170°	873.7	875.2	876.6	878.2	879.6	879.8	878.6	877.4	876.2	875.0	874.9
172.5°	876.4	878.0	879.6	881.1	882.7	882.9	881.7	880.6	879.4	878.2	878.1
175°	879.7	881.5	883.2	884.9	886.7	887.0	885.6	884.3	883.0	881.6	881.5
177.5°	881.8	883.2	884.6	886.0	887.4	887.7	886.7	885.8	884.8	883.9	883.7
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1181.6	1176.3	1172.5	1169.5	1161.2	1156.2	1152.4	1147.1	1141.0	1134.6	1126.6
5°	1248.7	1232.5	1220.8	1202.7	1185.6	1171.4	1156.7	1143.4	1127.3	1109.7	1096.9
7.5°	1319.2	1295.2	1264.4	1237.8	1207.8	1181.7	1158.4	1134.5	1109.6	1085.6	1063.5
10°	1364.0	1333.1	1299.0	1258.6	1220.8	1187.0	1155.7	1125.4	1096.0	1066.6	1041.4
12.5°	1412.1	1373.7	1323.2	1276.1	1233.6	1188.6	1150.8	1113.7	1078.2	1047.2	1017.9
15°	1476.8	1421.3	1363.0	1299.9	1243.9	1191.3	1139.6	1092.7	1052.8	1012.0	983.6
17.5°	1516.5	1447.9	1381.2	1315.3	1247.6	1181.2	1125.4	1071.2	1021.4	980.8	944.9
20°	1542.7	1474.4	1391.4	1325.5	1244.9	1176.6	1112.1	1051.9	999.7	956.5	919.5
22.5°	1565.5	1486.6	1403.6	1316.8	1236.5	1164.1	1093.5	1032.9	979.6	934.2	898.7
25°	1577.8	1487.2	1397.1	1310.8	1219.8	1133.9	1069.9	998.8	941.8	893.9	856.0
27.5°	1579.1	1482.3	1380.4	1284.4	1190.4	1110.5	1029.7	966.2	907.0	856.4	819.9
30°	1574.9	1474.0	1364.4	1260.5	1166.2	1079.4	1009.2	940.0	879.8	829.5	791.5
32.5°	1561.7	1456.5	1343.9	1233.9	1136.2	1051.3	978.8	913.0	854.3	804.8	765.0
35°	1523.3	1419.4	1299.4	1185.2	1085.0	999.3	933.8	866.9	808.2	761.2	722.7
37.5°	1463.2	1369.3	1247.3	1129.1	1030.8	944.6	879.8	819.3	766.2	718.5	679.2
40°	1410.9	1328.4	1206.0	1090.7	984.5	902.5	841.8	786.3	733.7	688.6	651.1
42.5°	1350.6	1278.6	1165.8	1043.7	941.3	858.9	799.7	749.8	700.3	658.6	621.2
45°	1243.0	1195.6	1089.3	976.5	869.8	792.0	735.6	692.0	650.2	609.4	578.1
47.5°	1119.3	1095.8	1006.4	899.2	797.9	721.2	672.3	632.0	595.4	560.9	533.2
50°	1036.3	1024.8	947.5	844.2	747.4	675.3	626.0	591.4	560.1	529.8	503.6
52.5°	954.3	953.9	884.2	789.5	700.0	630.5	581.6	549.3	522.2	497.5	474.0
55°	829.0	842.2	787.7	703.3	623.1	560.5	516.5	487.5	468.6	448.2	430.6
57.5°	713.9	735.9	691.0	616.6	549.7	492.0	453.7	431.9	411.7	399.4	386.6
60°	638.8	659.7	624.6	562.0	498.9	449.6	413.0	393.6	376.0	367.6	358.6
62.5°	572.0	590.7	564.6	506.6	451.8	404.5	373.6	354.9	343.0	333.8	327.8
65°	476.6	492.2	470.0	427.8	380.8	342.9	317.7	303.0	291.7	287.8	281.2
67.5°	385.3	399.5	387.4	351.6	314.0	285.2	265.6	251.5	244.7	241.4	236.7
70°	331.0	345.3	332.4	301.1	272.2	248.1	229.5	221.5	214.4	212.9	206.3
72.5°	285.1	294.8	282.0	257.5	232.7	212.4	198.0	189.6	185.9	183.3	179.8
75°	213.9	222.4	213.9	194.9	177.4	163.2	150.8	147.5	143.2	141.8	139.5
77.5°	151.4	158.8	152.2	140.4	127.2	116.3	109.7	105.4	104.4	101.9	103.1
80°	115.7	120.5	114.3	106.2	95.8	88.2	83.5	81.1	78.3	77.3	79.2
82.5°	83.1	85.2	82.0	76.6	68.8	63.9	60.7	58.0	57.4	57.6	57.6
85°	43.2	42.7	42.2	37.5	35.1	31.7	29.9	29.4	28.9	29.9	30.9
87.5°	16.9	17.0	16.4	14.6	13.1	11.7	11.0	10.3	11.0	11.7	12.4
90°	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0	3.6	5.3	6.9
92.5°	11.7	10.5	9.4	8.6	8.6	8.6	8.5	8.4	8.5	8.6	8.6
95°	14.3	14.1	14.0	16.4	21.4	26.4	31.4	36.4	31.4	26.4	21.4
97.5°	50.3	66.7	83.1	89.8	86.7	83.6	80.4	77.3	80.4	83.6	86.7
100°	69.7	90.1	110.3	119.1	116.5	113.9	111.2	108.5	111.2	113.9	116.5
102.5°	145.6	148.3	150.9	151.2	149.4	147.4	145.4	143.5	145.4	147.4	149.4
105°	205.0	204.3	203.6	202.8	201.9	201.0	200.1	199.2	200.1	201.0	201.9
107.5°	255.5	254.5	253.5	252.8	252.4	251.9	251.5	251.0	251.5	251.9	252.4
110°	290.2	289.3	288.4	287.7	287.3	286.9	286.4	286.0	286.4	286.9	287.3



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	324.4	324.0	323.6	323.0	322.2	321.5	320.7	319.9	320.7	321.5	322.2
115°	373.6	373.7	373.9	373.7	373.3	372.9	372.5	372.0	372.5	372.9	373.3
117.5°	422.4	422.1	421.8	421.3	420.7	420.2	419.5	419.0	419.5	420.2	420.7
120°	453.1	453.2	453.3	453.1	452.5	451.9	451.4	450.8	451.4	451.9	452.5
122.5°	482.5	482.3	482.1	481.8	481.4	481.1	480.7	480.5	480.7	481.1	481.4
125°	524.9	525.1	525.4	525.2	524.7	524.1	523.5	522.9	523.5	524.1	524.7
127.5°	565.5	564.8	564.2	563.7	563.6	563.5	563.3	563.1	563.3	563.5	563.6
130°	590.8	590.4	590.0	589.7	589.5	589.4	589.2	589.1	589.2	589.4	589.5
132.5°	615.5	614.9	614.4	613.9	613.7	613.5	613.2	613.0	613.2	613.5	613.7
135°	649.4	648.9	648.3	648.1	648.2	648.4	648.5	648.6	648.5	648.4	648.2
137.5°	682.2	681.5	680.9	680.6	680.5	680.5	680.4	680.3	680.4	680.5	680.5
140°	703.0	702.8	702.4	702.1	701.9	701.5	701.2	701.0	701.2	701.5	701.9
142.5°	722.3	722.1	721.9	721.6	721.0	720.6	720.1	719.5	720.1	720.6	721.0
145°	749.9	749.9	749.9	749.8	749.3	748.9	748.4	748.0	748.4	748.9	749.3
147.5°	773.9	774.1	774.2	773.9	773.0	772.2	771.4	770.6	771.4	772.2	773.0
150°	789.3	789.4	789.6	789.3	788.8	788.2	787.6	787.0	787.6	788.2	788.8
152.5°	802.3	802.5	802.7	802.6	802.2	801.7	801.2	800.8	801.2	801.7	802.2
155°	819.7	820.1	820.6	820.7	820.6	820.4	820.3	820.1	820.3	820.4	820.6
157.5°	834.7	835.3	835.7	836.1	836.2	836.2	836.3	836.4	836.3	836.2	836.2
160°	843.6	843.7	843.8	844.2	844.6	845.1	845.4	845.9	845.4	845.1	844.6
162.5°	851.5	851.7	851.8	852.1	852.7	853.3	853.8	854.3	853.8	853.3	852.7
165°	861.8	861.8	861.8	862.2	862.9	863.6	864.3	865.1	864.3	863.6	862.9
167.5°	870.0	870.0	870.1	870.5	871.3	872.1	872.8	873.6	872.8	872.1	871.3
170°	874.8	874.6	874.4	874.9	875.7	876.6	877.4	878.3	877.4	876.6	875.7
172.5°	877.9	877.8	877.6	878.0	878.9	879.8	880.7	881.5	880.7	879.8	878.9
175°	881.4	881.2	881.1	881.5	882.3	883.2	884.0	884.9	884.0	883.2	882.3
177.5°	883.4	883.2	883.0	883.2	884.0	884.9	885.7	886.5	885.7	884.9	884.0
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1122.8	1119.5	1114.5	1107.7	1102.0	1095.9	1094.4	1092.1	1096.6	1092.9	1091.7
5°	1086.0	1076.0	1063.3	1048.6	1040.0	1027.7	1025.3	1020.6	1015.8	1015.4	1010.6
7.5°	1047.0	1032.4	1015.7	1000.7	986.8	973.3	964.6	962.6	955.6	951.5	946.8
10°	1022.0	1004.0	984.5	970.3	954.2	940.0	930.0	924.3	919.5	914.4	909.6
12.5°	992.4	973.2	957.3	941.8	922.7	911.9	895.5	885.6	884.7	884.8	872.4
15°	958.0	939.0	914.4	892.5	882.1	861.2	852.2	840.8	833.7	826.6	820.9
17.5°	918.6	895.0	875.7	850.7	830.8	814.2	802.4	795.5	784.8	774.7	767.4
20°	893.9	868.8	848.5	821.9	800.0	779.6	769.7	760.2	752.2	743.6	735.6
22.5°	868.9	842.7	817.7	791.9	771.6	750.1	740.5	727.5	719.9	715.2	707.1
25°	829.5	801.0	772.6	747.9	727.0	708.0	695.3	685.3	676.7	673.0	667.7
27.5°	786.6	758.3	730.8	702.8	679.1	665.4	655.1	647.6	642.7	637.7	635.3
30°	759.3	729.9	700.4	674.4	652.6	638.8	629.3	624.1	620.3	618.0	615.5
32.5°	731.6	702.6	671.6	647.8	628.3	616.1	608.9	603.6	601.7	600.8	600.0
35°	687.2	657.8	629.3	608.0	589.5	584.8	578.5	575.8	574.8	578.1	579.5
37.5°	644.2	616.9	590.8	570.1	557.9	551.0	548.8	549.0	552.4	555.4	558.7
40°	616.5	590.0	565.3	547.2	535.9	531.6	530.7	533.1	536.8	540.2	543.9
42.5°	589.6	563.4	541.0	524.1	516.2	512.3	512.8	515.2	520.5	524.6	530.3
45°	547.8	525.9	504.1	490.4	483.8	484.6	484.6	488.9	494.2	500.3	506.5
47.5°	508.4	486.4	468.4	456.9	453.4	452.6	455.3	460.8	468.3	476.0	484.6
50°	481.8	460.9	445.3	434.9	431.1	432.5	436.3	441.5	450.5	460.0	469.0
52.5°	454.9	436.0	421.4	411.7	409.1	411.6	415.4	423.7	431.6	441.8	452.7
55°	413.0	396.9	385.6	378.4	377.5	378.9	383.2	392.2	403.6	416.4	426.9
57.5°	371.4	357.9	347.5	342.6	343.0	344.4	351.4	362.1	374.3	387.9	401.4
60°	343.4	331.0	322.5	318.7	319.1	322.0	330.6	340.5	355.7	369.0	383.2
62.5°	316.8	305.9	297.8	294.4	293.7	300.0	308.2	318.5	333.7	348.5	363.8
65°	274.1	265.6	259.0	257.1	258.5	263.2	273.7	287.4	300.2	315.8	332.0
67.5°	232.4	225.3	220.8	221.7	223.4	230.4	239.2	250.9	265.5	281.7	297.7
70°	205.8	199.2	195.4	195.8	198.7	207.2	214.8	226.7	242.4	259.0	272.2
72.5°	178.5	174.2	170.8	172.7	175.6	181.5	190.9	202.8	216.5	232.0	246.0
75°	137.1	137.1	135.2	136.6	140.9	146.5	153.6	165.9	179.8	192.1	203.5
77.5°	101.7	100.7	101.8	103.6	106.0	112.8	120.9	129.7	140.1	152.4	161.8
80°	77.8	78.3	80.6	83.5	84.4	89.6	98.2	106.2	114.3	124.8	133.8
82.5°	58.4	58.9	60.1	63.8	64.6	70.3	75.8	83.8	91.1	98.2	105.7
85°	31.7	31.7	34.2	35.6	37.9	41.7	45.0	49.8	56.4	61.2	68.3
87.5°	13.8	14.1	15.9	16.9	18.2	20.3	21.3	25.7	27.4	29.4	33.0
90°	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3	17.2	18.1	18.6
92.5°	8.6	9.4	10.5	11.7	12.8	14.0	14.9	15.8	16.7	17.6	18.0
95°	16.4	14.0	14.1	14.3	14.4	14.5	15.4	16.3	17.2	18.1	18.6
97.5°	89.8	83.1	66.7	50.3	33.9	17.5	17.6	17.7	17.7	17.8	17.9
100°	119.1	110.3	90.1	69.7	49.4	29.2	26.7	24.2	21.6	19.1	17.9
102.5°	151.2	150.9	148.3	145.6	142.9	140.4	113.3	86.4	59.4	32.5	18.9
105°	202.8	203.6	204.3	205.0	205.8	206.5	207.9	209.2	210.4	211.8	209.8
107.5°	252.8	253.5	254.5	255.5	256.5	257.4	258.2	258.8	259.4	260.1	260.6
110°	287.7	288.4	289.3	290.2	291.1	291.9	292.2	292.5	292.7	293.1	293.5



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	323.0	323.6	324.0	324.4	324.9	325.3	325.2	325.1	325.1	325.0	325.3
115°	373.7	373.9	373.7	373.6	373.4	373.3	373.6	373.9	374.2	374.5	374.6
117.5°	421.3	421.8	422.1	422.4	422.8	423.1	423.0	422.9	422.9	422.8	422.8
120°	453.1	453.3	453.2	453.1	452.9	452.7	453.1	453.3	453.6	453.9	453.9
122.5°	481.8	482.1	482.3	482.5	482.7	483.0	483.1	483.3	483.5	483.7	483.6
125°	525.2	525.4	525.1	524.9	524.5	524.2	524.7	525.1	525.6	526.0	526.3
127.5°	563.7	564.2	564.8	565.5	566.1	566.9	566.8	566.7	566.6	566.5	566.4
130°	589.7	590.0	590.4	590.8	591.3	591.7	591.9	592.0	592.2	592.4	592.4
132.5°	613.9	614.4	614.9	615.5	616.1	616.6	616.8	616.9	617.1	617.2	617.2
135°	648.1	648.3	648.9	649.4	650.1	650.7	650.9	651.2	651.6	651.8	652.1
137.5°	680.6	680.9	681.5	682.2	682.9	683.5	683.8	684.1	684.5	684.7	684.9
140°	702.1	702.4	702.8	703.0	703.3	703.6	704.0	704.5	704.9	705.3	705.7
142.5°	721.6	721.9	722.1	722.3	722.5	722.6	723.0	723.4	723.6	724.0	724.2
145°	749.8	749.9	749.9	749.9	749.9	749.9	750.1	750.2	750.4	750.6	750.7
147.5°	773.9	774.2	774.1	773.9	773.7	773.6	773.7	773.8	774.0	774.1	774.3
150°	789.3	789.6	789.4	789.3	789.2	789.0	789.0	789.0	789.0	789.0	789.1
152.5°	802.6	802.7	802.5	802.3	802.0	801.7	801.9	802.2	802.4	802.6	802.7
155°	820.7	820.6	820.1	819.7	819.2	818.8	819.4	819.9	820.6	821.1	821.2
157.5°	836.1	835.7	835.3	834.7	834.2	833.7	834.5	835.3	836.1	836.8	836.8
160°	844.2	843.8	843.7	843.6	843.4	843.3	844.2	845.1	845.9	846.8	846.8
162.5°	852.1	851.8	851.7	851.5	851.3	851.2	852.1	853.0	853.8	854.7	854.7
165°	862.2	861.8	861.8	861.8	861.8	861.8	863.0	864.2	865.3	866.5	866.5
167.5°	870.5	870.1	870.0	870.0	869.9	869.8	871.0	872.4	873.6	874.9	874.9
170°	874.9	874.4	874.6	874.8	874.9	875.0	876.2	877.4	878.6	879.8	879.6
172.5°	878.0	877.6	877.8	877.9	878.1	878.2	879.4	880.6	881.7	882.9	882.7
175°	881.5	881.1	881.2	881.4	881.5	881.6	883.0	884.3	885.6	887.0	886.7
177.5°	883.2	883.0	883.2	883.4	883.7	883.9	884.8	885.8	886.7	887.7	887.4
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1090.9	1090.2	1087.5	1087.2	1087.5	1090.2	1090.9	1091.7	1092.9	1096.6	1092.1
5°	1007.8	1005.4	1004.0	1009.2	1004.0	1005.4	1007.8	1010.6	1015.4	1015.8	1020.6
7.5°	945.0	943.2	939.0	937.7	939.0	943.2	945.0	946.8	951.5	955.6	962.6
10°	904.8	902.9	899.2	898.2	899.2	902.9	904.8	909.6	914.4	919.5	924.3
12.5°	866.1	862.4	861.6	862.6	861.6	862.4	866.1	872.4	884.8	884.7	885.6
15°	814.8	812.9	807.6	809.0	807.6	812.9	814.8	820.9	826.6	833.7	840.8
17.5°	764.1	761.8	755.5	761.1	755.5	761.8	764.1	767.4	774.7	784.8	795.5
20°	732.3	728.4	725.1	724.6	725.1	728.4	732.3	735.6	743.6	752.2	760.2
22.5°	701.9	698.5	698.2	695.1	698.2	698.5	701.9	707.1	715.2	719.9	727.5
25°	664.0	660.7	659.7	657.3	659.7	660.7	664.0	667.7	673.0	676.7	685.3
27.5°	634.8	633.2	631.5	632.2	631.5	633.2	634.8	635.3	637.7	642.7	647.6
30°	617.0	616.5	615.5	615.5	615.5	616.5	617.0	615.5	618.0	620.3	624.1
32.5°	602.2	602.1	602.7	602.7	602.7	602.1	602.2	600.0	600.8	601.7	603.6
35°	581.4	582.8	583.8	582.4	583.8	582.8	581.4	579.5	578.1	574.8	575.8
37.5°	562.7	564.1	565.4	567.0	565.4	564.1	562.7	558.7	555.4	552.4	549.0
40°	548.2	551.5	552.5	554.9	552.5	551.5	548.2	543.9	540.2	536.8	533.1
42.5°	534.6	538.2	540.7	541.2	540.7	538.2	534.6	530.3	524.6	520.5	515.2
45°	513.6	517.4	520.8	520.8	520.8	517.4	513.6	506.5	500.3	494.2	488.9
47.5°	491.9	497.4	500.7	501.6	500.7	497.4	491.9	484.6	476.0	468.3	460.8
50°	477.1	483.8	487.1	489.5	487.1	483.8	477.1	469.0	460.0	450.5	441.5
52.5°	462.7	469.3	473.8	475.0	473.8	469.3	462.7	452.7	441.8	431.6	423.7
55°	437.7	447.2	452.5	454.3	452.5	447.2	437.7	426.9	416.4	403.6	392.2
57.5°	414.2	422.9	429.0	430.4	429.0	422.9	414.2	401.4	387.9	374.3	362.1
60°	396.0	405.5	413.0	414.5	413.0	405.5	396.0	383.2	369.0	355.7	340.5
62.5°	377.4	387.3	394.1	397.8	394.1	387.3	377.4	363.8	348.5	333.7	318.5
65°	345.3	355.2	361.9	363.3	361.9	355.2	345.3	332.0	315.8	300.2	287.4
67.5°	310.1	320.1	324.5	327.3	324.5	320.1	310.1	297.7	281.7	265.5	250.9
70°	285.5	293.6	298.3	300.7	298.3	293.6	285.5	272.2	259.0	242.4	226.7
72.5°	257.4	265.8	271.3	271.8	271.3	265.8	257.4	246.0	232.0	216.5	202.8
75°	214.4	221.9	224.8	224.8	224.8	221.9	214.4	203.5	192.1	179.8	165.9
77.5°	169.7	173.6	177.2	177.9	177.2	173.6	169.7	161.8	152.4	140.1	129.7
80°	140.9	143.2	146.1	146.1	146.1	143.2	140.9	133.8	124.8	114.3	106.2
82.5°	111.3	113.2	116.1	115.7	116.1	113.2	111.3	105.7	98.2	91.1	83.8
85°	67.3	71.6	71.2	70.2	71.2	71.6	67.3	68.3	61.2	56.4	49.8
87.5°	34.2	34.6	35.8	36.6	35.8	34.6	34.2	33.0	29.4	27.4	25.7
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3
92.5°	18.1	18.2	18.2	18.3	18.2	18.2	18.1	18.0	17.6	16.7	15.8
95°	18.7	18.9	19.1	19.2	19.1	18.9	18.7	18.6	18.1	17.2	16.3
97.5°	18.1	18.3	18.4	18.5	18.4	18.3	18.1	17.9	17.8	17.7	17.7
100°	18.1	18.3	18.4	18.5	18.4	18.3	18.1	17.9	19.1	21.6	24.2
102.5°	19.0	19.0	19.0	19.1	19.0	19.0	19.0	18.9	32.5	59.4	86.4
105°	204.6	199.2	193.9	188.7	193.9	199.2	204.6	209.8	211.8	210.4	209.2
107.5°	261.3	261.8	262.3	262.9	262.3	261.8	261.3	260.6	260.1	259.4	258.8
110°	293.9	294.4	294.8	295.2	294.8	294.4	293.9	293.5	293.1	292.7	292.5



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	325.8	326.4	327.0	327.5	327.0	326.4	325.8	325.3	325.0	325.1	325.1
115°	374.6	374.6	374.6	374.6	374.6	374.6	374.6	374.6	374.5	374.2	373.9
117.5°	422.8	422.7	422.6	422.6	422.6	422.7	422.8	422.8	422.8	422.9	422.9
120°	453.6	453.3	453.1	452.7	453.1	453.3	453.6	453.9	453.9	453.6	453.3
122.5°	483.3	483.0	482.7	482.4	482.7	483.0	483.3	483.6	483.7	483.5	483.3
125°	526.5	526.6	526.7	526.9	526.7	526.6	526.5	526.3	526.0	525.6	525.1
127.5°	566.3	566.1	566.1	566.0	566.1	566.1	566.3	566.4	566.5	566.6	566.7
130°	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.2	592.0
132.5°	617.2	617.0	616.9	616.8	616.9	617.0	617.2	617.2	617.2	617.1	616.9
135°	652.4	652.7	653.0	653.3	653.0	652.7	652.4	652.1	651.8	651.6	651.2
137.5°	684.8	684.7	684.7	684.6	684.7	684.7	684.8	684.9	684.7	684.5	684.1
140°	705.8	706.0	706.1	706.2	706.1	706.0	705.8	705.7	705.3	704.9	704.5
142.5°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.6	723.4
145°	751.0	751.4	751.6	751.9	751.6	751.4	751.0	750.7	750.6	750.4	750.2
147.5°	774.4	774.5	774.7	774.8	774.7	774.5	774.4	774.3	774.1	774.0	773.8
150°	789.3	789.3	789.5	789.6	789.5	789.3	789.3	789.1	789.0	789.0	789.0
152.5°	802.6	802.5	802.5	802.4	802.5	802.5	802.6	802.7	802.6	802.4	802.2
155°	820.7	820.3	819.8	819.5	819.8	820.3	820.7	821.2	821.1	820.6	819.9
157.5°	836.1	835.3	834.5	833.7	834.5	835.3	836.1	836.8	836.8	836.1	835.3
160°	845.9	845.1	844.2	843.3	844.2	845.1	845.9	846.8	846.8	845.9	845.1
162.5°	853.7	852.7	851.7	850.7	851.7	852.7	853.7	854.7	854.7	853.8	853.0
165°	865.1	863.8	862.5	861.1	862.5	863.8	865.1	866.5	866.5	865.3	864.2
167.5°	873.3	871.9	870.4	869.0	870.4	871.9	873.3	874.9	874.9	873.6	872.4
170°	878.2	876.6	875.2	873.7	875.2	876.6	878.2	879.6	879.8	878.6	877.4
172.5°	881.1	879.6	878.0	876.4	878.0	879.6	881.1	882.7	882.9	881.7	880.6
175°	884.9	883.2	881.5	879.7	881.5	883.2	884.9	886.7	887.0	885.6	884.3
177.5°	886.0	884.6	883.2	881.8	883.2	884.6	886.0	887.4	887.7	886.7	885.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1094.4	1095.9	1102.0	1107.7	1114.5	1119.5	1122.8	1126.6	1134.6	1141.0	1147.1
5°	1025.3	1027.7	1040.0	1048.6	1063.3	1076.0	1086.0	1096.9	1109.7	1127.3	1143.4
7.5°	964.6	973.3	986.8	1000.7	1015.7	1032.4	1047.0	1063.5	1085.6	1109.6	1134.5
10°	930.0	940.0	954.2	970.3	984.5	1004.0	1022.0	1041.4	1066.6	1096.0	1125.4
12.5°	895.5	911.9	922.7	941.8	957.3	973.2	992.4	1017.9	1047.2	1078.2	1113.7
15°	852.2	861.2	882.1	892.5	914.4	939.0	958.0	983.6	1012.0	1052.8	1092.7
17.5°	802.4	814.2	830.8	850.7	875.7	895.0	918.6	944.9	980.8	1021.4	1071.2
20°	769.7	779.6	800.0	821.9	848.5	868.8	893.9	919.5	956.5	999.7	1051.9
22.5°	740.5	750.1	771.6	791.9	817.7	842.7	868.9	898.7	934.2	979.6	1032.9
25°	695.3	708.0	727.0	747.9	772.6	801.0	829.5	856.0	893.9	941.8	998.8
27.5°	655.1	665.4	679.1	702.8	730.8	758.3	786.6	819.9	856.4	907.0	966.2
30°	629.3	638.8	652.6	674.4	700.4	729.9	759.3	791.5	829.5	879.8	940.0
32.5°	608.9	616.1	628.3	647.8	671.6	702.6	731.6	765.0	804.8	854.3	913.0
35°	578.5	584.8	589.5	608.0	629.3	657.8	687.2	722.7	761.2	808.2	866.9
37.5°	548.8	551.0	557.9	570.1	590.8	616.9	644.2	679.2	718.5	766.2	819.3
40°	530.7	531.6	535.9	547.2	565.3	590.0	616.5	651.1	688.6	733.7	786.3
42.5°	512.8	512.3	516.2	524.1	541.0	563.4	589.6	621.2	658.6	700.3	749.8
45°	484.6	484.6	483.8	490.4	504.1	525.9	547.8	578.1	609.4	650.2	692.0
47.5°	455.3	452.6	453.4	456.9	468.4	486.4	508.4	533.2	560.9	595.4	632.0
50°	436.3	432.5	431.1	434.9	445.3	460.9	481.8	503.6	529.8	560.1	591.4
52.5°	415.4	411.6	409.1	411.7	421.4	436.0	454.9	474.0	497.5	522.2	549.3
55°	383.2	378.9	377.5	378.4	385.6	396.9	413.0	430.6	448.2	468.6	487.5
57.5°	351.4	344.4	343.0	342.6	347.5	357.9	371.4	386.6	399.4	411.7	431.9
60°	330.6	322.0	319.1	318.7	322.5	331.0	343.4	358.6	367.6	376.0	393.6
62.5°	308.2	300.0	293.7	294.4	297.8	305.9	316.8	327.8	333.8	343.0	354.9
65°	273.7	263.2	258.5	257.1	259.0	265.6	274.1	281.2	287.8	291.7	303.0
67.5°	239.2	230.4	223.4	221.7	220.8	225.3	232.4	236.7	241.4	244.7	251.5
70°	214.8	207.2	198.7	195.8	195.4	199.2	205.8	206.3	212.9	214.4	221.5
72.5°	190.9	181.5	175.6	172.7	170.8	174.2	178.5	179.8	183.3	185.9	189.6
75°	153.6	146.5	140.9	136.6	135.2	137.1	137.1	139.5	141.8	143.2	147.5
77.5°	120.9	112.8	106.0	103.6	101.8	100.7	101.7	103.1	101.9	104.4	105.4
80°	98.2	89.6	84.4	83.5	80.6	78.3	77.8	79.2	77.3	78.3	81.1
82.5°	75.8	70.3	64.6	63.8	60.1	58.9	58.4	57.6	57.6	57.4	58.0
85°	45.0	41.7	37.9	35.6	34.2	31.7	31.7	30.9	29.9	28.9	29.4
87.5°	21.3	20.3	18.2	16.9	15.9	14.1	13.8	12.4	11.7	11.0	10.3
90°	15.4	14.5	13.4	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0
92.5°	14.9	14.0	12.8	11.7	10.5	9.4	8.6	8.6	8.6	8.5	8.4
95°	15.4	14.5	14.4	14.3	14.1	14.0	16.4	21.4	26.4	31.4	36.4
97.5°	17.6	17.5	33.9	50.3	66.7	83.1	89.8	86.7	83.6	80.4	77.3
100°	26.7	29.2	49.4	69.7	90.1	110.3	119.1	116.5	113.9	111.2	108.5
102.5°	113.3	140.4	142.9	145.6	148.3	150.9	151.2	149.4	147.4	145.4	143.5
105°	207.9	206.5	205.8	205.0	204.3	203.6	202.8	201.9	201.0	200.1	199.2
107.5°	258.2	257.4	256.5	255.5	254.5	253.5	252.8	252.4	251.9	251.5	251.0
110°	292.2	291.9	291.1	290.2	289.3	288.4	287.7	287.3	286.9	286.4	286.0



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	325.2	325.3	324.9	324.4	324.0	323.6	323.0	322.2	321.5	320.7	319.9
115°	373.6	373.3	373.4	373.6	373.7	373.9	373.7	373.3	372.9	372.5	372.0
117.5°	423.0	423.1	422.8	422.4	422.1	421.8	421.3	420.7	420.2	419.5	419.0
120°	453.1	452.7	452.9	453.1	453.2	453.3	453.1	452.5	451.9	451.4	450.8
122.5°	483.1	483.0	482.7	482.5	482.3	482.1	481.8	481.4	481.1	480.7	480.5
125°	524.7	524.2	524.5	524.9	525.1	525.4	525.2	524.7	524.1	523.5	522.9
127.5°	566.8	566.9	566.1	565.5	564.8	564.2	563.7	563.6	563.5	563.3	563.1
130°	591.9	591.7	591.3	590.8	590.4	590.0	589.7	589.5	589.4	589.2	589.1
132.5°	616.8	616.6	616.1	615.5	614.9	614.4	613.9	613.7	613.5	613.2	613.0
135°	650.9	650.7	650.1	649.4	648.9	648.3	648.1	648.2	648.4	648.5	648.6
137.5°	683.8	683.5	682.9	682.2	681.5	680.9	680.6	680.5	680.5	680.4	680.3
140°	704.0	703.6	703.3	703.0	702.8	702.4	702.1	701.9	701.5	701.2	701.0
142.5°	723.0	722.6	722.5	722.3	722.1	721.9	721.6	721.0	720.6	720.1	719.5
145°	750.1	749.9	749.9	749.9	749.9	749.9	749.8	749.3	748.9	748.4	748.0
147.5°	773.7	773.6	773.7	773.9	774.1	774.2	773.9	773.0	772.2	771.4	770.6
150°	789.0	789.0	789.2	789.3	789.4	789.6	789.3	788.8	788.2	787.6	787.0
152.5°	801.9	801.7	802.0	802.3	802.5	802.7	802.6	802.2	801.7	801.2	800.8
155°	819.4	818.8	819.2	819.7	820.1	820.6	820.7	820.6	820.4	820.3	820.1
157.5°	834.5	833.7	834.2	834.7	835.3	835.7	836.1	836.2	836.2	836.3	836.4
160°	844.2	843.3	843.4	843.6	843.7	843.8	844.2	844.6	845.1	845.4	845.9
162.5°	852.1	851.2	851.3	851.5	851.7	851.8	852.1	852.7	853.3	853.8	854.3
165°	863.0	861.8	861.8	861.8	861.8	861.8	862.2	862.9	863.6	864.3	865.1
167.5°	871.0	869.8	869.9	870.0	870.0	870.1	870.5	871.3	872.1	872.8	873.6
170°	876.2	875.0	874.9	874.8	874.6	874.4	874.9	875.7	876.6	877.4	878.3
172.5°	879.4	878.2	878.1	877.9	877.8	877.6	878.0	878.9	879.8	880.7	881.5
175°	883.0	881.6	881.5	881.4	881.2	881.1	881.5	882.3	883.2	884.0	884.9
177.5°	884.8	883.9	883.7	883.4	883.2	883.0	883.2	884.0	884.9	885.7	886.5
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1152.4	1156.2	1161.2	1169.5	1172.5	1176.3	1181.6	1181.2	1182.8	1188.5	1200.6
5°	1156.7	1171.4	1185.6	1202.7	1220.8	1232.5	1248.7	1258.6	1268.6	1281.4	1303.2
7.5°	1158.4	1181.7	1207.8	1237.8	1264.4	1295.2	1319.2	1341.8	1362.1	1389.2	1415.1
10°	1155.7	1187.0	1220.8	1258.6	1299.0	1333.1	1364.0	1399.0	1428.9	1461.6	1491.0
12.5°	1150.8	1188.6	1233.6	1276.1	1323.2	1373.7	1412.1	1447.6	1487.4	1525.0	1570.3
15°	1139.6	1191.3	1243.9	1299.9	1363.0	1421.3	1476.8	1522.8	1565.5	1621.9	1681.2
17.5°	1125.4	1181.2	1247.6	1315.3	1381.2	1447.9	1516.5	1585.7	1639.6	1709.7	1756.0
20°	1112.1	1176.6	1244.9	1325.5	1391.4	1474.4	1542.7	1609.6	1683.6	1753.3	1808.7
22.5°	1093.5	1164.1	1236.5	1316.8	1403.6	1486.6	1565.5	1638.1	1712.0	1787.8	1855.0
25°	1069.9	1133.9	1219.8	1310.8	1397.1	1487.2	1577.8	1668.8	1748.6	1828.7	1891.3
27.5°	1029.7	1110.5	1190.4	1284.4	1380.4	1482.3	1579.1	1674.5	1757.9	1823.8	1862.6
30°	1009.2	1079.4	1166.2	1260.5	1364.4	1474.0	1574.9	1668.4	1746.1	1798.8	1814.5
32.5°	978.8	1051.3	1136.2	1233.9	1343.9	1456.5	1561.7	1649.8	1714.7	1742.3	1723.4
35°	933.8	999.3	1085.0	1185.2	1299.4	1419.4	1523.3	1597.8	1630.9	1604.8	1539.9
37.5°	879.8	944.6	1030.8	1129.1	1247.3	1369.3	1463.2	1516.8	1505.8	1440.9	1344.1
40°	841.8	902.5	984.5	1090.7	1206.0	1328.4	1410.9	1439.8	1409.4	1316.5	1213.6
42.5°	799.7	858.9	941.3	1043.7	1165.8	1278.6	1350.6	1352.9	1302.1	1191.0	1087.6
45°	735.6	792.0	869.8	976.5	1089.3	1195.6	1243.0	1219.8	1125.9	1018.7	914.8
47.5°	672.3	721.2	797.9	899.2	1006.4	1095.8	1119.3	1077.5	977.4	873.3	777.1
50°	626.0	675.3	747.4	844.2	947.5	1024.8	1036.3	980.7	882.6	777.8	702.4
52.5°	581.6	630.5	700.0	789.5	884.2	953.9	954.3	890.1	792.3	698.8	628.7
55°	516.5	560.5	623.1	703.3	787.7	842.2	829.0	762.6	677.7	596.6	535.4
57.5°	453.7	492.0	549.7	616.6	691.0	735.9	713.9	650.0	574.2	505.4	459.1
60°	413.0	449.6	498.9	562.0	624.6	659.7	638.8	580.9	511.2	455.8	415.4
62.5°	373.6	404.5	451.8	506.6	564.6	590.7	572.0	515.0	454.7	404.6	371.8
65°	317.7	342.9	380.8	427.8	470.0	492.2	476.6	423.5	377.5	341.4	315.4
67.5°	265.6	285.2	314.0	351.6	387.4	399.5	385.3	348.3	309.3	280.4	262.1
70°	229.5	248.1	272.2	301.1	332.4	345.3	331.0	301.6	269.8	243.3	225.2
72.5°	198.0	212.4	232.7	257.5	282.0	294.8	285.1	256.8	230.0	210.3	194.9
75°	150.8	163.2	177.4	194.9	213.9	222.4	213.9	194.5	175.9	161.2	150.3
77.5°	109.7	116.3	127.2	140.4	152.2	158.8	151.4	138.2	126.9	116.8	111.5
80°	83.5	88.2	95.8	106.2	114.3	120.5	115.7	104.8	95.8	89.2	86.8
82.5°	60.7	63.9	68.8	76.6	82.0	85.2	83.1	75.2	71.5	65.6	63.2
85°	29.9	31.7	35.1	37.5	42.2	42.7	43.2	39.9	36.6	35.1	33.2
87.5°	11.0	11.7	13.1	14.6	16.4	17.0	16.9	17.1	15.8	15.6	14.3
90°	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3
92.5°	8.5	8.6	8.6	8.6	9.4	10.5	11.7	12.8	14.0	14.9	15.8
95°	31.4	26.4	21.4	16.4	14.0	14.1	14.3	14.4	14.5	15.4	16.3
97.5°	80.4	83.6	86.7	89.8	83.1	66.7	50.3	33.9	17.5	17.6	17.7
100°	111.2	113.9	116.5	119.1	110.3	90.1	69.7	49.4	29.2	26.7	24.2
102.5°	145.4	147.4	149.4	151.2	150.9	148.3	145.6	142.9	140.4	113.3	86.4
105°	200.1	201.0	201.9	202.8	203.6	204.3	205.0	205.8	206.5	207.9	209.2
107.5°	251.5	251.9	252.4	252.8	253.5	254.5	255.5	256.5	257.4	258.2	258.8
110°	286.4	286.9	287.3	287.7	288.4	289.3	290.2	291.1	291.9	292.2	292.5



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	320.7	321.5	322.2	323.0	323.6	324.0	324.4	324.9	325.3	325.2	325.1
115°	372.5	372.9	373.3	373.7	373.9	373.7	373.6	373.4	373.3	373.6	373.9
117.5°	419.5	420.2	420.7	421.3	421.8	422.1	422.4	422.8	423.1	423.0	422.9
120°	451.4	451.9	452.5	453.1	453.3	453.2	453.1	452.9	452.7	453.1	453.3
122.5°	480.7	481.1	481.4	481.8	482.1	482.3	482.5	482.7	483.0	483.1	483.3
125°	523.5	524.1	524.7	525.2	525.4	525.1	524.9	524.5	524.2	524.7	525.1
127.5°	563.3	563.5	563.6	563.7	564.2	564.8	565.5	566.1	566.9	566.8	566.7
130°	589.2	589.4	589.5	589.7	590.0	590.4	590.8	591.3	591.7	591.9	592.0
132.5°	613.2	613.5	613.7	613.9	614.4	614.9	615.5	616.1	616.6	616.8	616.9
135°	648.5	648.4	648.2	648.1	648.3	648.9	649.4	650.1	650.7	650.9	651.2
137.5°	680.4	680.5	680.5	680.6	680.9	681.5	682.2	682.9	683.5	683.8	684.1
140°	701.2	701.5	701.9	702.1	702.4	702.8	703.0	703.3	703.6	704.0	704.5
142.5°	720.1	720.6	721.0	721.6	721.9	722.1	722.3	722.5	722.6	723.0	723.4
145°	748.4	748.9	749.3	749.8	749.9	749.9	749.9	749.9	749.9	750.1	750.2
147.5°	771.4	772.2	773.0	773.9	774.2	774.1	773.9	773.7	773.6	773.7	773.8
150°	787.6	788.2	788.8	789.3	789.6	789.4	789.3	789.2	789.0	789.0	789.0
152.5°	801.2	801.7	802.2	802.6	802.7	802.5	802.3	802.0	801.7	801.9	802.2
155°	820.3	820.4	820.6	820.7	820.6	820.1	819.7	819.2	818.8	819.4	819.9
157.5°	836.3	836.2	836.2	836.1	835.7	835.3	834.7	834.2	833.7	834.5	835.3
160°	845.4	845.1	844.6	844.2	843.8	843.7	843.6	843.4	843.3	844.2	845.1
162.5°	853.8	853.3	852.7	852.1	851.8	851.7	851.5	851.3	851.2	852.1	853.0
165°	864.3	863.6	862.9	862.2	861.8	861.8	861.8	861.8	861.8	863.0	864.2
167.5°	872.8	872.1	871.3	870.5	870.1	870.0	870.0	869.9	869.8	871.0	872.4
170°	877.4	876.6	875.7	874.9	874.4	874.6	874.8	874.9	875.0	876.2	877.4
172.5°	880.7	879.8	878.9	878.0	877.6	877.8	877.9	878.1	878.2	879.4	880.6
175°	884.0	883.2	882.3	881.5	881.1	881.2	881.4	881.5	881.6	883.0	884.3
177.5°	885.7	884.9	884.0	883.2	883.0	883.2	883.4	883.7	883.9	884.8	885.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1206.7	1207.5	1210.9	1213.5	1214.2	1218.1	1218.4
5°	1312.7	1320.8	1336.4	1337.8	1340.2	1352.5	1343.1
7.5°	1437.0	1457.4	1471.1	1483.2	1487.6	1492.9	1491.8
10°	1516.6	1547.0	1562.2	1586.4	1587.3	1593.5	1589.7
12.5°	1596.7	1632.0	1659.7	1664.1	1684.4	1687.6	1692.9
15°	1710.1	1747.6	1786.0	1799.7	1827.7	1834.4	1844.9
17.5°	1816.8	1855.0	1882.0	1917.5	1929.0	1944.4	1933.9
20°	1875.2	1916.9	1951.1	1979.1	1990.9	1999.4	1998.5
22.5°	1910.5	1952.6	1980.2	2001.4	2012.5	2016.2	2015.9
25°	1932.5	1956.8	1965.2	1973.4	1961.1	1956.8	1958.6
27.5°	1871.1	1864.8	1842.5	1813.3	1783.0	1758.9	1745.8
30°	1786.5	1749.5	1715.8	1657.0	1626.7	1608.6	1592.5
32.5°	1666.6	1608.0	1543.2	1489.3	1454.8	1428.1	1424.1
35°	1461.2	1373.0	1293.8	1227.8	1193.6	1164.8	1158.1
37.5°	1242.2	1150.6	1079.3	1021.3	984.5	964.1	945.0
40°	1096.9	1018.2	948.0	898.7	870.8	856.0	844.2
42.5°	985.0	913.1	843.3	805.7	780.4	771.4	764.5
45°	830.4	763.6	715.2	686.7	672.0	656.8	649.7
47.5°	706.6	652.2	620.3	596.1	580.4	571.4	566.9
50°	636.4	591.8	563.4	544.9	530.7	523.5	519.8
52.5°	574.2	537.6	513.7	499.0	489.4	484.1	482.6
55°	494.6	466.6	451.5	438.7	431.6	426.9	424.9
57.5°	430.0	408.4	396.1	385.6	382.8	378.8	377.5
60°	387.4	370.9	360.4	353.3	351.0	346.2	347.1
62.5°	349.9	336.4	327.4	323.3	320.2	316.2	317.5
65°	296.0	286.0	281.2	277.4	273.7	271.3	273.1
67.5°	248.3	241.5	235.1	232.8	231.0	230.6	228.5
70°	217.2	211.5	205.8	204.4	204.4	202.5	202.1
72.5°	187.3	183.1	179.2	178.3	176.7	177.5	175.5
75°	144.6	141.3	139.9	138.5	138.0	138.0	136.6
77.5°	106.9	104.4	102.2	102.2	100.4	99.8	99.6
80°	81.1	80.2	78.3	78.3	77.3	77.8	76.9
82.5°	61.0	59.7	59.3	58.5	57.2	57.2	56.4
85°	32.7	31.3	30.9	29.4	28.4	29.4	28.4
87.5°	14.8	14.6	14.4	13.6	13.4	13.4	12.3
90°	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	16.7	17.6	18.0	18.1	18.2	18.2	18.3
95°	17.2	18.1	18.6	18.7	18.9	19.1	19.2
97.5°	17.7	17.8	17.9	18.1	18.3	18.4	18.5
100°	21.6	19.1	17.9	18.1	18.3	18.4	18.5
102.5°	59.4	32.5	18.9	19.0	19.0	19.0	19.1
105°	210.4	211.8	209.8	204.6	199.2	193.9	188.7
107.5°	259.4	260.1	260.6	261.3	261.8	262.3	262.9
110°	292.7	293.1	293.5	293.9	294.4	294.8	295.2



TEST NUMBER: P332781-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	325.1	325.0	325.3	325.8	326.4	327.0	327.5
115°	374.2	374.5	374.6	374.6	374.6	374.6	374.6
117.5°	422.9	422.8	422.8	422.8	422.7	422.6	422.6
120°	453.6	453.9	453.9	453.6	453.3	453.1	452.7
122.5°	483.5	483.7	483.6	483.3	483.0	482.7	482.4
125°	525.6	526.0	526.3	526.5	526.6	526.7	526.9
127.5°	566.6	566.5	566.4	566.3	566.1	566.1	566.0
130°	592.2	592.4	592.4	592.4	592.4	592.4	592.4
132.5°	617.1	617.2	617.2	617.2	617.0	616.9	616.8
135°	651.6	651.8	652.1	652.4	652.7	653.0	653.3
137.5°	684.5	684.7	684.9	684.8	684.7	684.7	684.6
140°	704.9	705.3	705.7	705.8	706.0	706.1	706.2
142.5°	723.6	724.0	724.2	724.2	724.2	724.2	724.2
145°	750.4	750.6	750.7	751.0	751.4	751.6	751.9
147.5°	774.0	774.1	774.3	774.4	774.5	774.7	774.8
150°	789.0	789.0	789.1	789.3	789.3	789.5	789.6
152.5°	802.4	802.6	802.7	802.6	802.5	802.5	802.4
155°	820.6	821.1	821.2	820.7	820.3	819.8	819.5
157.5°	836.1	836.8	836.8	836.1	835.3	834.5	833.7
160°	845.9	846.8	846.8	845.9	845.1	844.2	843.3
162.5°	853.8	854.7	854.7	853.7	852.7	851.7	850.7
165°	865.3	866.5	866.5	865.1	863.8	862.5	861.1
167.5°	873.6	874.9	874.9	873.3	871.9	870.4	869.0
170°	878.6	879.8	879.6	878.2	876.6	875.2	873.7
172.5°	881.7	882.9	882.7	881.1	879.6	878.0	876.4
175°	885.6	887.0	886.7	884.9	883.2	881.5	879.7
177.5°	886.7	887.7	887.4	886.0	884.6	883.2	881.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9

(END OF REPORT)