

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332818-935

Luminaire Tested: **S124DIW-S1020D1050U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332818-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D1050U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7096.7 lumens  
Efficiency: N/A  
Efficacy: 116.0 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	52	48
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	41	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	45	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.0	2.0
10°-20°	431.5	6.1
20°-30°	684.2	9.6
30°-40°	761.4	10.7
40°-50°	693.1	9.8
50°-60°	566.4	8.0
60°-70°	404.3	5.7
70°-80°	222.6	3.1
80°-90°	64.2	0.9
90°-100°	74.4	1.0
100°-110°	220.4	3.1
110°-120°	374.0	5.3
120°-130°	493.2	6.9
130°-140°	553.9	7.8
140°-150°	544.3	7.7
150°-160°	457.8	6.5
160°-170°	304.6	4.3
170°-180°	106.6	1.5
0°-30°	1255.6	17.7
0°-40°	2017.1	28.4
0°-60°	3276.5	46.2
0°-90°	3967.7	55.9
90°-120°	668.7	9.4
90°-150°	2260.0	31.8
90°-180°	3129.0	44.1
0°-180°	7096.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	26	3	26	3	26	15
95°	69	52	69	52	69	72
105°	213	203	213	203	213	224
115°	377	380	377	380	377	373
125°	550	554	550	554	550	490
135°	715	714	715	714	715	552
145°	869	868	869	868	869	544
155°	994	994	994	994	994	457
165°	1080	1082	1080	1082	1080	304
175°	1121	1126	1121	1126	1121	106
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	15.7	17.0	17.0	17.4	18.3	18.6	18.9	18.1	19.8	20.1	21.6
90°	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5	20.3	19.2	17.7
92.5°	38.7	38.5	38.2	38.1	37.8	37.4	36.6	35.9	35.2	34.5	33.5
95°	68.9	68.9	68.9	68.9	68.9	68.6	68.0	67.4	66.9	66.3	64.9
97.5°	108.0	108.0	108.0	108.0	108.0	107.6	106.9	106.2	105.6	104.9	103.2
100°	135.2	135.2	135.2	135.2	135.2	135.0	134.6	134.2	133.8	133.5	131.7
102.5°	165.9	165.7	165.6	165.4	165.3	165.0	164.4	163.8	163.3	162.7	161.2
105°	212.8	212.2	211.6	211.1	210.5	209.9	209.3	208.8	208.2	207.6	206.8
107.5°	258.6	258.6	258.6	258.6	258.6	258.5	257.9	257.4	256.8	256.2	256.1
110°	291.4	290.8	290.2	289.6	289.0	288.9	289.3	289.6	290.1	290.4	290.7



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.9	324.7	324.6	324.5	324.3	324.3	324.4	324.5	324.6	324.7	325.0
115°	376.8	377.0	377.2	377.4	377.5	377.8	378.0	378.2	378.3	378.6	378.9
117.5°	426.4	426.7	427.1	427.5	427.9	428.4	429.0	429.7	430.4	431.0	431.4
120°	464.0	463.6	463.2	462.9	462.4	462.8	463.7	464.7	465.7	466.7	467.3
122.5°	495.4	496.1	496.8	497.5	498.2	498.9	499.6	500.2	500.8	501.5	501.8
125°	549.5	549.9	550.3	550.7	551.0	551.5	551.8	552.2	552.6	553.0	553.2
127.5°	599.6	599.9	600.2	600.5	600.8	601.2	601.6	601.9	602.4	602.7	603.0
130°	632.4	633.2	634.0	634.7	635.5	636.0	636.5	636.8	637.2	637.6	637.6
132.5°	667.3	667.5	667.9	668.2	668.5	668.8	669.3	669.6	670.0	670.4	670.5
135°	715.2	715.8	716.4	717.0	717.6	718.1	718.4	718.8	719.2	719.6	719.6
137.5°	765.6	765.5	765.4	765.3	765.2	765.3	765.9	766.4	766.9	767.4	767.1
140°	796.3	796.5	796.8	796.9	797.1	797.3	797.5	797.7	797.9	798.1	798.1
142.5°	827.1	827.1	827.2	827.2	827.2	827.2	827.2	827.3	827.3	827.4	827.6
145°	868.7	869.4	869.9	870.5	871.1	871.4	871.7	871.8	872.0	872.2	872.0
147.5°	910.9	911.1	911.4	911.5	911.7	911.9	912.1	912.2	912.4	912.5	912.7
150°	936.8	936.9	937.2	937.4	937.5	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	960.5	961.0	961.5	962.0	962.5	962.5	962.1	961.6	961.1	960.7	960.5
155°	993.5	994.3	995.1	995.8	996.6	996.6	995.8	995.1	994.3	993.5	993.7
157.5°	1023.0	1023.6	1024.2	1024.9	1025.6	1025.6	1025.0	1024.5	1023.9	1023.3	1023.3
160°	1039.7	1040.7	1041.6	1042.6	1043.5	1043.8	1043.2	1042.6	1042.0	1041.5	1041.6
162.5°	1057.1	1058.1	1059.1	1060.1	1061.0	1061.0	1059.9	1058.9	1057.8	1056.8	1057.0
165°	1079.8	1080.6	1081.3	1082.1	1082.9	1082.7	1081.6	1080.4	1079.3	1078.1	1078.5
167.5°	1096.1	1097.3	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.2	1096.1
170°	1105.1	1106.5	1107.8	1109.2	1110.5	1110.6	1109.5	1108.3	1107.2	1106.0	1105.8
172.5°	1112.8	1114.1	1115.5	1116.9	1118.2	1118.3	1116.9	1115.6	1114.3	1112.9	1112.9
175°	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8	1121.0
177.5°	1125.0	1126.3	1127.5	1128.7	1130.0	1130.1	1128.9	1127.9	1126.8	1125.7	1125.7
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	21.4	21.4	20.7	18.4	16.5	14.7	13.8	12.9	13.8	14.7	15.6
90°	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6	4.7	6.9	9.0
92.5°	32.4	31.3	30.2	28.4	26.0	23.6	21.1	18.7	21.1	23.6	26.0
95°	63.5	62.3	60.9	59.3	57.6	55.8	54.1	52.3	54.1	55.8	57.6
97.5°	101.7	100.0	98.5	97.0	95.6	94.2	92.8	91.4	92.8	94.2	95.6
100°	129.9	128.2	126.5	125.2	124.4	123.6	122.9	122.1	122.9	123.6	124.4
102.5°	159.5	158.0	156.4	155.4	155.2	154.8	154.5	154.2	154.5	154.8	155.2
105°	206.0	205.3	204.5	204.0	203.8	203.6	203.5	203.2	203.5	203.6	203.8
107.5°	256.1	255.9	255.8	255.6	255.4	255.1	254.9	254.7	254.9	255.1	255.4
110°	290.8	291.0	291.2	291.1	290.8	290.3	290.0	289.6	290.0	290.3	290.8





TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.4	325.7	326.1	326.1	326.1	326.1	326.0	325.9	326.0	326.1	326.1
115°	379.4	379.7	380.1	380.3	380.3	380.3	380.3	380.3	380.3	380.3	380.3
117.5°	431.6	431.9	432.1	432.2	432.0	431.9	431.7	431.6	431.7	431.9	432.0
120°	467.8	468.4	469.0	468.9	468.1	467.4	466.6	465.8	466.6	467.4	468.1
122.5°	502.0	502.3	502.7	502.6	502.3	502.0	501.7	501.4	501.7	502.0	502.3
125°	553.4	553.5	553.8	553.9	553.9	553.9	553.9	553.9	553.9	553.9	553.9
127.5°	603.3	603.6	604.0	603.8	603.2	602.6	602.1	601.5	602.1	602.6	603.2
130°	637.6	637.6	637.6	637.3	636.7	636.1	635.6	635.0	635.6	636.1	636.7
132.5°	670.7	670.9	671.0	670.9	670.5	670.0	669.6	669.2	669.6	670.0	670.5
135°	719.6	719.6	719.6	719.0	717.8	716.7	715.5	714.4	715.5	716.7	717.8
137.5°	766.8	766.5	766.1	765.7	765.2	764.7	764.1	763.5	764.1	764.7	765.2
140°	798.1	798.1	798.1	797.9	797.5	797.1	796.8	796.3	796.8	797.1	797.5
142.5°	827.7	827.9	828.0	827.9	827.5	827.2	826.7	826.4	826.7	827.2	827.5
145°	871.8	871.7	871.4	871.0	870.2	869.4	868.7	867.9	868.7	869.4	870.2
147.5°	912.8	913.0	913.2	912.7	911.8	910.9	910.0	909.0	910.0	910.9	911.8
150°	937.6	937.6	937.6	937.3	936.5	935.7	935.0	934.2	935.0	935.7	936.5
152.5°	960.4	960.2	960.0	959.8	959.2	958.8	958.4	957.9	958.4	958.8	959.2
155°	993.9	994.0	994.3	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4
157.5°	1023.4	1023.4	1023.5	1023.6	1024.0	1024.3	1024.7	1025.0	1024.7	1024.3	1024.0
160°	1041.8	1042.0	1042.2	1042.4	1042.6	1042.8	1043.0	1043.2	1043.0	1042.8	1042.6
162.5°	1057.2	1057.4	1057.6	1057.9	1058.4	1058.9	1059.5	1059.9	1059.5	1058.9	1058.4
165°	1078.8	1079.3	1079.6	1080.1	1080.7	1081.2	1081.8	1082.4	1081.8	1081.2	1080.7
167.5°	1096.1	1096.1	1096.1	1096.5	1097.3	1098.1	1098.9	1099.7	1098.9	1098.1	1097.3
170°	1105.6	1105.4	1105.2	1105.6	1106.6	1107.5	1108.5	1109.5	1108.5	1107.5	1106.6
172.5°	1112.9	1112.8	1112.8	1113.2	1114.0	1114.8	1115.6	1116.5	1115.6	1114.8	1114.0
175°	1121.2	1121.4	1121.6	1122.1	1123.2	1124.1	1125.1	1126.0	1125.1	1124.1	1123.2
177.5°	1125.7	1125.7	1125.7	1126.1	1126.9	1127.7	1128.4	1129.2	1128.4	1127.7	1126.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	17.5	17.8	20.1	21.4	23.1	25.7	26.9	32.4	34.5	37.1	41.6
90°	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5	22.6	23.8	24.6
92.5°	28.4	30.2	31.3	32.4	33.5	34.5	35.2	35.9	36.6	37.4	37.8
95°	59.3	60.9	62.3	63.5	64.9	66.3	66.9	67.4	68.0	68.6	68.9
97.5°	97.0	98.5	100.0	101.7	103.2	104.9	105.6	106.2	106.9	107.6	108.0
100°	125.2	126.5	128.2	129.9	131.7	133.5	133.8	134.2	134.6	135.0	135.2
102.5°	155.4	156.4	158.0	159.5	161.2	162.7	163.3	163.8	164.4	165.0	165.3
105°	204.0	204.5	205.3	206.0	206.8	207.6	208.2	208.8	209.3	209.9	210.5
107.5°	255.6	255.8	255.9	256.1	256.1	256.2	256.8	257.4	257.9	258.5	258.6
110°	291.1	291.2	291.0	290.8	290.7	290.4	290.1	289.6	289.3	288.9	289.0



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	326.1	326.1	325.7	325.4	325.0	324.7	324.6	324.5	324.4	324.3	324.3
115°	380.3	380.1	379.7	379.4	378.9	378.6	378.3	378.2	378.0	377.8	377.5
117.5°	432.2	432.1	431.9	431.6	431.4	431.0	430.4	429.7	429.0	428.4	427.9
120°	468.9	469.0	468.4	467.8	467.3	466.7	465.7	464.7	463.7	462.8	462.4
122.5°	502.6	502.7	502.3	502.0	501.8	501.5	500.8	500.2	499.6	498.9	498.2
125°	553.9	553.8	553.5	553.4	553.2	553.0	552.6	552.2	551.8	551.5	551.0
127.5°	603.8	604.0	603.6	603.3	603.0	602.7	602.4	601.9	601.6	601.2	600.8
130°	637.3	637.6	637.6	637.6	637.6	637.6	637.2	636.8	636.5	636.0	635.5
132.5°	670.9	671.0	670.9	670.7	670.5	670.4	670.0	669.6	669.3	668.8	668.5
135°	719.0	719.6	719.6	719.6	719.6	719.6	719.2	718.8	718.4	718.1	717.6
137.5°	765.7	766.1	766.5	766.8	767.1	767.4	766.9	766.4	765.9	765.3	765.2
140°	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.7	797.5	797.3	797.1
142.5°	827.9	828.0	827.9	827.7	827.6	827.4	827.3	827.3	827.2	827.2	827.2
145°	871.0	871.4	871.7	871.8	872.0	872.2	872.0	871.8	871.7	871.4	871.1
147.5°	912.7	913.2	913.0	912.8	912.7	912.5	912.4	912.2	912.1	911.9	911.7
150°	937.3	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.6	937.5
152.5°	959.8	960.0	960.2	960.4	960.5	960.7	961.1	961.6	962.1	962.5	962.5
155°	994.4	994.3	994.0	993.9	993.7	993.5	994.3	995.1	995.8	996.6	996.6
157.5°	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9	1024.5	1025.0	1025.6	1025.6
160°	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0	1042.6	1043.2	1043.8	1043.5
162.5°	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8	1058.9	1059.9	1061.0	1061.0
165°	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3	1080.4	1081.6	1082.7	1082.9
167.5°	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3	1098.5	1099.7	1100.9	1100.9
170°	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2	1108.3	1109.5	1110.6	1110.5
172.5°	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3	1115.6	1116.9	1118.3	1118.2
175°	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3
177.5°	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8	1127.9	1128.9	1130.1	1130.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	43.1	43.7	45.1	46.1	45.1	43.7	43.1	41.6	37.1	34.5	32.4
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5
92.5°	38.1	38.2	38.5	38.7	38.5	38.2	38.1	37.8	37.4	36.6	35.9
95°	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.9	68.6	68.0	67.4
97.5°	108.0	108.0	108.0	108.0	108.0	108.0	108.0	108.0	107.6	106.9	106.2
100°	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.0	134.6	134.2
102.5°	165.4	165.6	165.7	165.9	165.7	165.6	165.4	165.3	165.0	164.4	163.8
105°	211.1	211.6	212.2	212.8	212.2	211.6	211.1	210.5	209.9	209.3	208.8
107.5°	258.6	258.6	258.6	258.6	258.6	258.6	258.6	258.6	258.5	257.9	257.4
110°	289.6	290.2	290.8	291.4	290.8	290.2	289.6	289.0	288.9	289.3	289.6



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	324.5	324.6	324.7	324.9	324.7	324.6	324.5	324.3	324.3	324.4	324.5
115°	377.4	377.2	377.0	376.8	377.0	377.2	377.4	377.5	377.8	378.0	378.2
117.5°	427.5	427.1	426.7	426.4	426.7	427.1	427.5	427.9	428.4	429.0	429.7
120°	462.9	463.2	463.6	464.0	463.6	463.2	462.9	462.4	462.8	463.7	464.7
122.5°	497.5	496.8	496.1	495.4	496.1	496.8	497.5	498.2	498.9	499.6	500.2
125°	550.7	550.3	549.9	549.5	549.9	550.3	550.7	551.0	551.5	551.8	552.2
127.5°	600.5	600.2	599.9	599.6	599.9	600.2	600.5	600.8	601.2	601.6	601.9
130°	634.7	634.0	633.2	632.4	633.2	634.0	634.7	635.5	636.0	636.5	636.8
132.5°	668.2	667.9	667.5	667.3	667.5	667.9	668.2	668.5	668.8	669.3	669.6
135°	717.0	716.4	715.8	715.2	715.8	716.4	717.0	717.6	718.1	718.4	718.8
137.5°	765.3	765.4	765.5	765.6	765.5	765.4	765.3	765.2	765.3	765.9	766.4
140°	796.9	796.8	796.5	796.3	796.5	796.8	796.9	797.1	797.3	797.5	797.7
142.5°	827.2	827.2	827.1	827.1	827.1	827.2	827.2	827.2	827.2	827.2	827.3
145°	870.5	869.9	869.4	868.7	869.4	869.9	870.5	871.1	871.4	871.7	871.8
147.5°	911.5	911.4	911.1	910.9	911.1	911.4	911.5	911.7	911.9	912.1	912.2
150°	937.4	937.2	936.9	936.8	936.9	937.2	937.4	937.5	937.6	937.6	937.6
152.5°	962.0	961.5	961.0	960.5	961.0	961.5	962.0	962.5	962.5	962.1	961.6
155°	995.8	995.1	994.3	993.5	994.3	995.1	995.8	996.6	996.6	995.8	995.1
157.5°	1024.9	1024.2	1023.6	1023.0	1023.6	1024.2	1024.9	1025.6	1025.6	1025.0	1024.5
160°	1042.6	1041.6	1040.7	1039.7	1040.7	1041.6	1042.6	1043.5	1043.8	1043.2	1042.6
162.5°	1060.1	1059.1	1058.1	1057.1	1058.1	1059.1	1060.1	1061.0	1061.0	1059.9	1058.9
165°	1082.1	1081.3	1080.6	1079.8	1080.6	1081.3	1082.1	1082.9	1082.7	1081.6	1080.4
167.5°	1099.7	1098.5	1097.3	1096.1	1097.3	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5
170°	1109.2	1107.8	1106.5	1105.1	1106.5	1107.8	1109.2	1110.5	1110.6	1109.5	1108.3
172.5°	1116.9	1115.5	1114.1	1112.8	1114.1	1115.5	1116.9	1118.2	1118.3	1116.9	1115.6
175°	1124.9	1123.5	1122.1	1120.8	1122.1	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5
177.5°	1128.7	1127.5	1126.3	1125.0	1126.3	1127.5	1128.7	1130.0	1130.1	1128.9	1127.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	26.9	25.7	23.1	21.4	20.1	17.8	17.5	15.6	14.7	13.8	12.9
90°	20.3	19.2	17.7	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6
92.5°	35.2	34.5	33.5	32.4	31.3	30.2	28.4	26.0	23.6	21.1	18.7
95°	66.9	66.3	64.9	63.5	62.3	60.9	59.3	57.6	55.8	54.1	52.3
97.5°	105.6	104.9	103.2	101.7	100.0	98.5	97.0	95.6	94.2	92.8	91.4
100°	133.8	133.5	131.7	129.9	128.2	126.5	125.2	124.4	123.6	122.9	122.1
102.5°	163.3	162.7	161.2	159.5	158.0	156.4	155.4	155.2	154.8	154.5	154.2
105°	208.2	207.6	206.8	206.0	205.3	204.5	204.0	203.8	203.6	203.5	203.2
107.5°	256.8	256.2	256.1	256.1	255.9	255.8	255.6	255.4	255.1	254.9	254.7
110°	290.1	290.4	290.7	290.8	291.0	291.2	291.1	290.8	290.3	290.0	289.6



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.6	324.7	325.0	325.4	325.7	326.1	326.1	326.1	326.1	326.0	325.9
115°	378.3	378.6	378.9	379.4	379.7	380.1	380.3	380.3	380.3	380.3	380.3
117.5°	430.4	431.0	431.4	431.6	431.9	432.1	432.2	432.0	431.9	431.7	431.6
120°	465.7	466.7	467.3	467.8	468.4	469.0	468.9	468.1	467.4	466.6	465.8
122.5°	500.8	501.5	501.8	502.0	502.3	502.7	502.6	502.3	502.0	501.7	501.4
125°	552.6	553.0	553.2	553.4	553.5	553.8	553.9	553.9	553.9	553.9	553.9
127.5°	602.4	602.7	603.0	603.3	603.6	604.0	603.8	603.2	602.6	602.1	601.5
130°	637.2	637.6	637.6	637.6	637.6	637.6	637.3	636.7	636.1	635.6	635.0
132.5°	670.0	670.4	670.5	670.7	670.9	671.0	670.9	670.5	670.0	669.6	669.2
135°	719.2	719.6	719.6	719.6	719.6	719.6	719.0	717.8	716.7	715.5	714.4
137.5°	766.9	767.4	767.1	766.8	766.5	766.1	765.7	765.2	764.7	764.1	763.5
140°	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.5	797.1	796.8	796.3
142.5°	827.3	827.4	827.6	827.7	827.9	828.0	827.9	827.5	827.2	826.7	826.4
145°	872.0	872.2	872.0	871.8	871.7	871.4	871.0	870.2	869.4	868.7	867.9
147.5°	912.4	912.5	912.7	912.8	913.0	913.2	912.7	911.8	910.9	910.0	909.0
150°	937.6	937.6	937.6	937.6	937.6	937.6	937.3	936.5	935.7	935.0	934.2
152.5°	961.1	960.7	960.5	960.4	960.2	960.0	959.8	959.2	958.8	958.4	957.9
155°	994.3	993.5	993.7	993.9	994.0	994.3	994.4	994.4	994.4	994.4	994.4
157.5°	1023.9	1023.3	1023.3	1023.4	1023.4	1023.5	1023.6	1024.0	1024.3	1024.7	1025.0
160°	1042.0	1041.5	1041.6	1041.8	1042.0	1042.2	1042.4	1042.6	1042.8	1043.0	1043.2
162.5°	1057.8	1056.8	1057.0	1057.2	1057.4	1057.6	1057.9	1058.4	1058.9	1059.5	1059.9
165°	1079.3	1078.1	1078.5	1078.8	1079.3	1079.6	1080.1	1080.7	1081.2	1081.8	1082.4
167.5°	1097.3	1096.2	1096.1	1096.1	1096.1	1096.1	1096.5	1097.3	1098.1	1098.9	1099.7
170°	1107.2	1106.0	1105.8	1105.6	1105.4	1105.2	1105.6	1106.6	1107.5	1108.5	1109.5
172.5°	1114.3	1112.9	1112.9	1112.9	1112.8	1112.8	1113.2	1114.0	1114.8	1115.6	1116.5
175°	1122.1	1120.8	1121.0	1121.2	1121.4	1121.6	1122.1	1123.2	1124.1	1125.1	1126.0
177.5°	1126.8	1125.7	1125.7	1125.7	1125.7	1125.7	1126.1	1126.9	1127.7	1128.4	1129.2
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.8	14.7	16.5	18.4	20.7	21.4	21.4	21.6	20.1	19.8	18.1
90°	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5
92.5°	21.1	23.6	26.0	28.4	30.2	31.3	32.4	33.5	34.5	35.2	35.9
95°	54.1	55.8	57.6	59.3	60.9	62.3	63.5	64.9	66.3	66.9	67.4
97.5°	92.8	94.2	95.6	97.0	98.5	100.0	101.7	103.2	104.9	105.6	106.2
100°	122.9	123.6	124.4	125.2	126.5	128.2	129.9	131.7	133.5	133.8	134.2
102.5°	154.5	154.8	155.2	155.4	156.4	158.0	159.5	161.2	162.7	163.3	163.8
105°	203.5	203.6	203.8	204.0	204.5	205.3	206.0	206.8	207.6	208.2	208.8
107.5°	254.9	255.1	255.4	255.6	255.8	255.9	256.1	256.1	256.2	256.8	257.4
110°	290.0	290.3	290.8	291.1	291.2	291.0	290.8	290.7	290.4	290.1	289.6





TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.0	326.1	326.1	326.1	326.1	325.7	325.4	325.0	324.7	324.6	324.5
115°	380.3	380.3	380.3	380.3	380.1	379.7	379.4	378.9	378.6	378.3	378.2
117.5°	431.7	431.9	432.0	432.2	432.1	431.9	431.6	431.4	431.0	430.4	429.7
120°	466.6	467.4	468.1	468.9	469.0	468.4	467.8	467.3	466.7	465.7	464.7
122.5°	501.7	502.0	502.3	502.6	502.7	502.3	502.0	501.8	501.5	500.8	500.2
125°	553.9	553.9	553.9	553.9	553.8	553.5	553.4	553.2	553.0	552.6	552.2
127.5°	602.1	602.6	603.2	603.8	604.0	603.6	603.3	603.0	602.7	602.4	601.9
130°	635.6	636.1	636.7	637.3	637.6	637.6	637.6	637.6	637.6	637.2	636.8
132.5°	669.6	670.0	670.5	670.9	671.0	670.9	670.7	670.5	670.4	670.0	669.6
135°	715.5	716.7	717.8	719.0	719.6	719.6	719.6	719.6	719.6	719.2	718.8
137.5°	764.1	764.7	765.2	765.7	766.1	766.5	766.8	767.1	767.4	766.9	766.4
140°	796.8	797.1	797.5	797.9	798.1	798.1	798.1	798.1	798.1	797.9	797.7
142.5°	826.7	827.2	827.5	827.9	828.0	827.9	827.7	827.6	827.4	827.3	827.3
145°	868.7	869.4	870.2	871.0	871.4	871.7	871.8	872.0	872.2	872.0	871.8
147.5°	910.0	910.9	911.8	912.7	913.2	913.0	912.8	912.7	912.5	912.4	912.2
150°	935.0	935.7	936.5	937.3	937.6	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	958.4	958.8	959.2	959.8	960.0	960.2	960.4	960.5	960.7	961.1	961.6
155°	994.4	994.4	994.4	994.4	994.3	994.0	993.9	993.7	993.5	994.3	995.1
157.5°	1024.7	1024.3	1024.0	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9	1024.5
160°	1043.0	1042.8	1042.6	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0	1042.6
162.5°	1059.5	1058.9	1058.4	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8	1058.9
165°	1081.8	1081.2	1080.7	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3	1080.4
167.5°	1098.9	1098.1	1097.3	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3	1098.5
170°	1108.5	1107.5	1106.6	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2	1108.3
172.5°	1115.6	1114.8	1114.0	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3	1115.6
175°	1125.1	1124.1	1123.2	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1	1123.5
177.5°	1128.4	1127.7	1126.9	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8	1127.9
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	18.9	18.6	18.3	17.4	17.0	17.0	15.7
90°	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	36.6	37.4	37.8	38.1	38.2	38.5	38.7
95°	68.0	68.6	68.9	68.9	68.9	68.9	68.9
97.5°	106.9	107.6	108.0	108.0	108.0	108.0	108.0
100°	134.6	135.0	135.2	135.2	135.2	135.2	135.2
102.5°	164.4	165.0	165.3	165.4	165.6	165.7	165.9
105°	209.3	209.9	210.5	211.1	211.6	212.2	212.8
107.5°	257.9	258.5	258.6	258.6	258.6	258.6	258.6
110°	289.3	288.9	289.0	289.6	290.2	290.8	291.4



TEST NUMBER: P332818-935

CATALOG NUMBER: S124DIW-S1020D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	324.4	324.3	324.3	324.5	324.6	324.7	324.9
115°	378.0	377.8	377.5	377.4	377.2	377.0	376.8
117.5°	429.0	428.4	427.9	427.5	427.1	426.7	426.4
120°	463.7	462.8	462.4	462.9	463.2	463.6	464.0
122.5°	499.6	498.9	498.2	497.5	496.8	496.1	495.4
125°	551.8	551.5	551.0	550.7	550.3	549.9	549.5
127.5°	601.6	601.2	600.8	600.5	600.2	599.9	599.6
130°	636.5	636.0	635.5	634.7	634.0	633.2	632.4
132.5°	669.3	668.8	668.5	668.2	667.9	667.5	667.3
135°	718.4	718.1	717.6	717.0	716.4	715.8	715.2
137.5°	765.9	765.3	765.2	765.3	765.4	765.5	765.6
140°	797.5	797.3	797.1	796.9	796.8	796.5	796.3
142.5°	827.2	827.2	827.2	827.2	827.2	827.1	827.1
145°	871.7	871.4	871.1	870.5	869.9	869.4	868.7
147.5°	912.1	911.9	911.7	911.5	911.4	911.1	910.9
150°	937.6	937.6	937.5	937.4	937.2	936.9	936.8
152.5°	962.1	962.5	962.5	962.0	961.5	961.0	960.5
155°	995.8	996.6	996.6	995.8	995.1	994.3	993.5
157.5°	1025.0	1025.6	1025.6	1024.9	1024.2	1023.6	1023.0
160°	1043.2	1043.8	1043.5	1042.6	1041.6	1040.7	1039.7
162.5°	1059.9	1061.0	1061.0	1060.1	1059.1	1058.1	1057.1
165°	1081.6	1082.7	1082.9	1082.1	1081.3	1080.6	1079.8
167.5°	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.1
170°	1109.5	1110.6	1110.5	1109.2	1107.8	1106.5	1105.1
172.5°	1116.9	1118.3	1118.2	1116.9	1115.5	1114.1	1112.8
175°	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8
177.5°	1128.9	1130.1	1130.0	1128.7	1127.5	1126.3	1125.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8

(END OF REPORT)