

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332786-940

Luminaire Tested: **S124DIW-S795D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332786-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D770U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5414.3 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	33
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	2.1
10°-20°	314.1	5.8
20°-30°	462.3	8.5
30°-40°	537.4	9.9
40°-50°	537.5	9.9
50°-60°	470.1	8.7
60°-70°	349.1	6.4
70°-80°	198.4	3.7
80°-90°	59.8	1.1
90°-100°	56.4	1.0
100°-110°	167.2	3.1
110°-120°	283.8	5.2
120°-130°	374.2	6.9
130°-140°	420.2	7.8
140°-150°	413.0	7.6
150°-160°	347.3	6.4
160°-170°	231.1	4.3
170°-180°	80.9	1.5
0°-30°	887.8	16.4
0°-40°	1425.3	26.3
0°-60°	2432.8	44.9
0°-90°	3040.1	56.2
90°-120°	507.4	9.4
90°-150°	1714.8	31.7
90°-180°	2374.0	43.8
0°-180°	5414.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	2	9	14	18	20	5
95°	40	46	50	52	52	44
105°	154	155	158	160	162	164
115°	289	288	287	287	286	284
125°	420	420	420	418	417	374
135°	542	546	546	545	543	419
145°	658	661	662	661	659	412
155°	754	754	754	756	754	347
165°	821	819	818	822	819	231
175°	854	851	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.2	20.2	20.4	20.6	20.8	20.9	21.0	21.0	21.0	21.1	21.3
90°	2.0	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4
92.5°	14.2	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8
95°	39.7	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7
97.5°	69.4	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1
100°	92.6	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6
102.5°	117.0	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9
105°	154.2	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9
107.5°	193.2	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8
110°	219.7	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	247.3	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3
115°	288.6	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0
117.5°	327.4	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5
120°	353.4	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3
122.5°	380.4	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0
125°	420.3	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3
127.5°	456.4	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0
130°	481.8	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5
132.5°	507.7	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4
135°	542.1	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7
137.5°	579.3	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8
140°	604.2	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4
142.5°	627.0	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8
145°	658.5	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	689.7	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2
150°	708.8	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	726.8	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2
155°	754.5	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4
157.5°	777.8	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9
160°	791.6	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7
162.5°	804.2	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6
165°	821.4	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9
167.5°	834.4	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7
170°	841.9	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1
172.5°	847.1	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5
175°	854.4	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5
177.5°	856.8	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	21.5	21.7	21.8	21.9	22.0	22.0	22.1	22.2
90°	16.3	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.3	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.2	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	80.6	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	101.8	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.3	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.4	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.3	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.8	219.5	219.2	219.3	219.7	220.2	220.6	221.1



TEST NUMBER: P332786-940

CATALOG NUMBER: S124DIW-S795D770U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.2	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	287.0	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	326.1	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	352.6	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.5	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	419.0	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.7	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	483.2	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	508.1	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.4	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.5	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.3	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.8	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.6	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.3	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.1	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	803.4	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	819.7	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	833.6	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.0	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	846.5	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	855.8	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)