

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332852-935

Luminaire Tested: **S124DIW-S1195D1050U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332852-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1050U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7535.4 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58				
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49				
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41				
3	83	73	66	60	77	68	62	57	60	55	50	52	48	44	44	41	39	35				
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30				
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26				
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20				
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16				
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	19	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.6	2.1
10°-20°	455.3	6.0
20°-30°	670.1	8.9
30°-40°	779.0	10.3
40°-50°	779.1	10.3
50°-60°	681.5	9.0
60°-70°	506.1	6.7
70°-80°	287.5	3.8
80°-90°	86.3	1.1
90°-100°	74.4	1.0
100°-110°	220.4	2.9
110°-120°	374.0	5.0
120°-130°	493.2	6.5
130°-140°	553.9	7.4
140°-150°	544.3	7.2
150°-160°	457.8	6.1
160°-170°	304.6	4.0
170°-180°	106.6	1.4
0°-30°	1287.0	17.1
0°-40°	2066.0	27.4
0°-60°	3526.5	46.8
0°-90°	4406.4	58.5
90°-120°	668.7	8.9
90°-150°	2260.0	30.0
90°-180°	3129.0	41.5
0°-180°	7535.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	3	12	19	24	26	7
95°	52	60	66	69	69	58
105°	203	204	208	210	213	216
115°	380	380	379	378	377	375
125°	554	554	553	551	550	493
135°	714	719	720	718	715	552
145°	868	871	872	871	869	543
155°	994	994	994	997	994	457
165°	1082	1080	1078	1083	1080	305
175°	1126	1122	1121	1126	1121	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.1	29.3	29.4	29.7	29.9	30.0	30.0	30.1	30.1	30.2	30.5
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	18.7	21.1	23.6	26.0	28.4	30.2	31.3	32.4	33.5	34.5	35.2
95°	52.3	54.1	55.8	57.6	59.3	60.9	62.3	63.5	64.9	66.3	66.9
97.5°	91.4	92.8	94.2	95.6	97.0	98.5	100.0	101.7	103.2	104.9	105.6
100°	122.1	122.9	123.6	124.4	125.2	126.5	128.2	129.9	131.7	133.5	133.8
102.5°	154.2	154.5	154.8	155.2	155.4	156.4	158.0	159.5	161.2	162.7	163.3
105°	203.2	203.5	203.6	203.8	204.0	204.5	205.3	206.0	206.8	207.6	208.2
107.5°	254.7	254.9	255.1	255.4	255.6	255.8	255.9	256.1	256.1	256.2	256.8
110°	289.6	290.0	290.3	290.8	291.1	291.2	291.0	290.8	290.7	290.4	290.1



TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.9	326.0	326.1	326.1	326.1	326.1	325.7	325.4	325.0	324.7	324.6
115°	380.3	380.3	380.3	380.3	380.3	380.1	379.7	379.4	378.9	378.6	378.3
117.5°	431.6	431.7	431.9	432.0	432.2	432.1	431.9	431.6	431.4	431.0	430.4
120°	465.8	466.6	467.4	468.1	468.9	469.0	468.4	467.8	467.3	466.7	465.7
122.5°	501.4	501.7	502.0	502.3	502.6	502.7	502.3	502.0	501.8	501.5	500.8
125°	553.9	553.9	553.9	553.9	553.9	553.8	553.5	553.4	553.2	553.0	552.6
127.5°	601.5	602.1	602.6	603.2	603.8	604.0	603.6	603.3	603.0	602.7	602.4
130°	635.0	635.6	636.1	636.7	637.3	637.6	637.6	637.6	637.6	637.6	637.2
132.5°	669.2	669.6	670.0	670.5	670.9	671.0	670.9	670.7	670.5	670.4	670.0
135°	714.4	715.5	716.7	717.8	719.0	719.6	719.6	719.6	719.6	719.6	719.2
137.5°	763.5	764.1	764.7	765.2	765.7	766.1	766.5	766.8	767.1	767.4	766.9
140°	796.3	796.8	797.1	797.5	797.9	798.1	798.1	798.1	798.1	798.1	797.9
142.5°	826.4	826.7	827.2	827.5	827.9	828.0	827.9	827.7	827.6	827.4	827.3
145°	867.9	868.7	869.4	870.2	871.0	871.4	871.7	871.8	872.0	872.2	872.0
147.5°	909.0	910.0	910.9	911.8	912.7	913.2	913.0	912.8	912.7	912.5	912.4
150°	934.2	935.0	935.7	936.5	937.3	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	957.9	958.4	958.8	959.2	959.8	960.0	960.2	960.4	960.5	960.7	961.1
155°	994.4	994.4	994.4	994.4	994.4	994.3	994.0	993.9	993.7	993.5	994.3
157.5°	1025.0	1024.7	1024.3	1024.0	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9
160°	1043.2	1043.0	1042.8	1042.6	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0
162.5°	1059.9	1059.5	1058.9	1058.4	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8
165°	1082.4	1081.8	1081.2	1080.7	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3
167.5°	1099.7	1098.9	1098.1	1097.3	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3
170°	1109.5	1108.5	1107.5	1106.6	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2
172.5°	1116.5	1115.6	1114.8	1114.0	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3
175°	1126.0	1125.1	1124.1	1123.2	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1
177.5°	1129.2	1128.4	1127.7	1126.9	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	30.7	30.9	31.2	31.3	31.4	31.5	31.5	31.6
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	35.9	36.6	37.4	37.8	38.1	38.2	38.5	38.7
95°	67.4	68.0	68.6	68.9	68.9	68.9	68.9	68.9
97.5°	106.2	106.9	107.6	108.0	108.0	108.0	108.0	108.0
100°	134.2	134.6	135.0	135.2	135.2	135.2	135.2	135.2
102.5°	163.8	164.4	165.0	165.3	165.4	165.6	165.7	165.9
105°	208.8	209.3	209.9	210.5	211.1	211.6	212.2	212.8
107.5°	257.4	257.9	258.5	258.6	258.6	258.6	258.6	258.6
110°	289.6	289.3	288.9	289.0	289.6	290.2	290.8	291.4





TEST NUMBER: P332852-935

CATALOG NUMBER: S124DIW-S1195D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	324.5	324.4	324.3	324.3	324.5	324.6	324.7	324.9
115°	378.2	378.0	377.8	377.5	377.4	377.2	377.0	376.8
117.5°	429.7	429.0	428.4	427.9	427.5	427.1	426.7	426.4
120°	464.7	463.7	462.8	462.4	462.9	463.2	463.6	464.0
122.5°	500.2	499.6	498.9	498.2	497.5	496.8	496.1	495.4
125°	552.2	551.8	551.5	551.0	550.7	550.3	549.9	549.5
127.5°	601.9	601.6	601.2	600.8	600.5	600.2	599.9	599.6
130°	636.8	636.5	636.0	635.5	634.7	634.0	633.2	632.4
132.5°	669.6	669.3	668.8	668.5	668.2	667.9	667.5	667.3
135°	718.8	718.4	718.1	717.6	717.0	716.4	715.8	715.2
137.5°	766.4	765.9	765.3	765.2	765.3	765.4	765.5	765.6
140°	797.7	797.5	797.3	797.1	796.9	796.8	796.5	796.3
142.5°	827.3	827.2	827.2	827.2	827.2	827.2	827.1	827.1
145°	871.8	871.7	871.4	871.1	870.5	869.9	869.4	868.7
147.5°	912.2	912.1	911.9	911.7	911.5	911.4	911.1	910.9
150°	937.6	937.6	937.6	937.5	937.4	937.2	936.9	936.8
152.5°	961.6	962.1	962.5	962.5	962.0	961.5	961.0	960.5
155°	995.1	995.8	996.6	996.6	995.8	995.1	994.3	993.5
157.5°	1024.5	1025.0	1025.6	1025.6	1024.9	1024.2	1023.6	1023.0
160°	1042.6	1043.2	1043.8	1043.5	1042.6	1041.6	1040.7	1039.7
162.5°	1058.9	1059.9	1061.0	1061.0	1060.1	1059.1	1058.1	1057.1
165°	1080.4	1081.6	1082.7	1082.9	1082.1	1081.3	1080.6	1079.8
167.5°	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.1
170°	1108.3	1109.5	1110.6	1110.5	1109.2	1107.8	1106.5	1105.1
172.5°	1115.6	1116.9	1118.3	1118.2	1116.9	1115.5	1114.1	1112.8
175°	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8
177.5°	1127.9	1128.9	1130.1	1130.0	1128.7	1127.5	1126.3	1125.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8

(END OF REPORT)