

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333084-940

Luminaire Tested: **S124RDIW-S1020D1050U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333084-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7111.6 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12352	12352	12352	12352
5°	14327	12388	10950	12388
10°	16948	12336	9773	12336
15°	19578	12221	8398	12221
20°	21798	12064	7594	12064
25°	22502	11909	7050	11909
30°	19699	11723	6723	11723
35°	15334	11446	6525	11446
40°	11499	11129	6418	11129
45°	9079	10620	6361	10620
50°	7665	10034	6179	10034
55°	6681	9388	5847	9388
60°	6011	8719	5176	8719
65°	5299	7996	4451	7996
70°	4773	7246	4015	7246
75°	3999	6422	3425	6422
80°	3384	5472	3208	5472
85°	2862	4279	2862	4279



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.2	2.1
10°-20°	447.2	6.3
20°-30°	699.4	9.8
30°-40°	777.5	10.9
40°-50°	689.9	9.7
50°-60°	537.6	7.6
60°-70°	351.9	4.9
70°-80°	173.1	2.4
80°-90°	46.2	0.6
90°-100°	77.0	1.1
100°-110°	228.2	3.2
110°-120°	387.4	5.4
120°-130°	510.8	7.2
130°-140°	573.6	8.1
140°-150°	563.7	7.9
150°-160°	474.1	6.7
160°-170°	315.4	4.4
170°-180°	110.5	1.6
0°-30°	1294.9	18.2
0°-40°	2072.4	29.1
0°-60°	3299.8	46.4
0°-90°	3871.0	54.4
90°-120°	692.6	9.7
90°-150°	2340.6	32.9
90°-180°	3241.0	45.6
0°-180°	7111.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1530	1530	1530	1530	1530	
5°	1768	1529	1351	1529	1768	179
15°	2342	1462	1005	1462	2342	666
25°	2526	1337	792	1337	2526	1121
35°	1556	1161	662	1161	1556	975
45°	795	930	557	930	795	630
55°	475	667	415	667	475	432
65°	277	419	233	419	277	279
75°	128	206	110	206	128	141
85°	31	46	31	46	31	35
90°	27	3	27	3	27	15
95°	71	54	71	54	71	74
105°	220	210	220	210	220	232
115°	390	394	390	394	390	386
125°	569	574	569	574	569	508
135°	741	740	741	740	741	572
145°	900	899	900	899	900	563
155°	1029	1030	1029	1030	1029	474
165°	1118	1121	1118	1121	1118	315
175°	1161	1166	1161	1166	1161	110
180°	1168	1168	1168	1168	1168	



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1613.8	1618.3	1613.8	1613.4	1608.5	1607.0	1605.0	1598.6	1586.7	1579.8	1581.3
5°	1768.0	1783.3	1774.8	1773.5	1760.0	1746.4	1737.8	1718.1	1697.1	1682.9	1671.2
7.5°	1946.2	1955.1	1949.7	1941.1	1919.1	1906.7	1886.7	1860.6	1823.1	1794.3	1768.1
10°	2067.5	2074.9	2072.5	2056.5	2040.4	2007.8	1989.2	1952.9	1905.4	1867.9	1832.6
12.5°	2186.9	2194.8	2173.1	2173.8	2143.5	2117.7	2088.4	2042.6	1987.8	1939.3	1895.3
15°	2342.5	2332.6	2332.6	2320.3	2286.3	2250.7	2220.4	2172.4	2103.3	2045.3	1984.3
17.5°	2464.3	2467.7	2462.7	2433.6	2407.0	2370.0	2314.6	2258.5	2194.4	2116.7	2054.2
20°	2537.3	2537.3	2531.7	2512.0	2477.5	2438.0	2378.3	2317.2	2235.9	2157.6	2087.3
22.5°	2566.9	2568.8	2562.3	2546.0	2515.0	2476.5	2425.5	2363.6	2279.7	2191.6	2104.5
25°	2526.2	2537.9	2539.1	2534.8	2525.6	2502.1	2458.4	2394.9	2319.7	2224.1	2130.4
27.5°	2319.3	2334.1	2347.1	2368.4	2396.7	2411.5	2413.5	2381.2	2315.6	2223.7	2129.3
30°	2113.2	2125.5	2165.6	2218.0	2258.6	2295.6	2327.7	2336.3	2299.4	2216.7	2117.5
32.5°	1884.4	1901.1	1941.2	1997.5	2065.3	2128.0	2199.9	2236.7	2235.7	2186.1	2094.3
35°	1555.9	1568.3	1605.3	1664.4	1745.8	1838.9	1952.9	2041.7	2102.0	2097.7	2041.7
37.5°	1254.8	1268.7	1306.1	1355.2	1434.1	1549.3	1659.7	1782.0	1893.7	1956.5	1937.7
40°	1091.1	1091.7	1128.1	1178.7	1252.6	1353.1	1473.3	1608.9	1733.4	1835.1	1854.8
42.5°	961.9	962.0	986.1	1040.5	1093.9	1188.4	1303.1	1437.8	1583.5	1701.0	1753.3
45°	795.2	800.8	820.5	853.2	895.1	975.2	1067.0	1192.2	1355.6	1494.9	1581.8
47.5°	673.4	681.5	694.1	720.8	754.1	807.5	883.5	996.0	1128.8	1282.1	1405.8
50°	610.3	611.5	627.5	642.3	671.3	713.8	780.4	874.1	996.1	1143.5	1280.9
52.5°	556.1	555.8	565.4	584.2	607.7	640.9	694.6	779.9	888.1	1020.2	1162.1
55°	474.7	477.8	485.2	499.9	517.8	541.3	583.8	647.9	733.0	845.8	974.6
57.5°	412.8	414.4	420.2	426.4	442.8	459.9	491.8	536.3	608.1	700.4	820.5
60°	372.3	372.9	374.8	384.1	397.0	413.0	434.6	472.2	532.6	617.1	712.0
62.5°	332.9	333.9	336.8	343.6	353.6	364.7	387.3	417.5	467.5	539.7	625.2
65°	277.4	278.0	282.3	284.8	292.8	302.6	319.3	339.7	374.2	434.6	499.4
67.5°	231.8	231.8	232.0	235.3	240.9	247.4	257.4	273.7	299.7	336.8	393.9
70°	202.2	202.2	203.4	205.3	208.4	213.9	219.5	231.8	250.9	281.1	324.9
72.5°	174.6	175.0	176.3	176.6	178.3	182.8	186.9	194.8	209.0	231.8	267.2
75°	128.2	130.1	133.1	135.6	138.7	138.1	142.4	147.3	151.7	165.2	185.6
77.5°	95.4	94.4	94.8	96.9	97.3	97.9	100.9	104.8	108.0	114.4	121.7
80°	72.8	72.8	74.5	75.2	74.5	75.2	78.3	80.2	81.4	83.8	90.6
82.5°	55.0	56.0	55.4	56.0	56.4	57.0	59.6	59.9	61.2	62.2	65.0
85°	30.9	31.5	32.0	30.9	30.9	30.9	32.0	32.6	33.9	33.3	34.5
87.5°	16.2	15.7	16.1	16.1	16.4	15.8	16.1	16.8	15.5	15.8	15.5
90°	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3	21.0	19.9	18.3
92.5°	40.1	39.9	39.6	39.4	39.1	38.7	37.9	37.2	36.5	35.8	34.7
95°	71.3	71.3	71.3	71.3	71.3	71.1	70.4	69.8	69.3	68.7	67.2
97.5°	111.8	111.8	111.8	111.8	111.8	111.5	110.8	110.0	109.3	108.6	106.9
100°	140.0	140.0	140.0	140.0	140.0	139.8	139.4	139.0	138.6	138.2	136.4
102.5°	171.8	171.7	171.5	171.3	171.2	170.9	170.2	169.7	169.2	168.5	166.9
105°	220.4	219.8	219.2	218.6	218.0	217.4	216.8	216.2	215.6	215.0	214.2
107.5°	267.8	267.8	267.9	267.9	267.9	267.7	267.1	266.5	266.0	265.4	265.3
110°	301.8	301.1	300.5	299.9	299.3	299.2	299.6	300.0	300.4	300.8	301.0



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.4	336.3	336.2	336.1	335.9	335.9	336.0	336.1	336.2	336.3	336.6
115°	390.2	390.5	390.7	390.8	391.0	391.3	391.5	391.6	391.8	392.1	392.4
117.5°	441.6	441.9	442.4	442.7	443.2	443.7	444.3	445.1	445.8	446.4	446.7
120°	480.5	480.2	479.7	479.4	478.9	479.3	480.3	481.3	482.3	483.3	483.9
122.5°	513.1	513.8	514.5	515.2	515.9	516.7	517.4	518.1	518.7	519.4	519.7
125°	569.1	569.5	569.9	570.3	570.7	571.1	571.5	571.9	572.3	572.7	572.9
127.5°	621.0	621.3	621.6	621.9	622.2	622.6	623.0	623.4	623.8	624.2	624.6
130°	655.0	655.8	656.6	657.4	658.2	658.7	659.2	659.5	660.0	660.3	660.3
132.5°	691.1	691.3	691.7	692.1	692.3	692.7	693.1	693.5	693.9	694.3	694.5
135°	740.7	741.4	741.9	742.5	743.2	743.7	744.0	744.5	744.8	745.3	745.3
137.5°	792.9	792.8	792.7	792.6	792.5	792.6	793.2	793.7	794.2	794.8	794.4
140°	824.7	824.9	825.2	825.4	825.5	825.7	826.0	826.2	826.3	826.5	826.5
142.5°	856.6	856.6	856.7	856.7	856.7	856.8	856.8	856.8	856.8	856.9	857.1
145°	899.7	900.4	900.9	901.5	902.1	902.5	902.8	902.9	903.1	903.3	903.1
147.5°	943.4	943.6	943.9	944.1	944.2	944.4	944.6	944.8	944.9	945.0	945.2
150°	970.2	970.4	970.6	970.8	971.0	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	994.8	995.2	995.8	996.3	996.8	996.8	996.4	995.9	995.4	995.0	994.8
155°	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9	1029.1
157.5°	1059.4	1060.2	1060.8	1061.5	1062.2	1062.2	1061.6	1061.0	1060.4	1059.8	1059.8
160°	1076.7	1077.8	1078.8	1079.8	1080.8	1081.0	1080.4	1079.8	1079.1	1078.6	1078.8
162.5°	1094.8	1095.8	1096.9	1097.9	1098.9	1098.9	1097.7	1096.6	1095.6	1094.5	1094.7
165°	1118.3	1119.1	1119.9	1120.7	1121.5	1121.3	1120.2	1118.9	1117.8	1116.5	1117.0
167.5°	1135.1	1136.4	1137.6	1138.9	1140.1	1140.1	1138.9	1137.7	1136.5	1135.3	1135.2
170°	1144.5	1145.9	1147.4	1148.8	1150.1	1150.2	1149.1	1147.8	1146.7	1145.4	1145.2
172.5°	1152.4	1153.9	1155.3	1156.7	1158.1	1158.2	1156.7	1155.4	1154.1	1152.6	1152.6
175°	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8	1161.0
177.5°	1165.1	1166.4	1167.7	1168.9	1170.3	1170.4	1169.2	1168.1	1167.0	1165.8	1165.8
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1576.4	1569.5	1566.0	1558.1	1548.7	1543.8	1539.4	1532.9	1524.6	1515.7	1509.3
5°	1656.4	1641.6	1623.1	1600.9	1581.2	1562.1	1545.4	1528.7	1509.7	1490.0	1470.3
7.5°	1738.5	1709.4	1677.9	1641.6	1606.2	1574.0	1544.4	1516.1	1484.0	1455.3	1429.1
10°	1795.7	1756.2	1712.4	1666.3	1620.0	1579.9	1540.5	1504.8	1465.3	1430.1	1400.5
12.5°	1842.1	1795.7	1743.0	1685.5	1629.9	1581.4	1536.1	1489.4	1444.6	1406.5	1367.0
15°	1919.0	1855.5	1784.6	1715.6	1643.4	1577.4	1516.4	1462.2	1411.0	1357.5	1319.8
17.5°	1971.8	1896.6	1810.4	1727.4	1642.2	1564.4	1494.0	1429.4	1370.4	1315.6	1270.9
20°	2003.4	1920.2	1824.7	1730.4	1634.8	1551.6	1475.8	1404.3	1343.3	1284.1	1237.8
22.5°	2021.2	1929.1	1824.7	1725.9	1626.9	1536.8	1453.6	1379.1	1312.7	1253.5	1202.3
25°	2026.9	1928.2	1821.6	1708.2	1599.6	1504.1	1417.8	1337.0	1263.1	1203.9	1149.7
27.5°	2019.0	1902.8	1793.6	1677.2	1565.3	1464.5	1373.9	1289.1	1215.0	1151.6	1095.9
30°	2007.2	1882.6	1765.5	1644.7	1531.2	1434.5	1338.9	1257.6	1180.4	1114.5	1058.5
32.5°	1981.5	1858.0	1732.0	1608.2	1493.3	1393.6	1302.9	1221.0	1145.5	1078.1	1018.5
35°	1930.7	1805.5	1668.7	1541.8	1428.9	1325.3	1240.3	1161.4	1089.2	1017.2	954.2
37.5°	1863.8	1735.9	1599.8	1460.7	1347.8	1250.0	1172.0	1097.9	1027.5	961.6	892.0
40°	1800.6	1684.1	1543.6	1405.5	1289.6	1195.2	1123.2	1056.0	985.1	919.7	850.1
42.5°	1724.2	1625.0	1482.9	1344.3	1229.9	1139.1	1071.8	1006.1	941.6	878.3	805.7
45°	1596.6	1521.3	1388.2	1255.1	1139.8	1049.8	988.2	930.2	873.5	813.1	744.7
47.5°	1450.4	1399.5	1284.5	1148.2	1041.5	960.6	901.0	853.6	805.7	745.3	685.3
50°	1348.8	1316.1	1205.1	1080.7	978.9	904.3	843.3	798.9	758.8	700.9	647.3
52.5°	1240.3	1222.9	1129.2	1010.1	911.9	838.7	786.6	746.6	706.1	658.0	607.8
55°	1075.0	1084.3	1004.8	901.9	809.4	747.8	700.3	667.0	632.5	591.8	552.9
57.5°	906.2	940.0	886.5	796.2	709.5	652.6	616.8	588.8	559.8	526.1	492.9
60°	805.0	833.4	803.3	723.7	647.9	594.9	561.6	540.0	511.0	480.2	455.0
62.5°	706.4	736.7	718.9	654.7	584.2	538.7	509.3	489.2	467.6	440.8	414.5
65°	582.6	602.3	593.6	549.3	499.4	460.5	433.4	418.6	398.9	379.2	355.7
67.5°	446.2	484.3	479.2	455.7	412.5	382.2	364.4	351.3	333.4	318.7	302.8
70°	366.8	401.9	401.3	382.2	358.7	330.4	318.1	307.0	291.0	276.8	263.9
72.5°	300.2	332.4	337.2	322.5	306.5	285.1	273.2	265.6	250.0	240.3	229.8
75°	210.2	233.6	239.8	239.8	232.4	221.3	210.8	205.9	194.8	186.2	180.0
77.5°	137.9	152.7	162.3	164.4	165.6	161.8	153.3	149.8	141.2	138.2	132.3
80°	97.4	107.3	118.3	122.1	125.1	123.9	120.2	117.7	109.8	106.6	104.2
82.5°	67.3	72.8	81.9	90.0	89.2	92.4	89.2	87.2	81.1	80.0	77.6
85°	35.1	35.8	37.0	42.5	45.7	46.8	47.4	46.2	44.4	44.4	40.0
87.5°	15.2	14.4	15.0	14.6	14.7	16.2	17.3	17.3	16.2	15.2	14.2
90°	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7	4.9	7.1	9.4
92.5°	33.5	32.4	31.3	29.4	26.9	24.4	21.8	19.4	21.8	24.4	26.9
95°	65.8	64.5	63.0	61.4	59.7	57.8	56.0	54.2	56.0	57.8	59.7
97.5°	105.3	103.6	102.0	100.5	99.0	97.6	96.1	94.7	96.1	97.6	99.0
100°	134.6	132.8	131.0	129.7	128.9	128.0	127.2	126.4	127.2	128.0	128.9
102.5°	165.2	163.6	161.9	161.0	160.7	160.3	160.1	159.7	160.1	160.3	160.7
105°	213.4	212.6	211.8	211.2	211.1	210.9	210.7	210.4	210.7	210.9	211.1
107.5°	265.2	265.0	264.9	264.7	264.5	264.2	264.0	263.8	264.0	264.2	264.5
110°	301.2	301.4	301.6	301.5	301.1	300.7	300.3	299.9	300.3	300.7	301.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.0	337.3	337.7	337.8	337.7	337.7	337.6	337.5	337.6	337.7	337.7
115°	392.9	393.2	393.7	393.9	393.9	393.9	393.9	393.9	393.9	393.9	393.9
117.5°	447.0	447.3	447.5	447.6	447.5	447.3	447.1	447.0	447.1	447.3	447.5
120°	484.5	485.1	485.7	485.6	484.8	484.0	483.2	482.4	483.2	484.0	484.8
122.5°	520.0	520.2	520.6	520.5	520.2	519.9	519.6	519.2	519.6	519.9	520.2
125°	573.1	573.3	573.5	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6
127.5°	624.8	625.2	625.5	625.4	624.7	624.1	623.6	622.9	623.6	624.1	624.7
130°	660.3	660.3	660.3	660.0	659.4	658.8	658.3	657.6	658.3	658.8	659.4
132.5°	694.6	694.8	694.9	694.8	694.4	693.9	693.5	693.0	693.5	693.9	694.4
135°	745.3	745.3	745.3	744.7	743.4	742.3	741.0	739.9	741.0	742.3	743.4
137.5°	794.2	793.8	793.4	793.0	792.5	791.9	791.3	790.8	791.3	791.9	792.5
140°	826.5	826.5	826.5	826.3	826.0	825.5	825.2	824.7	825.2	825.5	826.0
142.5°	857.2	857.4	857.6	857.5	857.0	856.7	856.2	855.9	856.2	856.7	857.0
145°	902.9	902.8	902.5	902.1	901.3	900.4	899.6	898.8	899.6	900.4	901.3
147.5°	945.4	945.6	945.7	945.3	944.3	943.4	942.4	941.5	942.4	943.4	944.3
150°	971.1	971.1	971.1	970.7	969.9	969.1	968.3	967.5	968.3	969.1	969.9
152.5°	994.6	994.4	994.3	994.0	993.5	993.0	992.6	992.0	992.6	993.0	993.5
155°	1029.3	1029.5	1029.7	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8	1029.8
157.5°	1059.9	1059.9	1060.0	1060.2	1060.5	1060.9	1061.2	1061.6	1061.2	1060.9	1060.5
160°	1079.0	1079.1	1079.4	1079.6	1079.8	1080.0	1080.2	1080.4	1080.2	1080.0	1079.8
162.5°	1094.9	1095.1	1095.3	1095.6	1096.2	1096.7	1097.3	1097.7	1097.3	1096.7	1096.2
165°	1117.3	1117.8	1118.1	1118.7	1119.3	1119.8	1120.4	1121.1	1120.4	1119.8	1119.3
167.5°	1135.2	1135.2	1135.1	1135.6	1136.4	1137.3	1138.1	1138.9	1138.1	1137.3	1136.4
170°	1145.0	1144.9	1144.6	1145.0	1146.0	1147.0	1148.1	1149.1	1148.1	1147.0	1146.0
172.5°	1152.6	1152.5	1152.5	1152.9	1153.8	1154.6	1155.4	1156.3	1155.4	1154.6	1153.8
175°	1161.2	1161.4	1161.6	1162.2	1163.2	1164.2	1165.2	1166.2	1165.2	1164.2	1163.2
177.5°	1165.8	1165.8	1165.8	1166.3	1167.1	1167.9	1168.7	1169.5	1168.7	1167.9	1167.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1502.4	1497.4	1491.0	1483.6	1474.8	1466.9	1463.5	1466.4	1467.8	1463.9	1463.5
5°	1456.7	1441.3	1428.9	1410.4	1395.6	1383.3	1374.7	1371.0	1372.2	1362.4	1359.9
7.5°	1405.2	1387.0	1366.8	1344.8	1324.4	1306.3	1296.7	1291.6	1281.1	1276.7	1269.2
10°	1372.2	1347.6	1327.8	1301.9	1278.5	1257.0	1246.4	1237.8	1227.4	1222.4	1211.9
12.5°	1338.2	1309.6	1287.9	1261.0	1237.1	1211.0	1201.0	1185.1	1168.7	1158.3	1144.9
15°	1290.2	1255.7	1229.2	1197.1	1168.8	1139.2	1112.7	1083.1	1072.0	1048.6	1035.0
17.5°	1234.1	1199.1	1166.3	1123.3	1079.5	1042.8	1014.5	986.1	969.2	954.2	947.4
20°	1197.1	1165.1	1119.5	1069.5	1020.8	980.2	957.3	938.9	920.3	909.9	902.5
22.5°	1162.1	1121.1	1068.2	1014.3	965.6	933.8	914.4	895.5	880.4	870.4	860.6
25°	1103.4	1049.8	993.7	932.1	898.8	871.0	850.1	834.6	825.5	812.4	807.5
27.5°	1043.1	978.2	916.3	874.9	840.2	814.8	796.6	785.0	773.3	765.0	758.6
30°	996.8	930.9	875.4	835.9	800.8	779.8	765.0	751.4	742.2	735.4	730.5
32.5°	950.9	884.9	838.4	795.9	768.2	747.8	732.0	721.8	714.6	705.8	702.8
35°	884.6	826.0	785.3	747.2	718.8	700.3	688.0	677.4	671.3	668.9	667.0
37.5°	820.8	772.9	729.2	697.9	672.5	658.0	643.5	638.3	634.1	629.6	631.6
40°	780.4	735.4	696.6	663.3	642.9	627.0	618.3	612.2	608.4	608.4	608.4
42.5°	745.4	701.4	663.5	633.7	613.3	599.8	590.2	585.0	583.8	583.3	586.2
45°	691.1	650.3	612.2	587.5	570.2	556.6	551.1	546.8	546.8	549.3	549.8
47.5°	637.1	599.1	568.4	540.7	525.0	516.5	511.7	509.4	509.7	512.1	515.0
50°	604.1	566.5	536.3	511.7	496.9	488.8	484.6	483.3	484.6	484.6	488.8
52.5°	568.1	534.5	504.7	484.0	467.3	459.8	457.4	455.7	456.4	458.4	460.2
55°	515.3	485.2	456.8	437.0	424.7	419.8	414.3	414.8	413.7	414.8	414.8
57.5°	462.4	435.3	408.9	393.3	382.5	375.3	369.3	371.0	369.2	368.9	367.9
60°	428.5	398.9	377.9	363.7	351.3	345.2	339.7	340.9	339.0	337.8	335.4
62.5°	391.5	366.8	346.8	333.1	323.2	316.1	310.6	309.3	305.1	300.9	295.4
65°	337.8	317.4	299.6	286.7	277.4	271.9	267.5	263.9	254.6	244.7	239.8
67.5°	285.7	271.0	254.3	243.3	235.9	228.5	220.3	214.0	205.4	200.0	196.9
70°	252.1	237.9	223.7	213.3	205.3	198.5	189.2	184.9	178.8	176.3	173.3
72.5°	220.1	206.9	193.7	184.2	175.7	170.4	163.1	158.8	156.0	155.1	152.0
75°	171.4	160.9	151.1	142.4	135.6	131.9	128.9	125.7	124.5	119.0	115.9
77.5°	125.0	118.2	111.9	105.8	100.9	98.5	92.6	89.0	86.9	84.4	83.7
80°	97.4	92.5	86.3	82.6	75.8	73.4	70.9	70.3	69.6	69.0	68.4
82.5°	73.2	68.3	62.2	59.9	58.1	56.6	55.1	54.5	53.9	54.2	54.1
85°	37.0	34.5	34.5	33.9	33.3	32.6	32.0	32.0	31.5	32.0	31.5
87.5°	14.6	14.5	14.8	14.2	15.0	15.3	15.1	15.3	16.1	15.3	15.4
90°	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3	23.5	24.7	25.5
92.5°	29.4	31.3	32.4	33.5	34.7	35.8	36.5	37.2	37.9	38.7	39.1
95°	61.4	63.0	64.5	65.8	67.2	68.7	69.3	69.8	70.4	71.1	71.3
97.5°	100.5	102.0	103.6	105.3	106.9	108.6	109.3	110.0	110.8	111.5	111.8
100°	129.7	131.0	132.8	134.6	136.4	138.2	138.6	139.0	139.4	139.8	140.0
102.5°	161.0	161.9	163.6	165.2	166.9	168.5	169.2	169.7	170.2	170.9	171.2
105°	211.2	211.8	212.6	213.4	214.2	215.0	215.6	216.2	216.8	217.4	218.0
107.5°	264.7	264.9	265.0	265.2	265.3	265.4	266.0	266.5	267.1	267.7	267.9
110°	301.5	301.6	301.4	301.2	301.0	300.8	300.4	300.0	299.6	299.2	299.3



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	337.8	337.7	337.3	337.0	336.6	336.3	336.2	336.1	336.0	335.9	335.9
115°	393.9	393.7	393.2	392.9	392.4	392.1	391.8	391.6	391.5	391.3	391.0
117.5°	447.6	447.5	447.3	447.0	446.7	446.4	445.8	445.1	444.3	443.7	443.2
120°	485.6	485.7	485.1	484.5	483.9	483.3	482.3	481.3	480.3	479.3	478.9
122.5°	520.5	520.6	520.2	520.0	519.7	519.4	518.7	518.1	517.4	516.7	515.9
125°	573.6	573.5	573.3	573.1	572.9	572.7	572.3	571.9	571.5	571.1	570.7
127.5°	625.4	625.5	625.2	624.8	624.6	624.2	623.8	623.4	623.0	622.6	622.2
130°	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.5	659.2	658.7	658.2
132.5°	694.8	694.9	694.8	694.6	694.5	694.3	693.9	693.5	693.1	692.7	692.3
135°	744.7	745.3	745.3	745.3	745.3	745.3	744.8	744.5	744.0	743.7	743.2
137.5°	793.0	793.4	793.8	794.2	794.4	794.8	794.2	793.7	793.2	792.6	792.5
140°	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.2	826.0	825.7	825.5
142.5°	857.5	857.6	857.4	857.2	857.1	856.9	856.8	856.8	856.8	856.8	856.7
145°	902.1	902.5	902.8	902.9	903.1	903.3	903.1	902.9	902.8	902.5	902.1
147.5°	945.3	945.7	945.6	945.4	945.2	945.0	944.9	944.8	944.6	944.4	944.2
150°	970.7	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.0
152.5°	994.0	994.3	994.4	994.6	994.8	995.0	995.4	995.9	996.4	996.8	996.8
155°	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2
157.5°	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4	1061.0	1061.6	1062.2	1062.2
160°	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1	1079.8	1080.4	1081.0	1080.8
162.5°	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6	1096.6	1097.7	1098.9	1098.9
165°	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8	1118.9	1120.2	1121.3	1121.5
167.5°	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5	1137.7	1138.9	1140.1	1140.1
170°	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7	1147.8	1149.1	1150.2	1150.1
172.5°	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1	1155.4	1156.7	1158.2	1158.1
175°	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4
177.5°	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0	1168.1	1169.2	1170.4	1170.3
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1460.4	1461.4	1458.0	1457.1	1458.0	1461.4	1460.4	1463.5	1463.9	1467.8	1466.4
5°	1355.0	1353.7	1350.6	1351.2	1350.6	1353.7	1355.0	1359.9	1362.4	1372.2	1371.0
7.5°	1264.7	1259.9	1261.2	1256.3	1261.2	1259.9	1264.7	1269.2	1276.7	1281.1	1291.6
10°	1209.4	1202.7	1197.1	1192.2	1197.1	1202.7	1209.4	1211.9	1222.4	1227.4	1237.8
12.5°	1134.0	1128.2	1120.7	1122.2	1120.7	1128.2	1134.0	1144.9	1158.3	1168.7	1185.1
15°	1027.0	1017.7	1003.0	1004.8	1003.0	1017.7	1027.0	1035.0	1048.6	1072.0	1083.1
17.5°	936.4	936.5	929.7	931.3	929.7	936.5	936.4	947.4	954.2	969.2	986.1
20°	889.6	885.2	885.8	884.0	885.8	885.2	889.6	902.5	909.9	920.3	938.9
22.5°	857.0	851.7	847.4	843.6	847.4	851.7	857.0	860.6	870.4	880.4	895.5
25°	802.0	798.3	792.7	791.5	792.7	798.3	802.0	807.5	812.4	825.5	834.6
27.5°	753.7	753.0	750.7	747.9	750.7	753.0	753.7	758.6	765.0	773.3	785.0
30°	725.6	724.3	723.1	721.2	723.1	724.3	725.6	730.5	735.4	742.2	751.4
32.5°	700.4	699.6	698.4	698.6	698.4	699.6	700.4	702.8	705.8	714.6	721.8
35°	664.5	663.9	662.7	662.1	662.7	663.9	664.5	667.0	668.9	671.3	677.4
37.5°	631.0	632.6	631.9	631.7	631.9	632.6	631.0	631.6	629.6	634.1	638.3
40°	607.8	608.4	609.7	609.0	609.7	608.4	607.8	608.4	608.4	608.4	612.2
42.5°	588.6	588.7	590.4	588.4	590.4	588.7	588.6	586.2	583.3	583.8	585.0
45°	554.2	557.9	557.2	557.2	557.2	557.9	554.2	549.8	549.3	546.8	546.8
47.5°	516.6	519.8	520.7	520.5	520.7	519.8	516.6	515.0	512.1	509.7	509.4
50°	492.0	490.7	492.6	492.0	492.6	490.7	492.0	488.8	484.6	484.6	483.3
52.5°	461.8	462.1	462.0	461.4	462.0	462.1	461.8	460.2	458.4	456.4	455.7
55°	415.4	416.1	414.8	415.4	414.8	416.1	415.4	414.8	414.8	413.7	414.8
57.5°	365.2	362.2	363.5	361.9	363.5	362.2	365.2	367.9	368.9	369.2	371.0
60°	329.2	324.2	323.0	320.6	323.0	324.2	329.2	335.4	337.8	339.0	340.9
62.5°	288.7	285.3	281.1	283.0	281.1	285.3	288.7	295.4	300.9	305.1	309.3
65°	234.9	232.4	230.5	233.0	230.5	232.4	234.9	239.8	244.7	254.6	263.9
67.5°	194.4	193.1	193.1	191.8	193.1	193.1	194.4	196.9	200.0	205.4	214.0
70°	173.3	171.4	171.4	170.1	171.4	171.4	173.3	173.3	176.3	178.8	184.9
72.5°	151.5	149.6	150.2	149.5	150.2	149.6	151.5	152.0	155.1	156.0	158.8
75°	112.2	109.1	109.1	109.8	109.1	109.1	112.2	115.9	119.0	124.5	125.7
77.5°	83.7	83.1	84.0	82.8	84.0	83.1	83.7	83.7	84.4	86.9	89.0
80°	68.4	67.8	67.2	69.0	67.2	67.8	68.4	68.4	69.0	69.6	70.3
82.5°	53.1	53.1	52.9	55.2	52.9	53.1	53.1	54.1	54.2	53.9	54.5
85°	32.0	30.9	32.0	30.9	32.0	30.9	32.0	31.5	32.0	31.5	32.0
87.5°	16.5	16.1	15.7	16.2	15.7	16.1	16.5	15.4	15.3	16.1	15.3
90°	25.9	26.3	26.7	27.1	26.7	26.3	25.9	25.5	24.7	23.5	22.3
92.5°	39.4	39.6	39.9	40.1	39.9	39.6	39.4	39.1	38.7	37.9	37.2
95°	71.3	71.3	71.3	71.3	71.3	71.3	71.3	71.3	71.1	70.4	69.8
97.5°	111.8	111.8	111.8	111.8	111.8	111.8	111.8	111.8	111.5	110.8	110.0
100°	140.0	140.0	140.0	140.0	140.0	140.0	140.0	140.0	139.8	139.4	139.0
102.5°	171.3	171.5	171.7	171.8	171.7	171.5	171.3	171.2	170.9	170.2	169.7
105°	218.6	219.2	219.8	220.4	219.8	219.2	218.6	218.0	217.4	216.8	216.2
107.5°	267.9	267.9	267.8	267.8	267.8	267.9	267.9	267.9	267.7	267.1	266.5
110°	299.9	300.5	301.1	301.8	301.1	300.5	299.9	299.3	299.2	299.6	300.0



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	336.1	336.2	336.3	336.4	336.3	336.2	336.1	335.9	335.9	336.0	336.1
115°	390.8	390.7	390.5	390.2	390.5	390.7	390.8	391.0	391.3	391.5	391.6
117.5°	442.7	442.4	441.9	441.6	441.9	442.4	442.7	443.2	443.7	444.3	445.1
120°	479.4	479.7	480.2	480.5	480.2	479.7	479.4	478.9	479.3	480.3	481.3
122.5°	515.2	514.5	513.8	513.1	513.8	514.5	515.2	515.9	516.7	517.4	518.1
125°	570.3	569.9	569.5	569.1	569.5	569.9	570.3	570.7	571.1	571.5	571.9
127.5°	621.9	621.6	621.3	621.0	621.3	621.6	621.9	622.2	622.6	623.0	623.4
130°	657.4	656.6	655.8	655.0	655.8	656.6	657.4	658.2	658.7	659.2	659.5
132.5°	692.1	691.7	691.3	691.1	691.3	691.7	692.1	692.3	692.7	693.1	693.5
135°	742.5	741.9	741.4	740.7	741.4	741.9	742.5	743.2	743.7	744.0	744.5
137.5°	792.6	792.7	792.8	792.9	792.8	792.7	792.6	792.5	792.6	793.2	793.7
140°	825.4	825.2	824.9	824.7	824.9	825.2	825.4	825.5	825.7	826.0	826.2
142.5°	856.7	856.7	856.6	856.6	856.6	856.7	856.7	856.7	856.8	856.8	856.8
145°	901.5	900.9	900.4	899.7	900.4	900.9	901.5	902.1	902.5	902.8	902.9
147.5°	944.1	943.9	943.6	943.4	943.6	943.9	944.1	944.2	944.4	944.6	944.8
150°	970.8	970.6	970.4	970.2	970.4	970.6	970.8	971.0	971.1	971.1	971.1
152.5°	996.3	995.8	995.2	994.8	995.2	995.8	996.3	996.8	996.8	996.4	995.9
155°	1031.4	1030.6	1029.7	1028.9	1029.7	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6
157.5°	1061.5	1060.8	1060.2	1059.4	1060.2	1060.8	1061.5	1062.2	1062.2	1061.6	1061.0
160°	1079.8	1078.8	1077.8	1076.7	1077.8	1078.8	1079.8	1080.8	1081.0	1080.4	1079.8
162.5°	1097.9	1096.9	1095.8	1094.8	1095.8	1096.9	1097.9	1098.9	1098.9	1097.7	1096.6
165°	1120.7	1119.9	1119.1	1118.3	1119.1	1119.9	1120.7	1121.5	1121.3	1120.2	1118.9
167.5°	1138.9	1137.6	1136.4	1135.1	1136.4	1137.6	1138.9	1140.1	1140.1	1138.9	1137.7
170°	1148.8	1147.4	1145.9	1144.5	1145.9	1147.4	1148.8	1150.1	1150.2	1149.1	1147.8
172.5°	1156.7	1155.3	1153.9	1152.4	1153.9	1155.3	1156.7	1158.1	1158.2	1156.7	1155.4
175°	1165.0	1163.6	1162.2	1160.8	1162.2	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6
177.5°	1168.9	1167.7	1166.4	1165.1	1166.4	1167.7	1168.9	1170.3	1170.4	1169.2	1168.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1463.5	1466.9	1474.8	1483.6	1491.0	1497.4	1502.4	1509.3	1515.7	1524.6	1532.9
5°	1374.7	1383.3	1395.6	1410.4	1428.9	1441.3	1456.7	1470.3	1490.0	1509.7	1528.7
7.5°	1296.7	1306.3	1324.4	1344.8	1366.8	1387.0	1405.2	1429.1	1455.3	1484.0	1516.1
10°	1246.4	1257.0	1278.5	1301.9	1327.8	1347.6	1372.2	1400.5	1430.1	1465.3	1504.8
12.5°	1201.0	1211.0	1237.1	1261.0	1287.9	1309.6	1338.2	1367.0	1406.5	1444.6	1489.4
15°	1112.7	1139.2	1168.8	1197.1	1229.2	1255.7	1290.2	1319.8	1357.5	1411.0	1462.2
17.5°	1014.5	1042.8	1079.5	1123.3	1166.3	1199.1	1234.1	1270.9	1315.6	1370.4	1429.4
20°	957.3	980.2	1020.8	1069.5	1119.5	1165.1	1197.1	1237.8	1284.1	1343.3	1404.3
22.5°	914.4	933.8	965.6	1014.3	1068.2	1121.1	1162.1	1202.3	1253.5	1312.7	1379.1
25°	850.1	871.0	898.8	932.1	993.7	1049.8	1103.4	1149.7	1203.9	1263.1	1337.0
27.5°	796.6	814.8	840.2	874.9	916.3	978.2	1043.1	1095.9	1151.6	1215.0	1289.1
30°	765.0	779.8	800.8	835.9	875.4	930.9	996.8	1058.5	1114.5	1180.4	1257.6
32.5°	732.0	747.8	768.2	795.9	838.4	884.9	950.9	1018.5	1078.1	1145.5	1221.0
35°	688.0	700.3	718.8	747.2	785.3	826.0	884.6	954.2	1017.2	1089.2	1161.4
37.5°	643.5	658.0	672.5	697.9	729.2	772.9	820.8	892.0	961.6	1027.5	1097.9
40°	618.3	627.0	642.9	663.3	696.6	735.4	780.4	850.1	919.7	985.1	1056.0
42.5°	590.2	599.8	613.3	633.7	663.5	701.4	745.4	805.7	878.3	941.6	1006.1
45°	551.1	556.6	570.2	587.5	612.2	650.3	691.1	744.7	813.1	873.5	930.2
47.5°	511.7	516.5	525.0	540.7	568.4	599.1	637.1	685.3	745.3	805.7	853.6
50°	484.6	488.8	496.9	511.7	536.3	566.5	604.1	647.3	700.9	758.8	798.9
52.5°	457.4	459.8	467.3	484.0	504.7	534.5	568.1	607.8	658.0	706.1	746.6
55°	414.3	419.8	424.7	437.0	456.8	485.2	515.3	552.9	591.8	632.5	667.0
57.5°	369.3	375.3	382.5	393.3	408.9	435.3	462.4	492.9	526.1	559.8	588.8
60°	339.7	345.2	351.3	363.7	377.9	398.9	428.5	455.0	480.2	511.0	540.0
62.5°	310.6	316.1	323.2	333.1	346.8	366.8	391.5	414.5	440.8	467.6	489.2
65°	267.5	271.9	277.4	286.7	299.6	317.4	337.8	355.7	379.2	398.9	418.6
67.5°	220.3	228.5	235.9	243.3	254.3	271.0	285.7	302.8	318.7	333.4	351.3
70°	189.2	198.5	205.3	213.3	223.7	237.9	252.1	263.9	276.8	291.0	307.0
72.5°	163.1	170.4	175.7	184.2	193.7	206.9	220.1	229.8	240.3	250.0	265.6
75°	128.9	131.9	135.6	142.4	151.1	160.9	171.4	180.0	186.2	194.8	205.9
77.5°	92.6	98.5	100.9	105.8	111.9	118.2	125.0	132.3	138.2	141.2	149.8
80°	70.9	73.4	75.8	82.6	86.3	92.5	97.4	104.2	106.6	109.8	117.7
82.5°	55.1	56.6	58.1	59.9	62.2	68.3	73.2	77.6	80.0	81.1	87.2
85°	32.0	32.6	33.3	33.9	34.5	34.5	37.0	40.0	44.4	44.4	46.2
87.5°	15.1	15.3	15.0	14.2	14.8	14.5	14.6	14.2	15.2	16.2	17.3
90°	21.0	19.9	18.3	16.7	15.1	13.5	11.5	9.4	7.1	4.9	2.7
92.5°	36.5	35.8	34.7	33.5	32.4	31.3	29.4	26.9	24.4	21.8	19.4
95°	69.3	68.7	67.2	65.8	64.5	63.0	61.4	59.7	57.8	56.0	54.2
97.5°	109.3	108.6	106.9	105.3	103.6	102.0	100.5	99.0	97.6	96.1	94.7
100°	138.6	138.2	136.4	134.6	132.8	131.0	129.7	128.9	128.0	127.2	126.4
102.5°	169.2	168.5	166.9	165.2	163.6	161.9	161.0	160.7	160.3	160.1	159.7
105°	215.6	215.0	214.2	213.4	212.6	211.8	211.2	211.1	210.9	210.7	210.4
107.5°	266.0	265.4	265.3	265.2	265.0	264.9	264.7	264.5	264.2	264.0	263.8
110°	300.4	300.8	301.0	301.2	301.4	301.6	301.5	301.1	300.7	300.3	299.9



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	336.2	336.3	336.6	337.0	337.3	337.7	337.8	337.7	337.7	337.6	337.5
115°	391.8	392.1	392.4	392.9	393.2	393.7	393.9	393.9	393.9	393.9	393.9
117.5°	445.8	446.4	446.7	447.0	447.3	447.5	447.6	447.5	447.3	447.1	447.0
120°	482.3	483.3	483.9	484.5	485.1	485.7	485.6	484.8	484.0	483.2	482.4
122.5°	518.7	519.4	519.7	520.0	520.2	520.6	520.5	520.2	519.9	519.6	519.2
125°	572.3	572.7	572.9	573.1	573.3	573.5	573.6	573.6	573.6	573.6	573.6
127.5°	623.8	624.2	624.6	624.8	625.2	625.5	625.4	624.7	624.1	623.6	622.9
130°	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.4	658.8	658.3	657.6
132.5°	693.9	694.3	694.5	694.6	694.8	694.9	694.8	694.4	693.9	693.5	693.0
135°	744.8	745.3	745.3	745.3	745.3	745.3	744.7	743.4	742.3	741.0	739.9
137.5°	794.2	794.8	794.4	794.2	793.8	793.4	793.0	792.5	791.9	791.3	790.8
140°	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.0	825.5	825.2	824.7
142.5°	856.8	856.9	857.1	857.2	857.4	857.6	857.5	857.0	856.7	856.2	855.9
145°	903.1	903.3	903.1	902.9	902.8	902.5	902.1	901.3	900.4	899.6	898.8
147.5°	944.9	945.0	945.2	945.4	945.6	945.7	945.3	944.3	943.4	942.4	941.5
150°	971.1	971.1	971.1	971.1	971.1	971.1	970.7	969.9	969.1	968.3	967.5
152.5°	995.4	995.0	994.8	994.6	994.4	994.3	994.0	993.5	993.0	992.6	992.0
155°	1029.7	1028.9	1029.1	1029.3	1029.5	1029.7	1029.8	1029.8	1029.8	1029.8	1029.8
157.5°	1060.4	1059.8	1059.8	1059.9	1059.9	1060.0	1060.2	1060.5	1060.9	1061.2	1061.6
160°	1079.1	1078.6	1078.8	1079.0	1079.1	1079.4	1079.6	1079.8	1080.0	1080.2	1080.4
162.5°	1095.6	1094.5	1094.7	1094.9	1095.1	1095.3	1095.6	1096.2	1096.7	1097.3	1097.7
165°	1117.8	1116.5	1117.0	1117.3	1117.8	1118.1	1118.7	1119.3	1119.8	1120.4	1121.1
167.5°	1136.5	1135.3	1135.2	1135.2	1135.2	1135.1	1135.6	1136.4	1137.3	1138.1	1138.9
170°	1146.7	1145.4	1145.2	1145.0	1144.9	1144.6	1145.0	1146.0	1147.0	1148.1	1149.1
172.5°	1154.1	1152.6	1152.6	1152.6	1152.5	1152.5	1152.9	1153.8	1154.6	1155.4	1156.3
175°	1162.2	1160.8	1161.0	1161.2	1161.4	1161.6	1162.2	1163.2	1164.2	1165.2	1166.2
177.5°	1167.0	1165.8	1165.8	1165.8	1165.8	1165.8	1166.3	1167.1	1167.9	1168.7	1169.5
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1539.4	1543.8	1548.7	1558.1	1566.0	1569.5	1576.4	1581.3	1579.8	1586.7	1598.6
5°	1545.4	1562.1	1581.2	1600.9	1623.1	1641.6	1656.4	1671.2	1682.9	1697.1	1718.1
7.5°	1544.4	1574.0	1606.2	1641.6	1677.9	1709.4	1738.5	1768.1	1794.3	1823.1	1860.6
10°	1540.5	1579.9	1620.0	1666.3	1712.4	1756.2	1795.7	1832.6	1867.9	1905.4	1952.9
12.5°	1536.1	1581.4	1629.9	1685.5	1743.0	1795.7	1842.1	1895.3	1939.3	1987.8	2042.6
15°	1516.4	1577.4	1643.4	1715.6	1784.6	1855.5	1919.0	1984.3	2045.3	2103.3	2172.4
17.5°	1494.0	1564.4	1642.2	1727.4	1810.4	1896.6	1971.8	2054.2	2116.7	2194.4	2258.5
20°	1475.8	1551.6	1634.8	1730.4	1824.7	1920.2	2003.4	2087.3	2157.6	2235.9	2317.2
22.5°	1453.6	1536.8	1626.9	1725.9	1824.7	1929.1	2021.2	2104.5	2191.6	2279.7	2363.6
25°	1417.8	1504.1	1599.6	1708.2	1821.6	1928.2	2026.9	2130.4	2224.1	2319.7	2394.9
27.5°	1373.9	1464.5	1565.3	1677.2	1793.6	1902.8	2019.0	2129.3	2223.7	2315.6	2381.2
30°	1338.9	1434.5	1531.2	1644.7	1765.5	1882.6	2007.2	2117.5	2216.7	2299.4	2336.3
32.5°	1302.9	1393.6	1493.3	1608.2	1732.0	1858.0	1981.5	2094.3	2186.1	2235.7	2236.7
35°	1240.3	1325.3	1428.9	1541.8	1668.7	1805.5	1930.7	2041.7	2097.7	2102.0	2041.7
37.5°	1172.0	1250.0	1347.8	1460.7	1599.8	1735.9	1863.8	1937.7	1956.5	1893.7	1782.0
40°	1123.2	1195.2	1289.6	1405.5	1543.6	1684.1	1800.6	1854.8	1835.1	1733.4	1608.9
42.5°	1071.8	1139.1	1229.9	1344.3	1482.9	1625.0	1724.2	1753.3	1701.0	1583.5	1437.8
45°	988.2	1049.8	1139.8	1255.1	1388.2	1521.3	1596.6	1581.8	1494.9	1355.6	1192.2
47.5°	901.0	960.6	1041.5	1148.2	1284.5	1399.5	1450.4	1405.8	1282.1	1128.8	996.0
50°	843.3	904.3	978.9	1080.7	1205.1	1316.1	1348.8	1280.9	1143.5	996.1	874.1
52.5°	786.6	838.7	911.9	1010.1	1129.2	1222.9	1240.3	1162.1	1020.2	888.1	779.9
55°	700.3	747.8	809.4	901.9	1004.8	1084.3	1075.0	974.6	845.8	733.0	647.9
57.5°	616.8	652.6	709.5	796.2	886.5	940.0	906.2	820.5	700.4	608.1	536.3
60°	561.6	594.9	647.9	723.7	803.3	833.4	805.0	712.0	617.1	532.6	472.2
62.5°	509.3	538.7	584.2	654.7	718.9	736.7	706.4	625.2	539.7	467.5	417.5
65°	433.4	460.5	499.4	549.3	593.6	602.3	582.6	499.4	434.6	374.2	339.7
67.5°	364.4	382.2	412.5	455.7	479.2	484.3	446.2	393.9	336.8	299.7	273.7
70°	318.1	330.4	358.7	382.2	401.3	401.9	366.8	324.9	281.1	250.9	231.8
72.5°	273.2	285.1	306.5	322.5	337.2	332.4	300.2	267.2	231.8	209.0	194.8
75°	210.8	221.3	232.4	239.8	239.8	233.6	210.2	185.6	165.2	151.7	147.3
77.5°	153.3	161.8	165.6	164.4	162.3	152.7	137.9	121.7	114.4	108.0	104.8
80°	120.2	123.9	125.1	122.1	118.3	107.3	97.4	90.6	83.8	81.4	80.2
82.5°	89.2	92.4	89.2	90.0	81.9	72.8	67.3	65.0	62.2	61.2	59.9
85°	47.4	46.8	45.7	42.5	37.0	35.8	35.1	34.5	33.3	33.9	32.6
87.5°	17.3	16.2	14.7	14.6	15.0	14.4	15.2	15.5	15.8	15.5	16.8
90°	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0	22.3
92.5°	21.8	24.4	26.9	29.4	31.3	32.4	33.5	34.7	35.8	36.5	37.2
95°	56.0	57.8	59.7	61.4	63.0	64.5	65.8	67.2	68.7	69.3	69.8
97.5°	96.1	97.6	99.0	100.5	102.0	103.6	105.3	106.9	108.6	109.3	110.0
100°	127.2	128.0	128.9	129.7	131.0	132.8	134.6	136.4	138.2	138.6	139.0
102.5°	160.1	160.3	160.7	161.0	161.9	163.6	165.2	166.9	168.5	169.2	169.7
105°	210.7	210.9	211.1	211.2	211.8	212.6	213.4	214.2	215.0	215.6	216.2
107.5°	264.0	264.2	264.5	264.7	264.9	265.0	265.2	265.3	265.4	266.0	266.5
110°	300.3	300.7	301.1	301.5	301.6	301.4	301.2	301.0	300.8	300.4	300.0



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	337.6	337.7	337.7	337.8	337.7	337.3	337.0	336.6	336.3	336.2	336.1
115°	393.9	393.9	393.9	393.9	393.7	393.2	392.9	392.4	392.1	391.8	391.6
117.5°	447.1	447.3	447.5	447.6	447.5	447.3	447.0	446.7	446.4	445.8	445.1
120°	483.2	484.0	484.8	485.6	485.7	485.1	484.5	483.9	483.3	482.3	481.3
122.5°	519.6	519.9	520.2	520.5	520.6	520.2	520.0	519.7	519.4	518.7	518.1
125°	573.6	573.6	573.6	573.6	573.5	573.3	573.1	572.9	572.7	572.3	571.9
127.5°	623.6	624.1	624.7	625.4	625.5	625.2	624.8	624.6	624.2	623.8	623.4
130°	658.3	658.8	659.4	660.0	660.3	660.3	660.3	660.3	660.3	660.0	659.5
132.5°	693.5	693.9	694.4	694.8	694.9	694.8	694.6	694.5	694.3	693.9	693.5
135°	741.0	742.3	743.4	744.7	745.3	745.3	745.3	745.3	745.3	744.8	744.5
137.5°	791.3	791.9	792.5	793.0	793.4	793.8	794.2	794.4	794.8	794.2	793.7
140°	825.2	825.5	826.0	826.3	826.5	826.5	826.5	826.5	826.5	826.3	826.2
142.5°	856.2	856.7	857.0	857.5	857.6	857.4	857.2	857.1	856.9	856.8	856.8
145°	899.6	900.4	901.3	902.1	902.5	902.8	902.9	903.1	903.3	903.1	902.9
147.5°	942.4	943.4	944.3	945.3	945.7	945.6	945.4	945.2	945.0	944.9	944.8
150°	968.3	969.1	969.9	970.7	971.1	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	992.6	993.0	993.5	994.0	994.3	994.4	994.6	994.8	995.0	995.4	995.9
155°	1029.8	1029.8	1029.8	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7	1030.6
157.5°	1061.2	1060.9	1060.5	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4	1061.0
160°	1080.2	1080.0	1079.8	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1	1079.8
162.5°	1097.3	1096.7	1096.2	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6	1096.6
165°	1120.4	1119.8	1119.3	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8	1118.9
167.5°	1138.1	1137.3	1136.4	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5	1137.7
170°	1148.1	1147.0	1146.0	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7	1147.8
172.5°	1155.4	1154.6	1153.8	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1	1155.4
175°	1165.2	1164.2	1163.2	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2	1163.6
177.5°	1168.7	1167.9	1167.1	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0	1168.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1605.0	1607.0	1608.5	1613.4	1613.8	1618.3	1613.8
5°	1737.8	1746.4	1760.0	1773.5	1774.8	1783.3	1768.0
7.5°	1886.7	1906.7	1919.1	1941.1	1949.7	1955.1	1946.2
10°	1989.2	2007.8	2040.4	2056.5	2072.5	2074.9	2067.5
12.5°	2088.4	2117.7	2143.5	2173.8	2173.1	2194.8	2186.9
15°	2220.4	2250.7	2286.3	2320.3	2332.6	2332.6	2342.5
17.5°	2314.6	2370.0	2407.0	2433.6	2462.7	2467.7	2464.3
20°	2378.3	2438.0	2477.5	2512.0	2531.7	2537.3	2537.3
22.5°	2425.5	2476.5	2515.0	2546.0	2562.3	2568.8	2566.9
25°	2458.4	2502.1	2525.6	2534.8	2539.1	2537.9	2526.2
27.5°	2413.5	2411.5	2396.7	2368.4	2347.1	2334.1	2319.3
30°	2327.7	2295.6	2258.6	2218.0	2165.6	2125.5	2113.2
32.5°	2199.9	2128.0	2065.3	1997.5	1941.2	1901.1	1884.4
35°	1952.9	1838.9	1745.8	1664.4	1605.3	1568.3	1555.9
37.5°	1659.7	1549.3	1434.1	1355.2	1306.1	1268.7	1254.8
40°	1473.3	1353.1	1252.6	1178.7	1128.1	1091.7	1091.1
42.5°	1303.1	1188.4	1093.9	1040.5	986.1	962.0	961.9
45°	1067.0	975.2	895.1	853.2	820.5	800.8	795.2
47.5°	883.5	807.5	754.1	720.8	694.1	681.5	673.4
50°	780.4	713.8	671.3	642.3	627.5	611.5	610.3
52.5°	694.6	640.9	607.7	584.2	565.4	555.8	556.1
55°	583.8	541.3	517.8	499.9	485.2	477.8	474.7
57.5°	491.8	459.9	442.8	426.4	420.2	414.4	412.8
60°	434.6	413.0	397.0	384.1	374.8	372.9	372.3
62.5°	387.3	364.7	353.6	343.6	336.8	333.9	332.9
65°	319.3	302.6	292.8	284.8	282.3	278.0	277.4
67.5°	257.4	247.4	240.9	235.3	232.0	231.8	231.8
70°	219.5	213.9	208.4	205.3	203.4	202.2	202.2
72.5°	186.9	182.8	178.3	176.6	176.3	175.0	174.6
75°	142.4	138.1	138.7	135.6	133.1	130.1	128.2
77.5°	100.9	97.9	97.3	96.9	94.8	94.4	95.4
80°	78.3	75.2	74.5	75.2	74.5	72.8	72.8
82.5°	59.6	57.0	56.4	56.0	55.4	56.0	55.0
85°	32.0	30.9	30.9	30.9	32.0	31.5	30.9
87.5°	16.1	15.8	16.4	16.1	16.1	15.7	16.2
90°	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	37.9	38.7	39.1	39.4	39.6	39.9	40.1
95°	70.4	71.1	71.3	71.3	71.3	71.3	71.3
97.5°	110.8	111.5	111.8	111.8	111.8	111.8	111.8
100°	139.4	139.8	140.0	140.0	140.0	140.0	140.0
102.5°	170.2	170.9	171.2	171.3	171.5	171.7	171.8
105°	216.8	217.4	218.0	218.6	219.2	219.8	220.4
107.5°	267.1	267.7	267.9	267.9	267.9	267.8	267.8
110°	299.6	299.2	299.3	299.9	300.5	301.1	301.8



TEST NUMBER: P333084-940

CATALOG NUMBER: S124RDIW-S1020D1050U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	336.0	335.9	335.9	336.1	336.2	336.3	336.4
115°	391.5	391.3	391.0	390.8	390.7	390.5	390.2
117.5°	444.3	443.7	443.2	442.7	442.4	441.9	441.6
120°	480.3	479.3	478.9	479.4	479.7	480.2	480.5
122.5°	517.4	516.7	515.9	515.2	514.5	513.8	513.1
125°	571.5	571.1	570.7	570.3	569.9	569.5	569.1
127.5°	623.0	622.6	622.2	621.9	621.6	621.3	621.0
130°	659.2	658.7	658.2	657.4	656.6	655.8	655.0
132.5°	693.1	692.7	692.3	692.1	691.7	691.3	691.1
135°	744.0	743.7	743.2	742.5	741.9	741.4	740.7
137.5°	793.2	792.6	792.5	792.6	792.7	792.8	792.9
140°	826.0	825.7	825.5	825.4	825.2	824.9	824.7
142.5°	856.8	856.8	856.7	856.7	856.7	856.6	856.6
145°	902.8	902.5	902.1	901.5	900.9	900.4	899.7
147.5°	944.6	944.4	944.2	944.1	943.9	943.6	943.4
150°	971.1	971.1	971.0	970.8	970.6	970.4	970.2
152.5°	996.4	996.8	996.8	996.3	995.8	995.2	994.8
155°	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9
157.5°	1061.6	1062.2	1062.2	1061.5	1060.8	1060.2	1059.4
160°	1080.4	1081.0	1080.8	1079.8	1078.8	1077.8	1076.7
162.5°	1097.7	1098.9	1098.9	1097.9	1096.9	1095.8	1094.8
165°	1120.2	1121.3	1121.5	1120.7	1119.9	1119.1	1118.3
167.5°	1138.9	1140.1	1140.1	1138.9	1137.6	1136.4	1135.1
170°	1149.1	1150.2	1150.1	1148.8	1147.4	1145.9	1144.5
172.5°	1156.7	1158.2	1158.1	1156.7	1155.3	1153.9	1152.4
175°	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8
177.5°	1169.2	1170.4	1170.3	1168.9	1167.7	1166.4	1165.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1

(END OF REPORT)