

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332857-935

Luminaire Tested: **S124DIW-S1195D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332857-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9026.0 lumens  
Efficiency: N/A  
Efficacy: 118.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41				
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34				
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29				
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17				
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.6	1.8
10°-20°	455.3	5.0
20°-30°	670.1	7.4
30°-40°	779.0	8.6
40°-50°	779.1	8.6
50°-60°	681.5	7.5
60°-70°	506.1	5.6
70°-80°	287.5	3.2
80°-90°	87.3	1.0
90°-100°	51.1	0.6
100°-110°	325.6	3.6
110°-120°	622.9	6.9
120°-130°	790.7	8.8
130°-140°	846.0	9.4
140°-150°	791.1	8.8
150°-160°	638.0	7.1
160°-170°	411.5	4.6
170°-180°	141.8	1.6
0°-30°	1287.0	14.3
0°-40°	2066.0	22.9
0°-60°	3526.5	39.1
0°-90°	4407.4	48.8
90°-120°	999.5	11.1
90°-150°	3427.4	38.0
90°-180°	4619.0	51.2
0°-180°	9026.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	3	15	24	31	34	7
95°	61	26	24	31	32	79
105°	336	343	348	356	318	352
115°	628	631	630	632	632	617
125°	882	886	884	888	889	787
135°	1094	1094	1098	1100	1102	843
145°	1262	1265	1265	1266	1269	788
155°	1384	1385	1382	1385	1383	638
165°	1460	1454	1454	1462	1453	412
175°	1493	1487	1488	1496	1484	142
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.3	29.5	29.9	30.1	30.5	30.7	30.8	31.0	31.2	31.3	31.6
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	14.0	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1
95°	61.4	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1
97.5°	130.4	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6
100°	183.1	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9
102.5°	242.1	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2
105°	336.1	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7
107.5°	423.4	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5
110°	482.4	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0



TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.6	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7
115°	627.6	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3
117.5°	706.9	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8
120°	760.5	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4
122.5°	810.5	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1
125°	882.3	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2
127.5°	950.1	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2
130°	993.9	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7
132.5°	1034.1	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6
135°	1094.4	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3
137.5°	1147.8	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7
140°	1182.7	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8
142.5°	1213.9	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9
145°	1262.0	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6
147.5°	1300.1	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4
150°	1327.8	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2
152.5°	1351.1	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1
155°	1383.7	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4
157.5°	1411.2	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0
160°	1427.2	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3
162.5°	1441.5	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6
165°	1459.7	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0
167.5°	1473.9	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6
170°	1482.0	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3
172.5°	1487.3	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7
175°	1493.1	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8
177.5°	1495.8	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	31.9	32.2	32.5	32.7	32.8	32.9	33.0	33.1
90°	27.6	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	26.7	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	27.6	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	29.8	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	40.7	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	145.8	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	352.9	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	436.6	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	493.5	494.0	494.5	495.1	495.8	496.6	497.3	498.1





TEST NUMBER: P332857-935

CATALOG NUMBER: S124DIW-S1195D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	548.5	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	630.9	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.6	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.4	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.0	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.1	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	998.8	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1040.9	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1098.8	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.3	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1188.6	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.4	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1265.8	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.7	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.4	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1383.5	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1439.2	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1458.0	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1471.8	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1480.3	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1485.7	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1492.0	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1494.5	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)