

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863-935

Luminaire Tested: **S124DIW-S1195D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9778.0 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45				
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38				
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27				
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20				
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	1.7
10°-20°	455.3	4.7
20°-30°	670.1	6.9
30°-40°	779.0	8.0
40°-50°	779.1	8.0
50°-60°	681.5	7.0
60°-70°	506.1	5.2
70°-80°	287.5	2.9
80°-90°	88.0	0.9
90°-100°	59.4	0.6
100°-110°	378.6	3.9
110°-120°	724.2	7.4
120°-130°	919.3	9.4
130°-140°	983.6	10.1
140°-150°	919.8	9.4
150°-160°	741.8	7.6
160°-170°	478.4	4.9
170°-180°	164.9	1.7
0°-30°	1287.0	13.2
0°-40°	2066.0	21.1
0°-60°	3526.5	36.1
0°-90°	4408.1	45.1
90°-120°	1162.1	11.9
90°-150°	3984.9	40.8
90°-180°	5370.0	54.9
0°-180°	9778.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	4	18	29	36	39	7
95°	71	30	29	36	38	92
105°	391	399	405	414	370	409
115°	730	733	732	735	735	718
125°	1026	1030	1028	1032	1034	915
135°	1272	1272	1276	1279	1282	980
145°	1467	1471	1471	1472	1475	916
155°	1609	1610	1606	1611	1608	741
165°	1697	1691	1691	1700	1689	479
175°	1736	1729	1730	1740	1726	165
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.4	29.8	30.1	30.6	30.9	31.3	31.4	31.7	31.9	32.1	32.5
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	16.4	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3
95°	71.4	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3
97.5°	151.6	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4
100°	212.9	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3
102.5°	281.5	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3
105°	390.8	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7
107.5°	492.3	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4
110°	560.9	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9
115°	729.7	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9
117.5°	821.9	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8
120°	884.2	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7
122.5°	942.4	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7
125°	1025.8	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2
127.5°	1104.7	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8
130°	1155.6	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1
132.5°	1202.3	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9
135°	1272.5	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9
137.5°	1334.6	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1
142.5°	1411.4	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2
145°	1467.2	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4
147.5°	1511.7	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9
150°	1543.9	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7
152.5°	1570.8	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1
155°	1608.8	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3
157.5°	1640.7	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0
160°	1659.4	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0
162.5°	1676.0	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5
165°	1697.0	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8
167.5°	1713.6	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7
170°	1723.0	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8
172.5°	1729.2	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0
175°	1735.9	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1
177.5°	1739.1	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	32.8	33.1	33.5	33.8	33.8	33.9	34.1	34.2
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	31.0	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	32.0	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.6	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	47.4	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	169.4	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	410.3	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	507.6	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	573.8	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P332863-935

CATALOG NUMBER: S124DIW-S1195D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.8	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	733.5	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.7	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.0	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1030.1	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.6	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.4	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.2	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1277.5	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.0	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.0	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1418.9	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1471.7	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.0	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1573.6	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1608.4	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1673.3	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1695.1	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1711.2	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1721.1	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1727.3	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1734.7	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1737.6	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)