

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332845-935

Luminaire Tested: **S124DIW-S1195D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332845-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D770U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7048.7 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	68	68	68	68	68	68	68	68	63																	
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	57	57	57	57	57	57	57	57	57	57	57	53																	
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48	48	48	48	48	48	48	48	48	48	48	48	44																	
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	43	41	41	41	41	41	41	41	41	41	41	41	41	37																	
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	35	35	35	35	35	35	35	35	35	35	35	32																	
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	31	31	31	31	31	31	31	31	31	31	31	28																	
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	27	27	27	27	27	27	27	27	27	27	27	24																	
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	24	24	24	24	24	24	24	24	24	24	24	22																	
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	29	25	22	22	22	22	22	22	22	22	22	22	22	22	19																	
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	20	20	20	20	20	20	20	20	20	20	20	17																	
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	18	18	18	18	18	18	18	18	18	18	18	16																	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.3
10°-20°	455.3	6.5
20°-30°	670.1	9.5
30°-40°	779.0	11.1
40°-50°	779.1	11.1
50°-60°	681.5	9.7
60°-70°	506.1	7.2
70°-80°	287.5	4.1
80°-90°	85.4	1.2
90°-100°	29.2	0.4
100°-110°	186.3	2.6
110°-120°	356.5	5.1
120°-130°	452.5	6.4
130°-140°	484.2	6.9
140°-150°	452.7	6.4
150°-160°	365.1	5.2
160°-170°	235.5	3.3
170°-180°	81.2	1.2
0°-30°	1287.0	18.3
0°-40°	2066.0	29.3
0°-60°	3526.5	50.0
0°-90°	4405.5	62.5
90°-120°	572.0	8.1
90°-150°	1961.4	27.8
90°-180°	2643.0	37.5
0°-180°	7048.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	2	9	14	18	19	6
95°	35	15	14	18	18	45
105°	192	196	199	204	182	201
115°	359	361	360	362	362	353
125°	505	507	506	508	509	451
135°	626	626	628	630	631	482
145°	722	724	724	725	726	451
155°	792	792	791	793	791	365
165°	835	832	832	837	832	236
175°	854	851	851	856	849	81
180°	854	854	854	854	854	



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.0	29.0	29.1	29.2	29.3	29.3	29.3	29.3	29.2	29.2	29.4
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	8.1	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4
95°	35.1	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9
97.5°	74.6	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0
100°	104.8	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7
102.5°	138.5	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4
105°	192.3	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7
107.5°	242.4	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3
110°	276.1	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.8	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0
115°	359.2	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8
117.5°	404.6	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5
120°	435.2	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5
122.5°	463.9	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5
125°	504.9	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6
127.5°	543.7	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3
130°	568.8	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5
132.5°	591.9	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6
135°	626.3	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5
137.5°	656.9	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2
140°	676.8	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8
142.5°	694.7	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1
145°	722.2	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3
147.5°	744.1	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1
150°	759.9	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8
152.5°	773.2	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3
155°	791.9	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2
157.5°	807.6	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7
160°	816.7	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1
162.5°	824.9	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8
165°	835.3	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3
167.5°	843.5	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0
170°	848.1	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0
172.5°	851.2	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1
175°	854.5	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6
177.5°	856.0	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	29.5	29.7	29.9	30.0	30.0	30.1	30.1	30.2
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	15.2	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	15.8	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.0	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	23.3	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	83.4	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	202.0	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	249.9	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.4	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P332845-935

CATALOG NUMBER: S124DIW-S1195D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.0	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.7	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.0	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.2	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.6	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.6	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	628.8	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.6	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.2	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.4	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.4	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.2	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.6	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	791.7	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	823.6	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	834.4	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	842.3	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	847.1	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	850.2	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	853.9	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	855.3	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)