

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333112-940

Luminaire Tested: **S124RDIW-S1195D1560U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333112-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9295.3 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	80	73	71	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	71	67	64	61	57	53	51	49	43	42	40	35
3	82	73	66	60	75	67	61	56	57	52	49	48	44	42	39	37	35	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.2	1.8
10°-20°	516.5	5.6
20°-30°	807.8	8.7
30°-40°	898.0	9.7
40°-50°	796.7	8.6
50°-60°	620.8	6.7
60°-70°	406.5	4.4
70°-80°	199.9	2.2
80°-90°	54.5	0.6
90°-100°	114.7	1.2
100°-110°	339.7	3.7
110°-120°	576.5	6.2
120°-130°	760.2	8.2
130°-140°	853.8	9.2
140°-150°	839.0	9.0
150°-160°	705.6	7.6
160°-170°	469.5	5.1
170°-180°	164.4	1.8
0°-30°	1495.5	16.1
0°-40°	2393.5	25.7
0°-60°	3811.0	41.0
0°-90°	4471.9	48.1
90°-120°	1030.9	11.1
90°-150°	3483.9	37.5
90°-180°	4823.0	51.9
0°-180°	9295.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	40	4	40	4	40	22
95°	106	81	106	81	106	111
105°	328	313	328	313	328	346
115°	581	586	581	586	581	574
125°	847	854	847	854	847	756
135°	1102	1101	1102	1101	1102	851
145°	1339	1338	1339	1338	1339	838
155°	1531	1533	1531	1533	1531	705
165°	1665	1669	1665	1669	1665	469
175°	1728	1736	1728	1736	1728	164
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	20.6	19.9	20.3	20.2	20.7	19.9	20.1	20.9	19.4	19.6	19.1
90°	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2	31.4	29.6	27.2
92.5°	59.7	59.3	58.9	58.6	58.2	57.5	56.4	55.4	54.3	53.2	51.5
95°	106.2	106.2	106.2	106.2	106.2	105.8	104.9	104.0	103.1	102.2	100.1
97.5°	166.5	166.5	166.5	166.5	166.5	165.9	164.9	163.8	162.6	161.6	159.2
100°	208.4	208.4	208.4	208.4	208.4	208.1	207.5	206.9	206.3	205.7	203.0
102.5°	255.7	255.5	255.3	255.0	254.8	254.2	253.4	252.5	251.7	250.9	248.4
105°	328.1	327.2	326.3	325.4	324.5	323.6	322.7	321.8	320.9	320.0	318.8
107.5°	398.5	398.6	398.7	398.7	398.8	398.4	397.5	396.7	395.8	395.0	394.8
110°	449.1	448.2	447.3	446.4	445.5	445.3	445.9	446.6	447.1	447.7	448.0



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.7	500.5	500.3	500.2	500.0	500.0	500.1	500.2	500.3	500.4	501.0
115°	580.9	581.1	581.5	581.8	582.0	582.4	582.6	582.9	583.3	583.5	584.2
117.5°	657.2	657.8	658.4	659.0	659.6	660.4	661.5	662.5	663.4	664.5	664.9
120°	715.3	714.7	714.1	713.5	712.9	713.4	714.9	716.3	717.8	719.3	720.2
122.5°	763.8	764.8	765.9	767.0	768.0	769.1	770.1	771.1	772.1	773.1	773.6
125°	847.0	847.7	848.3	848.8	849.4	850.1	850.7	851.2	851.9	852.5	852.7
127.5°	924.3	924.7	925.2	925.7	926.1	926.7	927.3	927.9	928.4	929.1	929.6
130°	974.8	976.0	977.2	978.4	979.5	980.4	981.1	981.7	982.3	982.8	982.8
132.5°	1028.6	1029.0	1029.6	1030.0	1030.5	1031.0	1031.6	1032.2	1032.9	1033.4	1033.7
135°	1102.5	1103.4	1104.3	1105.2	1106.1	1106.9	1107.5	1108.0	1108.7	1109.3	1109.3
137.5°	1180.3	1180.1	1179.9	1179.7	1179.6	1179.8	1180.6	1181.4	1182.1	1182.9	1182.5
140°	1227.6	1227.9	1228.2	1228.5	1228.8	1229.0	1229.4	1229.7	1229.9	1230.3	1230.3
142.5°	1274.9	1275.0	1275.1	1275.1	1275.1	1275.2	1275.2	1275.3	1275.4	1275.4	1275.7
145°	1339.2	1340.1	1341.0	1341.8	1342.7	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1404.3	1404.5	1404.9	1405.2	1405.4	1405.7	1406.0	1406.2	1406.4	1406.7	1406.9
150°	1444.0	1444.4	1444.7	1444.9	1445.3	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1480.6	1481.4	1482.2	1482.9	1483.7	1483.7	1483.0	1482.3	1481.6	1480.9	1480.7
155°	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4	1531.8
157.5°	1576.9	1577.9	1579.0	1579.9	1580.9	1581.0	1580.1	1579.2	1578.3	1577.4	1577.5
160°	1602.7	1604.2	1605.7	1607.2	1608.6	1609.0	1608.1	1607.2	1606.3	1605.4	1605.7
162.5°	1629.6	1631.1	1632.6	1634.1	1635.6	1635.5	1633.9	1632.3	1630.7	1629.1	1629.3
165°	1664.6	1665.7	1667.0	1668.1	1669.4	1669.0	1667.2	1665.4	1663.7	1661.9	1662.5
167.5°	1689.5	1691.4	1693.3	1695.1	1697.0	1697.0	1695.2	1693.4	1691.7	1689.9	1689.8
170°	1703.5	1705.7	1707.7	1709.9	1711.9	1712.1	1710.3	1708.5	1706.6	1704.9	1704.6
172.5°	1715.4	1717.4	1719.6	1721.6	1723.8	1723.8	1721.7	1719.8	1717.7	1715.7	1715.6
175°	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8	1728.0
177.5°	1734.2	1736.2	1738.0	1739.9	1741.9	1742.0	1740.3	1738.7	1737.0	1735.3	1735.3
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	18.6	17.6	18.3	17.7	17.6	19.2	20.2	20.2	19.1	18.1	17.0
90°	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0	7.3	10.6	13.9
92.5°	49.9	48.2	46.5	43.9	40.0	36.3	32.5	28.8	32.5	36.3	40.0
95°	98.0	95.9	93.8	91.4	88.7	86.1	83.4	80.7	83.4	86.1	88.7
97.5°	156.7	154.3	151.9	149.5	147.4	145.2	143.0	140.9	143.0	145.2	147.4
100°	200.4	197.7	194.9	193.1	191.8	190.6	189.4	188.2	189.4	190.6	191.8
102.5°	246.0	243.5	241.1	239.6	239.2	238.7	238.2	237.7	238.2	238.7	239.2
105°	317.6	316.4	315.2	314.5	314.1	313.9	313.6	313.3	313.6	313.9	314.1
107.5°	394.7	394.5	394.3	394.0	393.7	393.3	393.0	392.6	393.0	393.3	393.7
110°	448.4	448.6	449.0	448.8	448.2	447.5	447.0	446.4	447.0	447.5	448.2





TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	501.5	502.0	502.6	502.8	502.7	502.6	502.5	502.3	502.5	502.6	502.7
115°	584.7	585.3	585.9	586.2	586.2	586.2	586.2	586.2	586.2	586.2	586.2
117.5°	665.3	665.8	666.2	666.3	666.0	665.8	665.5	665.3	665.5	665.8	666.0
120°	721.1	722.0	722.9	722.7	721.6	720.4	719.2	718.0	719.2	720.4	721.6
122.5°	773.9	774.4	774.8	774.7	774.3	773.8	773.3	772.8	773.3	773.8	774.3
125°	853.0	853.4	853.6	853.8	853.8	853.8	853.8	853.8	853.8	853.8	853.8
127.5°	930.1	930.5	931.0	930.8	929.9	929.0	928.1	927.2	928.1	929.0	929.9
130°	982.8	982.8	982.8	982.4	981.5	980.6	979.7	978.8	979.7	980.6	981.5
132.5°	1033.9	1034.1	1034.4	1034.2	1033.5	1032.9	1032.2	1031.5	1032.2	1032.9	1033.5
135°	1109.3	1109.3	1109.3	1108.4	1106.6	1104.7	1103.0	1101.2	1103.0	1104.7	1106.6
137.5°	1182.0	1181.5	1181.1	1180.4	1179.6	1178.7	1177.9	1177.1	1177.9	1178.7	1179.6
140°	1230.3	1230.3	1230.3	1229.9	1229.4	1228.8	1228.2	1227.6	1228.2	1228.8	1229.4
142.5°	1275.9	1276.1	1276.4	1276.2	1275.6	1275.1	1274.4	1273.8	1274.4	1275.1	1275.6
145°	1344.0	1343.6	1343.4	1342.6	1341.4	1340.2	1339.0	1337.8	1339.0	1340.2	1341.4
147.5°	1407.1	1407.4	1407.7	1407.0	1405.6	1404.2	1402.8	1401.3	1402.8	1404.2	1405.6
150°	1445.4	1445.4	1445.4	1444.8	1443.6	1442.4	1441.2	1440.0	1441.2	1442.4	1443.6
152.5°	1480.4	1480.2	1480.0	1479.4	1478.7	1478.0	1477.3	1476.6	1477.3	1478.0	1478.7
155°	1532.0	1532.3	1532.7	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8	1532.8
157.5°	1577.5	1577.6	1577.7	1578.0	1578.5	1579.0	1579.6	1580.1	1579.6	1579.0	1578.5
160°	1606.0	1606.3	1606.6	1606.9	1607.2	1607.5	1607.8	1608.1	1607.8	1607.5	1607.2
162.5°	1629.7	1630.0	1630.2	1630.8	1631.6	1632.4	1633.2	1633.9	1633.2	1632.4	1631.6
165°	1663.0	1663.7	1664.3	1665.0	1665.9	1666.8	1667.7	1668.6	1667.7	1666.8	1665.9
167.5°	1689.7	1689.7	1689.6	1690.2	1691.5	1692.7	1694.0	1695.2	1694.0	1692.7	1691.5
170°	1704.3	1704.0	1703.7	1704.3	1705.8	1707.3	1708.8	1710.3	1708.8	1707.3	1705.8
172.5°	1715.6	1715.5	1715.4	1716.0	1717.3	1718.5	1719.8	1721.0	1719.8	1718.5	1717.3
175°	1728.3	1728.7	1728.9	1729.8	1731.3	1732.9	1734.3	1735.8	1734.3	1732.9	1731.3
177.5°	1735.3	1735.3	1735.3	1735.9	1737.1	1738.3	1739.5	1740.6	1739.5	1738.3	1737.1
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	17.7	17.7	18.2	17.5	18.5	19.0	18.8	19.2	20.1	19.4	19.5
90°	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2	35.0	36.7	38.0
92.5°	43.9	46.5	48.2	49.9	51.5	53.2	54.3	55.4	56.4	57.5	58.2
95°	91.4	93.8	95.9	98.0	100.1	102.2	103.1	104.0	104.9	105.8	106.2
97.5°	149.5	151.9	154.3	156.7	159.2	161.6	162.6	163.8	164.9	165.9	166.5
100°	193.1	194.9	197.7	200.4	203.0	205.7	206.3	206.9	207.5	208.1	208.4
102.5°	239.6	241.1	243.5	246.0	248.4	250.9	251.7	252.5	253.4	254.2	254.8
105°	314.5	315.2	316.4	317.6	318.8	320.0	320.9	321.8	322.7	323.6	324.5
107.5°	394.0	394.3	394.5	394.7	394.8	395.0	395.8	396.7	397.5	398.4	398.8
110°	448.8	449.0	448.6	448.4	448.0	447.7	447.1	446.6	445.9	445.3	445.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	502.8	502.6	502.0	501.5	501.0	500.4	500.3	500.2	500.1	500.0	500.0
115°	586.2	585.9	585.3	584.7	584.2	583.5	583.3	582.9	582.6	582.4	582.0
117.5°	666.3	666.2	665.8	665.3	664.9	664.5	663.4	662.5	661.5	660.4	659.6
120°	722.7	722.9	722.0	721.1	720.2	719.3	717.8	716.3	714.9	713.4	712.9
122.5°	774.7	774.8	774.4	773.9	773.6	773.1	772.1	771.1	770.1	769.1	768.0
125°	853.8	853.6	853.4	853.0	852.7	852.5	851.9	851.2	850.7	850.1	849.4
127.5°	930.8	931.0	930.5	930.1	929.6	929.1	928.4	927.9	927.3	926.7	926.1
130°	982.4	982.8	982.8	982.8	982.8	982.8	982.3	981.7	981.1	980.4	979.5
132.5°	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9	1032.2	1031.6	1031.0	1030.5
135°	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7	1108.0	1107.5	1106.9	1106.1
137.5°	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1	1181.4	1180.6	1179.8	1179.6
140°	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.7	1229.4	1229.0	1228.8
142.5°	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4	1275.3	1275.2	1275.2	1275.1
145°	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3	1344.0	1343.6	1343.4	1342.7
147.5°	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4	1406.2	1406.0	1405.7	1405.4
150°	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.3
152.5°	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6	1482.3	1483.0	1483.7	1483.7
155°	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2
157.5°	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3	1579.2	1580.1	1581.0	1580.9
160°	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3	1607.2	1608.1	1609.0	1608.6
162.5°	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7	1632.3	1633.9	1635.5	1635.6
165°	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7	1665.4	1667.2	1669.0	1669.4
167.5°	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7	1693.4	1695.2	1697.0	1697.0
170°	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6	1708.5	1710.3	1712.1	1711.9
172.5°	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7	1719.8	1721.7	1723.8	1723.8
175°	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2
177.5°	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0	1738.7	1740.3	1742.0	1741.9
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	20.8	20.3	19.9	20.6	19.9	20.3	20.8	19.5	19.4	20.1	19.2
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	36.7	35.0	33.2
92.5°	58.6	58.9	59.3	59.7	59.3	58.9	58.6	58.2	57.5	56.4	55.4
95°	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2	105.8	104.9	104.0
97.5°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	165.9	164.9	163.8
100°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.1	207.5	206.9
102.5°	255.0	255.3	255.5	255.7	255.5	255.3	255.0	254.8	254.2	253.4	252.5
105°	325.4	326.3	327.2	328.1	327.2	326.3	325.4	324.5	323.6	322.7	321.8
107.5°	398.7	398.7	398.6	398.5	398.6	398.7	398.7	398.8	398.4	397.5	396.7
110°	446.4	447.3	448.2	449.1	448.2	447.3	446.4	445.5	445.3	445.9	446.6



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	500.2	500.3	500.5	500.7	500.5	500.3	500.2	500.0	500.0	500.1	500.2
115°	581.8	581.5	581.1	580.9	581.1	581.5	581.8	582.0	582.4	582.6	582.9
117.5°	659.0	658.4	657.8	657.2	657.8	658.4	659.0	659.6	660.4	661.5	662.5
120°	713.5	714.1	714.7	715.3	714.7	714.1	713.5	712.9	713.4	714.9	716.3
122.5°	767.0	765.9	764.8	763.8	764.8	765.9	767.0	768.0	769.1	770.1	771.1
125°	848.8	848.3	847.7	847.0	847.7	848.3	848.8	849.4	850.1	850.7	851.2
127.5°	925.7	925.2	924.7	924.3	924.7	925.2	925.7	926.1	926.7	927.3	927.9
130°	978.4	977.2	976.0	974.8	976.0	977.2	978.4	979.5	980.4	981.1	981.7
132.5°	1030.0	1029.6	1029.0	1028.6	1029.0	1029.6	1030.0	1030.5	1031.0	1031.6	1032.2
135°	1105.2	1104.3	1103.4	1102.5	1103.4	1104.3	1105.2	1106.1	1106.9	1107.5	1108.0
137.5°	1179.7	1179.9	1180.1	1180.3	1180.1	1179.9	1179.7	1179.6	1179.8	1180.6	1181.4
140°	1228.5	1228.2	1227.9	1227.6	1227.9	1228.2	1228.5	1228.8	1229.0	1229.4	1229.7
142.5°	1275.1	1275.1	1275.0	1274.9	1275.0	1275.1	1275.1	1275.1	1275.2	1275.2	1275.3
145°	1341.8	1341.0	1340.1	1339.2	1340.1	1341.0	1341.8	1342.7	1343.4	1343.6	1344.0
147.5°	1405.2	1404.9	1404.5	1404.3	1404.5	1404.9	1405.2	1405.4	1405.7	1406.0	1406.2
150°	1444.9	1444.7	1444.4	1444.0	1444.4	1444.7	1444.9	1445.3	1445.4	1445.4	1445.4
152.5°	1482.9	1482.2	1481.4	1480.6	1481.4	1482.2	1482.9	1483.7	1483.7	1483.0	1482.3
155°	1535.0	1533.8	1532.7	1531.4	1532.7	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8
157.5°	1579.9	1579.0	1577.9	1576.9	1577.9	1579.0	1579.9	1580.9	1581.0	1580.1	1579.2
160°	1607.2	1605.7	1604.2	1602.7	1604.2	1605.7	1607.2	1608.6	1609.0	1608.1	1607.2
162.5°	1634.1	1632.6	1631.1	1629.6	1631.1	1632.6	1634.1	1635.6	1635.5	1633.9	1632.3
165°	1668.1	1667.0	1665.7	1664.6	1665.7	1667.0	1668.1	1669.4	1669.0	1667.2	1665.4
167.5°	1695.1	1693.3	1691.4	1689.5	1691.4	1693.3	1695.1	1697.0	1697.0	1695.2	1693.4
170°	1709.9	1707.7	1705.7	1703.5	1705.7	1707.7	1709.9	1711.9	1712.1	1710.3	1708.5
172.5°	1721.6	1719.6	1717.4	1715.4	1717.4	1719.6	1721.6	1723.8	1723.8	1721.7	1719.8
175°	1734.0	1732.0	1729.8	1727.8	1729.8	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0
177.5°	1739.9	1738.0	1736.2	1734.2	1736.2	1738.0	1739.9	1741.9	1742.0	1740.3	1738.7
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	18.8	19.0	18.5	17.5	18.2	17.7	17.7	17.0	18.1	19.1	20.2
90°	31.4	29.6	27.2	24.8	22.4	20.1	17.2	13.9	10.6	7.3	4.0
92.5°	54.3	53.2	51.5	49.9	48.2	46.5	43.9	40.0	36.3	32.5	28.8
95°	103.1	102.2	100.1	98.0	95.9	93.8	91.4	88.7	86.1	83.4	80.7
97.5°	162.6	161.6	159.2	156.7	154.3	151.9	149.5	147.4	145.2	143.0	140.9
100°	206.3	205.7	203.0	200.4	197.7	194.9	193.1	191.8	190.6	189.4	188.2
102.5°	251.7	250.9	248.4	246.0	243.5	241.1	239.6	239.2	238.7	238.2	237.7
105°	320.9	320.0	318.8	317.6	316.4	315.2	314.5	314.1	313.9	313.6	313.3
107.5°	395.8	395.0	394.8	394.7	394.5	394.3	394.0	393.7	393.3	393.0	392.6
110°	447.1	447.7	448.0	448.4	448.6	449.0	448.8	448.2	447.5	447.0	446.4



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.3	500.4	501.0	501.5	502.0	502.6	502.8	502.7	502.6	502.5	502.3
115°	583.3	583.5	584.2	584.7	585.3	585.9	586.2	586.2	586.2	586.2	586.2
117.5°	663.4	664.5	664.9	665.3	665.8	666.2	666.3	666.0	665.8	665.5	665.3
120°	717.8	719.3	720.2	721.1	722.0	722.9	722.7	721.6	720.4	719.2	718.0
122.5°	772.1	773.1	773.6	773.9	774.4	774.8	774.7	774.3	773.8	773.3	772.8
125°	851.9	852.5	852.7	853.0	853.4	853.6	853.8	853.8	853.8	853.8	853.8
127.5°	928.4	929.1	929.6	930.1	930.5	931.0	930.8	929.9	929.0	928.1	927.2
130°	982.3	982.8	982.8	982.8	982.8	982.8	982.4	981.5	980.6	979.7	978.8
132.5°	1032.9	1033.4	1033.7	1033.9	1034.1	1034.4	1034.2	1033.5	1032.9	1032.2	1031.5
135°	1108.7	1109.3	1109.3	1109.3	1109.3	1109.3	1108.4	1106.6	1104.7	1103.0	1101.2
137.5°	1182.1	1182.9	1182.5	1182.0	1181.5	1181.1	1180.4	1179.6	1178.7	1177.9	1177.1
140°	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.4	1228.8	1228.2	1227.6
142.5°	1275.4	1275.4	1275.7	1275.9	1276.1	1276.4	1276.2	1275.6	1275.1	1274.4	1273.8
145°	1344.3	1344.5	1344.3	1344.0	1343.6	1343.4	1342.6	1341.4	1340.2	1339.0	1337.8
147.5°	1406.4	1406.7	1406.9	1407.1	1407.4	1407.7	1407.0	1405.6	1404.2	1402.8	1401.3
150°	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1444.8	1443.6	1442.4	1441.2	1440.0
152.5°	1481.6	1480.9	1480.7	1480.4	1480.2	1480.0	1479.4	1478.7	1478.0	1477.3	1476.6
155°	1532.7	1531.4	1531.8	1532.0	1532.3	1532.7	1532.8	1532.8	1532.8	1532.8	1532.8
157.5°	1578.3	1577.4	1577.5	1577.5	1577.6	1577.7	1578.0	1578.5	1579.0	1579.6	1580.1
160°	1606.3	1605.4	1605.7	1606.0	1606.3	1606.6	1606.9	1607.2	1607.5	1607.8	1608.1
162.5°	1630.7	1629.1	1629.3	1629.7	1630.0	1630.2	1630.8	1631.6	1632.4	1633.2	1633.9
165°	1663.7	1661.9	1662.5	1663.0	1663.7	1664.3	1665.0	1665.9	1666.8	1667.7	1668.6
167.5°	1691.7	1689.9	1689.8	1689.7	1689.7	1689.6	1690.2	1691.5	1692.7	1694.0	1695.2
170°	1706.6	1704.9	1704.6	1704.3	1704.0	1703.7	1704.3	1705.8	1707.3	1708.8	1710.3
172.5°	1717.7	1715.7	1715.6	1715.6	1715.5	1715.4	1716.0	1717.3	1718.5	1719.8	1721.0
175°	1729.8	1727.8	1728.0	1728.3	1728.7	1728.9	1729.8	1731.3	1732.9	1734.3	1735.8
177.5°	1737.0	1735.3	1735.3	1735.3	1735.3	1735.3	1735.9	1737.1	1738.3	1739.5	1740.6
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	20.2	19.2	17.6	17.7	18.3	17.6	18.6	19.1	19.6	19.4	20.9
90°	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4	33.2
92.5°	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3	55.4
95°	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1	104.0
97.5°	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6	163.8
100°	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3	206.9
102.5°	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7	252.5
105°	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9	321.8
107.5°	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8	396.7
110°	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1	446.6





TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3	500.2
115°	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3	582.9
117.5°	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4	662.5
120°	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8	716.3
122.5°	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1	771.1
125°	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9	851.2
127.5°	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4	927.9
130°	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3	981.7
132.5°	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9	1032.2
135°	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7	1108.0
137.5°	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1	1181.4
140°	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9	1229.7
142.5°	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4	1275.3
145°	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3	1344.0
147.5°	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4	1406.2
150°	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6	1482.3
155°	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7	1533.8
157.5°	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3	1579.2
160°	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3	1607.2
162.5°	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7	1632.3
165°	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7	1665.4
167.5°	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7	1693.4
170°	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6	1708.5
172.5°	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7	1719.8
175°	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8	1732.0
177.5°	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0	1738.7
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	20.1	19.9	20.7	20.2	20.3	19.9	20.6
90°	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	445.9	445.3	445.5	446.4	447.3	448.2	449.1



TEST NUMBER: P333112-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)