

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333113-940

Luminaire Tested: **S124RDIW-S1195D1560U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333113-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1560U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9863.2 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	32				
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27				
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	1.8
10°-20°	487.1	4.9
20°-30°	703.4	7.1
30°-40°	797.3	8.1
40°-50°	770.0	7.8
50°-60°	640.3	6.5
60°-70°	442.1	4.5
70°-80°	224.1	2.3
80°-90°	62.7	0.6
90°-100°	61.5	0.6
100°-110°	392.1	4.0
110°-120°	750.0	7.6
120°-130°	952.1	9.7
130°-140°	1018.7	10.3
140°-150°	952.6	9.7
150°-160°	768.2	7.8
160°-170°	495.5	5.0
170°-180°	170.8	1.7
0°-30°	1365.2	13.8
0°-40°	2162.6	21.9
0°-60°	3572.8	36.2
0°-90°	4301.7	43.6
90°-120°	1203.6	12.2
90°-150°	4127.0	41.8
90°-180°	5561.0	56.4
0°-180°	9863.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	4	19	30	37	40	7
95°	74	31	30	37	39	95
105°	405	413	420	428	383	423
115°	756	759	758	761	761	743
125°	1062	1067	1065	1069	1070	948
135°	1318	1317	1322	1325	1327	1015
145°	1520	1523	1524	1525	1528	949
155°	1666	1667	1663	1668	1665	768
165°	1758	1751	1751	1760	1750	496
175°	1798	1790	1791	1802	1787	171
180°	1798	1798	1798	1798	1798	



TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	27.0	25.7	24.3	22.9	21.6	21.0	21.2	21.4	21.7	21.8	21.9
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	16.9	17.1	17.3	17.5	17.7	18.9	21.3	23.7	26.1	28.5	30.3
95°	73.9	63.8	53.7	43.5	33.3	28.4	28.7	29.0	29.2	29.6	31.4
97.5°	157.0	163.4	169.7	176.1	182.4	168.9	135.5	102.2	68.8	35.5	35.7
100°	220.5	226.0	231.3	236.7	242.0	224.1	182.9	141.6	100.4	59.2	54.1
102.5°	291.5	295.5	299.4	303.4	307.3	306.6	301.2	295.9	290.4	285.1	230.2
105°	404.7	406.5	408.3	410.2	412.0	413.6	415.1	416.6	418.0	419.5	422.2
107.5°	509.9	510.9	511.8	512.6	513.5	515.0	517.0	519.1	521.0	523.1	524.4
110°	580.9	581.8	582.7	583.6	584.5	585.9	587.6	589.4	591.2	593.0	593.6



TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	649.8	651.4	653.0	654.6	656.2	657.5	658.3	659.2	660.0	660.8	660.7
115°	755.7	756.6	757.5	758.4	759.3	759.6	759.3	759.0	758.8	758.4	759.0
117.5°	851.2	852.4	853.6	854.8	856.0	856.9	857.6	858.3	858.9	859.5	859.4
120°	915.8	916.9	918.2	919.4	920.5	921.0	920.7	920.4	920.1	919.8	920.4
122.5°	976.0	976.7	977.4	978.1	978.9	979.5	979.9	980.3	980.7	981.1	981.5
125°	1062.4	1063.5	1064.7	1066.0	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0
127.5°	1144.1	1144.4	1144.7	1145.0	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5
130°	1196.9	1197.1	1197.4	1197.7	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5
132.5°	1245.2	1245.7	1246.3	1246.9	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0
135°	1317.9	1317.5	1317.2	1317.0	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5
137.5°	1382.2	1382.2	1382.3	1382.5	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2
140°	1424.1	1424.7	1425.3	1425.8	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4
142.5°	1461.7	1462.8	1463.9	1465.0	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8
145°	1519.6	1520.5	1521.3	1522.2	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8
147.5°	1565.6	1567.2	1568.9	1570.6	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0
150°	1598.9	1600.1	1601.2	1602.5	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9
152.5°	1626.8	1627.8	1628.8	1629.7	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2
155°	1666.2	1666.4	1666.7	1667.1	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6
157.5°	1699.2	1699.1	1698.9	1698.7	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4
160°	1718.6	1717.7	1716.8	1715.9	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0
162.5°	1735.8	1734.6	1733.5	1732.4	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1
165°	1757.6	1756.0	1754.6	1753.1	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2
167.5°	1774.8	1773.3	1771.7	1770.1	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6
170°	1784.5	1782.7	1780.8	1779.1	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1
172.5°	1790.9	1789.1	1787.3	1785.6	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5
175°	1797.9	1796.1	1794.3	1792.5	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9
177.5°	1801.2	1799.5	1797.8	1796.1	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	22.1	22.2	22.3	22.6	22.9	23.3	23.6	24.0
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	32.1	33.9	35.7	36.6	36.7	36.9	37.0	37.1
95°	33.2	35.0	36.7	37.8	38.1	38.4	38.7	39.0
97.5°	35.8	36.0	36.2	36.5	36.7	37.1	37.4	37.6
100°	49.0	44.0	38.9	36.5	36.7	37.1	37.4	37.6
102.5°	175.5	120.6	65.9	38.5	38.5	38.6	38.7	38.7
105°	424.9	427.7	430.3	426.2	415.5	404.7	394.0	383.3
107.5°	525.8	527.1	528.3	529.6	530.7	531.8	533.0	534.1
110°	594.2	594.9	595.4	596.2	597.1	598.0	598.9	599.8





TEST NUMBER: P333113-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	660.6	660.4	660.3	660.8	662.0	663.1	664.2	665.4
115°	759.6	760.2	760.8	761.2	761.2	761.2	761.2	761.2
117.5°	859.3	859.2	859.1	859.0	858.8	858.7	858.6	858.4
120°	921.0	921.6	922.2	922.2	921.6	921.0	920.4	919.8
122.5°	981.9	982.2	982.6	982.4	981.9	981.2	980.6	980.1
125°	1066.8	1067.7	1068.6	1069.3	1069.5	1069.8	1070.1	1070.4
127.5°	1151.3	1151.1	1150.9	1150.7	1150.5	1150.2	1150.0	1149.8
130°	1202.8	1203.1	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5
132.5°	1253.4	1253.7	1253.9	1254.0	1253.7	1253.5	1253.3	1253.0
135°	1323.0	1323.7	1324.3	1324.9	1325.4	1326.1	1326.7	1327.2
137.5°	1389.9	1390.5	1391.2	1391.4	1391.2	1391.1	1390.9	1390.7
140°	1431.3	1432.2	1433.1	1433.6	1434.0	1434.2	1434.5	1434.9
142.5°	1469.5	1470.2	1470.8	1471.1	1471.2	1471.3	1471.3	1471.4
145°	1524.2	1524.5	1524.7	1525.3	1525.8	1526.4	1527.1	1527.6
147.5°	1572.2	1572.4	1572.7	1573.0	1573.2	1573.5	1573.9	1574.1
150°	1602.9	1602.9	1602.9	1603.1	1603.4	1603.7	1604.0	1604.3
152.5°	1629.7	1630.1	1630.7	1630.8	1630.6	1630.4	1630.2	1630.0
155°	1665.8	1667.1	1668.2	1668.4	1667.5	1666.6	1665.7	1664.8
157.5°	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8
160°	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2
162.5°	1733.0	1734.7	1736.5	1736.3	1734.4	1732.3	1730.3	1728.2
165°	1755.6	1758.0	1760.4	1760.2	1757.6	1754.9	1752.2	1749.5
167.5°	1772.3	1774.9	1777.5	1777.4	1774.3	1771.4	1768.4	1765.4
170°	1782.5	1784.9	1787.3	1787.0	1784.0	1781.0	1778.1	1775.0
172.5°	1789.0	1791.4	1793.8	1793.3	1790.1	1786.9	1783.7	1780.4
175°	1796.5	1799.3	1802.0	1801.5	1797.9	1794.3	1790.7	1787.2
177.5°	1799.6	1801.5	1803.4	1803.0	1800.1	1797.2	1794.3	1791.4
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9

(END OF REPORT)