

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333114-940

Luminaire Tested: **S124RDIW-S1195D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333114-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9125.0 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40				40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34				34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29				29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25				25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22				22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19				19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17				17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16				16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16	14				14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	1.9
10°-20°	487.1	5.3
20°-30°	703.4	7.7
30°-40°	797.3	8.7
40°-50°	770.0	8.4
50°-60°	640.3	7.0
60°-70°	442.1	4.8
70°-80°	224.1	2.5
80°-90°	62.7	0.7
90°-100°	114.7	1.3
100°-110°	339.7	3.7
110°-120°	576.5	6.3
120°-130°	760.2	8.3
130°-140°	853.8	9.4
140°-150°	839.0	9.2
150°-160°	705.6	7.7
160°-170°	469.5	5.1
170°-180°	164.4	1.8
0°-30°	1365.2	15.0
0°-40°	2162.6	23.7
0°-60°	3572.8	39.2
0°-90°	4301.7	47.1
90°-120°	1030.9	11.3
90°-150°	3483.9	38.2
90°-180°	4823.0	52.9
0°-180°	9125.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	87
90°	4	19	30	37	40	9
95°	81	93	102	106	106	90
105°	313	315	320	324	328	332
115°	586	586	584	582	581	578
125°	854	854	852	850	847	761
135°	1101	1109	1109	1106	1102	852
145°	1338	1343	1344	1343	1339	837
155°	1533	1533	1531	1536	1531	705
165°	1669	1665	1662	1669	1665	470
175°	1736	1729	1728	1736	1728	165
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	27.0	25.7	24.3	22.9	21.6	21.0	21.2	21.4	21.7	21.8	21.9
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	28.8	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3
95°	80.7	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1
97.5°	140.9	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6
100°	188.2	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3
102.5°	237.7	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7
105°	313.3	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9
107.5°	392.6	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8
110°	446.4	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1



TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.3	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3
115°	586.2	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3
117.5°	665.3	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4
120°	718.0	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8
122.5°	772.8	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1
125°	853.8	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9
127.5°	927.2	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4
130°	978.8	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3
132.5°	1031.5	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9
135°	1101.2	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7
137.5°	1177.1	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1
140°	1227.6	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9
142.5°	1273.8	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4
145°	1337.8	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1401.3	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4
150°	1440.0	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1476.6	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6
155°	1532.8	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7
157.5°	1580.1	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3
160°	1608.1	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3
162.5°	1633.9	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7
165°	1668.6	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7
167.5°	1695.2	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7
170°	1710.3	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6
172.5°	1721.0	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7
175°	1735.8	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8
177.5°	1740.6	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	22.1	22.2	22.3	22.6	22.9	23.3	23.6	24.0
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	55.4	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.0	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	163.8	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	206.9	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	252.5	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	321.8	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	396.7	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	446.6	445.9	445.3	445.5	446.4	447.3	448.2	449.1





TEST NUMBER: P333114-940

CATALOG NUMBER: S124RDIW-S1195D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.2	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.9	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	662.5	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	716.3	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	771.1	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	851.2	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.9	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.7	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1032.2	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1108.0	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1181.4	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.7	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.3	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1344.0	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.2	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1482.3	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1579.2	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1607.2	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1632.3	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1665.4	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1693.4	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1708.5	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1719.8	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1738.7	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)