

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333099-940

Luminaire Tested: **S124RDIW-S1195D770U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333099-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D770U940-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7206.8 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																												
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53																												
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	54	52	50	46																												
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39																												
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	43	40	37	34																												
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30																												
6	66	54	46	40	62	51	44	39	46	40	35	41	36	32	36	32	29	27																												
7	61	49	41	36	57	47	39	34	42	36	31	37	32	29	33	29	26	24																												
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23	21																												
9	53	41	34	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19																												
10	50	38	30	26	47	36	29	25	32	27	23	29	24	21	26	22	19	18																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.2	2.4
10°-20°	516.5	7.2
20°-30°	807.8	11.2
30°-40°	898.0	12.5
40°-50°	796.7	11.1
50°-60°	620.8	8.6
60°-70°	406.5	5.6
70°-80°	199.9	2.8
80°-90°	51.9	0.7
90°-100°	30.3	0.4
100°-110°	193.0	2.7
110°-120°	369.2	5.1
120°-130°	468.7	6.5
130°-140°	501.4	7.0
140°-150°	468.9	6.5
150°-160°	378.1	5.2
160°-170°	243.9	3.4
170°-180°	84.1	1.2
0°-30°	1495.5	20.8
0°-40°	2393.5	33.2
0°-60°	3811.0	52.9
0°-90°	4469.3	62.0
90°-120°	592.4	8.2
90°-150°	2031.4	28.2
90°-180°	2737.0	38.0
0°-180°	7206.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	20	2	20	2	20	10
95°	19	36	19	36	19	15
105°	189	199	189	199	189	165
115°	375	372	375	372	375	371
125°	527	523	527	523	527	469
135°	653	649	653	649	653	503
145°	752	748	752	748	752	470
155°	820	820	820	820	820	378
165°	861	865	861	865	861	243
175°	880	885	880	885	880	84
180°	885	885	885	885	885	



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	16.5	15.9	16.4	16.3	16.9	16.1	16.6	17.5	16.2	16.6	16.3
90°	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3	15.4	14.5	13.4
92.5°	18.3	18.2	18.2	18.1	18.0	17.6	16.7	15.8	14.9	14.0	12.8
95°	19.2	19.1	18.9	18.7	18.6	18.1	17.2	16.3	15.4	14.5	14.4
97.5°	18.5	18.4	18.3	18.1	17.9	17.8	17.7	17.7	17.6	17.5	33.9
100°	18.5	18.4	18.3	18.1	17.9	19.1	21.6	24.2	26.7	29.2	49.4
102.5°	19.1	19.0	19.0	19.0	18.9	32.5	59.4	86.4	113.3	140.4	142.9
105°	188.7	193.9	199.2	204.6	209.8	211.8	210.4	209.2	207.9	206.5	205.8
107.5°	262.9	262.3	261.8	261.3	260.6	260.1	259.4	258.8	258.2	257.4	256.5
110°	295.2	294.8	294.4	293.9	293.5	293.1	292.7	292.5	292.2	291.9	291.1



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.5	327.0	326.4	325.8	325.3	325.0	325.1	325.1	325.2	325.3	324.9
115°	374.6	374.6	374.6	374.6	374.6	374.5	374.2	373.9	373.6	373.3	373.4
117.5°	422.6	422.6	422.7	422.8	422.8	422.8	422.9	422.9	423.0	423.1	422.8
120°	452.7	453.1	453.3	453.6	453.9	453.9	453.6	453.3	453.1	452.7	452.9
122.5°	482.4	482.7	483.0	483.3	483.6	483.7	483.5	483.3	483.1	483.0	482.7
125°	526.9	526.7	526.6	526.5	526.3	526.0	525.6	525.1	524.7	524.2	524.5
127.5°	566.0	566.1	566.1	566.3	566.4	566.5	566.6	566.7	566.8	566.9	566.1
130°	592.4	592.4	592.4	592.4	592.4	592.4	592.2	592.0	591.9	591.7	591.3
132.5°	616.8	616.9	617.0	617.2	617.2	617.2	617.1	616.9	616.8	616.6	616.1
135°	653.3	653.0	652.7	652.4	652.1	651.8	651.6	651.2	650.9	650.7	650.1
137.5°	684.6	684.7	684.7	684.8	684.9	684.7	684.5	684.1	683.8	683.5	682.9
140°	706.2	706.1	706.0	705.8	705.7	705.3	704.9	704.5	704.0	703.6	703.3
142.5°	724.2	724.2	724.2	724.2	724.2	724.0	723.6	723.4	723.0	722.6	722.5
145°	751.9	751.6	751.4	751.0	750.7	750.6	750.4	750.2	750.1	749.9	749.9
147.5°	774.8	774.7	774.5	774.4	774.3	774.1	774.0	773.8	773.7	773.6	773.7
150°	789.6	789.5	789.3	789.3	789.1	789.0	789.0	789.0	789.0	789.0	789.2
152.5°	802.4	802.5	802.5	802.6	802.7	802.6	802.4	802.2	801.9	801.7	802.0
155°	819.5	819.8	820.3	820.7	821.2	821.1	820.6	819.9	819.4	818.8	819.2
157.5°	833.7	834.5	835.3	836.1	836.8	836.8	836.1	835.3	834.5	833.7	834.2
160°	843.3	844.2	845.1	845.9	846.8	846.8	845.9	845.1	844.2	843.3	843.4
162.5°	850.7	851.7	852.7	853.7	854.7	854.7	853.8	853.0	852.1	851.2	851.3
165°	861.1	862.5	863.8	865.1	866.5	866.5	865.3	864.2	863.0	861.8	861.8
167.5°	869.0	870.4	871.9	873.3	874.9	874.9	873.6	872.4	871.0	869.8	869.9
170°	873.7	875.2	876.6	878.2	879.6	879.8	878.6	877.4	876.2	875.0	874.9
172.5°	876.4	878.0	879.6	881.1	882.7	882.9	881.7	880.6	879.4	878.2	878.1
175°	879.7	881.5	883.2	884.9	886.7	887.0	885.6	884.3	883.0	881.6	881.5
177.5°	881.8	883.2	884.6	886.0	887.4	887.7	886.7	885.8	884.8	883.9	883.7
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	16.1	15.3	16.2	16.0	16.1	18.1	19.5	19.8	18.4	17.0	15.6
90°	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0	3.6	5.3	6.9
92.5°	11.7	10.5	9.4	8.6	8.6	8.6	8.5	8.4	8.5	8.6	8.6
95°	14.3	14.1	14.0	16.4	21.4	26.4	31.4	36.4	31.4	26.4	21.4
97.5°	50.3	66.7	83.1	89.8	86.7	83.6	80.4	77.3	80.4	83.6	86.7
100°	69.7	90.1	110.3	119.1	116.5	113.9	111.2	108.5	111.2	113.9	116.5
102.5°	145.6	148.3	150.9	151.2	149.4	147.4	145.4	143.5	145.4	147.4	149.4
105°	205.0	204.3	203.6	202.8	201.9	201.0	200.1	199.2	200.1	201.0	201.9
107.5°	255.5	254.5	253.5	252.8	252.4	251.9	251.5	251.0	251.5	251.9	252.4
110°	290.2	289.3	288.4	287.7	287.3	286.9	286.4	286.0	286.4	286.9	287.3





TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	324.4	324.0	323.6	323.0	322.2	321.5	320.7	319.9	320.7	321.5	322.2
115°	373.6	373.7	373.9	373.7	373.3	372.9	372.5	372.0	372.5	372.9	373.3
117.5°	422.4	422.1	421.8	421.3	420.7	420.2	419.5	419.0	419.5	420.2	420.7
120°	453.1	453.2	453.3	453.1	452.5	451.9	451.4	450.8	451.4	451.9	452.5
122.5°	482.5	482.3	482.1	481.8	481.4	481.1	480.7	480.5	480.7	481.1	481.4
125°	524.9	525.1	525.4	525.2	524.7	524.1	523.5	522.9	523.5	524.1	524.7
127.5°	565.5	564.8	564.2	563.7	563.6	563.5	563.3	563.1	563.3	563.5	563.6
130°	590.8	590.4	590.0	589.7	589.5	589.4	589.2	589.1	589.2	589.4	589.5
132.5°	615.5	614.9	614.4	613.9	613.7	613.5	613.2	613.0	613.2	613.5	613.7
135°	649.4	648.9	648.3	648.1	648.2	648.4	648.5	648.6	648.5	648.4	648.2
137.5°	682.2	681.5	680.9	680.6	680.5	680.5	680.4	680.3	680.4	680.5	680.5
140°	703.0	702.8	702.4	702.1	701.9	701.5	701.2	701.0	701.2	701.5	701.9
142.5°	722.3	722.1	721.9	721.6	721.0	720.6	720.1	719.5	720.1	720.6	721.0
145°	749.9	749.9	749.9	749.8	749.3	748.9	748.4	748.0	748.4	748.9	749.3
147.5°	773.9	774.1	774.2	773.9	773.0	772.2	771.4	770.6	771.4	772.2	773.0
150°	789.3	789.4	789.6	789.3	788.8	788.2	787.6	787.0	787.6	788.2	788.8
152.5°	802.3	802.5	802.7	802.6	802.2	801.7	801.2	800.8	801.2	801.7	802.2
155°	819.7	820.1	820.6	820.7	820.6	820.4	820.3	820.1	820.3	820.4	820.6
157.5°	834.7	835.3	835.7	836.1	836.2	836.2	836.3	836.4	836.3	836.2	836.2
160°	843.6	843.7	843.8	844.2	844.6	845.1	845.4	845.9	845.4	845.1	844.6
162.5°	851.5	851.7	851.8	852.1	852.7	853.3	853.8	854.3	853.8	853.3	852.7
165°	861.8	861.8	861.8	862.2	862.9	863.6	864.3	865.1	864.3	863.6	862.9
167.5°	870.0	870.0	870.1	870.5	871.3	872.1	872.8	873.6	872.8	872.1	871.3
170°	874.8	874.6	874.4	874.9	875.7	876.6	877.4	878.3	877.4	876.6	875.7
172.5°	877.9	877.8	877.6	878.0	878.9	879.8	880.7	881.5	880.7	879.8	878.9
175°	881.4	881.2	881.1	881.5	882.3	883.2	884.0	884.9	884.0	883.2	882.3
177.5°	883.4	883.2	883.0	883.2	884.0	884.9	885.7	886.5	885.7	884.9	884.0
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	16.0	15.6	15.9	15.0	15.8	16.1	15.6	15.8	16.6	15.6	15.7
90°	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3	17.2	18.1	18.6
92.5°	8.6	9.4	10.5	11.7	12.8	14.0	14.9	15.8	16.7	17.6	18.0
95°	16.4	14.0	14.1	14.3	14.4	14.5	15.4	16.3	17.2	18.1	18.6
97.5°	89.8	83.1	66.7	50.3	33.9	17.5	17.6	17.7	17.7	17.8	17.9
100°	119.1	110.3	90.1	69.7	49.4	29.2	26.7	24.2	21.6	19.1	17.9
102.5°	151.2	150.9	148.3	145.6	142.9	140.4	113.3	86.4	59.4	32.5	18.9
105°	202.8	203.6	204.3	205.0	205.8	206.5	207.9	209.2	210.4	211.8	209.8
107.5°	252.8	253.5	254.5	255.5	256.5	257.4	258.2	258.8	259.4	260.1	260.6
110°	287.7	288.4	289.3	290.2	291.1	291.9	292.2	292.5	292.7	293.1	293.5



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	323.0	323.6	324.0	324.4	324.9	325.3	325.2	325.1	325.1	325.0	325.3
115°	373.7	373.9	373.7	373.6	373.4	373.3	373.6	373.9	374.2	374.5	374.6
117.5°	421.3	421.8	422.1	422.4	422.8	423.1	423.0	422.9	422.9	422.8	422.8
120°	453.1	453.3	453.2	453.1	452.9	452.7	453.1	453.3	453.6	453.9	453.9
122.5°	481.8	482.1	482.3	482.5	482.7	483.0	483.1	483.3	483.5	483.7	483.6
125°	525.2	525.4	525.1	524.9	524.5	524.2	524.7	525.1	525.6	526.0	526.3
127.5°	563.7	564.2	564.8	565.5	566.1	566.9	566.8	566.7	566.6	566.5	566.4
130°	589.7	590.0	590.4	590.8	591.3	591.7	591.9	592.0	592.2	592.4	592.4
132.5°	613.9	614.4	614.9	615.5	616.1	616.6	616.8	616.9	617.1	617.2	617.2
135°	648.1	648.3	648.9	649.4	650.1	650.7	650.9	651.2	651.6	651.8	652.1
137.5°	680.6	680.9	681.5	682.2	682.9	683.5	683.8	684.1	684.5	684.7	684.9
140°	702.1	702.4	702.8	703.0	703.3	703.6	704.0	704.5	704.9	705.3	705.7
142.5°	721.6	721.9	722.1	722.3	722.5	722.6	723.0	723.4	723.6	724.0	724.2
145°	749.8	749.9	749.9	749.9	749.9	749.9	750.1	750.2	750.4	750.6	750.7
147.5°	773.9	774.2	774.1	773.9	773.7	773.6	773.7	773.8	774.0	774.1	774.3
150°	789.3	789.6	789.4	789.3	789.2	789.0	789.0	789.0	789.0	789.0	789.1
152.5°	802.6	802.7	802.5	802.3	802.0	801.7	801.9	802.2	802.4	802.6	802.7
155°	820.7	820.6	820.1	819.7	819.2	818.8	819.4	819.9	820.6	821.1	821.2
157.5°	836.1	835.7	835.3	834.7	834.2	833.7	834.5	835.3	836.1	836.8	836.8
160°	844.2	843.8	843.7	843.6	843.4	843.3	844.2	845.1	845.9	846.8	846.8
162.5°	852.1	851.8	851.7	851.5	851.3	851.2	852.1	853.0	853.8	854.7	854.7
165°	862.2	861.8	861.8	861.8	861.8	861.8	863.0	864.2	865.3	866.5	866.5
167.5°	870.5	870.1	870.0	870.0	869.9	869.8	871.0	872.4	873.6	874.9	874.9
170°	874.9	874.4	874.6	874.8	874.9	875.0	876.2	877.4	878.6	879.8	879.6
172.5°	878.0	877.6	877.8	877.9	878.1	878.2	879.4	880.6	881.7	882.9	882.7
175°	881.5	881.1	881.2	881.4	881.5	881.6	883.0	884.3	885.6	887.0	886.7
177.5°	883.2	883.0	883.2	883.4	883.7	883.9	884.8	885.8	886.7	887.7	887.4
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	16.9	16.4	15.9	16.5	15.9	16.4	16.9	15.7	15.6	16.6	15.8
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3
92.5°	18.1	18.2	18.2	18.3	18.2	18.2	18.1	18.0	17.6	16.7	15.8
95°	18.7	18.9	19.1	19.2	19.1	18.9	18.7	18.6	18.1	17.2	16.3
97.5°	18.1	18.3	18.4	18.5	18.4	18.3	18.1	17.9	17.8	17.7	17.7
100°	18.1	18.3	18.4	18.5	18.4	18.3	18.1	17.9	19.1	21.6	24.2
102.5°	19.0	19.0	19.0	19.1	19.0	19.0	19.0	18.9	32.5	59.4	86.4
105°	204.6	199.2	193.9	188.7	193.9	199.2	204.6	209.8	211.8	210.4	209.2
107.5°	261.3	261.8	262.3	262.9	262.3	261.8	261.3	260.6	260.1	259.4	258.8
110°	293.9	294.4	294.8	295.2	294.8	294.4	293.9	293.5	293.1	292.7	292.5



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	325.8	326.4	327.0	327.5	327.0	326.4	325.8	325.3	325.0	325.1	325.1
115°	374.6	374.6	374.6	374.6	374.6	374.6	374.6	374.6	374.5	374.2	373.9
117.5°	422.8	422.7	422.6	422.6	422.6	422.7	422.8	422.8	422.8	422.9	422.9
120°	453.6	453.3	453.1	452.7	453.1	453.3	453.6	453.9	453.9	453.6	453.3
122.5°	483.3	483.0	482.7	482.4	482.7	483.0	483.3	483.6	483.7	483.5	483.3
125°	526.5	526.6	526.7	526.9	526.7	526.6	526.5	526.3	526.0	525.6	525.1
127.5°	566.3	566.1	566.1	566.0	566.1	566.1	566.3	566.4	566.5	566.6	566.7
130°	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.4	592.2	592.0
132.5°	617.2	617.0	616.9	616.8	616.9	617.0	617.2	617.2	617.2	617.1	616.9
135°	652.4	652.7	653.0	653.3	653.0	652.7	652.4	652.1	651.8	651.6	651.2
137.5°	684.8	684.7	684.7	684.6	684.7	684.7	684.8	684.9	684.7	684.5	684.1
140°	705.8	706.0	706.1	706.2	706.1	706.0	705.8	705.7	705.3	704.9	704.5
142.5°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.6	723.4
145°	751.0	751.4	751.6	751.9	751.6	751.4	751.0	750.7	750.6	750.4	750.2
147.5°	774.4	774.5	774.7	774.8	774.7	774.5	774.4	774.3	774.1	774.0	773.8
150°	789.3	789.3	789.5	789.6	789.5	789.3	789.3	789.1	789.0	789.0	789.0
152.5°	802.6	802.5	802.5	802.4	802.5	802.5	802.6	802.7	802.6	802.4	802.2
155°	820.7	820.3	819.8	819.5	819.8	820.3	820.7	821.2	821.1	820.6	819.9
157.5°	836.1	835.3	834.5	833.7	834.5	835.3	836.1	836.8	836.8	836.1	835.3
160°	845.9	845.1	844.2	843.3	844.2	845.1	845.9	846.8	846.8	845.9	845.1
162.5°	853.7	852.7	851.7	850.7	851.7	852.7	853.7	854.7	854.7	853.8	853.0
165°	865.1	863.8	862.5	861.1	862.5	863.8	865.1	866.5	866.5	865.3	864.2
167.5°	873.3	871.9	870.4	869.0	870.4	871.9	873.3	874.9	874.9	873.6	872.4
170°	878.2	876.6	875.2	873.7	875.2	876.6	878.2	879.6	879.8	878.6	877.4
172.5°	881.1	879.6	878.0	876.4	878.0	879.6	881.1	882.7	882.9	881.7	880.6
175°	884.9	883.2	881.5	879.7	881.5	883.2	884.9	886.7	887.0	885.6	884.3
177.5°	886.0	884.6	883.2	881.8	883.2	884.6	886.0	887.4	887.7	886.7	885.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	15.6	16.1	15.8	15.0	15.9	15.6	16.0	15.6	17.0	18.4	19.8
90°	15.4	14.5	13.4	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0
92.5°	14.9	14.0	12.8	11.7	10.5	9.4	8.6	8.6	8.6	8.5	8.4
95°	15.4	14.5	14.4	14.3	14.1	14.0	16.4	21.4	26.4	31.4	36.4
97.5°	17.6	17.5	33.9	50.3	66.7	83.1	89.8	86.7	83.6	80.4	77.3
100°	26.7	29.2	49.4	69.7	90.1	110.3	119.1	116.5	113.9	111.2	108.5
102.5°	113.3	140.4	142.9	145.6	148.3	150.9	151.2	149.4	147.4	145.4	143.5
105°	207.9	206.5	205.8	205.0	204.3	203.6	202.8	201.9	201.0	200.1	199.2
107.5°	258.2	257.4	256.5	255.5	254.5	253.5	252.8	252.4	251.9	251.5	251.0
110°	292.2	291.9	291.1	290.2	289.3	288.4	287.7	287.3	286.9	286.4	286.0



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	325.2	325.3	324.9	324.4	324.0	323.6	323.0	322.2	321.5	320.7	319.9
115°	373.6	373.3	373.4	373.6	373.7	373.9	373.7	373.3	372.9	372.5	372.0
117.5°	423.0	423.1	422.8	422.4	422.1	421.8	421.3	420.7	420.2	419.5	419.0
120°	453.1	452.7	452.9	453.1	453.2	453.3	453.1	452.5	451.9	451.4	450.8
122.5°	483.1	483.0	482.7	482.5	482.3	482.1	481.8	481.4	481.1	480.7	480.5
125°	524.7	524.2	524.5	524.9	525.1	525.4	525.2	524.7	524.1	523.5	522.9
127.5°	566.8	566.9	566.1	565.5	564.8	564.2	563.7	563.6	563.5	563.3	563.1
130°	591.9	591.7	591.3	590.8	590.4	590.0	589.7	589.5	589.4	589.2	589.1
132.5°	616.8	616.6	616.1	615.5	614.9	614.4	613.9	613.7	613.5	613.2	613.0
135°	650.9	650.7	650.1	649.4	648.9	648.3	648.1	648.2	648.4	648.5	648.6
137.5°	683.8	683.5	682.9	682.2	681.5	680.9	680.6	680.5	680.5	680.4	680.3
140°	704.0	703.6	703.3	703.0	702.8	702.4	702.1	701.9	701.5	701.2	701.0
142.5°	723.0	722.6	722.5	722.3	722.1	721.9	721.6	721.0	720.6	720.1	719.5
145°	750.1	749.9	749.9	749.9	749.9	749.9	749.8	749.3	748.9	748.4	748.0
147.5°	773.7	773.6	773.7	773.9	774.1	774.2	773.9	773.0	772.2	771.4	770.6
150°	789.0	789.0	789.2	789.3	789.4	789.6	789.3	788.8	788.2	787.6	787.0
152.5°	801.9	801.7	802.0	802.3	802.5	802.7	802.6	802.2	801.7	801.2	800.8
155°	819.4	818.8	819.2	819.7	820.1	820.6	820.7	820.6	820.4	820.3	820.1
157.5°	834.5	833.7	834.2	834.7	835.3	835.7	836.1	836.2	836.2	836.3	836.4
160°	844.2	843.3	843.4	843.6	843.7	843.8	844.2	844.6	845.1	845.4	845.9
162.5°	852.1	851.2	851.3	851.5	851.7	851.8	852.1	852.7	853.3	853.8	854.3
165°	863.0	861.8	861.8	861.8	861.8	861.8	862.2	862.9	863.6	864.3	865.1
167.5°	871.0	869.8	869.9	870.0	870.0	870.1	870.5	871.3	872.1	872.8	873.6
170°	876.2	875.0	874.9	874.8	874.6	874.4	874.9	875.7	876.6	877.4	878.3
172.5°	879.4	878.2	878.1	877.9	877.8	877.6	878.0	878.9	879.8	880.7	881.5
175°	883.0	881.6	881.5	881.4	881.2	881.1	881.5	882.3	883.2	884.0	884.9
177.5°	884.8	883.9	883.7	883.4	883.2	883.0	883.2	884.0	884.9	885.7	886.5
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.5	18.1	16.1	16.0	16.2	15.3	16.1	16.3	16.6	16.2	17.5
90°	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3
92.5°	8.5	8.6	8.6	8.6	9.4	10.5	11.7	12.8	14.0	14.9	15.8
95°	31.4	26.4	21.4	16.4	14.0	14.1	14.3	14.4	14.5	15.4	16.3
97.5°	80.4	83.6	86.7	89.8	83.1	66.7	50.3	33.9	17.5	17.6	17.7
100°	111.2	113.9	116.5	119.1	110.3	90.1	69.7	49.4	29.2	26.7	24.2
102.5°	145.4	147.4	149.4	151.2	150.9	148.3	145.6	142.9	140.4	113.3	86.4
105°	200.1	201.0	201.9	202.8	203.6	204.3	205.0	205.8	206.5	207.9	209.2
107.5°	251.5	251.9	252.4	252.8	253.5	254.5	255.5	256.5	257.4	258.2	258.8
110°	286.4	286.9	287.3	287.7	288.4	289.3	290.2	291.1	291.9	292.2	292.5





TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	320.7	321.5	322.2	323.0	323.6	324.0	324.4	324.9	325.3	325.2	325.1
115°	372.5	372.9	373.3	373.7	373.9	373.7	373.6	373.4	373.3	373.6	373.9
117.5°	419.5	420.2	420.7	421.3	421.8	422.1	422.4	422.8	423.1	423.0	422.9
120°	451.4	451.9	452.5	453.1	453.3	453.2	453.1	452.9	452.7	453.1	453.3
122.5°	480.7	481.1	481.4	481.8	482.1	482.3	482.5	482.7	483.0	483.1	483.3
125°	523.5	524.1	524.7	525.2	525.4	525.1	524.9	524.5	524.2	524.7	525.1
127.5°	563.3	563.5	563.6	563.7	564.2	564.8	565.5	566.1	566.9	566.8	566.7
130°	589.2	589.4	589.5	589.7	590.0	590.4	590.8	591.3	591.7	591.9	592.0
132.5°	613.2	613.5	613.7	613.9	614.4	614.9	615.5	616.1	616.6	616.8	616.9
135°	648.5	648.4	648.2	648.1	648.3	648.9	649.4	650.1	650.7	650.9	651.2
137.5°	680.4	680.5	680.5	680.6	680.9	681.5	682.2	682.9	683.5	683.8	684.1
140°	701.2	701.5	701.9	702.1	702.4	702.8	703.0	703.3	703.6	704.0	704.5
142.5°	720.1	720.6	721.0	721.6	721.9	722.1	722.3	722.5	722.6	723.0	723.4
145°	748.4	748.9	749.3	749.8	749.9	749.9	749.9	749.9	749.9	750.1	750.2
147.5°	771.4	772.2	773.0	773.9	774.2	774.1	773.9	773.7	773.6	773.7	773.8
150°	787.6	788.2	788.8	789.3	789.6	789.4	789.3	789.2	789.0	789.0	789.0
152.5°	801.2	801.7	802.2	802.6	802.7	802.5	802.3	802.0	801.7	801.9	802.2
155°	820.3	820.4	820.6	820.7	820.6	820.1	819.7	819.2	818.8	819.4	819.9
157.5°	836.3	836.2	836.2	836.1	835.7	835.3	834.7	834.2	833.7	834.5	835.3
160°	845.4	845.1	844.6	844.2	843.8	843.7	843.6	843.4	843.3	844.2	845.1
162.5°	853.8	853.3	852.7	852.1	851.8	851.7	851.5	851.3	851.2	852.1	853.0
165°	864.3	863.6	862.9	862.2	861.8	861.8	861.8	861.8	861.8	863.0	864.2
167.5°	872.8	872.1	871.3	870.5	870.1	870.0	870.0	869.9	869.8	871.0	872.4
170°	877.4	876.6	875.7	874.9	874.4	874.6	874.8	874.9	875.0	876.2	877.4
172.5°	880.7	879.8	878.9	878.0	877.6	877.8	877.9	878.1	878.2	879.4	880.6
175°	884.0	883.2	882.3	881.5	881.1	881.2	881.4	881.5	881.6	883.0	884.3
177.5°	885.7	884.9	884.0	883.2	883.0	883.2	883.4	883.7	883.9	884.8	885.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9	884.9



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	16.6	16.1	16.9	16.3	16.4	15.9	16.5
90°	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	16.7	17.6	18.0	18.1	18.2	18.2	18.3
95°	17.2	18.1	18.6	18.7	18.9	19.1	19.2
97.5°	17.7	17.8	17.9	18.1	18.3	18.4	18.5
100°	21.6	19.1	17.9	18.1	18.3	18.4	18.5
102.5°	59.4	32.5	18.9	19.0	19.0	19.0	19.1
105°	210.4	211.8	209.8	204.6	199.2	193.9	188.7
107.5°	259.4	260.1	260.6	261.3	261.8	262.3	262.9
110°	292.7	293.1	293.5	293.9	294.4	294.8	295.2



TEST NUMBER: P333099-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	325.1	325.0	325.3	325.8	326.4	327.0	327.5
115°	374.2	374.5	374.6	374.6	374.6	374.6	374.6
117.5°	422.9	422.8	422.8	422.8	422.7	422.6	422.6
120°	453.6	453.9	453.9	453.6	453.3	453.1	452.7
122.5°	483.5	483.7	483.6	483.3	483.0	482.7	482.4
125°	525.6	526.0	526.3	526.5	526.6	526.7	526.9
127.5°	566.6	566.5	566.4	566.3	566.1	566.1	566.0
130°	592.2	592.4	592.4	592.4	592.4	592.4	592.4
132.5°	617.1	617.2	617.2	617.2	617.0	616.9	616.8
135°	651.6	651.8	652.1	652.4	652.7	653.0	653.3
137.5°	684.5	684.7	684.9	684.8	684.7	684.7	684.6
140°	704.9	705.3	705.7	705.8	706.0	706.1	706.2
142.5°	723.6	724.0	724.2	724.2	724.2	724.2	724.2
145°	750.4	750.6	750.7	751.0	751.4	751.6	751.9
147.5°	774.0	774.1	774.3	774.4	774.5	774.7	774.8
150°	789.0	789.0	789.1	789.3	789.3	789.5	789.6
152.5°	802.4	802.6	802.7	802.6	802.5	802.5	802.4
155°	820.6	821.1	821.2	820.7	820.3	819.8	819.5
157.5°	836.1	836.8	836.8	836.1	835.3	834.5	833.7
160°	845.9	846.8	846.8	845.9	845.1	844.2	843.3
162.5°	853.8	854.7	854.7	853.7	852.7	851.7	850.7
165°	865.3	866.5	866.5	865.1	863.8	862.5	861.1
167.5°	873.6	874.9	874.9	873.3	871.9	870.4	869.0
170°	878.6	879.8	879.6	878.2	876.6	875.2	873.7
172.5°	881.7	882.9	882.7	881.1	879.6	878.0	876.4
175°	885.6	887.0	886.7	884.9	883.2	881.5	879.7
177.5°	886.7	887.7	887.4	886.0	884.6	883.2	881.8
180°	884.9	884.9	884.9	884.9	884.9	884.9	884.9

(END OF REPORT)