

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332739-935

Luminaire Tested: **S124DIW-S350D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332739-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6732.1 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	65	73	67	63	59	51	48	45	36	34	33	23	22	21	15
3	76	67	60	54	67	59	54	49	45	41	38	32	30	28	20	19	18	12
4	69	59	52	46	61	53	46	41	40	36	32	29	26	24	18	16	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12	8
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9	7
9	46	35	28	23	41	31	25	21	24	20	16	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3971	3971	3971	3971
5°	4676	3981	3514	3981
10°	5599	3963	3163	3963
15°	6624	3924	2906	3924
20°	7377	3882	2674	3882
25°	7496	3822	2515	3822
30°	6378	3765	2466	3765
35°	4904	3671	2466	3671
40°	3822	3561	2512	3561
45°	3186	3394	2555	3394
50°	2804	3191	2641	3191
55°	2570	2949	2747	2949
60°	2407	2730	2876	2730
65°	2243	2487	2982	2487
70°	2049	2245	3050	2245
75°	1831	1978	3013	1978
80°	1534	1623	2920	1623
85°	1130	1176	2788	1176



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	0.7
10°-20°	147.7	2.2
20°-30°	234.2	3.5
30°-40°	260.7	3.9
40°-50°	237.3	3.5
50°-60°	193.9	2.9
60°-70°	138.4	2.1
70°-80°	76.2	1.1
80°-90°	25.8	0.4
90°-100°	59.4	0.9
100°-110°	378.6	5.6
110°-120°	724.2	10.8
120°-130°	919.3	13.7
130°-140°	983.6	14.6
140°-150°	919.8	13.7
150°-160°	741.8	11.0
160°-170°	478.4	7.1
170°-180°	164.9	2.4
0°-30°	429.9	6.4
0°-40°	690.5	10.3
0°-60°	1121.7	16.7
0°-90°	1362.2	20.2
90°-120°	1162.1	17.3
90°-150°	3984.9	59.2
90°-180°	5370.0	79.8
0°-180°	6732.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	492	492	492	492	492	
5°	577	491	434	491	577	59
15°	793	470	348	470	793	224
25°	842	429	282	429	842	371
35°	498	372	250	372	498	316
45°	279	297	224	297	279	220
55°	183	210	195	210	183	165
65°	117	130	156	130	117	116
75°	59	63	97	63	59	62
85°	12	13	30	13	12	16
90°	39	4	39	4	39	17
95°	38	71	38	71	38	30
105°	370	391	370	391	370	323
115°	735	730	735	730	735	727
125°	1034	1026	1034	1026	1034	920
135°	1282	1272	1282	1272	1282	986
145°	1475	1467	1475	1467	1475	922
155°	1608	1609	1608	1609	1608	741
165°	1689	1697	1689	1697	1689	477
175°	1726	1736	1726	1736	1726	164
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	523.5	523.4	521.8	521.4	520.3	518.8	518.5	515.8	510.7	508.2	507.6
5°	577.0	581.2	575.8	574.8	574.2	567.5	564.0	560.0	550.6	545.1	540.8
7.5°	641.0	641.4	639.1	637.3	632.1	626.2	617.4	608.0	596.8	585.3	576.5
10°	683.0	684.7	682.0	681.7	671.2	664.7	651.7	640.7	628.0	614.0	601.2
12.5°	727.4	725.1	723.8	715.1	713.1	701.2	686.0	674.8	655.2	639.0	622.0
15°	792.6	788.2	785.3	773.4	767.4	750.9	734.8	722.4	696.9	672.6	654.3
17.5°	831.0	835.4	828.9	823.9	808.7	797.0	780.6	754.5	734.6	704.5	681.3
20°	858.7	859.1	855.4	850.3	838.4	823.6	805.7	777.2	753.4	723.4	691.6
22.5°	866.2	866.3	864.7	860.0	850.8	839.0	820.9	797.0	768.2	735.6	703.8
25°	841.5	840.8	842.6	847.9	844.5	840.8	830.3	812.6	785.7	751.3	717.0
27.5°	750.1	755.8	766.1	779.1	791.7	801.2	803.9	800.3	783.7	755.4	719.5
30°	684.2	691.2	699.0	712.0	737.3	751.7	767.6	779.6	772.9	750.3	716.9
32.5°	611.9	613.6	625.1	639.9	663.1	690.9	716.1	740.5	748.6	736.8	708.9
35°	497.6	500.5	512.9	527.5	555.9	590.0	627.8	661.7	689.6	700.8	686.5
37.5°	406.0	414.2	423.0	438.8	463.7	494.4	533.7	577.6	619.1	647.0	651.8
40°	362.7	367.8	374.1	386.2	407.3	437.5	471.3	521.4	565.7	605.6	618.6
42.5°	328.5	331.5	335.4	346.2	362.3	392.4	423.3	467.4	511.7	559.5	581.3
45°	279.1	282.2	288.8	295.1	307.3	328.0	356.8	393.0	437.7	483.7	524.1
47.5°	243.6	245.5	249.3	256.1	266.6	280.3	303.6	333.9	375.2	420.0	463.0
50°	223.3	225.0	228.0	234.1	242.1	254.3	273.5	301.8	334.2	379.2	421.4
52.5°	207.3	208.0	210.3	214.4	220.8	231.0	246.8	270.2	300.3	340.4	382.5
55°	182.6	183.4	185.5	188.5	194.0	200.5	212.5	230.1	256.3	291.2	327.7
57.5°	162.2	162.8	164.5	165.7	170.2	175.5	184.8	197.3	217.1	246.8	279.3
60°	149.1	148.8	150.8	151.8	154.9	159.4	166.5	178.5	195.8	219.6	249.6
62.5°	136.5	135.9	137.6	139.0	140.7	144.5	150.3	159.7	173.8	195.4	221.3
65°	117.4	116.6	117.6	119.2	120.8	122.9	127.2	135.5	146.7	162.2	181.9
67.5°	98.2	99.1	99.3	100.0	101.0	103.8	106.7	112.6	120.5	132.9	149.6
70°	86.8	87.0	87.8	87.8	88.4	90.9	93.3	96.8	104.5	116.0	129.6
72.5°	75.4	76.3	75.9	76.5	77.1	78.7	80.4	83.8	90.3	98.8	110.4
75°	58.7	59.3	59.3	59.5	60.1	60.7	62.2	64.6	69.3	75.6	83.5
77.5°	42.8	42.9	43.1	43.9	43.9	44.9	45.9	47.9	50.2	54.5	59.4
80°	33.0	33.4	33.2	33.7	33.7	34.4	34.9	37.3	38.3	41.2	45.0
82.5°	24.2	24.6	24.5	25.1	25.5	25.7	26.2	27.2	28.2	30.7	32.3
85°	12.2	12.7	12.2	12.7	13.3	13.4	14.0	14.3	15.1	15.7	17.1
87.5°	11.4	11.7	11.6	11.7	11.9	11.8	11.6	11.1	11.5	11.3	11.5
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0	29.3	27.6	25.2
95°	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0	30.3	28.6	28.2
97.5°	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6	34.4	34.3	66.5
100°	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4	52.3	57.2	96.9
102.5°	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4	222.3	275.3	280.4
105°	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3	407.7	405.1	403.6
107.5°	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6	506.4	505.1	503.1
110°	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8	573.2	572.6	570.8



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8	637.9	638.1	637.2
115°	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5	732.9	732.3	732.6
117.5°	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7	829.8	829.9	829.3
120°	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1	888.4
122.5°	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0	947.7	947.4	946.9
125°	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1	1029.2	1028.4	1028.9
127.5°	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6	1111.8	1112.0	1110.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4	1161.1	1160.8	1159.9
132.5°	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2	1209.9	1209.6	1208.5
135°	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5	1276.9	1276.3	1275.2
137.5°	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0	1341.4	1340.7	1339.5
140°	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0	1381.1	1380.2	1379.7
142.5°	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9	1418.2	1417.6	1417.3
145°	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7	1471.4	1471.1	1471.1
147.5°	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0	1517.9	1517.6	1517.9
150°	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7	1547.7	1547.7	1548.0
152.5°	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6	1573.1	1572.6	1573.1
155°	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4	1607.3	1606.1	1607.1
157.5°	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5	1636.5
160°	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2	1654.5
162.5°	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3	1671.5	1669.7	1670.1
165°	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1	1692.8	1690.6	1690.6
167.5°	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2	1708.7	1706.2	1706.3
170°	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1	1718.8	1716.5	1716.2
172.5°	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3	1725.0	1722.8	1722.4
175°	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7	1732.1	1729.5	1729.2
177.5°	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6	1735.8	1733.9	1733.5
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	507.7	505.4	503.8	502.5	498.9	496.8	495.2	492.9	490.3	487.5	484.1
5°	536.5	529.6	524.5	516.8	509.5	503.3	497.0	491.3	484.4	476.8	471.3
7.5°	566.8	556.5	543.3	531.8	518.9	507.7	497.7	487.5	476.8	466.4	456.9
10°	586.1	572.8	558.1	540.8	524.5	510.1	496.6	483.5	470.9	458.3	447.5
12.5°	606.7	590.2	568.5	548.3	530.0	510.7	494.5	478.5	463.2	450.0	437.4
15°	634.6	610.7	585.7	558.5	534.5	511.9	489.7	469.5	452.4	434.8	422.6
17.5°	651.6	622.1	593.5	565.2	536.1	507.5	483.5	460.3	438.9	421.5	406.0
20°	662.9	633.5	597.9	569.6	534.9	505.6	477.9	451.9	429.6	411.0	395.1
22.5°	672.6	638.8	603.0	565.8	531.3	500.2	469.8	443.8	420.9	401.4	386.2
25°	678.0	639.0	600.3	563.2	524.1	487.2	459.7	429.1	404.7	384.1	367.8
27.5°	678.6	636.9	593.1	551.9	511.5	477.2	442.5	415.1	389.8	368.0	352.3
30°	676.7	633.4	586.3	541.7	501.1	463.8	433.6	403.9	378.0	356.4	340.1
32.5°	671.0	625.9	577.5	530.2	488.2	451.7	420.6	392.3	367.0	345.8	328.6
35°	654.5	609.8	558.4	509.2	466.2	429.4	401.2	372.5	347.2	327.1	310.6
37.5°	628.7	588.4	536.0	485.2	442.9	405.9	378.0	352.1	329.2	308.8	291.9
40°	606.2	570.8	518.1	468.6	423.0	387.8	361.7	337.9	315.2	295.8	279.7
42.5°	580.3	549.4	500.9	448.5	404.4	369.0	343.6	322.2	300.9	283.0	266.9
45°	534.1	513.7	468.0	419.6	373.7	340.3	316.1	297.3	279.4	261.8	248.4
47.5°	481.0	470.8	432.4	386.3	342.9	309.9	288.9	271.6	255.8	241.0	229.1
50°	445.2	440.3	407.2	362.7	321.2	290.2	269.0	254.1	240.6	227.6	216.4
52.5°	410.0	409.8	379.9	339.2	300.7	271.0	249.9	236.0	224.4	213.8	203.7
55°	356.2	361.9	338.5	302.2	267.8	240.8	221.9	209.5	201.3	192.6	185.0
57.5°	306.8	316.2	296.9	264.9	236.2	211.5	194.9	185.6	176.9	171.6	166.1
60°	274.5	283.4	268.4	241.5	214.4	193.2	177.5	169.1	161.6	157.9	154.0
62.5°	245.8	253.7	242.6	217.7	194.2	173.7	160.5	152.5	147.4	143.4	140.9
65°	204.8	211.5	201.9	183.8	163.6	147.3	136.6	130.2	125.4	123.7	120.8
67.5°	165.6	171.7	166.5	151.1	134.9	122.5	114.1	108.1	105.1	103.8	101.7
70°	142.2	148.4	142.8	129.4	116.9	106.6	98.6	95.1	92.1	91.5	88.7
72.5°	122.5	126.7	121.1	110.6	100.0	91.3	85.1	81.5	79.9	78.8	77.2
75°	91.9	95.6	91.9	83.8	76.2	70.1	64.8	63.4	61.6	61.0	59.9
77.5°	65.0	68.2	65.4	60.4	54.7	49.9	47.1	45.3	44.9	43.8	44.3
80°	49.7	51.7	49.1	45.6	41.2	37.9	35.9	34.9	33.7	33.2	34.0
82.5°	35.7	36.6	35.2	32.9	29.6	27.5	26.1	24.9	24.6	24.7	24.7
85°	18.5	18.3	18.2	16.1	15.1	13.7	12.8	12.7	12.4	12.8	13.3
87.5°	11.0	10.7	10.1	8.9	7.7	6.6	5.9	5.0	5.9	6.6	7.4
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4	16.5	16.7	16.9
95°	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4	61.6	51.8	42.0
97.5°	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6	157.7	163.8	170.0
100°	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9	218.2	223.3	228.5
102.5°	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5	285.3	289.1	292.9
105°	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8	392.5	394.3	396.1
107.5°	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3	493.3	494.1	495.0
110°	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9	561.8	562.7	563.5



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4	629.0	630.5	632.1
115°	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7	730.6	731.4	732.3
117.5°	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9	823.0	824.2	825.4
120°	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2	885.4	886.6	887.7
122.5°	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4	943.1	943.7	944.4
125°	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8	1026.9	1028.0	1029.2
127.5°	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7	1105.0	1105.3	1105.5
130°	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6	1155.9	1156.2	1156.5
132.5°	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3	1202.8	1203.4	1203.9
135°	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5	1272.1	1271.9	1271.6
137.5°	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6	1334.6	1334.7	1334.9
140°	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4	1412.4	1413.5	1414.5
145°	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2	1468.1	1469.0	1469.8
147.5°	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7	1513.2	1514.8	1516.5
150°	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9	1545.0	1546.1	1547.3
152.5°	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8	1571.8	1572.7	1573.6
155°	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8	1609.0	1609.3	1609.6
157.5°	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7	1640.5	1640.4	1640.2
160°	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4	1658.5	1657.7	1656.8
162.5°	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0	1674.9	1673.8	1672.8
165°	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0	1695.6	1694.2	1692.7
167.5°	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6	1712.2	1710.6	1709.2
170°	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0	1721.3	1719.5	1717.8
172.5°	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2	1727.5	1725.8	1724.1
175°	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9	1734.2	1732.5	1730.8
177.5°	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1	1737.5	1735.9	1734.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	482.4	481.0	478.9	476.0	473.5	470.9	470.2	469.2	471.2	469.6	469.1
5°	466.7	462.4	456.8	450.6	446.9	441.6	440.6	438.5	436.4	436.3	434.2
7.5°	449.9	443.6	436.4	430.0	424.0	418.2	414.4	413.6	410.6	408.8	406.8
10°	439.1	431.4	423.0	416.9	410.0	403.9	399.6	397.2	395.1	392.9	390.8
12.5°	426.5	418.2	411.3	404.7	396.5	391.8	384.8	380.6	380.1	380.1	374.9
15°	411.6	403.5	392.9	383.5	379.0	370.1	366.2	361.3	358.3	355.2	352.8
17.5°	394.7	384.5	376.3	365.5	357.0	349.8	344.7	341.8	337.2	332.9	329.8
20°	384.1	373.3	364.5	353.1	343.8	335.0	330.7	326.7	323.2	319.5	316.1
22.5°	373.3	362.1	351.4	340.3	331.6	322.3	318.1	312.6	309.4	307.3	303.8
25°	356.4	344.1	331.9	321.3	312.4	304.2	298.8	294.5	290.8	289.1	286.9
27.5°	337.9	325.8	314.0	302.0	291.8	285.9	281.5	278.3	276.1	274.0	272.9
30°	326.2	313.6	301.0	289.7	280.4	274.5	270.4	268.2	266.6	265.5	264.5
32.5°	314.4	301.9	288.6	278.4	269.9	264.7	261.6	259.3	258.6	258.2	257.8
35°	295.2	282.7	270.4	261.2	253.3	251.2	248.6	247.4	246.9	248.4	249.0
37.5°	276.8	265.1	253.8	245.0	239.7	236.8	235.8	235.9	237.4	238.6	240.0
40°	264.9	253.5	242.9	235.1	230.2	228.4	228.0	229.0	230.7	232.1	233.8
42.5°	253.3	242.1	232.5	225.2	221.8	220.1	220.3	221.4	223.7	225.4	227.8
45°	235.4	226.0	216.6	210.7	207.8	208.3	208.3	210.1	212.3	215.0	217.7
47.5°	218.4	209.0	201.3	196.3	194.8	194.5	195.6	198.0	201.2	204.5	208.2
50°	207.1	198.0	191.3	186.8	185.2	185.8	187.4	189.7	193.6	197.7	201.6
52.5°	195.4	187.3	181.1	176.9	175.7	176.8	178.5	182.0	185.5	189.9	194.5
55°	177.5	170.6	165.7	162.6	162.2	162.8	164.6	168.5	173.4	178.9	183.4
57.5°	159.6	153.8	149.3	147.2	147.4	148.0	151.0	155.6	160.8	166.7	172.5
60°	147.5	142.2	138.5	136.9	137.2	138.4	142.1	146.3	152.8	158.5	164.6
62.5°	136.1	131.5	127.9	126.5	126.2	128.9	132.4	136.8	143.4	149.7	156.4
65°	117.8	114.1	111.2	110.5	111.1	113.1	117.6	123.5	129.0	135.7	142.7
67.5°	99.9	96.9	94.9	95.2	96.0	99.0	102.7	107.8	114.1	121.1	127.9
70°	88.4	85.6	83.9	84.1	85.4	89.0	92.3	97.4	104.1	111.2	116.9
72.5°	76.7	74.8	73.4	74.2	75.4	77.9	82.1	87.1	93.1	99.7	105.7
75°	58.9	58.9	58.1	58.7	60.5	62.9	66.0	71.3	77.2	82.6	87.4
77.5°	43.7	43.2	43.7	44.5	45.5	48.5	52.0	55.8	60.2	65.5	69.6
80°	33.4	33.7	34.6	35.9	36.2	38.5	42.2	45.6	49.1	53.6	57.4
82.5°	25.1	25.3	25.8	27.4	27.8	30.2	32.5	36.0	39.2	42.2	45.4
85°	13.7	13.7	14.6	15.3	16.3	17.9	19.4	21.4	24.3	26.3	29.4
87.5°	8.5	9.0	10.2	11.0	12.0	13.2	13.9	16.0	17.0	18.2	19.9
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0	32.7	34.4	35.4
95°	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0	33.8	35.5	36.5
97.5°	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6	34.8	35.0	35.2
100°	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4	42.4	37.5	35.2
102.5°	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4	116.5	63.6	37.2
105°	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3	412.9	415.5	411.6
107.5°	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6	508.9	510.1	511.3
110°	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8	574.4	574.9	575.7



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8	637.7	637.6	638.1
115°	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5	734.0	734.6	734.9
117.5°	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7	829.6	829.5	829.4
120°	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2	889.8	890.4	890.4
122.5°	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0	948.4	948.7	948.6
125°	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1	1031.0	1031.8	1032.4
127.5°	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6	1111.5	1111.3	1111.0
130°	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4	1161.7	1161.9	1162.1
132.5°	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2	1210.5	1210.7	1210.8
135°	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5	1278.1	1278.7	1279.3
137.5°	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0	1342.6	1343.3	1343.5
140°	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0	1382.9	1383.7	1384.2
142.5°	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9	1419.5	1420.1	1420.5
145°	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7	1472.0	1472.2	1472.7
147.5°	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0	1518.3	1518.5	1518.8
150°	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7	1547.7	1547.7	1547.9
152.5°	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6	1574.0	1574.5	1574.6
155°	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4	1609.6	1610.8	1610.9
157.5°	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5
160°	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1
162.5°	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3	1675.0	1676.7	1676.5
165°	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1	1697.5	1699.8	1699.6
167.5°	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2	1713.7	1716.3	1716.1
170°	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1	1723.5	1725.8	1725.4
172.5°	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3	1729.7	1732.0	1731.6
175°	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7	1737.3	1739.9	1739.5
177.5°	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6	1739.5	1741.3	1740.9
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	468.7	468.5	467.3	467.1	467.3	468.5	468.7	469.1	469.6	471.2	469.2
5°	433.0	432.0	431.4	433.6	431.4	432.0	433.0	434.2	436.3	436.4	438.5
7.5°	406.0	405.3	403.5	402.9	403.5	405.3	406.0	406.8	408.8	410.6	413.6
10°	388.8	388.0	386.3	385.9	386.3	388.0	388.8	390.8	392.9	395.1	397.2
12.5°	372.1	370.6	370.2	370.7	370.2	370.6	372.1	374.9	380.1	380.1	380.6
15°	350.1	349.2	347.0	347.7	347.0	349.2	350.1	352.8	355.2	358.3	361.3
17.5°	328.3	327.4	324.6	327.0	324.6	327.4	328.3	329.8	332.9	337.2	341.8
20°	314.6	313.0	311.6	311.3	311.6	313.0	314.6	316.1	319.5	323.2	326.7
22.5°	301.6	300.1	300.0	298.7	300.0	300.1	301.6	303.8	307.3	309.4	312.6
25°	285.2	283.9	283.4	282.4	283.4	283.9	285.2	286.9	289.1	290.8	294.5
27.5°	272.8	272.1	271.3	271.6	271.3	272.1	272.8	272.9	274.0	276.1	278.3
30°	265.1	264.9	264.5	264.5	264.5	264.9	265.1	264.5	265.5	266.6	268.2
32.5°	258.7	258.7	259.0	259.0	259.0	258.7	258.7	257.8	258.2	258.6	259.3
35°	249.9	250.5	250.8	250.2	250.8	250.5	249.9	249.0	248.4	246.9	247.4
37.5°	241.8	242.4	243.0	243.7	243.0	242.4	241.8	240.0	238.6	237.4	235.9
40°	235.6	236.9	237.4	238.4	237.4	236.9	235.6	233.8	232.1	230.7	229.0
42.5°	229.7	231.3	232.3	232.6	232.3	231.3	229.7	227.8	225.4	223.7	221.4
45°	220.7	222.3	223.8	223.8	223.8	222.3	220.7	217.7	215.0	212.3	210.1
47.5°	211.4	213.7	215.2	215.5	215.2	213.7	211.4	208.2	204.5	201.2	198.0
50°	205.0	207.8	209.3	210.3	209.3	207.8	205.0	201.6	197.7	193.6	189.7
52.5°	198.8	201.6	203.5	204.1	203.5	201.6	198.8	194.5	189.9	185.5	182.0
55°	188.0	192.2	194.4	195.2	194.4	192.2	188.0	183.4	178.9	173.4	168.5
57.5°	178.0	181.8	184.3	184.9	184.3	181.8	178.0	172.5	166.7	160.8	155.6
60°	170.1	174.3	177.5	178.1	177.5	174.3	170.1	164.6	158.5	152.8	146.3
62.5°	162.1	166.4	169.4	170.9	169.4	166.4	162.1	156.4	149.7	143.4	136.8
65°	148.4	152.7	155.5	156.1	155.5	152.7	148.4	142.7	135.7	129.0	123.5
67.5°	133.3	137.6	139.4	140.6	139.4	137.6	133.3	127.9	121.1	114.1	107.8
70°	122.7	126.1	128.2	129.2	128.2	126.1	122.7	116.9	111.2	104.1	97.4
72.5°	110.6	114.3	116.6	116.8	116.6	114.3	110.6	105.7	99.7	93.1	87.1
75°	92.1	95.4	96.6	96.6	96.6	95.4	92.1	87.4	82.6	77.2	71.3
77.5°	72.9	74.6	76.1	76.5	76.1	74.6	72.9	69.6	65.5	60.2	55.8
80°	60.5	61.6	62.8	62.8	62.8	61.6	60.5	57.4	53.6	49.1	45.6
82.5°	47.8	48.6	49.9	49.7	49.9	48.6	47.8	45.4	42.2	39.2	36.0
85°	28.9	30.7	30.6	30.1	30.6	30.7	28.9	29.4	26.3	24.3	21.4
87.5°	20.5	20.8	21.4	21.8	21.4	20.8	20.5	19.9	18.2	17.0	16.0
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	35.5	35.6	35.7	35.8	35.7	35.6	35.5	35.4	34.4	32.7	31.0
95°	36.8	37.1	37.4	37.6	37.4	37.1	36.8	36.5	35.5	33.8	32.0
97.5°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	35.0	34.8	34.6
100°	35.5	35.8	36.1	36.3	36.1	35.8	35.5	35.2	37.5	42.4	47.4
102.5°	37.2	37.3	37.4	37.4	37.4	37.3	37.2	37.2	63.6	116.5	169.4
105°	401.2	390.8	380.5	370.1	380.5	390.8	401.2	411.6	415.5	412.9	410.3
107.5°	512.5	513.5	514.6	515.7	514.6	513.5	512.5	511.3	510.1	508.9	507.6
110°	576.5	577.4	578.2	579.1	578.2	577.4	576.5	575.7	574.9	574.4	573.8



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	639.2	640.2	641.4	642.5	641.4	640.2	639.2	638.1	637.6	637.7	637.8
115°	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.9	734.6	734.0	733.5
117.5°	829.2	829.1	829.1	828.9	829.1	829.1	829.2	829.4	829.5	829.6	829.7
120°	889.8	889.2	888.7	888.1	888.7	889.2	889.8	890.4	890.4	889.8	889.2
122.5°	948.0	947.4	946.8	946.3	946.8	947.4	948.0	948.6	948.7	948.4	948.0
125°	1032.7	1032.9	1033.3	1033.5	1033.3	1032.9	1032.7	1032.4	1031.8	1031.0	1030.1
127.5°	1110.9	1110.6	1110.3	1110.2	1110.3	1110.6	1110.9	1111.0	1111.3	1111.5	1111.6
130°	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1162.1	1161.9	1161.7	1161.4
132.5°	1210.6	1210.3	1210.1	1209.9	1210.1	1210.3	1210.6	1210.8	1210.7	1210.5	1210.2
135°	1279.8	1280.4	1281.0	1281.5	1281.0	1280.4	1279.8	1279.3	1278.7	1278.1	1277.5
137.5°	1343.3	1343.2	1343.0	1342.8	1343.0	1343.2	1343.3	1343.5	1343.3	1342.6	1342.0
140°	1384.6	1384.8	1385.1	1385.4	1385.1	1384.8	1384.6	1384.2	1383.7	1382.9	1382.0
142.5°	1420.6	1420.6	1420.6	1420.7	1420.6	1420.6	1420.6	1420.5	1420.1	1419.5	1418.9
145°	1473.3	1473.9	1474.5	1475.0	1474.5	1473.9	1473.3	1472.7	1472.2	1472.0	1471.7
147.5°	1519.1	1519.3	1519.7	1519.9	1519.7	1519.3	1519.1	1518.8	1518.5	1518.3	1518.0
150°	1548.2	1548.4	1548.8	1549.0	1548.8	1548.4	1548.2	1547.9	1547.7	1547.7	1547.7
152.5°	1574.4	1574.3	1574.1	1573.9	1574.1	1574.3	1574.4	1574.6	1574.5	1574.0	1573.6
155°	1610.1	1609.2	1608.3	1607.5	1608.3	1609.2	1610.1	1610.9	1610.8	1609.6	1608.4
157.5°	1640.0	1638.5	1637.0	1635.5	1637.0	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5
160°	1659.4	1657.7	1656.0	1654.2	1656.0	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7
162.5°	1674.6	1672.7	1670.7	1668.7	1670.7	1672.7	1674.6	1676.5	1676.7	1675.0	1673.3
165°	1697.0	1694.4	1691.9	1689.3	1691.9	1694.4	1697.0	1699.6	1699.8	1697.5	1695.1
167.5°	1713.2	1710.4	1707.4	1704.6	1707.4	1710.4	1713.2	1716.1	1716.3	1713.7	1711.2
170°	1722.6	1719.7	1716.8	1713.9	1716.8	1719.7	1722.6	1725.4	1725.8	1723.5	1721.1
172.5°	1728.5	1725.4	1722.3	1719.1	1722.3	1725.4	1728.5	1731.6	1732.0	1729.7	1727.3
175°	1735.9	1732.5	1729.1	1725.6	1729.1	1732.5	1735.9	1739.5	1739.9	1737.3	1734.7
177.5°	1738.1	1735.3	1732.5	1729.7	1732.5	1735.3	1738.1	1740.9	1741.3	1739.5	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	470.2	470.9	473.5	476.0	478.9	481.0	482.4	484.1	487.5	490.3	492.9
5°	440.6	441.6	446.9	450.6	456.8	462.4	466.7	471.3	476.8	484.4	491.3
7.5°	414.4	418.2	424.0	430.0	436.4	443.6	449.9	456.9	466.4	476.8	487.5
10°	399.6	403.9	410.0	416.9	423.0	431.4	439.1	447.5	458.3	470.9	483.5
12.5°	384.8	391.8	396.5	404.7	411.3	418.2	426.5	437.4	450.0	463.2	478.5
15°	366.2	370.1	379.0	383.5	392.9	403.5	411.6	422.6	434.8	452.4	469.5
17.5°	344.7	349.8	357.0	365.5	376.3	384.5	394.7	406.0	421.5	438.9	460.3
20°	330.7	335.0	343.8	353.1	364.5	373.3	384.1	395.1	411.0	429.6	451.9
22.5°	318.1	322.3	331.6	340.3	351.4	362.1	373.3	386.2	401.4	420.9	443.8
25°	298.8	304.2	312.4	321.3	331.9	344.1	356.4	367.8	384.1	404.7	429.1
27.5°	281.5	285.9	291.8	302.0	314.0	325.8	337.9	352.3	368.0	389.8	415.1
30°	270.4	274.5	280.4	289.7	301.0	313.6	326.2	340.1	356.4	378.0	403.9
32.5°	261.6	264.7	269.9	278.4	288.6	301.9	314.4	328.6	345.8	367.0	392.3
35°	248.6	251.2	253.3	261.2	270.4	282.7	295.2	310.6	327.1	347.2	372.5
37.5°	235.8	236.8	239.7	245.0	253.8	265.1	276.8	291.9	308.8	329.2	352.1
40°	228.0	228.4	230.2	235.1	242.9	253.5	264.9	279.7	295.8	315.2	337.9
42.5°	220.3	220.1	221.8	225.2	232.5	242.1	253.3	266.9	283.0	300.9	322.2
45°	208.3	208.3	207.8	210.7	216.6	226.0	235.4	248.4	261.8	279.4	297.3
47.5°	195.6	194.5	194.8	196.3	201.3	209.0	218.4	229.1	241.0	255.8	271.6
50°	187.4	185.8	185.2	186.8	191.3	198.0	207.1	216.4	227.6	240.6	254.1
52.5°	178.5	176.8	175.7	176.9	181.1	187.3	195.4	203.7	213.8	224.4	236.0
55°	164.6	162.8	162.2	162.6	165.7	170.6	177.5	185.0	192.6	201.3	209.5
57.5°	151.0	148.0	147.4	147.2	149.3	153.8	159.6	166.1	171.6	176.9	185.6
60°	142.1	138.4	137.2	136.9	138.5	142.2	147.5	154.0	157.9	161.6	169.1
62.5°	132.4	128.9	126.2	126.5	127.9	131.5	136.1	140.9	143.4	147.4	152.5
65°	117.6	113.1	111.1	110.5	111.2	114.1	117.8	120.8	123.7	125.4	130.2
67.5°	102.7	99.0	96.0	95.2	94.9	96.9	99.9	101.7	103.8	105.1	108.1
70°	92.3	89.0	85.4	84.1	83.9	85.6	88.4	88.7	91.5	92.1	95.1
72.5°	82.1	77.9	75.4	74.2	73.4	74.8	76.7	77.2	78.8	79.9	81.5
75°	66.0	62.9	60.5	58.7	58.1	58.9	58.9	59.9	61.0	61.6	63.4
77.5°	52.0	48.5	45.5	44.5	43.7	43.2	43.7	44.3	43.8	44.9	45.3
80°	42.2	38.5	36.2	35.9	34.6	33.7	33.4	34.0	33.2	33.7	34.9
82.5°	32.5	30.2	27.8	27.4	25.8	25.3	25.1	24.7	24.7	24.6	24.9
85°	19.4	17.9	16.3	15.3	14.6	13.7	13.7	13.3	12.8	12.4	12.7
87.5°	13.9	13.2	12.0	11.0	10.2	9.0	8.5	7.4	6.6	5.9	5.0
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	29.3	27.6	25.2	22.9	20.6	18.3	17.0	16.9	16.7	16.5	16.4
95°	30.3	28.6	28.2	28.0	27.7	27.4	32.2	42.0	51.8	61.6	71.4
97.5°	34.4	34.3	66.5	98.7	130.9	163.1	176.2	170.0	163.8	157.7	151.6
100°	52.3	57.2	96.9	136.7	176.6	216.4	233.7	228.5	223.3	218.2	212.9
102.5°	222.3	275.3	280.4	285.7	290.8	296.0	296.7	292.9	289.1	285.3	281.5
105°	407.7	405.1	403.6	402.3	400.8	399.3	397.8	396.1	394.3	392.5	390.8
107.5°	506.4	505.1	503.1	501.2	499.2	497.2	495.8	495.0	494.1	493.3	492.3
110°	573.2	572.6	570.8	569.1	567.4	565.7	564.4	563.5	562.7	561.8	560.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	637.9	638.1	637.2	636.5	635.6	634.8	633.6	632.1	630.5	629.0	627.4
115°	732.9	732.3	732.6	732.9	733.1	733.5	733.1	732.3	731.4	730.6	729.7
117.5°	829.8	829.9	829.3	828.7	828.0	827.4	826.6	825.4	824.2	823.0	821.9
120°	888.7	888.1	888.4	888.7	889.0	889.2	888.8	887.7	886.6	885.4	884.2
122.5°	947.7	947.4	946.9	946.5	946.2	945.7	945.2	944.4	943.7	943.1	942.4
125°	1029.2	1028.4	1028.9	1029.5	1030.1	1030.6	1030.4	1029.2	1028.0	1026.9	1025.8
127.5°	1111.8	1112.0	1110.6	1109.3	1108.0	1106.6	1105.9	1105.5	1105.3	1105.0	1104.7
130°	1161.1	1160.8	1159.9	1159.1	1158.2	1157.4	1156.8	1156.5	1156.2	1155.9	1155.6
132.5°	1209.9	1209.6	1208.5	1207.4	1206.3	1205.2	1204.5	1203.9	1203.4	1202.8	1202.3
135°	1276.9	1276.3	1275.2	1274.0	1272.9	1271.7	1271.3	1271.6	1271.9	1272.1	1272.5
137.5°	1341.4	1340.7	1339.5	1338.3	1337.0	1335.7	1335.0	1334.9	1334.7	1334.6	1334.6
140°	1381.1	1380.2	1379.7	1379.1	1378.5	1377.9	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1418.2	1417.6	1417.3	1416.9	1416.6	1416.3	1415.6	1414.5	1413.5	1412.4	1411.4
145°	1471.4	1471.1	1471.1	1471.1	1471.1	1471.1	1470.7	1469.8	1469.0	1468.1	1467.2
147.5°	1517.9	1517.6	1517.9	1518.2	1518.5	1518.7	1518.1	1516.5	1514.8	1513.2	1511.7
150°	1547.7	1547.7	1548.0	1548.3	1548.6	1548.9	1548.4	1547.3	1546.1	1545.0	1543.9
152.5°	1573.1	1572.6	1573.1	1573.6	1574.2	1574.8	1574.5	1573.6	1572.7	1571.8	1570.8
155°	1607.3	1606.1	1607.1	1607.9	1608.8	1609.6	1609.9	1609.6	1609.3	1609.0	1608.8
157.5°	1637.0	1635.5	1636.5	1637.4	1638.4	1639.4	1640.0	1640.2	1640.4	1640.5	1640.7
160°	1656.0	1654.2	1654.5	1654.8	1655.0	1655.4	1656.0	1656.8	1657.7	1658.5	1659.4
162.5°	1671.5	1669.7	1670.1	1670.3	1670.6	1670.9	1671.6	1672.8	1673.8	1674.9	1676.0
165°	1692.8	1690.6	1690.6	1690.6	1690.6	1690.6	1691.3	1692.7	1694.2	1695.6	1697.0
167.5°	1708.7	1706.2	1706.3	1706.5	1706.7	1706.8	1707.6	1709.2	1710.6	1712.2	1713.6
170°	1718.8	1716.5	1716.2	1716.0	1715.6	1715.4	1716.1	1717.8	1719.5	1721.3	1723.0
172.5°	1725.0	1722.8	1722.4	1722.2	1721.9	1721.6	1722.3	1724.1	1725.8	1727.5	1729.2
175°	1732.1	1729.5	1729.2	1728.9	1728.6	1728.4	1729.1	1730.8	1732.5	1734.2	1735.9
177.5°	1735.8	1733.9	1733.5	1733.0	1732.5	1732.1	1732.7	1734.2	1735.9	1737.5	1739.1
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	495.2	496.8	498.9	502.5	503.8	505.4	507.7	507.6	508.2	510.7	515.8
5°	497.0	503.3	509.5	516.8	524.5	529.6	536.5	540.8	545.1	550.6	560.0
7.5°	497.7	507.7	518.9	531.8	543.3	556.5	566.8	576.5	585.3	596.8	608.0
10°	496.6	510.1	524.5	540.8	558.1	572.8	586.1	601.2	614.0	628.0	640.7
12.5°	494.5	510.7	530.0	548.3	568.5	590.2	606.7	622.0	639.0	655.2	674.8
15°	489.7	511.9	534.5	558.5	585.7	610.7	634.6	654.3	672.6	696.9	722.4
17.5°	483.5	507.5	536.1	565.2	593.5	622.1	651.6	681.3	704.5	734.6	754.5
20°	477.9	505.6	534.9	569.6	597.9	633.5	662.9	691.6	723.4	753.4	777.2
22.5°	469.8	500.2	531.3	565.8	603.0	638.8	672.6	703.8	735.6	768.2	797.0
25°	459.7	487.2	524.1	563.2	600.3	639.0	678.0	717.0	751.3	785.7	812.6
27.5°	442.5	477.2	511.5	551.9	593.1	636.9	678.6	719.5	755.4	783.7	800.3
30°	433.6	463.8	501.1	541.7	586.3	633.4	676.7	716.9	750.3	772.9	779.6
32.5°	420.6	451.7	488.2	530.2	577.5	625.9	671.0	708.9	736.8	748.6	740.5
35°	401.2	429.4	466.2	509.2	558.4	609.8	654.5	686.5	700.8	689.6	661.7
37.5°	378.0	405.9	442.9	485.2	536.0	588.4	628.7	651.8	647.0	619.1	577.6
40°	361.7	387.8	423.0	468.6	518.1	570.8	606.2	618.6	605.6	565.7	521.4
42.5°	343.6	369.0	404.4	448.5	500.9	549.4	580.3	581.3	559.5	511.7	467.4
45°	316.1	340.3	373.7	419.6	468.0	513.7	534.1	524.1	483.7	437.7	393.0
47.5°	288.9	309.9	342.9	386.3	432.4	470.8	481.0	463.0	420.0	375.2	333.9
50°	269.0	290.2	321.2	362.7	407.2	440.3	445.2	421.4	379.2	334.2	301.8
52.5°	249.9	271.0	300.7	339.2	379.9	409.8	410.0	382.5	340.4	300.3	270.2
55°	221.9	240.8	267.8	302.2	338.5	361.9	356.2	327.7	291.2	256.3	230.1
57.5°	194.9	211.5	236.2	264.9	296.9	316.2	306.8	279.3	246.8	217.1	197.3
60°	177.5	193.2	214.4	241.5	268.4	283.4	274.5	249.6	219.6	195.8	178.5
62.5°	160.5	173.7	194.2	217.7	242.6	253.7	245.8	221.3	195.4	173.8	159.7
65°	136.6	147.3	163.6	183.8	201.9	211.5	204.8	181.9	162.2	146.7	135.5
67.5°	114.1	122.5	134.9	151.1	166.5	171.7	165.6	149.6	132.9	120.5	112.6
70°	98.6	106.6	116.9	129.4	142.8	148.4	142.2	129.6	116.0	104.5	96.8
72.5°	85.1	91.3	100.0	110.6	121.1	126.7	122.5	110.4	98.8	90.3	83.8
75°	64.8	70.1	76.2	83.8	91.9	95.6	91.9	83.5	75.6	69.3	64.6
77.5°	47.1	49.9	54.7	60.4	65.4	68.2	65.0	59.4	54.5	50.2	47.9
80°	35.9	37.9	41.2	45.6	49.1	51.7	49.7	45.0	41.2	38.3	37.3
82.5°	26.1	27.5	29.6	32.9	35.2	36.6	35.7	32.3	30.7	28.2	27.2
85°	12.8	13.7	15.1	16.1	18.2	18.3	18.5	17.1	15.7	15.1	14.3
87.5°	5.9	6.6	7.7	8.9	10.1	10.7	11.0	11.5	11.3	11.5	11.1
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3	31.0
95°	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3	32.0
97.5°	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4	34.6
100°	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3	47.4
102.5°	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3	169.4
105°	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7	410.3
107.5°	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4	507.6
110°	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2	573.8



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9	637.8
115°	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9	733.5
117.5°	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8	829.7
120°	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7	889.2
122.5°	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7	948.0
125°	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2	1030.1
127.5°	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8	1111.6
130°	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1	1161.4
132.5°	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9	1210.2
135°	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9	1277.5
137.5°	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4	1342.0
140°	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1	1382.0
142.5°	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2	1418.9
145°	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4	1471.7
147.5°	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9	1518.0
150°	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7	1547.7
152.5°	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1	1573.6
155°	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3	1608.4
157.5°	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0	1638.5
160°	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0	1657.7
162.5°	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5	1673.3
165°	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8	1695.1
167.5°	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7	1711.2
170°	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8	1721.1
172.5°	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0	1727.3
175°	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1	1734.7
177.5°	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8	1737.6
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	518.5	518.8	520.3	521.4	521.8	523.4	523.5
5°	564.0	567.5	574.2	574.8	575.8	581.2	577.0
7.5°	617.4	626.2	632.1	637.3	639.1	641.4	641.0
10°	651.7	664.7	671.2	681.7	682.0	684.7	683.0
12.5°	686.0	701.2	713.1	715.1	723.8	725.1	727.4
15°	734.8	750.9	767.4	773.4	785.3	788.2	792.6
17.5°	780.6	797.0	808.7	823.9	828.9	835.4	831.0
20°	805.7	823.6	838.4	850.3	855.4	859.1	858.7
22.5°	820.9	839.0	850.8	860.0	864.7	866.3	866.2
25°	830.3	840.8	844.5	847.9	842.6	840.8	841.5
27.5°	803.9	801.2	791.7	779.1	766.1	755.8	750.1
30°	767.6	751.7	737.3	712.0	699.0	691.2	684.2
32.5°	716.1	690.9	663.1	639.9	625.1	613.6	611.9
35°	627.8	590.0	555.9	527.5	512.9	500.5	497.6
37.5°	533.7	494.4	463.7	438.8	423.0	414.2	406.0
40°	471.3	437.5	407.3	386.2	374.1	367.8	362.7
42.5°	423.3	392.4	362.3	346.2	335.4	331.5	328.5
45°	356.8	328.0	307.3	295.1	288.8	282.2	279.1
47.5°	303.6	280.3	266.6	256.1	249.3	245.5	243.6
50°	273.5	254.3	242.1	234.1	228.0	225.0	223.3
52.5°	246.8	231.0	220.8	214.4	210.3	208.0	207.3
55°	212.5	200.5	194.0	188.5	185.5	183.4	182.6
57.5°	184.8	175.5	170.2	165.7	164.5	162.8	162.2
60°	166.5	159.4	154.9	151.8	150.8	148.8	149.1
62.5°	150.3	144.5	140.7	139.0	137.6	135.9	136.5
65°	127.2	122.9	120.8	119.2	117.6	116.6	117.4
67.5°	106.7	103.8	101.0	100.0	99.3	99.1	98.2
70°	93.3	90.9	88.4	87.8	87.8	87.0	86.8
72.5°	80.4	78.7	77.1	76.5	75.9	76.3	75.4
75°	62.2	60.7	60.1	59.5	59.3	59.3	58.7
77.5°	45.9	44.9	43.9	43.9	43.1	42.9	42.8
80°	34.9	34.4	33.7	33.7	33.2	33.4	33.0
82.5°	26.2	25.7	25.5	25.1	24.5	24.6	24.2
85°	14.0	13.4	13.3	12.7	12.2	12.7	12.2
87.5°	11.6	11.8	11.9	11.7	11.6	11.7	11.4
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P332739-935

CATALOG NUMBER: S124DIW-S350D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)