

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333100-940

Luminaire Tested: **S124RDIW-S1195D770U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333100-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D770U940-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6843.4 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65								
1	102	98	94	91	96	92	89	86	82	79	77	72	70	68	63	62	61	56								
2	93	86	80	75	87	81	76	71	72	68	65	64	61	58	56	54	52	48								
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41								
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36								
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	32								
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	34	30	28								
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25								
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22								
9	54	41	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20								
10	50	38	31	26	47	36	30	25	33	28	24	30	25	22	27	23	20	18								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14266	14266	14266	14266
5°	16546	14309	12647	14309
10°	19575	14246	11287	14246
15°	22612	14114	9699	14114
20°	25175	13933	8771	13933
25°	25989	13755	8143	13755
30°	22750	13539	7764	13539
35°	17710	13219	7535	13219
40°	13281	12853	7413	12853
45°	10485	12265	7348	12265
50°	8852	11588	7135	11588
55°	7716	10842	6753	10842
60°	6943	10070	5977	10070
65°	6120	9234	5140	9234
70°	5511	8368	4638	8368
75°	4619	7417	3952	7417
80°	3905	6323	3705	6323
85°	3298	4946	3298	4946



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	2.5
10°-20°	516.5	7.5
20°-30°	807.8	11.8
30°-40°	898.0	13.1
40°-50°	796.7	11.6
50°-60°	620.8	9.1
60°-70°	406.5	5.9
70°-80°	199.9	2.9
80°-90°	51.9	0.8
90°-100°	56.4	0.8
100°-110°	167.2	2.4
110°-120°	283.8	4.1
120°-130°	374.2	5.5
130°-140°	420.2	6.1
140°-150°	413.0	6.0
150°-160°	347.3	5.1
160°-170°	231.1	3.4
170°-180°	80.9	1.2
0°-30°	1495.5	21.9
0°-40°	2393.5	35.0
0°-60°	3811.0	55.7
0°-90°	4469.3	65.3
90°-120°	507.4	7.4
90°-150°	1714.8	25.1
90°-180°	2374.0	34.7
0°-180°	6843.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1767	1767	1767	1767	1767	
5°	2042	1766	1561	1766	2042	207
15°	2706	1689	1160	1689	2706	769
25°	2918	1544	914	1544	2918	1294
35°	1797	1341	765	1341	1797	1126
45°	918	1074	644	1074	918	727
55°	548	770	480	770	548	499
65°	320	483	269	483	320	322
75°	148	238	127	238	148	163
85°	36	53	36	53	36	41
90°	20	2	20	2	20	12
95°	52	40	52	40	52	54
105°	162	154	162	154	162	170
115°	286	289	286	289	286	283
125°	417	420	417	420	417	372
135°	543	542	543	542	543	419
145°	659	658	659	658	659	412
155°	754	754	754	754	754	347
165°	819	821	819	821	819	231
175°	850	854	850	854	850	81
180°	856	856	856	856	856	



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1863.9	1869.0	1863.9	1863.3	1857.6	1855.9	1853.6	1846.2	1832.6	1824.6	1826.3
5°	2041.8	2059.7	2049.7	2048.3	2032.7	2017.0	2007.0	1984.2	1960.0	1943.7	1930.1
7.5°	2247.7	2258.0	2251.7	2241.8	2216.4	2202.1	2179.0	2148.9	2105.5	2072.3	2042.0
10°	2387.9	2396.4	2393.6	2375.1	2356.5	2318.8	2297.5	2255.5	2200.7	2157.2	2116.7
12.5°	2525.7	2534.9	2509.8	2510.6	2475.6	2445.9	2412.0	2359.1	2295.8	2239.8	2189.0
15°	2705.5	2694.0	2694.0	2679.8	2640.6	2599.3	2564.5	2508.9	2429.2	2362.2	2291.8
17.5°	2846.1	2850.1	2844.2	2810.7	2779.9	2737.2	2673.3	2608.4	2534.4	2444.5	2372.5
20°	2930.4	2930.4	2924.0	2901.2	2861.3	2815.8	2746.7	2676.2	2582.2	2491.8	2410.7
22.5°	2964.6	2966.8	2959.3	2940.5	2904.7	2860.2	2801.4	2729.8	2633.0	2531.1	2430.6
25°	2917.6	2931.1	2932.5	2927.6	2916.9	2889.8	2839.3	2765.9	2679.1	2568.8	2460.5
27.5°	2678.6	2695.7	2710.7	2735.3	2768.0	2785.2	2787.4	2750.1	2674.3	2568.1	2459.2
30°	2440.5	2454.8	2501.1	2561.6	2608.6	2651.3	2688.3	2698.3	2655.6	2560.2	2445.5
32.5°	2176.3	2195.7	2241.9	2307.0	2385.3	2457.6	2540.8	2583.2	2582.1	2524.9	2418.8
35°	1797.0	1811.2	1854.0	1922.3	2016.2	2123.8	2255.5	2358.0	2427.8	2422.8	2358.0
37.5°	1449.2	1465.3	1508.5	1565.1	1656.3	1789.4	1916.8	2058.1	2187.1	2259.6	2237.9
40°	1260.2	1260.9	1302.9	1361.3	1446.7	1562.7	1701.6	1858.1	2002.0	2119.5	2142.2
42.5°	1110.9	1111.1	1138.8	1201.8	1263.3	1372.5	1505.0	1660.5	1828.9	1964.5	2024.9
45°	918.4	924.8	947.6	985.3	1033.8	1126.3	1232.3	1376.9	1565.6	1726.4	1826.8
47.5°	777.8	787.1	801.6	832.4	871.0	932.6	1020.4	1150.2	1303.7	1480.7	1623.5
50°	704.8	706.2	724.8	741.8	775.3	824.5	901.3	1009.5	1150.5	1320.6	1479.4
52.5°	642.2	641.9	653.0	674.7	701.9	740.1	802.2	900.7	1025.7	1178.3	1342.2
55°	548.2	551.8	560.3	577.4	598.1	625.1	674.2	748.2	846.5	976.8	1125.6
57.5°	476.7	478.6	485.3	492.5	511.5	531.1	568.0	619.4	702.3	809.0	947.6
60°	430.0	430.7	432.8	443.5	458.5	477.0	501.9	545.4	615.1	712.7	822.3
62.5°	384.4	385.8	389.1	396.8	408.4	421.2	447.3	482.1	539.9	623.2	722.0
65°	320.4	321.1	326.1	329.0	338.1	349.6	368.8	392.3	432.1	501.9	576.7
67.5°	267.7	267.7	268.0	271.8	278.2	285.8	297.3	316.1	346.2	389.1	455.0
70°	233.5	233.5	235.0	237.1	240.7	247.0	253.4	267.7	289.8	324.7	375.2
72.5°	201.6	202.2	203.6	204.0	205.9	211.2	215.9	225.0	241.4	267.7	308.5
75°	148.1	150.3	153.8	156.7	160.2	159.4	164.4	170.1	175.1	190.8	214.3
77.5°	110.2	109.1	109.5	111.9	112.4	113.1	116.6	121.0	124.8	132.2	140.5
80°	84.0	84.0	86.1	86.9	86.1	86.9	90.4	92.6	94.0	96.8	104.7
82.5°	63.5	64.6	63.9	64.6	65.1	65.8	68.8	69.2	70.6	71.8	75.1
85°	35.6	36.3	37.0	35.6	35.6	35.6	37.0	37.7	39.1	38.4	39.9
87.5°	16.5	15.9	16.4	16.3	16.9	16.1	16.6	17.5	16.2	16.6	16.3
90°	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3	15.4	14.5	13.4
92.5°	29.4	29.2	29.1	28.9	28.7	28.4	27.8	27.3	26.8	26.2	25.4
95°	52.3	52.3	52.3	52.3	52.3	52.1	51.6	51.2	50.7	50.3	49.3
97.5°	81.9	81.9	81.9	81.9	81.9	81.7	81.1	80.6	80.1	79.5	78.4
100°	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.8	101.6	101.3	100.0
102.5°	125.9	125.7	125.6	125.6	125.4	125.1	124.8	124.3	123.9	123.5	122.3
105°	161.5	161.0	160.6	160.2	159.7	159.3	158.8	158.4	157.9	157.5	156.9
107.5°	196.2	196.2	196.3	196.3	196.3	196.1	195.6	195.3	194.8	194.5	194.4
110°	221.1	220.6	220.2	219.7	219.3	219.2	219.5	219.8	220.1	220.3	220.5



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	246.5	246.4	246.3	246.2	246.1	246.1	246.1	246.2	246.3	246.3	246.6
115°	285.9	286.1	286.2	286.3	286.5	286.6	286.8	287.0	287.0	287.2	287.5
117.5°	323.5	323.8	324.0	324.4	324.7	325.0	325.6	326.1	326.5	327.1	327.3
120°	352.0	351.8	351.5	351.2	350.9	351.2	351.9	352.6	353.3	354.1	354.5
122.5°	375.9	376.5	376.9	377.5	378.0	378.5	379.1	379.5	380.0	380.6	380.8
125°	417.0	417.2	417.5	417.9	418.1	418.4	418.7	419.0	419.3	419.5	419.7
127.5°	455.0	455.1	455.4	455.7	455.8	456.1	456.5	456.7	457.0	457.4	457.5
130°	479.8	480.4	481.0	481.6	482.1	482.6	482.9	483.2	483.5	483.8	483.8
132.5°	506.3	506.5	506.8	507.0	507.2	507.5	507.8	508.1	508.4	508.6	508.8
135°	542.7	543.1	543.6	544.0	544.5	544.8	545.1	545.4	545.7	546.0	546.0
137.5°	580.9	580.9	580.8	580.7	580.6	580.8	581.1	581.5	581.8	582.3	582.0
140°	604.2	604.4	604.5	604.7	604.8	604.9	605.1	605.3	605.4	605.6	605.6
142.5°	627.5	627.6	627.6	627.6	627.7	627.7	627.7	627.8	627.8	627.8	627.9
145°	659.2	659.6	660.0	660.5	660.9	661.2	661.4	661.6	661.6	661.8	661.6
147.5°	691.2	691.3	691.5	691.6	691.8	691.9	692.1	692.1	692.2	692.4	692.5
150°	710.8	711.0	711.1	711.2	711.4	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	728.8	729.2	729.6	730.0	730.3	730.3	730.0	729.6	729.2	728.9	728.8
155°	753.9	754.4	755.0	755.5	756.2	756.2	755.5	755.0	754.4	753.9	753.9
157.5°	776.1	776.7	777.2	777.7	778.2	778.2	777.8	777.3	776.9	776.4	776.5
160°	788.9	789.6	790.3	791.1	791.8	792.0	791.6	791.1	790.7	790.2	790.3
162.5°	802.1	802.9	803.6	804.3	805.0	805.0	804.2	803.4	802.6	801.8	802.0
165°	819.3	819.9	820.5	821.1	821.7	821.5	820.6	819.7	818.9	818.0	818.3
167.5°	831.6	832.6	833.5	834.4	835.3	835.3	834.4	833.6	832.7	831.8	831.7
170°	838.6	839.5	840.6	841.6	842.7	842.8	841.9	841.0	840.1	839.2	839.0
172.5°	844.4	845.3	846.4	847.4	848.5	848.5	847.5	846.5	845.5	844.5	844.5
175°	850.4	851.5	852.5	853.5	854.5	854.5	853.5	852.5	851.5	850.4	850.6
177.5°	853.6	854.5	855.5	856.4	857.4	857.5	856.6	855.8	855.0	854.2	854.2
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1820.6	1812.7	1808.7	1799.6	1788.7	1783.0	1777.9	1770.5	1760.8	1750.5	1743.1
5°	1913.0	1896.0	1874.6	1849.0	1826.1	1804.1	1784.8	1765.7	1743.6	1720.8	1698.0
7.5°	2007.9	1974.2	1938.0	1896.0	1855.0	1817.9	1783.7	1751.0	1714.0	1680.8	1650.6
10°	2073.9	2028.4	1977.8	1924.4	1871.0	1824.7	1779.1	1737.9	1692.3	1651.7	1617.6
12.5°	2127.4	2073.9	2013.1	1946.6	1882.4	1826.4	1774.1	1720.2	1668.4	1624.4	1578.9
15°	2216.3	2143.0	2061.1	1981.4	1898.1	1821.9	1751.4	1688.7	1629.7	1567.7	1524.3
17.5°	2277.4	2190.4	2090.9	1995.0	1896.7	1806.8	1725.5	1650.9	1582.7	1519.5	1467.8
20°	2313.8	2217.7	2107.4	1998.4	1888.1	1792.0	1704.4	1621.8	1551.3	1483.0	1429.6
22.5°	2334.3	2227.9	2107.4	1993.3	1879.0	1774.9	1678.7	1592.8	1516.0	1447.7	1388.6
25°	2340.9	2227.0	2103.8	1972.8	1847.5	1737.1	1637.4	1544.2	1458.7	1390.4	1327.8
27.5°	2331.8	2197.6	2071.5	1937.1	1807.8	1691.5	1586.8	1488.8	1403.3	1329.9	1265.7
30°	2318.1	2174.3	2039.0	1899.5	1768.4	1656.7	1546.3	1452.4	1363.4	1287.2	1222.4
32.5°	2288.5	2145.8	2000.3	1857.3	1724.7	1609.4	1504.8	1410.2	1322.9	1245.1	1176.3
35°	2229.8	2085.3	1927.3	1780.6	1650.3	1530.7	1432.4	1341.3	1258.0	1174.7	1102.1
37.5°	2152.5	2004.8	1847.6	1687.0	1556.6	1443.7	1353.5	1268.0	1186.7	1110.6	1030.2
40°	2079.6	1945.1	1782.7	1623.3	1489.4	1380.5	1297.2	1219.6	1137.7	1062.2	981.8
42.5°	1991.4	1876.7	1712.7	1552.6	1420.5	1315.5	1238.0	1162.1	1087.6	1014.4	930.5
45°	1844.0	1757.1	1603.3	1449.6	1316.4	1212.5	1141.3	1074.3	1008.8	939.1	860.1
47.5°	1675.1	1616.2	1483.5	1326.1	1202.9	1109.4	1040.6	985.9	930.5	860.8	791.4
50°	1557.7	1520.0	1391.9	1248.0	1130.6	1044.5	973.9	922.7	876.4	809.5	747.5
52.5°	1432.4	1412.4	1304.1	1166.6	1053.1	968.7	908.5	862.3	815.5	759.9	702.0
55°	1241.6	1252.3	1160.5	1041.6	934.8	863.6	808.8	770.3	730.5	683.5	638.6
57.5°	1046.6	1085.6	1024.0	919.5	819.5	753.7	712.4	680.0	646.6	607.6	569.3
60°	929.8	962.5	927.6	835.8	748.2	687.1	648.6	623.7	590.2	554.6	525.4
62.5°	815.9	851.0	830.3	756.1	674.8	622.1	588.2	565.0	540.1	509.1	478.8
65°	672.8	695.5	685.6	634.4	576.7	531.8	500.5	483.4	460.7	437.8	410.8
67.5°	515.3	559.3	553.5	526.3	476.4	441.4	420.9	405.8	385.0	368.1	349.7
70°	423.7	464.2	463.5	441.4	414.4	381.6	367.4	354.5	336.0	319.7	304.7
72.5°	346.7	383.9	389.4	372.5	354.0	329.2	315.6	306.7	288.7	277.5	265.4
75°	242.8	269.8	277.0	277.0	268.4	255.6	243.5	237.8	225.0	215.0	207.9
77.5°	159.2	176.3	187.3	189.9	191.3	187.0	177.0	173.0	163.2	159.6	152.8
80°	112.4	123.9	136.7	141.0	144.5	143.1	138.8	136.0	126.7	123.1	120.3
82.5°	77.8	84.0	94.5	104.0	102.9	106.6	102.9	100.7	93.7	92.4	89.5
85°	40.6	41.3	42.7	49.1	52.7	54.1	54.8	53.4	51.3	51.3	46.3
87.5°	16.1	15.3	16.2	16.0	16.1	18.1	19.5	19.8	18.4	17.0	15.6
90°	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0	3.6	5.3	6.9
92.5°	24.5	23.7	22.9	21.6	19.7	17.8	16.1	14.2	16.1	17.8	19.7
95°	48.2	47.2	46.2	45.0	43.7	42.4	41.0	39.7	41.0	42.4	43.7
97.5°	77.1	76.0	74.7	73.6	72.5	71.5	70.4	69.4	70.4	71.5	72.5
100°	98.6	97.3	95.9	95.0	94.4	93.8	93.3	92.6	93.3	93.8	94.4
102.5°	121.1	119.8	118.7	118.0	117.7	117.4	117.3	117.0	117.3	117.4	117.7
105°	156.3	155.8	155.2	154.8	154.6	154.5	154.4	154.2	154.4	154.5	154.6
107.5°	194.3	194.2	194.1	193.9	193.8	193.6	193.4	193.2	193.4	193.6	193.8
110°	220.7	220.8	221.0	220.9	220.6	220.3	220.0	219.7	220.0	220.3	220.6



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.8	247.1	247.4	247.4	247.4	247.4	247.3	247.3	247.3	247.4	247.4
115°	287.8	288.1	288.4	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
117.5°	327.5	327.7	327.9	328.0	327.8	327.7	327.6	327.4	327.6	327.7	327.8
120°	355.0	355.4	355.8	355.8	355.2	354.5	354.0	353.4	354.0	354.5	355.2
122.5°	380.9	381.2	381.4	381.4	381.1	380.8	380.7	380.4	380.7	380.8	381.1
125°	419.9	420.0	420.2	420.3	420.3	420.3	420.3	420.3	420.3	420.3	420.3
127.5°	457.8	458.0	458.3	458.2	457.7	457.3	456.8	456.4	456.8	457.3	457.7
130°	483.8	483.8	483.8	483.6	483.1	482.7	482.2	481.8	482.2	482.7	483.1
132.5°	508.9	509.0	509.2	509.1	508.7	508.4	508.1	507.7	508.1	508.4	508.7
135°	546.0	546.0	546.0	545.5	544.7	543.8	542.9	542.1	542.9	543.8	544.7
137.5°	581.8	581.6	581.3	581.0	580.6	580.1	579.8	579.3	579.8	580.1	580.6
140°	605.6	605.6	605.6	605.4	605.1	604.8	604.5	604.2	604.5	604.8	605.1
142.5°	628.0	628.1	628.3	628.2	627.9	627.6	627.3	627.0	627.3	627.6	627.9
145°	661.6	661.4	661.2	660.8	660.3	659.7	659.1	658.5	659.1	659.7	660.3
147.5°	692.6	692.8	692.9	692.6	691.9	691.2	690.5	689.7	690.5	691.2	691.9
150°	711.5	711.5	711.5	711.1	710.6	710.0	709.4	708.8	709.4	710.0	710.6
152.5°	728.7	728.5	728.4	728.3	727.9	727.5	727.2	726.8	727.2	727.5	727.9
155°	754.1	754.2	754.4	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
157.5°	776.5	776.5	776.6	776.7	776.9	777.2	777.5	777.8	777.5	777.2	776.9
160°	790.5	790.7	790.8	790.9	791.1	791.2	791.4	791.6	791.4	791.2	791.1
162.5°	802.2	802.3	802.5	802.7	803.1	803.4	803.9	804.2	803.9	803.4	803.1
165°	818.6	818.9	819.2	819.6	820.0	820.5	820.9	821.4	820.9	820.5	820.0
167.5°	831.7	831.7	831.6	832.0	832.6	833.2	833.8	834.4	833.8	833.2	832.6
170°	838.9	838.7	838.6	838.9	839.6	840.3	841.1	841.9	841.1	840.3	839.6
172.5°	844.5	844.4	844.4	844.6	845.3	845.9	846.5	847.1	846.5	845.9	845.3
175°	850.7	850.9	851.0	851.5	852.2	852.9	853.6	854.4	853.6	852.9	852.2
177.5°	854.2	854.2	854.2	854.4	855.1	855.6	856.2	856.8	856.2	855.6	855.1
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1735.2	1729.5	1722.1	1713.5	1703.3	1694.2	1690.1	1693.6	1695.3	1690.8	1690.1
5°	1682.3	1664.6	1650.3	1629.0	1611.9	1597.6	1587.7	1583.4	1584.8	1573.4	1570.6
7.5°	1623.0	1601.9	1578.5	1553.2	1529.6	1508.6	1497.6	1491.7	1479.6	1474.4	1465.8
10°	1584.8	1556.3	1533.6	1503.6	1476.6	1451.7	1439.6	1429.6	1417.5	1411.8	1399.7
12.5°	1545.5	1512.4	1487.4	1456.3	1428.7	1398.7	1387.1	1368.7	1349.7	1337.7	1322.2
15°	1490.1	1450.3	1419.6	1382.6	1349.9	1315.7	1285.0	1250.9	1238.1	1211.0	1195.3
17.5°	1425.3	1384.9	1347.0	1297.4	1246.8	1204.3	1171.7	1139.0	1119.4	1102.1	1094.1
20°	1382.6	1345.6	1292.9	1235.2	1179.0	1132.0	1105.6	1084.3	1062.9	1050.9	1042.3
22.5°	1342.2	1294.9	1233.7	1171.4	1115.2	1078.4	1056.1	1034.2	1016.8	1005.3	993.9
25°	1274.4	1212.5	1147.6	1076.5	1038.0	1006.0	981.8	963.9	953.3	938.3	932.6
27.5°	1204.8	1129.7	1058.3	1010.4	970.4	941.0	920.0	906.6	893.0	883.5	876.1
30°	1151.2	1075.0	1010.9	965.4	924.8	900.6	883.5	867.9	857.2	849.4	843.6
32.5°	1098.2	1022.1	968.2	919.3	887.3	863.6	845.3	833.7	825.3	815.2	811.7
35°	1021.6	954.0	907.0	862.9	830.1	808.8	794.5	782.5	775.3	772.5	770.3
37.5°	948.1	892.6	842.1	805.9	776.8	759.9	743.2	737.2	732.3	727.2	729.5
40°	901.3	849.4	804.5	766.1	742.5	724.1	714.1	706.9	702.7	702.7	702.7
42.5°	860.9	810.0	766.3	731.9	708.4	692.8	681.6	675.6	674.2	673.7	677.1
45°	798.1	751.1	706.9	678.5	658.5	642.9	636.5	631.5	631.5	634.4	635.1
47.5°	735.8	691.9	656.4	624.6	606.3	596.5	590.9	588.4	588.6	591.5	594.8
50°	697.7	654.2	619.4	590.9	573.8	564.5	559.5	558.2	559.5	559.5	564.5
52.5°	656.1	617.2	582.9	559.0	539.7	531.0	528.2	526.3	527.1	529.4	531.5
55°	595.2	560.3	527.5	504.8	490.5	484.8	478.4	479.1	477.7	479.1	479.1
57.5°	534.1	502.7	472.3	454.2	441.7	433.5	426.4	428.5	426.3	426.1	424.9
60°	494.8	460.7	436.4	420.1	405.8	398.7	392.3	393.7	391.6	390.1	387.3
62.5°	452.1	423.7	400.6	384.8	373.4	365.1	358.6	357.2	352.3	347.4	341.2
65°	390.1	366.7	346.0	331.1	320.4	314.0	309.0	304.7	294.0	282.7	277.0
67.5°	329.9	313.0	293.7	281.1	272.4	264.0	254.5	247.2	237.2	231.0	227.4
70°	291.1	274.8	258.4	246.3	237.1	229.3	218.6	213.6	206.4	203.6	200.1
72.5°	254.1	238.9	223.7	212.8	202.9	196.8	188.4	183.4	180.3	179.1	175.6
75°	198.0	185.8	174.4	164.4	156.7	152.4	148.8	145.3	143.8	137.4	133.8
77.5°	144.4	136.4	129.3	122.2	116.6	113.8	106.9	102.8	100.4	97.4	96.7
80°	112.4	106.8	99.7	95.4	87.6	84.7	81.9	81.1	80.4	79.7	79.0
82.5°	84.6	78.9	71.8	69.2	67.1	65.4	63.7	63.0	62.2	62.7	62.5
85°	42.7	39.9	39.9	39.1	38.4	37.7	37.0	37.0	36.3	37.0	36.3
87.5°	16.0	15.6	15.9	15.0	15.8	16.1	15.6	15.8	16.6	15.6	15.7
90°	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3	17.2	18.1	18.6
92.5°	21.6	22.9	23.7	24.5	25.4	26.2	26.8	27.3	27.8	28.4	28.7
95°	45.0	46.2	47.2	48.2	49.3	50.3	50.7	51.2	51.6	52.1	52.3
97.5°	73.6	74.7	76.0	77.1	78.4	79.5	80.1	80.6	81.1	81.7	81.9
100°	95.0	95.9	97.3	98.6	100.0	101.3	101.6	101.8	102.1	102.5	102.5
102.5°	118.0	118.7	119.8	121.1	122.3	123.5	123.9	124.3	124.8	125.1	125.4
105°	154.8	155.2	155.8	156.3	156.9	157.5	157.9	158.4	158.8	159.3	159.7
107.5°	193.9	194.1	194.2	194.3	194.4	194.5	194.8	195.3	195.6	196.1	196.3
110°	220.9	221.0	220.8	220.7	220.5	220.3	220.1	219.8	219.5	219.2	219.3



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	247.4	247.4	247.1	246.8	246.6	246.3	246.3	246.2	246.1	246.1	246.1
115°	288.6	288.4	288.1	287.8	287.5	287.2	287.0	287.0	286.8	286.6	286.5
117.5°	328.0	327.9	327.7	327.5	327.3	327.1	326.5	326.1	325.6	325.0	324.7
120°	355.8	355.8	355.4	355.0	354.5	354.1	353.3	352.6	351.9	351.2	350.9
122.5°	381.4	381.4	381.2	380.9	380.8	380.6	380.0	379.5	379.1	378.5	378.0
125°	420.3	420.2	420.0	419.9	419.7	419.5	419.3	419.0	418.7	418.4	418.1
127.5°	458.2	458.3	458.0	457.8	457.5	457.4	457.0	456.7	456.5	456.1	455.8
130°	483.6	483.8	483.8	483.8	483.8	483.8	483.5	483.2	482.9	482.6	482.1
132.5°	509.1	509.2	509.0	508.9	508.8	508.6	508.4	508.1	507.8	507.5	507.2
135°	545.5	546.0	546.0	546.0	546.0	546.0	545.7	545.4	545.1	544.8	544.5
137.5°	581.0	581.3	581.6	581.8	582.0	582.3	581.8	581.5	581.1	580.8	580.6
140°	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.3	605.1	604.9	604.8
142.5°	628.2	628.3	628.1	628.0	627.9	627.8	627.8	627.8	627.7	627.7	627.7
145°	660.8	661.2	661.4	661.6	661.6	661.8	661.6	661.6	661.4	661.2	660.9
147.5°	692.6	692.9	692.8	692.6	692.5	692.4	692.2	692.1	692.1	691.9	691.8
150°	711.1	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.5	711.4
152.5°	728.3	728.4	728.5	728.7	728.8	728.9	729.2	729.6	730.0	730.3	730.3
155°	754.5	754.4	754.2	754.1	753.9	753.9	754.4	755.0	755.5	756.2	756.2
157.5°	776.7	776.6	776.5	776.5	776.5	776.4	776.9	777.3	777.8	778.2	778.2
160°	790.9	790.8	790.7	790.5	790.3	790.2	790.7	791.1	791.6	792.0	791.8
162.5°	802.7	802.5	802.3	802.2	802.0	801.8	802.6	803.4	804.2	805.0	805.0
165°	819.6	819.2	818.9	818.6	818.3	818.0	818.9	819.7	820.6	821.5	821.7
167.5°	832.0	831.6	831.7	831.7	831.7	831.8	832.7	833.6	834.4	835.3	835.3
170°	838.9	838.6	838.7	838.9	839.0	839.2	840.1	841.0	841.9	842.8	842.7
172.5°	844.6	844.4	844.4	844.5	844.5	844.5	845.5	846.5	847.5	848.5	848.5
175°	851.5	851.0	850.9	850.7	850.6	850.4	851.5	852.5	853.5	854.5	854.5
177.5°	854.4	854.2	854.2	854.2	854.2	854.2	855.0	855.8	856.6	857.5	857.4
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1686.8	1687.9	1683.9	1682.7	1683.9	1687.9	1686.8	1690.1	1690.8	1695.3	1693.6
5°	1564.9	1563.4	1559.9	1560.6	1559.9	1563.4	1564.9	1570.6	1573.4	1584.8	1583.4
7.5°	1460.6	1455.1	1456.6	1451.0	1456.6	1455.1	1460.6	1465.8	1474.4	1479.6	1491.7
10°	1396.9	1389.0	1382.6	1376.9	1382.6	1389.0	1396.9	1399.7	1411.8	1417.5	1429.6
12.5°	1309.7	1303.0	1294.3	1296.0	1294.3	1303.0	1309.7	1322.2	1337.7	1349.7	1368.7
15°	1186.1	1175.5	1158.3	1160.5	1158.3	1175.5	1186.1	1195.3	1211.0	1238.1	1250.9
17.5°	1081.5	1081.6	1073.8	1075.6	1073.8	1081.6	1081.5	1094.1	1102.1	1119.4	1139.0
20°	1027.3	1022.3	1023.1	1020.9	1023.1	1022.3	1027.3	1042.3	1050.9	1062.9	1084.3
22.5°	989.7	983.6	978.7	974.2	978.7	983.6	989.7	993.9	1005.3	1016.8	1034.2
25°	926.2	921.9	915.6	914.2	915.6	921.9	926.2	932.6	938.3	953.3	963.9
27.5°	870.4	869.6	867.0	863.7	867.0	869.6	870.4	876.1	883.5	893.0	906.6
30°	837.9	836.5	835.1	832.9	835.1	836.5	837.9	843.6	849.4	857.2	867.9
32.5°	809.0	808.1	806.6	806.8	806.6	808.1	809.0	811.7	815.2	825.3	833.7
35°	767.5	766.8	765.4	764.6	765.4	766.8	767.5	770.3	772.5	775.3	782.5
37.5°	728.8	730.6	729.8	729.6	729.8	730.6	728.8	729.5	727.2	732.3	737.2
40°	702.0	702.7	704.1	703.4	704.1	702.7	702.0	702.7	702.7	702.7	706.9
42.5°	679.8	679.9	681.9	679.5	681.9	679.9	679.8	677.1	673.7	674.2	675.6
45°	640.1	644.4	643.6	643.6	643.6	644.4	640.1	635.1	634.4	631.5	631.5
47.5°	596.6	600.3	601.3	601.2	601.3	600.3	596.6	594.8	591.5	588.6	588.4
50°	568.1	566.7	568.8	568.1	568.8	566.7	568.1	564.5	559.5	559.5	558.2
52.5°	533.4	533.7	533.5	532.8	533.5	533.7	533.4	531.5	529.4	527.1	526.3
55°	479.8	480.5	479.1	479.8	479.1	480.5	479.8	479.1	479.1	477.7	479.1
57.5°	421.8	418.3	419.7	418.0	419.7	418.3	421.8	424.9	426.1	426.3	428.5
60°	380.2	374.5	373.1	370.2	373.1	374.5	380.2	387.3	390.1	391.6	393.7
62.5°	333.5	329.5	324.7	326.9	324.7	329.5	333.5	341.2	347.4	352.3	357.2
65°	271.3	268.4	266.3	269.1	266.3	268.4	271.3	277.0	282.7	294.0	304.7
67.5°	224.5	223.0	223.0	221.6	223.0	223.0	224.5	227.4	231.0	237.2	247.2
70°	200.1	198.0	198.0	196.5	198.0	198.0	200.1	200.1	203.6	206.4	213.6
72.5°	175.0	172.9	173.4	172.5	173.4	172.9	175.0	175.6	179.1	180.3	183.4
75°	129.6	126.0	126.0	126.7	126.0	126.0	129.6	133.8	137.4	143.8	145.3
77.5°	96.7	95.9	96.9	95.7	96.9	95.9	96.7	96.7	97.4	100.4	102.8
80°	79.0	78.3	77.6	79.7	77.6	78.3	79.0	79.0	79.7	80.4	81.1
82.5°	61.3	61.3	61.1	63.8	61.1	61.3	61.3	62.5	62.7	62.2	63.0
85°	37.0	35.6	37.0	35.6	37.0	35.6	37.0	36.3	37.0	36.3	37.0
87.5°	16.9	16.4	15.9	16.5	15.9	16.4	16.9	15.7	15.6	16.6	15.8
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.1	17.2	16.3
92.5°	28.9	29.1	29.2	29.4	29.2	29.1	28.9	28.7	28.4	27.8	27.3
95°	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.1	51.6	51.2
97.5°	81.9	81.9	81.9	81.9	81.9	81.9	81.9	81.9	81.7	81.1	80.6
100°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.8
102.5°	125.6	125.6	125.7	125.9	125.7	125.6	125.6	125.4	125.1	124.8	124.3
105°	160.2	160.6	161.0	161.5	161.0	160.6	160.2	159.7	159.3	158.8	158.4
107.5°	196.3	196.3	196.2	196.2	196.2	196.3	196.3	196.3	196.1	195.6	195.3
110°	219.7	220.2	220.6	221.1	220.6	220.2	219.7	219.3	219.2	219.5	219.8



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	246.2	246.3	246.4	246.5	246.4	246.3	246.2	246.1	246.1	246.1	246.2
115°	286.3	286.2	286.1	285.9	286.1	286.2	286.3	286.5	286.6	286.8	287.0
117.5°	324.4	324.0	323.8	323.5	323.8	324.0	324.4	324.7	325.0	325.6	326.1
120°	351.2	351.5	351.8	352.0	351.8	351.5	351.2	350.9	351.2	351.9	352.6
122.5°	377.5	376.9	376.5	375.9	376.5	376.9	377.5	378.0	378.5	379.1	379.5
125°	417.9	417.5	417.2	417.0	417.2	417.5	417.9	418.1	418.4	418.7	419.0
127.5°	455.7	455.4	455.1	455.0	455.1	455.4	455.7	455.8	456.1	456.5	456.7
130°	481.6	481.0	480.4	479.8	480.4	481.0	481.6	482.1	482.6	482.9	483.2
132.5°	507.0	506.8	506.5	506.3	506.5	506.8	507.0	507.2	507.5	507.8	508.1
135°	544.0	543.6	543.1	542.7	543.1	543.6	544.0	544.5	544.8	545.1	545.4
137.5°	580.7	580.8	580.9	580.9	580.9	580.8	580.7	580.6	580.8	581.1	581.5
140°	604.7	604.5	604.4	604.2	604.4	604.5	604.7	604.8	604.9	605.1	605.3
142.5°	627.6	627.6	627.6	627.5	627.6	627.6	627.6	627.7	627.7	627.7	627.8
145°	660.5	660.0	659.6	659.2	659.6	660.0	660.5	660.9	661.2	661.4	661.6
147.5°	691.6	691.5	691.3	691.2	691.3	691.5	691.6	691.8	691.9	692.1	692.1
150°	711.2	711.1	711.0	710.8	711.0	711.1	711.2	711.4	711.5	711.5	711.5
152.5°	730.0	729.6	729.2	728.8	729.2	729.6	730.0	730.3	730.3	730.0	729.6
155°	755.5	755.0	754.4	753.9	754.4	755.0	755.5	756.2	756.2	755.5	755.0
157.5°	777.7	777.2	776.7	776.1	776.7	777.2	777.7	778.2	778.2	777.8	777.3
160°	791.1	790.3	789.6	788.9	789.6	790.3	791.1	791.8	792.0	791.6	791.1
162.5°	804.3	803.6	802.9	802.1	802.9	803.6	804.3	805.0	805.0	804.2	803.4
165°	821.1	820.5	819.9	819.3	819.9	820.5	821.1	821.7	821.5	820.6	819.7
167.5°	834.4	833.5	832.6	831.6	832.6	833.5	834.4	835.3	835.3	834.4	833.6
170°	841.6	840.6	839.5	838.6	839.5	840.6	841.6	842.7	842.8	841.9	841.0
172.5°	847.4	846.4	845.3	844.4	845.3	846.4	847.4	848.5	848.5	847.5	846.5
175°	853.5	852.5	851.5	850.4	851.5	852.5	853.5	854.5	854.5	853.5	852.5
177.5°	856.4	855.5	854.5	853.6	854.5	855.5	856.4	857.4	857.5	856.6	855.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1690.1	1694.2	1703.3	1713.5	1722.1	1729.5	1735.2	1743.1	1750.5	1760.8	1770.5
5°	1587.7	1597.6	1611.9	1629.0	1650.3	1664.6	1682.3	1698.0	1720.8	1743.6	1765.7
7.5°	1497.6	1508.6	1529.6	1553.2	1578.5	1601.9	1623.0	1650.6	1680.8	1714.0	1751.0
10°	1439.6	1451.7	1476.6	1503.6	1533.6	1556.3	1584.8	1617.6	1651.7	1692.3	1737.9
12.5°	1387.1	1398.7	1428.7	1456.3	1487.4	1512.4	1545.5	1578.9	1624.4	1668.4	1720.2
15°	1285.0	1315.7	1349.9	1382.6	1419.6	1450.3	1490.1	1524.3	1567.7	1629.7	1688.7
17.5°	1171.7	1204.3	1246.8	1297.4	1347.0	1384.9	1425.3	1467.8	1519.5	1582.7	1650.9
20°	1105.6	1132.0	1179.0	1235.2	1292.9	1345.6	1382.6	1429.6	1483.0	1551.3	1621.8
22.5°	1056.1	1078.4	1115.2	1171.4	1233.7	1294.9	1342.2	1388.6	1447.7	1516.0	1592.8
25°	981.8	1006.0	1038.0	1076.5	1147.6	1212.5	1274.4	1327.8	1390.4	1458.7	1544.2
27.5°	920.0	941.0	970.4	1010.4	1058.3	1129.7	1204.8	1265.7	1329.9	1403.3	1488.8
30°	883.5	900.6	924.8	965.4	1010.9	1075.0	1151.2	1222.4	1287.2	1363.4	1452.4
32.5°	845.3	863.6	887.3	919.3	968.2	1022.1	1098.2	1176.3	1245.1	1322.9	1410.2
35°	794.5	808.8	830.1	862.9	907.0	954.0	1021.6	1102.1	1174.7	1258.0	1341.3
37.5°	743.2	759.9	776.8	805.9	842.1	892.6	948.1	1030.2	1110.6	1186.7	1268.0
40°	714.1	724.1	742.5	766.1	804.5	849.4	901.3	981.8	1062.2	1137.7	1219.6
42.5°	681.6	692.8	708.4	731.9	766.3	810.0	860.9	930.5	1014.4	1087.6	1162.1
45°	636.5	642.9	658.5	678.5	706.9	751.1	798.1	860.1	939.1	1008.8	1074.3
47.5°	590.9	596.5	606.3	624.6	656.4	691.9	735.8	791.4	860.8	930.5	985.9
50°	559.5	564.5	573.8	590.9	619.4	654.2	697.7	747.5	809.5	876.4	922.7
52.5°	528.2	531.0	539.7	559.0	582.9	617.2	656.1	702.0	759.9	815.5	862.3
55°	478.4	484.8	490.5	504.8	527.5	560.3	595.2	638.6	683.5	730.5	770.3
57.5°	426.4	433.5	441.7	454.2	472.3	502.7	534.1	569.3	607.6	646.6	680.0
60°	392.3	398.7	405.8	420.1	436.4	460.7	494.8	525.4	554.6	590.2	623.7
62.5°	358.6	365.1	373.4	384.8	400.6	423.7	452.1	478.8	509.1	540.1	565.0
65°	309.0	314.0	320.4	331.1	346.0	366.7	390.1	410.8	437.8	460.7	483.4
67.5°	254.5	264.0	272.4	281.1	293.7	313.0	329.9	349.7	368.1	385.0	405.8
70°	218.6	229.3	237.1	246.3	258.4	274.8	291.1	304.7	319.7	336.0	354.5
72.5°	188.4	196.8	202.9	212.8	223.7	238.9	254.1	265.4	277.5	288.7	306.7
75°	148.8	152.4	156.7	164.4	174.4	185.8	198.0	207.9	215.0	225.0	237.8
77.5°	106.9	113.8	116.6	122.2	129.3	136.4	144.4	152.8	159.6	163.2	173.0
80°	81.9	84.7	87.6	95.4	99.7	106.8	112.4	120.3	123.1	126.7	136.0
82.5°	63.7	65.4	67.1	69.2	71.8	78.9	84.6	89.5	92.4	93.7	100.7
85°	37.0	37.7	38.4	39.1	39.9	39.9	42.7	46.3	51.3	51.3	53.4
87.5°	15.6	16.1	15.8	15.0	15.9	15.6	16.0	15.6	17.0	18.4	19.8
90°	15.4	14.5	13.4	12.2	11.1	9.9	8.5	6.9	5.3	3.6	2.0
92.5°	26.8	26.2	25.4	24.5	23.7	22.9	21.6	19.7	17.8	16.1	14.2
95°	50.7	50.3	49.3	48.2	47.2	46.2	45.0	43.7	42.4	41.0	39.7
97.5°	80.1	79.5	78.4	77.1	76.0	74.7	73.6	72.5	71.5	70.4	69.4
100°	101.6	101.3	100.0	98.6	97.3	95.9	95.0	94.4	93.8	93.3	92.6
102.5°	123.9	123.5	122.3	121.1	119.8	118.7	118.0	117.7	117.4	117.3	117.0
105°	157.9	157.5	156.9	156.3	155.8	155.2	154.8	154.6	154.5	154.4	154.2
107.5°	194.8	194.5	194.4	194.3	194.2	194.1	193.9	193.8	193.6	193.4	193.2
110°	220.1	220.3	220.5	220.7	220.8	221.0	220.9	220.6	220.3	220.0	219.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	246.3	246.3	246.6	246.8	247.1	247.4	247.4	247.4	247.4	247.3	247.3
115°	287.0	287.2	287.5	287.8	288.1	288.4	288.6	288.6	288.6	288.6	288.6
117.5°	326.5	327.1	327.3	327.5	327.7	327.9	328.0	327.8	327.7	327.6	327.4
120°	353.3	354.1	354.5	355.0	355.4	355.8	355.8	355.2	354.5	354.0	353.4
122.5°	380.0	380.6	380.8	380.9	381.2	381.4	381.4	381.1	380.8	380.7	380.4
125°	419.3	419.5	419.7	419.9	420.0	420.2	420.3	420.3	420.3	420.3	420.3
127.5°	457.0	457.4	457.5	457.8	458.0	458.3	458.2	457.7	457.3	456.8	456.4
130°	483.5	483.8	483.8	483.8	483.8	483.8	483.6	483.1	482.7	482.2	481.8
132.5°	508.4	508.6	508.8	508.9	509.0	509.2	509.1	508.7	508.4	508.1	507.7
135°	545.7	546.0	546.0	546.0	546.0	546.0	545.5	544.7	543.8	542.9	542.1
137.5°	581.8	582.3	582.0	581.8	581.6	581.3	581.0	580.6	580.1	579.8	579.3
140°	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.1	604.8	604.5	604.2
142.5°	627.8	627.8	627.9	628.0	628.1	628.3	628.2	627.9	627.6	627.3	627.0
145°	661.6	661.8	661.6	661.6	661.4	661.2	660.8	660.3	659.7	659.1	658.5
147.5°	692.2	692.4	692.5	692.6	692.8	692.9	692.6	691.9	691.2	690.5	689.7
150°	711.5	711.5	711.5	711.5	711.5	711.5	711.1	710.6	710.0	709.4	708.8
152.5°	729.2	728.9	728.8	728.7	728.5	728.4	728.3	727.9	727.5	727.2	726.8
155°	754.4	753.9	753.9	754.1	754.2	754.4	754.5	754.5	754.5	754.5	754.5
157.5°	776.9	776.4	776.5	776.5	776.5	776.6	776.7	776.9	777.2	777.5	777.8
160°	790.7	790.2	790.3	790.5	790.7	790.8	790.9	791.1	791.2	791.4	791.6
162.5°	802.6	801.8	802.0	802.2	802.3	802.5	802.7	803.1	803.4	803.9	804.2
165°	818.9	818.0	818.3	818.6	818.9	819.2	819.6	820.0	820.5	820.9	821.4
167.5°	832.7	831.8	831.7	831.7	831.7	831.6	832.0	832.6	833.2	833.8	834.4
170°	840.1	839.2	839.0	838.9	838.7	838.6	838.9	839.6	840.3	841.1	841.9
172.5°	845.5	844.5	844.5	844.5	844.4	844.4	844.6	845.3	845.9	846.5	847.1
175°	851.5	850.4	850.6	850.7	850.9	851.0	851.5	852.2	852.9	853.6	854.4
177.5°	855.0	854.2	854.2	854.2	854.2	854.2	854.4	855.1	855.6	856.2	856.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1777.9	1783.0	1788.7	1799.6	1808.7	1812.7	1820.6	1826.3	1824.6	1832.6	1846.2
5°	1784.8	1804.1	1826.1	1849.0	1874.6	1896.0	1913.0	1930.1	1943.7	1960.0	1984.2
7.5°	1783.7	1817.9	1855.0	1896.0	1938.0	1974.2	2007.9	2042.0	2072.3	2105.5	2148.9
10°	1779.1	1824.7	1871.0	1924.4	1977.8	2028.4	2073.9	2116.7	2157.2	2200.7	2255.5
12.5°	1774.1	1826.4	1882.4	1946.6	2013.1	2073.9	2127.4	2189.0	2239.8	2295.8	2359.1
15°	1751.4	1821.9	1898.1	1981.4	2061.1	2143.0	2216.3	2291.8	2362.2	2429.2	2508.9
17.5°	1725.5	1806.8	1896.7	1995.0	2090.9	2190.4	2277.4	2372.5	2444.5	2534.4	2608.4
20°	1704.4	1792.0	1888.1	1998.4	2107.4	2217.7	2313.8	2410.7	2491.8	2582.2	2676.2
22.5°	1678.7	1774.9	1879.0	1993.3	2107.4	2227.9	2334.3	2430.6	2531.1	2633.0	2729.8
25°	1637.4	1737.1	1847.5	1972.8	2103.8	2227.0	2340.9	2460.5	2568.8	2679.1	2765.9
27.5°	1586.8	1691.5	1807.8	1937.1	2071.5	2197.6	2331.8	2459.2	2568.1	2674.3	2750.1
30°	1546.3	1656.7	1768.4	1899.5	2039.0	2174.3	2318.1	2445.5	2560.2	2655.6	2698.3
32.5°	1504.8	1609.4	1724.7	1857.3	2000.3	2145.8	2288.5	2418.8	2524.9	2582.1	2583.2
35°	1432.4	1530.7	1650.3	1780.6	1927.3	2085.3	2229.8	2358.0	2422.8	2427.8	2358.0
37.5°	1353.5	1443.7	1556.6	1687.0	1847.6	2004.8	2152.5	2237.9	2259.6	2187.1	2058.1
40°	1297.2	1380.5	1489.4	1623.3	1782.7	1945.1	2079.6	2142.2	2119.5	2002.0	1858.1
42.5°	1238.0	1315.5	1420.5	1552.6	1712.7	1876.7	1991.4	2024.9	1964.5	1828.9	1660.5
45°	1141.3	1212.5	1316.4	1449.6	1603.3	1757.1	1844.0	1826.8	1726.4	1565.6	1376.9
47.5°	1040.6	1109.4	1202.9	1326.1	1483.5	1616.2	1675.1	1623.5	1480.7	1303.7	1150.2
50°	973.9	1044.5	1130.6	1248.0	1391.9	1520.0	1557.7	1479.4	1320.6	1150.5	1009.5
52.5°	908.5	968.7	1053.1	1166.6	1304.1	1412.4	1432.4	1342.2	1178.3	1025.7	900.7
55°	808.8	863.6	934.8	1041.6	1160.5	1252.3	1241.6	1125.6	976.8	846.5	748.2
57.5°	712.4	753.7	819.5	919.5	1024.0	1085.6	1046.6	947.6	809.0	702.3	619.4
60°	648.6	687.1	748.2	835.8	927.6	962.5	929.8	822.3	712.7	615.1	545.4
62.5°	588.2	622.1	674.8	756.1	830.3	851.0	815.9	722.0	623.2	539.9	482.1
65°	500.5	531.8	576.7	634.4	685.6	695.5	672.8	576.7	501.9	432.1	392.3
67.5°	420.9	441.4	476.4	526.3	553.5	559.3	515.3	455.0	389.1	346.2	316.1
70°	367.4	381.6	414.4	441.4	463.5	464.2	423.7	375.2	324.7	289.8	267.7
72.5°	315.6	329.2	354.0	372.5	389.4	383.9	346.7	308.5	267.7	241.4	225.0
75°	243.5	255.6	268.4	277.0	277.0	269.8	242.8	214.3	190.8	175.1	170.1
77.5°	177.0	187.0	191.3	189.9	187.3	176.3	159.2	140.5	132.2	124.8	121.0
80°	138.8	143.1	144.5	141.0	136.7	123.9	112.4	104.7	96.8	94.0	92.6
82.5°	102.9	106.6	102.9	104.0	94.5	84.0	77.8	75.1	71.8	70.6	69.2
85°	54.8	54.1	52.7	49.1	42.7	41.3	40.6	39.9	38.4	39.1	37.7
87.5°	19.5	18.1	16.1	16.0	16.2	15.3	16.1	16.3	16.6	16.2	17.5
90°	3.6	5.3	6.9	8.5	9.9	11.1	12.2	13.4	14.5	15.4	16.3
92.5°	16.1	17.8	19.7	21.6	22.9	23.7	24.5	25.4	26.2	26.8	27.3
95°	41.0	42.4	43.7	45.0	46.2	47.2	48.2	49.3	50.3	50.7	51.2
97.5°	70.4	71.5	72.5	73.6	74.7	76.0	77.1	78.4	79.5	80.1	80.6
100°	93.3	93.8	94.4	95.0	95.9	97.3	98.6	100.0	101.3	101.6	101.8
102.5°	117.3	117.4	117.7	118.0	118.7	119.8	121.1	122.3	123.5	123.9	124.3
105°	154.4	154.5	154.6	154.8	155.2	155.8	156.3	156.9	157.5	157.9	158.4
107.5°	193.4	193.6	193.8	193.9	194.1	194.2	194.3	194.4	194.5	194.8	195.3
110°	220.0	220.3	220.6	220.9	221.0	220.8	220.7	220.5	220.3	220.1	219.8



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	247.3	247.4	247.4	247.4	247.4	247.1	246.8	246.6	246.3	246.3	246.2
115°	288.6	288.6	288.6	288.6	288.4	288.1	287.8	287.5	287.2	287.0	287.0
117.5°	327.6	327.7	327.8	328.0	327.9	327.7	327.5	327.3	327.1	326.5	326.1
120°	354.0	354.5	355.2	355.8	355.8	355.4	355.0	354.5	354.1	353.3	352.6
122.5°	380.7	380.8	381.1	381.4	381.4	381.2	380.9	380.8	380.6	380.0	379.5
125°	420.3	420.3	420.3	420.3	420.2	420.0	419.9	419.7	419.5	419.3	419.0
127.5°	456.8	457.3	457.7	458.2	458.3	458.0	457.8	457.5	457.4	457.0	456.7
130°	482.2	482.7	483.1	483.6	483.8	483.8	483.8	483.8	483.8	483.5	483.2
132.5°	508.1	508.4	508.7	509.1	509.2	509.0	508.9	508.8	508.6	508.4	508.1
135°	542.9	543.8	544.7	545.5	546.0	546.0	546.0	546.0	546.0	545.7	545.4
137.5°	579.8	580.1	580.6	581.0	581.3	581.6	581.8	582.0	582.3	581.8	581.5
140°	604.5	604.8	605.1	605.4	605.6	605.6	605.6	605.6	605.6	605.4	605.3
142.5°	627.3	627.6	627.9	628.2	628.3	628.1	628.0	627.9	627.8	627.8	627.8
145°	659.1	659.7	660.3	660.8	661.2	661.4	661.6	661.6	661.8	661.6	661.6
147.5°	690.5	691.2	691.9	692.6	692.9	692.8	692.6	692.5	692.4	692.2	692.1
150°	709.4	710.0	710.6	711.1	711.5	711.5	711.5	711.5	711.5	711.5	711.5
152.5°	727.2	727.5	727.9	728.3	728.4	728.5	728.7	728.8	728.9	729.2	729.6
155°	754.5	754.5	754.5	754.5	754.4	754.2	754.1	753.9	753.9	754.4	755.0
157.5°	777.5	777.2	776.9	776.7	776.6	776.5	776.5	776.5	776.4	776.9	777.3
160°	791.4	791.2	791.1	790.9	790.8	790.7	790.5	790.3	790.2	790.7	791.1
162.5°	803.9	803.4	803.1	802.7	802.5	802.3	802.2	802.0	801.8	802.6	803.4
165°	820.9	820.5	820.0	819.6	819.2	818.9	818.6	818.3	818.0	818.9	819.7
167.5°	833.8	833.2	832.6	832.0	831.6	831.7	831.7	831.7	831.8	832.7	833.6
170°	841.1	840.3	839.6	838.9	838.6	838.7	838.9	839.0	839.2	840.1	841.0
172.5°	846.5	845.9	845.3	844.6	844.4	844.4	844.5	844.5	844.5	845.5	846.5
175°	853.6	852.9	852.2	851.5	851.0	850.9	850.7	850.6	850.4	851.5	852.5
177.5°	856.2	855.6	855.1	854.4	854.2	854.2	854.2	854.2	854.2	855.0	855.8
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7	855.7



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1	1767.1
2.5°	1853.6	1855.9	1857.6	1863.3	1863.9	1869.0	1863.9
5°	2007.0	2017.0	2032.7	2048.3	2049.7	2059.7	2041.8
7.5°	2179.0	2202.1	2216.4	2241.8	2251.7	2258.0	2247.7
10°	2297.5	2318.8	2356.5	2375.1	2393.6	2396.4	2387.9
12.5°	2412.0	2445.9	2475.6	2510.6	2509.8	2534.9	2525.7
15°	2564.5	2599.3	2640.6	2679.8	2694.0	2694.0	2705.5
17.5°	2673.3	2737.2	2779.9	2810.7	2844.2	2850.1	2846.1
20°	2746.7	2815.8	2861.3	2901.2	2924.0	2930.4	2930.4
22.5°	2801.4	2860.2	2904.7	2940.5	2959.3	2966.8	2964.6
25°	2839.3	2889.8	2916.9	2927.6	2932.5	2931.1	2917.6
27.5°	2787.4	2785.2	2768.0	2735.3	2710.7	2695.7	2678.6
30°	2688.3	2651.3	2608.6	2561.6	2501.1	2454.8	2440.5
32.5°	2540.8	2457.6	2385.3	2307.0	2241.9	2195.7	2176.3
35°	2255.5	2123.8	2016.2	1922.3	1854.0	1811.2	1797.0
37.5°	1916.8	1789.4	1656.3	1565.1	1508.5	1465.3	1449.2
40°	1701.6	1562.7	1446.7	1361.3	1302.9	1260.9	1260.2
42.5°	1505.0	1372.5	1263.3	1201.8	1138.8	1111.1	1110.9
45°	1232.3	1126.3	1033.8	985.3	947.6	924.8	918.4
47.5°	1020.4	932.6	871.0	832.4	801.6	787.1	777.8
50°	901.3	824.5	775.3	741.8	724.8	706.2	704.8
52.5°	802.2	740.1	701.9	674.7	653.0	641.9	642.2
55°	674.2	625.1	598.1	577.4	560.3	551.8	548.2
57.5°	568.0	531.1	511.5	492.5	485.3	478.6	476.7
60°	501.9	477.0	458.5	443.5	432.8	430.7	430.0
62.5°	447.3	421.2	408.4	396.8	389.1	385.8	384.4
65°	368.8	349.6	338.1	329.0	326.1	321.1	320.4
67.5°	297.3	285.8	278.2	271.8	268.0	267.7	267.7
70°	253.4	247.0	240.7	237.1	235.0	233.5	233.5
72.5°	215.9	211.2	205.9	204.0	203.6	202.2	201.6
75°	164.4	159.4	160.2	156.7	153.8	150.3	148.1
77.5°	116.6	113.1	112.4	111.9	109.5	109.1	110.2
80°	90.4	86.9	86.1	86.9	86.1	84.0	84.0
82.5°	68.8	65.8	65.1	64.6	63.9	64.6	63.5
85°	37.0	35.6	35.6	35.6	37.0	36.3	35.6
87.5°	16.6	16.1	16.9	16.3	16.4	15.9	16.5
90°	17.2	18.1	18.6	19.0	19.3	19.5	19.9
92.5°	27.8	28.4	28.7	28.9	29.1	29.2	29.4
95°	51.6	52.1	52.3	52.3	52.3	52.3	52.3
97.5°	81.1	81.7	81.9	81.9	81.9	81.9	81.9
100°	102.1	102.5	102.5	102.5	102.5	102.5	102.5
102.5°	124.8	125.1	125.4	125.6	125.6	125.7	125.9
105°	158.8	159.3	159.7	160.2	160.6	161.0	161.5
107.5°	195.6	196.1	196.3	196.3	196.3	196.2	196.2
110°	219.5	219.2	219.3	219.7	220.2	220.6	221.1



TEST NUMBER: P333100-940

CATALOG NUMBER: S124RDIW-S1195D770U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	246.1	246.1	246.1	246.2	246.3	246.4	246.5
115°	286.8	286.6	286.5	286.3	286.2	286.1	285.9
117.5°	325.6	325.0	324.7	324.4	324.0	323.8	323.5
120°	351.9	351.2	350.9	351.2	351.5	351.8	352.0
122.5°	379.1	378.5	378.0	377.5	376.9	376.5	375.9
125°	418.7	418.4	418.1	417.9	417.5	417.2	417.0
127.5°	456.5	456.1	455.8	455.7	455.4	455.1	455.0
130°	482.9	482.6	482.1	481.6	481.0	480.4	479.8
132.5°	507.8	507.5	507.2	507.0	506.8	506.5	506.3
135°	545.1	544.8	544.5	544.0	543.6	543.1	542.7
137.5°	581.1	580.8	580.6	580.7	580.8	580.9	580.9
140°	605.1	604.9	604.8	604.7	604.5	604.4	604.2
142.5°	627.7	627.7	627.7	627.6	627.6	627.6	627.5
145°	661.4	661.2	660.9	660.5	660.0	659.6	659.2
147.5°	692.1	691.9	691.8	691.6	691.5	691.3	691.2
150°	711.5	711.5	711.4	711.2	711.1	711.0	710.8
152.5°	730.0	730.3	730.3	730.0	729.6	729.2	728.8
155°	755.5	756.2	756.2	755.5	755.0	754.4	753.9
157.5°	777.8	778.2	778.2	777.7	777.2	776.7	776.1
160°	791.6	792.0	791.8	791.1	790.3	789.6	788.9
162.5°	804.2	805.0	805.0	804.3	803.6	802.9	802.1
165°	820.6	821.5	821.7	821.1	820.5	819.9	819.3
167.5°	834.4	835.3	835.3	834.4	833.5	832.6	831.6
170°	841.9	842.8	842.7	841.6	840.6	839.5	838.6
172.5°	847.5	848.5	848.5	847.4	846.4	845.3	844.4
175°	853.5	854.5	854.5	853.5	852.5	851.5	850.4
177.5°	856.6	857.5	857.4	856.4	855.5	854.5	853.6
180°	855.7	855.7	855.7	855.7	855.7	855.7	855.7

(END OF REPORT)