

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332762-935

Luminaire Tested: **S124DIW-S575D1050U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332762-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1050U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5278.0 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.7	1.5
10°-20°	221.9	4.2
20°-30°	326.6	6.2
30°-40°	379.6	7.2
40°-50°	379.6	7.2
50°-60°	332.1	6.3
60°-70°	246.6	4.7
70°-80°	140.1	2.7
80°-90°	43.8	0.8
90°-100°	74.4	1.4
100°-110°	220.4	4.2
110°-120°	374.0	7.1
120°-130°	493.2	9.3
130°-140°	553.9	10.5
140°-150°	544.3	10.3
150°-160°	457.8	8.7
160°-170°	304.6	5.8
170°-180°	106.6	2.0
0°-30°	627.2	11.9
0°-40°	1006.8	19.1
0°-60°	1718.5	32.6
0°-90°	2149.1	40.7
90°-120°	668.7	12.7
90°-150°	2260.0	42.8
90°-180°	3129.0	59.3
0°-180°	5278.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	12	19	24	26	5
95°	52	60	66	69	69	58
105°	203	204	208	210	213	216
115°	380	380	379	378	377	375
125°	554	554	553	551	550	493
135°	714	719	720	718	715	552
145°	868	871	872	871	869	543
155°	994	994	994	997	994	457
165°	1082	1080	1078	1083	1080	305
175°	1126	1122	1121	1126	1121	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.5	14.8	15.1	15.4	15.7	15.9	16.1	16.4	16.5	16.7	17.0
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	18.7	21.1	23.6	26.0	28.4	30.2	31.3	32.4	33.5	34.5	35.2
95°	52.3	54.1	55.8	57.6	59.3	60.9	62.3	63.5	64.9	66.3	66.9
97.5°	91.4	92.8	94.2	95.6	97.0	98.5	100.0	101.7	103.2	104.9	105.6
100°	122.1	122.9	123.6	124.4	125.2	126.5	128.2	129.9	131.7	133.5	133.8
102.5°	154.2	154.5	154.8	155.2	155.4	156.4	158.0	159.5	161.2	162.7	163.3
105°	203.2	203.5	203.6	203.8	204.0	204.5	205.3	206.0	206.8	207.6	208.2
107.5°	254.7	254.9	255.1	255.4	255.6	255.8	255.9	256.1	256.1	256.2	256.8
110°	289.6	290.0	290.3	290.8	291.1	291.2	291.0	290.8	290.7	290.4	290.1



TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.9	326.0	326.1	326.1	326.1	326.1	325.7	325.4	325.0	324.7	324.6
115°	380.3	380.3	380.3	380.3	380.3	380.1	379.7	379.4	378.9	378.6	378.3
117.5°	431.6	431.7	431.9	432.0	432.2	432.1	431.9	431.6	431.4	431.0	430.4
120°	465.8	466.6	467.4	468.1	468.9	469.0	468.4	467.8	467.3	466.7	465.7
122.5°	501.4	501.7	502.0	502.3	502.6	502.7	502.3	502.0	501.8	501.5	500.8
125°	553.9	553.9	553.9	553.9	553.9	553.8	553.5	553.4	553.2	553.0	552.6
127.5°	601.5	602.1	602.6	603.2	603.8	604.0	603.6	603.3	603.0	602.7	602.4
130°	635.0	635.6	636.1	636.7	637.3	637.6	637.6	637.6	637.6	637.6	637.2
132.5°	669.2	669.6	670.0	670.5	670.9	671.0	670.9	670.7	670.5	670.4	670.0
135°	714.4	715.5	716.7	717.8	719.0	719.6	719.6	719.6	719.6	719.6	719.2
137.5°	763.5	764.1	764.7	765.2	765.7	766.1	766.5	766.8	767.1	767.4	766.9
140°	796.3	796.8	797.1	797.5	797.9	798.1	798.1	798.1	798.1	798.1	797.9
142.5°	826.4	826.7	827.2	827.5	827.9	828.0	827.9	827.7	827.6	827.4	827.3
145°	867.9	868.7	869.4	870.2	871.0	871.4	871.7	871.8	872.0	872.2	872.0
147.5°	909.0	910.0	910.9	911.8	912.7	913.2	913.0	912.8	912.7	912.5	912.4
150°	934.2	935.0	935.7	936.5	937.3	937.6	937.6	937.6	937.6	937.6	937.6
152.5°	957.9	958.4	958.8	959.2	959.8	960.0	960.2	960.4	960.5	960.7	961.1
155°	994.4	994.4	994.4	994.4	994.4	994.3	994.0	993.9	993.7	993.5	994.3
157.5°	1025.0	1024.7	1024.3	1024.0	1023.6	1023.5	1023.4	1023.4	1023.3	1023.3	1023.9
160°	1043.2	1043.0	1042.8	1042.6	1042.4	1042.2	1042.0	1041.8	1041.6	1041.5	1042.0
162.5°	1059.9	1059.5	1058.9	1058.4	1057.9	1057.6	1057.4	1057.2	1057.0	1056.8	1057.8
165°	1082.4	1081.8	1081.2	1080.7	1080.1	1079.6	1079.3	1078.8	1078.5	1078.1	1079.3
167.5°	1099.7	1098.9	1098.1	1097.3	1096.5	1096.1	1096.1	1096.1	1096.1	1096.2	1097.3
170°	1109.5	1108.5	1107.5	1106.6	1105.6	1105.2	1105.4	1105.6	1105.8	1106.0	1107.2
172.5°	1116.5	1115.6	1114.8	1114.0	1113.2	1112.8	1112.8	1112.9	1112.9	1112.9	1114.3
175°	1126.0	1125.1	1124.1	1123.2	1122.1	1121.6	1121.4	1121.2	1121.0	1120.8	1122.1
177.5°	1129.2	1128.4	1127.7	1126.9	1126.1	1125.7	1125.7	1125.7	1125.7	1125.7	1126.8
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8



TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	17.1	17.4	17.7	17.8	17.8	17.9	18.0	18.1
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	35.9	36.6	37.4	37.8	38.1	38.2	38.5	38.7
95°	67.4	68.0	68.6	68.9	68.9	68.9	68.9	68.9
97.5°	106.2	106.9	107.6	108.0	108.0	108.0	108.0	108.0
100°	134.2	134.6	135.0	135.2	135.2	135.2	135.2	135.2
102.5°	163.8	164.4	165.0	165.3	165.4	165.6	165.7	165.9
105°	208.8	209.3	209.9	210.5	211.1	211.6	212.2	212.8
107.5°	257.4	257.9	258.5	258.6	258.6	258.6	258.6	258.6
110°	289.6	289.3	288.9	289.0	289.6	290.2	290.8	291.4





TEST NUMBER: P332762-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	324.5	324.4	324.3	324.3	324.5	324.6	324.7	324.9
115°	378.2	378.0	377.8	377.5	377.4	377.2	377.0	376.8
117.5°	429.7	429.0	428.4	427.9	427.5	427.1	426.7	426.4
120°	464.7	463.7	462.8	462.4	462.9	463.2	463.6	464.0
122.5°	500.2	499.6	498.9	498.2	497.5	496.8	496.1	495.4
125°	552.2	551.8	551.5	551.0	550.7	550.3	549.9	549.5
127.5°	601.9	601.6	601.2	600.8	600.5	600.2	599.9	599.6
130°	636.8	636.5	636.0	635.5	634.7	634.0	633.2	632.4
132.5°	669.6	669.3	668.8	668.5	668.2	667.9	667.5	667.3
135°	718.8	718.4	718.1	717.6	717.0	716.4	715.8	715.2
137.5°	766.4	765.9	765.3	765.2	765.3	765.4	765.5	765.6
140°	797.7	797.5	797.3	797.1	796.9	796.8	796.5	796.3
142.5°	827.3	827.2	827.2	827.2	827.2	827.2	827.1	827.1
145°	871.8	871.7	871.4	871.1	870.5	869.9	869.4	868.7
147.5°	912.2	912.1	911.9	911.7	911.5	911.4	911.1	910.9
150°	937.6	937.6	937.6	937.5	937.4	937.2	936.9	936.8
152.5°	961.6	962.1	962.5	962.5	962.0	961.5	961.0	960.5
155°	995.1	995.8	996.6	996.6	995.8	995.1	994.3	993.5
157.5°	1024.5	1025.0	1025.6	1025.6	1024.9	1024.2	1023.6	1023.0
160°	1042.6	1043.2	1043.8	1043.5	1042.6	1041.6	1040.7	1039.7
162.5°	1058.9	1059.9	1061.0	1061.0	1060.1	1059.1	1058.1	1057.1
165°	1080.4	1081.6	1082.7	1082.9	1082.1	1081.3	1080.6	1079.8
167.5°	1098.5	1099.7	1100.9	1100.9	1099.7	1098.5	1097.3	1096.1
170°	1108.3	1109.5	1110.6	1110.5	1109.2	1107.8	1106.5	1105.1
172.5°	1115.6	1116.9	1118.3	1118.2	1116.9	1115.5	1114.1	1112.8
175°	1123.5	1124.9	1126.3	1126.3	1124.9	1123.5	1122.1	1120.8
177.5°	1127.9	1128.9	1130.1	1130.0	1128.7	1127.5	1126.3	1125.0
180°	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8	1127.8

(END OF REPORT)