

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332768-935

Luminaire Tested: **S124DIW-S575D1340U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332768-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1340U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6155.7 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.3
10°-20°	221.9	3.6
20°-30°	326.6	5.3
30°-40°	379.6	6.2
40°-50°	379.6	6.2
50°-60°	332.1	5.4
60°-70°	246.6	4.0
70°-80°	140.1	2.3
80°-90°	44.8	0.7
90°-100°	95.2	1.5
100°-110°	282.1	4.6
110°-120°	478.8	7.8
120°-130°	631.3	10.3
130°-140°	709.0	11.5
140°-150°	696.7	11.3
150°-160°	586.0	9.5
160°-170°	389.9	6.3
170°-180°	136.5	2.2
0°-30°	627.2	10.2
0°-40°	1006.8	16.4
0°-60°	1718.5	27.9
0°-90°	2150.0	34.9
90°-120°	856.1	13.9
90°-150°	2893.2	47.0
90°-180°	4006.0	65.1
0°-180°	6155.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	15	24	31	34	6
95°	67	77	85	88	88	75
105°	260	261	266	269	272	276
115°	487	487	485	484	482	480
125°	709	709	708	706	703	632
135°	914	921	921	919	916	707
145°	1111	1115	1117	1115	1112	695
155°	1273	1273	1272	1276	1272	585
165°	1386	1382	1380	1386	1382	390
175°	1442	1436	1435	1442	1435	137
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.6	15.1	15.5	15.9	16.3	16.7	17.0	17.2	17.5	17.7	18.1
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	23.9	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1
95°	67.0	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6
97.5°	117.0	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1
100°	156.4	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3
102.5°	197.4	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1
105°	260.2	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5
107.5°	326.1	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7
110°	370.7	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.2	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5
115°	486.8	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4
117.5°	552.5	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0
120°	596.2	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2
122.5°	641.8	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2
125°	709.0	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4
127.5°	770.0	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1
130°	812.9	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7
132.5°	856.7	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7
135°	914.5	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8
137.5°	977.5	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7
140°	1019.5	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5
142.5°	1057.9	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2
145°	1111.0	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1163.7	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0
150°	1195.9	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.2	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5
155°	1272.9	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8
157.5°	1312.3	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8
160°	1335.5	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9
162.5°	1356.9	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3
165°	1385.7	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6
167.5°	1407.8	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9
170°	1420.3	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4
172.5°	1429.3	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5
175°	1441.6	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6
177.5°	1445.5	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	18.3	18.7	18.9	19.2	19.3	19.4	19.5	19.5
90°	27.6	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.0	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	86.4	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.0	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	171.9	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	209.7	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	267.3	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	329.4	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.8	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P332768-935

CATALOG NUMBER: S124DIW-S575D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.4	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	484.1	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	550.2	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	595.0	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	640.3	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	707.0	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.6	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	815.3	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	857.2	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	920.2	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	981.1	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.2	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1116.1	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.8	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.1	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1311.5	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1334.7	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1355.6	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1383.1	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1406.4	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1418.8	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1428.1	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1443.9	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)