

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332774-935

Luminaire Tested: **S124DIW-S575D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332774-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S575D1560U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6808.0 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.7	1.2
10°-20°	221.9	3.3
20°-30°	326.6	4.8
30°-40°	379.6	5.6
40°-50°	379.6	5.6
50°-60°	332.1	4.9
60°-70°	246.6	3.6
70°-80°	140.1	2.1
80°-90°	45.5	0.7
90°-100°	110.7	1.6
100°-110°	328.0	4.8
110°-120°	556.7	8.2
120°-130°	734.0	10.8
130°-140°	824.4	12.1
140°-150°	810.1	11.9
150°-160°	681.3	10.0
160°-170°	453.3	6.7
170°-180°	158.7	2.3
0°-30°	627.2	9.2
0°-40°	1006.8	14.8
0°-60°	1718.5	25.2
0°-90°	2150.7	31.6
90°-120°	995.4	14.6
90°-150°	3363.9	49.4
90°-180°	4657.0	68.4
0°-180°	6808.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	4	18	29	36	39	7
95°	78	89	99	102	102	87
105°	302	304	309	313	317	321
115°	566	566	563	562	561	558
125°	824	824	823	820	818	734
135°	1063	1071	1071	1068	1064	822
145°	1292	1297	1298	1297	1293	808
155°	1480	1480	1479	1483	1479	681
165°	1611	1607	1605	1612	1607	454
175°	1676	1670	1668	1676	1668	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.7	15.2	15.8	16.3	16.8	17.2	17.6	17.9	18.3	18.6	18.9
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	27.8	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4
95°	77.9	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5
97.5°	136.0	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0
100°	181.8	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2
102.5°	229.5	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1
105°	302.5	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9
107.5°	379.1	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2
110°	431.0	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7



TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.0	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1
115°	566.0	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2
117.5°	642.4	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6
120°	693.3	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1
122.5°	746.2	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5
125°	824.4	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5
127.5°	895.3	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5
130°	945.1	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5
132.5°	996.0	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3
135°	1063.2	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5
137.5°	1136.5	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4
140°	1185.3	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6
142.5°	1229.9	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5
145°	1291.8	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1353.1	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0
150°	1390.4	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1425.7	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6
155°	1480.0	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9
157.5°	1525.7	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0
160°	1552.7	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0
162.5°	1577.6	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5
165°	1611.1	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4
167.5°	1636.8	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4
170°	1651.4	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9
172.5°	1661.7	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5
175°	1676.0	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3
177.5°	1680.7	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	19.3	19.6	20.0	20.2	20.3	20.4	20.6	20.7
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	53.5	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	100.4	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	158.2	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	199.8	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	243.8	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	310.7	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.1	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	431.2	430.6	430.0	430.2	431.0	431.9	432.7	433.6





TEST NUMBER: P332774-935

CATALOG NUMBER: S124DIW-S575D1560U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.8	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	639.6	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	691.6	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	744.5	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.9	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	896.0	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.9	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.7	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.9	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.7	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.3	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.4	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.7	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.8	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.2	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1524.8	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1551.9	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1576.1	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1608.1	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1635.1	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1649.7	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1660.5	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1678.8	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)