

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333045-940

Luminaire Tested: **S124RDIW-S575D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333045-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1050U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5833.8 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.5
10°-20°	237.4	4.1
20°-30°	342.8	5.9
30°-40°	388.6	6.7
40°-50°	375.2	6.4
50°-60°	312.0	5.3
60°-70°	215.4	3.7
70°-80°	109.2	1.9
80°-90°	31.5	0.5
90°-100°	41.3	0.7
100°-110°	263.4	4.5
110°-120°	503.9	8.6
120°-130°	639.7	11.0
130°-140°	684.4	11.7
140°-150°	640.0	11.0
150°-160°	516.1	8.8
160°-170°	332.9	5.7
170°-180°	114.7	2.0
0°-30°	665.3	11.4
0°-40°	1053.9	18.1
0°-60°	1741.1	29.8
0°-90°	2097.2	36.0
90°-120°	808.6	13.9
90°-150°	2772.8	47.5
90°-180°	3737.0	64.1
0°-180°	5833.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	3	12	20	25	27	4
95°	50	21	20	25	26	64
105°	272	277	282	288	258	285
115°	508	510	510	511	511	499
125°	714	717	716	718	719	637
135°	885	885	888	890	892	682
145°	1021	1023	1024	1025	1026	638
155°	1119	1120	1118	1121	1118	516
165°	1181	1177	1176	1183	1175	334
175°	1208	1203	1204	1210	1201	115
180°	1208	1208	1208	1208	1208	



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.3	12.8	12.2	11.7	11.1	11.0	11.1	11.3	11.6	11.8	11.9
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	11.4	11.5	11.6	11.8	11.9	12.8	14.4	16.0	17.6	19.2	20.3
95°	49.7	42.9	36.0	29.2	22.4	19.1	19.3	19.4	19.7	19.9	21.0
97.5°	105.5	109.8	114.0	118.3	122.5	113.5	91.0	68.7	46.3	23.8	24.0
100°	148.2	151.8	155.4	159.0	162.6	150.6	122.9	95.1	67.5	39.8	36.4
102.5°	195.9	198.5	201.2	203.8	206.4	206.0	202.4	198.8	195.1	191.5	154.7
105°	272.0	273.1	274.4	275.5	276.8	277.9	278.8	279.9	280.9	281.9	283.7
107.5°	342.6	343.2	343.8	344.4	345.0	346.0	347.3	348.7	350.1	351.4	352.3
110°	390.3	390.9	391.5	392.1	392.7	393.6	394.8	396.0	397.3	398.4	398.9



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.6	437.7	438.7	439.8	440.9	441.8	442.3	442.8	443.4	444.0	443.9
115°	507.7	508.4	509.0	509.5	510.1	510.3	510.1	510.0	509.8	509.5	510.0
117.5°	571.9	572.7	573.5	574.3	575.1	575.7	576.1	576.6	577.0	577.5	577.4
120°	615.3	616.1	616.9	617.7	618.5	618.8	618.6	618.4	618.1	618.0	618.4
122.5°	655.8	656.2	656.7	657.2	657.6	658.1	658.4	658.6	658.9	659.2	659.4
125°	713.7	714.5	715.3	716.1	716.9	717.1	716.8	716.3	716.0	715.5	716.1
127.5°	768.7	768.8	769.1	769.3	769.5	770.0	771.0	771.9	772.8	773.7	773.6
130°	804.1	804.3	804.5	804.7	804.9	805.3	805.9	806.5	807.1	807.7	807.9
132.5°	836.6	837.0	837.3	837.7	838.0	838.7	839.4	840.2	840.9	841.7	841.9
135°	885.4	885.2	885.0	884.8	884.6	884.9	885.7	886.5	887.3	888.1	888.5
137.5°	928.5	928.6	928.7	928.8	928.9	929.3	930.2	931.1	932.0	932.9	933.4
140°	956.8	957.2	957.6	958.0	958.4	958.8	959.2	959.6	960.0	960.4	961.0
142.5°	982.0	982.8	983.5	984.3	985.0	985.4	985.7	985.9	986.1	986.4	986.9
145°	1020.9	1021.5	1022.1	1022.7	1023.3	1023.6	1023.6	1023.6	1023.6	1023.6	1023.9
147.5°	1051.8	1052.9	1054.1	1055.2	1056.3	1056.8	1056.6	1056.4	1056.1	1056.0	1056.1
150°	1074.2	1075.0	1075.8	1076.7	1077.5	1077.7	1077.5	1077.4	1077.1	1076.9	1076.9
152.5°	1093.0	1093.7	1094.3	1094.9	1095.6	1095.7	1095.4	1095.0	1094.7	1094.3	1094.6
155°	1119.4	1119.6	1119.8	1120.0	1120.2	1120.0	1119.4	1118.8	1118.2	1117.6	1118.4
157.5°	1141.7	1141.5	1141.4	1141.2	1141.1	1140.8	1140.1	1139.3	1138.7	1138.0	1139.1
160°	1154.6	1154.1	1153.4	1152.8	1152.2	1151.8	1151.6	1151.4	1151.2	1151.0	1152.2
162.5°	1166.2	1165.5	1164.7	1163.9	1163.1	1162.6	1162.4	1162.3	1162.1	1161.8	1163.1
165°	1180.8	1179.8	1178.8	1177.8	1176.8	1176.3	1176.3	1176.3	1176.3	1176.3	1177.9
167.5°	1192.4	1191.3	1190.3	1189.3	1188.2	1187.7	1187.5	1187.4	1187.3	1187.1	1188.9
170°	1198.9	1197.7	1196.5	1195.2	1194.1	1193.6	1193.7	1194.0	1194.2	1194.4	1196.0
172.5°	1203.2	1202.0	1200.8	1199.6	1198.4	1197.9	1198.1	1198.3	1198.5	1198.7	1200.3
175°	1207.9	1206.8	1205.5	1204.3	1203.1	1202.7	1202.8	1203.0	1203.2	1203.5	1205.2
177.5°	1210.1	1209.0	1207.8	1206.8	1205.6	1205.2	1205.5	1205.9	1206.1	1206.5	1207.7
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	11.9	12.1	12.2	12.4	12.6	12.8	13.0	13.2
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	21.6	22.7	24.0	24.6	24.7	24.8	24.9	25.0
95°	22.3	23.5	24.7	25.4	25.6	25.8	26.0	26.2
97.5°	24.1	24.3	24.3	24.5	24.7	24.9	25.1	25.3
100°	32.9	29.5	26.1	24.5	24.7	24.9	25.1	25.3
102.5°	117.9	81.1	44.2	25.9	25.9	25.9	25.9	26.0
105°	285.5	287.3	289.1	286.4	279.2	272.0	264.7	257.5
107.5°	353.2	354.1	355.0	355.8	356.6	357.3	358.1	358.8
110°	399.2	399.7	400.0	400.6	401.2	401.7	402.3	403.0



TEST NUMBER: P333045-940

CATALOG NUMBER: S124RDIW-S575D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	443.8	443.7	443.6	444.0	444.8	445.5	446.3	447.0
115°	510.3	510.8	511.1	511.4	511.4	511.4	511.4	511.4
117.5°	577.3	577.3	577.2	577.1	577.0	576.9	576.8	576.8
120°	618.8	619.2	619.6	619.6	619.2	618.8	618.4	618.0
122.5°	659.7	659.9	660.1	660.0	659.7	659.2	658.9	658.4
125°	716.8	717.4	717.9	718.4	718.5	718.7	719.0	719.2
127.5°	773.5	773.4	773.2	773.1	772.9	772.8	772.6	772.5
130°	808.1	808.3	808.5	808.6	808.6	808.6	808.6	808.6
132.5°	842.0	842.3	842.5	842.5	842.3	842.1	842.0	841.9
135°	888.9	889.3	889.7	890.1	890.6	890.9	891.4	891.7
137.5°	933.8	934.2	934.7	934.9	934.7	934.6	934.5	934.3
140°	961.6	962.2	962.8	963.2	963.4	963.6	963.8	964.0
142.5°	987.3	987.7	988.2	988.4	988.5	988.5	988.6	988.6
145°	1024.0	1024.2	1024.4	1024.8	1025.1	1025.6	1025.9	1026.4
147.5°	1056.3	1056.4	1056.6	1056.8	1057.0	1057.2	1057.4	1057.6
150°	1076.9	1076.9	1076.9	1077.0	1077.2	1077.5	1077.6	1077.8
152.5°	1094.9	1095.2	1095.6	1095.6	1095.6	1095.4	1095.3	1095.2
155°	1119.2	1120.0	1120.8	1120.9	1120.3	1119.7	1119.1	1118.5
157.5°	1140.1	1141.1	1142.2	1142.2	1141.1	1140.1	1139.1	1138.0
160°	1153.4	1154.6	1155.8	1155.8	1154.6	1153.4	1152.2	1151.0
162.5°	1164.2	1165.5	1166.6	1166.6	1165.2	1163.9	1162.5	1161.1
165°	1179.6	1181.2	1182.8	1182.6	1180.8	1179.0	1177.2	1175.4
167.5°	1190.7	1192.5	1194.2	1194.1	1192.1	1190.1	1188.1	1186.1
170°	1197.6	1199.2	1200.8	1200.6	1198.5	1196.6	1194.5	1192.6
172.5°	1201.9	1203.5	1205.1	1204.9	1202.7	1200.5	1198.4	1196.1
175°	1207.0	1208.8	1210.7	1210.3	1207.9	1205.5	1203.1	1200.7
177.5°	1209.1	1210.3	1211.7	1211.3	1209.3	1207.5	1205.5	1203.6
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9

(END OF REPORT)