

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332755-935

Luminaire Tested: **S124DIW-S575D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332755-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D770U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4791.4 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38				
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32				
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27				
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20				
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.6
10°-20°	221.9	4.6
20°-30°	326.6	6.8
30°-40°	379.6	7.9
40°-50°	379.6	7.9
50°-60°	332.1	6.9
60°-70°	246.6	5.1
70°-80°	140.1	2.9
80°-90°	42.9	0.9
90°-100°	29.2	0.6
100°-110°	186.3	3.9
110°-120°	356.5	7.4
120°-130°	452.5	9.4
130°-140°	484.2	10.1
140°-150°	452.7	9.4
150°-160°	365.1	7.6
160°-170°	235.5	4.9
170°-180°	81.2	1.7
0°-30°	627.2	13.1
0°-40°	1006.8	21.0
0°-60°	1718.5	35.9
0°-90°	2148.2	44.8
90°-120°	572.0	11.9
90°-150°	1961.4	40.9
90°-180°	2643.0	55.2
0°-180°	4791.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	2	9	14	18	19	4
95°	35	15	14	18	18	45
105°	192	196	199	204	182	201
115°	359	361	360	362	362	353
125°	505	507	506	508	509	451
135°	626	626	628	630	631	482
145°	722	724	724	725	726	451
155°	792	792	791	793	791	365
165°	835	832	832	837	832	236
175°	854	851	851	856	849	81
180°	854	854	854	854	854	



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.3	14.6	14.7	14.9	15.1	15.2	15.3	15.5	15.6	15.7	15.8
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	8.1	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4
95°	35.1	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9
97.5°	74.6	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0
100°	104.8	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7
102.5°	138.5	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4
105°	192.3	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7
107.5°	242.4	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3
110°	276.1	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.8	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0
115°	359.2	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8
117.5°	404.6	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5
120°	435.2	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5
122.5°	463.9	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5
125°	504.9	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6
127.5°	543.7	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3
130°	568.8	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5
132.5°	591.9	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6
135°	626.3	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5
137.5°	656.9	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2
140°	676.8	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8
142.5°	694.7	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1
145°	722.2	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3
147.5°	744.1	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1
150°	759.9	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8
152.5°	773.2	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3
155°	791.9	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2
157.5°	807.6	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7
160°	816.7	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1
162.5°	824.9	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8
165°	835.3	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3
167.5°	843.5	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0
170°	848.1	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0
172.5°	851.2	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1
175°	854.5	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6
177.5°	856.0	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	16.0	16.2	16.4	16.4	16.5	16.6	16.6	16.7
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	15.2	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	15.8	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.0	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	23.3	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	83.4	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	202.0	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	249.9	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.4	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P332755-935

CATALOG NUMBER: S124DIW-S575D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.0	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.7	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.0	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.2	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.6	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.6	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	628.8	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.6	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.2	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.4	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.4	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.2	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.6	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	791.7	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	823.6	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	834.4	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	842.3	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	847.1	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	850.2	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	853.9	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	855.3	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)