

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333049-940

Luminaire Tested: **S124RDIW-S575D1340U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333049-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6881.6 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	66	61	56	53	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.2
10°-20°	237.4	3.4
20°-30°	342.8	5.0
30°-40°	388.6	5.6
40°-50°	375.2	5.5
50°-60°	312.0	4.5
60°-70°	215.4	3.1
70°-80°	109.2	1.6
80°-90°	32.5	0.5
90°-100°	52.9	0.8
100°-110°	337.2	4.9
110°-120°	645.1	9.4
120°-130°	818.9	11.9
130°-140°	876.2	12.7
140°-150°	819.3	11.9
150°-160°	660.7	9.6
160°-170°	426.2	6.2
170°-180°	146.9	2.1
0°-30°	665.3	9.7
0°-40°	1053.9	15.3
0°-60°	1741.1	25.3
0°-90°	2098.2	30.5
90°-120°	1035.2	15.0
90°-150°	3549.6	51.6
90°-180°	4783.0	69.5
0°-180°	6881.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	4	16	25	32	35	5
95°	64	26	25	32	34	82
105°	348	355	361	368	330	364
115°	650	653	652	654	655	639
125°	914	918	916	919	921	815
135°	1134	1133	1137	1139	1142	873
145°	1307	1310	1310	1312	1314	816
155°	1433	1434	1431	1435	1432	660
165°	1512	1506	1506	1514	1505	427
175°	1546	1540	1541	1550	1537	147
180°	1546	1546	1546	1546	1546	



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.5	13.0	12.7	12.2	11.8	11.7	12.0	12.3	12.6	12.8	13.0
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	14.5	14.7	14.9	15.1	15.2	16.3	18.4	20.4	22.5	24.5	26.0
95°	63.6	54.8	46.1	37.4	28.6	24.4	24.7	25.0	25.1	25.4	27.0
97.5°	135.1	140.5	146.0	151.4	156.9	145.3	116.5	87.9	59.2	30.5	30.7
100°	189.7	194.3	198.9	203.6	208.2	192.8	157.3	121.8	86.3	50.9	46.5
102.5°	250.7	254.1	257.5	260.9	264.3	263.7	259.0	254.5	249.9	245.2	198.0
105°	348.1	349.6	351.2	352.8	354.3	355.7	357.0	358.3	359.5	360.9	363.2
107.5°	438.5	439.3	440.1	440.9	441.7	442.9	444.7	446.4	448.2	450.0	451.0
110°	499.6	500.4	501.2	501.9	502.7	503.9	505.4	506.9	508.5	510.1	510.6



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.8	560.3	561.7	563.0	564.5	565.4	566.2	566.9	567.7	568.4	568.3
115°	650.0	650.8	651.6	652.3	653.1	653.4	653.1	652.8	652.6	652.3	652.8
117.5°	732.1	733.2	734.1	735.2	736.2	737.0	737.6	738.2	738.7	739.3	739.2
120°	787.6	788.6	789.7	790.8	791.8	792.1	791.9	791.7	791.4	791.1	791.7
122.5°	839.5	840.1	840.7	841.3	842.0	842.4	842.8	843.1	843.5	843.8	844.2
125°	913.7	914.7	915.8	916.8	917.8	918.1	917.6	917.0	916.5	916.1	916.8
127.5°	984.0	984.3	984.5	984.8	985.1	985.8	986.9	988.1	989.4	990.5	990.3
130°	1029.4	1029.7	1029.9	1030.1	1030.4	1030.9	1031.7	1032.4	1033.2	1034.0	1034.3
132.5°	1071.0	1071.5	1071.9	1072.4	1072.8	1073.6	1074.6	1075.5	1076.5	1077.5	1077.7
135°	1133.5	1133.2	1132.9	1132.7	1132.5	1132.8	1133.8	1134.9	1136.0	1136.9	1137.5
137.5°	1188.7	1188.8	1188.9	1189.1	1189.2	1189.8	1190.9	1192.0	1193.2	1194.3	1194.9
140°	1224.9	1225.4	1225.8	1226.4	1226.9	1227.4	1227.9	1228.4	1229.0	1229.5	1230.2
142.5°	1257.2	1258.1	1259.1	1260.0	1261.0	1261.5	1261.9	1262.1	1262.5	1262.8	1263.4
145°	1307.0	1307.7	1308.5	1309.3	1310.0	1310.5	1310.5	1310.5	1310.5	1310.5	1310.7
147.5°	1346.5	1347.9	1349.4	1350.9	1352.3	1352.9	1352.6	1352.4	1352.1	1351.8	1352.0
150°	1375.2	1376.3	1377.2	1378.3	1379.3	1379.7	1379.5	1379.2	1378.9	1378.7	1378.7
152.5°	1399.3	1400.1	1400.9	1401.7	1402.6	1402.8	1402.3	1401.8	1401.3	1400.9	1401.3
155°	1433.1	1433.2	1433.5	1433.8	1434.0	1433.8	1433.1	1432.3	1431.5	1430.7	1431.7
157.5°	1461.5	1461.3	1461.2	1461.0	1460.9	1460.4	1459.5	1458.6	1457.8	1456.9	1458.2
160°	1478.1	1477.4	1476.6	1475.8	1475.1	1474.5	1474.3	1474.0	1473.7	1473.6	1475.1
162.5°	1492.9	1491.9	1491.0	1490.0	1489.1	1488.4	1488.2	1487.9	1487.6	1487.4	1488.9
165°	1511.7	1510.4	1509.1	1507.8	1506.5	1505.9	1505.9	1505.9	1505.9	1505.9	1508.0
167.5°	1526.5	1525.2	1523.8	1522.5	1521.2	1520.4	1520.3	1520.1	1519.9	1519.7	1522.1
170°	1534.8	1533.3	1531.7	1530.2	1528.7	1528.0	1528.2	1528.5	1528.7	1529.0	1531.1
172.5°	1540.3	1538.8	1537.3	1535.7	1534.2	1533.6	1533.8	1534.1	1534.3	1534.5	1536.6
175°	1546.4	1544.8	1543.3	1541.8	1540.2	1539.5	1539.8	1540.1	1540.3	1540.6	1542.9
177.5°	1549.2	1547.7	1546.2	1544.8	1543.4	1542.8	1543.3	1543.7	1544.1	1544.5	1546.1
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	13.2	13.4	13.6	13.8	14.0	14.3	14.4	14.7
90°	28.5	30.1	31.7	32.6	33.2	33.7	34.2	34.7
92.5°	27.6	29.2	30.7	31.5	31.7	31.7	31.8	31.9
95°	28.5	30.1	31.7	32.5	32.7	33.0	33.3	33.5
97.5°	30.9	31.0	31.1	31.4	31.7	31.8	32.1	32.4
100°	42.2	37.8	33.4	31.4	31.7	31.8	32.1	32.4
102.5°	151.0	103.8	56.6	33.1	33.2	33.2	33.3	33.3
105°	365.5	367.8	370.1	366.7	357.4	348.1	338.9	329.7
107.5°	452.2	453.3	454.4	455.5	456.5	457.4	458.4	459.4
110°	511.1	511.6	512.1	512.7	513.5	514.3	515.1	515.9



TEST NUMBER: P333049-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.1	568.0	567.9	568.4	569.4	570.3	571.3	572.3
115°	653.4	653.9	654.3	654.6	654.6	654.6	654.6	654.6
117.5°	739.0	739.0	738.9	738.8	738.7	738.6	738.5	738.3
120°	792.1	792.6	793.2	793.2	792.6	792.1	791.7	791.1
122.5°	844.5	844.8	845.1	845.0	844.5	843.9	843.5	842.9
125°	917.6	918.4	919.1	919.6	919.9	920.2	920.4	920.7
127.5°	990.2	990.1	989.9	989.7	989.5	989.3	989.1	988.9
130°	1034.5	1034.7	1035.0	1035.2	1035.2	1035.2	1035.2	1035.2
132.5°	1078.0	1078.3	1078.5	1078.5	1078.3	1078.2	1077.9	1077.7
135°	1138.0	1138.4	1139.0	1139.5	1140.1	1140.5	1141.0	1141.6
137.5°	1195.4	1196.0	1196.6	1196.8	1196.6	1196.5	1196.3	1196.1
140°	1231.0	1231.8	1232.5	1233.1	1233.3	1233.6	1233.9	1234.1
142.5°	1263.9	1264.4	1265.1	1265.3	1265.4	1265.4	1265.5	1265.5
145°	1310.9	1311.2	1311.4	1311.9	1312.3	1312.9	1313.4	1313.9
147.5°	1352.3	1352.5	1352.6	1352.9	1353.2	1353.4	1353.6	1353.9
150°	1378.7	1378.7	1378.7	1378.8	1379.0	1379.3	1379.6	1379.8
152.5°	1401.7	1402.1	1402.5	1402.7	1402.5	1402.3	1402.2	1402.0
155°	1432.8	1433.8	1434.9	1434.9	1434.2	1433.4	1432.6	1431.9
157.5°	1459.6	1460.9	1462.2	1462.2	1460.9	1459.6	1458.2	1456.9
160°	1476.6	1478.1	1479.7	1479.7	1478.1	1476.6	1475.1	1473.6
162.5°	1490.5	1492.0	1493.5	1493.4	1491.7	1490.0	1488.2	1486.5
165°	1510.0	1512.1	1514.1	1513.9	1511.7	1509.4	1507.1	1504.8
167.5°	1524.3	1526.5	1528.8	1528.7	1526.1	1523.5	1521.0	1518.4
170°	1533.1	1535.2	1537.2	1537.0	1534.5	1531.9	1529.3	1526.7
172.5°	1538.6	1540.8	1542.8	1542.5	1539.6	1536.9	1534.1	1531.3
175°	1545.2	1547.6	1549.9	1549.4	1546.4	1543.3	1540.2	1537.1
177.5°	1547.8	1549.4	1551.1	1550.7	1548.2	1545.8	1543.3	1540.8
180°	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.4

(END OF REPORT)