

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333050-940

Luminaire Tested: **S124RDIW-S575D1340U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333050-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6246.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.4
10°-20°	237.4	3.8
20°-30°	342.8	5.5
30°-40°	388.6	6.2
40°-50°	375.2	6.0
50°-60°	312.0	5.0
60°-70°	215.4	3.4
70°-80°	109.2	1.7
80°-90°	32.5	0.5
90°-100°	98.6	1.6
100°-110°	292.2	4.7
110°-120°	495.9	7.9
120°-130°	653.9	10.5
130°-140°	734.3	11.8
140°-150°	721.6	11.6
150°-160°	606.9	9.7
160°-170°	403.8	6.5
170°-180°	141.4	2.3
0°-30°	665.3	10.7
0°-40°	1053.9	16.9
0°-60°	1741.1	27.9
0°-90°	2098.2	33.6
90°-120°	886.7	14.2
90°-150°	2996.4	48.0
90°-180°	4149.0	66.4
0°-180°	6246.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	4	16	25	32	35	6
95°	69	80	88	91	91	77
105°	270	271	275	279	282	286
115°	504	504	502	501	500	497
125°	734	734	733	731	728	654
135°	947	954	954	952	948	732
145°	1151	1155	1156	1155	1152	720
155°	1318	1318	1317	1321	1317	606
165°	1435	1432	1429	1436	1432	404
175°	1493	1487	1486	1493	1486	142
180°	1495	1495	1495	1495	1495	



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.5	13.0	12.7	12.2	11.8	11.7	12.0	12.3	12.6	12.8	13.0
90°	3.5	6.3	9.1	11.9	14.8	17.2	19.3	21.3	23.4	25.4	27.0
92.5°	24.8	28.0	31.2	34.4	37.7	40.0	41.5	42.9	44.3	45.8	46.7
95°	69.4	71.7	74.0	76.3	78.6	80.7	82.5	84.3	86.1	87.9	88.6
97.5°	121.2	123.1	124.9	126.7	128.6	130.5	132.7	134.8	136.9	139.0	139.9
100°	161.9	162.9	164.0	165.0	166.0	167.6	170.0	172.3	174.6	176.9	177.5
102.5°	204.5	204.9	205.3	205.7	206.1	207.3	209.5	211.6	213.7	215.8	216.5
105°	269.5	269.7	270.0	270.2	270.5	271.1	272.2	273.2	274.2	275.3	276.0
107.5°	337.7	338.0	338.3	338.6	338.9	339.1	339.3	339.5	339.7	339.7	340.5
110°	384.0	384.4	385.0	385.5	386.0	386.1	385.8	385.6	385.4	385.1	384.6



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.0	432.1	432.2	432.4	432.5	432.3	431.9	431.3	430.9	430.4	430.3
115°	504.2	504.2	504.2	504.2	504.2	504.0	503.5	502.9	502.4	501.9	501.7
117.5°	572.2	572.4	572.7	572.8	573.0	572.9	572.6	572.2	571.9	571.5	570.6
120°	617.5	618.6	619.6	620.6	621.6	621.8	621.0	620.3	619.5	618.7	617.4
122.5°	664.7	665.1	665.6	665.9	666.4	666.4	666.0	665.7	665.3	664.9	664.1
125°	734.3	734.3	734.3	734.3	734.3	734.2	734.0	733.7	733.4	733.2	732.6
127.5°	797.5	798.3	799.1	799.8	800.6	800.8	800.3	800.0	799.5	799.1	798.6
130°	841.9	842.7	843.5	844.2	845.0	845.3	845.3	845.3	845.3	845.3	844.8
132.5°	887.3	887.8	888.3	888.9	889.5	889.7	889.5	889.2	889.0	888.9	888.3
135°	947.1	948.7	950.2	951.7	953.3	954.0	954.0	954.0	954.0	954.0	953.6
137.5°	1012.4	1013.1	1013.8	1014.5	1015.2	1015.8	1016.2	1016.6	1017.0	1017.4	1016.7
140°	1055.9	1056.3	1056.9	1057.4	1057.9	1058.1	1058.1	1058.1	1058.1	1058.1	1057.9
142.5°	1095.6	1096.1	1096.6	1097.2	1097.7	1097.8	1097.6	1097.4	1097.3	1097.0	1097.0
145°	1150.7	1151.7	1152.7	1153.8	1154.8	1155.4	1155.7	1155.9	1156.2	1156.5	1156.2
147.5°	1205.2	1206.5	1207.7	1209.0	1210.1	1210.7	1210.5	1210.3	1210.1	1209.9	1209.7
150°	1238.6	1239.6	1240.6	1241.6	1242.7	1243.1	1243.1	1243.1	1243.1	1243.1	1243.1
152.5°	1270.0	1270.6	1271.2	1271.8	1272.5	1272.9	1273.1	1273.3	1273.5	1273.7	1274.3
155°	1318.3	1318.3	1318.3	1318.3	1318.3	1318.2	1317.9	1317.7	1317.4	1317.2	1318.2
157.5°	1359.1	1358.6	1358.2	1357.6	1357.2	1356.9	1356.9	1356.8	1356.8	1356.7	1357.5
160°	1383.1	1382.9	1382.6	1382.3	1382.1	1381.8	1381.5	1381.3	1381.1	1380.8	1381.5
162.5°	1405.3	1404.6	1404.0	1403.3	1402.7	1402.2	1401.9	1401.7	1401.4	1401.1	1402.6
165°	1435.1	1434.4	1433.6	1432.8	1432.1	1431.5	1430.9	1430.4	1429.9	1429.3	1430.9
167.5°	1458.0	1457.0	1455.9	1454.8	1453.8	1453.2	1453.3	1453.3	1453.4	1453.4	1455.0
170°	1471.0	1469.7	1468.5	1467.1	1465.9	1465.3	1465.6	1465.9	1466.2	1466.3	1467.9
172.5°	1480.2	1479.2	1478.1	1477.0	1476.0	1475.4	1475.5	1475.5	1475.6	1475.6	1477.4
175°	1493.0	1491.7	1490.4	1489.2	1487.8	1487.0	1486.8	1486.6	1486.3	1486.0	1487.8
177.5°	1497.1	1496.1	1495.0	1494.1	1493.0	1492.5	1492.5	1492.5	1492.5	1492.5	1494.0
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	13.2	13.4	13.6	13.8	14.0	14.3	14.4	14.7
90°	28.5	30.1	31.6	32.6	33.2	33.7	34.2	34.7
92.5°	47.6	48.6	49.5	50.1	50.4	50.7	51.0	51.4
95°	89.4	90.2	91.0	91.4	91.4	91.4	91.4	91.4
97.5°	140.9	141.8	142.7	143.2	143.2	143.2	143.2	143.2
100°	178.0	178.5	179.0	179.2	179.2	179.2	179.2	179.2
102.5°	217.2	217.9	218.6	219.1	219.4	219.5	219.7	220.0
105°	276.8	277.6	278.3	279.1	279.8	280.6	281.4	282.1
107.5°	341.2	341.9	342.7	343.0	343.0	342.9	342.9	342.8
110°	384.1	383.5	383.1	383.2	384.0	384.7	385.5	386.3



TEST NUMBER: P333050-940

CATALOG NUMBER: S124RDIW-S575D1340U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	430.3	430.2	430.0	430.1	430.2	430.3	430.5	430.7
115°	501.4	501.1	500.9	500.6	500.3	500.1	499.8	499.6
117.5°	569.8	568.9	568.0	567.3	566.8	566.3	565.8	565.3
120°	616.2	614.8	613.6	613.1	613.7	614.2	614.7	615.2
122.5°	663.2	662.4	661.5	660.6	659.6	658.7	657.8	656.8
125°	732.2	731.6	731.1	730.6	730.1	729.6	729.1	728.5
127.5°	798.1	797.5	797.0	796.6	796.2	795.8	795.3	795.0
130°	844.4	843.8	843.3	842.6	841.5	840.4	839.5	838.4
132.5°	887.8	887.3	886.8	886.4	885.9	885.5	885.1	884.7
135°	953.1	952.5	952.0	951.4	950.6	949.9	949.0	948.2
137.5°	1016.1	1015.5	1014.8	1014.5	1014.7	1014.9	1014.9	1015.1
140°	1057.7	1057.4	1057.1	1056.9	1056.6	1056.3	1056.1	1055.9
142.5°	1096.9	1096.9	1096.8	1096.7	1096.7	1096.6	1096.6	1096.5
145°	1155.9	1155.7	1155.4	1154.9	1154.1	1153.3	1152.6	1151.8
147.5°	1209.4	1209.2	1209.1	1208.8	1208.5	1208.3	1208.1	1207.8
150°	1243.1	1243.1	1243.1	1243.0	1242.8	1242.5	1242.2	1242.1
152.5°	1275.0	1275.6	1276.2	1276.1	1275.5	1274.8	1274.2	1273.5
155°	1319.3	1320.3	1321.3	1321.3	1320.3	1319.3	1318.2	1317.2
157.5°	1358.3	1359.1	1359.9	1359.8	1358.9	1358.0	1357.2	1356.3
160°	1382.3	1383.1	1383.8	1383.6	1382.3	1381.1	1379.7	1378.5
162.5°	1403.9	1405.3	1406.7	1406.8	1405.4	1404.2	1402.9	1401.6
165°	1432.4	1434.0	1435.6	1435.8	1434.8	1433.7	1432.7	1431.6
167.5°	1456.5	1458.0	1459.6	1459.6	1457.9	1456.3	1454.8	1453.2
170°	1469.5	1471.0	1472.6	1472.4	1470.6	1468.8	1467.0	1465.3
172.5°	1479.1	1480.9	1482.6	1482.6	1480.8	1479.0	1477.2	1475.4
175°	1489.6	1491.4	1493.3	1493.3	1491.4	1489.6	1487.8	1486.0
177.5°	1495.4	1496.8	1498.3	1498.2	1496.6	1494.9	1493.3	1491.6
180°	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3	1495.3

(END OF REPORT)