

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333054-940

Luminaire Tested: **S124RDIW-S575D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333054-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1560U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6922.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	30
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	32	32	32	32	26
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	27	27	27	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	24	24	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	20	20	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	19	18	18	18	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	16	16	16	12
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	14	14	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	13	13	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	11	11	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.2
10°-20°	237.4	3.4
20°-30°	342.8	5.0
30°-40°	388.6	5.6
40°-50°	375.2	5.4
50°-60°	312.0	4.5
60°-70°	215.4	3.1
70°-80°	109.2	1.6
80°-90°	33.2	0.5
90°-100°	114.7	1.7
100°-110°	339.7	4.9
110°-120°	576.5	8.3
120°-130°	760.2	11.0
130°-140°	853.8	12.3
140°-150°	839.0	12.1
150°-160°	705.6	10.2
160°-170°	469.5	6.8
170°-180°	164.4	2.4
0°-30°	665.3	9.6
0°-40°	1053.9	15.2
0°-60°	1741.1	25.2
0°-90°	2098.9	30.3
90°-120°	1030.9	14.9
90°-150°	3483.9	50.3
90°-180°	4823.0	69.7
0°-180°	6922.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	4	19	30	37	40	7
95°	81	93	102	106	106	90
105°	313	315	320	324	328	332
115°	586	586	584	582	581	578
125°	854	854	852	850	847	761
135°	1101	1109	1109	1106	1102	852
145°	1338	1343	1344	1343	1339	837
155°	1533	1533	1531	1536	1531	705
165°	1669	1665	1662	1669	1665	470
175°	1736	1729	1728	1736	1728	165
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.6	13.3	12.9	12.6	12.2	12.3	12.7	13.0	13.4	13.6	13.9
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	28.8	32.5	36.3	40.0	43.9	46.5	48.2	49.9	51.5	53.2	54.3
95°	80.7	83.4	86.1	88.7	91.4	93.8	95.9	98.0	100.1	102.2	103.1
97.5°	140.9	143.0	145.2	147.4	149.5	151.9	154.3	156.7	159.2	161.6	162.6
100°	188.2	189.4	190.6	191.8	193.1	194.9	197.7	200.4	203.0	205.7	206.3
102.5°	237.7	238.2	238.7	239.2	239.6	241.1	243.5	246.0	248.4	250.9	251.7
105°	313.3	313.6	313.9	314.1	314.5	315.2	316.4	317.6	318.8	320.0	320.9
107.5°	392.6	393.0	393.3	393.7	394.0	394.3	394.5	394.7	394.8	395.0	395.8
110°	446.4	447.0	447.5	448.2	448.8	449.0	448.6	448.4	448.0	447.7	447.1



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.3	502.5	502.6	502.7	502.8	502.6	502.0	501.5	501.0	500.4	500.3
115°	586.2	586.2	586.2	586.2	586.2	585.9	585.3	584.7	584.2	583.5	583.3
117.5°	665.3	665.5	665.8	666.0	666.3	666.2	665.8	665.3	664.9	664.5	663.4
120°	718.0	719.2	720.4	721.6	722.7	722.9	722.0	721.1	720.2	719.3	717.8
122.5°	772.8	773.3	773.8	774.3	774.7	774.8	774.4	773.9	773.6	773.1	772.1
125°	853.8	853.8	853.8	853.8	853.8	853.6	853.4	853.0	852.7	852.5	851.9
127.5°	927.2	928.1	929.0	929.9	930.8	931.0	930.5	930.1	929.6	929.1	928.4
130°	978.8	979.7	980.6	981.5	982.4	982.8	982.8	982.8	982.8	982.8	982.3
132.5°	1031.5	1032.2	1032.9	1033.5	1034.2	1034.4	1034.1	1033.9	1033.7	1033.4	1032.9
135°	1101.2	1103.0	1104.7	1106.6	1108.4	1109.3	1109.3	1109.3	1109.3	1109.3	1108.7
137.5°	1177.1	1177.9	1178.7	1179.6	1180.4	1181.1	1181.5	1182.0	1182.5	1182.9	1182.1
140°	1227.6	1228.2	1228.8	1229.4	1229.9	1230.3	1230.3	1230.3	1230.3	1230.3	1229.9
142.5°	1273.8	1274.4	1275.1	1275.6	1276.2	1276.4	1276.1	1275.9	1275.7	1275.4	1275.4
145°	1337.8	1339.0	1340.2	1341.4	1342.6	1343.4	1343.6	1344.0	1344.3	1344.5	1344.3
147.5°	1401.3	1402.8	1404.2	1405.6	1407.0	1407.7	1407.4	1407.1	1406.9	1406.7	1406.4
150°	1440.0	1441.2	1442.4	1443.6	1444.8	1445.4	1445.4	1445.4	1445.4	1445.4	1445.4
152.5°	1476.6	1477.3	1478.0	1478.7	1479.4	1480.0	1480.2	1480.4	1480.7	1480.9	1481.6
155°	1532.8	1532.8	1532.8	1532.8	1532.8	1532.7	1532.3	1532.0	1531.8	1531.4	1532.7
157.5°	1580.1	1579.6	1579.0	1578.5	1578.0	1577.7	1577.6	1577.5	1577.5	1577.4	1578.3
160°	1608.1	1607.8	1607.5	1607.2	1606.9	1606.6	1606.3	1606.0	1605.7	1605.4	1606.3
162.5°	1633.9	1633.2	1632.4	1631.6	1630.8	1630.2	1630.0	1629.7	1629.3	1629.1	1630.7
165°	1668.6	1667.7	1666.8	1665.9	1665.0	1664.3	1663.7	1663.0	1662.5	1661.9	1663.7
167.5°	1695.2	1694.0	1692.7	1691.5	1690.2	1689.6	1689.7	1689.7	1689.8	1689.9	1691.7
170°	1710.3	1708.8	1707.3	1705.8	1704.3	1703.7	1704.0	1704.3	1704.6	1704.9	1706.6
172.5°	1721.0	1719.8	1718.5	1717.3	1716.0	1715.4	1715.5	1715.6	1715.6	1715.7	1717.7
175°	1735.8	1734.3	1732.9	1731.3	1729.8	1728.9	1728.7	1728.3	1728.0	1727.8	1729.8
177.5°	1740.6	1739.5	1738.3	1737.1	1735.9	1735.3	1735.3	1735.3	1735.3	1735.3	1737.0
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	14.2	14.4	14.6	14.9	15.1	15.3	15.6	15.9
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	55.4	56.4	57.5	58.2	58.6	58.9	59.3	59.7
95°	104.0	104.9	105.8	106.2	106.2	106.2	106.2	106.2
97.5°	163.8	164.9	165.9	166.5	166.5	166.5	166.5	166.5
100°	206.9	207.5	208.1	208.4	208.4	208.4	208.4	208.4
102.5°	252.5	253.4	254.2	254.8	255.0	255.3	255.5	255.7
105°	321.8	322.7	323.6	324.5	325.4	326.3	327.2	328.1
107.5°	396.7	397.5	398.4	398.8	398.7	398.7	398.6	398.5
110°	446.6	445.9	445.3	445.5	446.4	447.3	448.2	449.1



TEST NUMBER: P333054-940

CATALOG NUMBER: S124RDIW-S575D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.2	500.1	500.0	500.0	500.2	500.3	500.5	500.7
115°	582.9	582.6	582.4	582.0	581.8	581.5	581.1	580.9
117.5°	662.5	661.5	660.4	659.6	659.0	658.4	657.8	657.2
120°	716.3	714.9	713.4	712.9	713.5	714.1	714.7	715.3
122.5°	771.1	770.1	769.1	768.0	767.0	765.9	764.8	763.8
125°	851.2	850.7	850.1	849.4	848.8	848.3	847.7	847.0
127.5°	927.9	927.3	926.7	926.1	925.7	925.2	924.7	924.3
130°	981.7	981.1	980.4	979.5	978.4	977.2	976.0	974.8
132.5°	1032.2	1031.6	1031.0	1030.5	1030.0	1029.6	1029.0	1028.6
135°	1108.0	1107.5	1106.9	1106.1	1105.2	1104.3	1103.4	1102.5
137.5°	1181.4	1180.6	1179.8	1179.6	1179.7	1179.9	1180.1	1180.3
140°	1229.7	1229.4	1229.0	1228.8	1228.5	1228.2	1227.9	1227.6
142.5°	1275.3	1275.2	1275.2	1275.1	1275.1	1275.1	1275.0	1274.9
145°	1344.0	1343.6	1343.4	1342.7	1341.8	1341.0	1340.1	1339.2
147.5°	1406.2	1406.0	1405.7	1405.4	1405.2	1404.9	1404.5	1404.3
150°	1445.4	1445.4	1445.4	1445.3	1444.9	1444.7	1444.4	1444.0
152.5°	1482.3	1483.0	1483.7	1483.7	1482.9	1482.2	1481.4	1480.6
155°	1533.8	1535.0	1536.2	1536.2	1535.0	1533.8	1532.7	1531.4
157.5°	1579.2	1580.1	1581.0	1580.9	1579.9	1579.0	1577.9	1576.9
160°	1607.2	1608.1	1609.0	1608.6	1607.2	1605.7	1604.2	1602.7
162.5°	1632.3	1633.9	1635.5	1635.6	1634.1	1632.6	1631.1	1629.6
165°	1665.4	1667.2	1669.0	1669.4	1668.1	1667.0	1665.7	1664.6
167.5°	1693.4	1695.2	1697.0	1697.0	1695.1	1693.3	1691.4	1689.5
170°	1708.5	1710.3	1712.1	1711.9	1709.9	1707.7	1705.7	1703.5
172.5°	1719.8	1721.7	1723.8	1723.8	1721.6	1719.6	1717.4	1715.4
175°	1732.0	1734.0	1736.2	1736.2	1734.0	1732.0	1729.8	1727.8
177.5°	1738.7	1740.3	1742.0	1741.9	1739.9	1738.0	1736.2	1734.2
180°	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5	1738.5

(END OF REPORT)