

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333038-940

Luminaire Tested: **S124RDIW-S575D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333038-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3544.8 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	2.4
10°-20°	237.4	6.7
20°-30°	342.8	9.7
30°-40°	388.6	11.0
40°-50°	375.2	10.6
50°-60°	312.0	8.8
60°-70°	215.4	6.1
70°-80°	109.2	3.1
80°-90°	29.6	0.8
90°-100°	34.5	1.0
100°-110°	102.1	2.9
110°-120°	173.3	4.9
120°-130°	228.5	6.4
130°-140°	256.6	7.2
140°-150°	252.1	7.1
150°-160°	212.1	6.0
160°-170°	141.1	4.0
170°-180°	49.4	1.4
0°-30°	665.3	18.8
0°-40°	1053.9	29.7
0°-60°	1741.1	49.1
0°-90°	2095.3	59.1
90°-120°	309.8	8.7
90°-150°	1047.0	29.5
90°-180°	1450.0	40.9
0°-180°	3544.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	1	6	9	11	12	3
95°	24	28	31	32	32	27
105°	94	95	96	97	99	100
115°	176	176	175	175	175	174
125°	256	256	256	255	255	229
135°	331	333	333	332	331	256
145°	402	404	404	404	402	252
155°	461	461	460	462	460	212
165°	501	500	499	502	500	141
175°	522	520	519	522	519	49
180°	522	522	522	522	522	



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.0	12.2	11.4	10.6	9.8	9.5	9.5	9.5	9.5	9.5	9.5
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	8.6	9.8	10.9	12.0	13.2	14.0	14.5	15.0	15.5	16.0	16.3
95°	24.3	25.1	25.9	26.7	27.5	28.2	28.8	29.4	30.1	30.7	30.9
97.5°	42.4	43.0	43.6	44.3	44.9	45.7	46.4	47.1	47.8	48.6	48.9
100°	56.5	56.9	57.2	57.6	58.1	58.6	59.4	60.2	61.0	61.8	62.0
102.5°	71.4	71.6	71.7	71.9	72.1	72.5	73.2	73.9	74.6	75.4	75.6
105°	94.2	94.3	94.3	94.4	94.5	94.7	95.1	95.4	95.8	96.1	96.4
107.5°	118.0	118.1	118.2	118.3	118.4	118.5	118.6	118.6	118.7	118.7	119.0
110°	134.1	134.3	134.5	134.6	134.8	134.9	134.8	134.7	134.6	134.6	134.4



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	151.0	151.0	151.1	151.1	151.1	151.1	150.9	150.7	150.5	150.4	150.3
115°	176.2	176.2	176.2	176.2	176.2	176.1	175.9	175.8	175.6	175.4	175.3
117.5°	199.9	200.0	200.1	200.2	200.2	200.2	200.1	199.9	199.8	199.7	199.4
120°	215.8	216.2	216.5	216.9	217.2	217.2	217.0	216.7	216.4	216.2	215.7
122.5°	232.3	232.4	232.6	232.6	232.8	232.8	232.7	232.6	232.5	232.4	232.0
125°	256.5	256.5	256.5	256.5	256.5	256.5	256.5	256.4	256.3	256.2	256.0
127.5°	278.7	278.9	279.2	279.5	279.7	279.8	279.6	279.5	279.4	279.2	279.0
130°	294.2	294.4	294.7	295.0	295.2	295.3	295.3	295.3	295.3	295.3	295.2
132.5°	310.0	310.2	310.4	310.6	310.8	310.9	310.8	310.7	310.7	310.6	310.4
135°	330.9	331.4	332.0	332.5	333.1	333.3	333.3	333.3	333.3	333.3	333.1
137.5°	353.7	354.0	354.2	354.5	354.7	354.9	355.1	355.3	355.3	355.5	355.3
140°	368.9	369.1	369.3	369.4	369.6	369.7	369.7	369.7	369.7	369.7	369.6
142.5°	382.8	383.0	383.2	383.3	383.5	383.6	383.5	383.4	383.3	383.3	383.3
145°	402.1	402.4	402.8	403.1	403.5	403.7	403.8	403.9	403.9	404.0	403.9
147.5°	421.2	421.5	422.0	422.4	422.8	423.0	422.9	422.8	422.8	422.8	422.7
150°	432.7	433.1	433.5	433.8	434.2	434.4	434.4	434.4	434.4	434.4	434.4
152.5°	443.7	444.0	444.2	444.4	444.6	444.8	444.8	444.9	445.0	445.1	445.2
155°	460.7	460.7	460.7	460.7	460.7	460.6	460.5	460.4	460.3	460.2	460.6
157.5°	474.8	474.7	474.6	474.4	474.2	474.1	474.1	474.1	474.0	474.0	474.3
160°	483.3	483.2	483.1	483.0	483.0	482.9	482.8	482.7	482.6	482.5	482.8
162.5°	491.1	490.8	490.5	490.4	490.1	489.9	489.8	489.7	489.6	489.5	490.1
165°	501.4	501.1	500.9	500.6	500.3	500.2	500.0	499.8	499.6	499.4	500.0
167.5°	509.4	509.1	508.7	508.4	507.9	507.7	507.7	507.8	507.8	507.8	508.4
170°	514.0	513.5	513.1	512.6	512.2	512.0	512.1	512.2	512.3	512.4	512.9
172.5°	517.2	516.8	516.5	516.1	515.7	515.5	515.5	515.6	515.6	515.6	516.2
175°	521.7	521.2	520.8	520.3	519.9	519.6	519.5	519.4	519.3	519.2	519.9
177.5°	523.1	522.7	522.4	522.0	521.7	521.5	521.5	521.5	521.5	521.5	522.0
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	9.5	9.5	9.5	9.5	9.7	9.9	10.1	10.2
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.7	16.9	17.3	17.5	17.7	17.7	17.8	17.9
95°	31.2	31.5	31.7	31.9	31.9	31.9	31.9	31.9
97.5°	49.2	49.6	49.8	50.0	50.0	50.0	50.0	50.0
100°	62.2	62.3	62.5	62.6	62.6	62.6	62.6	62.6
102.5°	75.9	76.2	76.4	76.6	76.6	76.7	76.8	76.9
105°	96.8	97.0	97.3	97.6	97.8	98.1	98.4	98.6
107.5°	119.2	119.5	119.8	119.8	119.8	119.8	119.8	119.8
110°	134.2	134.0	133.8	133.8	134.1	134.4	134.6	134.9



TEST NUMBER: P333038-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	150.3	150.3	150.3	150.3	150.3	150.3	150.4	150.4
115°	175.2	175.1	175.0	175.0	174.9	174.8	174.7	174.6
117.5°	199.1	198.8	198.5	198.2	198.0	197.9	197.7	197.5
120°	215.3	214.8	214.4	214.3	214.5	214.6	214.8	215.0
122.5°	231.8	231.4	231.1	230.8	230.5	230.2	229.8	229.5
125°	255.8	255.7	255.5	255.3	255.1	254.9	254.8	254.6
127.5°	278.8	278.7	278.5	278.3	278.2	278.0	277.9	277.8
130°	295.0	294.8	294.6	294.4	294.0	293.6	293.3	292.9
132.5°	310.2	310.0	309.9	309.7	309.5	309.4	309.2	309.2
135°	333.0	332.8	332.6	332.4	332.2	331.9	331.6	331.4
137.5°	355.0	354.8	354.5	354.5	354.5	354.5	354.6	354.7
140°	369.5	369.4	369.3	369.3	369.2	369.1	369.0	368.9
142.5°	383.3	383.3	383.3	383.2	383.2	383.2	383.2	383.2
145°	403.9	403.8	403.7	403.5	403.2	403.0	402.7	402.4
147.5°	422.6	422.5	422.5	422.4	422.3	422.2	422.1	422.0
150°	434.4	434.4	434.4	434.4	434.3	434.2	434.1	434.0
152.5°	445.5	445.7	445.9	445.9	445.7	445.4	445.2	445.0
155°	460.9	461.3	461.6	461.6	461.3	460.9	460.6	460.2
157.5°	474.6	474.8	475.1	475.1	474.8	474.5	474.2	473.9
160°	483.0	483.3	483.6	483.5	483.0	482.6	482.1	481.6
162.5°	490.5	491.1	491.5	491.5	491.1	490.6	490.2	489.7
165°	500.5	501.1	501.6	501.7	501.3	501.0	500.6	500.2
167.5°	508.9	509.4	510.0	510.0	509.4	508.9	508.3	507.7
170°	513.4	514.0	514.5	514.4	513.8	513.2	512.6	511.9
172.5°	516.8	517.5	518.0	518.0	517.4	516.7	516.1	515.5
175°	520.5	521.1	521.7	521.7	521.1	520.5	519.9	519.2
177.5°	522.5	523.0	523.5	523.4	522.9	522.4	521.7	521.2
180°	522.5	522.5	522.5	522.5	522.5	522.5	522.5	522.5

(END OF REPORT)